

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




—, — .

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			C1	REVISED PER ECR-11-001036	21JAN11	HMR GJ

- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS,
BREAKS MAY BE PRESENT.
- 2
- WIRE RANGE FOR NEW APPLICATIONS : 1.27–2.38mm²
[2500–4700 CMA](WIRE RANGE APPROVED FOR APPLICATIONS
IMPLEMENTED PRIOR TO 2005: 2000–5300 CMA).
- 3
- CRIMP WIDTH: 3.05[.120] F TYPE.
CRIMP HEIGHT IN INCHES (±.002)=(TOTAL CMA OF
WIRES +12240)/220000.



40868

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 18OCT2004	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK G.D. PORTA 18OCT2004				
		APVD G.D. PORTA 18OCT2004	NAME SPLICE			
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± 1° 0'	PRODUCT SPEC —	SIZE A3 CAGE CODE 00779 DRAWING NO C-40868 RESTRICTED TO —			
		APPLICATION SPEC 114-2088				
MATERIAL BRASS	FINISH TIN	WEIGHT —	CUSTOMER DRAWING			
		SCALE 10:1		SHEET 1 OF 1		REV C1