

156-00072



Article Number: 156-00072

Heavy Duty Fir Tree with Cable Tie, 9" Length, Mount Hole Dia .04"-.62", PA66HIRHSUV, Black, 100/pkg

RoHS

Download drawing

Download spec sheet

Base Data

Local Order Number	156-00072
Type	WSSFT9B
Color	Black (BK)
Features and Benefits	• The “H” profile provides a broad surface contact to minimize the pinching of bundles. • Heavy duty fir tree mounts are equipped with a friction tab that will hold the tie in the mount, allowing them to be preassembled prior to installation. • Designed specifically for HellermannTyton 120 - 250 lb. cable ties for heavy duty applications.
Product Description	HellermannTyton heavy duty fir tree mounts are designed with heavy duty applications in mind. These are optimized for up to 3 to 1 extraction versus insertion force to make assembly fast and easy. These mounts are sold as an assembly with a cable tie.
Short Description	Heavy Duty Fir Tree with Cable Tie, 9" Length, Mount Hole Dia .04"-.62", PA66HIRHSUV, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	120.0 lbs
Minimum Tensile Strength (Metric)	534 N
Length L (Imperial)	9.0 "
Length L (Metric)	228.0 mm
Fixation Method	Fir Tree
Identification Plate Position	none
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5 "
Width W (Metric)	12.7 mm
Width W2 (Imperial)	0.51 "
Width W2 (Metric)	13.0 mm
Height H (Imperial)	1.1 "
Height H (Metric)	28.5 mm
Height H2 (Imperial)	0.73 "
Height H2 (Metric)	18.4 mm
Bundle Diameter Max. (Imperial)	2.3 "
Bundle Diameter Max. (Metric)	57.0 mm
Disc Diameter (Imperial)	0.9 "
Disc Diameter (Metric)	21.6 mm
Panel Thickness Max. (Imperial)	0.62 "

Panel Thickness Max. (Metric)	15.8 mm		
Panel Thickness Min. (Imperial)	0.04 "		
Panel Thickness Min. (Metric)	1.0 mm		
Mounting Hole Diameter D (Metric)	8.75 - 9.25 mm		
Mounting Hole Diameter D Min. (Imperial)	0.34 "	Mounting Hole Diameter D Max. (Imperial)	0.36 "
		Mounting Hole Diameter D Max. (Metric)	9.25 mm
Mounting Hole Diameter D Min. (Metric)			8.75 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100
Carton Quantity	500

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB
Operating Temperature	-65°F to +212°F (-54°C to +100°C)
ROHS Compliant	Yes