


# MCY97 Series Reed Relays




## General Specifications

Contact Characteristics		Units	MCY97-380S-5D	MCY97-38CS-5D
Contact Materials	-	-	Rhodium	
Current rating	-	A	0.5	
Switching Voltage	-	V	120	
		V	200	
Minimum Switching Requirement	Minimum	mA	10	
Coil Characteristics				
Operating Range	% of Nominal	-	80% to 110%	
Average Consumption	-	W	0.29	
Drop-out Voltage Threshold	-	-	10%	
Performance Characteristics				
Electrical Life	Operations at Rated Current (Resistive)	-	50,000,000	
Mechanical Life	Unpowered	-	100,000,000	
Operating Time (Response Time)	-	ms	0.45	
Rated insulation Voltage	Between Coil and Contact	V	500	
Dielectric strength	Between Poles	V	500	
rms Voltage	Between Contacts	V	150	
Environment				
Ambient Air Temperature	Storage	°C	-40 to +85	
Around the Device	Operation	°C	-40 to +55	
Vibration Resistance	Operational	g-n	20, 10-200 Hz	
Shock Resistance	-	g-n	50	
Weight	-	grams	1	


# MCY97 Series Reed Relays



## MCY97-380S-5D, MCY97-38CS-5D



Drawing enlarged to 200% of actual size.



When spacing MCY97 relays, the relays require 1/2 inch spacing from the side of the adjacent relay

Dimensions : Inches (Millimetres)



MCY97-360D-5D  
MCY97-380D-12D  
MCY97-38CD-5D

## General Specifications

Contact Characteristics		Units	MCY97-360D-5D	MCY97-380D-12D	MCY97-38CD-5D
Contact Materials	-	-	Rhodium	Rhodium	
Current rating	-	A	0.5	0.5	
Switching Voltage	-	V	120	60	
		V	100	100	
Minimum Switching Requirement	Minimum	mA	10	10	
Coil Characteristics					
Operating Range	% of Nominal	-	80% to 110%	80% to 110%	
Average Consumption	-	W	0.29	0.29	
Drop-out Voltage Threshold	-	-	10%	10%	
Performance Characteristics					
Electrical Life	Operations at Rated Current (Resistive)	-	50,000,000	50,000,000	
Mechanical Life	Unpowered	-	100,000,000	100,000,000	
Operating Time (Response Time)	-	ms	1	1	




# MCY97 Series Reed Relays



## General Specifications

Performance Characteristics		Units	MCY97-360D-5D	MCY97-380D-12D	MCY97-38CD-5D
Rated insulation Voltage	Between Coil and Contact	V	1,000	1,000	
Dielectric strength	Between Poles	V	1,000	1,000	
rms Voltage	Between Contacts	V	200	200	
Environment					
Ambient Air Temperature	Storage	°C	-40 to +85	-40 to +85	
Around the Device	Operation		-40 to +55	-40 to +55	
Vibration Resistance	Operational	g-n	20, 10-200 Hz	20, 10-200 Hz	
Shock Resistance	-	g-n	50	50	
Weight	-	grams	1	1	

### MCY97-360D-5D, MCY97-380D-12D, MCY97-38CD-5D



Dimensions : Inches (Millimetres)

Drawing enlarged to 200% of actual size.


## Specification Table

Nominal Input Voltage	Nominal Coil Resistance ( $\Omega$ )	Contact Configuration	Figure	Part Number
5 V dc	500 $\Omega$	SPST-NO	A	MCY97-380S-5D
5 V dc	500 $\Omega$	SPST-NO w / Clamping Diode	B	MCY97-38CS-5D
5 V dc	500 $\Omega$	DPST-NO	E	MCY97-360D-5D
12 V dc	1,000 $\Omega$	SPST-NO	C	MCY97-380D-12D
5 V dc	500 $\Omega$	SPST-NO w / Clamping Diode	D	MCY97-38CD-5D


# MCY97 Series Reed Relays




## Wiring Diagrams Top View




**Figure A**  
SPST-NO without diode




**Figure B**  
SPDT-NO with diode



**Figure C**  
SPST-NO without diode




**Figure D**  
SPDT-NO with diode




**Figure E**  
DPST-NO without diode

**MCY97-380S-5D, MCY97-38CS-5D**  
Circuit board pin spacing  
Viewed from component side  
(Top View)



0.1 in grid  
(2.54 mm)

**MCY97-360D-5D, MCY97-380D-12D, MCY97-38CD-5D**  
Circuit board pin spacing  
Viewed from component side  
(Top View)



Circuit board pin spacing enlarged to 200% of actual size

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

