

MODEL NO: 17-215UGC/TR8  
**0.8mm Height Flat Top LEDs**

Device Number : DSE-175-003 REV. 1.3

ECN : ----- Page: 1/8

### ■ Features :

- Package in 8mm tape on 7" diameter reel .
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.


### ■ Descriptions :

- The 17-215 SMD Taping is much smaller than leaded components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, light Weight makes them ideal for miniature application, etc.

### ■ Applications :

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

### ■ Package Dimensions :



### ■ Notes :

Tolerances Unless Dimension  $\pm$   
0.1mm  
Angle  $\pm$  0.5°

PART NO	CHIP		Lens	Color
	Material	Emitted Color		
17-215UGC/TR8	GaP	Super Green	Water	Clear

Office: NO. 25, Lane 76, Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL: 886-2-2267-2000, 2267-9936

FAX: 886-2-2267-6244, 2267-6189, 2267-6306



<http://www.everlight.com>

MODEL NO: 17-215UGC/TR8  
**0.8mm Height Flat Top LEDs**


Device Number : DSE-175-003 REV. 1.3

ECN : ----- Page: 2/8

### ■ Package Dimensions :



### ■ Loaded quantity per reel 3000 pcs/reel :



TOLERANCES UNLESS DIMENSION ± 0.1  
ANGLE ± 0.5  
UNIT:mm



MODEL NO: 17-215UGC/TR8

Device Number : DSE-175-003 REV. 1.3

**0.8mm Height Flat Top LEDs**

ECN : Page: 3/8

**■ Absolute Maximum Ratings at Ta = 25°C**

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	30	mA
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +90	°C
Soldering Temperature	Tsol	260 (for 5 second)	°C
Power Dissipation	Pd	100	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

**■ Electronic Optical Characteristics :**

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous intensity	Iv	8.5	14.5	-----	mcd	If=20mA
Viewing Angle	2θ 1/2	-----	130	-----	deg	If=20mA
Peak Wavelength	λ p	-----	570	-----	nm	If=20mA
Dominant Wavelength	λ d	-----	571	-----	nm	If=20mA
Spectrum Radiation Bandwidth	△λ	-----	30	-----	nm	If=20mA
Forward Voltage	Vf	1.7	2.1	2.4	V	If=20mA
Reverse Current	Ir	-----	-----	10	μA	Vr=5V



EVERLIGHT ELECTRONICS CO.,LTD.

MODEL NO: 17-215UGC/TR8

Device Number : DSE-175-003 REV. 1.3

**0.8mm Height Flat Top LEDs**

ECN : Page: 4/8

## ■ Reliability Test Item And Condition

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 Pcs	0/1
2	Temperature Cycle	H : +85°C 30min ↓ 5 min L : -55°C 30min	50 CYCLE	76 Pcs	0/1
3	Thermal Shock	H : +100°C 5min ↓ 10 sec L : -10°C 5min	50 CYCLE	76 Pcs	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 Pcs	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 Pcs	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 Pcs	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 Pcs	0/1







MODEL NO: 17-215UGC/TR8

Device Number : DSE-175-003 REV. 1.3

**0.8mm Height Flat Top LEDs**

ECN :

Page: 5/8

**Typical Electro-Optical Characteristic Curves**


MODEL NO: 17-215UGC/TR8

Device Number : DSE-175-003 REV. 1.3

**0.8mm Height Flat Top LEDs**

ECN :

Page: 6/8

**■ Test Circuit****■ Precautions For Use****1. Over-current-proof**

Customer must apply resistors for protection , otherwise slight voltage shift will cause big current change ( Burn out will happen ).

**2. Storage time**

2.1 The operation of temperature and R.H. are :  $5^{\circ}\text{C} \sim 35^{\circ}\text{C}$  , R.H.60%.

2.2 Once the package is opened, the products should be used within a week.

Otherwise, they should be keeping in a damp-proof box with desiccants.

Considering the tape life , we suggest our customers to use our products within a year(from production date).

2.3 If opened more than one week in an atmosphere  $5^{\circ}\text{C} \sim 35^{\circ}\text{C}$  , R.H.60%, they should be treated at  $60^{\circ}\text{C} \pm 5^{\circ}\text{C}$  for 15hrs.

2.4 When you discover that the desiccant in the package has a pink color (normal = blue) , you should treat them in the same conditions as 2.3.


MODEL NO: 17-215UGC/TR8  
***0.8mm Height Flat Top LEDs***

Device Number : DSE-175-003 REV. 1.3

ECN : ----- Page: 7/8

### ■ Soldering heat reliability ( DIP )

Please refer to the following figure :




### ■ Soldering Iron

Basic spec is  $\leq 5$  sec when  $260^{\circ}\text{C}$ . If temperature is higher, time should be shorter ( $+10^{\circ}\text{C} \rightarrow -1\text{sec}$ ). Power dissipation of iron should be smaller than 15 W, and temperature should be controllable. Surface temperature of the device should be under  $230^{\circ}\text{C}$ .

### ■ Rework

1. Customer must finish rework within 5 sec under  $260^{\circ}\text{C}$ .
2. The head of iron can not touch copper foil.
3. Twin-head type is preferred.



MODEL NO: 17-215UGC/TR8  
***0.8mm Height Flat Top LEDs***

Device Number : DSE-175-003 REV. 1.3

ECN : ..... Page: 8/8

■ Reflow Temp / Time :

