




NOTES


1. ROHS COMPLIANT.
2. UL 94-HB FLAMMABILITY RATING.
3. -40°C TO 85°C OPERATING TEMPERATURE.
4. SUITABLE FOR LIGHT PIPE WITH Ø2.2MM JACKET AND OPTICAL CORE NO GREATER THAN Ø1.5MM.
5. DO NOT WAVE SOLDER WITH THIS DEVICE.
6. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDS WITH OUTPUT POWER GREATER THAN 100mcd.




REVISIONS					
ECN #	REV.	DESCRIPTION	DATE	INITIALS	CHK'D
388	000	INITIAL RELEASE	1/4/12	KH	AZ
404	001	REVISED PER ECR 020612KH01	2/6/12	KH	AZ




SECTION A-A
SCALE 4 : 1



LIGHT PIPE PREPARATION
AND SEQUENCE OF ASSEMBLY



LIGHT PIPE
AS ASSEMBLED



RECOMMENDED PWB
DEVICE LAYOUT

DIMENSION STYLE: INCHES / MM GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
INCHES		DRAWN		1/4/12	
X		CHECKED		1/10/12	
XX		MATERIAL		NYLON 6/6, BLACK UL 94-HB	
XXX		FINISH		SEE NOTES	
ANGLE 1/2		DO NOT SCALE DRAWING		SCALE: 5:1	
THIRD ANGLE PROJECTION		TITLE:		MOUNT, 5mm THROUGH- HOLE LED	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC IS PROHIBITED.		SIZE		DWG. NO.	
		B		THR 5 22	
		REV		001	
		SHEET 1 OF 1			

VCC OPTOELECTRONICS
190 BOSSTICK BLVD. SUITE 101 SAN MARCOS, CA 92069 U.S.A.
PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vccsite.com