




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



CIRCUIT



MOUNTING HARDWARE



NOTES:

MATERIALS:

BUSHING - TIN PLATED STEEL

LEAD - SOLDER PLATED COPPER

NUT - TIN PLATED BRASS

L'WASHER - TIN PLATED PHOSPHOR BRONZE

MOUNTING TORQUE: 8 lb - ins. max

SEAL TESTED PER MIL-STD-202

METHOD 112 CONDITION A.

VOLTAGE DROP 0.15 VDC MAX.

MAX. SOLDER TEMPERATURE 500°F

REF. Cx (μF)	WVDC 125°C	CURRENT DC	DWV	IR MIN.	MIN. NO LOAD INSERTION LOSS (dB) PER MIL-STD 220 @ +25°C					
					30 KHz	150 KHz	300 KHz	1 MHz	10 MHz	1GHz
1.2	50	15 A	200 VDC 60 SEC.	10 GΩ	15	28	33	44	60	70

X-2015 Rev-0	REVISION RECORD		REVISED NOTES, ADDED IR, DWV, MOUNTING HARDWARE, PROJECTION, DELETED NUT & WASHER. SHOW AS HERMETIC & DIM .385 WAS .375. S.M. 07-22-02	1	20020716-7-01	--TOLERANCES-- Unless Otherwise Specified		Title MIL-15733/49-0007 COAXIAL BROADBAND - "L"	
	Original Release					DECIMAL ±			
	C.O. 19990712-7-01					ANGLES ±			
						TUSONIX TUCSON, ARIZONA			
						A			
						4601-500			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4601-500](#)