

8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION 19	
© COPYRIGHT 2000		ALL RIGHTS RESERVED.	

2				1			
LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

[illegible]

SEE APPLICATION SPEC. 114-18464
siehe Verarbeitungsspez. 114-18464

7- VARIANTS FOR NEW APPLICATIONS

NOTES


Bemerkungen

- 4 ONLY FOR FLR-WIRE SEE DIN 72551, PART 6
AND AWG WIRE ACCORDING DC-SPEC:
MS-8288 ; MS-7889 ; MS-9532
Nur fuer FLR-Leitung nach DIN 72551, Teil 6
und AWG Leitung nach DC-SPEC:
MS-8288 ; MS-7889 ; MS-9532
- 5 PRE TIN SnAg 1.0 TO 3.0µm
Vorverzinkt SnAg 1.0 bis 3.0µm
- 6 SPRING GOLD PLATED MIN. 0.8µm (only contact area)
Kontaktfeder galv. vergoldet min.0.8µm (nur Kontaktzone)
- 7 SPRING SILVER PLATED 2.0 TO 5.0µm (only contact area)
Kontaktfeder galv. versilbert 2.0 bis 5.0µm (nur Kontaktzone)
- 8 BODY PRE TIN Sn 1.0 TO 3.0µm
Kontaktkoerper vorverzinkt Sn 1.0 bis 3.0µm
- 9 REINFORCED WIRE ACCORDING TO LV 112-4
Zugverstaerkte Leitung nach LV 112-4

[illegible]

SEE APPLICATION SPEC. 114-18464
siehe Verarbeitungsspez. 114-18464

0- VARIANTS SUPERSEDED BY 7- VARIANTS (SEE TABLE ON TOP)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG E. Horn 11NOV2011 CHK R. Meier 11NOV2011 APP'D V. Seigel 11NOV2011		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: h-PLC ±0.2 k-PLC ±0.2 k-PLC ±0.2 k-PLC ±0.2 ANGLES ±1° FINISH		NAME MCON 1.2 LL (LOCKING-LANCE)	
		PRODUCT SPEC 108-18782 APPLICATION SPEC 116-18646 WEIGHT -		SIZE CASE CODE DRAWING NO A1 00779 C-1452674 RESTRICTED TO -	
MATERIAL -		Customer Drawing		SCALE - SHEET 2 of 2 REV C	