

Surface mount type TPC Series

RoHS compliance, Halogen free
Low profile: 1.1mm (B1)

Specifications

Items	Condition			Specifications			
Rated voltage (V)	—			6.3	8.0	10	12.5
Surge voltage (V)	—			7.2	9.2	12	14
Category temperature range (°C)	—			-55 to +105			
Capacitance tolerance (%)	120Hz/20°C			M : ±20			
Rated capacitance range (μF)	120Hz/20°C			10 to 470			
Dissipation Factor (DF)	120Hz/20°C			Please see the attached characteristics list			
Leakage current	Rated voltage applied, after 5 minutes			Please see the attached characteristics list			
Equivalent series resistance (ESR)	100kHz/+20°C			Please see the attached characteristics list			
Characteristics of impedance ratio at high temp. and low temp.	100kHz/20°C	-55°C	Z/Z _{20°C}	0.6 to 2.0			
		+105°C	Z/Z _{20°C}	0.6 to 2.0			
Endurance	105°C, 2,000h B2 size :105°C, 1,000h. Rated voltage applied ※Rated temp. 85°C products: 85°C, 1,000h, rated voltage applied	ΔC/C	Within±20% of the initial value				
		DF	≤ 1.5 times of the initial limit				
		LC	Within the initial limit				
Damp heat (Steady State)	60°C, 90 to 95%RH, 500h, No-applied voltage	ΔC/C	Within+40%, -20% of the initial value				
		DF	≤ 1.5 times of the initial limit				
		LC	≤ 3 times of the initial limit				
Surge	105°C, 1,000 cycles, 1kΩdischarge resistance, surge voltage applied ※Rated temp. 85°C products:85°C	ΔC/C	Within±5% of the initial value				
		DF	Within the initial limit				
		LC	≤ 3 times of the initial limit				

Marking and dimensions

B1size

D2size

(unit : mm)

Size code	L ±0.2	W ±0.2	H ±0.1	S ±0.2	W1 ±0.1
B1	3.5	2.8	1.1	0.8	2.2
D2	7.3	4.3	1.9	1.3	2.4

※1 The rated voltage is as follows.


R.V.	6.3	8.0	10	12.5
Mark	j	k	A	B

※2 Lot.No.shows roughly manufacturing date.

※3 The rated capacitance is as follows.

Capacitance(μF)	10	15	22	33	47
Mark	A7	E7	J7	N7	S7

Recommended land pattern dimension of PWB

		(unit : mm)		
Size code	a	b	c	
B1	1.6	2.7	1.4	
D2	2.4	2.9	3.7	

Size list

RV:Rated voltage

RV	6.3	8.0	10.0	12.5
μF				
10				B1
15				B1
22		B1		
33	B1		B1	
47	B1			
68			D2	
100	D2		D2	
150	D2	D2		
330	D2			

TPC series characteristics list

Size code	Part number	Rated voltage (V)	Rated temperature (°C)	Rated capacitance (μF)	Category voltage (V)	Category temperature (°C)	DF (% max)	LC (μA) max/5min.	ESR (mΩ max) 100kHz/20°C	Maximum allowable ripple current (mA rms) 100kHz※1	MSL	
B1	12TPC15M	12.5	85	15	10	105	10	18.8	80	800	3	3
	12TPC10M	12.5	85	10	10	105	10	12.5	80	800	3	3
	8TPC22M	8.0	85	22	6.3	105	10	17.6	70	1000	3	3
	6TPC47MB	6.3	85	47	5.0	105	10	29.6	70	1000	3	3
	6TPC47M	6.3	85	47	5.0	105	10	29.6	55	1100	3	3
D2	10TPC100M	10	105	100	10	105	10	100.0	45	1700	3	2a
	10TPC68M	10	105	68	10	105	10	68.0	45	1700	3	2a
	8TPC150M	8.0	105	150	8.0	105	10	120.0	40	1900	3	2a
	6TPC330MA	6.3	85	330	5.0	105	10	207.9	40	1900	3	2a
	6TPC150M	6.3	105	150	6.3	105	10	94.5	40	1900	3	2a
	6TPC100M	6.3	105	100	6.3	105	10	63.0	45	1700	3	2a

※1 100k~500kHz,45°C