









- 1 MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
- 2 SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
- 3 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 5 NOT MANUFACTURED IN U.S.
- 6 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON EACH SIDE OF HOUSING.




PARTIAL DETAIL D 
OPTIONAL CONSTRUCTION




DETAIL B
350736-4 ONLY



350736-4 3-DIMENSIONAL MODEL
NTS



3-DIMENSIONAL MODEL NTS



VIEW A—A
350736-4 ONLY

BLACK	1-350736-9
GRAY	1-350736-8
BLUE	1-350736-6
GREEN	1-350736-5
YELLOW	1-350736-4
ORANGE	1-350736-3
RED	1-350736-2
BROWN	1-350736-1
	350736-4
NATURAL	350736-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG K. WHITAKER	20FE992	 ITE Connectivity		PART NUMBER	
		CHK R. SWING	20FE992				
DIMENSIONS:		24FE992		NAME	PLUG, 15 CIRCUIT, UNIVERSAL MATE-N-LOK™		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		D. SELF					
mm	PRODUCT SPEC						
	0. PLC	± .	APPLICATION SPEC				
	1. PLC	± .					
	2. PLC	± 0.13					
	3. PLC	± .					
	4. PLC	± .					
ANGLES		± 0°30'					
MATERIAL	FINISH	WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
NYLON,UL 94V-0	-			A1	00779	C=350736	-
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1
				REV	Y		