











PCB LAYOUT




SPRING WASHER



METAL NUT



15	PUSH LEVEL	Brass/Ni Plated	1
14	INSULATOR	PPS/Black	1
13	METAL SHELL	Brass/Ni Plated	1
12	SOCKET CONTACTS	Brass/Au Plated	4
11	CIRCUIT BOARD	FIBER GRASS	1
10	INSULATOR	PPS/Black	1
9	SPRING	SUS 304/Ni Plated	1
8	LATCH SPRING	SUS 304/Ni Plated	1
7	MACHINED SHELL	Brass/Ni Plated	1
6	CONTACTS	Brass/Au Plated	2
5	CONTACTS	Brass/Au Plated	2
4	METAL NUT	Brass/Ni Plated	1
3	SPRING WASHER	SUS 304/Ni Plated	1
2	GROUND CONTACT	Brass/Ni Plated	1
1	SUPPORT	PA6/Black	1
	DESCRIPTION	MATERIAL & FINISH	QTY



ISO VIEW
(SCALE 1:1)

Notes:
1. Part must conform to RoHS compliance
2. Plastic parts conform to UL94 V-0 compliant.

Specification: Electrical
Contact Resistance: <0.03 ohm
Insulation Resistance: >500Megaohm
Dielectric Strength: 1000VDC
Rated Current: 5A

Mechanical
Mating: >5000 cycles
Insertion/withdrawal Force: >10N & <30N.

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				0	FIRST ISSUE	MH	04-10-12	----
LINEAR	ANGULAR	REV.				CHANGE DETAILS				CHG/No
X ± 0.50	X° ± 1°	CAD FILE: 55010859000110				DRN: MH				DATE: 04-10-12
X/X ± 0.25	X°/X° ± 30°	MATERIAL: SEE NOTES				CKD: MH				DATE: 04-10-12
X/X ± 0.10	X°/X° ± 15°	DO NOT SCALE				APP'D: PM				DATE: 04-10-12
DIMENSIONS IN MILLIMETRES		THIRD ANGLE PROJECTION				SCALE: 2 : 1				PART No: AG3FCCH
						SIZE: A4				TITLE: MINI XLR 3 SKT FEMALE PANEL MOUNT RA PCB CUSTOMER DRAWING
										Amphenol Amphenol Australia Pty Ltd, 2 Fireways Blvd, Keysborough, Vic 3173 DRAWING NO. 55010859-000-1 SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AG6FCCH](#) [AG3FCCH](#) [AG5FCCH](#) [AG4FCCH](#)