

SlimFix
SF 6/21 MC NE RT V2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	SF 6/21 MC NE RT V2
Order No.	1919180000
Version	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, red
GTIN (EAN)	4032248555574
Qty.	160 pc(s).
Alternative product	1919160000
compatible printer	1324380000 2438520000 2438510000

SlimFix
SF 6/21 MC NE RT V2
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	8.4 mm
Height	21 mm
Depth	8.5 mm
Net weight	0.975 g

Width (inches)	0.331 inch
Height (inches)	0.827 inch
Depth (inches)	0.335 inch

General data

Colour	red
Material	Polyamide 66
Recommended industries	Transportation, Machinery
Type of printing	neutral
Width	8.4 mm

Halogen	No
Operating temperature range	-40...100 °C
Size of labelling field	21 x 8.4 mm
UL 94 flammability rating	V-2

Conductor and cable markers

Conductor O.D.	5.8 - 7.8 mm
Conductor O.D., min.	5.8 mm
Conductor cross-section, min.	10 mm ²

Conductor O.D., max.	7.8 mm
Conductor cross-section, max.	16 mm ²
Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01
eClass 10.0	27-40-04-01	UNSPSC	44-12-17-08

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Product Change Notification	Technical change - DE Technical change - EN
Software	M-Print PRO configuration file

SlimFix SF 6/21 MC NE RT V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

