

FEATURES

- * 3.0 -INCH (76.2 -mm) MATRIX HEIGHT.
- * LOW POWER REQUIREMENT.
- * EXCELLENT CHARACTERS APPEARANCE.
- * HIGH BRIGHTNESS & HIGH CONTRAST.
- * WIDE VIEWING ANGLE.
- * SOLID STATE RELIABILITY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.
- * STACKABLE VERTICALLY AND HORIZONTALLY.


DESCRIPTION

The is a 3.0 -inch (76.2 -mm) matrix height 5×7 dot-matrix display. This device utilizes ultra yellow LED chips, which are made from GaAsP on a transparent GaP substrate, and has a gray face and white dots.


DEVICE

PART NO.	DESCRIPTION
YELLOW	CATHODE COLUMN
LTP-3157AY	ANODE ROW

PACKAGE DIMENSIONS



INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

No.	CONNECTION
1	ANODE ROW 5
2	ANODE ROW 7
3	CATHODE COLUMN 2
4	CATHODE COLUMN 3
5	ANODE ROW 4
6	CATHODE COLUMN 5
7	ANODE ROW 6
8	ANODE ROW 3
9	ANODE ROW 1
10	CATHODE COLUMN 4
11	NO CONNECTION
12	NO CONNECTION
13	CATHODE COLUMN 1
14	ANODE ROW 2

ABSOLUTE MAXIMUM RATING AT T_A=25°C

PARAMETER	MAXIMUM RATING	UNIT
Average Power Dissipation Per Dot	60	mW
Peak Forward Current Per Dot	80	mA
Continuous Forward Current Per Dot	8	mA
Derating Linear From 25°C Per Dot	0.11	mA/°C
Reverse Voltage Per Dot	10	V
Operating Temperature Range	-35°C to +85°C	
Storage Temperature Range	-35°C to +85°C	
Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260°C		

ELECTRICAL / OPTICAL CHARACTERISTICS AT T_A=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _V	3000	9600		μcd	I _F =80mA, 1/16 Duty
Peak Emission Wavelength	λ _P		585		nm	I _F =20mA
Spectral Line Half-Width	Δλ		35		nm	I _F =20mA
Dominant Wavelength	λ _d		588		nm	I _F =20mA
Forward Voltage Per Dot	V _F		4.2	5.2	V	I _F =20mA
			6.0	7.4	V	I _F =80mA
Reverse Current Per Dot	I _R			100	μA	V _R =10V
Luminous Intensity Matching Ratio	I _V -m			2:1		I _F =80mA, 1/16 Duty

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig 1. RELATIVE INTENSITY VS. WAVELENGTH




Fig 2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig 3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig 4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig 5. MAX AVERAGE FORWARD CURRENT VS. AMBIENT TEMPERATURE.




Fig 6. MAX PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE : Y=YELLOW