

	13	12	11	10	9	8	7	6	5	4	3	2	1								
J	ENG. NO.	PIN NO.	DIM. L	DIM. X	DIM. Z	DIM. Y	DIM. W	DIM. R	DIM. G	DIM. T				J							
	A-7478-NA222	2766-41(222) OR 4266-0667	(18.80) .740	(6.71) .264	(3.58) .141	(3.05) .120	90° .046	(1.17) .046	N/A	OVERALL											
I	A-7478-NA241	4266-0666	(18.80) .740	(6.71) .264	(3.58) .141	(3.05) .120	90° .046	(1.17) .046	(4.57) .180	(3.43) .135											
	A-7478-NA241T	4266-0666	(18.80) .740	(6.71) .264	(3.58) .141	(3.05) .120	90° .046	(1.17) .046	(4.57) .180	(3.43) .135											
	A-7478-NA197T	4266-0662	(18.80) .740	(6.71) .264	(3.58) .141	(3.05) .120	90° .046	(1.17) .046	N/A	OVERALL											
H														H							
G														G							
F														F							
E														E							
D														D							
C														C							
B							CHANGE PLATING EC NO: UCP2012-1821 DRAWN:MMSTROH 2011/12/09 CHKD:MKIPPER 2012/01/03 APPR:FSMITH 2012/02/02		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± ---°		DIMENSION STYLE MM/IN DRAWN BY DATE GUZIK 1987/07/10 CHECKED BY DATE PATEL 1987/07/10 APPROVED BY DATE LENZ 1987/07/10		SCALE --- INCH		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		B
A							AA		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART SIZE C		MATERIAL NO. DOCUMENT NO.		FRICITION LOCK HEADER ASY .100 CL BENT SQ PINS 7478 SERIES DWG MOLEX INCORPORATED SDA-7478		SHEET NO. 2 OF 7		A		
	12	11	10	9	8	7	6	5	4	3	2	1									

1b_frame_C_P_ME_T
Rev. F 2009/06/18

12

11

10

9

8

7

6

5

4

3

2

1

13		12		11		10		9		8		7		6		5		4		3		2		1	
A-7478-NA222				A-7478-NA241				A-7478-NA241T				A-7478-NA197T													
PART NO.		ENG. NO.		PART NO.		ENG. NO.		PART NO.		ENG. NO.		PART NO.		ENG. NO.				PART NO.		ENG. NO.		PART NO.		ENG. NO.	
22-05-302I		A-7478-2A222		22-12-2024		A-7478-2A241		50-29-1710		A-7478-2A241T		50-34-8500		A-7478-2A197T											
22-05-303I		A-7478-3A222		22-12-2034		A-7478-3A241		50-29-1711		A-7478-3A241T		50-34-8501		A-7478-3A197T											
22-05-304I		A-7478-4A222		22-12-2044		A-7478-4A241		50-29-1705		A-7478-4A241T		50-34-8502		A-7478-4A197T											
22-05-305I		A-7478-5A222		22-12-2054		A-7478-5A241		50-29-1712		A-7478-5A241T															
22-05-306I		A-7478-6A222		22-12-2064		A-7478-6A241		50-29-1713		A-7478-6A241T															
22-05-307I		A-7478-7A222		22-12-2074		A-7478-7A241		50-29-1714		A-7478-7A241T															
22-05-308I		A-7478-8A222		22-12-2084		A-7478-8A241		50-29-1715		A-7478-8A241T															
22-05-309I		A-7478-9A222		22-12-2094		A-7478-9A241		50-29-1716		A-7478-9A241T															
22-05-310I		A-7478-10A222		22-12-2104		A-7478-10A241		50-29-1717		A-7478-10A241T															
22-05-311I		A-7478-11A222		22-12-2114		A-7478-11A241		50-29-1718		A-7478-11A241T															
22-05-312I		A-7478-12A222		22-12-2124		A-7478-12A241		50-29-1719		A-7478-12A241T															
22-05-313I		A-7478-13A222		22-12-2134		A-7478-13A241		50-29-1720		A-7478-13A241T															
22-05-314I		A-7478-14A222		22-12-2144		A-7478-14A241		50-29-1721		A-7478-14A241T															
22-05-315I		A-7478-15A222		22-12-2154		A-7478-15A241		50-29-1722		A-7478-15A241T															
22-05-316I		A-7478-16A222		22-12-2164		A-7478-16A241		50-29-1723		A-7478-16A241T															
22-05-317I		A-7478-17A222		22-12-2174		A-7478-17A241		50-29-1724		A-7478-17A241T															
22-05-318I		A-7478-18A222		22-12-2184		A-7478-18A241		50-29-1725		A-7478-18A241T															
22-05-319I		A-7478-19A222		22-12-2194		A-7478-19A241		50-29-1726		A-7478-19A241T															
22-05-320I		A-7478-20A222		22-12-2204		A-7478-20A241		50-29-1727		A-7478-20A241T															
22-05-321I		A-7478-21A222		22-12-2214		A-7478-21A241		50-29-1728		A-7478-21A241T															
22-05-322I		A-7478-22A222		22-12-2224		A-7478-22A241		50-29-1729		A-7478-22A241T															
22-05-323I		A-7478-23A222		22-12-2234		A-7478-23A241		50-29-1730		A-7478-23A241T															
22-05-324I		A-7478-24A222		22-12-2244		A-7478-24A241		50-29-1731		A-7478-24A241T															
22-05-325I		A-7478-25A222		22-12-2254		A-7478-25A241		50-29-1732		A-7478-25A241T															
22-05-326I		A-7478-26A222		22-12-2264		A-7478-26A241		50-29-1733		A-7478-26A241T															
22-05-327I		A-7478-27A222		22-12-2274		A-7478-27A241		50-29-1734		A-7478-27A241T															
22-05-328I		A-7478-28A222		22-12-2284		A-7478-28A241		50-29-1735		A-7478-28A241T															