



REVISIONS				
REV.	ECO. NO.	DESCRIPTION	DATE	BY
A	2144	INITIAL RELEASE	07/16/2010	LH



## NOTES:

1. INSULATOR MATERIAL: NYLON 66.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. PLATING: GOLD FLASH OVERALL.
4. UL FLAMMABILITY RATING: 94V-2.
5. DIELECTRIC WITHSTANDING VOLTAGE: 650V AC.
6. CURRENT RATING: 1 AMP PER CONTACT.
7. CONTACT RESISTANCE: 30 MILLI OHMS MAX.
8. INSULATION RESISTANCE: 1000 MEGA OHMS.
9. OPERATING TEMPERATURE: -40 °C TO +85 °C.
10. DOUBLE TUNING FORK TYPE CONTACT, ACCOMMODATES .016"[0.40mm] SQ PINS, .050"[1.27mm] PITCH LOW PROFILE MINI TYPE.



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES[MM]  
TOLERANCES:  
ANGULAR:  $\pm 30^\circ$   
.XX= $\pm .012$  [.30]  
.XXX= $\pm .008$  [.20]  
.XXXX= $\pm .004$  [.10]  
  
INTERPRET DIMENSIONS AND GEOMETRIC  
TOLERANCING  
PER: ASME Y14.5M-2009

SIZE	DWG. NO.	REV
C	11499	A
SCALE: 16:1		SHEET 1 OF 1

DATE NAME  
DRAWN 7/16/2010 LH  
THE INFORMATION HEREIN CONTAINS  
PROPRIETARY INFORMATION OF  
SULLINS ELECTRONICS AND IS NOT  
TO BE REPRODUCED, USED OR  
DISCLOSED TO OTHERS FOR ANY  
PURPOSE EXCEPT AS SPECIFICALLY  
AUTHORIZED IN WRITING BY AN  
OFFICER OF SULLINS ELECTRONICS.

DESCRIPTION  
MINI SHUNT, .050" CC, CLOSED TOP  
PART NUMBER  
NPB02SVAN-RC