





- 1 PARTS COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.000076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 5 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.000076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 6 PRELIMINARY - NOT FOR PRODUCTION
- 7 SUPERSEDED BY 640900-3



PHOSPHOR BRONZE, PRE-TIN	NYLON, UL94V-0, BLUE	6 1-640900-4
PHOSPHOR BRONZE, PRE-TIN	NYLON, UL94V-0, RED	6 1-640900-2
PHOSPHOR BRONZE, GOLD 5	NYLON, UL94V-0, NATURAL	640900-3
PHOSPHOR BRONZE, GOLD 4	NYLON, UL94V-0, NATURAL	640900-2
PHOSPHOR BRONZE, PRE-TIN	NYLON, UL94V-0, NATURAL	640900-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK S. RIDGILL APVD S. RIDGILL	18JAN2005 18JAN2005 18JAN2005	TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	SIZE	CAGE CODE	DRAWING NO
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	APPLICATION SPEC	RESTRICTED TO	
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	A1	00779	640900
CUSTOMER DRAWING		SCALE	5:1	SHEET	1 OF 1
		REV	N3		