

# Audio Transformer

## PC Mount

# TY-141P

#### **Description:**

These transformers operate in the 200 Hz to 15,000 Hz range, making them suitable for a broad application spectrum in the audio industry. These devices are used in line matching, telephone coupling, pulse trigger, driver, interstage, output, isolation and input applications.

Operating Temperature Range: 0° C to 105° C

### Electrical Specifications at 25° C:

Frequency Response: ± 2dB from 200 to 15,000 Hz
 Impedance Matching: 10% over full frequency range

7. Longitudinal Balance > 45dB
8. Insertion Loss @ 1K Hz: < 1.5dB
9. Return Loss: > 26dB

10. Total Harmonic Distortion < 0.5% between 275Hz and 3.5KHz

11. DCR:

Primary (1-3) 820Ω Nominal 1

Secondary (4-6) 1070Ω Nominal

12. Turns Ratio: 1 : 1

13. Dielectric Strength 1500V Pri to Sec to Core

#### **Construction:**


Bobbin has plug-in terminals which are spaced to provide fixed mounting centers. Pins are rugged, minimizing the incidence of bent pins from handling.

## **Outline Dimensions:**

A. Dimensions: As figures show B. PIN DIM. : .042" x .020"

C. Weight.: 0.51 oz.

#### **Schematic:**



**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

\*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html



