



THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND ITS SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE. SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER ASSUMES ALL RESPONSIBILITY FOR THE PROPER USE AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.



NOTES:

- 1. MATERIALS AND FINISHES:**
 INSULATOR: GLASS FILLED POLYESTER PER MIL-M-24519, UL 94V-0, COLOR: BLUE.
 CONTACTS: PRECISION MACHINED COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.
 SHELLS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
 MOUNTING BRACKETS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
 ALIGNMENT BAR: NYLON, COLOR: BLACK.
 PUSH FASTENERS: BERYLLIUM COPPER WITH TIN PLATE.
- 2. ELECTRICAL CHARACTERISTICS:**
 CONTACT CURRENT RATING: 5 AMPERES NOMINAL.
 INITIAL CONTACT RESISTANCE: 0.010 OHMS MAX.
 INSULATOR RESISTANCE: 5 G OHMS.
 WORKING VOLTAGE: 300 VAC [rms]
- 3. TEMPERATURE RANGE: -55°C TO +125°C**
- 4. DIMENSIONS ARE IN INCHES [MILLIMETERS].**

CONTACT HOLE PATTERN



DATE	REV	REVISION/RECORD	APP	DR	CK
8-12-09	Nc	ECO 31419	ECW	BS	TK
9-03-09	A	ECO 31489	ECW	BS	TK

POSITRONIC INDUSTRIES INC.
 www.connectpositronic.com
 FSCM 28198

SCALE: N.T.S.
 DRAWN BY: B SHELLBOY
 APPROVED BY: R WILLIAMS

CBD15W4FR7N00
 SK10950

DATE: 8-12-09
 DRAWING NUMBER: SK10950
 REV: A

SK10950