



HIGH PERFORMANCE LED SEARCHLIGHTS

Working on the existing model, the **PANTHER LED** range uses the latest in LED technology and thermal power management, providing intense light power and durability. Featuring 9 Cree® LEDs they produce 1500 lumens and a beam distance of 1000m.

The tried and tested design ensures it retains all the original robust features; but the upgrade to LED means vastly improved operating times, no heat risk and requires no replacement bulbs (LED offers 50,000h+ lifetime). LEDs also offer a much clearer white light, flooding the immediate area and providing a strong spot beam for long distance lighting.


LED also allows for various mode options, and additional to the high power, the **PANTHER LED** range features low mode (1000 lumens), designed for extended runtimes or closer applications and Flashing/Strobe modes for signalling purposes or emergencies/defence.



- 1500 | 1000 lumens
- LEDs offer 50,000h life
- No heat
- 1000 metre beam
- 4 modes: High, low, flashing, strobe
- Detachable shoulder strap and adjustable stand
- Battery charging indicator (red to green)
- Supplied with:** Mains charger and shoulder strap
- Used by:** MoD, Police, Search & Rescue and Railways
- Applications:** Utility maintenance, Overhead line inspection, Jointing, Track/tunnel inspection, Line of sight, Security patrol, Public order

OPTIONAL EXTRAS

- Vehicle charger
- Vehicle charging base (CB option)
- Vehicle/wall mounting bracket
- Protective carry case
- IP65 version available



PANTHER LED LITE

Use of Lithium-ion batteries offers optimized weight, power and battery life. This option is designed for professional applications where high performance, long running times, but low weight are crucial.

Unlike Lead acid batteries, high performance Li-ion require low maintenance and can be left in a fully discharged state without damaging the battery, nor will they suffer from 'memory effect', associated with other batteries.

Weighing in at only 1.6Kg (reduced by 1.4Kg) the **PANTHER LED LITE** offers the ultimate power to weight ratio and an incredible running time of 8h at full power.



SPECIFICATION

	Panther LED	Panther LED LITE
Light output	1500 1000 lumens	1500 1000 lumens
Light source	9 Cree® LED	9 Cree® LED
Light modes	High, Low, Flash, Strobe	High, Low, Flash, Strobe
Run time	5h 10h30	8h 14h
Battery	12V 7Ah lead acid	14.8V 7.8Ah Li-ion
Charge time	8h	7h
Product size (mm)	L260 x W150 x H180	L260 x W150 x H180
Product weight (kg)	3	1.6
Boxed size (mm)	L269 x W224 x H204	L269 x W224 x H204
Boxed weight (kg)	3.5	2.1
Part No.	NSPANTHERLED	NSPANTHERLEDLITE

CAT/PAD No. LED LITE 0111/103516