


CATALOG LISTING
PAGE 1 OF 1
REPLACES
1XE3-4
RELEASE NO. PR-19628
CHECK
REVISIONS
A CO-1
94274
J J A
23 MAR 99
CHECK
D A W
7 OCT 91
CHECK
4 OCT 91
D D M / C A D
DRAWN



NOTES
 1 MOUNTING HOLES WILL ACCEPT .087 MAX Ø PINS OR SCREWS ON .188 ± .002 CENTERS
 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
 3 WEIGHT OF SWITCH ONLY IS .16 OZ MAX WEIGHT OF SWITCH WITH WIRE LEADS IS .90 OZ MAX

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.			THIRD ANGLE PROJECTION	
CHARACTERISTICS	ELECTRICAL DATA		SCALE 2:1	DO NOT SCALE PRINT
OPERATING FORCE — — — — 5-17 OZ	CONTACT ARRANGEMENT S P N O		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 4 OZ MIN	28 VOLTS DC RATING		ONE PLACE (.0) ±.030	
RELEASE TRAVEL — — — — .004 MIN	INDUCTIVE — — — SEA LEVEL — — — 4 AMP		TWO PLACE (.00) ±.015	
DIFFERENTIAL TRAVEL — — — .005 MAX	50,000 FT — 2.5 AMP		THREE PLACE (.000) ±.005	
OVERTRAVEL — — — — — .004 MIN	RESISTIVE — — — SEA LEVEL — — — 7 AMP		ANGLES ±	
	50,000 FT — — — 7 AMP			
	MAXIMUM INRUSH — — — — — 24 AMP		WEIGHT 3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1XE3-4](#)