

INTERCONNECTS

SERIES 350, 450, 801, 803 • .100" GRID (.025" DIA. PINS), LOW PROFILE HEADERS & VERSATILE SOCKETS • SINGLE & DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5

- Series 350 and 450 single and double row pin headers use MM #0290 pins. See page 215 for details
- Series 801 and 803 single and double row low profile sockets use MM #1303 receptacles. See page 180 for details
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #16 contact rated at 4.5 amps. Receptacles accept .025" diameter and .025" square pins. See page 256 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 350...001 Single Row .025" Pin / .018" Solder Tail																						
	350-XX-1 -00-001000 Specify number of pins 01-64																						
FIG. 2	Series 450...001 Double Row .025" Pin / .018" Solder Tail																						
	450-XX-2 -00-001000 Specify number of pins 02-64																						
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264																							
SPECIFY PLATING CODE XX=																							
<table><tr><td>10</td><td>90</td><td>40</td><td></td></tr><tr><td>Pin Plating </td><td>10 μ" Au</td><td>200 μ" Sn/Pb</td><td>200 μ" Sn</td></tr></table>			10	90	40		Pin Plating 	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn													
10	90	40																					
Pin Plating 	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn																				
FIG. 3	Series 801...003 Low Profile Socket (short insulator)																						
	801-XX-0 -10-003000 Specify number of pins 01-64																						
FIG. 4	Series 801...013 Low Profile Socket (long insulator)																						
	801-XX-0 -10-013000 Specify number of pins 01-36																						
FIG. 5	Series 803...003 Double Row Low Profile Socket																						
	803-XX-0 -10-003000 Specify number of pins 02-72																						
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264																							
SPECIFY PLATING CODE XX=																							
<table><tr><td></td><td></td><td></td><td></td><td>41</td><td>43</td><td></td></tr><tr><td>Sleeve (Pin) </td><td></td><td></td><td></td><td>200 μ" Sn</td><td>200 μ" Sn</td><td></td></tr><tr><td>Contact (Clip) </td><td></td><td></td><td></td><td>10 μ" Au</td><td>30 μ" Au</td><td></td></tr></table>							41	43		Sleeve (Pin) 				200 μ" Sn	200 μ" Sn		Contact (Clip) 				10 μ" Au	30 μ" Au	
				41	43																		
Sleeve (Pin) 				200 μ" Sn	200 μ" Sn																		
Contact (Clip) 				10 μ" Au	30 μ" Au																		

