



	10	9	8	7	6	5	4	3	2	19073
	MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	"S"	"W"	"C" MIN 	"L" MAX 	"I.D."	PACKAGING	
F	I90730036	AA-832-04	04	.119(3.02)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)	LOOSE PIECE	
	I90730038	AA-832-06	06	.146(3.71)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)		
	I90730042	AA-832-08	08	.173(4.39)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)		
	I90730046	AA-833-04	04	.119(3.02)	.27(6.9)	.24(6.1)	.82(20.7)	.062(1.57)		
	I90730047	AA-833-06	06	.146(3.71)	.27(6.9)	.24(6.1)	.82(20.7)	.062(1.57)		
	I90730048	AA-833-08	08	.173(4.39)	.27(6.9)	.24(6.1)	.82(20.7)	.062(1.57)		
	I90730049	AA-833-10	10	.198(5.03)	.27(6.9)	.24(6.1)	.82(20.7)	.062(1.57)		
E	I90730001	AA-8111-02	02	.094(2.38)	.19(4.8)	.17(4.4)	.72(18.2)	.054(1.37)		
	I90730003	AA-8111-04	04	.119(3.02)	.19(4.8)	.17(4.4)	.72(18.2)	.054(1.37)		
	I90730037	AA-832-04T	04	.119(3.02)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)		
	I90730040	AA-832-06T	06	.146(3.71)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)	TAPE MOUNTED	
	I90730043	AA-832-08T	08	.173(4.39)	.25(6.5)	.24(6.1)	 .81 (20.6)	.062(1.57)		
	I90730050	AA-833-10T	10	.198(5.03)	.27(6.9)	.24(6.1)	.82(20.7)	.062(1.57)		
	I90730002	AA-8111-02T	02	.094(2.38)	.19(4.8)	.17(4.4)	.72(18.2)	.054(1.37)		
	I90730004	AA-8111-04T	04	.119(3.02)	.19(4.8)	.17(4.4)	.72(18.2)	.054(1.37)		



- NOTES:
1. MATERIAL: COPPER
PLATING: ELECTROPLATE TIN
 2. FERRULE: TIN-PLATED BRASS
 3. INSULATION: RED NYLON
 4. MWID=MAXIMUM WIRE INSULATION DIA.
 5. ALL DIMENSIONS IN INCHES (MM).
 6. PARTS ARE ROHS COMPLIANT.

FIX TOLERANCES EC NO: WNA2010-0470 DRAWN BY: DRWINETHRODAHL 2010/01/27 CHKD: JMAGNEIL 2010/01/27 APPR: JMAGNEIL 2010/01/27	C1	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
				▽=0	INCH		IN/MM		1:1	INCH	⊙ □	
				▽=0	mm	INCH	DRAWN BY	DATE	RING TONGUE TERMINAL 22-18 AWG AVIKRIMP, 800-SERIES MOLEX INCORPORATED			
				4 PLACES ± --- ± ---	ASAYDEH	05/12/07						
				3 PLACES ± --- ± .005	CHECKED BY	DATE						
				2 PLACES ± 0.13 ± .01	JLOMASTRO	05/12/07						
				1 PLACE ± 0.25 ± ---	APPROVED BY	DATE						
				ANGULAR ±1/2°		RDEROSS	05/12/07	MOLEX				
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.						DOCUMENT NO.
						SEE CHART		SD-19073-004		1 OF 1		
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										