

Features

- Halogen free available upon request by adding suffix "-HF"
- Low forward voltage drop
- Super long operating life
- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

Maximum Ratings

- Operating Temperature: -65°C to +175°C
- Storage Temperature: -65°C to +175°C

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MBR10200UPS	10200U	200V	140V	200V

Electrical Characteristics @ 25°C Unless Otherwise Specified


Average Forward Current	$I_{F(AV)}$	10A	$T_L = 135^\circ\text{C}$
Peak Forward Surge Current	I_{FSM}	180A	8.3ms, half sine
Maximum Forward Voltage Drop Per Element	V_F	0.82V 0.67V 0.88V	$I_F=5A \ T_J = 25^\circ\text{C}$ $I_F=5A \ T_J = 125^\circ\text{C}$ $I_F=10A \ T_J = 25^\circ\text{C}$
Maximum DC Reverse Current At Rated DC Blocking Voltage	I_R	0.1mA 10mA	$T_J = 25^\circ\text{C}$ $T_J = 125^\circ\text{C}$
Maximum thermal Resistance	R_{thJA}	77	$^\circ\text{C/W}$

Notes: 1. High Temperature Solder Exemption Applied, see EU Directive Annex 7.

MBR10200UPS

10 Amp Schottky Barrier Rectifier 200 Volts

TO-277B



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.039	.047	1.00	1.20	
A2	.006	.017	0.15	0.43	
b1	.030	.041	0.75	1.05	
b2	.065	.077	1.65	1.95	
D	.148	.169	3.75	4.30	
D2	.110	.126	2.80	3.20	
E	.250	.264	6.35	6.70	
e	.065	.077	1.65	1.95	
E1	.207	.228	5.25	5.80	
E2	.120	.142	3.05	3.60	
L	.028	.051	0.70	1.30	
W	.031	.056	0.80	1.42	

RATING AND CHARACTERISTIC CUEVES

Fig.1 - Forward Current Derating Curve




Fig. 2 - Instantaneous Forward Characteristics





Fig. 3 - Reverse Characteristics



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel: 5Kpcs/Reel

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

*****IMPORTANT NOTICE*****

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes .
Micro Commercial Components Corp. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

*****APPLICATIONS DISCLAIMER*****

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.