






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
—	—		C	Hsg mat change to readily available PBT resin	03JAN2014	PS JK

POS. PER ROW 'N'	L	PART NUMBER	
—	—	—	—
2	5.08	215308-2	OBSOLETE
3	7.62	-3	OBSOLETE
4	10.16	-4	
5	12.70	-5	
6	15.24	-6	OBSOLETE
7	17.78	-7	
8	20.32	-8	
9	22.86	-9	
10	25.40	1-	-0 OBSOLETE
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3 OBSOLETE
14	35.56	1-	-4 OBSOLETE
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7 OBSOLETE
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1 OBSOLETE
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6 OBSOLETE
27	68.58	2-	-7 OBSOLETE
28	71.12	2-	-8
29	73.66	2-	-9 OBSOLETE
30	76.20	3-	-0
31	78.74	3-	-1 OBSOLETE
32	81.28	3-	-2
33	83.82	3-	-3 OBSOLETE
34	86.36	3-	-4 OBSOLETE
35	88.90	3-	-5
36	91.44	3- 215308	-6



NOTES:

- TO DETERMINE DIMENSIONS TAKE 2xN = NR. OF POS.
FOR EXAMPLE: 2x10 POS.: N x 2,54 = 25,4 mm.
FOR ORDERNR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE: 2x2 POS.= 215 308-2 (SHORTEST VERSION)
2x36 POS.= 3-215 308-6 (LONGEST VERSION)
- HOUSING MATERIAL: GREEN GLASS FILLED PBT, UL 94V-0
CONTACT MATERIAL: PHOSPHOR BRONZE.
- PLATING: 2.5 – 4.0µm TIN OVER 0.5µm NICKEL
- MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- CONTACT-POINT.
- RECOMMENDED PC-BOARD-THICKNESS: 1.6 mm
- PC-BOARD RETENTION FEATURE.
- HV100 CONNECTOR PACKED IN ANTI-STATIC BLISTER TRAY.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO 24.02.89	 TE Connectivity			
		CHK M.SCHAARSCHMIDT 24.02.89				
		APVD G.FELDMEIER	NAME			
		PRODUCT SPEC 108-19056	HV 100 VERTICAL CONNECTOR DUAL ROW, 7,0mm HEIGHT, TOP ENTRY, TIN			
		APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT —	A3	00779	C-215308	—
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV C		