

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

56120-8728

Status:

Active

Overview:

CRC™ (Compact Robotic Connectors)

Description:

CRC™ Shielded Rectangular I/O Female Terminal, Signal, Low-Insertion Force Type, Bag, Lead-Free



Documents:

Drawing (PDF)

Product Specification PS-500810-001 (PDF)

Product Specification PS-51238-017 (PDF)

Product Specification PS-51238-018 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

I/O Connectors

Series

56120

Application

N/A

Component Type

Terminal

Overview

CRC™ (Compact Robotic Connectors)

Product Name

CRC™

Type

N/A

Physical

Boot Color

N/A

Circuits (Loaded)

N/A

Durability (mating cycles max)

50

Gender

Female

Lock to Mating Part

Yes

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Orientation

Vertical

PCB Locator

No

Packaging Type

Bag

Panel Mount

N/A

Pitch - Mating Interface

N/A

Plating min - Mating

0.254µm

Plating min - Termination

1.016µm

Polarized to Mating Part

N/A

Polarized to PCB

N/A

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-55°C to +105°C

Termination Interface: Style

Crimp or Compression

Waterproof / Dustproof

No

Wire Insulation Diameter

1.60mm max.

Wire Size AWG

24, 28

Electrical

Current - Maximum per Contact

1.5A, 2.5A

Shielded

No

Voltage - Maximum

250V AC (RMS)/DC

Material Info

UPC

822350008242

Reference - Drawing Numbers

Product Specification

PS-500810-001, PS-51238-017, PS-51238-018, RPS-51238-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

56120Series

Mates With

56116 24-28 AWG Sequential Type Terminal, 56117 18-22 AWG Sequential Type Terminal, 56118 24-28 AWG Terminal, 56119 18-22 AWG Terminal

Use With

51238 Receptacle Housing, 51239 Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Hand Tool for I/O Male Terminals,A34 24-28 AWG Wire

Product #

0638192000

Extraction Tool for 0638133200
Compact Robot
Connector Crimp
Female Terminal for
18-28 AWG Wire

Japan

Description	Product #
New Handtool (Straight Action)	<u>0574075300</u>
Hand Extraction Tool	<u>0574076100</u>

This document was generated on 06/22/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION