


THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND ITS SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE. SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER ASSUMES ALL RESPONSIBILITY FOR THE INFORMATION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

SK10744

DATE	REV	REVISION RECORD	APP	DR	CK
7-30-09	NC	ECO 31054	RCW	BS	COLF



NOTES:

1. MATERIALS AND FINISHES:

INSULATOR: GLASS FILLED POLYESTER PER MIL-M-24519, UL 94V-0, BLUE COLOR.

CONTACTS: PRECISION MACHINED BRASS ALLOY WITH BERYLLIUM COPPER CLIP, 0.000050 [1.25μ] GOLD OVER NICKEL PLATE.

SHEETS: STEEL, ZINC PLATE WITH CHROMATE SEAL.

2. ELECTRICAL CHARACTERISTICS:

CONTACT CURRENT RATING: 7.5 AMPERES NOMINAL.

INITIAL CONTACT RESISTANCE: 0.008 OHMS MAXIMUM.

INSULATOR RESISTANCE: 5 G OHMS.

WORKING VOLTAGE: 300 V r.m.s.


3. TEMPERATURE RANGE: -55°C TO +125°C.

4. DIMENSIONS ARE IN INCHES [MILLIMETERS].



POSITRONIC
INDUSTRIES INC.
www.connectpositronic.com

FSCM 28198



CBM SERIES

SCALE
N.T.S.

DRAWN BY
B SHELLBOY

APPROVED BY
R WILLIAMS

DECIMAL TOL.
± 0.015 [0.38]

TITLE

CBM24WS20000

ANGULAR TOL.
± 5°

DATE
7-30-09

DRAWING NUMBER
SK10744

REV.
NC