⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

C02E.pdf
Sep.25,2013

# Chip Monolithic Ceramic Capacitors





muRata Innovator in Electronics

Murata Manufacturing Co., Ltd.

# Explanation of Symbols in This Catalog

**Ultra-compact** L x W dimension: products of 0.6 x 0.3 mm or less

**HiQ** Low dissipation for high frequency
By devising ceramic materials and electrode materials, low dissipation is achieved in frequency bands of VHF, UHF and microwave or beyond.

**Low ESL** Low inductance
This capacitor is designed so that the parasitic inductance component (ESL) that the capacitor has on the high frequency side becomes lower.

**Anti-noise** Product suitable for acoustic noise reduction and low distortion
This product suppresses acoustic noise, which occurs when a ceramic capacitor is used, by devising the materials and configuration.

**Deflecting crack** Product resistant to deflection cracking
This capacitor is designed to prevent failures as much as possible by short mode caused by cracking when there is board deflection.

**Soldering crack** Product with solder cracking suppression
This capacitor is configured with metal terminals and leads connected to the chip.
The metal terminals and leads relieve the stress from expansion and contraction of the solder, to suppress solder cracking.

**Derating** Voltage and temperature derating recommended product
This product is suitable when a voltage continuously applied to a capacitor in an operating circuit, is used below (derated) the rated voltage of the capacitor.
This model guarantees the test conditions in the endurance test, at a rated voltage x 100% at the maximum operating temperature.
A reliability assurance level equivalent to a common product can be secured, by using this product within the voltage and temperature derated conditions recommended in the figure below.

・Recommended Conditions of the Derating Operating Voltage and Temperature




**EU RoHS Compliant**

・All the products in this catalog comply with EU RoHS.
・EU RoHS is "the European Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment."
・For more details, please refer to our website 'Murata's Approach for EU RoHS' (http://www.murata.com/info/rohs.html).



# For General Purpose GRM Series
# Capacitance Table





# Contents



Product specifications are as of August 2013.

Part Numbering ····· p2
Selection Guide ····· p5
Capacitance Table ····· p6

## Chip Monolithic Ceramic Capacitors

| | | Cap. Table |
|---|---|---|
| For General Purpose GRM Series ····· | p16 | separate volume |
| High Frequency High Q Type 1005(in mm)/0402(in inch) Size Max. GJM Series ····· | p83 | p7 |
| Top & Bottom Electrode Type for Bonding GMA Series ····· | p105 | p8 |
| Compatible to Bonding / AuSn Soldering GMD Series ····· | p107 | p9 |
| High Frequency High Q Type 1608(in mm)/0603(in inch) Size Min. GQM Series ····· | p110 | p10 |
| Resin External Electrode Type GRJ Series ····· | p119 | p11 |
| High Effective Capacitance & High Allowable Ripple Current GR3 Series ····· | p121 | p11 |
| Metal Terminal Type For General Purpose KRM Series ····· | p123 | p12 |
| Metal Terminal Type High Effective Capacitance & High Allowable Ripple Current KR3 Series ····· | p126 | p13 |
| 8-Terminal Low ESL Type LLA Series ····· | p129 | p13 |
| LW Reversed Low ESL Type LLL Series ····· | p131 | p14 |
| 10-Terminal Low ESL Type LLM Series ····· | p133 | p14 |
| ESR Controlled Low ESL Type LLR Series ····· | p135 | p14 |

⚠Caution/Notice ····· p137
Qualified Standards ····· p158
Introduction of Website SimSurfing ····· p160
EMICON-FUN! ····· p161
Product Information ····· p162

Please check the MURATA home page (http://www.murata.com/)
if you cannot find the part number in the catalog.

## ● Part Numbering

### Chip Monolithic Ceramic Capacitors for General

(Part Number)

| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D |
|---|---|---|---|---|---|---|---|---|---|
| ❶ | ❷ | ❸ | ❹ | ❺ | ❻ | ❼ | ❽ | ❾ | ❿ |

❶Product ID ❷Series

| Product ID | Code | Series |
|---|---|---|
| GJ | M | High frequency HiQ type 1005(in mm)/0402(in inch) size max. |
| GM | A | Top & bottom electrode type for bonding |
| | D | Product for bonding/AuSn soldering |
| GQ | M | High frequency HiQ type 1608(in mm)/0603(in inch) size min. |
| GR | 3 | High effective capacitance & High allowable ripple current |
| | J | Resin external electrode type |
| | M | General purpose products |
| KR | 3 | Metal terminal type/High effective capacitance & High allowable ripple current |
| | M | Metal terminal type |
| LL | A | 8-terminal low ESL type |
| | L | LW reversed low ESL type |
| | M | 10-terminal low ESL type |
| | R | Controlled ESR low ESL type |

❸Chip Dimensions (L×W)

| Code | Dimensions (L×W) | Size Code (in inch) |
|---|---|---|
| 02 | 0.4×0.2mm | 01005 |
| 03 | 0.6×0.3mm | 0201 |
| 05 | 0.5×0.5mm | 0202 |
| 08 | 0.8×0.8mm | 0303 |
| 0D | 0.38×0.38mm | 015015 |
| 15 | 1.0×0.5mm | 0402 |
| 18 | 1.6×0.8mm | 0603 |
| 1U | 0.6×1.0mm | 02404 |
| 21 | 2.0×1.25mm | 0805 |
| 22 | 2.8×2.8mm | 1111 |
| 31 | 3.2×1.6mm | 1206 |
| 32 | 3.2×2.5mm | 1210 |
| 42 | 4.5×2.0mm | 1808 |
| 43 | 4.5×3.2mm | 1812 |
| 55 | 5.7×5.0mm | 2220 |

❹Height Dimension (T) (Except **KR**□)

| Code | Dimension (T) |
|---|---|
| 2 | 0.2mm |
| 3 | 0.3mm |
| 4 | 0.4mm |
| 5 | 0.5mm |
| 6 | 0.6mm |
| 7 | 0.7mm |
| 8 | 0.8mm |
| 9 | 0.85mm |
| A | 1.0mm |
| B | 1.25mm |
| C | 1.6mm |
| D | 2.0mm |
| E | 2.5mm |
| M | 1.15mm |
| Q | 1.5mm |
| R | 1.8mm |
| S | 2.8mm |
| X | Depends on individual standards. |

❹Height Dimension (T) (**KR**□ Only)

| Code | Dimension (T) |
|---|---|
| E | 1.8mm |
| F | 1.9mm |
| K | 2.7mm |
| L | 2.8mm |
| Q | 3.7mm |
| T | 4.8mm |
| W | 6.4mm |

Continued on the following page.

Please check the MURATA home page (http://www.murata.com/) if you cannot find the part number in the catalog.

(Part Number)

| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D |
|---|---|---|---|---|---|---|---|---|---|
| ❶ | ❷ | ❸ | ❹ | ❺ | ❻ | ❼ | ❽ | ❾ | ❿ |

Continued from the preceding page.

❺Temperature Characteristics

| Temperature Characteristic Codes | | | Temperature Characteristics | | | Operating Temperature Range | Capacitance Change Each Temperature (%) | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | | | | | | | –55°C | | *3 | | –10°C | |
| Code | Public STD Code | | Reference Temperature | Temperature Range | Capacitance Change or Temperature Coefficient | | Max. | Min. | Max. | Min. | Max. | Min. |
| 1X | SL | JIS | 20°C | 20 to 85°C | +350 to –1000ppm/°C | –55 to 125°C | - | - | - | - | - | - |
| 2C | CH | JIS | 20°C | 20 to 125°C | 0±60ppm/°C | –55 to 125°C | 0.82 | –0.45 | 0.49 | –0.27 | 0.33 | –0.18 |
| 3C | CJ | JIS | 20°C | 20 to 125°C | 0±120ppm/°C | –55 to 125°C | 1.37 | –0.9 | 0.82 | –0.54 | 0.55 | –0.36 |
| 3U | UJ | JIS | 20°C | 20 to 85°C | –750±120ppm/°C | –25 to 85°C | - | - | 4.94 | 2.84 | 3.29 | 1.89 |
| 4C | CK | JIS | 20°C | 20 to 125°C | 0±250ppm/°C | –55 to 125°C | 2.56 | –1.88 | 1.54 | –1.13 | 1.02 | –0.75 |
| 5C | C0G | EIA | 25°C | 25 to 125°C | 0±30ppm/°C | –55 to 125°C | 0.58 | –0.24 | 0.4 | –0.17 | 0.25 | –0.11 |
| 7U | U2J | EIA | 25°C | 25 to 125°C *2 | –750±120ppm/°C | –55 to 125°C | 8.78 | 5.04 | 6.04 | 3.47 | 3.84 | 2.21 |
| B1 | B *1 | JIS | 20°C | –25 to 85°C | ±10% | –25 to 85°C | - | - | - | - | - | - |
| B3 | B | JIS | 20°C | –25 to 85°C | ±10% | –25 to 85°C | - | - | - | - | - | - |
| C6 | X5S | EIA | 25°C | –55 to 85°C | ±22% | –55 to 85°C | - | - | - | - | - | - |
| C7 | X7S | EIA | 25°C | –55 to 125°C | ±22% | –55 to 125°C | - | - | - | - | - | - |
| C8 | X6S | EIA | 25°C | –55 to 105°C | ±22% | –55 to 105°C | - | - | - | - | - | - |
| D7 | X7T | EIA | 25°C | –55 to 125°C | +22%, –33% | –55 to 125°C | - | - | - | - | - | - |
| D8 | X6T | EIA | 25°C | –55 to 105°C | +22%, –33% | –55 to 105°C | - | - | - | - | - | - |
| E7 | X7U | EIA | 25°C | –55 to 125°C | +22%, –56% | –55 to 125°C | - | - | - | - | - | - |
| R1 | R *1 | JIS | 20°C | –55 to 125°C | ±15% | –55 to 125°C | - | - | - | - | - | - |
| R6 | X5R | EIA | 25°C | –55 to 85°C | ±15% | –55 to 85°C | - | - | - | - | - | - |
| R7 | X7R | EIA | 25°C | –55 to 125°C | ±15% | –55 to 125°C | - | - | - | - | - | - |

*1 Capacitance change is specified with 50% rated voltage applied.
*2 Rated Voltage 100Vdc max: 25 to 85°C
*3 –25°C (Reference Temperature 20°C) / –30°C (Reference Temperature 25°C)

❻Rated Voltage

| Code | Rated Voltage |
|---|---|
| 0E | DC2.5V |
| 0G | DC4V |
| 0J | DC6.3V |
| 1A | DC10V |
| 1C | DC16V |
| 1E | DC25V |
| 1H | DC50V |
| 1J | DC63V |
| 1K | DC80V |
| 2A | DC100V |
| 2D | DC200V |
| 2E | DC250V |
| 2W | DC450V |
| 2H | DC500V |
| 2J | DC630V |
| 3A | DC1kV |
| 3D | DC2kV |
| 3F | DC3.15kV |
| YA | DC35V |

❼Capacitance

Expressed by three-digit alphanumerics. The unit is picofarad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two numbers. If there is a decimal point, it is expressed by the capital letter "**R**." In this case, all figures are significant digits.
If any alphabet, other than "**R**", is included, this indicates the specific part number is a non-standard part.

Ex.)

| Code | Capacitance |
|---|---|
| R50 | 0.50pF |
| 1R0 | 1.0pF |
| 100 | 10pF |
| 103 | 10000pF |

❽Capacitance Tolerance

| Code | Capacitance Tolerance |
|---|---|
| B | ±0.1pF |
| C | ±0.25pF |
| D | ±0.5pF (10pF and below) |
| | ±0.5% (10pF and over) |
| F | ±1% |
| G | ±2% |
| J | ±5% |
| K | ±10% |
| M | ±20% |
| W | ±0.05pF |

Continued on the following page.

(Part Number)

| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D |
|---|---|---|---|---|---|---|---|---|---|
| ❶ | ❷ | ❸ | ❹ | ❺ | ❻ | ❼ | ❽ | ❾ | ❿ |

Continued from the preceding page.

❾Individual Specification Code (Except **LLR**)

Expressed by three figures.

❾ESR (**LLR** Only)

| Code | ESR |
|---|---|
| **E01** | 100mΩ |
| **E03** | 220mΩ |
| **E05** | 470mΩ |
| **E07** | 1000mΩ |

❿Packaging

| Code | Packaging |
|---|---|
| **L** | ø180mm Embossed Taping |
| **D/E/W** | ø180mm Paper Taping |
| **K** | ø330mm Embossed Taping |
| **J/F** | ø330mm Paper Taping |
| **B** | Bulk |
| **C** | Bulk Case |
| **T** | Bulk Tray |

Please contact us if you find any part number not provided in this table.

Please check the MURATA home page (http://www.murata.com/) if you cannot find the part number in the catalog.

# Selection Guide for Chip Monolithic Ceramic Capacitors



# Capacitance Table

## How to read the Capacitance Table

| L×W (mm) | 0.4×0.2 | | 0.6×0.3 | | 1.0 |
|---|---|---|---|---|---|
| T max. (mm) | 0.22 | | 0.33 | | 0. |
| Rated Voltage (Vdc) | 25 | | 25 | | 5 |
| Cap. / TC Code | C0G | CΔ | C0G | CΔ | C0G |
| 0.10pF | | | | | *p97* |
| 0.20pF | *p84* | *p87* | *p90* | *p93* | *p97* |
| 1.0pF | *p84* | *p87* | *p90* | *p94* | *p97* |
| 2.0pF | *p84* | *p87* | *p91* | *p94* | *p97* |
| 3.0pF | *p84* | *p87* | *p91* | *p94* | *p98* |

The values can be narrowed down in the order of size, rated voltage, and temperature characteristics.

Refers to the page of the part number list.
Check the part number list for the applicable product number.

## Temperature Characteristics Table

The Table is colored by temperature characteristic codes.
Refer to the following Table for the meaning of each code.

EIA: C0G | U2J | X7R | X7S | X7T | X7U | X6S | X6T | X5R | X5S
JIS: CK | CJ | CH | SL | UJ | R | B

| Temperature Characteristic Codes | | Temperature Characteristics | | | Operating Temperature Range | Capacitance Change Each Temperature (%) | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| Public STD Code | | Reference Temperature | Temperature Range | Capacitance Change or Temperature Coefficient | | –55°C | | *2 | | –10°C | |
| | | | | | | Max. | Min. | Max. | Min. | Max. | Min. |
| C0G | EIA | 25°C | 25 to 125°C | 0±30ppm/°C | –55 to 125°C | 0.58 | –0.24 | 0.4 | –0.17 | 0.25 | –0.11 |
| CK | JIS | 20°C | 20 to 125°C | 0±250ppm/°C | –55 to 125°C | 2.56 | –1.88 | 1.54 | –1.13 | 1.02 | –0.75 |
| CJ | JIS | 20°C | 20 to 125°C | 0±120ppm/°C | –55 to 125°C | 1.37 | –0.9 | 0.82 | –0.54 | 0.55 | –0.36 |
| CH | JIS | 20°C | 20 to 125°C | 0±60ppm/°C | –55 to 125°C | 0.82 | –0.45 | 0.49 | –0.27 | 0.33 | –0.18 |
| SL | JIS | 20°C | 20 to 85°C | +350 to –1000ppm/°C | –55 to 125°C | - | - | - | - | - | - |
| U2J | EIA | 25°C | 25 to 125°C *1 | –750±120ppm/°C | –55 to 125°C | 8.78 | 5.04 | 6.04 | 3.47 | 3.84 | 2.21 |
| UJ | JIS | 20°C | 20 to 85°C | –750±120ppm/°C | –25 to 85°C | - | - | 4.94 | 2.84 | 3.29 | 1.89 |
| X7R | EIA | 25°C | –55 to 125°C | ±15% | –55 to 125°C | - | - | - | - | - | - |
| X7S | EIA | 25°C | –55 to 125°C | ±22% | –55 to 125°C | - | - | - | - | - | - |
| X7T | EIA | 25°C | –55 to 125°C | +22%, –33% | –55 to 125°C | - | - | - | - | - | - |
| X7U | EIA | 25°C | –55 to 125°C | +22%, –56% | –55 to 125°C | - | - | - | - | - | - |
| R | JIS | 20°C | –55 to 125°C | ±15% | –55 to 125°C | - | - | - | - | - | - |
| X6S | EIA | 25°C | –55 to 105°C | ±22% | –55 to 105°C | - | - | - | - | - | - |
| X6T | EIA | 25°C | –55 to 105°C | +22%, –33% | –55 to 105°C | - | - | - | - | - | - |
| X5R | EIA | 25°C | –55 to 85°C | ±15% | –55 to 85°C | - | - | - | - | - | - |
| X5S | EIA | 25°C | –55 to 85°C | ±22% | –55 to 85°C | - | - | - | - | - | - |
| B | JIS | 20°C | –25 to 85°C | ±10% | –25 to 85°C | - | - | - | - | - | - |

*1 Rated Voltage 100Vdc max: 25 to 85°C
*2 –25°C (Reference Temperature 20°C) / –30°C (Reference Temperature 25°C)

## ■ GRM Series

**For the Capacitance Table of General Purpose GRM Series, please review the inserted Capacitance Table of "Chip Monolithic Ceramic Capacitors For General Purpose GRM Series".**

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GRM Series Temperature Compensating Type

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 0.4×0.2 | | | | 0.6×0.3 | | | | 1.0×0.5 | | | | | | | 1.6×0.8 | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.22 | | | | 0.33 | | | | 0.55 | | | | | | | 0.5 | | | | | | 0.9 | |
| Rated Voltage (Vdc) | 16 | | 10 | | 100 | | 50 | | 100 | | 50 | | 10 | | | 50 | | | 10 | | | 100 | |
| Cap. / TC Code | C0G | CΔ | C0G | CH | C0G | CΔ | C0G | CΔ | C0G | CΔ | C0G | CΔ | SL | U2J | UJ | SL | U2J | UJ | SL | U2J | UJ | C0G | CΔ |
| 0.10pF | | | | | p23 | p26 | p30 | p33 | p36 | p40 | p43 | p47 | | | | | | | | | | | |
| 0.20pF | p17 | p20 | | | p23 | p26 | p30 | p33 | p36 | p40 | p43 | p47 | | | | | | | | | | | |
| 0.50pF | p17 | p20 | | | p23 | p26 | p30 | p33 | p36 | p40 | p43 | p47 | | | | | | | | | | p51 | p54 |
| 1.0pF | p17 | p20 | | | p23 | p27 | p30 | p33 | p37 | p40 | p43 | p47 | | | | | | | | | | p51 | p54 |
| 2.0pF | p17 | p20 | | | p24 | p27 | p30 | p33 | p37 | p40 | p44 | p47 | | | | | | | | | | p51 | p54 |
| 3.0pF | p17 | p20 | | | p24 | p27 | p30 | p34 | p37 | p40 | p44 | p47 | | | | | | | | | | p51 | p55 |
| 4.0pF | p18 | p21 | | | p24 | p27 | p31 | p34 | p37 | p41 | p44 | p48 | | | | | | | | | | p52 | p55 |
| 5.0pF | p18 | p21 | | | p25 | p28 | p31 | p34 | p38 | p41 | p44 | p48 | | | | | | | | | | p52 | p55 |
| 6.0pF | p18 | p21 | | | p25 | p28 | p31 | p35 | p38 | p41 | p45 | p48 | | | | | | | | | | p52 | p56 |
| 7.0pF | p19 | p22 | | | p25 | p28 | p32 | p35 | p38 | p42 | p45 | p49 | | | | | | | | | | p53 | p56 |
| 8.0pF | p19 | p22 | | | p26 | p29 | p32 | p35 | p39 | p42 | p45 | p49 | | | | | | | | | | p53 | p56 |
| 9.0pF | p19 | p23 | | | p26 | p29 | p32 | p36 | p39 | p42 | p46 | p49 | | | | | | | | | | p53 | p57 |
| 10pF | p20 | p23 | | | p26 | p30 | p33 | p36 | p39 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 12pF | p20 | p23 | | | p26 | p30 | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 15pF | p20 | p23 | | | p26 | p30 | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 18pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 22pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 27pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 33pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 39pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 47pF | p20 | p23 | | | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 56pF | | | p23 | p23 | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 68pF | | | p23 | p23 | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 82pF | | | p23 | p23 | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 100pF | | | p23 | p23 | | | p33 | p36 | p40 | p43 | p46 | p50 | | | | | | | | | | p54 | p57 |
| 120pF | | | | | | | p33 | p36 | | | p46 | p50 | | | | | | | | | | p54 | p57 |
| 150pF | | | | | | | | | | | p46 | p50 | | | | | | | | | | p54 | p57 |
| 180pF | | | | | | | | | | | p46 | p50 | | | | | | | | | | p54 | p57 |
| 220pF | | | | | | | | | | | p46 | p50 | | | | | | | | | | p54 | p57 |
| 270pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 330pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 390pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 470pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 560pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 680pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 820pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 1000pF | | | | | | | | | | | p47 | p50 | | | | | | | | | | p54 | p57 |
| 1200pF | | | | | | | | | | | | | p50 | p50 | p50 | | | | | | | p54 | p57 |
| 1500pF | | | | | | | | | | | | | p50 | p50 | p50 | | | | | | | p54 | p57 |
| 1800pF | | | | | | | | | | | | | p50 | p50 | p50 | | | | | | | | |
| 2200pF | | | | | | | | | | | | | p50 | p50 | p50 | p50 | p51 | p51 | | | | | |
| 2700pF | | | | | | | | | | | | | p50 | p50 | p50 | p51 | p51 | p51 | | | | | |
| 3300pF | | | | | | | | | | | | | p50 | p50 | p50 | p51 | p51 | p51 | | | | | |
| 3900pF | | | | | | | | | | | | | p50 | p50 | p50 | p51 | p51 | p51 | | | | | |
| 4700pF | | | | | | | | | | | | | p50 | p50 | p50 | p51 | p51 | p51 | | | | | |
| 5600pF | | | | | | | | | | | | | | | | | | | p51 | p51 | p51 | | |
| 6800pF | | | | | | | | | | | | | | | | | | | p51 | p51 | p51 | | |
| 8200pF | | | | | | | | | | | | | | | | | | | p51 | p51 | p51 | | |
| 10000pF | | | | | | | | | | | | | | | | | | | p51 | p51 | p51 | | |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 1.6×0.8 | | | | | | | | 2.0×1.25 | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.9 | | | | | | | | 0.7 | | | | | | | 0.95 | | | | | | | |
| Rated Voltage (Vdc) | 50 | | | | | 10 | | | 100 | | 50 | | | | | 50 | | | | | 10 | | |
| Cap. / TC Code | C0G | CΔ | SL | U2J | UJ | SL | UJ | U2J | C0G | CH | C0G | CH | SL | U2J | UJ | C0G | CH | SL | U2J | UJ | SL | U2J | UJ |
| 0.50pF | p57 | p61 | | | | | | | | | | | | | | | | | | | | | |
| 1.0pF | p57 | p61 | | | | | | | | | | | | | | | | | | | | | |
| 2.0pF | p58 | p61 | | | | | | | | | | | | | | | | | | | | | |
| 3.0pF | p58 | p61 | | | | | | | | | | | | | | | | | | | | | |
| 4.0pF | p58 | p62 | | | | | | | | | | | | | | | | | | | | | |
| 5.0pF | p59 | p62 | | | | | | | | | | | | | | | | | | | | | |
| 6.0pF | p59 | p62 | | | | | | | | | | | | | | | | | | | | | |
| 7.0pF | p59 | p63 | | | | | | | | | | | | | | | | | | | | | |
| 8.0pF | p60 | p63 | | | | | | | | | | | | | | | | | | | | | |
| 9.0pF | p60 | p63 | | | | | | | | | | | | | | | | | | | | | |
| 10pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 12pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 15pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 18pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 22pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 27pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 33pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 39pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 47pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 56pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 68pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 82pF | p60 | p64 | | | | | | | | | | | | | | | | | | | | | |
| 100pF | p60 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 120pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 150pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 180pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 220pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 270pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 330pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 390pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 470pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 560pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 680pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 820pF | p61 | p64 | | | | | | | p65 | p65 | | | | | | | | | | | | | |
| 1000pF | p61 | p64 | | | p64 | | | | p65 | p65 | | | | | | | | | | | | | |
| 1200pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 1500pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 1800pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 2200pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 2700pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 3300pF | p61 | p64 | p64 | p64 | p64 | | | | p65 | p65 | p65 | p65 | | | | | | | | | | | |
| 3900pF | p61 | p64 | p64 | p64 | p64 | | | | | | p65 | p65 | | | | | | | | | | | |
| 4700pF | p61 | p64 | p64 | p64 | p64 | | | | | | p65 | p65 | | | | | | | | | | | |
| 5600pF | p61 | p64 | p64 | p64 | p64 | | | | | | | | | | | p65 | p65 | | | | | | |
| 6800pF | p61 | p64 | p64 | p64 | p64 | | | | | | | | | | | p65 | p65 | | | | | | |
| 8200pF | p61 | p64 | p64 | p64 | p64 | | | | | | | | | | | p65 | p65 | | | | | | |
| 10000pF | p61 | p64 | p64 | p64 | p64 | | | | | | | | | | p65 | p65 | p65 | | | | | | |
| 12000pF | | | | | | p64 | p64 | p65 | | | | | p65 | p65 | p65 | p65 | p65 | | | | | | |
| 15000pF | | | | | | p64 | p65 | p65 | | | | | p65 | p65 | p65 | p65 | p65 | | | | | | |
| 18000pF | | | | | | p64 | p65 | p65 | | | | | p65 | p65 | p65 | | | | | | | | |
| 22000pF | | | | | | p64 | p65 | p65 | | | | | | | | | | p65 | p65 | p65 | | | |
| 27000pF | | | | | | | | | | | | | | | | | | p65 | p65 | p65 | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 39000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 47000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 56000pF | | | | | | | | | | | | | | | | | | | | | p65 | p65 | p65 |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

separate volume 2

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 2.0×1.25 | | | | | | | | | | | | | | | | 3.2×1.6 | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.0 | | | | | | | 1.35 | | | | | | | | 1.45 | | 0.95 | | | | |
| Rated Voltage (Vdc) | 250 | | 200 | | 50 | | | 50 | | | | | 10 | | | 250 | 200 | 100 | | 50 | | | |
| Cap. / TC Code | C0G | U2J | C0G | U2J | SL | U2J | UJ | CH | C0G | SL | U2J | UJ | SL | U2J | UJ | U2J | U2J | C0G | CH | C0G | CH | SL | U2J |
| 10pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 12pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 15pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 18pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 22pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 27pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 33pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 39pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 47pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 56pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 68pF | p65 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 82pF | p66 | | p66 | | | | | | | | | | | | | | | | | | | | |
| 100pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 120pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 150pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 180pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 220pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 270pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 330pF | p66 | p66 | p66 | p66 | | | | | | | | | | | | | | | | | | | |
| 390pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 470pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 560pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 680pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 820pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 1000pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 1200pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 1500pF | | p66 | | p66 | | | | | | | | | | | | | | | | | | | |
| 1800pF | | p66 | | p66 | | | | | | | | | | | | | | p66 | p67 | | | | |
| 2200pF | | p66 | | p66 | | | | | | | | | | | | | | p66 | p67 | | | | |
| 2700pF | | | | | | | | | | | | | | | | p66 | p66 | p66 | p67 | | | | |
| 3300pF | | | | | | | | | | | | | | | | p66 | p66 | p66 | p67 | | | | |
| 3900pF | | | | | | | | | | | | | | | | p66 | p66 | p66 | p67 | | | | |
| 4700pF | | | | | | | | | | | | | | | | p66 | p66 | p66 | p67 | | | | |
| 5600pF | | | | | | | | | | | | | | | | p66 | p66 | p66 | p67 | | | | |
| 6800pF | | | | | | | | | | | | | | | | | | p66 | p67 | | | | |
| 8200pF | | | | | | | | | | | | | | | | | | p66 | p67 | | | | |
| 10000pF | | | | | | | | | | | | | | | | | | p66 | p67 | | | | |
| 12000pF | | | | | | | | | | | | | | | | | | p67 | p67 | p67 | p67 | | |
| 15000pF | | | | | | | | | | | | | | | | | | p67 | p67 | p67 | p67 | | |
| 18000pF | | | | | | | | p66 | p66 | | | | | | | | | p67 | p67 | p67 | p67 | | |
| 22000pF | | | | | | | | p66 | p66 | | | | | | | | | p67 | p67 | p67 | p67 | | |
| 27000pF | | | | | | | | | | | | | | | | | | | | p67 | p67 | | |
| 33000pF | | | | | p66 | p66 | p66 | | | | | | | | | | | | | p67 | p67 | | |
| 39000pF | | | | | | | | | | p66 | p66 | p66 | | | | | | | | p67 | p67 | | |
| 47000pF | | | | | | | | | | p66 | p66 | p66 | | | | | | | | | | | |
| 56000pF | | | | | | | | | | | | | | | | | | | | | | p67 | p67 |
| 68000pF | | | | | | | | | | | | | p66 | p66 | p66 | | | | | | | | |
| 82000pF | | | | | | | | | | | | | p66 | p66 | p66 | | | | | | | | |
| 0.10μF | | | | | | | | | | | | | p66 | p66 | p66 | | | | | | | | |



muRata

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 3.2×1.6 | | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.95 | 1.0 | | | | | | | | | 1.25 | | | | | | | | | | | | 1.8 |
| Rated Voltage (Vdc) | 50 | 2000 | 1000 | | 630 | | 500 | | 250 | 200 | 1000 | 630 | | 500 | | 250 | 200 | 50 | | | | | 1000 |
| Cap. / TC Code | UJ | U2J | C0G | U2J | C0G | U2J | C0G | U2J | U2J | U2J | U2J | C0G | U2J | C0G | U2J | U2J | U2J | C0G | CH | SL | U2J | UJ | U2J |
| 10pF | | p67 | p67 | p67 | p67 | p67 | p68 | p68 | | | | | | | | | | | | | | | |
| 12pF | | p67 | p67 | p67 | p67 | p67 | p68 | p68 | | | | | | | | | | | | | | | |
| 15pF | | p67 | p67 | p67 | p67 | p67 | p68 | p68 | | | | | | | | | | | | | | | |
| 18pF | | p67 | p67 | p67 | p67 | p67 | p68 | p68 | | | | | | | | | | | | | | | |
| 22pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 27pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 33pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 39pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 47pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 56pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 68pF | | p67 | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 82pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 100pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 120pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 150pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 180pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 220pF | | | p67 | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 270pF | | | | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 330pF | | | | p67 | p67 | p68 | p68 | p68 | | | | | | | | | | | | | | | |
| 390pF | | | | | p67 | p68 | p68 | p68 | | | p68 | | | | | | | | | | | | |
| 470pF | | | | | p67 | p68 | p68 | p68 | | | p68 | | | | | | | | | | | | |
| 560pF | | | | | p67 | p68 | p68 | p68 | | | p68 | | | | | | | | | | | | |
| 680pF | | | | | | p68 | | p68 | | | p68 | p68 | | p68 | | | | | | | | | |
| 820pF | | | | | | p68 | | p68 | | | | p68 | | p68 | | | | | | | | | p69 |
| 1000pF | | | | | | p68 | | p68 | | | | p68 | | p68 | | | | | | | | | p69 |
| 1200pF | | | | | | p68 | | p68 | | | | | | | | | | | | | | | |
| 1500pF | | | | | | p68 | | p68 | | | | | | | | | | | | | | | |
| 1800pF | | | | | | p68 | | p68 | | | | | | | | | | | | | | | |
| 2200pF | | | | | | p68 | | p68 | | | | | | | | | | | | | | | |
| 2700pF | | | | | | | | | p68 | p68 | | | p68 | | p68 | | | | | | | | |
| 3300pF | | | | | | | | | p68 | p68 | | | p68 | | p68 | | | | | | | | |
| 3900pF | | | | | | | | | p68 | p68 | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | p68 | p68 | | | | | | | | | | | | | |
| 5600pF | | | | | | | | | p68 | p68 | | | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | | | p68 | p68 | | | | | | |
| 8200pF | | | | | | | | | | | | | | | | p68 | p68 | | | | | | |
| 10000pF | | | | | | | | | | | | | | | | p68 | p68 | | | | | | |
| 12000pF | | | | | | | | | | | | | | | | p68 | | | | | | | |
| 15000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 18000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 22000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 27000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 39000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 47000pF | | | | | | | | | | | | | | | | | | p68 | p69 | | | | |
| 56000pF | p67 | | | | | | | | | | | | | | | | | p69 | p69 | | | | |
| 68000pF | | | | | | | | | | | | | | | | | | | | p69 | p69 | p69 | |
| 82000pF | | | | | | | | | | | | | | | | | | | | p69 | p69 | p69 | |
| 0.10μF | | | | | | | | | | | | | | | | | | | | p69 | p69 | p69 | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 3.2×1.6 | | | | | 3.2×2.5 | | | | | | | | | | | | | | | 4.5×2.0 | 4.5×3.2 | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.8 | | | | | 1.0 | | | 1.25 | | | | 1.5 | | | | 2.0 | | | | 1.0 | 1.5 | |
| Rated Voltage (Vdc) | 630 | 500 | 250 | 50 | | 2000 | 630 | 500 | 2000 | 1000 | 630 | 500 | 1000 | 630 | 500 | 250 | 1000 | 630 | 500 | 250 | 3150 | 1000 | 630 |
| Cap. / TC Code | U2J | U2J | U2J | C0G | CH | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J |
| 27pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 33pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 39pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 47pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 56pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 68pF | | | | | | | | | | | | | | | | | | | | | p69 | | |
| 82pF | | | | | | p69 | | | | | | | | | | | | | | | p69 | | |
| 100pF | | | | | | p69 | | | | | | | | | | | | | | | p69 | | |
| 120pF | | | | | | p69 | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | p69 | | | | | | | | | | | | | | | | | |
| 180pF | | | | | | | | | p69 | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | p69 | | | | | | | | | | | | | | |
| 270pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 390pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | |
| 560pF | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1200pF | | | | | | | p69 | p69 | | p69 | | | | | | | | | | | | | |
| 1500pF | | | | | | | p69 | p69 | | | | | p69 | | | | | | | | | | |
| 1800pF | | | | | | | p69 | p69 | | | | | | | | | p69 | | | | | | |
| 2200pF | | | | | | | p69 | p69 | | | | | | | | | p69 | | | | | | |
| 2700pF | | | | | | | | | | | | | | | | | | | | | | p69 | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | p69 | |
| 3900pF | p69 | p69 | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | p69 | p69 | | | | | | | | | | | | | | | | | | | | | |
| 5600pF | | | | | | | | | | | p69 | p69 | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | p69 | p69 | | | | | | | | |
| 8200pF | | | | | | | | | | | | | | | | | | p69 | p69 | | | | |
| 10000pF | | | | | | | | | | | | | | | | | | p69 | p69 | | | | |
| 12000pF | | | | | | | | | | | | | | | | | | | | | | | p69 |
| 15000pF | | | p69 | | | | | | | | | | | | | | | | | | | | |
| 18000pF | | | p69 | | | | | | | | | | | | | | | | | | | | |
| 22000pF | | | p69 | | | | | | | | | | | | | | | | | | | | |
| 27000pF | | | | | | | | | | | | | | | | p69 | | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | p69 | | | |
| 39000pF | | | | | | | | | | | | | | | | | | | | p69 | | | |
| 47000pF | | | | | | | | | | | | | | | | | | | | p69 | | | |
| 56000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 68000pF | | | | p69 | p69 | | | | | | | | | | | | | | | | | | |
| 82000pF | | | | p69 | p69 | | | | | | | | | | | | | | | | | | |
| 0.10μF | | | | p69 | p69 | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| L×W (mm) | 4.5×3.2 | | | | 5.7×5.0 | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.5 | 2.0 | | | 1.5 | | | 2.0 | | |
| Rated Voltage (Vdc) | 500 | 1000 | 630 | 500 | 1000 | 630 | 500 | 1000 | 630 | 500 |
| Cap. / TC Code | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J | U2J |
| 3900pF | | p69 | | | | | | | | |
| 4700pF | | p69 | | | | | | | | |
| 5600pF | | | | | p69 | | | | | |
| 6800pF | | | | | p69 | | | | | |
| 8200pF | | | | | | | | p69 | | |
| 10000pF | | | | | | | | p69 | | |
| 12000pF | p69 | | | | | | | | | |
| 15000pF | | | p69 | p69 | | | | | | |
| 18000pF | | | p69 | p69 | | | | | | |
| 22000pF | | | p69 | p69 | | | | | | |
| 27000pF | | | | | | p69 | p69 | | | |
| 33000pF | | | | | | | | | p69 | p69 |
| 39000pF | | | | | | | | | p69 | p69 |
| 47000pF | | | | | | | | | p69 | p70 |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GRM Series High Dielectric Constant Type

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 0.4×0.2 | | | | 0.6×0.3 | | | | | | | | | | 1.0×0.5 | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.22 | | | | 0.33 | | | | | | | | | | 0.22 | | | | | | |
| Rated Voltage (Vdc) | 10 | | 6.3 | 4 | 50 | | 25 | | 16 | | 10 | | 6.3 | | 4 | 10 | 6.3 | | 4 | | 2.5 |
| Cap. / TC Code | X7R | X5R, B | X5R, B | X5R | X7R | B | X7R, R | X5R, B | X7R, R | X5R, B | X7R, R | X5R, B | X7R, R | X6S | X5R, B | X6S | X5R, B | X6S | X5R, B | X7T | X6Δ | X5R | X7T |
| 100pF | p71 | p71 p71 | | | p71 | p72 | p72 | | | | | | | | | | | | | | | | |
| 150pF | p71 | p71 p71 | | | p72 | p72 | p72 | | | | | | | | | | | | | | | | |
| 220pF | p71 | p71 p71 | | | p72 | p72 | p72 | | | | | | | | | | | | | | | | |
| 330pF | p71 | p71 p71 | | | p72 | p72 | p72 | | | | | | | | | | | | | | | | |
| 470pF | p71 | p71 p71 | | | p72 | p72 | p72 | | | | | | | | | | | | | | | | |
| 680pF | p71 | p71 p71 | | | p72 | p72 | p72 | | | | | | | | | | | | | | | | |
| 820pF | p71 | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | p71 | p71 p71 | p71 p71 | | p72 | p72 | p72 p72 | p72 | | | | | | | | | | | | | | | |
| 1500pF | | p71 p71 | p71 p71 | | p72 | p72 | p72 p72 | p72 | | | | | | | | | | | | | | | |
| 2200pF | | p71 p71 | p71 p71 | | | | p72 | p72 | p72 p72 | p72 | | | | | | | | | | | | | |
| 3300pF | | p71 p71 | p71 p71 | | | | p72 | p72 | p72 p72 | p72 | | | | | | | | | | | | | |
| 4700pF | | p71 p71 | p71 p71 | | | | | p72 | | | p72 p72 | p73 p73 | p73 p73 | | p73 | | | | | | | | |
| 6800pF | | p71 p71 | p71 p71 | | | | | p72 | | | p72 p72 | p73 p73 | p73 p73 | | p73 | | | | | | | | |
| 10000pF | | p71 p71 | p71 p71 | | | | p72 p72 | | p72 p72 | | p72 p72 | | p73 p73 | | | | | | | | | | |
| 15000pF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | p73 | | | | | | | | |
| 22000pF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | p73 | | | | | | | | |
| 33000pF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | p73 | | | | | | | | |
| 47000pF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | | | | | | | | | |
| 68000pF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | | | | | | | | | |
| 0.10μF | | | p71 | p71 | | | | | p72 p72 | | | p73 p73 | | p73 | | | p73 p73 | p73 | p73 p73 | p73 | p73 | | p73 |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | | p73 | | p73 | p73 | p73 | p73 p73 | p73 | p73 p73 | p73 | p73 | | p73 |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | p73 p73 | | p73 | | |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | | | | | | | | | | | | | | | | | | | p73 | | p73 | p73 | |
| 2.2μF | | | | | | | | | | | | | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | | | | | | | | | | | | | |
| 10μF | | | | | | | | | | | | | | | | | | | | | | | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 47μF | | | | | | | | | | | | | | | | | | | | | | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 1.0×0.5 | | | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.3 | | | | | | | 0.33 | | | | 0.55 | | | | | | | | | | | | |
| Rated Voltage (Vdc) | 50 | | 25 | | 16 | | 10 | 10 | 6.3 | | 4 | 100 | 50 | | 25 | | 16 | | 10 | | 6.3 | | | |
| Cap. / TC Code | X7R, R | B | X7R | B | X7R | B | X5R | X5R, B | X6T | X5R, B | X6T | X7R | X7R, R | X5R, B | X7R, R | X5R, B | X7R, R | X5R, B | X6S | X5R, B | X7R | X6S | X5R, B |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | p74 | p73 | p74 | | | | | | | | | p74 | p74 | p74 | p74 | | | | | | | | | |
| 330pF | p74 | p73 | p74 | | | | | | | | | p74 | p74 | p74 | p74 | | | | | | | | | |
| 470pF | p74 | p73 | p74 | | | | | | | | | p74 | p74 | p74 | p74 | | | | | | | | | |
| 680pF | p74 | p74 | p74 | | | | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | p74 | p74 | p74 | | | | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 1500pF | p74 | p74 | p74 | | | | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 2200pF | | | p74 | p74 | | | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 3300pF | | | | | p74 | p74 | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 4700pF | | | | | p74 | p74 | | | | | | p74 | p74 | p74 | p75 | | | | | | | | | |
| 6800pF | | | | | p74 | p74 | | | | | | | p74 | p74 | p75 | p75 | | | | | | | | |
| 10000pF | | | | | p74 | p74 | | | | | | | p74 | p74 | p75 | p75 | p75 | p75 | | | | | | |
| 15000pF | | | | | | | p74 | | | | | | p74 | p75 | p75 | p75 | p75 | | | | | | | |
| 22000pF | | | | | | | p74 | | | | | | p74 | p75 | p75 | p75 | p75 | | | | | | | |
| 33000pF | | | | | | | p74 | | | | | | p74 | p74 | p75 | p75 | p75 | | | | | | | |
| 47000pF | | | | | | | | | | | | | p74 | p74 | p75 | p75 | p75 | | | | | | | |
| 68000pF | | | | | | | | | | | | | p74 | p74 | p75 | p75 | p75 | p75 | p75 | | | | | |
| 0.10μF | | | | | | | | | | | | | p74 | p74 | p75 | p75 | p75 | p75 | | | | | | |
| 0.15μF | | | | | | | | | | | | | | | | | | p75 | | | p75 | p75 | | p75 | p76 |
| 0.22μF | | | | | | | | | | | | | | | | | | p75 | p75 | | p75 | p75 | | p75 | p76 |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | p75 | p75 | | p75 | p76 |
| 0.47μF | | | | | | | | | | | | | | | | | p75 | | | | p75 | p75 | | p75 | p76 |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | p75 | p75 | | p75 | p76 |
| 1.0μF | | | | | | | | p74 | p74 | p74 | p74 | p74 | | | | | p75 | p75 | p75 | p75 | | | p75 | | |
| 2.2μF | | | | | | | | | | | | | | | | | | | | | p75 | | p75 | p75 | |
| 4.7μF | | | | | | | | | | | | | | | | | | | | | | | | |
| 10μF | | | | | | | | | | | | | | | | | | | | | | | | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | | | |
| 47μF | | | | | | | | | | | | | | | | | | | | | | | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 1.0×0.5 | | | | | | | | | | | | | | 1.6×0.8 | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.55 | 0.6 | | | | | | 0.7 | | | | | | | 0.5 | | 0.9 | | | | |
| Rated Voltage (Vdc) | 4 | 35 | 25 | 16 | 6.3 | 4 | 2.5 | 25 | 16 | | 10 | | 6.3 | 4 | 2.5 | 25 | 16 | 250 | 200 | 100 | 50 | 25 |
| Cap. / TC Code | X7R | X5R | X6S | X6S | X5R, B | X5R, B | X6T | X5R | X6S | X5R | X7S | X6S | X7S | X5R | X5R | X5R, B | X5R, B | X7R | X7R | X7R | X7R, R | X5R, B | X7R, R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 330pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 470pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 680pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 1500pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 2200pF | | | | | | | | | | | | | | | | | | p76 | p76 | p76 | p76 p76 | p77 | |
| 3300pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p76 | p77 | |
| 4700pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p76 | p77 | |
| 6800pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p77 | p77 | |
| 10000pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p77 | p77 | |
| 15000pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p77 | p77 | |
| 22000pF | | | | | | | | | | | | | | | | | | | | p76 | p76 p77 | p77 | |
| 33000pF | | | | | | | | | | | | | | | | | | | | | p76 p77 | p77 | p77 p77 |
| 47000pF | | | | | | | | | | | | | | | | | | | | | p76 p77 | p77 | p77 p77 |
| 68000pF | | | | | | | | | | | | | | | | | | | | | p76 p77 | p77 | p77 p77 |
| 0.10μF | | | | | | | | | | | | | | | | | | | | | p76 p77 | p77 | |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | | p77 | p77 p77 |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | | p77 | p77 p77 |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | p77 | |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | p76 | p76 | p76 | p76 | | | | | | | | | | | | p76 | p76 p76 p76 | | | | | p77 | p77 p77 |
| 2.2μF | | | | | | | | p76 | p76 | p76 | p76 | p76 | p76 | | | | | | | | | | |
| 4.7μF | | | | | p76 | p76 | p76 | p76 | p76 | | | | | | | | | | | | | | |
| 10μF | | | | | | | | | | | | | | p76 | p76 | | | | | | | | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 47μF | | | | | | | | | | | | | | | | | | | | | | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 1.6×0.8 | | | | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.9 | | | | | | | 0.95 | | | | | 1.0 | | | | | | | | | | | | |
| Rated Voltage (Vdc) | 25 | 16 | | | 10 | | 6.3 | 25 | 16 | | 10 | | 50 | 35 | | 25 | | | 16 | | 10 | 6.3 | |
| Cap. / TC Code | X5R, B | X7R, R | X6S | X5R, B | X7Δ | X5R, B | B | X5R | X6S | X5R, B | X7S | B | X5R | X6S | X5R | X7S | X6S | X5R | X7S | X6S | X7T | X7T | X5R, B |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 15000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 22000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 33000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 47000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 68000pF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.10μF | p77 | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.15μF | p77 | p77 | | | | | | | | | | | | | | | | | | | | | | | |
| 0.22μF | p77 p77 | p77 | | | | | | | | | | | | | | | | | | | | | | | |
| 0.33μF | | p77 p77 | | p77 | p78 | p78 p78 | | | | | | | | | | | | | | | | | | | |
| 0.47μF | p77 p77 | p77 p77 | | | | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | p77 p77 | | | p77 p78 | p78 | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | p77 p77 | p77 | | | | | | | | | | | | | | | | | | | | | | | |
| 2.2μF | p77 p77 | | p77 | p77 p78 | p78 | p78 | | | | | | | p78 | p78 | | p78 | p78 | | p78 | | | | | | |
| 4.7μF | | | | | | | | p78 | p78 | p78 p78 | p78 | | | | p78 | | p78 | | | | | | | | |
| 10μF | | | | | | | p78 | | | p78 | | p78 | | | | | | p78 | | p78 | p78 | p78 | | | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | | p78 | p78 | |
| 47μF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 1.6×0.8 | | 2.0×1.25 | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.0 | | 0.7 | 0.95 | | | | | | | | | | | | | | | | | | | 1.0 | |
| Rated Voltage (Vdc) | 4 | | 16 | 100 | 50 | | 35 | | 25 | | | 16 | | | 10 | | 6.3 | | 4 | | 2.5 | 250 | 200 |
| Cap. / TC Code | X6S | X5R, B | X6S | X7R | X7R, R | X5R, B | X6S | X5R | X7R, R | X6S | X5R, B | X7R, R | X6S | X5R, B | X7Δ | X5R, B | X6S | X5R, B | X6S | X5R | X6T | X7R | X7R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 150pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 220pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 330pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 470pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 680pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 820pF | | | | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 1000pF | | | | p78 | p78 | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | p78 | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | p78 | p78 | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | | | | | | | | | | |
| 10000pF | | | | | | | | | p78 | | | | | | | | | | | | | | |
| 15000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 22000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 47000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 68000pF | | | | | | | | | p78 | | | | | | | | | | | | | | |
| 0.10μF | | | | | | | | | p78 | | | | | | | | | | | | | | |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.33μF | | | | | p78 | p78 | | | | | | p78 | | | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | | | | | | | | | p78 | | | p78 | | | | | | | | | | | |
| 1.0μF | | | p78 | | p78 | | | | p78 | | | | | | | | | | | | | | |
| 2.2μF | | | | | p78 | p78 | p78 | | | p78 | p78 | p78 | | | p79 | | | | | | | | |
| 4.7μF | | | | | | | | p78 | | | p78 | | p78 | p78 | p79 | | | | | | | | |
| 10μF | | | | | | | | | | | p78 | | | p78 | | | p79 | | p79 | | | | |
| 22μF | p78 | p78 | p78 | | | | | | | | | | | | | p79 | | p79 | | | | | |
| 47μF | | | | | | | | | | | | | | | | | | | | p79 | p79 | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 2.0×1.25 | | | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.0 | | 1.35 | | | | | | | | 1.4 | | | | | | | | | | | | 1.45 | |
| Rated Voltage (Vdc) | 50 | 16 | 100 | 50 | | 25 | | | 16 | | 50 | 25 | | 16 | | 10 | | 6.3 | | 4 | | 250 | 200 |
| Cap. / TC Code | X7R | X5R | X7R | X7R, R | B | R | X6S | X5R, B | X7R | X5R, B | X5R, B | X7R, R | X5R, B | X7R | X6S | X7R | B | X7R | X6S | X7U | X6S | X7R | X7R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | | | | | | | | | | |
| 10000pF | | | p79 | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 15000pF | | | p79 | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 22000pF | p79 | | p79 | | | | | | | | | | | | | | | | | | | p79 | p79 |
| 33000pF | | | p79 | | | | | | | | | | | | | | | | | | | | |
| 47000pF | | | p79 | p79 | | | | | | | | | | | | | | | | | | | |
| 68000pF | | | p79 | p79 | | | | | | | | | | | | | | | | | | | |
| 0.10µF | | | p79 | p79 | p79 | | | | | | | | | | | | | | | | | | |
| 0.15µF | | | | p79 | p79 | p79 | | | | | | | | | | | | | | | | | |
| 0.22µF | | | | p79 | p79 | | | | | | | | | | | | | | | | | | |
| 0.33µF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.47µF | | | | p79 | p79 | | | | | | | | | | | | | | | | | | |
| 0.68µF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0µF | | | | | | | | | | | | p79 | p79 | | | | | | | | | | |
| 2.2µF | | | | | | | | p79 | p79 | | p79 | p79 | | | | | | | | | | | |
| 4.7µF | | | | | | | p79 | p79 | p79 | | p79 | p79 | p79 | p79 | | p79 | | | | | | | |
| 10µF | | | | | | | | | | p79 | p79 | | p79 | p79 | p79 | p79 | | p79 | | | | | |
| 22µF | | p79 | | | | | | | | | | | | | | | p79 | | p79 | p79 | p79 | | |
| 47µF | | | | | | | | | | | | | | | | | | | | | | | |
| 100µF | | | | | | | | | | | | | | | | | | | | | | | |
| 150µF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 2.0×1.25 | | | | | | | | | | | | 3.2×1.6 | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.45 | | | | | | | | | | | | 0.95 | | | | | | 1.0 | | 1.25 | | |
| Rated Voltage (Vdc) | 25 | | 16 | | | 10 | | | 6.3 | | 4 | | 35 | 25 | 16 | 10 | 6.3 | | 630 | 500 | 1000 | 630 | 500 |
| Cap. / TC Code | X6S | X5R | X7S | X6S | X5R | X7T | X6S | X5R | X7T | X5R, B | X6S | X5R, B | X5R | R | X5R, B | X5R, B | X6S | X5R, B | X7R | X7R | X7R | X7R | X7R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | p80 | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | p80 | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | p80 | p80 | p80 | p80 | p80 |
| 1500pF | | | | | | | | | | | | | | | | | | | p80 | p80 | p80 | p80 | p80 |
| 2200pF | | | | | | | | | | | | | | | | | | | p80 | p80 | p80 | p80 | p80 |
| 3300pF | | | | | | | | | | | | | | | | | | | p80 | p80 | p80 | p80 | p80 |
| 4700pF | | | | | | | | | | | | | | | | | | | p80 | p80 | p80 | p80 | p80 |
| 6800pF | | | | | | | | | | | | | | | | | | | | | | p80 | p80 |
| 10000pF | | | | | | | | | | | | | | | | | | | | | | p80 | p80 |
| 15000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 22000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 47000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 68000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.10μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.33μF | | | | | | | | | | | | | | p80 | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | | | | | | | | | | | | | | | | | | | | | | | |
| 2.2μF | | | | | | | | | | | | | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | | | | | | | | | | | | | |
| 10μF | p79 | | p80 | | | | | | | | | | p80 | | p80 | p80 | | | | | | | |
| 22μF | | p80 | | p80 | p80 | p80 | p80 | p80 | p80 | | | | | | p80 | p80 | p80 | p80 | p80 | p80 | p80 | p80 | | |
| 47μF | | | | | | | | | | p80 | p80 | p80 | p80 | p80 | | | | | | | | | |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 3.2×1.6 | | | | | | | | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.25 | | | | | 1.8 | | | | | | | | | | | | | | | | | |
| Rated Voltage (Vdc) | 250 | 200 | 50 | | 25 | 1000 | 630 | 500 | 250 | 200 | 50 | | 25 | | 16 | | | 10 | | 6.3 | | | 4 |
| Cap. / TC Code | X7R | X7R | X7R | B | X5R | X7R | X7R | X7R | X7R | X7R | X7R | X5R, B | X7R | X5R, B | X7R | X6S | X5R, B | X7R | X5R, B | X7Δ | X6S | X5R, B | X7U |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | p80 | | | | | | | | | | | | | | | | | |
| 10000pF | | | | | | p80 | | | | | | | | | | | | | | | | | |
| 15000pF | p80 | p80 | | | | | p80 | p80 | | | | | | | | | | | | | | | |
| 22000pF | p80 | p80 | | | | | p80 | p80 | | | | | | | | | | | | | | | |
| 33000pF | | | | | | | | | p80 | p80 | | | | | | | | | | | | | |
| 47000pF | | | | | | | | | p80 | p80 | | | | | | | | | | | | | |
| 68000pF | p80 | p80 | | | | | | | | | | | | | | | | | | | | | |
| 0.10μF | | | | | | | | | p80 | p80 | | | | | | | | | | | | | |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.47μF | | | p80 | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | | | p80 | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | | | p80 | p80 | | | | | | | | | | | | | | | | | | | |
| 2.2μF | | | | | | | | | | | p80 | p80 | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | p80 | p80 | p80 | | p80 | | | | | | | | |
| 10μF | | | | | p80 | | | | | | | p80 | p80 | p80 | | | | | | | | | |
| 22μF | | | | | | | | | | | | | | p80 | | p80 | p80 | p80 | p81 | | p81 | | |
| 47μF | | | | | | | | | | | | | | | | | | | p81 | p81 | p81 | p81 | p81 | p81 | p81 |
| 100μF | | | | | | | | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 3.2×1.6 | | | | | | | 3.2×2.5 | | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.8 | 1.9 | | | | | | 1.5 | | | | | 1.8 | | | | 2.0 | | | | | 2.2 | 2.7 |
| Rated Voltage (Vdc) | 4 | 100 | 6.3 | | 4 | | | 1000 | 630 | 500 | 250 | 200 | 6.3 | 4 | | 2.5 | 1000 | 630 | 500 | 250 | 200 | 25 | 80 |
| Cap. / TC Code | X6S | X7R | X6T | X5R | X7U | X6T | X5R | X7R | X7R | X7R | X7R | X7R | X5S | X6T | X5S | X6T | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | | | p81 | | | | | | | | | | | | | | | |
| 10000pF | | | | | | | | p81 | | | | | | | | | | | | | | | |
| 15000pF | | | | | | | | | | | | | | | | | p81 | | | | | | |
| 22000pF | | | | | | | | | p81 | p81 | | | | | | | p81 | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | p81 | p81 | | | | |
| 47000pF | | | | | | | | | | | | | | | | | | p81 | p81 | | | | |
| 68000pF | | | | | | | | | | | p81 | p81 | | | | | | | | | | | |
| 0.10μF | | | | | | | | | | | | | | | | | | | | p81 | p81 | | |
| 0.15μF | | | | | | | | | | | p81 | p81 | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | | | | | | | | | | p81 | p81 | | |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | | | | | | | | | | | | | | | | | | | | | | | |
| 2.2μF | | p81 | | | | | | | | | | | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | | | | | | | | | | | | | p81 |
| 10μF | | | | | | | | | | | | | | | | | | | | | | p81 | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | | |
| 47μF | p81 | | | | | | | | | | | | | | | | | | | | | | |
| 100μF | | | p81 | p81 | p81 | p81 | p81 | | | | | | | | | | | | | | | | |
| 150μF | | | | | | | | | | | | | p81 | p81 | p81 | p81 | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 3.2×2.5 | | | | | | | | | | | | | | 4.5×3.2 | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 2.7 | | | | | | | | | | | | | | 1.5 | | | | 2.0 | | | |
| Rated Voltage (Vdc) | 63 | 50 | | 35 | | 25 | | 16 | | | 10 | | 6.3 | | 4 | 630 | 500 | 250 | 200 | 1000 | 630 | 500 | 250 |
| Cap. / TC Code | X7R | X7R | X5R, B | X7R | X5R, B | X7R | X5R, B | X7R | X6S | X5R, B | X7R | X5R, B | X7Δ | X5R, B | X7U | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 100pF | | | | | | | | | | | | | | | | | | | | | | | |
| 150pF | | | | | | | | | | | | | | | | | | | | | | | |
| 220pF | | | | | | | | | | | | | | | | | | | | | | | |
| 330pF | | | | | | | | | | | | | | | | | | | | | | | |
| 470pF | | | | | | | | | | | | | | | | | | | | | | | |
| 680pF | | | | | | | | | | | | | | | | | | | | | | | |
| 820pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 1500pF | | | | | | | | | | | | | | | | | | | | | | | |
| 2200pF | | | | | | | | | | | | | | | | | | | | | | | |
| 3300pF | | | | | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | | | | | |
| 6800pF | | | | | | | | | | | | | | | | | | | | | | | |
| 10000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 15000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 22000pF | | | | | | | | | | | | | | | | | | | | | | | |
| 33000pF | | | | | | | | | | | | | | | | | | | | p81 | | | |
| 47000pF | | | | | | | | | | | | | | | | | | | | p81 | | | |
| 68000pF | | | | | | | | | | | | | | | | p81 | p81 | | | | | | |
| 0.10μF | | | | | | | | | | | | | | | | | | | | | p81 | p81 | |
| 0.15μF | | | | | | | | | | | | | | | | | | p81 | p81 | | | | |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | | | p81 |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | | p81 |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | | p81 |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | | |
| 1.0μF | | | | | | | | | | | | | | | | | | | | | | | |
| 2.2μF | | | | | | | | | | | | | | | | | | | | | | | |
| 4.7μF | | p81 | | | | | | | | | | | | | | | | | | | | | |
| 10μF | p81 | p81 | p81 | p81 | p81 | p81 | p81 | | | | | | | | | | | | | | | | |
| 22μF | | | | | | p81 | p81 | p81 | p81 | | | | | | | | | | | | | | |
| 47μF | | | | | | | | | p81 | p81 | p81 | p81 | p81 | p81 | p81 | | | | | | | | |
| 100μF | | | | | | | | | | | | p81 | p81 | p81 | p81 | | | | | | | | |
| 150μF | | | | | | | | | | | | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| L×W (mm) | 4.5×3.2 | 5.7×5.0 | | | | |
|---|---|---|---|---|---|---|
| T max. (mm) | 2.0 | 2.0 | | | | |
| Rated Voltage (Vdc) | 200 | 1000 | 630 | 500 | 250 | 200 |
| Cap. / TC Code | X7R | X7R | X7R | X7R | X7R | X7R |
| 100pF | | | | | | |
| 150pF | | | | | | |
| 220pF | | | | | | |
| 330pF | | | | | | |
| 470pF | | | | | | |
| 680pF | | | | | | |
| 820pF | | | | | | |
| 1000pF | | | | | | |
| 1500pF | | | | | | |
| 2200pF | | | | | | |
| 3300pF | | | | | | |
| 4700pF | | | | | | |
| 6800pF | | | | | | |
| 10000pF | | | | | | |
| 15000pF | | | | | | |
| 22000pF | | | | | | |
| 33000pF | | | | | | |
| 47000pF | | | | | | |
| 68000pF | | p81 | | | | |
| 0.10μF | | p81 | | | | |
| 0.15μF | | | p81 | p81 | | |
| 0.22μF | p81 | | p81 | p81 | | |
| 0.33μF | p81 | | | | p82 | p82 |
| 0.47μF | p81 | | | | p82 | p82 |
| 0.68μF | | | | | p82 | p82 |
| 1.0μF | | | | | p82 | p82 |
| 2.2μF | | | | | | |
| 4.7μF | | | | | | |
| 10μF | | | | | | |
| 22μF | | | | | | |
| 47μF | | | | | | |
| 100μF | | | | | | |
| 150μF | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GJM Series Temperature Compensating Type

p00 ← Part Number List JIS: CK CJ CH EIA: C0G

| L×W (mm) | 0.4×0.2 | | 0.6×0.3 | | 1.0×0.5 | |
|---|---|---|---|---|---|---|
| T max. (mm) | 0.22 | | 0.33 | | 0.55 | |
| Rated Voltage (Vdc) | 25 | | 25 | | 50 | |
| Cap. / TC Code | C0G | CΔ | C0G | CΔ | C0G | CΔ |
| 0.10pF | | | | | p97 | p100 |
| 0.20pF | p84 | p87 | p90 | p93 | p97 | p100 |
| 1.0pF | p84 | p87 | p90 | p94 | p97 | p101 |
| 2.0pF | p84 | p87 | p91 | p94 | p97 | p101 |
| 3.0pF | p84 | p87 | p91 | p94 | p98 | p101 |
| 4.0pF | p85 | p88 | p91 | p94 | p98 | p101 |
| 5.0pF | p85 | p88 | p91 | p95 | p98 | p102 |
| 6.0pF | p85 | p88 | p92 | p95 | p98 | p102 |
| 7.0pF | p86 | p89 | p92 | p95 | p99 | p102 |
| 8.0pF | p86 | p89 | p92 | p96 | p99 | p103 |
| 9.0pF | p86 | p90 | p93 | p96 | p100 | p103 |
| 10pF | p87 | p90 | p93 | p97 | p100 | p103 |
| 11pF | p87 | p90 | p93 | p97 | p100 | p103 |
| 12pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 13pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 15pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 16pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 18pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 20pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 22pF | p87 | p90 | p93 | p97 | p100 | p104 |
| 24pF | | | p93 | p97 | p100 | p104 |
| 27pF | | | p93 | p97 | p100 | p104 |
| 30pF | | | p93 | p97 | p100 | p104 |
| 33pF | | | p93 | p97 | p100 | p104 |
| 36pF | | | | | p100 | p104 |
| 39pF | | | | | p100 | p104 |
| 43pF | | | | | p100 | p104 |
| 47pF | | | | | p100 | p104 |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GMA Series High Dielectric Constant Type

p00 ← Part Number List JIS: R B EIA: X7R X5R

| L×W (mm) | 0.38×0.38 | | 0.5×0.5 | | | | | | | | 0.8×0.8 | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.35 | | 0.4 | | | | | | | | 0.6 | | | | | | | |
| Rated Voltage (Vdc) | 10 | | 100 | 25 | | 10 | | | 6.3 | | 100 | 25 | | 10 | | | 6.3 | |
| Cap. / TC Code | X7R | R | X7R | X7R | B | X7R | R | B | X5R | B | X7R | X7R | B | X7R | R | B | X5R | B |
| 100pF | | | p106 | | | | | | | | | | | | | | | |
| 150pF | | | p106 | | | | | | | | | | | | | | | |
| 220pF | | | p106 | | | | | | | | | | | | | | | |
| 330pF | | | p106 | | | | | | | | | | | | | | | |
| 470pF | | | p106 | | | | | | | | | | | | | | | |
| 680pF | | | p106 | | | | | | | | | | | | | | | |
| 1000pF | | | p106 | | | | | | | | | | | | | | | |
| 1500pF | | | | p106 | p106 | | | | | | p106 | | | | | | | |
| 2200pF | | | | p106 | p106 | | | | | | p106 | | | | | | | |
| 3300pF | | | | p106 | p106 | | | | | | p106 | | | | | | | |
| 4700pF | | | | p106 | p106 | | | | | | p106 | | | | | | | |
| 6800pF | | | | | | p106 | p106 | p106 | | | p106 | | | | | | | |
| 10000pF | p106 | p106 | | | | p106 | p106 | p106 | | | | p106 | p106 | | | | | |
| 15000pF | | | | | | p106 | p106 | p106 | | | | p106 | p106 | | | | | |
| 22000pF | | | | | | p106 | p106 | p106 | | | | p106 | p106 | | | | | |
| 33000pF | | | | | | | | | | | | | | p106 | p106 | p106 | | |
| 47000pF | | | | | | | | | | | | | | p106 | p106 | p106 | | |
| 68000pF | | | | | | | | | | | | | | p106 | p106 | p106 | | |
| 0.10μF | | | | | | | | | p106 | p106 | | | | p106 | p106 | p106 | | |
| 0.47μF | | | | | | | | | | | | | | | | | p106 | p106 |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GMD Series High Dielectric Constant Type

p00 ← Part Number List JIS: R B EIA: X7R X5R

| L×W (mm) | 0.6×0.3 | | | | | | | | | | | 1.0×0.5 | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.33 | | | | | | | | | | | 0.55 | | | | | | | | | | |
| Rated Voltage (Vdc) | 25 | | | 16 | | | 10 | | | 6.3 | | 50 | | | 25 | | | 16 | | | 10 | |
| Cap. / TC Code | X7R | R | B | X7R | R | B | X7R | R | B | X5R | B | X7R | R | B | X7R | R | B | X7R | R | B | X5R | B |
| 100pF | p108 | p108 | p108 | | | | | | | | | | | | | | | | | | | |
| 120pF | p108 | p108 | p108 | | | | | | | | | | | | | | | | | | | |
| 150pF | p108 | p108 | p108 | | | | | | | | | | | | | | | | | | | |
| 180pF | p108 | p108 | p108 | | | | | | | | | | | | | | | | | | | |
| 220pF | p108 | p108 | p108 | | | | | | | | | p108 | p108 | p109 | | | | | | | | |
| 270pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 330pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 390pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 470pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 560pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 680pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 820pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 1000pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 1200pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 1500pF | p108 | p108 | p108 | | | | | | | | | p108 | p109 | p109 | | | | | | | | |
| 1800pF | | | | p108 | p108 | p108 | | | | | | p108 | p109 | p109 | | | | | | | | |
| 2200pF | | | | p108 | p108 | p108 | | | | | | p108 | p109 | p109 | | | | | | | | |
| 2700pF | | | | p108 | p108 | p108 | | | | | | p108 | p109 | p109 | | | | | | | | |
| 3300pF | | | | p108 | p108 | p108 | | | | | | p108 | p109 | p109 | | | | | | | | |
| 3900pF | | | | | | | p108 | p108 | p108 | | | p108 | p109 | p109 | | | | | | | | |
| 4700pF | | | | | | | p108 | p108 | p108 | | | p108 | p109 | p109 | | | | | | | | |
| 5600pF | | | | | | | p108 | p108 | p108 | | | | | | p109 | p109 | p109 | | | | | |
| 6800pF | | | | | | | p108 | p108 | p108 | | | | | | p109 | p109 | p109 | | | | | |
| 8200pF | | | | | | | p108 | p108 | p108 | | | | | | p109 | p109 | p109 | | | | | |
| 10000pF | | | | | | | p108 | p108 | p108 | | | | | | p109 | p109 | p109 | | | | | |
| 12000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 15000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 18000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 22000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 27000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 33000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 39000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 47000pF | | | | | | | | | | | | | | | p109 | p109 | p109 | | | | | |
| 56000pF | | | | | | | | | | p108 | p108 | | | | | | | p109 | p109 | p109 | | |
| 68000pF | | | | | | | | | | p108 | p108 | | | | | | | p109 | p109 | p109 | | |
| 82000pF | | | | | | | | | | p108 | p108 | | | | | | | p109 | p109 | p109 | | |
| 0.10μF | | | | | | | | | | p108 | p108 | | | | | | | p109 | p109 | p109 | | |
| 0.12μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.15μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.18μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.22μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.27μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.39μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | p109 | p109 |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GQM Series Temperature Compensating Type

p00 ← Part Number List JIS: CK CJ CH EIA: C0G

| L×W (mm) | 1.6×0.8 | | | | | 2.0×1.25 | | | | | 2.8×2.8 |
|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.8 | 0.9 | | | | 0.95 | | | | 1.0 | 1.35 |
| Rated Voltage (Vdc) | 250 | 100 | | 50 | | 100 | | 50 | | 250 | 500 |
| Cap. / TC Code | C0G | C0G | CΔ | C0G | CH | C0G | CΔ | C0G | CH | C0G | C0G |
| 1.0pF | p111 | p111 | p112 | | | p113 | p114 | | | p116 | p117 |
| 2.0pF | p111 | p112 | p112 | | | p114 | p114 | | | p116 | p117 |
| 3.0pF | p111 | p112 | p112 | | | p114 | p114 | | | p116 | p117 |
| 4.0pF | p111 | p112 | p112 | | | p114 | p114 | | | p116 | p117 |
| 5.0pF | p111 | p112 | p112 | | | p114 | p114 | | | p116 | p117 |
| 6.0pF | p111 | p112 | p112 | | | p114 | p115 | | | p116 | p117 |
| 7.0pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 8.0pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 9.0pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 10pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 11pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 12pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 13pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 15pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 16pF | p111 | | | p112 | p113 | p114 | p115 | | | p116 | p117 |
| 18pF | p111 | | | p113 | p113 | p114 | p115 | | | p116 | p117 |
| 20pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 22pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 24pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 27pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 30pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 33pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 36pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 39pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 43pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 47pF | p111 | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 51pF | | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 56pF | | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 62pF | | | | p113 | p113 | | | p115 | p115 | p116 | p117 |
| 68pF | | | | p113 | p113 | | | p115 | p115 | p116 | p118 |
| 75pF | | | | p113 | p113 | | | p115 | p115 | p116 | p118 |
| 82pF | | | | p113 | p113 | | | p115 | p115 | p116 | p118 |
| 91pF | | | | p113 | p113 | | | p115 | p115 | p116 | p118 |
| 100pF | | | | p113 | p113 | | | p115 | p115 | p117 | p118 |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ GRJ Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7R

| L×W (mm) | 2.0×1.25 | | 3.2×1.6 | | | | | | 3.2×2.5 | | | | | | 4.5×3.2 | | | | | 5.7×5.0 | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.0 | 1.45 | 1.25 | | | 1.8 | | | 1.5 | | | 2.0 | | | 1.5 | | 2.0 | | | 2.0 | | |
| Rated Voltage (Vdc) | 250 | 250 | 1000 | 630 | 250 | 1000 | 630 | 250 | 1000 | 630 | 250 | 1000 | 630 | 250 | 630 | 250 | 1000 | 630 | 250 | 1000 | 630 | 250 |
| Cap. / TC Code | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 470pF | | | p120 | | | | | | | | | | | | | | | | | | | |
| 680pF | | | p120 | | | | | | | | | | | | | | | | | | | |
| 1000pF | p120 | | p120 | p120 | | | | | | | | | | | | | | | | | | |
| 1500pF | p120 | | p120 | p120 | | | | | | | | | | | | | | | | | | |
| 2200pF | p120 | | p120 | p120 | | | | | | | | | | | | | | | | | | |
| 3300pF | p120 | | p120 | p120 | | | | | | | | | | | | | | | | | | |
| 4700pF | p120 | | p120 | p120 | | | | | | | | | | | | | | | | | | |
| 6800pF | p120 | | | p120 | | p120 | | | p120 | | | | | | | | | | | | | |
| 10000pF | | p120 | | p120 | | p120 | | | p120 | | | | | | | | | | | | | |
| 15000pF | | p120 | | | p120 | | p120 | | | | | p120 | | | | | | | | | | |
| 22000pF | | p120 | | | p120 | | p120 | | | p120 | | p120 | | | | | | | | | | |
| 33000pF | | | | | | | | p120 | | | | | p120 | | | | p120 | | | | | |
| 47000pF | | | | | | | | p120 | | | | | p120 | | | | p120 | | | | | |
| 68000pF | | | | | p120 | | | | | | p120 | | | | p120 | | | | | p120 | | |
| 0.10μF | | | | | | | | p120 | | | | | | p120 | | | | p120 | | p120 | | |
| 0.15μF | | | | | | | | | | | p120 | | | | | p120 | | | | | p120 | |
| 0.22μF | | | | | | | | | | | | | | p120 | | | | p120 | | | p120 | |
| 0.33μF | | | | | | | | | | | | | | | | | | p120 | | | | p120 |
| 0.47μF | | | | | | | | | | | | | | | | | | p120 | | | | p120 |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | p120 |
| 1.0μF | | | | | | | | | | | | | | | | | | | | | | p120 |

## ■ GR3 Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7T

| L×W (mm) | 2.0×1.25 | | 3.2×1.6 | | | | | | | | 3.2×2.5 | | | | | 4.5×3.2 | | | | 5.7×5.0 | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.0 | 1.45 | 1.0 | | 1.25 | | | 1.8 | | | 1.5 | | 2.0 | | | 1.5 | 2.0 | | | 2.0 | | | 2.7 | | |
| Rated Voltage (Vdc) | 250 | 250 | 450 | 250 | 630 | 450 | 250 | 630 | 450 | 250 | 630 | 250 | 630 | 450 | 250 | 250 | 630 | 450 | 250 | 630 | 450 | 250 | 630 | 450 | 250 |
| Cap. / TC Code | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T |
| 10000pF | p122 | | p122 | | p122 | | | | | | | | | | | | | | | | | | | | |
| 15000pF | p122 | | p122 | | | | | p122 | | | | | | | | | | | | | | | | | |
| 22000pF | | p122 | | | | p122 | | | | | p122 | | | | | | | | | | | | | | |
| 33000pF | | | | p122 | | p122 | | | | | | | p122 | | | | | | | | | | | | |
| 47000pF | | | | | | | p122 | | p122 | | | | p122 | | | | | | | | | | | | |
| 68000pF | | | | | | | | | | p122 | | | | p122 | | | p122 | | | | | | | | |
| 0.10μF | | | | | | | | | | | | p122 | | p122 | | | | | | p122 | | | | | |
| 0.15μF | | | | | | | | | | | | | | | p122 | | | p122 | | p122 | | | | | |
| 0.22μF | | | | | | | | | | | | | | | | p122 | | | | | p122 | | p122 | | |
| 0.27μF | | | | | | | | | | | | | | | | | | | | | | | p122 | | |
| 0.33μF | | | | | | | | | | | | | | | | | | | p122 | | p122 | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | p122 | p122 | | | |
| 0.56μF | | | | | | | | | | | | | | | | | | | | | | | | p122 | |
| 0.68μF | | | | | | | | | | | | | | | | | | | | | | p122 | | | |
| 1.0μF | | | | | | | | | | | | | | | | | | | | | | | | | p122 |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ KRM Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7R X6S X5R

| L×W (mm) | 2.2×1.25 | | 3.5×1.7 | | | | | 3.6×1.7 | 3.7×1.85 | 6.1×5.3 | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 1.9 | | 2.0 | 2.9 | | | | 2.9 | 2.9 | 3.0 | | | | | | | | 3.9 | | | | |
| Rated Voltage (Vdc) | 25 | 16 | 25 | 100 | 50 | 35 | 25 | 50 | 100 | 1000 | 630 | 250 | 100 | 63 | 50 | 35 | 25 | 100 | 63 | 50 | 35 | 25 |
| Cap. / TC Code | X5R | X5R | X5R | X7R | X7R | X6S | X6S | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 68000pF | | | | | | | | | | p125 | | | | | | | | | | | | |
| 0.10μF | | | | | | | | | | p125 | | | | | | | | | | | | |
| 0.15μF | | | | | | | | | | | p125 | | | | | | | | | | | |
| 0.22μF | | | | | | | | | | | p125 | | | | | | | | | | | |
| 0.33μF | | | | | | | | | | | | | | | | | | | | | | |
| 0.47μF | | | | | | | | | | | | | | | | | | | | | | |
| 0.68μF | | | | | | | | | | | | p125 | | | | | | | | | | |
| 1.0μF | | | | p125 | | | | | | | | p125 | | | | | | | | | | |
| 1.5μF | | | | | | | | | | | | | | | | | | | | | | |
| 2.2μF | | | | | | | | p125 | p125 | | | | | | | | | | | | | |
| 4.7μF | | | | | p125 | | | | | | | | p125 | p125 | p125 | | | | | | | |
| 6.8μF | | | | | | | | | | | | | | | | | | p125 | | | | |
| 10μF | p125 | p125 | p125 | | | p125 | p125 | | | | | | | | | p125 | | | p125 | p125 | | |
| 15μF | | | | | | | | | | | | | | | | | p125 | | | | | |
| 17μF | | | | | | | | | | | | | | | | | | | | | p125 | |
| 22μF | | | | | | | | | | | | | | | | | | | | | | p125 |
| 33μF | | | | | | | | | | | | | | | | | | | | | | |
| 47μF | | | | | | | | | | | | | | | | | | | | | | |

| L×W (mm) | 6.1×5.3 | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 5.0 | | | | | | 6.7 | | | | |
| Rated Voltage (Vdc) | 1000 | 630 | 250 | 100 | 35 | 25 | 100 | 63 | 50 | 35 | 25 |
| Cap. / TC Code | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 68000pF | | | | | | | | | | | |
| 0.10μF | | | | | | | | | | | |
| 0.15μF | p125 | | | | | | | | | | |
| 0.22μF | p125 | | | | | | | | | | |
| 0.33μF | | p125 | | | | | | | | | |
| 0.47μF | | p125 | | | | | | | | | |
| 0.68μF | | | | | | | | | | | |
| 1.0μF | | | | | | | | | | | |
| 1.5μF | | | p125 | | | | | | | | |
| 2.2μF | | | p125 | | | | | | | | |
| 4.7μF | | | | | | | | | | | |
| 6.8μF | | | | | | | | | | | |
| 10μF | | | | p125 | | | | | | | |
| 15μF | | | | | | | p125 | | | | |
| 17μF | | | | | | | | | | | |
| 22μF | | | | | p125 | | | p125 | p125 | | |
| 33μF | | | | | | p125 | | | | p125 | |
| 47μF | | | | | | | | | | | p125 |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ KR3 Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7T

| L×W (mm) | 6.1×5.3 | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 3.0 | | | 3.9 | | | 5.0 | | 6.7 | | |
| Rated Voltage (Vdc) | 630 | 450 | 250 | 630 | 450 | 250 | 450 | 250 | 630 | 450 | 250 |
| Cap. / TC Code | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T | X7T |
| 0.10μF | p128 | | | | | | | | | | |
| 0.15μF | p128 | | | | | | | | | | |
| 0.22μF | | p128 | | p128 | | | | | | | |
| 0.27μF | | | | p128 | | | | | | | |
| 0.33μF | | p128 | | | | | | | | | |
| 0.47μF | | p128 | p128 | | | | | | p128 | | |
| 0.56μF | | | | | p128 | | | | p128 | | |
| 0.68μF | | | p128 | | | | p128 | | | | |
| 1.0μF | | | | | | p128 | p128 | | | | |
| 1.2μF | | | | | | | | | | p128 | |
| 1.5μF | | | | | | | | p128 | | | |
| 2.2μF | | | | | | | | | | | p128 |

## ■ LLA Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7R X7S

| L×W (mm) | 1.6×0.8 | 2.0×1.25 | | | | | | | | | | 3.2×1.6 | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.55 | 0.55 | | | | | 0.95 | | | | | 0.55 | | | 0.95 | | 1.25 | |
| Rated Voltage (Vdc) | 4 | 25 | 16 | 10 | 6.3 | 4 | 25 | 16 | 10 | 6.3 | 4 | 16 | 10 | 6.3 | 16 | 10 | 16 | 10 |
| Cap. / TC Code | X7S | X7R | X7R | X7R | X7R | X7S | X7R | X7R | X7R | X7R | X7S | X7R | X7R | X7R | X7R | X7R | X7R | X7R |
| 10000pF | | p130 | | | | | p130 | | | | | | | | | | | |
| 22000pF | | p130 | | | | | p130 | | | | | | | | | | | |
| 47000pF | | | p130 | | | | p130 | | | | | | | | | | | |
| 0.10μF | p130 | | p130 | | | | | p130 | | | | | | | | | | |
| 0.22μF | p130 | | | p130 | | | | p130 | | | | p130 | | | | | | |
| 0.47μF | p130 | | | | p130 | | | | p130 | | | | p130 | | p130 | | | |
| 1.0μF | | | | | | p130 | | | | p130 | | | | p130 | | p130 | p130 | |
| 2.2μF | p130 | | | | | | | | | | p130 | | | p130 | | | | p130 |
| 4.7μF | | | | | | p130 | | | | | | | | | | | | |

# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

## ■ LLL Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7R X7S X6S X5R

| L×W (mm) | 0.5×1.0 | | | 0.6×1.0 | 0.8×1.6 | | | | | | | | | | 1.25×2.0 | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.35 | | | 0.45 | 0.5 | | | | 0.55 | 0.6 | | | | | 0.5 | | | | | | 0.7 | |
| Rated Voltage (Vdc) | 6.3 | 4 | | 4 | 25 | 16 | 10 | 4 | 4 | 50 | 25 | 16 | 10 | 4 | 50 | 25 | 16 | 10 | 6.3 | 4 | 50 | 25 |
| Cap. / TC Code | X6S | X7S | X6S | X5R | X7R | X7R | X7R | X7S | X7S | X7R | X7R | X7R | X7R | X7S | X7R | X7R | X7R | X7R | X7R | X7S | X7R | X7R |
| 2200pF | | | | | | | | | | p132 | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | p132 | | | | | | | | | | | | |
| 10000pF | | | | | p132 | | | | | | p132 | | | | p132 | | | | | | p132 | |
| 22000pF | | | | | | p132 | | | | | p132 | | | | | p132 | | | | | p132 | |
| 47000pF | | | | | | p132 | | | | | | p132 | | | | | p132 | | | | | p132 |
| 0.10μF | p132 | | | | | | p132 | | | | | | p132 | | | | p132 | | | | | p132 |
| 0.22μF | p132 | | | | | | | p132 | | | | | p132 | | | | | p132 | | | | |
| 0.47μF | | p132 | | | | | | | | | | | | p132 | | | | | p132 | | | |
| 1.0μF | | | p132 | | | | | | | | | | | | | | | | | p132 | | |
| 2.2μF | | | | | | | | | p132 | | | | | | | | | | | | | |
| 4.3μF | | | | p132 | | | | | | | | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | | | | | | | | | | | | |
| 10μF | | | | | | | | | | | | | | | | | | | | | | |

| L×W (mm) | 1.25×2.0 | | | | 1.6×3.2 | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.7 | 0.95 | | | 0.5 | | | | 0.8 | | | | | 1.25 | | | | | |
| Rated Voltage (Vdc) | 10 | 16 | 10 | 4 | 50 | 25 | 16 | 10 | 50 | 25 | 16 | 10 | 6.3 | 50 | 25 | 16 | 10 | 6.3 | |
| Cap. / TC Code | X7R | X7R | X7R | X7S | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X7R | X5R |
| 2200pF | | | | | | | | | | | | | | | | | | | |
| 4700pF | | | | | | | | | | | | | | | | | | | |
| 10000pF | | | | | p132 | | | | p132 | | | | | | | | | | |
| 22000pF | | | | | p132 | | | | p132 | | | | | | | | | | |
| 47000pF | | | | | | p132 | | | p132 | | | | | | | | | | |
| 0.10μF | | | | | | p132 | | | | p132 | | | | p132 | | | | | |
| 0.22μF | p132 | p132 | | | | | p132 | | | | p132 | | | | p132 | | | | |
| 0.47μF | | | p132 | | | | | p132 | | | p132 | | | | p132 | | | | |
| 1.0μF | | | p132 | | | | | | | | | p132 | | | | p132 | | | |
| 2.2μF | | | | p132 | | | | | | | | | p132 | | | | p132 | | |
| 4.3μF | | | | | | | | | | | | | | | | | | | |
| 4.7μF | | | | | | | | | | | | | | | | | | p132 | |
| 10μF | | | | | | | | | | | | | | | | | | | p132 |

## ■ LLM Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7R X7S

| L×W (mm) | 2.0×1.25 | | | | 3.2×1.6 | | |
|---|---|---|---|---|---|---|---|
| T max. (mm) | 0.55 | | | | 0.55 | | |
| Rated Voltage (Vdc) | 25 | 16 | 6.3 | 4 | 16 | 10 | 6.3 |
| Cap. / TC Code | X7R | X7R | X7R | X7S | X7R | X7R | X7R |
| 10000pF | p134 | | | | | | |
| 22000pF | p134 | | | | | | |
| 47000pF | | p134 | | | | | |
| 0.10μF | | p134 | | | p134 | | |
| 0.22μF | | | p134 | | p134 | | |
| 0.47μF | | | p134 | | | p134 | |
| 1.0μF | | | | p134 | | | |
| 2.2μF | | | | | | | p134 |

## ■ LLR Series High Dielectric Constant Type

p00 ← Part Number List EIA: X7S

| L×W (mm) | 0.8×1.6 | | | |
|---|---|---|---|---|
| T max. (mm) | 0.55 | | | |
| Rated Voltage (Vdc) | 4 | | | |
| TC Code | X7S | | | |
| Cap. / ESR (mΩ) | 100 | 220 | 470 | 1000 |
| 1.0μF | p136 | p136 | p136 | p136 |

# Search Capacitors

Specifications and Test Methods, Package, Chart of Characteristic Data, please refer to the search web page.
http://www.murata.com/products/capacitor/




## Data Sheet

The product details page can be output in PDF.

## Status and Features Icons

The status and features of products can be checked at once. When ? is clicked, a description of each icon will be displayed.

## Characteristics & Applications

This links to the introduction page of each series.

## Detailed Specifications Sheet

- Rated value
- Specifications and Test Methods
- Package
- Caution, Notice
  (Storage, Soldering and Mounting, ....etc.)

## Characteristics Data

The following characteristics data of the main products can be acquired.

- SPICE Netlist (mod type)
- S parameter (S2P type)
- Reliability Test Data *Typical data

- Shape (Dimensions)
- Rated Values

- Specification by Packaging Code/ Minimum Order Quantity
- Weight (1 pc/ø180mm reel)

## Chart of Characteristic Data

The main products published characteristic data.

- Frequency characteristics (ESR, Impedance)
- S parameter (Smith chart S11)
- DC bias characteristics
- AC voltage characteristics
- Capacitance - temperature characteristics
- Calorific property by ripple current

For General Purpose

# GRM Series

**This is Murata primary products renowned for both small size and large capacitance value with latest advanced technology.**

## Features

### ① Achieves large-capacity and small size in a multilayer structure.



<Example of Structure>










### ② Sn plating is applied to the external electrodes; excellent solderability.

### ③ High reliability with no polarity.

| | Ceramic Capacitor | Tantalum Capacitor | Aluminum Electrolytic Capacitor | Conductive Polymer Capacitor |
|---|---|---|---|---|
| Price | ○ | ○ | ◎ | ○ |
| Comparison between Impedance Frequency Characteristics | ◎ | △ | △ | ○ |
| Capacitance temperature characteristics | ○ | ◎ | ○ | ○ |
| DC breakdown voltage | ◎ | △ | △ | △ |
| Polarity | No | Yes | Yes | Yes |
| Pulse response | ◎ | △ | △ | ○ |
| Allowable ripple current | ◎ | △ | △ | △ |
| Reliability | ◎ | ○ | ○ | ○ |
| DC bias characteristics | △ | ◎ | ◎ | ◎ |

◎: Particularly excellent ○: Excellent △: Inferior

## Specifications

| | |
|---|---|
| Size | 0.4×0.2mm to 5.7×5.0mm |
| Rated Voltage | DC2.5V to 3.15kV |
| Capacitance | 0.1pF to 150µF |
| Main Applications | 1. Rated voltage 100V Max.<br>High Dielectric Constant Type · · · For decoupling and smoothing circuits<br>Temperature Compensating Type · · · For tuning circuits, oscillating circuits, and high frequency filter circuits<br>2. Rated voltage 200V min.<br>High Dielectric Constant Type · · · For clamp snubber circuits and smoothing circuits<br>Temperature Compensating Type · · · Power supply damper snubber |



<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GRM Series Temperature Compensating Type Part Number List

## ■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 16Vdc | C0G | 0.20pF | ±0.05pF | **GRM0225C1CR20WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR20BD05#** | |
| | | | 0.30pF | ±0.05pF | **GRM0225C1CR30WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR30BD05#** | |
| | | | 0.40pF | ±0.05pF | **GRM0225C1CR40WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR40BD05#** | |
| | | | 0.50pF | ±0.05pF | **GRM0225C1CR50WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR50BD05#** | |
| | | | 0.60pF | ±0.05pF | **GRM0225C1CR60WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR60BD05#** | |
| | | | 0.70pF | ±0.05pF | **GRM0225C1CR70WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR70BD05#** | |
| | | | 0.80pF | ±0.05pF | **GRM0225C1CR80WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR80BD05#** | |
| | | | 0.90pF | ±0.05pF | **GRM0225C1CR90WD05#** | |
| | | | | ±0.1pF | **GRM0225C1CR90BD05#** | |
| | | | 1.0pF | ±0.05pF | **GRM0225C1C1R0WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R0BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R0CD05#** | |
| | | | 1.1pF | ±0.05pF | **GRM0225C1C1R1WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R1BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R1CD05#** | |
| | | | 1.2pF | ±0.05pF | **GRM0225C1C1R2WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R2BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R2CD05#** | |
| | | | 1.3pF | ±0.05pF | **GRM0225C1C1R3WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R3BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R3CD05#** | |
| | | | 1.4pF | ±0.05pF | **GRM0225C1C1R4WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R4BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R4CD05#** | |
| | | | 1.5pF | ±0.05pF | **GRM0225C1C1R5WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R5BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R5CD05#** | |
| | | | 1.6pF | ±0.05pF | **GRM0225C1C1R6WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R6BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R6CD05#** | |
| | | | 1.7pF | ±0.05pF | **GRM0225C1C1R7WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R7BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R7CD05#** | |
| | | | 1.8pF | ±0.05pF | **GRM0225C1C1R8WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R8BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R8CD05#** | |
| | | | 1.9pF | ±0.05pF | **GRM0225C1C1R9WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C1R9BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C1R9CD05#** | |
| | | | 2.0pF | ±0.05pF | **GRM0225C1C2R0WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R0BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R0CD05#** | |
| | | | 2.1pF | ±0.05pF | **GRM0225C1C2R1WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R1BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R1CD05#** | |
| 0.22mm | 16Vdc | C0G | 2.2pF | ±0.05pF | **GRM0225C1C2R2WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R2BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R2CD05#** | |
| | | | 2.3pF | ±0.05pF | **GRM0225C1C2R3WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R3BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R3CD05#** | |
| | | | 2.4pF | ±0.05pF | **GRM0225C1C2R4WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R4BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R4CD05#** | |
| | | | 2.5pF | ±0.05pF | **GRM0225C1C2R5WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R5BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R5CD05#** | |
| | | | 2.6pF | ±0.05pF | **GRM0225C1C2R6WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R6BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R6CD05#** | |
| | | | 2.7pF | ±0.05pF | **GRM0225C1C2R7WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R7BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R7CD05#** | |
| | | | 2.8pF | ±0.05pF | **GRM0225C1C2R8WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R8BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R8CD05#** | |
| | | | 2.9pF | ±0.05pF | **GRM0225C1C2R9WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C2R9BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C2R9CD05#** | |
| | | | 3.0pF | ±0.05pF | **GRM0225C1C3R0WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R0BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R0CD05#** | |
| | | | 3.1pF | ±0.05pF | **GRM0225C1C3R1WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R1BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R1CD05#** | |
| | | | 3.2pF | ±0.05pF | **GRM0225C1C3R2WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R2BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R2CD05#** | |
| | | | 3.3pF | ±0.05pF | **GRM0225C1C3R3WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R3BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R3CD05#** | |
| | | | 3.4pF | ±0.05pF | **GRM0225C1C3R4WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R4BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R4CD05#** | |
| | | | 3.5pF | ±0.05pF | **GRM0225C1C3R5WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R5BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R5CD05#** | |
| | | | 3.6pF | ±0.05pF | **GRM0225C1C3R6WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R6BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R6CD05#** | |
| | | | 3.7pF | ±0.05pF | **GRM0225C1C3R7WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R7BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R7CD05#** | |
| | | | 3.8pF | ±0.05pF | **GRM0225C1C3R8WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R8BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R8CD05#** | |
| | | | 3.9pF | ±0.05pF | **GRM0225C1C3R9WD05#** | |
| | | | | ±0.1pF | **GRM0225C1C3R9BD05#** | |
| | | | | ±0.25pF | **GRM0225C1C3R9CD05#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | C0G | 4.0pF | ±0.05pF | **GRM0225C1C4R0WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R0BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R0CD05#** |
| | | | 4.1pF | ±0.05pF | **GRM0225C1C4R1WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R1BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R1CD05#** |
| | | | 4.2pF | ±0.05pF | **GRM0225C1C4R2WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R2BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R2CD05#** |
| | | | 4.3pF | ±0.05pF | **GRM0225C1C4R3WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R3BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R3CD05#** |
| | | | 4.4pF | ±0.05pF | **GRM0225C1C4R4WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R4BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R4CD05#** |
| | | | 4.5pF | ±0.05pF | **GRM0225C1C4R5WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R5BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R5CD05#** |
| | | | 4.6pF | ±0.05pF | **GRM0225C1C4R6WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R6BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R6CD05#** |
| | | | 4.7pF | ±0.05pF | **GRM0225C1C4R7WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R7BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R7CD05#** |
| | | | 4.8pF | ±0.05pF | **GRM0225C1C4R8WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R8BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R8CD05#** |
| | | | 4.9pF | ±0.05pF | **GRM0225C1C4R9WD05#** |
| | | | | ±0.1pF | **GRM0225C1C4R9BD05#** |
| | | | | ±0.25pF | **GRM0225C1C4R9CD05#** |
| | | | 5.0pF | ±0.05pF | **GRM0225C1C5R0WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R0BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R0CD05#** |
| | | | 5.1pF | ±0.05pF | **GRM0225C1C5R1WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R1BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R1CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R1DD05#** |
| | | | 5.2pF | ±0.05pF | **GRM0225C1C5R2WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R2BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R2CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R2DD05#** |
| | | | 5.3pF | ±0.05pF | **GRM0225C1C5R3WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R3BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R3CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R3DD05#** |
| | | | 5.4pF | ±0.05pF | **GRM0225C1C5R4WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R4BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R4CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R4DD05#** |
| | | | 5.5pF | ±0.05pF | **GRM0225C1C5R5WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R5BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R5CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R5DD05#** |
| | | | 5.6pF | ±0.05pF | **GRM0225C1C5R6WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R6BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R6CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R6DD05#** |
| | | | 5.7pF | ±0.05pF | **GRM0225C1C5R7WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R7BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R7CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R7DD05#** |
| | | | 5.8pF | ±0.05pF | **GRM0225C1C5R8WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R8BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R8CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R8DD05#** |
| | | | 5.9pF | ±0.05pF | **GRM0225C1C5R9WD05#** |
| | | | | ±0.1pF | **GRM0225C1C5R9BD05#** |
| | | | | ±0.25pF | **GRM0225C1C5R9CD05#** |
| | | | | ±0.5pF | **GRM0225C1C5R9DD05#** |
| | | | 6.0pF | ±0.05pF | **GRM0225C1C6R0WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R0BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R0CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R0DD05#** |
| | | | 6.1pF | ±0.05pF | **GRM0225C1C6R1WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R1BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R1CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R1DD05#** |
| | | | 6.2pF | ±0.05pF | **GRM0225C1C6R2WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R2BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R2CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R2DD05#** |
| | | | 6.3pF | ±0.05pF | **GRM0225C1C6R3WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R3BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R3CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R3DD05#** |
| | | | 6.4pF | ±0.05pF | **GRM0225C1C6R4WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R4BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R4CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R4DD05#** |
| | | | 6.5pF | ±0.05pF | **GRM0225C1C6R5WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R5BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R5CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R5DD05#** |
| | | | 6.6pF | ±0.05pF | **GRM0225C1C6R6WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R6BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R6CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R6DD05#** |
| | | | 6.7pF | ±0.05pF | **GRM0225C1C6R7WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R7BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R7CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R7DD05#** |
| | | | 6.8pF | ±0.05pF | **GRM0225C1C6R8WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R8BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R8CD05#** |
| | | | | ±0.5pF | **GRM0225C1C6R8DD05#** |
| | | | 6.9pF | ±0.05pF | **GRM0225C1C6R9WD05#** |
| | | | | ±0.1pF | **GRM0225C1C6R9BD05#** |
| | | | | ±0.25pF | **GRM0225C1C6R9CD05#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | C0G | 6.9pF | ±0.5pF | GRM0225C1C6R9DD05# |
| | | | 7.0pF | ±0.05pF | GRM0225C1C7R0WD05# |
| | | | | ±0.1pF | GRM0225C1C7R0BD05# |
| | | | | ±0.25pF | GRM0225C1C7R0CD05# |
| | | | | ±0.5pF | GRM0225C1C7R0DD05# |
| | | | 7.1pF | ±0.05pF | GRM0225C1C7R1WD05# |
| | | | | ±0.1pF | GRM0225C1C7R1BD05# |
| | | | | ±0.25pF | GRM0225C1C7R1CD05# |
| | | | | ±0.5pF | GRM0225C1C7R1DD05# |
| | | | 7.2pF | ±0.05pF | GRM0225C1C7R2WD05# |
| | | | | ±0.1pF | GRM0225C1C7R2BD05# |
| | | | | ±0.25pF | GRM0225C1C7R2CD05# |
| | | | | ±0.5pF | GRM0225C1C7R2DD05# |
| | | | 7.3pF | ±0.05pF | GRM0225C1C7R3WD05# |
| | | | | ±0.1pF | GRM0225C1C7R3BD05# |
| | | | | ±0.25pF | GRM0225C1C7R3CD05# |
| | | | | ±0.5pF | GRM0225C1C7R3DD05# |
| | | | 7.4pF | ±0.05pF | GRM0225C1C7R4WD05# |
| | | | | ±0.1pF | GRM0225C1C7R4BD05# |
| | | | | ±0.25pF | GRM0225C1C7R4CD05# |
| | | | | ±0.5pF | GRM0225C1C7R4DD05# |
| | | | 7.5pF | ±0.05pF | GRM0225C1C7R5WD05# |
| | | | | ±0.1pF | GRM0225C1C7R5BD05# |
| | | | | ±0.25pF | GRM0225C1C7R5CD05# |
| | | | | ±0.5pF | GRM0225C1C7R5DD05# |
| | | | 7.6pF | ±0.05pF | GRM0225C1C7R6WD05# |
| | | | | ±0.1pF | GRM0225C1C7R6BD05# |
| | | | | ±0.25pF | GRM0225C1C7R6CD05# |
| | | | | ±0.5pF | GRM0225C1C7R6DD05# |
| | | | 7.7pF | ±0.05pF | GRM0225C1C7R7WD05# |
| | | | | ±0.1pF | GRM0225C1C7R7BD05# |
| | | | | ±0.25pF | GRM0225C1C7R7CD05# |
| | | | | ±0.5pF | GRM0225C1C7R7DD05# |
| | | | 7.8pF | ±0.05pF | GRM0225C1C7R8WD05# |
| | | | | ±0.1pF | GRM0225C1C7R8BD05# |
| | | | | ±0.25pF | GRM0225C1C7R8CD05# |
| | | | | ±0.5pF | GRM0225C1C7R8DD05# |
| | | | 7.9pF | ±0.05pF | GRM0225C1C7R9WD05# |
| | | | | ±0.1pF | GRM0225C1C7R9BD05# |
| | | | | ±0.25pF | GRM0225C1C7R9CD05# |
| | | | | ±0.5pF | GRM0225C1C7R9DD05# |
| | | | 8.0pF | ±0.05pF | GRM0225C1C8R0WD05# |
| | | | | ±0.1pF | GRM0225C1C8R0BD05# |
| | | | | ±0.25pF | GRM0225C1C8R0CD05# |
| | | | | ±0.5pF | GRM0225C1C8R0DD05# |
| | | | 8.1pF | ±0.05pF | GRM0225C1C8R1WD05# |
| | | | | ±0.1pF | GRM0225C1C8R1BD05# |
| | | | | ±0.25pF | GRM0225C1C8R1CD05# |
| | | | | ±0.5pF | GRM0225C1C8R1DD05# |
| | | | 8.2pF | ±0.05pF | GRM0225C1C8R2WD05# |
| | | | | ±0.1pF | GRM0225C1C8R2BD05# |
| | | | | ±0.25pF | GRM0225C1C8R2CD05# |
| | | | | ±0.5pF | GRM0225C1C8R2DD05# |
| | | | 8.3pF | ±0.05pF | GRM0225C1C8R3WD05# |
| | | | | ±0.1pF | GRM0225C1C8R3BD05# |
| | | | | ±0.25pF | GRM0225C1C8R3CD05# |
| | | | | ±0.5pF | GRM0225C1C8R3DD05# |
| | | | 8.4pF | ±0.05pF | GRM0225C1C8R4WD05# |
| | | | | ±0.1pF | GRM0225C1C8R4BD05# |
| | | | | ±0.25pF | GRM0225C1C8R4CD05# |
| | | | | ±0.5pF | GRM0225C1C8R4DD05# |
| | | | 8.5pF | ±0.05pF | GRM0225C1C8R5WD05# |
| | | | | ±0.1pF | GRM0225C1C8R5BD05# |
| | | | | ±0.25pF | GRM0225C1C8R5CD05# |
| | | | | ±0.5pF | GRM0225C1C8R5DD05# |
| | | | 8.6pF | ±0.05pF | GRM0225C1C8R6WD05# |
| | | | | ±0.1pF | GRM0225C1C8R6BD05# |
| | | | | ±0.25pF | GRM0225C1C8R6CD05# |
| | | | | ±0.5pF | GRM0225C1C8R6DD05# |
| | | | 8.7pF | ±0.05pF | GRM0225C1C8R7WD05# |
| | | | | ±0.1pF | GRM0225C1C8R7BD05# |
| | | | | ±0.25pF | GRM0225C1C8R7CD05# |
| | | | | ±0.5pF | GRM0225C1C8R7DD05# |
| | | | 8.8pF | ±0.05pF | GRM0225C1C8R8WD05# |
| | | | | ±0.1pF | GRM0225C1C8R8BD05# |
| | | | | ±0.25pF | GRM0225C1C8R8CD05# |
| | | | | ±0.5pF | GRM0225C1C8R8DD05# |
| | | | 8.9pF | ±0.05pF | GRM0225C1C8R9WD05# |
| | | | | ±0.1pF | GRM0225C1C8R9BD05# |
| | | | | ±0.25pF | GRM0225C1C8R9CD05# |
| | | | | ±0.5pF | GRM0225C1C8R9DD05# |
| | | | 9.0pF | ±0.05pF | GRM0225C1C9R0WD05# |
| | | | | ±0.1pF | GRM0225C1C9R0BD05# |
| | | | | ±0.25pF | GRM0225C1C9R0CD05# |
| | | | | ±0.5pF | GRM0225C1C9R0DD05# |
| | | | 9.1pF | ±0.05pF | GRM0225C1C9R1WD05# |
| | | | | ±0.1pF | GRM0225C1C9R1BD05# |
| | | | | ±0.25pF | GRM0225C1C9R1CD05# |
| | | | | ±0.5pF | GRM0225C1C9R1DD05# |
| | | | 9.2pF | ±0.05pF | GRM0225C1C9R2WD05# |
| | | | | ±0.1pF | GRM0225C1C9R2BD05# |
| | | | | ±0.25pF | GRM0225C1C9R2CD05# |
| | | | | ±0.5pF | GRM0225C1C9R2DD05# |
| | | | 9.3pF | ±0.05pF | GRM0225C1C9R3WD05# |
| | | | | ±0.1pF | GRM0225C1C9R3BD05# |
| | | | | ±0.25pF | GRM0225C1C9R3CD05# |
| | | | | ±0.5pF | GRM0225C1C9R3DD05# |
| | | | 9.4pF | ±0.05pF | GRM0225C1C9R4WD05# |
| | | | | ±0.1pF | GRM0225C1C9R4BD05# |
| | | | | ±0.25pF | GRM0225C1C9R4CD05# |
| | | | | ±0.5pF | GRM0225C1C9R4DD05# |
| | | | 9.5pF | ±0.05pF | GRM0225C1C9R5WD05# |
| | | | | ±0.1pF | GRM0225C1C9R5BD05# |
| | | | | ±0.25pF | GRM0225C1C9R5CD05# |
| | | | | ±0.5pF | GRM0225C1C9R5DD05# |
| | | | 9.6pF | ±0.05pF | GRM0225C1C9R6WD05# |
| | | | | ±0.1pF | GRM0225C1C9R6BD05# |
| | | | | ±0.25pF | GRM0225C1C9R6CD05# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | C0G | 9.6pF | ±0.5pF | **GRM0225C1C9R6DD05#** |
| | | | 9.7pF | ±0.05pF | **GRM0225C1C9R7WD05#** |
| | | | | ±0.1pF | **GRM0225C1C9R7BD05#** |
| | | | | ±0.25pF | **GRM0225C1C9R7CD05#** |
| | | | | ±0.5pF | **GRM0225C1C9R7DD05#** |
| | | | 9.8pF | ±0.05pF | **GRM0225C1C9R8WD05#** |
| | | | | ±0.1pF | **GRM0225C1C9R8BD05#** |
| | | | | ±0.25pF | **GRM0225C1C9R8CD05#** |
| | | | | ±0.5pF | **GRM0225C1C9R8DD05#** |
| | | | 9.9pF | ±0.05pF | **GRM0225C1C9R9WD05#** |
| | | | | ±0.1pF | **GRM0225C1C9R9BD05#** |
| | | | | ±0.25pF | **GRM0225C1C9R9CD05#** |
| | | | | ±0.5pF | **GRM0225C1C9R9DD05#** |
| | | | 10pF | ±2% | **GRM0225C1C100GD05#** |
| | | | | ±5% | **GRM0225C1C100JD05#** |
| | | | 12pF | ±2% | **GRM0225C1C120GD05#** |
| | | | | ±5% | **GRM0225C1C120JD05#** |
| | | | 15pF | ±2% | **GRM0225C1C150GD05#** |
| | | | | ±5% | **GRM0225C1C150JD05#** |
| | | | 18pF | ±2% | **GRM0225C1C180GD05#** |
| | | | | ±5% | **GRM0225C1C180JD05#** |
| | | | 22pF | ±2% | **GRM0225C1C220GD05#** |
| | | | | ±5% | **GRM0225C1C220JD05#** |
| | | | 27pF | ±2% | **GRM0225C1C270GD05#** |
| | | | | ±5% | **GRM0225C1C270JD05#** |
| | | | 33pF | ±2% | **GRM0225C1C330GD05#** |
| | | | | ±5% | **GRM0225C1C330JD05#** |
| | | | 39pF | ±2% | **GRM0225C1C390GD05#** |
| | | | | ±5% | **GRM0225C1C390JD05#** |
| | | | 47pF | ±2% | **GRM0225C1C470GD05#** |
| | | | | ±5% | **GRM0225C1C470JD05#** |
| | | CK | 0.20pF | ±0.05pF | **GRM0224C1CR20WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR20BD05#** |
| | | | 0.30pF | ±0.05pF | **GRM0224C1CR30WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR30BD05#** |
| | | | 0.40pF | ±0.05pF | **GRM0224C1CR40WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR40BD05#** |
| | | | 0.50pF | ±0.05pF | **GRM0224C1CR50WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR50BD05#** |
| | | | 0.60pF | ±0.05pF | **GRM0224C1CR60WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR60BD05#** |
| | | | 0.70pF | ±0.05pF | **GRM0224C1CR70WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR70BD05#** |
| | | | 0.80pF | ±0.05pF | **GRM0224C1CR80WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR80BD05#** |
| | | | 0.90pF | ±0.05pF | **GRM0224C1CR90WD05#** |
| | | | | ±0.1pF | **GRM0224C1CR90BD05#** |
| | | | 1.0pF | ±0.05pF | **GRM0224C1C1R0WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R0BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R0CD05#** |
| | | | 1.1pF | ±0.05pF | **GRM0224C1C1R1WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R1BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R1CD05#** |
| | | | 1.2pF | ±0.05pF | **GRM0224C1C1R2WD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R2CD05#** |
| | | | 1.3pF | ±0.05pF | **GRM0224C1C1R3WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R3BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R3CD05#** |
| | | | 1.4pF | ±0.05pF | **GRM0224C1C1R4WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R4BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R4CD05#** |
| | | | 1.5pF | ±0.05pF | **GRM0224C1C1R5WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R5BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R5CD05#** |
| | | | 1.6pF | ±0.05pF | **GRM0224C1C1R6WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R6BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R6CD05#** |
| | | | 1.7pF | ±0.05pF | **GRM0224C1C1R7WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R7BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R7CD05#** |
| | | | 1.8pF | ±0.05pF | **GRM0224C1C1R8WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R8BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R8CD05#** |
| | | | 1.9pF | ±0.05pF | **GRM0224C1C1R9WD05#** |
| | | | | ±0.1pF | **GRM0224C1C1R9BD05#** |
| | | | | ±0.25pF | **GRM0224C1C1R9CD05#** |
| | | | 2.0pF | ±0.05pF | **GRM0224C1C2R0WD05#** |
| | | | | ±0.1pF | **GRM0224C1C2R0BD05#** |
| | | | | ±0.25pF | **GRM0224C1C2R0CD05#** |
| | | CJ | 2.1pF | ±0.05pF | **GRM0223C1C2R1WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R1BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R1CD05#** |
| | | | 2.2pF | ±0.05pF | **GRM0223C1C2R2WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R2BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R2CD05#** |
| | | | 2.3pF | ±0.05pF | **GRM0223C1C2R3WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R3BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R3CD05#** |
| | | | 2.4pF | ±0.05pF | **GRM0223C1C2R4WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R4BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R4CD05#** |
| | | | 2.5pF | ±0.05pF | **GRM0223C1C2R5WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R5BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R5CD05#** |
| | | | 2.6pF | ±0.05pF | **GRM0223C1C2R6WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R6BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R6CD05#** |
| | | | 2.7pF | ±0.05pF | **GRM0223C1C2R7WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R7BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R7CD05#** |
| | | | 2.8pF | ±0.05pF | **GRM0223C1C2R8WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R8BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R8CD05#** |
| | | | 2.9pF | ±0.05pF | **GRM0223C1C2R9WD05#** |
| | | | | ±0.1pF | **GRM0223C1C2R9BD05#** |
| | | | | ±0.25pF | **GRM0223C1C2R9CD05#** |
| | | | 3.0pF | ±0.05pF | **GRM0223C1C3R0WD05#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CJ | 3.0pF | ±0.1pF | GRM0223C1C3R0BD05# |
| | | | | ±0.25pF | GRM0223C1C3R0CD05# |
| | | | 3.1pF | ±0.05pF | GRM0223C1C3R1WD05# |
| | | | | ±0.1pF | GRM0223C1C3R1BD05# |
| | | | | ±0.25pF | GRM0223C1C3R1CD05# |
| | | | 3.2pF | ±0.05pF | GRM0223C1C3R2WD05# |
| | | | | ±0.1pF | GRM0223C1C3R2BD05# |
| | | | | ±0.25pF | GRM0223C1C3R2CD05# |
| | | | 3.3pF | ±0.05pF | GRM0223C1C3R3WD05# |
| | | | | ±0.1pF | GRM0223C1C3R3BD05# |
| | | | | ±0.25pF | GRM0223C1C3R3CD05# |
| | | | 3.4pF | ±0.05pF | GRM0223C1C3R4WD05# |
| | | | | ±0.1pF | GRM0223C1C3R4BD05# |
| | | | | ±0.25pF | GRM0223C1C3R4CD05# |
| | | | 3.5pF | ±0.05pF | GRM0223C1C3R5WD05# |
| | | | | ±0.1pF | GRM0223C1C3R5BD05# |
| | | | | ±0.25pF | GRM0223C1C3R5CD05# |
| | | | 3.6pF | ±0.05pF | GRM0223C1C3R6WD05# |
| | | | | ±0.1pF | GRM0223C1C3R6BD05# |
| | | | | ±0.25pF | GRM0223C1C3R6CD05# |
| | | | 3.7pF | ±0.05pF | GRM0223C1C3R7WD05# |
| | | | | ±0.1pF | GRM0223C1C3R7BD05# |
| | | | | ±0.25pF | GRM0223C1C3R7CD05# |
| | | | 3.8pF | ±0.05pF | GRM0223C1C3R8WD05# |
| | | | | ±0.1pF | GRM0223C1C3R8BD05# |
| | | | | ±0.25pF | GRM0223C1C3R8CD05# |
| | | | 3.9pF | ±0.05pF | GRM0223C1C3R9WD05# |
| | | | | ±0.1pF | GRM0223C1C3R9BD05# |
| | | | | ±0.25pF | GRM0223C1C3R9CD05# |
| | | CH | 4.0pF | ±0.05pF | GRM0222C1C4R0WD05# |
| | | | | ±0.1pF | GRM0222C1C4R0BD05# |
| | | | | ±0.25pF | GRM0222C1C4R0CD05# |
| | | | 4.1pF | ±0.05pF | GRM0222C1C4R1WD05# |
| | | | | ±0.1pF | GRM0222C1C4R1BD05# |
| | | | | ±0.25pF | GRM0222C1C4R1CD05# |
| | | | 4.2pF | ±0.05pF | GRM0222C1C4R2WD05# |
| | | | | ±0.1pF | GRM0222C1C4R2BD05# |
| | | | | ±0.25pF | GRM0222C1C4R2CD05# |
| | | | 4.3pF | ±0.05pF | GRM0222C1C4R3WD05# |
| | | | | ±0.1pF | GRM0222C1C4R3BD05# |
| | | | | ±0.25pF | GRM0222C1C4R3CD05# |
| | | | 4.4pF | ±0.05pF | GRM0222C1C4R4WD05# |
| | | | | ±0.1pF | GRM0222C1C4R4BD05# |
| | | | | ±0.25pF | GRM0222C1C4R4CD05# |
| | | | 4.5pF | ±0.05pF | GRM0222C1C4R5WD05# |
| | | | | ±0.1pF | GRM0222C1C4R5BD05# |
| | | | | ±0.25pF | GRM0222C1C4R5CD05# |
| | | | 4.6pF | ±0.05pF | GRM0222C1C4R6WD05# |
| | | | | ±0.1pF | GRM0222C1C4R6BD05# |
| | | | | ±0.25pF | GRM0222C1C4R6CD05# |
| | | | 4.7pF | ±0.05pF | GRM0222C1C4R7WD05# |
| | | | | ±0.1pF | GRM0222C1C4R7BD05# |
| | | | | ±0.25pF | GRM0222C1C4R7CD05# |
| | | | 4.8pF | ±0.05pF | GRM0222C1C4R8WD05# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CH | 4.8pF | ±0.1pF | GRM0222C1C4R8BD05# |
| | | | | ±0.25pF | GRM0222C1C4R8CD05# |
| | | | 4.9pF | ±0.05pF | GRM0222C1C4R9WD05# |
| | | | | ±0.1pF | GRM0222C1C4R9BD05# |
| | | | | ±0.25pF | GRM0222C1C4R9CD05# |
| | | | 5.0pF | ±0.05pF | GRM0222C1C5R0WD05# |
| | | | | ±0.1pF | GRM0222C1C5R0BD05# |
| | | | | ±0.25pF | GRM0222C1C5R0CD05# |
| | | | 5.1pF | ±0.05pF | GRM0222C1C5R1WD05# |
| | | | | ±0.1pF | GRM0222C1C5R1BD05# |
| | | | | ±0.25pF | GRM0222C1C5R1CD05# |
| | | | | ±0.5pF | GRM0222C1C5R1DD05# |
| | | | 5.2pF | ±0.05pF | GRM0222C1C5R2WD05# |
| | | | | ±0.1pF | GRM0222C1C5R2BD05# |
| | | | | ±0.25pF | GRM0222C1C5R2CD05# |
| | | | | ±0.5pF | GRM0222C1C5R2DD05# |
| | | | 5.3pF | ±0.05pF | GRM0222C1C5R3WD05# |
| | | | | ±0.1pF | GRM0222C1C5R3BD05# |
| | | | | ±0.25pF | GRM0222C1C5R3CD05# |
| | | | | ±0.5pF | GRM0222C1C5R3DD05# |
| | | | 5.4pF | ±0.05pF | GRM0222C1C5R4WD05# |
| | | | | ±0.1pF | GRM0222C1C5R4BD05# |
| | | | | ±0.25pF | GRM0222C1C5R4CD05# |
| | | | | ±0.5pF | GRM0222C1C5R4DD05# |
| | | | 5.5pF | ±0.05pF | GRM0222C1C5R5WD05# |
| | | | | ±0.1pF | GRM0222C1C5R5BD05# |
| | | | | ±0.25pF | GRM0222C1C5R5CD05# |
| | | | | ±0.5pF | GRM0222C1C5R5DD05# |
| | | | 5.6pF | ±0.05pF | GRM0222C1C5R6WD05# |
| | | | | ±0.1pF | GRM0222C1C5R6BD05# |
| | | | | ±0.25pF | GRM0222C1C5R6CD05# |
| | | | | ±0.5pF | GRM0222C1C5R6DD05# |
| | | | 5.7pF | ±0.05pF | GRM0222C1C5R7WD05# |
| | | | | ±0.1pF | GRM0222C1C5R7BD05# |
| | | | | ±0.25pF | GRM0222C1C5R7CD05# |
| | | | | ±0.5pF | GRM0222C1C5R7DD05# |
| | | | 5.8pF | ±0.05pF | GRM0222C1C5R8WD05# |
| | | | | ±0.1pF | GRM0222C1C5R8BD05# |
| | | | | ±0.25pF | GRM0222C1C5R8CD05# |
| | | | | ±0.5pF | GRM0222C1C5R8DD05# |
| | | | 5.9pF | ±0.05pF | GRM0222C1C5R9WD05# |
| | | | | ±0.1pF | GRM0222C1C5R9BD05# |
| | | | | ±0.25pF | GRM0222C1C5R9CD05# |
| | | | | ±0.5pF | GRM0222C1C5R9DD05# |
| | | | 6.0pF | ±0.05pF | GRM0222C1C6R0WD05# |
| | | | | ±0.1pF | GRM0222C1C6R0BD05# |
| | | | | ±0.25pF | GRM0222C1C6R0CD05# |
| | | | | ±0.5pF | GRM0222C1C6R0DD05# |
| | | | 6.1pF | ±0.05pF | GRM0222C1C6R1WD05# |
| | | | | ±0.1pF | GRM0222C1C6R1BD05# |
| | | | | ±0.25pF | GRM0222C1C6R1CD05# |
| | | | | ±0.5pF | GRM0222C1C6R1DD05# |
| | | | 6.2pF | ±0.05pF | GRM0222C1C6R2WD05# |
| | | | | ±0.1pF | GRM0222C1C6R2BD05# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CH | 6.2pF | ±0.25pF | GRM0222C1C6R2CD05# |
| | | | | ±0.5pF | GRM0222C1C6R2DD05# |
| | | | 6.3pF | ±0.05pF | GRM0222C1C6R3WD05# |
| | | | | ±0.1pF | GRM0222C1C6R3BD05# |
| | | | | ±0.25pF | GRM0222C1C6R3CD05# |
| | | | | ±0.5pF | GRM0222C1C6R3DD05# |
| | | | 6.4pF | ±0.05pF | GRM0222C1C6R4WD05# |
| | | | | ±0.1pF | GRM0222C1C6R4BD05# |
| | | | | ±0.25pF | GRM0222C1C6R4CD05# |
| | | | | ±0.5pF | GRM0222C1C6R4DD05# |
| | | | 6.5pF | ±0.05pF | GRM0222C1C6R5WD05# |
| | | | | ±0.1pF | GRM0222C1C6R5BD05# |
| | | | | ±0.25pF | GRM0222C1C6R5CD05# |
| | | | | ±0.5pF | GRM0222C1C6R5DD05# |
| | | | 6.6pF | ±0.05pF | GRM0222C1C6R6WD05# |
| | | | | ±0.1pF | GRM0222C1C6R6BD05# |
| | | | | ±0.25pF | GRM0222C1C6R6CD05# |
| | | | | ±0.5pF | GRM0222C1C6R6DD05# |
| | | | 6.7pF | ±0.05pF | GRM0222C1C6R7WD05# |
| | | | | ±0.1pF | GRM0222C1C6R7BD05# |
| | | | | ±0.25pF | GRM0222C1C6R7CD05# |
| | | | | ±0.5pF | GRM0222C1C6R7DD05# |
| | | | 6.8pF | ±0.05pF | GRM0222C1C6R8WD05# |
| | | | | ±0.1pF | GRM0222C1C6R8BD05# |
| | | | | ±0.25pF | GRM0222C1C6R8CD05# |
| | | | | ±0.5pF | GRM0222C1C6R8DD05# |
| | | | 6.9pF | ±0.05pF | GRM0222C1C6R9WD05# |
| | | | | ±0.1pF | GRM0222C1C6R9BD05# |
| | | | | ±0.25pF | GRM0222C1C6R9CD05# |
| | | | | ±0.5pF | GRM0222C1C6R9DD05# |
| | | | 7.0pF | ±0.05pF | GRM0222C1C7R0WD05# |
| | | | | ±0.1pF | GRM0222C1C7R0BD05# |
| | | | | ±0.25pF | GRM0222C1C7R0CD05# |
| | | | | ±0.5pF | GRM0222C1C7R0DD05# |
| | | | 7.1pF | ±0.05pF | GRM0222C1C7R1WD05# |
| | | | | ±0.1pF | GRM0222C1C7R1BD05# |
| | | | | ±0.25pF | GRM0222C1C7R1CD05# |
| | | | | ±0.5pF | GRM0222C1C7R1DD05# |
| | | | 7.2pF | ±0.05pF | GRM0222C1C7R2WD05# |
| | | | | ±0.1pF | GRM0222C1C7R2BD05# |
| | | | | ±0.25pF | GRM0222C1C7R2CD05# |
| | | | | ±0.5pF | GRM0222C1C7R2DD05# |
| | | | 7.3pF | ±0.05pF | GRM0222C1C7R3WD05# |
| | | | | ±0.1pF | GRM0222C1C7R3BD05# |
| | | | | ±0.25pF | GRM0222C1C7R3CD05# |
| | | | | ±0.5pF | GRM0222C1C7R3DD05# |
| | | | 7.4pF | ±0.05pF | GRM0222C1C7R4WD05# |
| | | | | ±0.1pF | GRM0222C1C7R4BD05# |
| | | | | ±0.25pF | GRM0222C1C7R4CD05# |
| | | | | ±0.5pF | GRM0222C1C7R4DD05# |
| | | | 7.5pF | ±0.05pF | GRM0222C1C7R5WD05# |
| | | | | ±0.1pF | GRM0222C1C7R5BD05# |
| | | | | ±0.25pF | GRM0222C1C7R5CD05# |
| | | | | ±0.5pF | GRM0222C1C7R5DD05# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CH | 7.6pF | ±0.05pF | GRM0222C1C7R6WD05# |
| | | | | ±0.1pF | GRM0222C1C7R6BD05# |
| | | | | ±0.25pF | GRM0222C1C7R6CD05# |
| | | | | ±0.5pF | GRM0222C1C7R6DD05# |
| | | | 7.7pF | ±0.05pF | GRM0222C1C7R7WD05# |
| | | | | ±0.1pF | GRM0222C1C7R7BD05# |
| | | | | ±0.25pF | GRM0222C1C7R7CD05# |
| | | | | ±0.5pF | GRM0222C1C7R7DD05# |
| | | | 7.8pF | ±0.05pF | GRM0222C1C7R8WD05# |
| | | | | ±0.1pF | GRM0222C1C7R8BD05# |
| | | | | ±0.25pF | GRM0222C1C7R8CD05# |
| | | | | ±0.5pF | GRM0222C1C7R8DD05# |
| | | | 7.9pF | ±0.05pF | GRM0222C1C7R9WD05# |
| | | | | ±0.1pF | GRM0222C1C7R9BD05# |
| | | | | ±0.25pF | GRM0222C1C7R9CD05# |
| | | | | ±0.5pF | GRM0222C1C7R9DD05# |
| | | | 8.0pF | ±0.05pF | GRM0222C1C8R0WD05# |
| | | | | ±0.1pF | GRM0222C1C8R0BD05# |
| | | | | ±0.25pF | GRM0222C1C8R0CD05# |
| | | | | ±0.5pF | GRM0222C1C8R0DD05# |
| | | | 8.1pF | ±0.05pF | GRM0222C1C8R1WD05# |
| | | | | ±0.1pF | GRM0222C1C8R1BD05# |
| | | | | ±0.25pF | GRM0222C1C8R1CD05# |
| | | | | ±0.5pF | GRM0222C1C8R1DD05# |
| | | | 8.2pF | ±0.05pF | GRM0222C1C8R2WD05# |
| | | | | ±0.1pF | GRM0222C1C8R2BD05# |
| | | | | ±0.25pF | GRM0222C1C8R2CD05# |
| | | | | ±0.5pF | GRM0222C1C8R2DD05# |
| | | | 8.3pF | ±0.05pF | GRM0222C1C8R3WD05# |
| | | | | ±0.1pF | GRM0222C1C8R3BD05# |
| | | | | ±0.25pF | GRM0222C1C8R3CD05# |
| | | | | ±0.5pF | GRM0222C1C8R3DD05# |
| | | | 8.4pF | ±0.05pF | GRM0222C1C8R4WD05# |
| | | | | ±0.1pF | GRM0222C1C8R4BD05# |
| | | | | ±0.25pF | GRM0222C1C8R4CD05# |
| | | | | ±0.5pF | GRM0222C1C8R4DD05# |
| | | | 8.5pF | ±0.05pF | GRM0222C1C8R5WD05# |
| | | | | ±0.1pF | GRM0222C1C8R5BD05# |
| | | | | ±0.25pF | GRM0222C1C8R5CD05# |
| | | | | ±0.5pF | GRM0222C1C8R5DD05# |
| | | | 8.6pF | ±0.05pF | GRM0222C1C8R6WD05# |
| | | | | ±0.1pF | GRM0222C1C8R6BD05# |
| | | | | ±0.25pF | GRM0222C1C8R6CD05# |
| | | | | ±0.5pF | GRM0222C1C8R6DD05# |
| | | | 8.7pF | ±0.05pF | GRM0222C1C8R7WD05# |
| | | | | ±0.1pF | GRM0222C1C8R7BD05# |
| | | | | ±0.25pF | GRM0222C1C8R7CD05# |
| | | | | ±0.5pF | GRM0222C1C8R7DD05# |
| | | | 8.8pF | ±0.05pF | GRM0222C1C8R8WD05# |
| | | | | ±0.1pF | GRM0222C1C8R8BD05# |
| | | | | ±0.25pF | GRM0222C1C8R8CD05# |
| | | | | ±0.5pF | GRM0222C1C8R8DD05# |
| | | | 8.9pF | ±0.05pF | GRM0222C1C8R9WD05# |
| | | | | ±0.1pF | GRM0222C1C8R9BD05# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CH | 8.9pF | ±0.25pF | GRM0222C1C8R9CD05# | |
| | | | | ±0.5pF | GRM0222C1C8R9DD05# | |
| | | | 9.0pF | ±0.05pF | GRM0222C1C9R0WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R0BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R0CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R0DD05# | |
| | | | 9.1pF | ±0.05pF | GRM0222C1C9R1WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R1BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R1CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R1DD05# | |
| | | | 9.2pF | ±0.05pF | GRM0222C1C9R2WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R2BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R2CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R2DD05# | |
| | | | 9.3pF | ±0.05pF | GRM0222C1C9R3WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R3BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R3CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R3DD05# | |
| | | | 9.4pF | ±0.05pF | GRM0222C1C9R4WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R4BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R4CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R4DD05# | |
| | | | 9.5pF | ±0.05pF | GRM0222C1C9R5WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R5BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R5CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R5DD05# | |
| | | | 9.6pF | ±0.05pF | GRM0222C1C9R6WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R6BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R6CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R6DD05# | |
| | | | 9.7pF | ±0.05pF | GRM0222C1C9R7WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R7BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R7CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R7DD05# | |
| | | | 9.8pF | ±0.05pF | GRM0222C1C9R8WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R8BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R8CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R8DD05# | |
| | | | 9.9pF | ±0.05pF | GRM0222C1C9R9WD05# | |
| | | | | ±0.1pF | GRM0222C1C9R9BD05# | |
| | | | | ±0.25pF | GRM0222C1C9R9CD05# | |
| | | | | ±0.5pF | GRM0222C1C9R9DD05# | |
| | | | 10pF | ±2% | GRM0222C1C100GD05# | |
| | | | | ±5% | GRM0222C1C100JD05# | |
| | | | 12pF | ±2% | GRM0222C1C120GD05# | |
| | | | | ±5% | GRM0222C1C120JD05# | |
| | | | 15pF | ±2% | GRM0222C1C150GD05# | |
| | | | | ±5% | GRM0222C1C150JD05# | |
| | | | 18pF | ±2% | GRM0222C1C180GD05# | |
| | | | | ±5% | GRM0222C1C180JD05# | |
| | | | 22pF | ±2% | GRM0222C1C220GD05# | |
| | | | | ±5% | GRM0222C1C220JD05# | |
| | | | 27pF | ±2% | GRM0222C1C270GD05# | |
| | | | | ±5% | GRM0222C1C270JD05# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 16Vdc | CH | 33pF | ±2% | GRM0222C1C330GD05# | |
| | | | | ±5% | GRM0222C1C330JD05# | |
| | | | 39pF | ±2% | GRM0222C1C390GD05# | |
| | | | | ±5% | GRM0222C1C390JD05# | |
| | | | 47pF | ±2% | GRM0222C1C470GD05# | |
| | | | | ±5% | GRM0222C1C470JD05# | |
| | 10Vdc | C0G | 56pF | ±2% | GRM0225C1A560GD05# | |
| | | | | ±5% | GRM0225C1A560JD05# | |
| | | | 68pF | ±2% | GRM0225C1A680GD05# | |
| | | | | ±5% | GRM0225C1A680JD05# | |
| | | | 82pF | ±2% | GRM0225C1A820GD05# | |
| | | | | ±5% | GRM0225C1A820JD05# | |
| | | | 100pF | ±2% | GRM0225C1A101GD05# | |
| | | | | ±5% | GRM0225C1A101JD05# | |
| | | CH | 56pF | ±2% | GRM0222C1A560GD05# | |
| | | | | ±5% | GRM0222C1A560JD05# | |
| | | | 68pF | ±2% | GRM0222C1A680GD05# | |
| | | | | ±5% | GRM0222C1A680JD05# | |
| | | | 82pF | ±2% | GRM0222C1A820GD05# | |
| | | | | ±5% | GRM0222C1A820JD05# | |
| | | | 100pF | ±2% | GRM0222C1A101GD05# | |
| | | | | ±5% | GRM0222C1A101JD05# | |

## ■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | C0G | 0.10pF | ±0.05pF | GRM0335C2AR10WA01# | |
| | | | 0.20pF | ±0.05pF | GRM0335C2AR20WA01# | |
| | | | | ±0.1pF | GRM0335C2AR20BA01# | |
| | | | 0.30pF | ±0.05pF | GRM0335C2AR30WA01# | |
| | | | | ±0.1pF | GRM0335C2AR30BA01# | |
| | | | 0.40pF | ±0.05pF | GRM0335C2AR40WA01# | |
| | | | | ±0.1pF | GRM0335C2AR40BA01# | |
| | | | 0.50pF | ±0.05pF | GRM0335C2AR50WA01# | |
| | | | | ±0.1pF | GRM0335C2AR50BA01# | |
| | | | 0.60pF | ±0.05pF | GRM0335C2AR60WA01# | |
| | | | | ±0.1pF | GRM0335C2AR60BA01# | |
| | | | 0.70pF | ±0.05pF | GRM0335C2AR70WA01# | |
| | | | | ±0.1pF | GRM0335C2AR70BA01# | |
| | | | 0.80pF | ±0.05pF | GRM0335C2AR80WA01# | |
| | | | | ±0.1pF | GRM0335C2AR80BA01# | |
| | | | 0.90pF | ±0.05pF | GRM0335C2AR90WA01# | |
| | | | | ±0.1pF | GRM0335C2AR90BA01# | |
| | | | 1.0pF | ±0.05pF | GRM0335C2A1R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R0CA01# | |
| | | | 1.1pF | ±0.05pF | GRM0335C2A1R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R1CA01# | |
| | | | 1.2pF | ±0.05pF | GRM0335C2A1R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R2CA01# | |
| | | | 1.3pF | ±0.05pF | GRM0335C2A1R3WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | C0G | 1.3pF | ±0.1pF | GRM0335C2A1R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R3CA01# | |
| | | | 1.4pF | ±0.05pF | GRM0335C2A1R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R4CA01# | |
| | | | 1.5pF | ±0.05pF | GRM0335C2A1R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R5CA01# | |
| | | | 1.6pF | ±0.05pF | GRM0335C2A1R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R6CA01# | |
| | | | 1.7pF | ±0.05pF | GRM0335C2A1R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R7CA01# | |
| | | | 1.8pF | ±0.05pF | GRM0335C2A1R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R8CA01# | |
| | | | 1.9pF | ±0.05pF | GRM0335C2A1R9WA01# | |
| | | | | ±0.1pF | GRM0335C2A1R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A1R9CA01# | |
| | | | 2.0pF | ±0.05pF | GRM0335C2A2R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R0CA01# | |
| | | | 2.1pF | ±0.05pF | GRM0335C2A2R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R1CA01# | |
| | | | 2.2pF | ±0.05pF | GRM0335C2A2R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R2CA01# | |
| | | | 2.3pF | ±0.05pF | GRM0335C2A2R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R3CA01# | |
| | | | 2.4pF | ±0.05pF | GRM0335C2A2R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R4CA01# | |
| | | | 2.5pF | ±0.05pF | GRM0335C2A2R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R5CA01# | |
| | | | 2.6pF | ±0.05pF | GRM0335C2A2R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R6CA01# | |
| | | | 2.7pF | ±0.05pF | GRM0335C2A2R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R7CA01# | |
| | | | 2.8pF | ±0.05pF | GRM0335C2A2R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R8CA01# | |
| | | | 2.9pF | ±0.05pF | GRM0335C2A2R9WA01# | |
| | | | | ±0.1pF | GRM0335C2A2R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A2R9CA01# | |
| | | | 3.0pF | ±0.05pF | GRM0335C2A3R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R0CA01# | |
| | | | 3.1pF | ±0.05pF | GRM0335C2A3R1WA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | C0G | 3.1pF | ±0.1pF | GRM0335C2A3R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R1CA01# | |
| | | | 3.2pF | ±0.05pF | GRM0335C2A3R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R2CA01# | |
| | | | 3.3pF | ±0.05pF | GRM0335C2A3R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R3CA01# | |
| | | | 3.4pF | ±0.05pF | GRM0335C2A3R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R4CA01# | |
| | | | 3.5pF | ±0.05pF | GRM0335C2A3R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM0335C2A3R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM0335C2A3R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R7CA01# | |
| | | | 3.8pF | ±0.05pF | GRM0335C2A3R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R8CA01# | |
| | | | 3.9pF | ±0.05pF | GRM0335C2A3R9WA01# | |
| | | | | ±0.1pF | GRM0335C2A3R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A3R9CA01# | |
| | | | 4.0pF | ±0.05pF | GRM0335C2A4R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R0CA01# | |
| | | | 4.1pF | ±0.05pF | GRM0335C2A4R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R1CA01# | |
| | | | 4.2pF | ±0.05pF | GRM0335C2A4R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R2CA01# | |
| | | | 4.3pF | ±0.05pF | GRM0335C2A4R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM0335C2A4R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM0335C2A4R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM0335C2A4R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM0335C2A4R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM0335C2A4R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A4R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM0335C2A4R9WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | C0G | 4.9pF | ±0.1pF | GRM0335C2A4R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM0335C2A5R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM0335C2A5R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R1CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM0335C2A5R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R2CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM0335C2A5R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R3CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM0335C2A5R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R4CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM0335C2A5R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R5CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM0335C2A5R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R6CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM0335C2A5R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R7CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R7DA01# | |
| | | | 5.8pF | ±0.05pF | GRM0335C2A5R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R8CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R8DA01# | |
| | | | 5.9pF | ±0.05pF | GRM0335C2A5R9WA01# | |
| | | | | ±0.1pF | GRM0335C2A5R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A5R9CA01# | |
| | | | | ±0.5pF | GRM0335C2A5R9DA01# | |
| | | | 6.0pF | ±0.05pF | GRM0335C2A6R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R0CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R0DA01# | |
| | | | 6.1pF | ±0.05pF | GRM0335C2A6R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R1CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R1DA01# | |
| | | | 6.2pF | ±0.05pF | GRM0335C2A6R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R2CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R2DA01# | |
| | | | 6.3pF | ±0.05pF | GRM0335C2A6R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R3CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R3DA01# | |
| | | | 6.4pF | ±0.05pF | GRM0335C2A6R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R4CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R4DA01# | |
| | | | 6.5pF | ±0.05pF | GRM0335C2A6R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R5CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R5DA01# | |
| | | | 6.6pF | ±0.05pF | GRM0335C2A6R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R6CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R6DA01# | |
| | | | 6.7pF | ±0.05pF | GRM0335C2A6R7WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R7BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R7CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R7DA01# | |
| | | | 6.8pF | ±0.05pF | GRM0335C2A6R8WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R8BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R8CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R8DA01# | |
| | | | 6.9pF | ±0.05pF | GRM0335C2A6R9WA01# | |
| | | | | ±0.1pF | GRM0335C2A6R9BA01# | |
| | | | | ±0.25pF | GRM0335C2A6R9CA01# | |
| | | | | ±0.5pF | GRM0335C2A6R9DA01# | |
| | | | 7.0pF | ±0.05pF | GRM0335C2A7R0WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R0BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R0CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R0DA01# | |
| | | | 7.1pF | ±0.05pF | GRM0335C2A7R1WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R1BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R1CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R1DA01# | |
| | | | 7.2pF | ±0.05pF | GRM0335C2A7R2WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R2BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R2CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R2DA01# | |
| | | | 7.3pF | ±0.05pF | GRM0335C2A7R3WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R3BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R3CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R3DA01# | |
| | | | 7.4pF | ±0.05pF | GRM0335C2A7R4WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R4BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R4CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R4DA01# | |
| | | | 7.5pF | ±0.05pF | GRM0335C2A7R5WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R5BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R5CA01# | |
| | | | | ±0.5pF | GRM0335C2A7R5DA01# | |
| | | | 7.6pF | ±0.05pF | GRM0335C2A7R6WA01# | |
| | | | | ±0.1pF | GRM0335C2A7R6BA01# | |
| | | | | ±0.25pF | GRM0335C2A7R6CA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | C0G | 7.6pF | ±0.5pF | **GRM0335C2A7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM0335C2A7R7WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A7R7BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A7R7CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM0335C2A7R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A7R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A7R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM0335C2A7R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A7R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A7R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM0335C2A8R0WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R0BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R0CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM0335C2A8R1WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R1BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R1CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM0335C2A8R2WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R2BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R2CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM0335C2A8R3WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R3BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R3CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM0335C2A8R4WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R4BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R4CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R4DA01#** | |
| | | | 8.5pF | ±0.05pF | **GRM0335C2A8R5WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R5BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R5CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R5DA01#** | |
| | | | 8.6pF | ±0.05pF | **GRM0335C2A8R6WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R6BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R6CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R6DA01#** | |
| | | | 8.7pF | ±0.05pF | **GRM0335C2A8R7WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R7BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R7CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R7DA01#** | |
| | | | 8.8pF | ±0.05pF | **GRM0335C2A8R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R8DA01#** | |
| | | | 8.9pF | ±0.05pF | **GRM0335C2A8R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A8R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A8R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A8R9DA01#** | |
| | | | 9.0pF | ±0.05pF | **GRM0335C2A9R0WA01#** | |
| 0.33mm | 100Vdc | C0G | 9.0pF | ±0.1pF | **GRM0335C2A9R0BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R0CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R0DA01#** | |
| | | | 9.1pF | ±0.05pF | **GRM0335C2A9R1WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R1BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R1CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R1DA01#** | |
| | | | 9.2pF | ±0.05pF | **GRM0335C2A9R2WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R2BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R2CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R2DA01#** | |
| | | | 9.3pF | ±0.05pF | **GRM0335C2A9R3WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R3BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R3CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R3DA01#** | |
| | | | 9.4pF | ±0.05pF | **GRM0335C2A9R4WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R4BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R4CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R4DA01#** | |
| | | | 9.5pF | ±0.05pF | **GRM0335C2A9R5WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R5BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R5CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R5DA01#** | |
| | | | 9.6pF | ±0.05pF | **GRM0335C2A9R6WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R6BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R6CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R6DA01#** | |
| | | | 9.7pF | ±0.05pF | **GRM0335C2A9R7WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R7BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R7CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R7DA01#** | |
| | | | 9.8pF | ±0.05pF | **GRM0335C2A9R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R8DA01#** | |
| | | | 9.9pF | ±0.05pF | **GRM0335C2A9R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C2A9R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C2A9R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C2A9R9DA01#** | |
| | | | 10pF | ±2% | **GRM0335C2A100GA01#** | |
| | | | | ±5% | **GRM0335C2A100JA01#** | |
| | | | 12pF | ±2% | **GRM0335C2A120GA01#** | |
| | | | | ±5% | **GRM0335C2A120JA01#** | |
| | | | 15pF | ±2% | **GRM0335C2A150GA01#** | |
| | | | | ±5% | **GRM0335C2A150JA01#** | |
| | | CK | 0.10pF | ±0.05pF | **GRM0334C2AR10WA01#** | |
| | | | 0.20pF | ±0.05pF | **GRM0334C2AR20WA01#** | |
| | | | | ±0.1pF | **GRM0334C2AR20BA01#** | |
| | | | 0.30pF | ±0.05pF | **GRM0334C2AR30WA01#** | |
| | | | | ±0.1pF | **GRM0334C2AR30BA01#** | |
| | | | 0.40pF | ±0.05pF | **GRM0334C2AR40WA01#** | |
| | | | | ±0.1pF | **GRM0334C2AR40BA01#** | |
| | | | 0.50pF | ±0.05pF | **GRM0334C2AR50WA01#** | |
| | | | | ±0.1pF | **GRM0334C2AR50BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CK | 0.60pF | ±0.05pF | GRM0334C2AR60WA01# |
| | | | | ±0.1pF | GRM0334C2AR60BA01# |
| | | | 0.70pF | ±0.05pF | GRM0334C2AR70WA01# |
| | | | | ±0.1pF | GRM0334C2AR70BA01# |
| | | | 0.80pF | ±0.05pF | GRM0334C2AR80WA01# |
| | | | | ±0.1pF | GRM0334C2AR80BA01# |
| | | | 0.90pF | ±0.05pF | GRM0334C2AR90WA01# |
| | | | | ±0.1pF | GRM0334C2AR90BA01# |
| | | | 1.0pF | ±0.05pF | GRM0334C2A1R0WA01# |
| | | | | ±0.1pF | GRM0334C2A1R0BA01# |
| | | | | ±0.25pF | GRM0334C2A1R0CA01# |
| | | | 1.1pF | ±0.05pF | GRM0334C2A1R1WA01# |
| | | | | ±0.1pF | GRM0334C2A1R1BA01# |
| | | | | ±0.25pF | GRM0334C2A1R1CA01# |
| | | | 1.2pF | ±0.05pF | GRM0334C2A1R2WA01# |
| | | | | ±0.1pF | GRM0334C2A1R2BA01# |
| | | | | ±0.25pF | GRM0334C2A1R2CA01# |
| | | | 1.3pF | ±0.05pF | GRM0334C2A1R3WA01# |
| | | | | ±0.1pF | GRM0334C2A1R3BA01# |
| | | | | ±0.25pF | GRM0334C2A1R3CA01# |
| | | | 1.4pF | ±0.05pF | GRM0334C2A1R4WA01# |
| | | | | ±0.1pF | GRM0334C2A1R4BA01# |
| | | | | ±0.25pF | GRM0334C2A1R4CA01# |
| | | | 1.5pF | ±0.05pF | GRM0334C2A1R5WA01# |
| | | | | ±0.1pF | GRM0334C2A1R5BA01# |
| | | | | ±0.25pF | GRM0334C2A1R5CA01# |
| | | | 1.6pF | ±0.05pF | GRM0334C2A1R6WA01# |
| | | | | ±0.1pF | GRM0334C2A1R6BA01# |
| | | | | ±0.25pF | GRM0334C2A1R6CA01# |
| | | | 1.7pF | ±0.05pF | GRM0334C2A1R7WA01# |
| | | | | ±0.1pF | GRM0334C2A1R7BA01# |
| | | | | ±0.25pF | GRM0334C2A1R7CA01# |
| | | | 1.8pF | ±0.05pF | GRM0334C2A1R8WA01# |
| | | | | ±0.1pF | GRM0334C2A1R8BA01# |
| | | | | ±0.25pF | GRM0334C2A1R8CA01# |
| | | | 1.9pF | ±0.05pF | GRM0334C2A1R9WA01# |
| | | | | ±0.1pF | GRM0334C2A1R9BA01# |
| | | | | ±0.25pF | GRM0334C2A1R9CA01# |
| | | | 2.0pF | ±0.05pF | GRM0334C2A2R0WA01# |
| | | | | ±0.1pF | GRM0334C2A2R0BA01# |
| | | | | ±0.25pF | GRM0334C2A2R0CA01# |
| | | CJ | 2.1pF | ±0.05pF | GRM0333C2A2R1WA01# |
| | | | | ±0.1pF | GRM0333C2A2R1BA01# |
| | | | | ±0.25pF | GRM0333C2A2R1CA01# |
| | | | 2.2pF | ±0.05pF | GRM0333C2A2R2WA01# |
| | | | | ±0.1pF | GRM0333C2A2R2BA01# |
| | | | | ±0.25pF | GRM0333C2A2R2CA01# |
| | | | 2.3pF | ±0.05pF | GRM0333C2A2R3WA01# |
| | | | | ±0.1pF | GRM0333C2A2R3BA01# |
| | | | | ±0.25pF | GRM0333C2A2R3CA01# |
| | | | 2.4pF | ±0.05pF | GRM0333C2A2R4WA01# |
| | | | | ±0.1pF | GRM0333C2A2R4BA01# |
| | | | | ±0.25pF | GRM0333C2A2R4CA01# |
| | | | 2.5pF | ±0.05pF | GRM0333C2A2R5WA01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CJ | 2.5pF | ±0.1pF | GRM0333C2A2R5BA01# |
| | | | | ±0.25pF | GRM0333C2A2R5CA01# |
| | | | 2.6pF | ±0.05pF | GRM0333C2A2R6WA01# |
| | | | | ±0.1pF | GRM0333C2A2R6BA01# |
| | | | | ±0.25pF | GRM0333C2A2R6CA01# |
| | | | 2.7pF | ±0.05pF | GRM0333C2A2R7WA01# |
| | | | | ±0.1pF | GRM0333C2A2R7BA01# |
| | | | | ±0.25pF | GRM0333C2A2R7CA01# |
| | | | 2.8pF | ±0.05pF | GRM0333C2A2R8WA01# |
| | | | | ±0.1pF | GRM0333C2A2R8BA01# |
| | | | | ±0.25pF | GRM0333C2A2R8CA01# |
| | | | 2.9pF | ±0.05pF | GRM0333C2A2R9WA01# |
| | | | | ±0.1pF | GRM0333C2A2R9BA01# |
| | | | | ±0.25pF | GRM0333C2A2R9CA01# |
| | | | 3.0pF | ±0.05pF | GRM0333C2A3R0WA01# |
| | | | | ±0.1pF | GRM0333C2A3R0BA01# |
| | | | | ±0.25pF | GRM0333C2A3R0CA01# |
| | | | 3.1pF | ±0.05pF | GRM0333C2A3R1WA01# |
| | | | | ±0.1pF | GRM0333C2A3R1BA01# |
| | | | | ±0.25pF | GRM0333C2A3R1CA01# |
| | | | 3.2pF | ±0.05pF | GRM0333C2A3R2WA01# |
| | | | | ±0.1pF | GRM0333C2A3R2BA01# |
| | | | | ±0.25pF | GRM0333C2A3R2CA01# |
| | | | 3.3pF | ±0.05pF | GRM0333C2A3R3WA01# |
| | | | | ±0.1pF | GRM0333C2A3R3BA01# |
| | | | | ±0.25pF | GRM0333C2A3R3CA01# |
| | | | 3.4pF | ±0.05pF | GRM0333C2A3R4WA01# |
| | | | | ±0.1pF | GRM0333C2A3R4BA01# |
| | | | | ±0.25pF | GRM0333C2A3R4CA01# |
| | | | 3.5pF | ±0.05pF | GRM0333C2A3R5WA01# |
| | | | | ±0.1pF | GRM0333C2A3R5BA01# |
| | | | | ±0.25pF | GRM0333C2A3R5CA01# |
| | | | 3.6pF | ±0.05pF | GRM0333C2A3R6WA01# |
| | | | | ±0.1pF | GRM0333C2A3R6BA01# |
| | | | | ±0.25pF | GRM0333C2A3R6CA01# |
| | | | 3.7pF | ±0.05pF | GRM0333C2A3R7WA01# |
| | | | | ±0.1pF | GRM0333C2A3R7BA01# |
| | | | | ±0.25pF | GRM0333C2A3R7CA01# |
| | | | 3.8pF | ±0.05pF | GRM0333C2A3R8WA01# |
| | | | | ±0.1pF | GRM0333C2A3R8BA01# |
| | | | | ±0.25pF | GRM0333C2A3R8CA01# |
| | | | 3.9pF | ±0.05pF | GRM0333C2A3R9WA01# |
| | | | | ±0.1pF | GRM0333C2A3R9BA01# |
| | | | | ±0.25pF | GRM0333C2A3R9CA01# |
| | | CH | 4.0pF | ±0.05pF | GRM0332C2A4R0WA01# |
| | | | | ±0.1pF | GRM0332C2A4R0BA01# |
| | | | | ±0.25pF | GRM0332C2A4R0CA01# |
| | | | 4.1pF | ±0.05pF | GRM0332C2A4R1WA01# |
| | | | | ±0.1pF | GRM0332C2A4R1BA01# |
| | | | | ±0.25pF | GRM0332C2A4R1CA01# |
| | | | 4.2pF | ±0.05pF | GRM0332C2A4R2WA01# |
| | | | | ±0.1pF | GRM0332C2A4R2BA01# |
| | | | | ±0.25pF | GRM0332C2A4R2CA01# |
| | | | 4.3pF | ±0.05pF | GRM0332C2A4R3WA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CH | 4.3pF | ±0.1pF | GRM0332C2A4R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM0332C2A4R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM0332C2A4R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM0332C2A4R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM0332C2A4R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM0332C2A4R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM0332C2A4R9WA01# | |
| | | | | ±0.1pF | GRM0332C2A4R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM0332C2A5R0WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R0BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM0332C2A5R1WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R1BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R1CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM0332C2A5R2WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R2BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R2CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM0332C2A5R3WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R3CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM0332C2A5R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R4CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM0332C2A5R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R5CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM0332C2A5R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R6CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM0332C2A5R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R7CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R7DA01# | |
| | | | 5.8pF | ±0.05pF | GRM0332C2A5R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R8CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CH | 5.8pF | ±0.5pF | GRM0332C2A5R8DA01# | |
| | | | 5.9pF | ±0.05pF | GRM0332C2A5R9WA01# | |
| | | | | ±0.1pF | GRM0332C2A5R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A5R9CA01# | |
| | | | | ±0.5pF | GRM0332C2A5R9DA01# | |
| | | | 6.0pF | ±0.05pF | GRM0332C2A6R0WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R0BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R0CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R0DA01# | |
| | | | 6.1pF | ±0.05pF | GRM0332C2A6R1WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R1BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R1CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R1DA01# | |
| | | | 6.2pF | ±0.05pF | GRM0332C2A6R2WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R2BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R2CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R2DA01# | |
| | | | 6.3pF | ±0.05pF | GRM0332C2A6R3WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R3CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R3DA01# | |
| | | | 6.4pF | ±0.05pF | GRM0332C2A6R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R4CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R4DA01# | |
| | | | 6.5pF | ±0.05pF | GRM0332C2A6R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R5CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R5DA01# | |
| | | | 6.6pF | ±0.05pF | GRM0332C2A6R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R6CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R6DA01# | |
| | | | 6.7pF | ±0.05pF | GRM0332C2A6R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R7CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R7DA01# | |
| | | | 6.8pF | ±0.05pF | GRM0332C2A6R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R8CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R8DA01# | |
| | | | 6.9pF | ±0.05pF | GRM0332C2A6R9WA01# | |
| | | | | ±0.1pF | GRM0332C2A6R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A6R9CA01# | |
| | | | | ±0.5pF | GRM0332C2A6R9DA01# | |
| | | | 7.0pF | ±0.05pF | GRM0332C2A7R0WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R0BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R0CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R0DA01# | |
| | | | 7.1pF | ±0.05pF | GRM0332C2A7R1WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R1BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R1CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R1DA01# | |
| | | | 7.2pF | ±0.05pF | GRM0332C2A7R2WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CH | 7.2pF | ±0.1pF | GRM0332C2A7R2BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R2CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R2DA01# | |
| | | | 7.3pF | ±0.05pF | GRM0332C2A7R3WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R3CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R3DA01# | |
| | | | 7.4pF | ±0.05pF | GRM0332C2A7R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R4CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R4DA01# | |
| | | | 7.5pF | ±0.05pF | GRM0332C2A7R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R5CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R5DA01# | |
| | | | 7.6pF | ±0.05pF | GRM0332C2A7R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R6CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R6DA01# | |
| | | | 7.7pF | ±0.05pF | GRM0332C2A7R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R7CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R7DA01# | |
| | | | 7.8pF | ±0.05pF | GRM0332C2A7R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R8CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R8DA01# | |
| | | | 7.9pF | ±0.05pF | GRM0332C2A7R9WA01# | |
| | | | | ±0.1pF | GRM0332C2A7R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A7R9CA01# | |
| | | | | ±0.5pF | GRM0332C2A7R9DA01# | |
| | | | 8.0pF | ±0.05pF | GRM0332C2A8R0WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R0BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R0CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R0DA01# | |
| | | | 8.1pF | ±0.05pF | GRM0332C2A8R1WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R1BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R1CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R1DA01# | |
| | | | 8.2pF | ±0.05pF | GRM0332C2A8R2WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R2BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R2CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R2DA01# | |
| | | | 8.3pF | ±0.05pF | GRM0332C2A8R3WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R3CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R3DA01# | |
| | | | 8.4pF | ±0.05pF | GRM0332C2A8R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R4CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R4DA01# | |
| | | | 8.5pF | ±0.05pF | GRM0332C2A8R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R5CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CH | 8.5pF | ±0.5pF | GRM0332C2A8R5DA01# | |
| | | | 8.6pF | ±0.05pF | GRM0332C2A8R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R6CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R6DA01# | |
| | | | 8.7pF | ±0.05pF | GRM0332C2A8R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R7CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R7DA01# | |
| | | | 8.8pF | ±0.05pF | GRM0332C2A8R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R8CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R8DA01# | |
| | | | 8.9pF | ±0.05pF | GRM0332C2A8R9WA01# | |
| | | | | ±0.1pF | GRM0332C2A8R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A8R9CA01# | |
| | | | | ±0.5pF | GRM0332C2A8R9DA01# | |
| | | | 9.0pF | ±0.05pF | GRM0332C2A9R0WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R0BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R0CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R0DA01# | |
| | | | 9.1pF | ±0.05pF | GRM0332C2A9R1WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R1BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R1CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R1DA01# | |
| | | | 9.2pF | ±0.05pF | GRM0332C2A9R2WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R2BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R2CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R2DA01# | |
| | | | 9.3pF | ±0.05pF | GRM0332C2A9R3WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R3BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R3CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R3DA01# | |
| | | | 9.4pF | ±0.05pF | GRM0332C2A9R4WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R4BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R4CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R4DA01# | |
| | | | 9.5pF | ±0.05pF | GRM0332C2A9R5WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R5BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R5CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R5DA01# | |
| | | | 9.6pF | ±0.05pF | GRM0332C2A9R6WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R6BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R6CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R6DA01# | |
| | | | 9.7pF | ±0.05pF | GRM0332C2A9R7WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R7BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R7CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R7DA01# | |
| | | | 9.8pF | ±0.05pF | GRM0332C2A9R8WA01# | |
| | | | | ±0.1pF | GRM0332C2A9R8BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R8CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R8DA01# | |
| | | | 9.9pF | ±0.05pF | GRM0332C2A9R9WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 100Vdc | CH | 9.9pF | ±0.1pF | GRM0332C2A9R9BA01# | |
| | | | | ±0.25pF | GRM0332C2A9R9CA01# | |
| | | | | ±0.5pF | GRM0332C2A9R9DA01# | |
| | | | 10pF | ±2% | GRM0332C2A100GA01# | |
| | | | | ±5% | GRM0332C2A100JA01# | |
| | | | 12pF | ±2% | GRM0332C2A120GA01# | |
| | | | | ±5% | GRM0332C2A120JA01# | |
| | | | 15pF | ±2% | GRM0332C2A150GA01# | |
| | | | | ±5% | GRM0332C2A150JA01# | |
| | 50Vdc | C0G | 0.10pF | ±0.05pF | GRM0335C1HR10WA01# | |
| | | | 0.20pF | ±0.05pF | GRM0335C1HR20WA01# | |
| | | | | ±0.1pF | GRM0335C1HR20BA01# | |
| | | | 0.30pF | ±0.05pF | GRM0335C1HR30WA01# | |
| | | | | ±0.1pF | GRM0335C1HR30BA01# | |
| | | | 0.40pF | ±0.05pF | GRM0335C1HR40WA01# | |
| | | | | ±0.1pF | GRM0335C1HR40BA01# | |
| | | | 0.50pF | ±0.05pF | GRM0335C1HR50WA01# | |
| | | | | ±0.1pF | GRM0335C1HR50BA01# | |
| | | | 0.60pF | ±0.05pF | GRM0335C1HR60WA01# | |
| | | | | ±0.1pF | GRM0335C1HR60BA01# | |
| | | | 0.70pF | ±0.05pF | GRM0335C1HR70WA01# | |
| | | | | ±0.1pF | GRM0335C1HR70BA01# | |
| | | | 0.80pF | ±0.05pF | GRM0335C1HR80WA01# | |
| | | | | ±0.1pF | GRM0335C1HR80BA01# | |
| | | | 0.90pF | ±0.05pF | GRM0335C1HR90WA01# | |
| | | | | ±0.1pF | GRM0335C1HR90BA01# | |
| | | | 1.0pF | ±0.05pF | GRM0335C1H1R0WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R0BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R0CA01# | |
| | | | 1.1pF | ±0.05pF | GRM0335C1H1R1WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R1BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R1CA01# | |
| | | | 1.2pF | ±0.05pF | GRM0335C1H1R2WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R2BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R2CA01# | |
| | | | 1.3pF | ±0.05pF | GRM0335C1H1R3WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R3BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R3CA01# | |
| | | | 1.4pF | ±0.05pF | GRM0335C1H1R4WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R4BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R4CA01# | |
| | | | 1.5pF | ±0.05pF | GRM0335C1H1R5WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R5BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R5CA01# | |
| | | | 1.6pF | ±0.05pF | GRM0335C1H1R6WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R6BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R6CA01# | |
| | | | 1.7pF | ±0.05pF | GRM0335C1H1R7WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R7BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R7CA01# | |
| | | | 1.8pF | ±0.05pF | GRM0335C1H1R8WA01# | |
| | | | | ±0.1pF | GRM0335C1H1R8BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R8CA01# | |
| | | | 1.9pF | ±0.05pF | GRM0335C1H1R9WA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | C0G | 1.9pF | ±0.1pF | GRM0335C1H1R9BA01# | |
| | | | | ±0.25pF | GRM0335C1H1R9CA01# | |
| | | | 2.0pF | ±0.05pF | GRM0335C1H2R0WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R0BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R0CA01# | |
| | | | 2.1pF | ±0.05pF | GRM0335C1H2R1WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R1BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R1CA01# | |
| | | | 2.2pF | ±0.05pF | GRM0335C1H2R2WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R2BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R2CA01# | |
| | | | 2.3pF | ±0.05pF | GRM0335C1H2R3WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R3BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R3CA01# | |
| | | | 2.4pF | ±0.05pF | GRM0335C1H2R4WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R4BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R4CA01# | |
| | | | 2.5pF | ±0.05pF | GRM0335C1H2R5WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R5BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R5CA01# | |
| | | | 2.6pF | ±0.05pF | GRM0335C1H2R6WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R6BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R6CA01# | |
| | | | 2.7pF | ±0.05pF | GRM0335C1H2R7WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R7BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R7CA01# | |
| | | | 2.8pF | ±0.05pF | GRM0335C1H2R8WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R8BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R8CA01# | |
| | | | 2.9pF | ±0.05pF | GRM0335C1H2R9WA01# | |
| | | | | ±0.1pF | GRM0335C1H2R9BA01# | |
| | | | | ±0.25pF | GRM0335C1H2R9CA01# | |
| | | | 3.0pF | ±0.05pF | GRM0335C1H3R0WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R0BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R0CA01# | |
| | | | 3.1pF | ±0.05pF | GRM0335C1H3R1WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R1BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R1CA01# | |
| | | | 3.2pF | ±0.05pF | GRM0335C1H3R2WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R2BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R2CA01# | |
| | | | 3.3pF | ±0.05pF | GRM0335C1H3R3WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R3BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R3CA01# | |
| | | | 3.4pF | ±0.05pF | GRM0335C1H3R4WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R4BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R4CA01# | |
| | | | 3.5pF | ±0.05pF | GRM0335C1H3R5WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R5BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM0335C1H3R6WA01# | |
| | | | | ±0.1pF | GRM0335C1H3R6BA01# | |
| | | | | ±0.25pF | GRM0335C1H3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM0335C1H3R7WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 50Vdc | C0G | 3.7pF | ±0.1pF | GRM0335C1H3R7BA01# |
| | | | | ±0.25pF | GRM0335C1H3R7CA01# |
| | | | 3.8pF | ±0.05pF | GRM0335C1H3R8WA01# |
| | | | | ±0.1pF | GRM0335C1H3R8BA01# |
| | | | | ±0.25pF | GRM0335C1H3R8CA01# |
| | | | 3.9pF | ±0.05pF | GRM0335C1H3R9WA01# |
| | | | | ±0.1pF | GRM0335C1H3R9BA01# |
| | | | | ±0.25pF | GRM0335C1H3R9CA01# |
| | | | 4.0pF | ±0.05pF | GRM0335C1H4R0WA01# |
| | | | | ±0.1pF | GRM0335C1H4R0BA01# |
| | | | | ±0.25pF | GRM0335C1H4R0CA01# |
| | | | 4.1pF | ±0.05pF | GRM0335C1H4R1WA01# |
| | | | | ±0.1pF | GRM0335C1H4R1BA01# |
| | | | | ±0.25pF | GRM0335C1H4R1CA01# |
| | | | 4.2pF | ±0.05pF | GRM0335C1H4R2WA01# |
| | | | | ±0.1pF | GRM0335C1H4R2BA01# |
| | | | | ±0.25pF | GRM0335C1H4R2CA01# |
| | | | 4.3pF | ±0.05pF | GRM0335C1H4R3WA01# |
| | | | | ±0.1pF | GRM0335C1H4R3BA01# |
| | | | | ±0.25pF | GRM0335C1H4R3CA01# |
| | | | 4.4pF | ±0.05pF | GRM0335C1H4R4WA01# |
| | | | | ±0.1pF | GRM0335C1H4R4BA01# |
| | | | | ±0.25pF | GRM0335C1H4R4CA01# |
| | | | 4.5pF | ±0.05pF | GRM0335C1H4R5WA01# |
| | | | | ±0.1pF | GRM0335C1H4R5BA01# |
| | | | | ±0.25pF | GRM0335C1H4R5CA01# |
| | | | 4.6pF | ±0.05pF | GRM0335C1H4R6WA01# |
| | | | | ±0.1pF | GRM0335C1H4R6BA01# |
| | | | | ±0.25pF | GRM0335C1H4R6CA01# |
| | | | 4.7pF | ±0.05pF | GRM0335C1H4R7WA01# |
| | | | | ±0.1pF | GRM0335C1H4R7BA01# |
| | | | | ±0.25pF | GRM0335C1H4R7CA01# |
| | | | 4.8pF | ±0.05pF | GRM0335C1H4R8WA01# |
| | | | | ±0.1pF | GRM0335C1H4R8BA01# |
| | | | | ±0.25pF | GRM0335C1H4R8CA01# |
| | | | 4.9pF | ±0.05pF | GRM0335C1H4R9WA01# |
| | | | | ±0.1pF | GRM0335C1H4R9BA01# |
| | | | | ±0.25pF | GRM0335C1H4R9CA01# |
| | | | 5.0pF | ±0.05pF | GRM0335C1H5R0WA01# |
| | | | | ±0.1pF | GRM0335C1H5R0BA01# |
| | | | | ±0.25pF | GRM0335C1H5R0CA01# |
| | | | 5.1pF | ±0.05pF | GRM0335C1H5R1WA01# |
| | | | | ±0.1pF | GRM0335C1H5R1BA01# |
| | | | | ±0.25pF | GRM0335C1H5R1CA01# |
| | | | | ±0.5pF | GRM0335C1H5R1DA01# |
| | | | 5.2pF | ±0.05pF | GRM0335C1H5R2WA01# |
| | | | | ±0.1pF | GRM0335C1H5R2BA01# |
| | | | | ±0.25pF | GRM0335C1H5R2CA01# |
| | | | | ±0.5pF | GRM0335C1H5R2DA01# |
| | | | 5.3pF | ±0.05pF | GRM0335C1H5R3WA01# |
| | | | | ±0.1pF | GRM0335C1H5R3BA01# |
| | | | | ±0.25pF | GRM0335C1H5R3CA01# |
| | | | | ±0.5pF | GRM0335C1H5R3DA01# |
| | | | 5.4pF | ±0.05pF | GRM0335C1H5R4WA01# |
| | | | | ±0.1pF | GRM0335C1H5R4BA01# |
| | | | | ±0.25pF | GRM0335C1H5R4CA01# |
| | | | | ±0.5pF | GRM0335C1H5R4DA01# |
| | | | 5.5pF | ±0.05pF | GRM0335C1H5R5WA01# |
| | | | | ±0.1pF | GRM0335C1H5R5BA01# |
| | | | | ±0.25pF | GRM0335C1H5R5CA01# |
| | | | | ±0.5pF | GRM0335C1H5R5DA01# |
| | | | 5.6pF | ±0.05pF | GRM0335C1H5R6WA01# |
| | | | | ±0.1pF | GRM0335C1H5R6BA01# |
| | | | | ±0.25pF | GRM0335C1H5R6CA01# |
| | | | | ±0.5pF | GRM0335C1H5R6DA01# |
| | | | 5.7pF | ±0.05pF | GRM0335C1H5R7WA01# |
| | | | | ±0.1pF | GRM0335C1H5R7BA01# |
| | | | | ±0.25pF | GRM0335C1H5R7CA01# |
| | | | | ±0.5pF | GRM0335C1H5R7DA01# |
| | | | 5.8pF | ±0.05pF | GRM0335C1H5R8WA01# |
| | | | | ±0.1pF | GRM0335C1H5R8BA01# |
| | | | | ±0.25pF | GRM0335C1H5R8CA01# |
| | | | | ±0.5pF | GRM0335C1H5R8DA01# |
| | | | 5.9pF | ±0.05pF | GRM0335C1H5R9WA01# |
| | | | | ±0.1pF | GRM0335C1H5R9BA01# |
| | | | | ±0.25pF | GRM0335C1H5R9CA01# |
| | | | | ±0.5pF | GRM0335C1H5R9DA01# |
| | | | 6.0pF | ±0.05pF | GRM0335C1H6R0WA01# |
| | | | | ±0.1pF | GRM0335C1H6R0BA01# |
| | | | | ±0.25pF | GRM0335C1H6R0CA01# |
| | | | | ±0.5pF | GRM0335C1H6R0DA01# |
| | | | 6.1pF | ±0.05pF | GRM0335C1H6R1WA01# |
| | | | | ±0.1pF | GRM0335C1H6R1BA01# |
| | | | | ±0.25pF | GRM0335C1H6R1CA01# |
| | | | | ±0.5pF | GRM0335C1H6R1DA01# |
| | | | 6.2pF | ±0.05pF | GRM0335C1H6R2WA01# |
| | | | | ±0.1pF | GRM0335C1H6R2BA01# |
| | | | | ±0.25pF | GRM0335C1H6R2CA01# |
| | | | | ±0.5pF | GRM0335C1H6R2DA01# |
| | | | 6.3pF | ±0.05pF | GRM0335C1H6R3WA01# |
| | | | | ±0.1pF | GRM0335C1H6R3BA01# |
| | | | | ±0.25pF | GRM0335C1H6R3CA01# |
| | | | | ±0.5pF | GRM0335C1H6R3DA01# |
| | | | 6.4pF | ±0.05pF | GRM0335C1H6R4WA01# |
| | | | | ±0.1pF | GRM0335C1H6R4BA01# |
| | | | | ±0.25pF | GRM0335C1H6R4CA01# |
| | | | | ±0.5pF | GRM0335C1H6R4DA01# |
| | | | 6.5pF | ±0.05pF | GRM0335C1H6R5WA01# |
| | | | | ±0.1pF | GRM0335C1H6R5BA01# |
| | | | | ±0.25pF | GRM0335C1H6R5CA01# |
| | | | | ±0.5pF | GRM0335C1H6R5DA01# |
| | | | 6.6pF | ±0.05pF | GRM0335C1H6R6WA01# |
| | | | | ±0.1pF | GRM0335C1H6R6BA01# |
| | | | | ±0.25pF | GRM0335C1H6R6CA01# |
| | | | | ±0.5pF | GRM0335C1H6R6DA01# |
| | | | 6.7pF | ±0.05pF | GRM0335C1H6R7WA01# |
| | | | | ±0.1pF | GRM0335C1H6R7BA01# |
| | | | | ±0.25pF | GRM0335C1H6R7CA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | C0G | 6.7pF | ±0.5pF | **GRM0335C1H6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM0335C1H6R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H6R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H6R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM0335C1H6R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H6R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H6R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM0335C1H7R0WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R0BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R0CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM0335C1H7R1WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R1BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R1CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM0335C1H7R2WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R2BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R2CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM0335C1H7R3WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R3BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R3CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM0335C1H7R4WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R4BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R4CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM0335C1H7R5WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R5BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R5CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM0335C1H7R6WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R6BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R6CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM0335C1H7R7WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R7BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R7CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM0335C1H7R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM0335C1H7R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H7R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H7R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM0335C1H8R0WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R0BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R0CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM0335C1H8R1WA01#** | |
| 0.33mm | 50Vdc | C0G | 8.1pF | ±0.1pF | **GRM0335C1H8R1BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R1CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM0335C1H8R2WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R2BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R2CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM0335C1H8R3WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R3BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R3CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM0335C1H8R4WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R4BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R4CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R4DA01#** | |
| | | | 8.5pF | ±0.05pF | **GRM0335C1H8R5WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R5BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R5CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R5DA01#** | |
| | | | 8.6pF | ±0.05pF | **GRM0335C1H8R6WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R6BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R6CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R6DA01#** | |
| | | | 8.7pF | ±0.05pF | **GRM0335C1H8R7WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R7BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R7CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R7DA01#** | |
| | | | 8.8pF | ±0.05pF | **GRM0335C1H8R8WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R8BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R8CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R8DA01#** | |
| | | | 8.9pF | ±0.05pF | **GRM0335C1H8R9WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H8R9BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H8R9CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H8R9DA01#** | |
| | | | 9.0pF | ±0.05pF | **GRM0335C1H9R0WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H9R0BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H9R0CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H9R0DA01#** | |
| | | | 9.1pF | ±0.05pF | **GRM0335C1H9R1WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H9R1BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H9R1CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H9R1DA01#** | |
| | | | 9.2pF | ±0.05pF | **GRM0335C1H9R2WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H9R2BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H9R2CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H9R2DA01#** | |
| | | | 9.3pF | ±0.05pF | **GRM0335C1H9R3WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H9R3BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H9R3CA01#** | |
| | | | | ±0.5pF | **GRM0335C1H9R3DA01#** | |
| | | | 9.4pF | ±0.05pF | **GRM0335C1H9R4WA01#** | |
| | | | | ±0.1pF | **GRM0335C1H9R4BA01#** | |
| | | | | ±0.25pF | **GRM0335C1H9R4CA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 50Vdc | C0G | 9.4pF | ±0.5pF | **GRM0335C1H9R4DA01#** |
| | | | 9.5pF | ±0.05pF | **GRM0335C1H9R5WA01#** |
| | | | | ±0.1pF | **GRM0335C1H9R5BA01#** |
| | | | | ±0.25pF | **GRM0335C1H9R5CA01#** |
| | | | | ±0.5pF | **GRM0335C1H9R5DA01#** |
| | | | 9.6pF | ±0.05pF | **GRM0335C1H9R6WA01#** |
| | | | | ±0.1pF | **GRM0335C1H9R6BA01#** |
| | | | | ±0.25pF | **GRM0335C1H9R6CA01#** |
| | | | | ±0.5pF | **GRM0335C1H9R6DA01#** |
| | | | 9.7pF | ±0.05pF | **GRM0335C1H9R7WA01#** |
| | | | | ±0.1pF | **GRM0335C1H9R7BA01#** |
| | | | | ±0.25pF | **GRM0335C1H9R7CA01#** |
| | | | | ±0.5pF | **GRM0335C1H9R7DA01#** |
| | | | 9.8pF | ±0.05pF | **GRM0335C1H9R8WA01#** |
| | | | | ±0.1pF | **GRM0335C1H9R8BA01#** |
| | | | | ±0.25pF | **GRM0335C1H9R8CA01#** |
| | | | | ±0.5pF | **GRM0335C1H9R8DA01#** |
| | | | 9.9pF | ±0.05pF | **GRM0335C1H9R9WA01#** |
| | | | | ±0.1pF | **GRM0335C1H9R9BA01#** |
| | | | | ±0.25pF | **GRM0335C1H9R9CA01#** |
| | | | | ±0.5pF | **GRM0335C1H9R9DA01#** |
| | | | 10pF | ±2% | **GRM0335C1H100GA01#** |
| | | | | ±5% | **GRM0335C1H100JA01#** |
| | | | 12pF | ±2% | **GRM0335C1H120GA01#** |
| | | | | ±5% | **GRM0335C1H120JA01#** |
| | | | 15pF | ±2% | **GRM0335C1H150GA01#** |
| | | | | ±5% | **GRM0335C1H150JA01#** |
| | | | 18pF | ±2% | **GRM0335C1H180GA01#** |
| | | | | ±5% | **GRM0335C1H180JA01#** |
| | | | 22pF | ±2% | **GRM0335C1H220GA01#** |
| | | | | ±5% | **GRM0335C1H220JA01#** |
| | | | 27pF | ±2% | **GRM0335C1H270GA01#** |
| | | | | ±5% | **GRM0335C1H270JA01#** |
| | | | 33pF | ±2% | **GRM0335C1H330GA01#** |
| | | | | ±5% | **GRM0335C1H330JA01#** |
| | | | 39pF | ±2% | **GRM0335C1H390GA01#** |
| | | | | ±5% | **GRM0335C1H390JA01#** |
| | | | 47pF | ±2% | **GRM0335C1H470GA01#** |
| | | | | ±5% | **GRM0335C1H470JA01#** |
| | | | 56pF | ±2% | **GRM0335C1H560GA01#** |
| | | | | ±5% | **GRM0335C1H560JA01#** |
| | | | 68pF | ±2% | **GRM0335C1H680GA01#** |
| | | | | ±5% | **GRM0335C1H680JA01#** |
| | | | 82pF | ±2% | **GRM0335C1H820GA01#** |
| | | | | ±5% | **GRM0335C1H820JA01#** |
| | | | 100pF | ±2% | **GRM0335C1H101GA01#** |
| | | | | ±5% | **GRM0335C1H101JA01#** |
| | | | 120pF | ±2% | **GRM0335C1H121GA01#** |
| | | | | ±5% | **GRM0335C1H121JA01#** |
| | | CK | 0.10pF | ±0.05pF | **GRM0334C1HR10WA01#** |
| | | | 0.20pF | ±0.05pF | **GRM0334C1HR20WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR20BA01#** |
| | | | 0.30pF | ±0.05pF | **GRM0334C1HR30WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR30BA01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 50Vdc | CK | 0.40pF | ±0.05pF | **GRM0334C1HR40WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR40BA01#** |
| | | | 0.50pF | ±0.05pF | **GRM0334C1HR50WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR50BA01#** |
| | | | 0.60pF | ±0.05pF | **GRM0334C1HR60WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR60BA01#** |
| | | | 0.70pF | ±0.05pF | **GRM0334C1HR70WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR70BA01#** |
| | | | 0.80pF | ±0.05pF | **GRM0334C1HR80WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR80BA01#** |
| | | | 0.90pF | ±0.05pF | **GRM0334C1HR90WA01#** |
| | | | | ±0.1pF | **GRM0334C1HR90BA01#** |
| | | | 1.0pF | ±0.05pF | **GRM0334C1H1R0WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R0BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R0CA01#** |
| | | | 1.1pF | ±0.05pF | **GRM0334C1H1R1WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R1BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R1CA01#** |
| | | | 1.2pF | ±0.05pF | **GRM0334C1H1R2WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R2BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R2CA01#** |
| | | | 1.3pF | ±0.05pF | **GRM0334C1H1R3WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R3BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R3CA01#** |
| | | | 1.4pF | ±0.05pF | **GRM0334C1H1R4WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R4BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R4CA01#** |
| | | | 1.5pF | ±0.05pF | **GRM0334C1H1R5WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R5BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R5CA01#** |
| | | | 1.6pF | ±0.05pF | **GRM0334C1H1R6WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R6BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R6CA01#** |
| | | | 1.7pF | ±0.05pF | **GRM0334C1H1R7WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R7BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R7CA01#** |
| | | | 1.8pF | ±0.05pF | **GRM0334C1H1R8WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R8BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R8CA01#** |
| | | | 1.9pF | ±0.05pF | **GRM0334C1H1R9WA01#** |
| | | | | ±0.1pF | **GRM0334C1H1R9BA01#** |
| | | | | ±0.25pF | **GRM0334C1H1R9CA01#** |
| | | | 2.0pF | ±0.05pF | **GRM0334C1H2R0WA01#** |
| | | | | ±0.1pF | **GRM0334C1H2R0BA01#** |
| | | | | ±0.25pF | **GRM0334C1H2R0CA01#** |
| | | CJ | 2.1pF | ±0.05pF | **GRM0333C1H2R1WA01#** |
| | | | | ±0.1pF | **GRM0333C1H2R1BA01#** |
| | | | | ±0.25pF | **GRM0333C1H2R1CA01#** |
| | | | 2.2pF | ±0.05pF | **GRM0333C1H2R2WA01#** |
| | | | | ±0.1pF | **GRM0333C1H2R2BA01#** |
| | | | | ±0.25pF | **GRM0333C1H2R2CA01#** |
| | | | 2.3pF | ±0.05pF | **GRM0333C1H2R3WA01#** |
| | | | | ±0.1pF | **GRM0333C1H2R3BA01#** |
| | | | | ±0.25pF | **GRM0333C1H2R3CA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | CJ | 2.4pF | ±0.05pF | GRM0333C1H2R4WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R4BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R4CA01# | |
| | | | 2.5pF | ±0.05pF | GRM0333C1H2R5WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R5BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R5CA01# | |
| | | | 2.6pF | ±0.05pF | GRM0333C1H2R6WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R6BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R6CA01# | |
| | | | 2.7pF | ±0.05pF | GRM0333C1H2R7WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R7BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R7CA01# | |
| | | | 2.8pF | ±0.05pF | GRM0333C1H2R8WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R8BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R8CA01# | |
| | | | 2.9pF | ±0.05pF | GRM0333C1H2R9WA01# | |
| | | | | ±0.1pF | GRM0333C1H2R9BA01# | |
| | | | | ±0.25pF | GRM0333C1H2R9CA01# | |
| | | | 3.0pF | ±0.05pF | GRM0333C1H3R0WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R0BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R0CA01# | |
| | | | 3.1pF | ±0.05pF | GRM0333C1H3R1WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R1BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R1CA01# | |
| | | | 3.2pF | ±0.05pF | GRM0333C1H3R2WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R2BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R2CA01# | |
| | | | 3.3pF | ±0.05pF | GRM0333C1H3R3WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R3BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R3CA01# | |
| | | | 3.4pF | ±0.05pF | GRM0333C1H3R4WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R4BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R4CA01# | |
| | | | 3.5pF | ±0.05pF | GRM0333C1H3R5WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R5BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM0333C1H3R6WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R6BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM0333C1H3R7WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R7BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R7CA01# | |
| | | | 3.8pF | ±0.05pF | GRM0333C1H3R8WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R8BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R8CA01# | |
| | | | 3.9pF | ±0.05pF | GRM0333C1H3R9WA01# | |
| | | | | ±0.1pF | GRM0333C1H3R9BA01# | |
| | | | | ±0.25pF | GRM0333C1H3R9CA01# | |
| | | CH | 4.0pF | ±0.05pF | GRM0332C1H4R0WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R0BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R0CA01# | |
| | | | 4.1pF | ±0.05pF | GRM0332C1H4R1WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R1BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R1CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | CH | 4.2pF | ±0.05pF | GRM0332C1H4R2WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R2BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R2CA01# | |
| | | | 4.3pF | ±0.05pF | GRM0332C1H4R3WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R3BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM0332C1H4R4WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R4BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM0332C1H4R5WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R5BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM0332C1H4R6WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R6BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM0332C1H4R7WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R7BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM0332C1H4R8WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R8BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM0332C1H4R9WA01# | |
| | | | | ±0.1pF | GRM0332C1H4R9BA01# | |
| | | | | ±0.25pF | GRM0332C1H4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM0332C1H5R0WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R0BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM0332C1H5R1WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R1BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R1CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM0332C1H5R2WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R2BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R2CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM0332C1H5R3WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R3BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R3CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM0332C1H5R4WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R4BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R4CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM0332C1H5R5WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R5BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R5CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM0332C1H5R6WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R6BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R6CA01# | |
| | | | | ±0.5pF | GRM0332C1H5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM0332C1H5R7WA01# | |
| | | | | ±0.1pF | GRM0332C1H5R7BA01# | |
| | | | | ±0.25pF | GRM0332C1H5R7CA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | CH | 5.7pF | ±0.5pF | **GRM0332C1H5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM0332C1H5R8WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H5R8BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H5R8CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM0332C1H5R9WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H5R9BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H5R9CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H5R9DA01#** | |
| | | | 6.0pF | ±0.05pF | **GRM0332C1H6R0WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R0BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R0CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM0332C1H6R1WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R1BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R1CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM0332C1H6R2WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R2BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R2CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM0332C1H6R3WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R3BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R3CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM0332C1H6R4WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R4BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R4CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM0332C1H6R5WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R5BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R5CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM0332C1H6R6WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R6BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R6CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM0332C1H6R7WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R7BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R7CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM0332C1H6R8WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R8BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R8CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM0332C1H6R9WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H6R9BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H6R9CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM0332C1H7R0WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R0BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R0CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM0332C1H7R1WA01#** | |
| 0.33mm | 50Vdc | CH | 7.1pF | ±0.1pF | **GRM0332C1H7R1BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R1CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM0332C1H7R2WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R2BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R2CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM0332C1H7R3WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R3BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R3CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM0332C1H7R4WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R4BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R4CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM0332C1H7R5WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R5BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R5CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM0332C1H7R6WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R6BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R6CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM0332C1H7R7WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R7BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R7CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM0332C1H7R8WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R8BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R8CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM0332C1H7R9WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H7R9BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H7R9CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM0332C1H8R0WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R0BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R0CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM0332C1H8R1WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R1BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R1CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM0332C1H8R2WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R2BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R2CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM0332C1H8R3WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R3BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R3CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM0332C1H8R4WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R4BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R4CA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | CH | 8.4pF | ±0.5pF | **GRM0332C1H8R4DA01#** | |
| | | | 8.5pF | ±0.05pF | **GRM0332C1H8R5WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R5BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R5CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R5DA01#** | |
| | | | 8.6pF | ±0.05pF | **GRM0332C1H8R6WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R6BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R6CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R6DA01#** | |
| | | | 8.7pF | ±0.05pF | **GRM0332C1H8R7WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R7BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R7CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R7DA01#** | |
| | | | 8.8pF | ±0.05pF | **GRM0332C1H8R8WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R8BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R8CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R8DA01#** | |
| | | | 8.9pF | ±0.05pF | **GRM0332C1H8R9WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H8R9BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H8R9CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H8R9DA01#** | |
| | | | 9.0pF | ±0.05pF | **GRM0332C1H9R0WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R0BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R0CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R0DA01#** | |
| | | | 9.1pF | ±0.05pF | **GRM0332C1H9R1WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R1BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R1CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R1DA01#** | |
| | | | 9.2pF | ±0.05pF | **GRM0332C1H9R2WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R2BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R2CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R2DA01#** | |
| | | | 9.3pF | ±0.05pF | **GRM0332C1H9R3WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R3BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R3CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R3DA01#** | |
| | | | 9.4pF | ±0.05pF | **GRM0332C1H9R4WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R4BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R4CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R4DA01#** | |
| | | | 9.5pF | ±0.05pF | **GRM0332C1H9R5WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R5BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R5CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R5DA01#** | |
| | | | 9.6pF | ±0.05pF | **GRM0332C1H9R6WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R6BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R6CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R6DA01#** | |
| | | | 9.7pF | ±0.05pF | **GRM0332C1H9R7WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R7BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R7CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R7DA01#** | |
| | | | 9.8pF | ±0.05pF | **GRM0332C1H9R8WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R8BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R8CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R8DA01#** | |
| | | | 9.9pF | ±0.05pF | **GRM0332C1H9R9WA01#** | |
| | | | | ±0.1pF | **GRM0332C1H9R9BA01#** | |
| | | | | ±0.25pF | **GRM0332C1H9R9CA01#** | |
| | | | | ±0.5pF | **GRM0332C1H9R9DA01#** | |
| | | | 10pF | ±2% | **GRM0332C1H100GA01#** | |
| | | | | ±5% | **GRM0332C1H100JA01#** | |
| | | | 12pF | ±2% | **GRM0332C1H120GA01#** | |
| | | | | ±5% | **GRM0332C1H120JA01#** | |
| | | | 15pF | ±2% | **GRM0332C1H150GA01#** | |
| | | | | ±5% | **GRM0332C1H150JA01#** | |
| | | | 18pF | ±2% | **GRM0332C1H180GA01#** | |
| | | | | ±5% | **GRM0332C1H180JA01#** | |
| | | | 22pF | ±2% | **GRM0332C1H220GA01#** | |
| | | | | ±5% | **GRM0332C1H220JA01#** | |
| | | | 27pF | ±2% | **GRM0332C1H270GA01#** | |
| | | | | ±5% | **GRM0332C1H270JA01#** | |
| | | | 33pF | ±2% | **GRM0332C1H330GA01#** | |
| | | | | ±5% | **GRM0332C1H330JA01#** | |
| | | | 39pF | ±2% | **GRM0332C1H390GA01#** | |
| | | | | ±5% | **GRM0332C1H390JA01#** | |
| | | | 47pF | ±2% | **GRM0332C1H470GA01#** | |
| | | | | ±5% | **GRM0332C1H470JA01#** | |
| | | | 56pF | ±2% | **GRM0332C1H560GA01#** | |
| | | | | ±5% | **GRM0332C1H560JA01#** | |
| | | | 68pF | ±2% | **GRM0332C1H680GA01#** | |
| | | | | ±5% | **GRM0332C1H680JA01#** | |
| | | | 82pF | ±2% | **GRM0332C1H820GA01#** | |
| | | | | ±5% | **GRM0332C1H820JA01#** | |
| | | | 100pF | ±2% | **GRM0332C1H101GA01#** | |
| | | | | ±5% | **GRM0332C1H101JA01#** | |
| | | | 120pF | ±2% | **GRM0332C1H121GA01#** | |
| | | | | ±5% | **GRM0332C1H121JA01#** | |

## ■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 0.10pF | ±0.05pF | **GRM1555C2AR10WA01#** | |
| | | | 0.20pF | ±0.05pF | **GRM1555C2AR20WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR20BA01#** | |
| | | | 0.30pF | ±0.05pF | **GRM1555C2AR30WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR30BA01#** | |
| | | | 0.40pF | ±0.05pF | **GRM1555C2AR40WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR40BA01#** | |
| | | | 0.50pF | ±0.05pF | **GRM1555C2AR50WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR50BA01#** | |
| | | | 0.60pF | ±0.05pF | **GRM1555C2AR60WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR60BA01#** | |
| | | | 0.70pF | ±0.05pF | **GRM1555C2AR70WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR70BA01#** | |
| | | | 0.80pF | ±0.05pF | **GRM1555C2AR80WA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 0.80pF | ±0.1pF | **GRM1555C2AR80BA01#** | |
| | | | 0.90pF | ±0.05pF | **GRM1555C2AR90WA01#** | |
| | | | | ±0.1pF | **GRM1555C2AR90BA01#** | |
| | | | 1.0pF | ±0.05pF | **GRM1555C2A1R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R0CA01#** | |
| | | | 1.1pF | ±0.05pF | **GRM1555C2A1R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R1CA01#** | |
| | | | 1.2pF | ±0.05pF | **GRM1555C2A1R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R2CA01#** | |
| | | | 1.3pF | ±0.05pF | **GRM1555C2A1R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R3CA01#** | |
| | | | 1.4pF | ±0.05pF | **GRM1555C2A1R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R4CA01#** | |
| | | | 1.5pF | ±0.05pF | **GRM1555C2A1R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R5CA01#** | |
| | | | 1.6pF | ±0.05pF | **GRM1555C2A1R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R6CA01#** | |
| | | | 1.7pF | ±0.05pF | **GRM1555C2A1R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R7CA01#** | |
| | | | 1.8pF | ±0.05pF | **GRM1555C2A1R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R8CA01#** | |
| | | | 1.9pF | ±0.05pF | **GRM1555C2A1R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A1R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A1R9CA01#** | |
| | | | 2.0pF | ±0.05pF | **GRM1555C2A2R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R0CA01#** | |
| | | | 2.1pF | ±0.05pF | **GRM1555C2A2R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R1CA01#** | |
| | | | 2.2pF | ±0.05pF | **GRM1555C2A2R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R2CA01#** | |
| | | | 2.3pF | ±0.05pF | **GRM1555C2A2R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R3CA01#** | |
| | | | 2.4pF | ±0.05pF | **GRM1555C2A2R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R4CA01#** | |
| | | | 2.5pF | ±0.05pF | **GRM1555C2A2R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R5CA01#** | |
| | | | 2.6pF | ±0.05pF | **GRM1555C2A2R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R6CA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 2.7pF | ±0.05pF | **GRM1555C2A2R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R7CA01#** | |
| | | | 2.8pF | ±0.05pF | **GRM1555C2A2R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R8CA01#** | |
| | | | 2.9pF | ±0.05pF | **GRM1555C2A2R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A2R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A2R9CA01#** | |
| | | | 3.0pF | ±0.05pF | **GRM1555C2A3R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R0CA01#** | |
| | | | 3.1pF | ±0.05pF | **GRM1555C2A3R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R1CA01#** | |
| | | | 3.2pF | ±0.05pF | **GRM1555C2A3R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R2CA01#** | |
| | | | 3.3pF | ±0.05pF | **GRM1555C2A3R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R3CA01#** | |
| | | | 3.4pF | ±0.05pF | **GRM1555C2A3R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R4CA01#** | |
| | | | 3.5pF | ±0.05pF | **GRM1555C2A3R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R5CA01#** | |
| | | | 3.6pF | ±0.05pF | **GRM1555C2A3R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R6CA01#** | |
| | | | 3.7pF | ±0.05pF | **GRM1555C2A3R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R7CA01#** | |
| | | | 3.8pF | ±0.05pF | **GRM1555C2A3R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R8CA01#** | |
| | | | 3.9pF | ±0.05pF | **GRM1555C2A3R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A3R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A3R9CA01#** | |
| | | | 4.0pF | ±0.05pF | **GRM1555C2A4R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R0CA01#** | |
| | | | 4.1pF | ±0.05pF | **GRM1555C2A4R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R1CA01#** | |
| | | | 4.2pF | ±0.05pF | **GRM1555C2A4R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R2CA01#** | |
| | | | 4.3pF | ±0.05pF | **GRM1555C2A4R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R3CA01#** | |
| | | | 4.4pF | ±0.05pF | **GRM1555C2A4R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R4CA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 4.5pF | ±0.05pF | **GRM1555C2A4R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R5CA01#** | |
| | | | 4.6pF | ±0.05pF | **GRM1555C2A4R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R6CA01#** | |
| | | | 4.7pF | ±0.05pF | **GRM1555C2A4R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R7CA01#** | |
| | | | 4.8pF | ±0.05pF | **GRM1555C2A4R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R8CA01#** | |
| | | | 4.9pF | ±0.05pF | **GRM1555C2A4R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A4R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A4R9CA01#** | |
| | | | 5.0pF | ±0.05pF | **GRM1555C2A5R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R0CA01#** | |
| | | | 5.1pF | ±0.05pF | **GRM1555C2A5R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R1DA01#** | |
| | | | 5.2pF | ±0.05pF | **GRM1555C2A5R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R2DA01#** | |
| | | | 5.3pF | ±0.05pF | **GRM1555C2A5R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R3DA01#** | |
| | | | 5.4pF | ±0.05pF | **GRM1555C2A5R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R4DA01#** | |
| | | | 5.5pF | ±0.05pF | **GRM1555C2A5R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R5DA01#** | |
| | | | 5.6pF | ±0.05pF | **GRM1555C2A5R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R6DA01#** | |
| | | | 5.7pF | ±0.05pF | **GRM1555C2A5R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM1555C2A5R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM1555C2A5R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A5R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A5R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A5R9DA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 6.0pF | ±0.05pF | **GRM1555C2A6R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM1555C2A6R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM1555C2A6R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM1555C2A6R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM1555C2A6R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM1555C2A6R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM1555C2A6R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM1555C2A6R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM1555C2A6R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM1555C2A6R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A6R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A6R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM1555C2A7R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM1555C2A7R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM1555C2A7R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM1555C2A7R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R3BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 7.3pF | ±0.25pF | **GRM1555C2A7R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM1555C2A7R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM1555C2A7R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM1555C2A7R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM1555C2A7R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM1555C2A7R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM1555C2A7R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A7R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A7R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM1555C2A8R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM1555C2A8R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM1555C2A8R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM1555C2A8R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM1555C2A8R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R4DA01#** | |
| | | | 8.5pF | ±0.05pF | **GRM1555C2A8R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R5DA01#** | |
| | | | 8.6pF | ±0.05pF | **GRM1555C2A8R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R6DA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 8.7pF | ±0.05pF | **GRM1555C2A8R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R7DA01#** | |
| | | | 8.8pF | ±0.05pF | **GRM1555C2A8R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R8DA01#** | |
| | | | 8.9pF | ±0.05pF | **GRM1555C2A8R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A8R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A8R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A8R9DA01#** | |
| | | | 9.0pF | ±0.05pF | **GRM1555C2A9R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R0DA01#** | |
| | | | 9.1pF | ±0.05pF | **GRM1555C2A9R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R1DA01#** | |
| | | | 9.2pF | ±0.05pF | **GRM1555C2A9R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R2DA01#** | |
| | | | 9.3pF | ±0.05pF | **GRM1555C2A9R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R3DA01#** | |
| | | | 9.4pF | ±0.05pF | **GRM1555C2A9R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R4DA01#** | |
| | | | 9.5pF | ±0.05pF | **GRM1555C2A9R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R5DA01#** | |
| | | | 9.6pF | ±0.05pF | **GRM1555C2A9R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R6DA01#** | |
| | | | 9.7pF | ±0.05pF | **GRM1555C2A9R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R7DA01#** | |
| | | | 9.8pF | ±0.05pF | **GRM1555C2A9R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R8DA01#** | |
| | | | 9.9pF | ±0.05pF | **GRM1555C2A9R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C2A9R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C2A9R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C2A9R9DA01#** | |
| | | | 10pF | ±2% | **GRM1555C2A100GA01#** | |
| | | | | ±5% | **GRM1555C2A100JA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | C0G | 12pF | ±2% | **GRM1555C2A120GA01#** | |
| | | | | ±5% | **GRM1555C2A120JA01#** | |
| | | | 15pF | ±2% | **GRM1555C2A150GA01#** | |
| | | | | ±5% | **GRM1555C2A150JA01#** | |
| | | | 18pF | ±2% | **GRM1555C2A180GA01#** | |
| | | | | ±5% | **GRM1555C2A180JA01#** | |
| | | | 22pF | ±2% | **GRM1555C2A220GA01#** | |
| | | | | ±5% | **GRM1555C2A220JA01#** | |
| | | | 27pF | ±2% | **GRM1555C2A270GA01#** | |
| | | | | ±5% | **GRM1555C2A270JA01#** | |
| | | | 33pF | ±2% | **GRM1555C2A330GA01#** | |
| | | | | ±5% | **GRM1555C2A330JA01#** | |
| | | | 39pF | ±2% | **GRM1555C2A390GA01#** | |
| | | | | ±5% | **GRM1555C2A390JA01#** | |
| | | | 47pF | ±2% | **GRM1555C2A470GA01#** | |
| | | | | ±5% | **GRM1555C2A470JA01#** | |
| | | | 56pF | ±2% | **GRM1555C2A560GA01#** | |
| | | | | ±5% | **GRM1555C2A560JA01#** | |
| | | | 68pF | ±2% | **GRM1555C2A680GA01#** | |
| | | | | ±5% | **GRM1555C2A680JA01#** | |
| | | | 82pF | ±2% | **GRM1555C2A820GA01#** | |
| | | | | ±5% | **GRM1555C2A820JA01#** | |
| | | | 100pF | ±2% | **GRM1555C2A101GA01#** | |
| | | | | ±5% | **GRM1555C2A101JA01#** | |
| | | CK | 0.10pF | ±0.05pF | **GRM1554C2AR10WA01#** | |
| | | | 0.20pF | ±0.05pF | **GRM1554C2AR20WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR20BA01#** | |
| | | | 0.30pF | ±0.05pF | **GRM1554C2AR30WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR30BA01#** | |
| | | | 0.40pF | ±0.05pF | **GRM1554C2AR40WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR40BA01#** | |
| | | | 0.50pF | ±0.05pF | **GRM1554C2AR50WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR50BA01#** | |
| | | | 0.60pF | ±0.05pF | **GRM1554C2AR60WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR60BA01#** | |
| | | | 0.70pF | ±0.05pF | **GRM1554C2AR70WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR70BA01#** | |
| | | | 0.80pF | ±0.05pF | **GRM1554C2AR80WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR80BA01#** | |
| | | | 0.90pF | ±0.05pF | **GRM1554C2AR90WA01#** | |
| | | | | ±0.1pF | **GRM1554C2AR90BA01#** | |
| | | | 1.0pF | ±0.05pF | **GRM1554C2A1R0WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R0BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R0CA01#** | |
| | | | 1.1pF | ±0.05pF | **GRM1554C2A1R1WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R1BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R1CA01#** | |
| | | | 1.2pF | ±0.05pF | **GRM1554C2A1R2WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R2BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R2CA01#** | |
| | | | 1.3pF | ±0.05pF | **GRM1554C2A1R3WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R3BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R3CA01#** | |
| | | | 1.4pF | ±0.05pF | **GRM1554C2A1R4WA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | CK | 1.4pF | ±0.1pF | **GRM1554C2A1R4BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R4CA01#** | |
| | | | 1.5pF | ±0.05pF | **GRM1554C2A1R5WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R5BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R5CA01#** | |
| | | | 1.6pF | ±0.05pF | **GRM1554C2A1R6WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R6BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R6CA01#** | |
| | | | 1.7pF | ±0.05pF | **GRM1554C2A1R7WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R7BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R7CA01#** | |
| | | | 1.8pF | ±0.05pF | **GRM1554C2A1R8WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R8BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R8CA01#** | |
| | | | 1.9pF | ±0.05pF | **GRM1554C2A1R9WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A1R9BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A1R9CA01#** | |
| | | | 2.0pF | ±0.05pF | **GRM1554C2A2R0WA01#** | |
| | | | | ±0.1pF | **GRM1554C2A2R0BA01#** | |
| | | | | ±0.25pF | **GRM1554C2A2R0CA01#** | |
| | | CJ | 2.1pF | ±0.05pF | **GRM1553C2A2R1WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R1BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R1CA01#** | |
| | | | 2.2pF | ±0.05pF | **GRM1553C2A2R2WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R2BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R2CA01#** | |
| | | | 2.3pF | ±0.05pF | **GRM1553C2A2R3WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R3BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R3CA01#** | |
| | | | 2.4pF | ±0.05pF | **GRM1553C2A2R4WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R4BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R4CA01#** | |
| | | | 2.5pF | ±0.05pF | **GRM1553C2A2R5WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R5BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R5CA01#** | |
| | | | 2.6pF | ±0.05pF | **GRM1553C2A2R6WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R6BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R6CA01#** | |
| | | | 2.7pF | ±0.05pF | **GRM1553C2A2R7WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R7BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R7CA01#** | |
| | | | 2.8pF | ±0.05pF | **GRM1553C2A2R8WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R8BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R8CA01#** | |
| | | | 2.9pF | ±0.05pF | **GRM1553C2A2R9WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A2R9BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A2R9CA01#** | |
| | | | 3.0pF | ±0.05pF | **GRM1553C2A3R0WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A3R0BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A3R0CA01#** | |
| | | | 3.1pF | ±0.05pF | **GRM1553C2A3R1WA01#** | |
| | | | | ±0.1pF | **GRM1553C2A3R1BA01#** | |
| | | | | ±0.25pF | **GRM1553C2A3R1CA01#** | |
| | | | 3.2pF | ±0.05pF | **GRM1553C2A3R2WA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 100Vdc | CJ | 3.2pF | ±0.1pF | **GRM1553C2A3R2BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R2CA01#** |
| | | | 3.3pF | ±0.05pF | **GRM1553C2A3R3WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R3BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R3CA01#** |
| | | | 3.4pF | ±0.05pF | **GRM1553C2A3R4WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R4BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R4CA01#** |
| | | | 3.5pF | ±0.05pF | **GRM1553C2A3R5WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R5BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R5CA01#** |
| | | | 3.6pF | ±0.05pF | **GRM1553C2A3R6WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R6BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R6CA01#** |
| | | | 3.7pF | ±0.05pF | **GRM1553C2A3R7WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R7BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R7CA01#** |
| | | | 3.8pF | ±0.05pF | **GRM1553C2A3R8WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R8BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R8CA01#** |
| | | | 3.9pF | ±0.05pF | **GRM1553C2A3R9WA01#** |
| | | | | ±0.1pF | **GRM1553C2A3R9BA01#** |
| | | | | ±0.25pF | **GRM1553C2A3R9CA01#** |
| | | CH | 4.0pF | ±0.05pF | **GRM1552C2A4R0WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R0CA01#** |
| | | | 4.1pF | ±0.05pF | **GRM1552C2A4R1WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R1BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R1CA01#** |
| | | | 4.2pF | ±0.05pF | **GRM1552C2A4R2WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R2BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R2CA01#** |
| | | | 4.3pF | ±0.05pF | **GRM1552C2A4R3WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R3BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R3CA01#** |
| | | | 4.4pF | ±0.05pF | **GRM1552C2A4R4WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R4BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R4CA01#** |
| | | | 4.5pF | ±0.05pF | **GRM1552C2A4R5WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R5BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R5CA01#** |
| | | | 4.6pF | ±0.05pF | **GRM1552C2A4R6WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R6BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R6CA01#** |
| | | | 4.7pF | ±0.05pF | **GRM1552C2A4R7WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R7BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R7CA01#** |
| | | | 4.8pF | ±0.05pF | **GRM1552C2A4R8WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R8BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R8CA01#** |
| | | | 4.9pF | ±0.05pF | **GRM1552C2A4R9WA01#** |
| | | | | ±0.1pF | **GRM1552C2A4R9BA01#** |
| | | | | ±0.25pF | **GRM1552C2A4R9CA01#** |
| | | | 5.0pF | ±0.05pF | **GRM1552C2A5R0WA01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 100Vdc | CH | 5.0pF | ±0.1pF | **GRM1552C2A5R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R0CA01#** |
| | | | 5.1pF | ±0.05pF | **GRM1552C2A5R1WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R1BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R1CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R1DA01#** |
| | | | 5.2pF | ±0.05pF | **GRM1552C2A5R2WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R2BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R2CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R2DA01#** |
| | | | 5.3pF | ±0.05pF | **GRM1552C2A5R3WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R3BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R3CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R3DA01#** |
| | | | 5.4pF | ±0.05pF | **GRM1552C2A5R4WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R4BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R4CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R4DA01#** |
| | | | 5.5pF | ±0.05pF | **GRM1552C2A5R5WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R5BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R5CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R5DA01#** |
| | | | 5.6pF | ±0.05pF | **GRM1552C2A5R6WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R6BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R6CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R6DA01#** |
| | | | 5.7pF | ±0.05pF | **GRM1552C2A5R7WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R7BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R7CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R7DA01#** |
| | | | 5.8pF | ±0.05pF | **GRM1552C2A5R8WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R8BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R8CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R8DA01#** |
| | | | 5.9pF | ±0.05pF | **GRM1552C2A5R9WA01#** |
| | | | | ±0.1pF | **GRM1552C2A5R9BA01#** |
| | | | | ±0.25pF | **GRM1552C2A5R9CA01#** |
| | | | | ±0.5pF | **GRM1552C2A5R9DA01#** |
| | | | 6.0pF | ±0.05pF | **GRM1552C2A6R0WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R0CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R0DA01#** |
| | | | 6.1pF | ±0.05pF | **GRM1552C2A6R1WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R1BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R1CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R1DA01#** |
| | | | 6.2pF | ±0.05pF | **GRM1552C2A6R2WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R2BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R2CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R2DA01#** |
| | | | 6.3pF | ±0.05pF | **GRM1552C2A6R3WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R3BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R3CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R3DA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 100Vdc | CH | 6.4pF | ±0.05pF | **GRM1552C2A6R4WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R4BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R4CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R4DA01#** |
| | | | 6.5pF | ±0.05pF | **GRM1552C2A6R5WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R5BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R5CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R5DA01#** |
| | | | 6.6pF | ±0.05pF | **GRM1552C2A6R6WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R6BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R6CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R6DA01#** |
| | | | 6.7pF | ±0.05pF | **GRM1552C2A6R7WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R7BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R7CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R7DA01#** |
| | | | 6.8pF | ±0.05pF | **GRM1552C2A6R8WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R8BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R8CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R8DA01#** |
| | | | 6.9pF | ±0.05pF | **GRM1552C2A6R9WA01#** |
| | | | | ±0.1pF | **GRM1552C2A6R9BA01#** |
| | | | | ±0.25pF | **GRM1552C2A6R9CA01#** |
| | | | | ±0.5pF | **GRM1552C2A6R9DA01#** |
| | | | 7.0pF | ±0.05pF | **GRM1552C2A7R0WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R0CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R0DA01#** |
| | | | 7.1pF | ±0.05pF | **GRM1552C2A7R1WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R1BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R1CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R1DA01#** |
| | | | 7.2pF | ±0.05pF | **GRM1552C2A7R2WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R2BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R2CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R2DA01#** |
| | | | 7.3pF | ±0.05pF | **GRM1552C2A7R3WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R3BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R3CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R3DA01#** |
| | | | 7.4pF | ±0.05pF | **GRM1552C2A7R4WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R4BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R4CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R4DA01#** |
| | | | 7.5pF | ±0.05pF | **GRM1552C2A7R5WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R5BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R5CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R5DA01#** |
| | | | 7.6pF | ±0.05pF | **GRM1552C2A7R6WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R6BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R6CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R6DA01#** |
| | | | 7.7pF | ±0.05pF | **GRM1552C2A7R7WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R7BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R7CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R7DA01#** |
| | | | 7.8pF | ±0.05pF | **GRM1552C2A7R8WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R8BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R8CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R8DA01#** |
| | | | 7.9pF | ±0.05pF | **GRM1552C2A7R9WA01#** |
| | | | | ±0.1pF | **GRM1552C2A7R9BA01#** |
| | | | | ±0.25pF | **GRM1552C2A7R9CA01#** |
| | | | | ±0.5pF | **GRM1552C2A7R9DA01#** |
| | | | 8.0pF | ±0.05pF | **GRM1552C2A8R0WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R0CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R0DA01#** |
| | | | 8.1pF | ±0.05pF | **GRM1552C2A8R1WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R1BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R1CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R1DA01#** |
| | | | 8.2pF | ±0.05pF | **GRM1552C2A8R2WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R2BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R2CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R2DA01#** |
| | | | 8.3pF | ±0.05pF | **GRM1552C2A8R3WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R3BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R3CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R3DA01#** |
| | | | 8.4pF | ±0.05pF | **GRM1552C2A8R4WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R4BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R4CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R4DA01#** |
| | | | 8.5pF | ±0.05pF | **GRM1552C2A8R5WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R5BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R5CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R5DA01#** |
| | | | 8.6pF | ±0.05pF | **GRM1552C2A8R6WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R6BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R6CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R6DA01#** |
| | | | 8.7pF | ±0.05pF | **GRM1552C2A8R7WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R7BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R7CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R7DA01#** |
| | | | 8.8pF | ±0.05pF | **GRM1552C2A8R8WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R8BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R8CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R8DA01#** |
| | | | 8.9pF | ±0.05pF | **GRM1552C2A8R9WA01#** |
| | | | | ±0.1pF | **GRM1552C2A8R9BA01#** |
| | | | | ±0.25pF | **GRM1552C2A8R9CA01#** |
| | | | | ±0.5pF | **GRM1552C2A8R9DA01#** |
| | | | 9.0pF | ±0.05pF | **GRM1552C2A9R0WA01#** |
| | | | | ±0.1pF | **GRM1552C2A9R0BA01#** |
| | | | | ±0.25pF | **GRM1552C2A9R0CA01#** |
| | | | | ±0.5pF | **GRM1552C2A9R0DA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 100Vdc | CH | 9.1pF | ±0.05pF | GRM1552C2A9R1WA01# |
| | | | | ±0.1pF | GRM1552C2A9R1BA01# |
| | | | | ±0.25pF | GRM1552C2A9R1CA01# |
| | | | | ±0.5pF | GRM1552C2A9R1DA01# |
| | | | 9.2pF | ±0.05pF | GRM1552C2A9R2WA01# |
| | | | | ±0.1pF | GRM1552C2A9R2BA01# |
| | | | | ±0.25pF | GRM1552C2A9R2CA01# |
| | | | | ±0.5pF | GRM1552C2A9R2DA01# |
| | | | 9.3pF | ±0.05pF | GRM1552C2A9R3WA01# |
| | | | | ±0.1pF | GRM1552C2A9R3BA01# |
| | | | | ±0.25pF | GRM1552C2A9R3CA01# |
| | | | | ±0.5pF | GRM1552C2A9R3DA01# |
| | | | 9.4pF | ±0.05pF | GRM1552C2A9R4WA01# |
| | | | | ±0.1pF | GRM1552C2A9R4BA01# |
| | | | | ±0.25pF | GRM1552C2A9R4CA01# |
| | | | | ±0.5pF | GRM1552C2A9R4DA01# |
| | | | 9.5pF | ±0.05pF | GRM1552C2A9R5WA01# |
| | | | | ±0.1pF | GRM1552C2A9R5BA01# |
| | | | | ±0.25pF | GRM1552C2A9R5CA01# |
| | | | | ±0.5pF | GRM1552C2A9R5DA01# |
| | | | 9.6pF | ±0.05pF | GRM1552C2A9R6WA01# |
| | | | | ±0.1pF | GRM1552C2A9R6BA01# |
| | | | | ±0.25pF | GRM1552C2A9R6CA01# |
| | | | | ±0.5pF | GRM1552C2A9R6DA01# |
| | | | 9.7pF | ±0.05pF | GRM1552C2A9R7WA01# |
| | | | | ±0.1pF | GRM1552C2A9R7BA01# |
| | | | | ±0.25pF | GRM1552C2A9R7CA01# |
| | | | | ±0.5pF | GRM1552C2A9R7DA01# |
| | | | 9.8pF | ±0.05pF | GRM1552C2A9R8WA01# |
| | | | | ±0.1pF | GRM1552C2A9R8BA01# |
| | | | | ±0.25pF | GRM1552C2A9R8CA01# |
| | | | | ±0.5pF | GRM1552C2A9R8DA01# |
| | | | 9.9pF | ±0.05pF | GRM1552C2A9R9WA01# |
| | | | | ±0.1pF | GRM1552C2A9R9BA01# |
| | | | | ±0.25pF | GRM1552C2A9R9CA01# |
| | | | | ±0.5pF | GRM1552C2A9R9DA01# |
| | | | 10pF | ±2% | GRM1552C2A100GA01# |
| | | | | ±5% | GRM1552C2A100JA01# |
| | | | 12pF | ±2% | GRM1552C2A120GA01# |
| | | | | ±5% | GRM1552C2A120JA01# |
| | | | 15pF | ±2% | GRM1552C2A150GA01# |
| | | | | ±5% | GRM1552C2A150JA01# |
| | | | 18pF | ±2% | GRM1552C2A180GA01# |
| | | | | ±5% | GRM1552C2A180JA01# |
| | | | 22pF | ±2% | GRM1552C2A220GA01# |
| | | | | ±5% | GRM1552C2A220JA01# |
| | | | 27pF | ±2% | GRM1552C2A270GA01# |
| | | | | ±5% | GRM1552C2A270JA01# |
| | | | 33pF | ±2% | GRM1552C2A330GA01# |
| | | | | ±5% | GRM1552C2A330JA01# |
| | | | 39pF | ±2% | GRM1552C2A390GA01# |
| | | | | ±5% | GRM1552C2A390JA01# |
| | | | 47pF | ±2% | GRM1552C2A470GA01# |
| | | | | ±5% | GRM1552C2A470JA01# |
| 0.55mm | 100Vdc | CH | 56pF | ±2% | GRM1552C2A560GA01# |
| | | | | ±5% | GRM1552C2A560JA01# |
| | | | 68pF | ±2% | GRM1552C2A680GA01# |
| | | | | ±5% | GRM1552C2A680JA01# |
| | | | 82pF | ±2% | GRM1552C2A820GA01# |
| | | | | ±5% | GRM1552C2A820JA01# |
| | | | 100pF | ±2% | GRM1552C2A101GA01# |
| | | | | ±5% | GRM1552C2A101JA01# |
| | 50Vdc | C0G | 0.10pF | ±0.05pF | GRM1555C1HR10WA01# |
| | | | 0.20pF | ±0.05pF | GRM1555C1HR20WA01# |
| | | | | ±0.1pF | GRM1555C1HR20BA01# |
| | | | 0.30pF | ±0.05pF | GRM1555C1HR30WA01# |
| | | | | ±0.1pF | GRM1555C1HR30BA01# |
| | | | 0.40pF | ±0.05pF | GRM1555C1HR40WA01# |
| | | | | ±0.1pF | GRM1555C1HR40BA01# |
| | | | 0.50pF | ±0.05pF | GRM1555C1HR50WA01# |
| | | | | ±0.1pF | GRM1555C1HR50BA01# |
| | | | 0.60pF | ±0.05pF | GRM1555C1HR60WA01# |
| | | | | ±0.1pF | GRM1555C1HR60BA01# |
| | | | 0.70pF | ±0.05pF | GRM1555C1HR70WA01# |
| | | | | ±0.1pF | GRM1555C1HR70BA01# |
| | | | 0.80pF | ±0.05pF | GRM1555C1HR80WA01# |
| | | | | ±0.1pF | GRM1555C1HR80BA01# |
| | | | 0.90pF | ±0.05pF | GRM1555C1HR90WA01# |
| | | | | ±0.1pF | GRM1555C1HR90BA01# |
| | | | 1.0pF | ±0.05pF | GRM1555C1H1R0WA01# |
| | | | | ±0.1pF | GRM1555C1H1R0BA01# |
| | | | | ±0.25pF | GRM1555C1H1R0CA01# |
| | | | 1.1pF | ±0.05pF | GRM1555C1H1R1WA01# |
| | | | | ±0.1pF | GRM1555C1H1R1BA01# |
| | | | | ±0.25pF | GRM1555C1H1R1CA01# |
| | | | 1.2pF | ±0.05pF | GRM1555C1H1R2WA01# |
| | | | | ±0.1pF | GRM1555C1H1R2BA01# |
| | | | | ±0.25pF | GRM1555C1H1R2CA01# |
| | | | 1.3pF | ±0.05pF | GRM1555C1H1R3WA01# |
| | | | | ±0.1pF | GRM1555C1H1R3BA01# |
| | | | | ±0.25pF | GRM1555C1H1R3CA01# |
| | | | 1.4pF | ±0.05pF | GRM1555C1H1R4WA01# |
| | | | | ±0.1pF | GRM1555C1H1R4BA01# |
| | | | | ±0.25pF | GRM1555C1H1R4CA01# |
| | | | 1.5pF | ±0.05pF | GRM1555C1H1R5WA01# |
| | | | | ±0.1pF | GRM1555C1H1R5BA01# |
| | | | | ±0.25pF | GRM1555C1H1R5CA01# |
| | | | 1.6pF | ±0.05pF | GRM1555C1H1R6WA01# |
| | | | | ±0.1pF | GRM1555C1H1R6BA01# |
| | | | | ±0.25pF | GRM1555C1H1R6CA01# |
| | | | 1.7pF | ±0.05pF | GRM1555C1H1R7WA01# |
| | | | | ±0.1pF | GRM1555C1H1R7BA01# |
| | | | | ±0.25pF | GRM1555C1H1R7CA01# |
| | | | 1.8pF | ±0.05pF | GRM1555C1H1R8WA01# |
| | | | | ±0.1pF | GRM1555C1H1R8BA01# |
| | | | | ±0.25pF | GRM1555C1H1R8CA01# |
| | | | 1.9pF | ±0.05pF | GRM1555C1H1R9WA01# |
| | | | | ±0.1pF | GRM1555C1H1R9BA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 1.9pF | ±0.25pF | **GRM1555C1H1R9CA01#** | |
| | | | 2.0pF | ±0.05pF | **GRM1555C1H2R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R0CA01#** | |
| | | | 2.1pF | ±0.05pF | **GRM1555C1H2R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R1CA01#** | |
| | | | 2.2pF | ±0.05pF | **GRM1555C1H2R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R2CA01#** | |
| | | | 2.3pF | ±0.05pF | **GRM1555C1H2R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R3CA01#** | |
| | | | 2.4pF | ±0.05pF | **GRM1555C1H2R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R4CA01#** | |
| | | | 2.5pF | ±0.05pF | **GRM1555C1H2R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R5CA01#** | |
| | | | 2.6pF | ±0.05pF | **GRM1555C1H2R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R6CA01#** | |
| | | | 2.7pF | ±0.05pF | **GRM1555C1H2R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R7CA01#** | |
| | | | 2.8pF | ±0.05pF | **GRM1555C1H2R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R8CA01#** | |
| | | | 2.9pF | ±0.05pF | **GRM1555C1H2R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H2R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H2R9CA01#** | |
| | | | 3.0pF | ±0.05pF | **GRM1555C1H3R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R0CA01#** | |
| | | | 3.1pF | ±0.05pF | **GRM1555C1H3R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R1CA01#** | |
| | | | 3.2pF | ±0.05pF | **GRM1555C1H3R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R2CA01#** | |
| | | | 3.3pF | ±0.05pF | **GRM1555C1H3R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R3CA01#** | |
| | | | 3.4pF | ±0.05pF | **GRM1555C1H3R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R4CA01#** | |
| | | | 3.5pF | ±0.05pF | **GRM1555C1H3R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R5CA01#** | |
| | | | 3.6pF | ±0.05pF | **GRM1555C1H3R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R6CA01#** | |
| | | | 3.7pF | ±0.05pF | **GRM1555C1H3R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R7BA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 3.7pF | ±0.25pF | **GRM1555C1H3R7CA01#** | |
| | | | 3.8pF | ±0.05pF | **GRM1555C1H3R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R8CA01#** | |
| | | | 3.9pF | ±0.05pF | **GRM1555C1H3R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H3R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H3R9CA01#** | |
| | | | 4.0pF | ±0.05pF | **GRM1555C1H4R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R0CA01#** | |
| | | | 4.1pF | ±0.05pF | **GRM1555C1H4R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R1CA01#** | |
| | | | 4.2pF | ±0.05pF | **GRM1555C1H4R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R2CA01#** | |
| | | | 4.3pF | ±0.05pF | **GRM1555C1H4R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R3CA01#** | |
| | | | 4.4pF | ±0.05pF | **GRM1555C1H4R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R4CA01#** | |
| | | | 4.5pF | ±0.05pF | **GRM1555C1H4R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R5CA01#** | |
| | | | 4.6pF | ±0.05pF | **GRM1555C1H4R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R6CA01#** | |
| | | | 4.7pF | ±0.05pF | **GRM1555C1H4R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R7CA01#** | |
| | | | 4.8pF | ±0.05pF | **GRM1555C1H4R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R8CA01#** | |
| | | | 4.9pF | ±0.05pF | **GRM1555C1H4R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H4R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H4R9CA01#** | |
| | | | 5.0pF | ±0.05pF | **GRM1555C1H5R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R0CA01#** | |
| | | | 5.1pF | ±0.05pF | **GRM1555C1H5R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R1DA01#** | |
| | | | 5.2pF | ±0.05pF | **GRM1555C1H5R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R2DA01#** | |
| | | | 5.3pF | ±0.05pF | **GRM1555C1H5R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R3DA01#** | |
| | | | 5.4pF | ±0.05pF | **GRM1555C1H5R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R4BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 5.4pF | ±0.25pF | **GRM1555C1H5R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R4DA01#** | |
| | | | 5.5pF | ±0.05pF | **GRM1555C1H5R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R5DA01#** | |
| | | | 5.6pF | ±0.05pF | **GRM1555C1H5R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R6DA01#** | |
| | | | 5.7pF | ±0.05pF | **GRM1555C1H5R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM1555C1H5R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM1555C1H5R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H5R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H5R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H5R9DA01#** | |
| | | | 6.0pF | ±0.05pF | **GRM1555C1H6R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM1555C1H6R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM1555C1H6R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM1555C1H6R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM1555C1H6R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM1555C1H6R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM1555C1H6R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM1555C1H6R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R7DA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 6.8pF | ±0.05pF | **GRM1555C1H6R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM1555C1H6R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H6R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H6R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM1555C1H7R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM1555C1H7R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R1BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R1CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM1555C1H7R2WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R2BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R2CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM1555C1H7R3WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R3BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R3CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM1555C1H7R4WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R4BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R4CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM1555C1H7R5WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R5BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R5CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM1555C1H7R6WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R6BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R6CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM1555C1H7R7WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R7BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R7CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM1555C1H7R8WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R8BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R8CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM1555C1H7R9WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H7R9BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H7R9CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM1555C1H8R0WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H8R0BA01#** | |
| | | | | ±0.25pF | **GRM1555C1H8R0CA01#** | |
| | | | | ±0.5pF | **GRM1555C1H8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM1555C1H8R1WA01#** | |
| | | | | ±0.1pF | **GRM1555C1H8R1BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 8.1pF | ±0.25pF | GRM1555C1H8R1CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R1DA01# | |
| | | | 8.2pF | ±0.05pF | GRM1555C1H8R2WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R2BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R2CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R2DA01# | |
| | | | 8.3pF | ±0.05pF | GRM1555C1H8R3WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R3BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R3CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R3DA01# | |
| | | | 8.4pF | ±0.05pF | GRM1555C1H8R4WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R4BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R4CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R4DA01# | |
| | | | 8.5pF | ±0.05pF | GRM1555C1H8R5WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R5BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R5CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R5DA01# | |
| | | | 8.6pF | ±0.05pF | GRM1555C1H8R6WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R6BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R6CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R6DA01# | |
| | | | 8.7pF | ±0.05pF | GRM1555C1H8R7WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R7BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R7CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R7DA01# | |
| | | | 8.8pF | ±0.05pF | GRM1555C1H8R8WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R8BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R8CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R8DA01# | |
| | | | 8.9pF | ±0.05pF | GRM1555C1H8R9WA01# | |
| | | | | ±0.1pF | GRM1555C1H8R9BA01# | |
| | | | | ±0.25pF | GRM1555C1H8R9CA01# | |
| | | | | ±0.5pF | GRM1555C1H8R9DA01# | |
| | | | 9.0pF | ±0.05pF | GRM1555C1H9R0WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R0BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R0CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R0DA01# | |
| | | | 9.1pF | ±0.05pF | GRM1555C1H9R1WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R1BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R1CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R1DA01# | |
| | | | 9.2pF | ±0.05pF | GRM1555C1H9R2WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R2BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R2CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R2DA01# | |
| | | | 9.3pF | ±0.05pF | GRM1555C1H9R3WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R3BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R3CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R3DA01# | |
| | | | 9.4pF | ±0.05pF | GRM1555C1H9R4WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R4BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R4CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R4DA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 9.5pF | ±0.05pF | GRM1555C1H9R5WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R5BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R5CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R5DA01# | |
| | | | 9.6pF | ±0.05pF | GRM1555C1H9R6WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R6BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R6CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R6DA01# | |
| | | | 9.7pF | ±0.05pF | GRM1555C1H9R7WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R7BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R7CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R7DA01# | |
| | | | 9.8pF | ±0.05pF | GRM1555C1H9R8WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R8BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R8CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R8DA01# | |
| | | | 9.9pF | ±0.05pF | GRM1555C1H9R9WA01# | |
| | | | | ±0.1pF | GRM1555C1H9R9BA01# | |
| | | | | ±0.25pF | GRM1555C1H9R9CA01# | |
| | | | | ±0.5pF | GRM1555C1H9R9DA01# | |
| | | | 10pF | ±2% | GRM1555C1H100GA01# | |
| | | | | ±5% | GRM1555C1H100JA01# | |
| | | | 12pF | ±2% | GRM1555C1H120GA01# | |
| | | | | ±5% | GRM1555C1H120JA01# | |
| | | | 15pF | ±2% | GRM1555C1H150GA01# | |
| | | | | ±5% | GRM1555C1H150JA01# | |
| | | | 18pF | ±2% | GRM1555C1H180GA01# | |
| | | | | ±5% | GRM1555C1H180JA01# | |
| | | | 22pF | ±2% | GRM1555C1H220GA01# | |
| | | | | ±5% | GRM1555C1H220JA01# | |
| | | | 27pF | ±2% | GRM1555C1H270GA01# | |
| | | | | ±5% | GRM1555C1H270JA01# | |
| | | | 33pF | ±2% | GRM1555C1H330GA01# | |
| | | | | ±5% | GRM1555C1H330JA01# | |
| | | | 39pF | ±2% | GRM1555C1H390GA01# | |
| | | | | ±5% | GRM1555C1H390JA01# | |
| | | | 47pF | ±2% | GRM1555C1H470GA01# | |
| | | | | ±5% | GRM1555C1H470JA01# | |
| | | | 56pF | ±2% | GRM1555C1H560GA01# | |
| | | | | ±5% | GRM1555C1H560JA01# | |
| | | | 68pF | ±2% | GRM1555C1H680GA01# | |
| | | | | ±5% | GRM1555C1H680JA01# | |
| | | | 82pF | ±2% | GRM1555C1H820GA01# | |
| | | | | ±5% | GRM1555C1H820JA01# | |
| | | | 100pF | ±2% | GRM1555C1H101GA01# | |
| | | | | ±5% | GRM1555C1H101JA01# | |
| | | | 120pF | ±2% | GRM1555C1H121GA01# | |
| | | | | ±5% | GRM1555C1H121JA01# | |
| | | | 150pF | ±2% | GRM1555C1H151GA01# | |
| | | | | ±5% | GRM1555C1H151JA01# | |
| | | | 180pF | ±2% | GRM1555C1H181GA01# | |
| | | | | ±5% | GRM1555C1H181JA01# | |
| | | | 220pF | ±2% | GRM1555C1H221GA01# | |
| | | | | ±5% | GRM1555C1H221JA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 270pF | ±2% | GRM1555C1H271GA01# |
| | | | | ±5% | GRM1555C1H271JA01# |
| | | | 330pF | ±2% | GRM1555C1H331GA01# |
| | | | | ±5% | GRM1555C1H331JA01# |
| | | | 390pF | ±2% | GRM1555C1H391GA01# |
| | | | | ±5% | GRM1555C1H391JA01# |
| | | | 470pF | ±2% | GRM1555C1H471GA01# |
| | | | | ±5% | GRM1555C1H471JA01# |
| | | | 560pF | ±2% | GRM1555C1H561GA01# |
| | | | | ±5% | GRM1555C1H561JA01# |
| | | | 680pF | ±2% | GRM1555C1H681GA01# |
| | | | | ±5% | GRM1555C1H681JA01# |
| | | | 820pF | ±2% | GRM1555C1H821GA01# |
| | | | | ±5% | GRM1555C1H821JA01# |
| | | | 1000pF | ±2% | GRM1555C1H102GA01# |
| | | | | ±5% | GRM1555C1H102JA01# |
| | | CK | 0.10pF | ±0.05pF | GRM1554C1HR10WA01# |
| | | | 0.20pF | ±0.05pF | GRM1554C1HR20WA01# |
| | | | | ±0.1pF | GRM1554C1HR20BA01# |
| | | | 0.30pF | ±0.05pF | GRM1554C1HR30WA01# |
| | | | | ±0.1pF | GRM1554C1HR30BA01# |
| | | | 0.40pF | ±0.05pF | GRM1554C1HR40WA01# |
| | | | | ±0.1pF | GRM1554C1HR40BA01# |
| | | | 0.50pF | ±0.05pF | GRM1554C1HR50WA01# |
| | | | | ±0.1pF | GRM1554C1HR50BA01# |
| | | | 0.60pF | ±0.05pF | GRM1554C1HR60WA01# |
| | | | | ±0.1pF | GRM1554C1HR60BA01# |
| | | | 0.70pF | ±0.05pF | GRM1554C1HR70WA01# |
| | | | | ±0.1pF | GRM1554C1HR70BA01# |
| | | | 0.80pF | ±0.05pF | GRM1554C1HR80WA01# |
| | | | | ±0.1pF | GRM1554C1HR80BA01# |
| | | | 0.90pF | ±0.05pF | GRM1554C1HR90WA01# |
| | | | | ±0.1pF | GRM1554C1HR90BA01# |
| | | | 1.0pF | ±0.05pF | GRM1554C1H1R0WA01# |
| | | | | ±0.1pF | GRM1554C1H1R0BA01# |
| | | | | ±0.25pF | GRM1554C1H1R0CA01# |
| | | | 1.1pF | ±0.05pF | GRM1554C1H1R1WA01# |
| | | | | ±0.1pF | GRM1554C1H1R1BA01# |
| | | | | ±0.25pF | GRM1554C1H1R1CA01# |
| | | | 1.2pF | ±0.05pF | GRM1554C1H1R2WA01# |
| | | | | ±0.1pF | GRM1554C1H1R2BA01# |
| | | | | ±0.25pF | GRM1554C1H1R2CA01# |
| | | | 1.3pF | ±0.05pF | GRM1554C1H1R3WA01# |
| | | | | ±0.1pF | GRM1554C1H1R3BA01# |
| | | | | ±0.25pF | GRM1554C1H1R3CA01# |
| | | | 1.4pF | ±0.05pF | GRM1554C1H1R4WA01# |
| | | | | ±0.1pF | GRM1554C1H1R4BA01# |
| | | | | ±0.25pF | GRM1554C1H1R4CA01# |
| | | | 1.5pF | ±0.05pF | GRM1554C1H1R5WA01# |
| | | | | ±0.1pF | GRM1554C1H1R5BA01# |
| | | | | ±0.25pF | GRM1554C1H1R5CA01# |
| | | | 1.6pF | ±0.05pF | GRM1554C1H1R6WA01# |
| | | | | ±0.1pF | GRM1554C1H1R6BA01# |
| | | | | ±0.25pF | GRM1554C1H1R6CA01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CK | 1.7pF | ±0.05pF | GRM1554C1H1R7WA01# |
| | | | | ±0.1pF | GRM1554C1H1R7BA01# |
| | | | | ±0.25pF | GRM1554C1H1R7CA01# |
| | | | 1.8pF | ±0.05pF | GRM1554C1H1R8WA01# |
| | | | | ±0.1pF | GRM1554C1H1R8BA01# |
| | | | | ±0.25pF | GRM1554C1H1R8CA01# |
| | | | 1.9pF | ±0.05pF | GRM1554C1H1R9WA01# |
| | | | | ±0.1pF | GRM1554C1H1R9BA01# |
| | | | | ±0.25pF | GRM1554C1H1R9CA01# |
| | | | 2.0pF | ±0.05pF | GRM1554C1H2R0WA01# |
| | | | | ±0.1pF | GRM1554C1H2R0BA01# |
| | | | | ±0.25pF | GRM1554C1H2R0CA01# |
| | | CJ | 2.1pF | ±0.05pF | GRM1553C1H2R1WA01# |
| | | | | ±0.1pF | GRM1553C1H2R1BA01# |
| | | | | ±0.25pF | GRM1553C1H2R1CA01# |
| | | | 2.2pF | ±0.05pF | GRM1553C1H2R2WA01# |
| | | | | ±0.1pF | GRM1553C1H2R2BA01# |
| | | | | ±0.25pF | GRM1553C1H2R2CA01# |
| | | | 2.3pF | ±0.05pF | GRM1553C1H2R3WA01# |
| | | | | ±0.1pF | GRM1553C1H2R3BA01# |
| | | | | ±0.25pF | GRM1553C1H2R3CA01# |
| | | | 2.4pF | ±0.05pF | GRM1553C1H2R4WA01# |
| | | | | ±0.1pF | GRM1553C1H2R4BA01# |
| | | | | ±0.25pF | GRM1553C1H2R4CA01# |
| | | | 2.5pF | ±0.05pF | GRM1553C1H2R5WA01# |
| | | | | ±0.1pF | GRM1553C1H2R5BA01# |
| | | | | ±0.25pF | GRM1553C1H2R5CA01# |
| | | | 2.6pF | ±0.05pF | GRM1553C1H2R6WA01# |
| | | | | ±0.1pF | GRM1553C1H2R6BA01# |
| | | | | ±0.25pF | GRM1553C1H2R6CA01# |
| | | | 2.7pF | ±0.05pF | GRM1553C1H2R7WA01# |
| | | | | ±0.1pF | GRM1553C1H2R7BA01# |
| | | | | ±0.25pF | GRM1553C1H2R7CA01# |
| | | | 2.8pF | ±0.05pF | GRM1553C1H2R8WA01# |
| | | | | ±0.1pF | GRM1553C1H2R8BA01# |
| | | | | ±0.25pF | GRM1553C1H2R8CA01# |
| | | | 2.9pF | ±0.05pF | GRM1553C1H2R9WA01# |
| | | | | ±0.1pF | GRM1553C1H2R9BA01# |
| | | | | ±0.25pF | GRM1553C1H2R9CA01# |
| | | | 3.0pF | ±0.05pF | GRM1553C1H3R0WA01# |
| | | | | ±0.1pF | GRM1553C1H3R0BA01# |
| | | | | ±0.25pF | GRM1553C1H3R0CA01# |
| | | | 3.1pF | ±0.05pF | GRM1553C1H3R1WA01# |
| | | | | ±0.1pF | GRM1553C1H3R1BA01# |
| | | | | ±0.25pF | GRM1553C1H3R1CA01# |
| | | | 3.2pF | ±0.05pF | GRM1553C1H3R2WA01# |
| | | | | ±0.1pF | GRM1553C1H3R2BA01# |
| | | | | ±0.25pF | GRM1553C1H3R2CA01# |
| | | | 3.3pF | ±0.05pF | GRM1553C1H3R3WA01# |
| | | | | ±0.1pF | GRM1553C1H3R3BA01# |
| | | | | ±0.25pF | GRM1553C1H3R3CA01# |
| | | | 3.4pF | ±0.05pF | GRM1553C1H3R4WA01# |
| | | | | ±0.1pF | GRM1553C1H3R4BA01# |
| | | | | ±0.25pF | GRM1553C1H3R4CA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CJ | 3.5pF | ±0.05pF | GRM1553C1H3R5WA01# | |
| | | | | ±0.1pF | GRM1553C1H3R5BA01# | |
| | | | | ±0.25pF | GRM1553C1H3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM1553C1H3R6WA01# | |
| | | | | ±0.1pF | GRM1553C1H3R6BA01# | |
| | | | | ±0.25pF | GRM1553C1H3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM1553C1H3R7WA01# | |
| | | | | ±0.1pF | GRM1553C1H3R7BA01# | |
| | | | | ±0.25pF | GRM1553C1H3R7CA01# | |
| | | | 3.8pF | ±0.05pF | GRM1553C1H3R8WA01# | |
| | | | | ±0.1pF | GRM1553C1H3R8BA01# | |
| | | | | ±0.25pF | GRM1553C1H3R8CA01# | |
| | | | 3.9pF | ±0.05pF | GRM1553C1H3R9WA01# | |
| | | | | ±0.1pF | GRM1553C1H3R9BA01# | |
| | | | | ±0.25pF | GRM1553C1H3R9CA01# | |
| | | CH | 4.0pF | ±0.05pF | GRM1552C1H4R0WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R0BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R0CA01# | |
| | | | 4.1pF | ±0.05pF | GRM1552C1H4R1WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R1BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R1CA01# | |
| | | | 4.2pF | ±0.05pF | GRM1552C1H4R2WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R2BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R2CA01# | |
| | | | 4.3pF | ±0.05pF | GRM1552C1H4R3WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R3BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM1552C1H4R4WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R4BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM1552C1H4R5WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R5BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM1552C1H4R6WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R6BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM1552C1H4R7WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R7BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM1552C1H4R8WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R8BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM1552C1H4R9WA01# | |
| | | | | ±0.1pF | GRM1552C1H4R9BA01# | |
| | | | | ±0.25pF | GRM1552C1H4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM1552C1H5R0WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R0BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM1552C1H5R1WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R1BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R1CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM1552C1H5R2WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R2BA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 5.2pF | ±0.25pF | GRM1552C1H5R2CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM1552C1H5R3WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R3BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R3CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM1552C1H5R4WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R4BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R4CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM1552C1H5R5WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R5BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R5CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM1552C1H5R6WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R6BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R6CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM1552C1H5R7WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R7BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R7CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R7DA01# | |
| | | | 5.8pF | ±0.05pF | GRM1552C1H5R8WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R8BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R8CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R8DA01# | |
| | | | 5.9pF | ±0.05pF | GRM1552C1H5R9WA01# | |
| | | | | ±0.1pF | GRM1552C1H5R9BA01# | |
| | | | | ±0.25pF | GRM1552C1H5R9CA01# | |
| | | | | ±0.5pF | GRM1552C1H5R9DA01# | |
| | | | 6.0pF | ±0.05pF | GRM1552C1H6R0WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R0BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R0CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R0DA01# | |
| | | | 6.1pF | ±0.05pF | GRM1552C1H6R1WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R1BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R1CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R1DA01# | |
| | | | 6.2pF | ±0.05pF | GRM1552C1H6R2WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R2BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R2CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R2DA01# | |
| | | | 6.3pF | ±0.05pF | GRM1552C1H6R3WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R3BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R3CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R3DA01# | |
| | | | 6.4pF | ±0.05pF | GRM1552C1H6R4WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R4BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R4CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R4DA01# | |
| | | | 6.5pF | ±0.05pF | GRM1552C1H6R5WA01# | |
| | | | | ±0.1pF | GRM1552C1H6R5BA01# | |
| | | | | ±0.25pF | GRM1552C1H6R5CA01# | |
| | | | | ±0.5pF | GRM1552C1H6R5DA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 6.6pF | ±0.05pF | GRM1552C1H6R6WA01# |
| | | | | ±0.1pF | GRM1552C1H6R6BA01# |
| | | | | ±0.25pF | GRM1552C1H6R6CA01# |
| | | | | ±0.5pF | GRM1552C1H6R6DA01# |
| | | | 6.7pF | ±0.05pF | GRM1552C1H6R7WA01# |
| | | | | ±0.1pF | GRM1552C1H6R7BA01# |
| | | | | ±0.25pF | GRM1552C1H6R7CA01# |
| | | | | ±0.5pF | GRM1552C1H6R7DA01# |
| | | | 6.8pF | ±0.05pF | GRM1552C1H6R8WA01# |
| | | | | ±0.1pF | GRM1552C1H6R8BA01# |
| | | | | ±0.25pF | GRM1552C1H6R8CA01# |
| | | | | ±0.5pF | GRM1552C1H6R8DA01# |
| | | | 6.9pF | ±0.05pF | GRM1552C1H6R9WA01# |
| | | | | ±0.1pF | GRM1552C1H6R9BA01# |
| | | | | ±0.25pF | GRM1552C1H6R9CA01# |
| | | | | ±0.5pF | GRM1552C1H6R9DA01# |
| | | | 7.0pF | ±0.05pF | GRM1552C1H7R0WA01# |
| | | | | ±0.1pF | GRM1552C1H7R0BA01# |
| | | | | ±0.25pF | GRM1552C1H7R0CA01# |
| | | | | ±0.5pF | GRM1552C1H7R0DA01# |
| | | | 7.1pF | ±0.05pF | GRM1552C1H7R1WA01# |
| | | | | ±0.1pF | GRM1552C1H7R1BA01# |
| | | | | ±0.25pF | GRM1552C1H7R1CA01# |
| | | | | ±0.5pF | GRM1552C1H7R1DA01# |
| | | | 7.2pF | ±0.05pF | GRM1552C1H7R2WA01# |
| | | | | ±0.1pF | GRM1552C1H7R2BA01# |
| | | | | ±0.25pF | GRM1552C1H7R2CA01# |
| | | | | ±0.5pF | GRM1552C1H7R2DA01# |
| | | | 7.3pF | ±0.05pF | GRM1552C1H7R3WA01# |
| | | | | ±0.1pF | GRM1552C1H7R3BA01# |
| | | | | ±0.25pF | GRM1552C1H7R3CA01# |
| | | | | ±0.5pF | GRM1552C1H7R3DA01# |
| | | | 7.4pF | ±0.05pF | GRM1552C1H7R4WA01# |
| | | | | ±0.1pF | GRM1552C1H7R4BA01# |
| | | | | ±0.25pF | GRM1552C1H7R4CA01# |
| | | | | ±0.5pF | GRM1552C1H7R4DA01# |
| | | | 7.5pF | ±0.05pF | GRM1552C1H7R5WA01# |
| | | | | ±0.1pF | GRM1552C1H7R5BA01# |
| | | | | ±0.25pF | GRM1552C1H7R5CA01# |
| | | | | ±0.5pF | GRM1552C1H7R5DA01# |
| | | | 7.6pF | ±0.05pF | GRM1552C1H7R6WA01# |
| | | | | ±0.1pF | GRM1552C1H7R6BA01# |
| | | | | ±0.25pF | GRM1552C1H7R6CA01# |
| | | | | ±0.5pF | GRM1552C1H7R6DA01# |
| | | | 7.7pF | ±0.05pF | GRM1552C1H7R7WA01# |
| | | | | ±0.1pF | GRM1552C1H7R7BA01# |
| | | | | ±0.25pF | GRM1552C1H7R7CA01# |
| | | | | ±0.5pF | GRM1552C1H7R7DA01# |
| | | | 7.8pF | ±0.05pF | GRM1552C1H7R8WA01# |
| | | | | ±0.1pF | GRM1552C1H7R8BA01# |
| | | | | ±0.25pF | GRM1552C1H7R8CA01# |
| | | | | ±0.5pF | GRM1552C1H7R8DA01# |
| | | | 7.9pF | ±0.05pF | GRM1552C1H7R9WA01# |
| | | | | ±0.1pF | GRM1552C1H7R9BA01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 7.9pF | ±0.25pF | GRM1552C1H7R9CA01# |
| | | | | ±0.5pF | GRM1552C1H7R9DA01# |
| | | | 8.0pF | ±0.05pF | GRM1552C1H8R0WA01# |
| | | | | ±0.1pF | GRM1552C1H8R0BA01# |
| | | | | ±0.25pF | GRM1552C1H8R0CA01# |
| | | | | ±0.5pF | GRM1552C1H8R0DA01# |
| | | | 8.1pF | ±0.05pF | GRM1552C1H8R1WA01# |
| | | | | ±0.1pF | GRM1552C1H8R1BA01# |
| | | | | ±0.25pF | GRM1552C1H8R1CA01# |
| | | | | ±0.5pF | GRM1552C1H8R1DA01# |
| | | | 8.2pF | ±0.05pF | GRM1552C1H8R2WA01# |
| | | | | ±0.1pF | GRM1552C1H8R2BA01# |
| | | | | ±0.25pF | GRM1552C1H8R2CA01# |
| | | | | ±0.5pF | GRM1552C1H8R2DA01# |
| | | | 8.3pF | ±0.05pF | GRM1552C1H8R3WA01# |
| | | | | ±0.1pF | GRM1552C1H8R3BA01# |
| | | | | ±0.25pF | GRM1552C1H8R3CA01# |
| | | | | ±0.5pF | GRM1552C1H8R3DA01# |
| | | | 8.4pF | ±0.05pF | GRM1552C1H8R4WA01# |
| | | | | ±0.1pF | GRM1552C1H8R4BA01# |
| | | | | ±0.25pF | GRM1552C1H8R4CA01# |
| | | | | ±0.5pF | GRM1552C1H8R4DA01# |
| | | | 8.5pF | ±0.05pF | GRM1552C1H8R5WA01# |
| | | | | ±0.1pF | GRM1552C1H8R5BA01# |
| | | | | ±0.25pF | GRM1552C1H8R5CA01# |
| | | | | ±0.5pF | GRM1552C1H8R5DA01# |
| | | | 8.6pF | ±0.05pF | GRM1552C1H8R6WA01# |
| | | | | ±0.1pF | GRM1552C1H8R6BA01# |
| | | | | ±0.25pF | GRM1552C1H8R6CA01# |
| | | | | ±0.5pF | GRM1552C1H8R6DA01# |
| | | | 8.7pF | ±0.05pF | GRM1552C1H8R7WA01# |
| | | | | ±0.1pF | GRM1552C1H8R7BA01# |
| | | | | ±0.25pF | GRM1552C1H8R7CA01# |
| | | | | ±0.5pF | GRM1552C1H8R7DA01# |
| | | | 8.8pF | ±0.05pF | GRM1552C1H8R8WA01# |
| | | | | ±0.1pF | GRM1552C1H8R8BA01# |
| | | | | ±0.25pF | GRM1552C1H8R8CA01# |
| | | | | ±0.5pF | GRM1552C1H8R8DA01# |
| | | | 8.9pF | ±0.05pF | GRM1552C1H8R9WA01# |
| | | | | ±0.1pF | GRM1552C1H8R9BA01# |
| | | | | ±0.25pF | GRM1552C1H8R9CA01# |
| | | | | ±0.5pF | GRM1552C1H8R9DA01# |
| | | | 9.0pF | ±0.05pF | GRM1552C1H9R0WA01# |
| | | | | ±0.1pF | GRM1552C1H9R0BA01# |
| | | | | ±0.25pF | GRM1552C1H9R0CA01# |
| | | | | ±0.5pF | GRM1552C1H9R0DA01# |
| | | | 9.1pF | ±0.05pF | GRM1552C1H9R1WA01# |
| | | | | ±0.1pF | GRM1552C1H9R1BA01# |
| | | | | ±0.25pF | GRM1552C1H9R1CA01# |
| | | | | ±0.5pF | GRM1552C1H9R1DA01# |
| | | | 9.2pF | ±0.05pF | GRM1552C1H9R2WA01# |
| | | | | ±0.1pF | GRM1552C1H9R2BA01# |
| | | | | ±0.25pF | GRM1552C1H9R2CA01# |
| | | | | ±0.5pF | GRM1552C1H9R2DA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 9.3pF | ±0.05pF | **GRM1552C1H9R3WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R3BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R3CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R3DA01#** | |
| | | | 9.4pF | ±0.05pF | **GRM1552C1H9R4WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R4BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R4CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R4DA01#** | |
| | | | 9.5pF | ±0.05pF | **GRM1552C1H9R5WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R5BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R5CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R5DA01#** | |
| | | | 9.6pF | ±0.05pF | **GRM1552C1H9R6WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R6BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R6CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R6DA01#** | |
| | | | 9.7pF | ±0.05pF | **GRM1552C1H9R7WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R7BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R7CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R7DA01#** | |
| | | | 9.8pF | ±0.05pF | **GRM1552C1H9R8WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R8BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R8CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R8DA01#** | |
| | | | 9.9pF | ±0.05pF | **GRM1552C1H9R9WA01#** | |
| | | | | ±0.1pF | **GRM1552C1H9R9BA01#** | |
| | | | | ±0.25pF | **GRM1552C1H9R9CA01#** | |
| | | | | ±0.5pF | **GRM1552C1H9R9DA01#** | |
| | | | 10pF | ±2% | **GRM1552C1H100GA01#** | |
| | | | | ±5% | **GRM1552C1H100JA01#** | |
| | | | 12pF | ±2% | **GRM1552C1H120GA01#** | |
| | | | | ±5% | **GRM1552C1H120JA01#** | |
| | | | 15pF | ±2% | **GRM1552C1H150GA01#** | |
| | | | | ±5% | **GRM1552C1H150JA01#** | |
| | | | 18pF | ±2% | **GRM1552C1H180GA01#** | |
| | | | | ±5% | **GRM1552C1H180JA01#** | |
| | | | 22pF | ±2% | **GRM1552C1H220GA01#** | |
| | | | | ±5% | **GRM1552C1H220JA01#** | |
| | | | 27pF | ±2% | **GRM1552C1H270GA01#** | |
| | | | | ±5% | **GRM1552C1H270JA01#** | |
| | | | 33pF | ±2% | **GRM1552C1H330GA01#** | |
| | | | | ±5% | **GRM1552C1H330JA01#** | |
| | | | 39pF | ±2% | **GRM1552C1H390GA01#** | |
| | | | | ±5% | **GRM1552C1H390JA01#** | |
| | | | 47pF | ±2% | **GRM1552C1H470GA01#** | |
| | | | | ±5% | **GRM1552C1H470JA01#** | |
| | | | 56pF | ±2% | **GRM1552C1H560GA01#** | |
| | | | | ±5% | **GRM1552C1H560JA01#** | |
| | | | 68pF | ±2% | **GRM1552C1H680GA01#** | |
| | | | | ±5% | **GRM1552C1H680JA01#** | |
| | | | 82pF | ±2% | **GRM1552C1H820GA01#** | |
| | | | | ±5% | **GRM1552C1H820JA01#** | |
| | | | 100pF | ±2% | **GRM1552C1H101GA01#** | |
| | | | | ±5% | **GRM1552C1H101JA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 120pF | ±2% | **GRM1552C1H121GA01#** | |
| | | | | ±5% | **GRM1552C1H121JA01#** | |
| | | | 150pF | ±2% | **GRM1552C1H151GA01#** | |
| | | | | ±5% | **GRM1552C1H151JA01#** | |
| | | | 180pF | ±2% | **GRM1552C1H181GA01#** | |
| | | | | ±5% | **GRM1552C1H181JA01#** | |
| | | | 220pF | ±2% | **GRM1552C1H221GA01#** | |
| | | | | ±5% | **GRM1552C1H221JA01#** | |
| | | | 270pF | ±2% | **GRM1552C1H271GA01#** | |
| | | | | ±5% | **GRM1552C1H271JA01#** | |
| | | | 330pF | ±2% | **GRM1552C1H331GA01#** | |
| | | | | ±5% | **GRM1552C1H331JA01#** | |
| | | | 390pF | ±2% | **GRM1552C1H391GA01#** | |
| | | | | ±5% | **GRM1552C1H391JA01#** | |
| | | | 470pF | ±2% | **GRM1552C1H471GA01#** | |
| | | | | ±5% | **GRM1552C1H471JA01#** | |
| | | | 560pF | ±2% | **GRM1552C1H561GA01#** | |
| | | | | ±5% | **GRM1552C1H561JA01#** | |
| | | | 680pF | ±2% | **GRM1552C1H681GA01#** | |
| | | | | ±5% | **GRM1552C1H681JA01#** | |
| | | | 820pF | ±2% | **GRM1552C1H821GA01#** | |
| | | | | ±5% | **GRM1552C1H821JA01#** | |
| | | | 1000pF | ±2% | **GRM1552C1H102GA01#** | |
| | | | | ±5% | **GRM1552C1H102JA01#** | |
| | 10Vdc | SL | 1200pF | ±5% | **GRM1551X1A122JA01#** | |
| | | | 1500pF | ±5% | **GRM1551X1A152JA01#** | |
| | | | 1800pF | ±5% | **GRM1551X1A182JA01#** | |
| | | | 2200pF | ±5% | **GRM1551X1A222JA01#** | |
| | | | 2700pF | ±5% | **GRM1551X1A272JA01#** | |
| | | | 3300pF | ±5% | **GRM1551X1A332JA01#** | |
| | | | 3900pF | ±5% | **GRM1551X1A392JA01#** | |
| | | | 4700pF | ±5% | **GRM1551X1A472JA01#** | |
| | | U2J | 1200pF | ±5% | **GRM1557U1A122JA01#** | |
| | | | 1500pF | ±5% | **GRM1557U1A152JA01#** | |
| | | | 1800pF | ±5% | **GRM1557U1A182JA01#** | |
| | | | 2200pF | ±5% | **GRM1557U1A222JA01#** | |
| | | | 2700pF | ±5% | **GRM1557U1A272JA01#** | |
| | | | 3300pF | ±5% | **GRM1557U1A332JA01#** | |
| | | | 3900pF | ±5% | **GRM1557U1A392JA01#** | |
| | | | 4700pF | ±5% | **GRM1557U1A472JA01#** | |
| | | UJ | 1200pF | ±5% | **GRM1553U1A122JA01#** | |
| | | | 1500pF | ±5% | **GRM1553U1A152JA01#** | |
| | | | 1800pF | ±5% | **GRM1553U1A182JA01#** | |
| | | | 2200pF | ±5% | **GRM1553U1A222JA01#** | |
| | | | 2700pF | ±5% | **GRM1553U1A272JA01#** | |
| | | | 3300pF | ±5% | **GRM1553U1A332JA01#** | |
| | | | 3900pF | ±5% | **GRM1553U1A392JA01#** | |
| | | | 4700pF | ±5% | **GRM1553U1A472JA01#** | |

## ■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.5mm | 50Vdc | SL | 2200pF | ±5% | **GRM1851X1H222JA44#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.5mm | 50Vdc | SL | 2700pF | ±5% | **GRM1851X1H272JA44#** |
| | | | 3300pF | ±5% | **GRM1851X1H332JA44#** |
| | | | 3900pF | ±5% | **GRM1851X1H392JA44#** |
| | | | 4700pF | ±5% | **GRM1851X1H472JA44#** |
| | | U2J | 2200pF | ±5% | **GRM1857U1H222JA44#** |
| | | | 2700pF | ±5% | **GRM1857U1H272JA44#** |
| | | | 3300pF | ±5% | **GRM1857U1H332JA44#** |
| | | | 3900pF | ±5% | **GRM1857U1H392JA44#** |
| | | | 4700pF | ±5% | **GRM1857U1H472JA44#** |
| | | UJ | 2200pF | ±5% | **GRM1853U1H222JA44#** |
| | | | 2700pF | ±5% | **GRM1853U1H272JA44#** |
| | | | 3300pF | ±5% | **GRM1853U1H332JA44#** |
| | | | 3900pF | ±5% | **GRM1853U1H392JA44#** |
| | | | 4700pF | ±5% | **GRM1853U1H472JA44#** |
| | 10Vdc | SL | 5600pF | ±5% | **GRM1851X1A562JA44#** |
| | | | 6800pF | ±5% | **GRM1851X1A682JA44#** |
| | | | 8200pF | ±5% | **GRM1851X1A822JA44#** |
| | | | 10000pF | ±5% | **GRM1851X1A103JA44#** |
| | | U2J | 5600pF | ±5% | **GRM1857U1A562JA44#** |
| | | | 6800pF | ±5% | **GRM1857U1A682JA44#** |
| | | | 8200pF | ±5% | **GRM1857U1A822JA44#** |
| | | | 10000pF | ±5% | **GRM1857U1A103JA44#** |
| | | UJ | 5600pF | ±5% | **GRM1853U1A562JA44#** |
| | | | 6800pF | ±5% | **GRM1853U1A682JA44#** |
| | | | 8200pF | ±5% | **GRM1853U1A822JA44#** |
| | | | 10000pF | ±5% | **GRM1853U1A103JA44#** |
| 0.9mm | 100Vdc | C0G | 0.50pF | ±0.05pF | **GRM1885C2AR50WA01#** |
| | | | | ±0.1pF | **GRM1885C2AR50BA01#** |
| | | | 0.60pF | ±0.05pF | **GRM1885C2AR60WA01#** |
| | | | | ±0.1pF | **GRM1885C2AR60BA01#** |
| | | | 0.70pF | ±0.05pF | **GRM1885C2AR70WA01#** |
| | | | | ±0.1pF | **GRM1885C2AR70BA01#** |
| | | | 0.80pF | ±0.05pF | **GRM1885C2AR80WA01#** |
| | | | | ±0.1pF | **GRM1885C2AR80BA01#** |
| | | | 0.90pF | ±0.05pF | **GRM1885C2AR90WA01#** |
| | | | | ±0.1pF | **GRM1885C2AR90BA01#** |
| | | | 1.0pF | ±0.05pF | **GRM1885C2A1R0WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R0BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R0CA01#** |
| | | | 1.1pF | ±0.05pF | **GRM1885C2A1R1WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R1BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R1CA01#** |
| | | | 1.2pF | ±0.05pF | **GRM1885C2A1R2WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R2BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R2CA01#** |
| | | | 1.3pF | ±0.05pF | **GRM1885C2A1R3WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R3BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R3CA01#** |
| | | | 1.4pF | ±0.05pF | **GRM1885C2A1R4WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R4BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R4CA01#** |
| | | | 1.5pF | ±0.05pF | **GRM1885C2A1R5WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R5BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R5CA01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 1.6pF | ±0.05pF | **GRM1885C2A1R6WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R6BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R6CA01#** |
| | | | 1.7pF | ±0.05pF | **GRM1885C2A1R7WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R7BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R7CA01#** |
| | | | 1.8pF | ±0.05pF | **GRM1885C2A1R8WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R8BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R8CA01#** |
| | | | 1.9pF | ±0.05pF | **GRM1885C2A1R9WA01#** |
| | | | | ±0.1pF | **GRM1885C2A1R9BA01#** |
| | | | | ±0.25pF | **GRM1885C2A1R9CA01#** |
| | | | 2.0pF | ±0.05pF | **GRM1885C2A2R0WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R0BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R0CA01#** |
| | | | 2.1pF | ±0.05pF | **GRM1885C2A2R1WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R1BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R1CA01#** |
| | | | 2.2pF | ±0.05pF | **GRM1885C2A2R2WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R2BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R2CA01#** |
| | | | 2.3pF | ±0.05pF | **GRM1885C2A2R3WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R3BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R3CA01#** |
| | | | 2.4pF | ±0.05pF | **GRM1885C2A2R4WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R4BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R4CA01#** |
| | | | 2.5pF | ±0.05pF | **GRM1885C2A2R5WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R5BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R5CA01#** |
| | | | 2.6pF | ±0.05pF | **GRM1885C2A2R6WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R6BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R6CA01#** |
| | | | 2.7pF | ±0.05pF | **GRM1885C2A2R7WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R7BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R7CA01#** |
| | | | 2.8pF | ±0.05pF | **GRM1885C2A2R8WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R8BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R8CA01#** |
| | | | 2.9pF | ±0.05pF | **GRM1885C2A2R9WA01#** |
| | | | | ±0.1pF | **GRM1885C2A2R9BA01#** |
| | | | | ±0.25pF | **GRM1885C2A2R9CA01#** |
| | | | 3.0pF | ±0.05pF | **GRM1885C2A3R0WA01#** |
| | | | | ±0.1pF | **GRM1885C2A3R0BA01#** |
| | | | | ±0.25pF | **GRM1885C2A3R0CA01#** |
| | | | 3.1pF | ±0.05pF | **GRM1885C2A3R1WA01#** |
| | | | | ±0.1pF | **GRM1885C2A3R1BA01#** |
| | | | | ±0.25pF | **GRM1885C2A3R1CA01#** |
| | | | 3.2pF | ±0.05pF | **GRM1885C2A3R2WA01#** |
| | | | | ±0.1pF | **GRM1885C2A3R2BA01#** |
| | | | | ±0.25pF | **GRM1885C2A3R2CA01#** |
| | | | 3.3pF | ±0.05pF | **GRM1885C2A3R3WA01#** |
| | | | | ±0.1pF | **GRM1885C2A3R3BA01#** |
| | | | | ±0.25pF | **GRM1885C2A3R3CA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 3.4pF | ±0.05pF | GRM1885C2A3R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R4CA01# | |
| | | | 3.5pF | ±0.05pF | GRM1885C2A3R5WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM1885C2A3R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM1885C2A3R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R7CA01# | |
| | | | 3.8pF | ±0.05pF | GRM1885C2A3R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R8CA01# | |
| | | | 3.9pF | ±0.05pF | GRM1885C2A3R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A3R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A3R9CA01# | |
| | | | 4.0pF | ±0.05pF | GRM1885C2A4R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R0CA01# | |
| | | | 4.1pF | ±0.05pF | GRM1885C2A4R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R1CA01# | |
| | | | 4.2pF | ±0.05pF | GRM1885C2A4R2WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R2BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R2CA01# | |
| | | | 4.3pF | ±0.05pF | GRM1885C2A4R3WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R3BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM1885C2A4R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM1885C2A4R5WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM1885C2A4R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM1885C2A4R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM1885C2A4R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM1885C2A4R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A4R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM1885C2A5R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM1885C2A5R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R1CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 5.1pF | ±0.5pF | GRM1885C2A5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM1885C2A5R2WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R2BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R2CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM1885C2A5R3WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R3BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R3CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM1885C2A5R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R4CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM1885C2A5R5WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R5CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM1885C2A5R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R6CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM1885C2A5R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R7CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R7DA01# | |
| | | | 5.8pF | ±0.05pF | GRM1885C2A5R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R8CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R8DA01# | |
| | | | 5.9pF | ±0.05pF | GRM1885C2A5R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A5R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A5R9CA01# | |
| | | | | ±0.5pF | GRM1885C2A5R9DA01# | |
| | | | 6.0pF | ±0.05pF | GRM1885C2A6R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R0CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R0DA01# | |
| | | | 6.1pF | ±0.05pF | GRM1885C2A6R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R1CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R1DA01# | |
| | | | 6.2pF | ±0.05pF | GRM1885C2A6R2WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R2BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R2CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R2DA01# | |
| | | | 6.3pF | ±0.05pF | GRM1885C2A6R3WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R3BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R3CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R3DA01# | |
| | | | 6.4pF | ±0.05pF | GRM1885C2A6R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R4CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R4DA01# | |
| | | | 6.5pF | ±0.05pF | GRM1885C2A6R5WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 6.5pF | ±0.1pF | GRM1885C2A6R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R5CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R5DA01# | |
| | | | 6.6pF | ±0.05pF | GRM1885C2A6R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R6CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R6DA01# | |
| | | | 6.7pF | ±0.05pF | GRM1885C2A6R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R7CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R7DA01# | |
| | | | 6.8pF | ±0.05pF | GRM1885C2A6R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R8CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R8DA01# | |
| | | | 6.9pF | ±0.05pF | GRM1885C2A6R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A6R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A6R9CA01# | |
| | | | | ±0.5pF | GRM1885C2A6R9DA01# | |
| | | | 7.0pF | ±0.05pF | GRM1885C2A7R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R0CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R0DA01# | |
| | | | 7.1pF | ±0.05pF | GRM1885C2A7R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R1CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R1DA01# | |
| | | | 7.2pF | ±0.05pF | GRM1885C2A7R2WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R2BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R2CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R2DA01# | |
| | | | 7.3pF | ±0.05pF | GRM1885C2A7R3WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R3BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R3CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R3DA01# | |
| | | | 7.4pF | ±0.05pF | GRM1885C2A7R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R4CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R4DA01# | |
| | | | 7.5pF | ±0.05pF | GRM1885C2A7R5WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R5CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R5DA01# | |
| | | | 7.6pF | ±0.05pF | GRM1885C2A7R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R6CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R6DA01# | |
| | | | 7.7pF | ±0.05pF | GRM1885C2A7R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R7CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R7DA01# | |
| | | | 7.8pF | ±0.05pF | GRM1885C2A7R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R8CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 7.8pF | ±0.5pF | GRM1885C2A7R8DA01# | |
| | | | 7.9pF | ±0.05pF | GRM1885C2A7R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A7R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A7R9CA01# | |
| | | | | ±0.5pF | GRM1885C2A7R9DA01# | |
| | | | 8.0pF | ±0.05pF | GRM1885C2A8R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R0CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R0DA01# | |
| | | | 8.1pF | ±0.05pF | GRM1885C2A8R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R1CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R1DA01# | |
| | | | 8.2pF | ±0.05pF | GRM1885C2A8R2WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R2BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R2CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R2DA01# | |
| | | | 8.3pF | ±0.05pF | GRM1885C2A8R3WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R3BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R3CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R3DA01# | |
| | | | 8.4pF | ±0.05pF | GRM1885C2A8R4WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R4BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R4CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R4DA01# | |
| | | | 8.5pF | ±0.05pF | GRM1885C2A8R5WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R5BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R5CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R5DA01# | |
| | | | 8.6pF | ±0.05pF | GRM1885C2A8R6WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R6BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R6CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R6DA01# | |
| | | | 8.7pF | ±0.05pF | GRM1885C2A8R7WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R7BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R7CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R7DA01# | |
| | | | 8.8pF | ±0.05pF | GRM1885C2A8R8WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R8BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R8CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R8DA01# | |
| | | | 8.9pF | ±0.05pF | GRM1885C2A8R9WA01# | |
| | | | | ±0.1pF | GRM1885C2A8R9BA01# | |
| | | | | ±0.25pF | GRM1885C2A8R9CA01# | |
| | | | | ±0.5pF | GRM1885C2A8R9DA01# | |
| | | | 9.0pF | ±0.05pF | GRM1885C2A9R0WA01# | |
| | | | | ±0.1pF | GRM1885C2A9R0BA01# | |
| | | | | ±0.25pF | GRM1885C2A9R0CA01# | |
| | | | | ±0.5pF | GRM1885C2A9R0DA01# | |
| | | | 9.1pF | ±0.05pF | GRM1885C2A9R1WA01# | |
| | | | | ±0.1pF | GRM1885C2A9R1BA01# | |
| | | | | ±0.25pF | GRM1885C2A9R1CA01# | |
| | | | | ±0.5pF | GRM1885C2A9R1DA01# | |
| | | | 9.2pF | ±0.05pF | GRM1885C2A9R2WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 9.2pF | ±0.1pF | **GRM1885C2A9R2BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R2CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R2DA01#** |
| | | | 9.3pF | ±0.05pF | **GRM1885C2A9R3WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R3BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R3CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R3DA01#** |
| | | | 9.4pF | ±0.05pF | **GRM1885C2A9R4WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R4BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R4CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R4DA01#** |
| | | | 9.5pF | ±0.05pF | **GRM1885C2A9R5WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R5BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R5CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R5DA01#** |
| | | | 9.6pF | ±0.05pF | **GRM1885C2A9R6WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R6BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R6CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R6DA01#** |
| | | | 9.7pF | ±0.05pF | **GRM1885C2A9R7WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R7BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R7CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R7DA01#** |
| | | | 9.8pF | ±0.05pF | **GRM1885C2A9R8WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R8BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R8CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R8DA01#** |
| | | | 9.9pF | ±0.05pF | **GRM1885C2A9R9WA01#** |
| | | | | ±0.1pF | **GRM1885C2A9R9BA01#** |
| | | | | ±0.25pF | **GRM1885C2A9R9CA01#** |
| | | | | ±0.5pF | **GRM1885C2A9R9DA01#** |
| | | | 10pF | ±5% | **GRM1885C2A100JA01#** |
| | | | 12pF | ±5% | **GRM1885C2A120JA01#** |
| | | | 15pF | ±5% | **GRM1885C2A150JA01#** |
| | | | 18pF | ±5% | **GRM1885C2A180JA01#** |
| | | | 22pF | ±5% | **GRM1885C2A220JA01#** |
| | | | 27pF | ±5% | **GRM1885C2A270JA01#** |
| | | | 33pF | ±5% | **GRM1885C2A330JA01#** |
| | | | 39pF | ±5% | **GRM1885C2A390JA01#** |
| | | | 47pF | ±5% | **GRM1885C2A470JA01#** |
| | | | 56pF | ±5% | **GRM1885C2A560JA01#** |
| | | | 68pF | ±5% | **GRM1885C2A680JA01#** |
| | | | 82pF | ±5% | **GRM1885C2A820JA01#** |
| | | | 100pF | ±5% | **GRM1885C2A101JA01#** |
| | | | 120pF | ±5% | **GRM1885C2A121JA01#** |
| | | | 150pF | ±5% | **GRM1885C2A151JA01#** |
| | | | 180pF | ±5% | **GRM1885C2A181JA01#** |
| | | | 220pF | ±5% | **GRM1885C2A221JA01#** |
| | | | 270pF | ±5% | **GRM1885C2A271JA01#** |
| | | | 330pF | ±5% | **GRM1885C2A331JA01#** |
| | | | 390pF | ±5% | **GRM1885C2A391JA01#** |
| | | | 470pF | ±5% | **GRM1885C2A471JA01#** |
| | | | 560pF | ±5% | **GRM1885C2A561JA01#** |
| | | | 680pF | ±5% | **GRM1885C2A681JA01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 820pF | ±5% | **GRM1885C2A821JA01#** |
| | | | 1000pF | ±5% | **GRM1885C2A102JA01#** |
| | | | 1200pF | ±5% | **GRM1885C2A122JA01#** |
| | | | 1500pF | ±5% | **GRM1885C2A152JA01#** |
| | | CK | 0.50pF | ±0.05pF | **GRM1884C2AR50WA01#** |
| | | | | ±0.1pF | **GRM1884C2AR50BA01#** |
| | | | 0.60pF | ±0.05pF | **GRM1884C2AR60WA01#** |
| | | | | ±0.1pF | **GRM1884C2AR60BA01#** |
| | | | 0.70pF | ±0.05pF | **GRM1884C2AR70WA01#** |
| | | | | ±0.1pF | **GRM1884C2AR70BA01#** |
| | | | 0.80pF | ±0.05pF | **GRM1884C2AR80WA01#** |
| | | | | ±0.1pF | **GRM1884C2AR80BA01#** |
| | | | 0.90pF | ±0.05pF | **GRM1884C2AR90WA01#** |
| | | | | ±0.1pF | **GRM1884C2AR90BA01#** |
| | | | 1.0pF | ±0.05pF | **GRM1884C2A1R0WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R0BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R0CA01#** |
| | | | 1.1pF | ±0.05pF | **GRM1884C2A1R1WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R1BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R1CA01#** |
| | | | 1.2pF | ±0.05pF | **GRM1884C2A1R2WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R2BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R2CA01#** |
| | | | 1.3pF | ±0.05pF | **GRM1884C2A1R3WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R3BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R3CA01#** |
| | | | 1.4pF | ±0.05pF | **GRM1884C2A1R4WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R4BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R4CA01#** |
| | | | 1.5pF | ±0.05pF | **GRM1884C2A1R5WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R5BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R5CA01#** |
| | | | 1.6pF | ±0.05pF | **GRM1884C2A1R6WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R6BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R6CA01#** |
| | | | 1.7pF | ±0.05pF | **GRM1884C2A1R7WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R7BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R7CA01#** |
| | | | 1.8pF | ±0.05pF | **GRM1884C2A1R8WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R8BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R8CA01#** |
| | | | 1.9pF | ±0.05pF | **GRM1884C2A1R9WA01#** |
| | | | | ±0.1pF | **GRM1884C2A1R9BA01#** |
| | | | | ±0.25pF | **GRM1884C2A1R9CA01#** |
| | | | 2.0pF | ±0.05pF | **GRM1884C2A2R0WA01#** |
| | | | | ±0.1pF | **GRM1884C2A2R0BA01#** |
| | | | | ±0.25pF | **GRM1884C2A2R0CA01#** |
| | | CJ | 2.1pF | ±0.05pF | **GRM1883C2A2R1WA01#** |
| | | | | ±0.1pF | **GRM1883C2A2R1BA01#** |
| | | | | ±0.25pF | **GRM1883C2A2R1CA01#** |
| | | | 2.2pF | ±0.05pF | **GRM1883C2A2R2WA01#** |
| | | | | ±0.1pF | **GRM1883C2A2R2BA01#** |
| | | | | ±0.25pF | **GRM1883C2A2R2CA01#** |
| | | | 2.3pF | ±0.05pF | **GRM1883C2A2R3WA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CJ | 2.3pF | ±0.1pF | GRM1883C2A2R3BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R3CA01# | |
| | | | 2.4pF | ±0.05pF | GRM1883C2A2R4WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R4BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R4CA01# | |
| | | | 2.5pF | ±0.05pF | GRM1883C2A2R5WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R5BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R5CA01# | |
| | | | 2.6pF | ±0.05pF | GRM1883C2A2R6WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R6BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R6CA01# | |
| | | | 2.7pF | ±0.05pF | GRM1883C2A2R7WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R7BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R7CA01# | |
| | | | 2.8pF | ±0.05pF | GRM1883C2A2R8WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R8BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R8CA01# | |
| | | | 2.9pF | ±0.05pF | GRM1883C2A2R9WA01# | |
| | | | | ±0.1pF | GRM1883C2A2R9BA01# | |
| | | | | ±0.25pF | GRM1883C2A2R9CA01# | |
| | | | 3.0pF | ±0.05pF | GRM1883C2A3R0WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R0BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R0CA01# | |
| | | | 3.1pF | ±0.05pF | GRM1883C2A3R1WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R1BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R1CA01# | |
| | | | 3.2pF | ±0.05pF | GRM1883C2A3R2WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R2BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R2CA01# | |
| | | | 3.3pF | ±0.05pF | GRM1883C2A3R3WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R3BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R3CA01# | |
| | | | 3.4pF | ±0.05pF | GRM1883C2A3R4WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R4BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R4CA01# | |
| | | | 3.5pF | ±0.05pF | GRM1883C2A3R5WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R5BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R5CA01# | |
| | | | 3.6pF | ±0.05pF | GRM1883C2A3R6WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R6BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R6CA01# | |
| | | | 3.7pF | ±0.05pF | GRM1883C2A3R7WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R7BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R7CA01# | |
| | | | 3.8pF | ±0.05pF | GRM1883C2A3R8WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R8BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R8CA01# | |
| | | | 3.9pF | ±0.05pF | GRM1883C2A3R9WA01# | |
| | | | | ±0.1pF | GRM1883C2A3R9BA01# | |
| | | | | ±0.25pF | GRM1883C2A3R9CA01# | |
| | | CH | 4.0pF | ±0.05pF | GRM1882C2A4R0WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R0BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R0CA01# | |
| | | | 4.1pF | ±0.05pF | GRM1882C2A4R1WA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CH | 4.1pF | ±0.1pF | GRM1882C2A4R1BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R1CA01# | |
| | | | 4.2pF | ±0.05pF | GRM1882C2A4R2WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R2BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R2CA01# | |
| | | | 4.3pF | ±0.05pF | GRM1882C2A4R3WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R3BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R3CA01# | |
| | | | 4.4pF | ±0.05pF | GRM1882C2A4R4WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R4BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R4CA01# | |
| | | | 4.5pF | ±0.05pF | GRM1882C2A4R5WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R5BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R5CA01# | |
| | | | 4.6pF | ±0.05pF | GRM1882C2A4R6WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R6BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R6CA01# | |
| | | | 4.7pF | ±0.05pF | GRM1882C2A4R7WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R7BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R7CA01# | |
| | | | 4.8pF | ±0.05pF | GRM1882C2A4R8WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R8BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R8CA01# | |
| | | | 4.9pF | ±0.05pF | GRM1882C2A4R9WA01# | |
| | | | | ±0.1pF | GRM1882C2A4R9BA01# | |
| | | | | ±0.25pF | GRM1882C2A4R9CA01# | |
| | | | 5.0pF | ±0.05pF | GRM1882C2A5R0WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R0BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R0CA01# | |
| | | | 5.1pF | ±0.05pF | GRM1882C2A5R1WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R1BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R1CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R1DA01# | |
| | | | 5.2pF | ±0.05pF | GRM1882C2A5R2WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R2BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R2CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R2DA01# | |
| | | | 5.3pF | ±0.05pF | GRM1882C2A5R3WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R3BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R3CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R3DA01# | |
| | | | 5.4pF | ±0.05pF | GRM1882C2A5R4WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R4BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R4CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R4DA01# | |
| | | | 5.5pF | ±0.05pF | GRM1882C2A5R5WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R5BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R5CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R5DA01# | |
| | | | 5.6pF | ±0.05pF | GRM1882C2A5R6WA01# | |
| | | | | ±0.1pF | GRM1882C2A5R6BA01# | |
| | | | | ±0.25pF | GRM1882C2A5R6CA01# | |
| | | | | ±0.5pF | GRM1882C2A5R6DA01# | |
| | | | 5.7pF | ±0.05pF | GRM1882C2A5R7WA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CH | 5.7pF | ±0.1pF | **GRM1882C2A5R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A5R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM1882C2A5R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A5R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A5R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM1882C2A5R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A5R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A5R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A5R9DA01#** | |
| | | | 6.0pF | ±0.05pF | **GRM1882C2A6R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM1882C2A6R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM1882C2A6R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM1882C2A6R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM1882C2A6R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM1882C2A6R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R5CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM1882C2A6R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM1882C2A6R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM1882C2A6R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM1882C2A6R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A6R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A6R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM1882C2A7R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R0CA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CH | 7.0pF | ±0.5pF | **GRM1882C2A7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM1882C2A7R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM1882C2A7R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM1882C2A7R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM1882C2A7R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM1882C2A7R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R5CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM1882C2A7R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM1882C2A7R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM1882C2A7R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM1882C2A7R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A7R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A7R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM1882C2A8R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A8R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A8R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM1882C2A8R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A8R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A8R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM1882C2A8R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A8R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A8R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM1882C2A8R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C2A8R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C2A8R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C2A8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM1882C2A8R4WA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CH | 8.4pF | ±0.1pF | GRM1882C2A8R4BA01# |
| | | | | ±0.25pF | GRM1882C2A8R4CA01# |
| | | | | ±0.5pF | GRM1882C2A8R4DA01# |
| | | | 8.5pF | ±0.05pF | GRM1882C2A8R5WA01# |
| | | | | ±0.1pF | GRM1882C2A8R5BA01# |
| | | | | ±0.25pF | GRM1882C2A8R5CA01# |
| | | | | ±0.5pF | GRM1882C2A8R5DA01# |
| | | | 8.6pF | ±0.05pF | GRM1882C2A8R6WA01# |
| | | | | ±0.1pF | GRM1882C2A8R6BA01# |
| | | | | ±0.25pF | GRM1882C2A8R6CA01# |
| | | | | ±0.5pF | GRM1882C2A8R6DA01# |
| | | | 8.7pF | ±0.05pF | GRM1882C2A8R7WA01# |
| | | | | ±0.1pF | GRM1882C2A8R7BA01# |
| | | | | ±0.25pF | GRM1882C2A8R7CA01# |
| | | | | ±0.5pF | GRM1882C2A8R7DA01# |
| | | | 8.8pF | ±0.05pF | GRM1882C2A8R8WA01# |
| | | | | ±0.1pF | GRM1882C2A8R8BA01# |
| | | | | ±0.25pF | GRM1882C2A8R8CA01# |
| | | | | ±0.5pF | GRM1882C2A8R8DA01# |
| | | | 8.9pF | ±0.05pF | GRM1882C2A8R9WA01# |
| | | | | ±0.1pF | GRM1882C2A8R9BA01# |
| | | | | ±0.25pF | GRM1882C2A8R9CA01# |
| | | | | ±0.5pF | GRM1882C2A8R9DA01# |
| | | | 9.0pF | ±0.05pF | GRM1882C2A9R0WA01# |
| | | | | ±0.1pF | GRM1882C2A9R0BA01# |
| | | | | ±0.25pF | GRM1882C2A9R0CA01# |
| | | | | ±0.5pF | GRM1882C2A9R0DA01# |
| | | | 9.1pF | ±0.05pF | GRM1882C2A9R1WA01# |
| | | | | ±0.1pF | GRM1882C2A9R1BA01# |
| | | | | ±0.25pF | GRM1882C2A9R1CA01# |
| | | | | ±0.5pF | GRM1882C2A9R1DA01# |
| | | | 9.2pF | ±0.05pF | GRM1882C2A9R2WA01# |
| | | | | ±0.1pF | GRM1882C2A9R2BA01# |
| | | | | ±0.25pF | GRM1882C2A9R2CA01# |
| | | | | ±0.5pF | GRM1882C2A9R2DA01# |
| | | | 9.3pF | ±0.05pF | GRM1882C2A9R3WA01# |
| | | | | ±0.1pF | GRM1882C2A9R3BA01# |
| | | | | ±0.25pF | GRM1882C2A9R3CA01# |
| | | | | ±0.5pF | GRM1882C2A9R3DA01# |
| | | | 9.4pF | ±0.05pF | GRM1882C2A9R4WA01# |
| | | | | ±0.1pF | GRM1882C2A9R4BA01# |
| | | | | ±0.25pF | GRM1882C2A9R4CA01# |
| | | | | ±0.5pF | GRM1882C2A9R4DA01# |
| | | | 9.5pF | ±0.05pF | GRM1882C2A9R5WA01# |
| | | | | ±0.1pF | GRM1882C2A9R5BA01# |
| | | | | ±0.25pF | GRM1882C2A9R5CA01# |
| | | | | ±0.5pF | GRM1882C2A9R5DA01# |
| | | | 9.6pF | ±0.05pF | GRM1882C2A9R6WA01# |
| | | | | ±0.1pF | GRM1882C2A9R6BA01# |
| | | | | ±0.25pF | GRM1882C2A9R6CA01# |
| | | | | ±0.5pF | GRM1882C2A9R6DA01# |
| | | | 9.7pF | ±0.05pF | GRM1882C2A9R7WA01# |
| | | | | ±0.1pF | GRM1882C2A9R7BA01# |
| | | | | ±0.25pF | GRM1882C2A9R7CA01# |
| 0.9mm | 100Vdc | CH | 9.7pF | ±0.5pF | GRM1882C2A9R7DA01# |
| | | | 9.8pF | ±0.05pF | GRM1882C2A9R8WA01# |
| | | | | ±0.1pF | GRM1882C2A9R8BA01# |
| | | | | ±0.25pF | GRM1882C2A9R8CA01# |
| | | | | ±0.5pF | GRM1882C2A9R8DA01# |
| | | | 9.9pF | ±0.05pF | GRM1882C2A9R9WA01# |
| | | | | ±0.1pF | GRM1882C2A9R9BA01# |
| | | | | ±0.25pF | GRM1882C2A9R9CA01# |
| | | | | ±0.5pF | GRM1882C2A9R9DA01# |
| | | | 10pF | ±5% | GRM1882C2A100JA01# |
| | | | 12pF | ±5% | GRM1882C2A120JA01# |
| | | | 15pF | ±5% | GRM1882C2A150JA01# |
| | | | 18pF | ±5% | GRM1882C2A180JA01# |
| | | | 22pF | ±5% | GRM1882C2A220JA01# |
| | | | 27pF | ±5% | GRM1882C2A270JA01# |
| | | | 33pF | ±5% | GRM1882C2A330JA01# |
| | | | 39pF | ±5% | GRM1882C2A390JA01# |
| | | | 47pF | ±5% | GRM1882C2A470JA01# |
| | | | 56pF | ±5% | GRM1882C2A560JA01# |
| | | | 68pF | ±5% | GRM1882C2A680JA01# |
| | | | 82pF | ±5% | GRM1882C2A820JA01# |
| | | | 100pF | ±5% | GRM1882C2A101JA01# |
| | | | 120pF | ±5% | GRM1882C2A121JA01# |
| | | | 150pF | ±5% | GRM1882C2A151JA01# |
| | | | 180pF | ±5% | GRM1882C2A181JA01# |
| | | | 220pF | ±5% | GRM1882C2A221JA01# |
| | | | 270pF | ±5% | GRM1882C2A271JA01# |
| | | | 330pF | ±5% | GRM1882C2A331JA01# |
| | | | 390pF | ±5% | GRM1882C2A391JA01# |
| | | | 470pF | ±5% | GRM1882C2A471JA01# |
| | | | 560pF | ±5% | GRM1882C2A561JA01# |
| | | | 680pF | ±5% | GRM1882C2A681JA01# |
| | | | 820pF | ±5% | GRM1882C2A821JA01# |
| | | | 1000pF | ±5% | GRM1882C2A102JA01# |
| | | | 1200pF | ±5% | GRM1882C2A122JA01# |
| | | | 1500pF | ±5% | GRM1882C2A152JA01# |
| | 50Vdc | C0G | 0.50pF | ±0.05pF | GRM1885C1HR50WA01# |
| | | | | ±0.1pF | GRM1885C1HR50BA01# |
| | | | 0.60pF | ±0.05pF | GRM1885C1HR60WA01# |
| | | | | ±0.1pF | GRM1885C1HR60BA01# |
| | | | 0.70pF | ±0.05pF | GRM1885C1HR70WA01# |
| | | | | ±0.1pF | GRM1885C1HR70BA01# |
| | | | 0.80pF | ±0.05pF | GRM1885C1HR80WA01# |
| | | | | ±0.1pF | GRM1885C1HR80BA01# |
| | | | 0.90pF | ±0.05pF | GRM1885C1HR90WA01# |
| | | | | ±0.1pF | GRM1885C1HR90BA01# |
| | | | 1.0pF | ±0.05pF | GRM1885C1H1R0WA01# |
| | | | | ±0.1pF | GRM1885C1H1R0BA01# |
| | | | | ±0.25pF | GRM1885C1H1R0CA01# |
| | | | 1.1pF | ±0.05pF | GRM1885C1H1R1WA01# |
| | | | | ±0.1pF | GRM1885C1H1R1BA01# |
| | | | | ±0.25pF | GRM1885C1H1R1CA01# |
| | | | 1.2pF | ±0.05pF | GRM1885C1H1R2WA01# |
| | | | | ±0.1pF | GRM1885C1H1R2BA01# |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 1.2pF | ±0.25pF | **GRM1885C1H1R2CA01#** | |
| | | | 1.3pF | ±0.05pF | **GRM1885C1H1R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R3CA01#** | |
| | | | 1.4pF | ±0.05pF | **GRM1885C1H1R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R4CA01#** | |
| | | | 1.5pF | ±0.05pF | **GRM1885C1H1R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R5CA01#** | |
| | | | 1.6pF | ±0.05pF | **GRM1885C1H1R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R6CA01#** | |
| | | | 1.7pF | ±0.05pF | **GRM1885C1H1R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R7CA01#** | |
| | | | 1.8pF | ±0.05pF | **GRM1885C1H1R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R8BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R8CA01#** | |
| | | | 1.9pF | ±0.05pF | **GRM1885C1H1R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H1R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H1R9CA01#** | |
| | | | 2.0pF | ±0.05pF | **GRM1885C1H2R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R0BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R0CA01#** | |
| | | | 2.1pF | ±0.05pF | **GRM1885C1H2R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R1CA01#** | |
| | | | 2.2pF | ±0.05pF | **GRM1885C1H2R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R2CA01#** | |
| | | | 2.3pF | ±0.05pF | **GRM1885C1H2R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R3CA01#** | |
| | | | 2.4pF | ±0.05pF | **GRM1885C1H2R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R4CA01#** | |
| | | | 2.5pF | ±0.05pF | **GRM1885C1H2R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R5CA01#** | |
| | | | 2.6pF | ±0.05pF | **GRM1885C1H2R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R6CA01#** | |
| | | | 2.7pF | ±0.05pF | **GRM1885C1H2R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R7CA01#** | |
| | | | 2.8pF | ±0.05pF | **GRM1885C1H2R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R8BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R8CA01#** | |
| | | | 2.9pF | ±0.05pF | **GRM1885C1H2R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H2R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H2R9CA01#** | |
| | | | 3.0pF | ±0.05pF | **GRM1885C1H3R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R0BA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 3.0pF | ±0.25pF | **GRM1885C1H3R0CA01#** | |
| | | | 3.1pF | ±0.05pF | **GRM1885C1H3R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R1CA01#** | |
| | | | 3.2pF | ±0.05pF | **GRM1885C1H3R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R2CA01#** | |
| | | | 3.3pF | ±0.05pF | **GRM1885C1H3R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R3CA01#** | |
| | | | 3.4pF | ±0.05pF | **GRM1885C1H3R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R4CA01#** | |
| | | | 3.5pF | ±0.05pF | **GRM1885C1H3R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R5CA01#** | |
| | | | 3.6pF | ±0.05pF | **GRM1885C1H3R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R6CA01#** | |
| | | | 3.7pF | ±0.05pF | **GRM1885C1H3R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R7CA01#** | |
| | | | 3.8pF | ±0.05pF | **GRM1885C1H3R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R8BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R8CA01#** | |
| | | | 3.9pF | ±0.05pF | **GRM1885C1H3R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H3R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H3R9CA01#** | |
| | | | 4.0pF | ±0.05pF | **GRM1885C1H4R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R0BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R0CA01#** | |
| | | | 4.1pF | ±0.05pF | **GRM1885C1H4R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R1CA01#** | |
| | | | 4.2pF | ±0.05pF | **GRM1885C1H4R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R2CA01#** | |
| | | | 4.3pF | ±0.05pF | **GRM1885C1H4R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R3CA01#** | |
| | | | 4.4pF | ±0.05pF | **GRM1885C1H4R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R4CA01#** | |
| | | | 4.5pF | ±0.05pF | **GRM1885C1H4R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R5CA01#** | |
| | | | 4.6pF | ±0.05pF | **GRM1885C1H4R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R6CA01#** | |
| | | | 4.7pF | ±0.05pF | **GRM1885C1H4R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R7CA01#** | |
| | | | 4.8pF | ±0.05pF | **GRM1885C1H4R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R8BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 4.8pF | ±0.25pF | **GRM1885C1H4R8CA01#** | |
| | | | 4.9pF | ±0.05pF | **GRM1885C1H4R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H4R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H4R9CA01#** | |
| | | | 5.0pF | ±0.05pF | **GRM1885C1H5R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R0BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R0CA01#** | |
| | | | 5.1pF | ±0.05pF | **GRM1885C1H5R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R1CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R1DA01#** | |
| | | | 5.2pF | ±0.05pF | **GRM1885C1H5R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R2CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R2DA01#** | |
| | | | 5.3pF | ±0.05pF | **GRM1885C1H5R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R3CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R3DA01#** | |
| | | | 5.4pF | ±0.05pF | **GRM1885C1H5R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R4CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R4DA01#** | |
| | | | 5.5pF | ±0.05pF | **GRM1885C1H5R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R5CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R5DA01#** | |
| | | | 5.6pF | ±0.05pF | **GRM1885C1H5R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R6CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R6DA01#** | |
| | | | 5.7pF | ±0.05pF | **GRM1885C1H5R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R7CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM1885C1H5R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R8BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R8CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM1885C1H5R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H5R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H5R9CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H5R9DA01#** | |
| | | | 6.0pF | ±0.05pF | **GRM1885C1H6R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R0BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R0CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM1885C1H6R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R1CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM1885C1H6R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R2CA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 6.2pF | ±0.5pF | **GRM1885C1H6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM1885C1H6R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R3CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM1885C1H6R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R4CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM1885C1H6R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R5CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM1885C1H6R6WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R6BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R6CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM1885C1H6R7WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R7BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R7CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM1885C1H6R8WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R8BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R8CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM1885C1H6R9WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H6R9BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H6R9CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM1885C1H7R0WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R0BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R0CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM1885C1H7R1WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R1BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R1CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM1885C1H7R2WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R2BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R2CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM1885C1H7R3WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R3BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R3CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM1885C1H7R4WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R4BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R4CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM1885C1H7R5WA01#** | |
| | | | | ±0.1pF | **GRM1885C1H7R5BA01#** | |
| | | | | ±0.25pF | **GRM1885C1H7R5CA01#** | |
| | | | | ±0.5pF | **GRM1885C1H7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM1885C1H7R6WA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 7.6pF | ±0.1pF | GRM1885C1H7R6BA01# | |
| | | | | ±0.25pF | GRM1885C1H7R6CA01# | |
| | | | | ±0.5pF | GRM1885C1H7R6DA01# | |
| | | | 7.7pF | ±0.05pF | GRM1885C1H7R7WA01# | |
| | | | | ±0.1pF | GRM1885C1H7R7BA01# | |
| | | | | ±0.25pF | GRM1885C1H7R7CA01# | |
| | | | | ±0.5pF | GRM1885C1H7R7DA01# | |
| | | | 7.8pF | ±0.05pF | GRM1885C1H7R8WA01# | |
| | | | | ±0.1pF | GRM1885C1H7R8BA01# | |
| | | | | ±0.25pF | GRM1885C1H7R8CA01# | |
| | | | | ±0.5pF | GRM1885C1H7R8DA01# | |
| | | | 7.9pF | ±0.05pF | GRM1885C1H7R9WA01# | |
| | | | | ±0.1pF | GRM1885C1H7R9BA01# | |
| | | | | ±0.25pF | GRM1885C1H7R9CA01# | |
| | | | | ±0.5pF | GRM1885C1H7R9DA01# | |
| | | | 8.0pF | ±0.05pF | GRM1885C1H8R0WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R0BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R0CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R0DA01# | |
| | | | 8.1pF | ±0.05pF | GRM1885C1H8R1WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R1BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R1CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R1DA01# | |
| | | | 8.2pF | ±0.05pF | GRM1885C1H8R2WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R2BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R2CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R2DA01# | |
| | | | 8.3pF | ±0.05pF | GRM1885C1H8R3WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R3BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R3CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R3DA01# | |
| | | | 8.4pF | ±0.05pF | GRM1885C1H8R4WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R4BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R4CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R4DA01# | |
| | | | 8.5pF | ±0.05pF | GRM1885C1H8R5WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R5BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R5CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R5DA01# | |
| | | | 8.6pF | ±0.05pF | GRM1885C1H8R6WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R6BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R6CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R6DA01# | |
| | | | 8.7pF | ±0.05pF | GRM1885C1H8R7WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R7BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R7CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R7DA01# | |
| | | | 8.8pF | ±0.05pF | GRM1885C1H8R8WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R8BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R8CA01# | |
| | | | | ±0.5pF | GRM1885C1H8R8DA01# | |
| | | | 8.9pF | ±0.05pF | GRM1885C1H8R9WA01# | |
| | | | | ±0.1pF | GRM1885C1H8R9BA01# | |
| | | | | ±0.25pF | GRM1885C1H8R9CA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 8.9pF | ±0.5pF | GRM1885C1H8R9DA01# | |
| | | | 9.0pF | ±0.05pF | GRM1885C1H9R0WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R0BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R0CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R0DA01# | |
| | | | 9.1pF | ±0.05pF | GRM1885C1H9R1WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R1BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R1CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R1DA01# | |
| | | | 9.2pF | ±0.05pF | GRM1885C1H9R2WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R2BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R2CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R2DA01# | |
| | | | 9.3pF | ±0.05pF | GRM1885C1H9R3WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R3BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R3CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R3DA01# | |
| | | | 9.4pF | ±0.05pF | GRM1885C1H9R4WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R4BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R4CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R4DA01# | |
| | | | 9.5pF | ±0.05pF | GRM1885C1H9R5WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R5BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R5CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R5DA01# | |
| | | | 9.6pF | ±0.05pF | GRM1885C1H9R6WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R6BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R6CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R6DA01# | |
| | | | 9.7pF | ±0.05pF | GRM1885C1H9R7WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R7BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R7CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R7DA01# | |
| | | | 9.8pF | ±0.05pF | GRM1885C1H9R8WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R8BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R8CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R8DA01# | |
| | | | 9.9pF | ±0.05pF | GRM1885C1H9R9WA01# | |
| | | | | ±0.1pF | GRM1885C1H9R9BA01# | |
| | | | | ±0.25pF | GRM1885C1H9R9CA01# | |
| | | | | ±0.5pF | GRM1885C1H9R9DA01# | |
| | | | 10pF | ±5% | GRM1885C1H100JA01# | |
| | | | 12pF | ±5% | GRM1885C1H120JA01# | |
| | | | 15pF | ±5% | GRM1885C1H150JA01# | |
| | | | 18pF | ±5% | GRM1885C1H180JA01# | |
| | | | 22pF | ±5% | GRM1885C1H220JA01# | |
| | | | 27pF | ±5% | GRM1885C1H270JA01# | |
| | | | 33pF | ±5% | GRM1885C1H330JA01# | |
| | | | 39pF | ±5% | GRM1885C1H390JA01# | |
| | | | 47pF | ±5% | GRM1885C1H470JA01# | |
| | | | 56pF | ±5% | GRM1885C1H560JA01# | |
| | | | 68pF | ±5% | GRM1885C1H680JA01# | |
| | | | 82pF | ±5% | GRM1885C1H820JA01# | |
| | | | 100pF | ±5% | GRM1885C1H101JA01# | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 120pF | ±5% | **GRM1885C1H121JA01#** | |
| | | | 150pF | ±5% | **GRM1885C1H151JA01#** | |
| | | | 180pF | ±5% | **GRM1885C1H181JA01#** | |
| | | | 220pF | ±5% | **GRM1885C1H221JA01#** | |
| | | | 270pF | ±5% | **GRM1885C1H271JA01#** | |
| | | | 330pF | ±5% | **GRM1885C1H331JA01#** | |
| | | | 390pF | ±5% | **GRM1885C1H391JA01#** | |
| | | | 470pF | ±5% | **GRM1885C1H471JA01#** | |
| | | | 560pF | ±5% | **GRM1885C1H561JA01#** | |
| | | | 680pF | ±5% | **GRM1885C1H681JA01#** | |
| | | | 820pF | ±5% | **GRM1885C1H821JA01#** | |
| | | | 1000pF | ±5% | **GRM1885C1H102JA01#** | |
| | | | 1200pF | ±5% | **GRM1885C1H122JA01#** | |
| | | | 1500pF | ±5% | **GRM1885C1H152JA01#** | |
| | | | 1800pF | ±5% | **GRM1885C1H182JA01#** | |
| | | | 2200pF | ±5% | **GRM1885C1H222JA01#** | |
| | | | 2700pF | ±5% | **GRM1885C1H272JA01#** | |
| | | | 3300pF | ±5% | **GRM1885C1H332JA01#** | |
| | | | 3900pF | ±5% | **GRM1885C1H392JA01#** | |
| | | | 4700pF | ±5% | **GRM1885C1H472JA01#** | |
| | | | 5600pF | ±5% | **GRM1885C1H562JA01#** | |
| | | | 6800pF | ±5% | **GRM1885C1H682JA01#** | |
| | | | 8200pF | ±5% | **GRM1885C1H822JA01#** | |
| | | | 10000pF | ±5% | **GRM1885C1H103JA01#** | |
| | | CK | 0.50pF | ±0.05pF | **GRM1884C1HR50WA01#** | |
| | | | | ±0.1pF | **GRM1884C1HR50BA01#** | |
| | | | 0.60pF | ±0.05pF | **GRM1884C1HR60WA01#** | |
| | | | | ±0.1pF | **GRM1884C1HR60BA01#** | |
| | | | 0.70pF | ±0.05pF | **GRM1884C1HR70WA01#** | |
| | | | | ±0.1pF | **GRM1884C1HR70BA01#** | |
| | | | 0.80pF | ±0.05pF | **GRM1884C1HR80WA01#** | |
| | | | | ±0.1pF | **GRM1884C1HR80BA01#** | |
| | | | 0.90pF | ±0.05pF | **GRM1884C1HR90WA01#** | |
| | | | | ±0.1pF | **GRM1884C1HR90BA01#** | |
| | | | 1.0pF | ±0.05pF | **GRM1884C1H1R0WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R0BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R0CA01#** | |
| | | | 1.1pF | ±0.05pF | **GRM1884C1H1R1WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R1BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R1CA01#** | |
| | | | 1.2pF | ±0.05pF | **GRM1884C1H1R2WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R2BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R2CA01#** | |
| | | | 1.3pF | ±0.05pF | **GRM1884C1H1R3WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R3BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R3CA01#** | |
| | | | 1.4pF | ±0.05pF | **GRM1884C1H1R4WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R4BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R4CA01#** | |
| | | | 1.5pF | ±0.05pF | **GRM1884C1H1R5WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R5BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R5CA01#** | |
| | | | 1.6pF | ±0.05pF | **GRM1884C1H1R6WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R6BA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CK | 1.6pF | ±0.25pF | **GRM1884C1H1R6CA01#** | |
| | | | 1.7pF | ±0.05pF | **GRM1884C1H1R7WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R7BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R7CA01#** | |
| | | | 1.8pF | ±0.05pF | **GRM1884C1H1R8WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R8BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R8CA01#** | |
| | | | 1.9pF | ±0.05pF | **GRM1884C1H1R9WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H1R9BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H1R9CA01#** | |
| | | | 2.0pF | ±0.05pF | **GRM1884C1H2R0WA01#** | |
| | | | | ±0.1pF | **GRM1884C1H2R0BA01#** | |
| | | | | ±0.25pF | **GRM1884C1H2R0CA01#** | |
| | | CJ | 2.1pF | ±0.05pF | **GRM1883C1H2R1WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R1BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R1CA01#** | |
| | | | 2.2pF | ±0.05pF | **GRM1883C1H2R2WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R2BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R2CA01#** | |
| | | | 2.3pF | ±0.05pF | **GRM1883C1H2R3WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R3BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R3CA01#** | |
| | | | 2.4pF | ±0.05pF | **GRM1883C1H2R4WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R4BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R4CA01#** | |
| | | | 2.5pF | ±0.05pF | **GRM1883C1H2R5WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R5BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R5CA01#** | |
| | | | 2.6pF | ±0.05pF | **GRM1883C1H2R6WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R6BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R6CA01#** | |
| | | | 2.7pF | ±0.05pF | **GRM1883C1H2R7WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R7BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R7CA01#** | |
| | | | 2.8pF | ±0.05pF | **GRM1883C1H2R8WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R8BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R8CA01#** | |
| | | | 2.9pF | ±0.05pF | **GRM1883C1H2R9WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H2R9BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H2R9CA01#** | |
| | | | 3.0pF | ±0.05pF | **GRM1883C1H3R0WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R0BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R0CA01#** | |
| | | | 3.1pF | ±0.05pF | **GRM1883C1H3R1WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R1BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R1CA01#** | |
| | | | 3.2pF | ±0.05pF | **GRM1883C1H3R2WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R2BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R2CA01#** | |
| | | | 3.3pF | ±0.05pF | **GRM1883C1H3R3WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R3BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R3CA01#** | |
| | | | 3.4pF | ±0.05pF | **GRM1883C1H3R4WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R4BA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CJ | 3.4pF | ±0.25pF | **GRM1883C1H3R4CA01#** | |
| | | | 3.5pF | ±0.05pF | **GRM1883C1H3R5WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R5BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R5CA01#** | |
| | | | 3.6pF | ±0.05pF | **GRM1883C1H3R6WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R6BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R6CA01#** | |
| | | | 3.7pF | ±0.05pF | **GRM1883C1H3R7WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R7BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R7CA01#** | |
| | | | 3.8pF | ±0.05pF | **GRM1883C1H3R8WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R8BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R8CA01#** | |
| | | | 3.9pF | ±0.05pF | **GRM1883C1H3R9WA01#** | |
| | | | | ±0.1pF | **GRM1883C1H3R9BA01#** | |
| | | | | ±0.25pF | **GRM1883C1H3R9CA01#** | |
| | | CH | 4.0pF | ±0.05pF | **GRM1882C1H4R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R0CA01#** | |
| | | | 4.1pF | ±0.05pF | **GRM1882C1H4R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R1CA01#** | |
| | | | 4.2pF | ±0.05pF | **GRM1882C1H4R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R2CA01#** | |
| | | | 4.3pF | ±0.05pF | **GRM1882C1H4R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R3CA01#** | |
| | | | 4.4pF | ±0.05pF | **GRM1882C1H4R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R4CA01#** | |
| | | | 4.5pF | ±0.05pF | **GRM1882C1H4R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R5CA01#** | |
| | | | 4.6pF | ±0.05pF | **GRM1882C1H4R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R6CA01#** | |
| | | | 4.7pF | ±0.05pF | **GRM1882C1H4R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R7CA01#** | |
| | | | 4.8pF | ±0.05pF | **GRM1882C1H4R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R8CA01#** | |
| | | | 4.9pF | ±0.05pF | **GRM1882C1H4R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H4R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H4R9CA01#** | |
| | | | 5.0pF | ±0.05pF | **GRM1882C1H5R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R0CA01#** | |
| | | | 5.1pF | ±0.05pF | **GRM1882C1H5R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R1DA01#** | |
| | | | 5.2pF | ±0.05pF | **GRM1882C1H5R2WA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CH | 5.2pF | ±0.1pF | **GRM1882C1H5R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R2DA01#** | |
| | | | 5.3pF | ±0.05pF | **GRM1882C1H5R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R3DA01#** | |
| | | | 5.4pF | ±0.05pF | **GRM1882C1H5R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R4DA01#** | |
| | | | 5.5pF | ±0.05pF | **GRM1882C1H5R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R5CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R5DA01#** | |
| | | | 5.6pF | ±0.05pF | **GRM1882C1H5R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R6DA01#** | |
| | | | 5.7pF | ±0.05pF | **GRM1882C1H5R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R7DA01#** | |
| | | | 5.8pF | ±0.05pF | **GRM1882C1H5R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R8DA01#** | |
| | | | 5.9pF | ±0.05pF | **GRM1882C1H5R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H5R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H5R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H5R9DA01#** | |
| | | | 6.0pF | ±0.05pF | **GRM1882C1H6R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R0DA01#** | |
| | | | 6.1pF | ±0.05pF | **GRM1882C1H6R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R1DA01#** | |
| | | | 6.2pF | ±0.05pF | **GRM1882C1H6R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R2DA01#** | |
| | | | 6.3pF | ±0.05pF | **GRM1882C1H6R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R3DA01#** | |
| | | | 6.4pF | ±0.05pF | **GRM1882C1H6R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R4DA01#** | |
| | | | 6.5pF | ±0.05pF | **GRM1882C1H6R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R5CA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CH | 6.5pF | ±0.5pF | **GRM1882C1H6R5DA01#** | |
| | | | 6.6pF | ±0.05pF | **GRM1882C1H6R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R6DA01#** | |
| | | | 6.7pF | ±0.05pF | **GRM1882C1H6R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R7DA01#** | |
| | | | 6.8pF | ±0.05pF | **GRM1882C1H6R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R8DA01#** | |
| | | | 6.9pF | ±0.05pF | **GRM1882C1H6R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H6R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H6R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H6R9DA01#** | |
| | | | 7.0pF | ±0.05pF | **GRM1882C1H7R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R0DA01#** | |
| | | | 7.1pF | ±0.05pF | **GRM1882C1H7R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R1DA01#** | |
| | | | 7.2pF | ±0.05pF | **GRM1882C1H7R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R2DA01#** | |
| | | | 7.3pF | ±0.05pF | **GRM1882C1H7R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R3DA01#** | |
| | | | 7.4pF | ±0.05pF | **GRM1882C1H7R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R4DA01#** | |
| | | | 7.5pF | ±0.05pF | **GRM1882C1H7R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R5CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R5DA01#** | |
| | | | 7.6pF | ±0.05pF | **GRM1882C1H7R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R6DA01#** | |
| | | | 7.7pF | ±0.05pF | **GRM1882C1H7R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R7DA01#** | |
| | | | 7.8pF | ±0.05pF | **GRM1882C1H7R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R8DA01#** | |
| | | | 7.9pF | ±0.05pF | **GRM1882C1H7R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H7R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H7R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H7R9DA01#** | |
| | | | 8.0pF | ±0.05pF | **GRM1882C1H8R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R0DA01#** | |
| | | | 8.1pF | ±0.05pF | **GRM1882C1H8R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R1DA01#** | |
| | | | 8.2pF | ±0.05pF | **GRM1882C1H8R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R2CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R2DA01#** | |
| | | | 8.3pF | ±0.05pF | **GRM1882C1H8R3WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R3BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R3CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R3DA01#** | |
| | | | 8.4pF | ±0.05pF | **GRM1882C1H8R4WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R4BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R4CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R4DA01#** | |
| | | | 8.5pF | ±0.05pF | **GRM1882C1H8R5WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R5BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R5CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R5DA01#** | |
| | | | 8.6pF | ±0.05pF | **GRM1882C1H8R6WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R6BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R6CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R6DA01#** | |
| | | | 8.7pF | ±0.05pF | **GRM1882C1H8R7WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R7BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R7CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R7DA01#** | |
| | | | 8.8pF | ±0.05pF | **GRM1882C1H8R8WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R8BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R8CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R8DA01#** | |
| | | | 8.9pF | ±0.05pF | **GRM1882C1H8R9WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H8R9BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H8R9CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H8R9DA01#** | |
| | | | 9.0pF | ±0.05pF | **GRM1882C1H9R0WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H9R0BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H9R0CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H9R0DA01#** | |
| | | | 9.1pF | ±0.05pF | **GRM1882C1H9R1WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H9R1BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H9R1CA01#** | |
| | | | | ±0.5pF | **GRM1882C1H9R1DA01#** | |
| | | | 9.2pF | ±0.05pF | **GRM1882C1H9R2WA01#** | |
| | | | | ±0.1pF | **GRM1882C1H9R2BA01#** | |
| | | | | ±0.25pF | **GRM1882C1H9R2CA01#** | |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CH | 9.2pF | ±0.5pF | **GRM1882C1H9R2DA01#** |
| | | | 9.3pF | ±0.05pF | **GRM1882C1H9R3WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R3BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R3CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R3DA01#** |
| | | | 9.4pF | ±0.05pF | **GRM1882C1H9R4WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R4BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R4CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R4DA01#** |
| | | | 9.5pF | ±0.05pF | **GRM1882C1H9R5WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R5BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R5CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R5DA01#** |
| | | | 9.6pF | ±0.05pF | **GRM1882C1H9R6WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R6BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R6CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R6DA01#** |
| | | | 9.7pF | ±0.05pF | **GRM1882C1H9R7WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R7BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R7CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R7DA01#** |
| | | | 9.8pF | ±0.05pF | **GRM1882C1H9R8WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R8BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R8CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R8DA01#** |
| | | | 9.9pF | ±0.05pF | **GRM1882C1H9R9WA01#** |
| | | | | ±0.1pF | **GRM1882C1H9R9BA01#** |
| | | | | ±0.25pF | **GRM1882C1H9R9CA01#** |
| | | | | ±0.5pF | **GRM1882C1H9R9DA01#** |
| | | | 10pF | ±5% | **GRM1882C1H100JA01#** |
| | | | 12pF | ±5% | **GRM1882C1H120JA01#** |
| | | | 15pF | ±5% | **GRM1882C1H150JA01#** |
| | | | 18pF | ±5% | **GRM1882C1H180JA01#** |
| | | | 22pF | ±5% | **GRM1882C1H220JA01#** |
| | | | 27pF | ±5% | **GRM1882C1H270JA01#** |
| | | | 33pF | ±5% | **GRM1882C1H330JA01#** |
| | | | 39pF | ±5% | **GRM1882C1H390JA01#** |
| | | | 47pF | ±5% | **GRM1882C1H470JA01#** |
| | | | 56pF | ±5% | **GRM1882C1H560JA01#** |
| | | | 68pF | ±5% | **GRM1882C1H680JA01#** |
| | | | 82pF | ±5% | **GRM1882C1H820JA01#** |
| | | | 100pF | ±5% | **GRM1882C1H101JA01#** |
| | | | 120pF | ±5% | **GRM1882C1H121JA01#** |
| | | | 150pF | ±5% | **GRM1882C1H151JA01#** |
| | | | 180pF | ±5% | **GRM1882C1H181JA01#** |
| | | | 220pF | ±5% | **GRM1882C1H221JA01#** |
| | | | 270pF | ±5% | **GRM1882C1H271JA01#** |
| | | | 330pF | ±5% | **GRM1882C1H331JA01#** |
| | | | 390pF | ±5% | **GRM1882C1H391JA01#** |
| | | | 470pF | ±5% | **GRM1882C1H471JA01#** |
| | | | 560pF | ±5% | **GRM1882C1H561JA01#** |
| | | | 680pF | ±5% | **GRM1882C1H681JA01#** |
| | | | 820pF | ±5% | **GRM1882C1H821JA01#** |
| | | | 1000pF | ±5% | **GRM1882C1H102JA01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CH | 1200pF | ±5% | **GRM1882C1H122JA01#** |
| | | | 1500pF | ±5% | **GRM1882C1H152JA01#** |
| | | | 1800pF | ±5% | **GRM1882C1H182JA01#** |
| | | | 2200pF | ±5% | **GRM1882C1H222JA01#** |
| | | | 2700pF | ±5% | **GRM1882C1H272JA01#** |
| | | | 3300pF | ±5% | **GRM1882C1H332JA01#** |
| | | | 3900pF | ±5% | **GRM1882C1H392JA01#** |
| | | | 4700pF | ±5% | **GRM1882C1H472JA01#** |
| | | | 5600pF | ±5% | **GRM1882C1H562JA01#** |
| | | | 6800pF | ±5% | **GRM1882C1H682JA01#** |
| | | | 8200pF | ±5% | **GRM1882C1H822JA01#** |
| | | | 10000pF | ±5% | **GRM1882C1H103JA01#** |
| | | SL | 1200pF | ±5% | **GRM1881X1H122JA01#** |
| | | | 1500pF | ±5% | **GRM1881X1H152JA01#** |
| | | | 1800pF | ±5% | **GRM1881X1H182JA01#** |
| | | | 2200pF | ±5% | **GRM1881X1H222JA01#** |
| | | | 2700pF | ±5% | **GRM1881X1H272JA01#** |
| | | | 3300pF | ±5% | **GRM1881X1H332JA01#** |
| | | | 3900pF | ±5% | **GRM1881X1H392JA01#** |
| | | | 4700pF | ±5% | **GRM1881X1H472JA01#** |
| | | | 5600pF | ±5% | **GRM1881X1H562JA01#** |
| | | | 6800pF | ±5% | **GRM1881X1H682JA01#** |
| | | | 8200pF | ±5% | **GRM1881X1H822JA01#** |
| | | | 10000pF | ±5% | **GRM1881X1H103JA01#** |
| | | U2J | 1200pF | ±5% | **GRM1887U1H122JA01#** |
| | | | 1500pF | ±5% | **GRM1887U1H152JA01#** |
| | | | 1800pF | ±5% | **GRM1887U1H182JA01#** |
| | | | 2200pF | ±5% | **GRM1887U1H222JA01#** |
| | | | 2700pF | ±5% | **GRM1887U1H272JA01#** |
| | | | 3300pF | ±5% | **GRM1887U1H332JA01#** |
| | | | 3900pF | ±5% | **GRM1887U1H392JA01#** |
| | | | 4700pF | ±5% | **GRM1887U1H472JA01#** |
| | | | 5600pF | ±5% | **GRM1887U1H562JA01#** |
| | | | 6800pF | ±5% | **GRM1887U1H682JA01#** |
| | | | 8200pF | ±5% | **GRM1887U1H822JA01#** |
| | | | 10000pF | ±5% | **GRM1887U1H103JA01#** |
| | | UJ | 1000pF | ±5% | **GRM1883U1H102JA01#** |
| | | | 1200pF | ±5% | **GRM1883U1H122JA01#** |
| | | | 1500pF | ±5% | **GRM1883U1H152JA01#** |
| | | | 1800pF | ±5% | **GRM1883U1H182JA01#** |
| | | | 2200pF | ±5% | **GRM1883U1H222JA01#** |
| | | | 2700pF | ±5% | **GRM1883U1H272JA01#** |
| | | | 3300pF | ±5% | **GRM1883U1H332JA01#** |
| | | | 3900pF | ±5% | **GRM1883U1H392JA01#** |
| | | | 4700pF | ±5% | **GRM1883U1H472JA01#** |
| | | | 5600pF | ±5% | **GRM1883U1H562JA01#** |
| | | | 6800pF | ±5% | **GRM1883U1H682JA01#** |
| | | | 8200pF | ±5% | **GRM1883U1H822JA01#** |
| | | | 10000pF | ±5% | **GRM1883U1H103JA01#** |
| | 10Vdc | SL | 12000pF | ±5% | **GRM1881X1A123JA01#** |
| | | | 15000pF | ±5% | **GRM1881X1A153JA01#** |
| | | | 18000pF | ±5% | **GRM1881X1A183JA01#** |
| | | | 22000pF | ±5% | **GRM1881X1A223JA01#** |
| | | U2J | 12000pF | ±5% | **GRM1887U1A123JA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 10Vdc | U2J | 15000pF | ±5% | **GRM1887U1A153JA01#** |
| | | | 18000pF | ±5% | **GRM1887U1A183JA01#** |
| | | | 22000pF | ±5% | **GRM1887U1A223JA01#** |
| | | UJ | 12000pF | ±5% | **GRM1883U1A123JA01#** |
| | | | 15000pF | ±5% | **GRM1883U1A153JA01#** |
| | | | 18000pF | ±5% | **GRM1883U1A183JA01#** |
| | | | 22000pF | ±5% | **GRM1883U1A223JA01#** |

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.7mm | 100Vdc | C0G | 100pF | ±5% | **GRM2165C2A101JA01#** |
| | | | 120pF | ±5% | **GRM2165C2A121JA01#** |
| | | | 150pF | ±5% | **GRM2165C2A151JA01#** |
| | | | 180pF | ±5% | **GRM2165C2A181JA01#** |
| | | | 220pF | ±5% | **GRM2165C2A221JA01#** |
| | | | 270pF | ±5% | **GRM2165C2A271JA01#** |
| | | | 330pF | ±5% | **GRM2165C2A331JA01#** |
| | | | 390pF | ±5% | **GRM2165C2A391JA01#** |
| | | | 470pF | ±5% | **GRM2165C2A471JA01#** |
| | | | 560pF | ±5% | **GRM2165C2A561JA01#** |
| | | | 680pF | ±5% | **GRM2165C2A681JA01#** |
| | | | 820pF | ±5% | **GRM2165C2A821JA01#** |
| | | | 1000pF | ±5% | **GRM2165C2A102JA01#** |
| | | | 1200pF | ±5% | **GRM2165C2A122JA01#** |
| | | | 1500pF | ±5% | **GRM2165C2A152JA01#** |
| | | | 1800pF | ±5% | **GRM2165C2A182JA01#** |
| | | | 2200pF | ±5% | **GRM2165C2A222JA01#** |
| | | | 2700pF | ±5% | **GRM2165C2A272JA01#** |
| | | | 3300pF | ±5% | **GRM2165C2A332JA01#** |
| | | CH | 100pF | ±5% | **GRM2162C2A101JA01#** |
| | | | 120pF | ±5% | **GRM2162C2A121JA01#** |
| | | | 150pF | ±5% | **GRM2162C2A151JA01#** |
| | | | 180pF | ±5% | **GRM2162C2A181JA01#** |
| | | | 220pF | ±5% | **GRM2162C2A221JA01#** |
| | | | 270pF | ±5% | **GRM2162C2A271JA01#** |
| | | | 330pF | ±5% | **GRM2162C2A331JA01#** |
| | | | 390pF | ±5% | **GRM2162C2A391JA01#** |
| | | | 470pF | ±5% | **GRM2162C2A471JA01#** |
| | | | 560pF | ±5% | **GRM2162C2A561JA01#** |
| | | | 680pF | ±5% | **GRM2162C2A681JA01#** |
| | | | 820pF | ±5% | **GRM2162C2A821JA01#** |
| | | | 1000pF | ±5% | **GRM2162C2A102JA01#** |
| | | | 1200pF | ±5% | **GRM2162C2A122JA01#** |
| | | | 1500pF | ±5% | **GRM2162C2A152JA01#** |
| | | | 1800pF | ±5% | **GRM2162C2A182JA01#** |
| | | | 2200pF | ±5% | **GRM2162C2A222JA01#** |
| | | | 2700pF | ±5% | **GRM2162C2A272JA01#** |
| | | | 3300pF | ±5% | **GRM2162C2A332JA01#** |
| | 50Vdc | C0G | 1200pF | ±5% | **GRM2165C1H122JA01#** |
| | | | 1500pF | ±5% | **GRM2165C1H152JA01#** |
| | | | 1800pF | ±5% | **GRM2165C1H182JA01#** |
| | | | 2200pF | ±5% | **GRM2165C1H222JA01#** |
| 0.7mm | 50Vdc | C0G | 2700pF | ±5% | **GRM2165C1H272JA01#** |
| | | | 3300pF | ±5% | **GRM2165C1H332JA01#** |
| | | | 3900pF | ±5% | **GRM2165C1H392JA01#** |
| | | | 4700pF | ±5% | **GRM2165C1H472JA01#** |
| | | CH | 1200pF | ±5% | **GRM2162C1H122JA01#** |
| | | | 1500pF | ±5% | **GRM2162C1H152JA01#** |
| | | | 1800pF | ±5% | **GRM2162C1H182JA01#** |
| | | | 2200pF | ±5% | **GRM2162C1H222JA01#** |
| | | | 2700pF | ±5% | **GRM2162C1H272JA01#** |
| | | | 3300pF | ±5% | **GRM2162C1H332JA01#** |
| | | | 3900pF | ±5% | **GRM2162C1H392JA01#** |
| | | | 4700pF | ±5% | **GRM2162C1H472JA01#** |
| | | SL | 12000pF | ±5% | **GRM2161X1H123JA01#** |
| | | | 15000pF | ±5% | **GRM2161X1H153JA01#** |
| | | | 18000pF | ±5% | **GRM2161X1H183JA01#** |
| | | U2J | 12000pF | ±5% | **GRM2167U1H123JA01#** |
| | | | 15000pF | ±5% | **GRM2167U1H153JA01#** |
| | | | 18000pF | ±5% | **GRM2167U1H183JA01#** |
| | | UJ | 10000pF | ±5% | **GRM2163U1H103JA01#** |
| | | | 12000pF | ±5% | **GRM2163U1H123JA01#** |
| | | | 15000pF | ±5% | **GRM2163U1H153JA01#** |
| | | | 18000pF | ±5% | **GRM2163U1H183JA01#** |
| 0.95mm | 50Vdc | C0G | 5600pF | ±5% | **GRM2195C1H562JA01#** |
| | | | 6800pF | ±5% | **GRM2195C1H682JA01#** |
| | | | 8200pF | ±5% | **GRM2195C1H822JA01#** |
| | | | 10000pF | ±5% | **GRM2195C1H103JA01#** |
| | | | 12000pF | ±5% | **GRM2195C1H123JA01#** |
| | | | 15000pF | ±5% | **GRM2195C1H153JA01#** |
| | | CH | 5600pF | ±5% | **GRM2192C1H562JA01#** |
| | | | 6800pF | ±5% | **GRM2192C1H682JA01#** |
| | | | 8200pF | ±5% | **GRM2192C1H822JA01#** |
| | | | 10000pF | ±5% | **GRM2192C1H103JA01#** |
| | | | 12000pF | ±5% | **GRM2192C1H123JA01#** |
| | | | 15000pF | ±5% | **GRM2192C1H153JA01#** |
| | | SL | 22000pF | ±5% | **GRM2191X1H223JA01#** |
| | | | 27000pF | ±5% | **GRM2191X1H273JA01#** |
| | | U2J | 22000pF | ±5% | **GRM2197U1H223JA01#** |
| | | | 27000pF | ±5% | **GRM2197U1H273JA01#** |
| | | UJ | 22000pF | ±5% | **GRM2193U1H223JA01#** |
| | | | 27000pF | ±5% | **GRM2193U1H273JA01#** |
| | 10Vdc | SL | 56000pF | ±5% | **GRM2191X1A563JA01#** |
| | | U2J | 56000pF | ±5% | **GRM2197U1A563JA01#** |
| | | UJ | 56000pF | ±5% | **GRM2193U1A563JA01#** |
| 1.0mm | 250Vdc | C0G | 10pF | ±5% | **GRM21A5C2E100JW01#** |
| | | | 12pF | ±5% | **GRM21A5C2E120JW01#** |
| | | | 15pF | ±5% | **GRM21A5C2E150JW01#** |
| | | | 18pF | ±5% | **GRM21A5C2E180JW01#** |
| | | | 22pF | ±5% | **GRM21A5C2E220JW01#** |
| | | | 27pF | ±5% | **GRM21A5C2E270JW01#** |
| | | | 33pF | ±5% | **GRM21A5C2E330JW01#** |
| | | | 39pF | ±5% | **GRM21A5C2E390JW01#** |
| | | | 47pF | ±5% | **GRM21A5C2E470JW01#** |
| | | | 56pF | ±5% | **GRM21A5C2E560JW01#** |
| | | | 68pF | ±5% | **GRM21A5C2E680JW01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 250Vdc | C0G | 82pF | ±5% | **GRM21A5C2E820JW01#** |
| | | | 100pF | ±5% | **GRM21A5C2E101JW01#** |
| | | | 120pF | ±5% | **GRM21A5C2E121JW01#** |
| | | | 150pF | ±5% | **GRM21A5C2E151JW01#** |
| | | | 180pF | ±5% | **GRM21A5C2E181JW01#** |
| | | | 220pF | ±5% | **GRM21A5C2E221JW01#** |
| | | | 270pF | ±5% | **GRM21A5C2E271JW01#** |
| | | | 330pF | ±5% | **GRM21A5C2E331JW01#** |
| | | U2J | 100pF | ±5% | **GRM21A7U2E101JW31#** |
| | | | 120pF | ±5% | **GRM21A7U2E121JW31#** |
| | | | 150pF | ±5% | **GRM21A7U2E151JW31#** |
| | | | 180pF | ±5% | **GRM21A7U2E181JW31#** |
| | | | 220pF | ±5% | **GRM21A7U2E221JW31#** |
| | | | 270pF | ±5% | **GRM21A7U2E271JW31#** |
| | | | 330pF | ±5% | **GRM21A7U2E331JW31#** |
| | | | 390pF | ±5% | **GRM21A7U2E391JW31#** |
| | | | 470pF | ±5% | **GRM21A7U2E471JW31#** |
| | | | 560pF | ±5% | **GRM21A7U2E561JW31#** |
| | | | 680pF | ±5% | **GRM21A7U2E681JW31#** |
| | | | 820pF | ±5% | **GRM21A7U2E821JW31#** |
| | | | 1000pF | ±5% | **GRM21A7U2E102JW31#** |
| | | | 1200pF | ±5% | **GRM21A7U2E122JW31#** |
| | | | 1500pF | ±5% | **GRM21A7U2E152JW31#** |
| | | | 1800pF | ±5% | **GRM21A7U2E182JW31#** |
| | | | 2200pF | ±5% | **GRM21A7U2E222JW31#** |
| | 200Vdc | C0G | 10pF | ±5% | **GRM21A5C2D100JW01#** |
| | | | 12pF | ±5% | **GRM21A5C2D120JW01#** |
| | | | 15pF | ±5% | **GRM21A5C2D150JW01#** |
| | | | 18pF | ±5% | **GRM21A5C2D180JW01#** |
| | | | 22pF | ±5% | **GRM21A5C2D220JW01#** |
| | | | 27pF | ±5% | **GRM21A5C2D270JW01#** |
| | | | 33pF | ±5% | **GRM21A5C2D330JW01#** |
| | | | 39pF | ±5% | **GRM21A5C2D390JW01#** |
| | | | 47pF | ±5% | **GRM21A5C2D470JW01#** |
| | | | 56pF | ±5% | **GRM21A5C2D560JW01#** |
| | | | 68pF | ±5% | **GRM21A5C2D680JW01#** |
| | | | 82pF | ±5% | **GRM21A5C2D820JW01#** |
| | | | 100pF | ±5% | **GRM21A5C2D101JW01#** |
| | | | 120pF | ±5% | **GRM21A5C2D121JW01#** |
| | | | 150pF | ±5% | **GRM21A5C2D151JW01#** |
| | | | 180pF | ±5% | **GRM21A5C2D181JW01#** |
| | | | 220pF | ±5% | **GRM21A5C2D221JW01#** |
| | | | 270pF | ±5% | **GRM21A5C2D271JW01#** |
| | | | 330pF | ±5% | **GRM21A5C2D331JW01#** |
| | | U2J | 100pF | ±5% | **GRM21A7U2D101JW31#** |
| | | | 120pF | ±5% | **GRM21A7U2D121JW31#** |
| | | | 150pF | ±5% | **GRM21A7U2D151JW31#** |
| | | | 180pF | ±5% | **GRM21A7U2D181JW31#** |
| | | | 220pF | ±5% | **GRM21A7U2D221JW31#** |
| | | | 270pF | ±5% | **GRM21A7U2D271JW31#** |
| | | | 330pF | ±5% | **GRM21A7U2D331JW31#** |
| | | | 390pF | ±5% | **GRM21A7U2D391JW31#** |
| | | | 470pF | ±5% | **GRM21A7U2D471JW31#** |
| | | | 560pF | ±5% | **GRM21A7U2D561JW31#** |
| 1.0mm | 200Vdc | U2J | 680pF | ±5% | **GRM21A7U2D681JW31#** |
| | | | 820pF | ±5% | **GRM21A7U2D821JW31#** |
| | | | 1000pF | ±5% | **GRM21A7U2D102JW31#** |
| | | | 1200pF | ±5% | **GRM21A7U2D122JW31#** |
| | | | 1500pF | ±5% | **GRM21A7U2D152JW31#** |
| | | | 1800pF | ±5% | **GRM21A7U2D182JW31#** |
| | | | 2200pF | ±5% | **GRM21A7U2D222JW31#** |
| | 50Vdc | SL | 33000pF | ±5% | **GRM21A1X1H333JA39#** |
| | | U2J | 33000pF | ±5% | **GRM21A7U1H333JA39#** |
| | | UJ | 33000pF | ±5% | **GRM21A3U1H333JA39#** |
| 1.35mm | 50Vdc | C0G | 18000pF | ±5% | **GRM21B5C1H183JA01#** |
| | | | 22000pF | ±5% | **GRM21B5C1H223JA01#** |
| | | CH | 18000pF | ±5% | **GRM21B2C1H183JA01#** |
| | | | 22000pF | ±5% | **GRM21B2C1H223JA01#** |
| | | SL | 39000pF | ±5% | **GRM21B1X1H393JA01#** |
| | | | 47000pF | ±5% | **GRM21B1X1H473JA01#** |
| | | U2J | 39000pF | ±5% | **GRM21B7U1H393JA01#** |
| | | | 47000pF | ±5% | **GRM21B7U1H473JA01#** |
| | | UJ | 39000pF | ±5% | **GRM21B3U1H393JA01#** |
| | | | 47000pF | ±5% | **GRM21B3U1H473JA01#** |
| | 10Vdc | SL | 68000pF | ±5% | **GRM21B1X1A683JA01#** |
| | | | 82000pF | ±5% | **GRM21B1X1A823JA01#** |
| | | | 0.10µF | ±5% | **GRM21B1X1A104JA01#** |
| | | U2J | 68000pF | ±5% | **GRM21B7U1A683JA01#** |
| | | | 82000pF | ±5% | **GRM21B7U1A823JA01#** |
| | | | 0.10µF | ±5% | **GRM21B7U1A104JA01#** |
| | | UJ | 68000pF | ±5% | **GRM21B3U1A683JA01#** |
| | | | 82000pF | ±5% | **GRM21B3U1A823JA01#** |
| | | | 0.10µF | ±5% | **GRM21B3U1A104JA01#** |
| 1.45mm | 250Vdc | U2J | 2700pF | ±5% | **GRM21B7U2E272JW32#** |
| | | | 3300pF | ±5% | **GRM21B7U2E332JW32#** |
| | | | 3900pF | ±5% | **GRM21B7U2E392JW32#** |
| | | | 4700pF | ±5% | **GRM21B7U2E472JW32#** |
| | | | 5600pF | ±5% | **GRM21B7U2E562JW32#** |
| | 200Vdc | U2J | 2700pF | ±5% | **GRM21B7U2D272JW32#** |
| | | | 3300pF | ±5% | **GRM21B7U2D332JW32#** |
| | | | 3900pF | ±5% | **GRM21B7U2D392JW32#** |
| | | | 4700pF | ±5% | **GRM21B7U2D472JW32#** |
| | | | 5600pF | ±5% | **GRM21B7U2D562JW32#** |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 100Vdc | C0G | 1800pF | ±5% | **GRM3195C2A182JA01#** |
| | | | 2200pF | ±5% | **GRM3195C2A222JA01#** |
| | | | 2700pF | ±5% | **GRM3195C2A272JA01#** |
| | | | 3300pF | ±5% | **GRM3195C2A332JA01#** |
| | | | 3900pF | ±5% | **GRM3195C2A392JA01#** |
| | | | 4700pF | ±5% | **GRM3195C2A472JA01#** |
| | | | 5600pF | ±5% | **GRM3195C2A562JA01#** |
| | | | 6800pF | ±5% | **GRM3195C2A682JA01#** |
| | | | 8200pF | ±5% | **GRM3195C2A822JA01#** |
| | | | 10000pF | ±5% | **GRM3195C2A103JA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 100Vdc | C0G | 12000pF | ±5% | **GRM3195C2A123JA01#** |
| | | | 15000pF | ±5% | **GRM3195C2A153JA01#** |
| | | | 18000pF | ±5% | **GRM3195C2A183JA01#** |
| | | | 22000pF | ±5% | **GRM3195C2A223JA01#** |
| | | CH | 1800pF | ±5% | **GRM3192C2A182JA01#** |
| | | | 2200pF | ±5% | **GRM3192C2A222JA01#** |
| | | | 2700pF | ±5% | **GRM3192C2A272JA01#** |
| | | | 3300pF | ±5% | **GRM3192C2A332JA01#** |
| | | | 3900pF | ±5% | **GRM3192C2A392JA01#** |
| | | | 4700pF | ±5% | **GRM3192C2A472JA01#** |
| | | | 5600pF | ±5% | **GRM3192C2A562JA01#** |
| | | | 6800pF | ±5% | **GRM3192C2A682JA01#** |
| | | | 8200pF | ±5% | **GRM3192C2A822JA01#** |
| | | | 10000pF | ±5% | **GRM3192C2A103JA01#** |
| | | | 12000pF | ±5% | **GRM3192C2A123JA01#** |
| | | | 15000pF | ±5% | **GRM3192C2A153JA01#** |
| | | | 18000pF | ±5% | **GRM3192C2A183JA01#** |
| | | | 22000pF | ±5% | **GRM3192C2A223JA01#** |
| | 50Vdc | C0G | 12000pF | ±5% | **GRM3195C1H123JA01#** |
| | | | 15000pF | ±5% | **GRM3195C1H153JA01#** |
| | | | 18000pF | ±5% | **GRM3195C1H183JA01#** |
| | | | 22000pF | ±5% | **GRM3195C1H223JA01#** |
| | | | 27000pF | ±5% | **GRM3195C1H273JA01#** |
| | | | 33000pF | ±5% | **GRM3195C1H333JA01#** |
| | | | 39000pF | ±5% | **GRM3195C1H393JA01#** |
| | | CH | 12000pF | ±5% | **GRM3192C1H123JA01#** |
| | | | 15000pF | ±5% | **GRM3192C1H153JA01#** |
| | | | 18000pF | ±5% | **GRM3192C1H183JA01#** |
| | | | 22000pF | ±5% | **GRM3192C1H223JA01#** |
| | | | 27000pF | ±5% | **GRM3192C1H273JA01#** |
| | | | 33000pF | ±5% | **GRM3192C1H333JA01#** |
| | | | 39000pF | ±5% | **GRM3192C1H393JA01#** |
| | | SL | 56000pF | ±5% | **GRM3191X1H563JA01#** |
| | | U2J | 56000pF | ±5% | **GRM3197U1H563JA01#** |
| | | UJ | 56000pF | ±5% | **GRM3193U1H563JA01#** |
| 1.0mm | 2000Vdc | U2J | 10pF | ±5% | **GRM31A7U3D100JW31#** |
| | | | 12pF | ±5% | **GRM31A7U3D120JW31#** |
| | | | 15pF | ±5% | **GRM31A7U3D150JW31#** |
| | | | 18pF | ±5% | **GRM31A7U3D180JW31#** |
| | | | 22pF | ±5% | **GRM31A7U3D220JW31#** |
| | | | 27pF | ±5% | **GRM31A7U3D270JW31#** |
| | | | 33pF | ±5% | **GRM31A7U3D330JW31#** |
| | | | 39pF | ±5% | **GRM31A7U3D390JW31#** |
| | | | 47pF | ±5% | **GRM31A7U3D470JW31#** |
| | | | 56pF | ±5% | **GRM31A7U3D560JW31#** |
| | | | 68pF | ±5% | **GRM31A7U3D680JW31#** |
| | 1000Vdc | C0G | 10pF | ±5% | **GRM31A5C3A100JW01#** |
| | | | 12pF | ±5% | **GRM31A5C3A120JW01#** |
| | | | 15pF | ±5% | **GRM31A5C3A150JW01#** |
| | | | 18pF | ±5% | **GRM31A5C3A180JW01#** |
| | | | 22pF | ±5% | **GRM31A5C3A220JW01#** |
| | | | 27pF | ±5% | **GRM31A5C3A270JW01#** |
| | | | 33pF | ±5% | **GRM31A5C3A330JW01#** |
| | | | 39pF | ±5% | **GRM31A5C3A390JW01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 1000Vdc | C0G | 47pF | ±5% | **GRM31A5C3A470JW01#** |
| | | | 56pF | ±5% | **GRM31A5C3A560JW01#** |
| | | | 68pF | ±5% | **GRM31A5C3A680JW01#** |
| | | | 82pF | ±5% | **GRM31A5C3A820JW01#** |
| | | | 100pF | ±5% | **GRM31A5C3A101JW01#** |
| | | | 120pF | ±5% | **GRM31A5C3A121JW01#** |
| | | | 150pF | ±5% | **GRM31A5C3A151JW01#** |
| | | | 180pF | ±5% | **GRM31A5C3A181JW01#** |
| | | | 220pF | ±5% | **GRM31A5C3A221JW01#** |
| | | U2J | 10pF | ±5% | **GRM31A7U3A100JW31#** |
| | | | 12pF | ±5% | **GRM31A7U3A120JW31#** |
| | | | 15pF | ±5% | **GRM31A7U3A150JW31#** |
| | | | 18pF | ±5% | **GRM31A7U3A180JW31#** |
| | | | 22pF | ±5% | **GRM31A7U3A220JW31#** |
| | | | 27pF | ±5% | **GRM31A7U3A270JW31#** |
| | | | 33pF | ±5% | **GRM31A7U3A330JW31#** |
| | | | 39pF | ±5% | **GRM31A7U3A390JW31#** |
| | | | 47pF | ±5% | **GRM31A7U3A470JW31#** |
| | | | 56pF | ±5% | **GRM31A7U3A560JW31#** |
| | | | 68pF | ±5% | **GRM31A7U3A680JW31#** |
| | | | 82pF | ±5% | **GRM31A7U3A820JW31#** |
| | | | 100pF | ±5% | **GRM31A7U3A101JW31#** |
| | | | 120pF | ±5% | **GRM31A7U3A121JW31#** |
| | | | 150pF | ±5% | **GRM31A7U3A151JW31#** |
| | | | 180pF | ±5% | **GRM31A7U3A181JW31#** |
| | | | 220pF | ±5% | **GRM31A7U3A221JW31#** |
| | | | 270pF | ±5% | **GRM31A7U3A271JW31#** |
| | | | 330pF | ±5% | **GRM31A7U3A331JW31#** |
| | 630Vdc | C0G | 10pF | ±5% | **GRM31A5C2J100JW01#** |
| | | | 12pF | ±5% | **GRM31A5C2J120JW01#** |
| | | | 15pF | ±5% | **GRM31A5C2J150JW01#** |
| | | | 18pF | ±5% | **GRM31A5C2J180JW01#** |
| | | | 22pF | ±5% | **GRM31A5C2J220JW01#** |
| | | | 27pF | ±5% | **GRM31A5C2J270JW01#** |
| | | | 33pF | ±5% | **GRM31A5C2J330JW01#** |
| | | | 39pF | ±5% | **GRM31A5C2J390JW01#** |
| | | | 47pF | ±5% | **GRM31A5C2J470JW01#** |
| | | | 56pF | ±5% | **GRM31A5C2J560JW01#** |
| | | | 68pF | ±5% | **GRM31A5C2J680JW01#** |
| | | | 82pF | ±5% | **GRM31A5C2J820JW01#** |
| | | | 100pF | ±5% | **GRM31A5C2J101JW01#** |
| | | | 120pF | ±5% | **GRM31A5C2J121JW01#** |
| | | | 150pF | ±5% | **GRM31A5C2J151JW01#** |
| | | | 180pF | ±5% | **GRM31A5C2J181JW01#** |
| | | | 220pF | ±5% | **GRM31A5C2J221JW01#** |
| | | | 270pF | ±5% | **GRM31A5C2J271JW01#** |
| | | | 330pF | ±5% | **GRM31A5C2J331JW01#** |
| | | | 390pF | ±5% | **GRM31A5C2J391JW01#** |
| | | | 470pF | ±5% | **GRM31A5C2J471JW01#** |
| | | | 560pF | ±5% | **GRM31A5C2J561JW01#** |
| | | U2J | 10pF | ±5% | **GRM31A7U2J100JW31#** |
| | | | 12pF | ±5% | **GRM31A7U2J120JW31#** |
| | | | 15pF | ±5% | **GRM31A7U2J150JW31#** |
| | | | 18pF | ±5% | **GRM31A7U2J180JW31#** |

Part number # indicates the package specification code.





muRata

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 630Vdc | U2J | 22pF | ±5% | **GRM31A7U2J220JW31#** |
| | | | 27pF | ±5% | **GRM31A7U2J270JW31#** |
| | | | 33pF | ±5% | **GRM31A7U2J330JW31#** |
| | | | 39pF | ±5% | **GRM31A7U2J390JW31#** |
| | | | 47pF | ±5% | **GRM31A7U2J470JW31#** |
| | | | 56pF | ±5% | **GRM31A7U2J560JW31#** |
| | | | 68pF | ±5% | **GRM31A7U2J680JW31#** |
| | | | 82pF | ±5% | **GRM31A7U2J820JW31#** |
| | | | 100pF | ±5% | **GRM31A7U2J101JW31#** |
| | | | 120pF | ±5% | **GRM31A7U2J121JW31#** |
| | | | 150pF | ±5% | **GRM31A7U2J151JW31#** |
| | | | 180pF | ±5% | **GRM31A7U2J181JW31#** |
| | | | 220pF | ±5% | **GRM31A7U2J221JW31#** |
| | | | 270pF | ±5% | **GRM31A7U2J271JW31#** |
| | | | 330pF | ±5% | **GRM31A7U2J331JW31#** |
| | | | 390pF | ±5% | **GRM31A7U2J391JW31#** |
| | | | 470pF | ±5% | **GRM31A7U2J471JW31#** |
| | | | 560pF | ±5% | **GRM31A7U2J561JW31#** |
| | | | 680pF | ±5% | **GRM31A7U2J681JW31#** |
| | | | 820pF | ±5% | **GRM31A7U2J821JW31#** |
| | | | 1000pF | ±5% | **GRM31A7U2J102JW31#** |
| | | | 1200pF | ±5% | **GRM31A7U2J122JW31#** |
| | | | 1500pF | ±5% | **GRM31A7U2J152JW31#** |
| | | | 1800pF | ±5% | **GRM31A7U2J182JW31#** |
| | | | 2200pF | ±5% | **GRM31A7U2J222JW31#** |
| | 500Vdc | C0G | 10pF | ±5% | **GRM31A5C2H100JW01#** |
| | | | 12pF | ±5% | **GRM31A5C2H120JW01#** |
| | | | 15pF | ±5% | **GRM31A5C2H150JW01#** |
| | | | 18pF | ±5% | **GRM31A5C2H180JW01#** |
| | | | 22pF | ±5% | **GRM31A5C2H220JW01#** |
| | | | 27pF | ±5% | **GRM31A5C2H270JW01#** |
| | | | 33pF | ±5% | **GRM31A5C2H330JW01#** |
| | | | 39pF | ±5% | **GRM31A5C2H390JW01#** |
| | | | 47pF | ±5% | **GRM31A5C2H470JW01#** |
| | | | 56pF | ±5% | **GRM31A5C2H560JW01#** |
| | | | 68pF | ±5% | **GRM31A5C2H680JW01#** |
| | | | 82pF | ±5% | **GRM31A5C2H820JW01#** |
| | | | 100pF | ±5% | **GRM31A5C2H101JW01#** |
| | | | 120pF | ±5% | **GRM31A5C2H121JW01#** |
| | | | 150pF | ±5% | **GRM31A5C2H151JW01#** |
| | | | 180pF | ±5% | **GRM31A5C2H181JW01#** |
| | | | 220pF | ±5% | **GRM31A5C2H221JW01#** |
| | | | 270pF | ±5% | **GRM31A5C2H271JW01#** |
| | | | 330pF | ±5% | **GRM31A5C2H331JW01#** |
| | | | 390pF | ±5% | **GRM31A5C2H391JW01#** |
| | | | 470pF | ±5% | **GRM31A5C2H471JW01#** |
| | | | 560pF | ±5% | **GRM31A5C2H561JW01#** |
| | | U2J | 10pF | ±5% | **GRM31A7U2H100JW31#** |
| | | | 12pF | ±5% | **GRM31A7U2H120JW31#** |
| | | | 15pF | ±5% | **GRM31A7U2H150JW31#** |
| | | | 18pF | ±5% | **GRM31A7U2H180JW31#** |
| | | | 22pF | ±5% | **GRM31A7U2H220JW31#** |
| | | | 27pF | ±5% | **GRM31A7U2H270JW31#** |
| | | | 33pF | ±5% | **GRM31A7U2H330JW31#** |
| 1.0mm | 500Vdc | U2J | 39pF | ±5% | **GRM31A7U2H390JW31#** |
| | | | 47pF | ±5% | **GRM31A7U2H470JW31#** |
| | | | 56pF | ±5% | **GRM31A7U2H560JW31#** |
| | | | 68pF | ±5% | **GRM31A7U2H680JW31#** |
| | | | 82pF | ±5% | **GRM31A7U2H820JW31#** |
| | | | 100pF | ±5% | **GRM31A7U2H101JW31#** |
| | | | 120pF | ±5% | **GRM31A7U2H121JW31#** |
| | | | 150pF | ±5% | **GRM31A7U2H151JW31#** |
| | | | 180pF | ±5% | **GRM31A7U2H181JW31#** |
| | | | 220pF | ±5% | **GRM31A7U2H221JW31#** |
| | | | 270pF | ±5% | **GRM31A7U2H271JW31#** |
| | | | 330pF | ±5% | **GRM31A7U2H331JW31#** |
| | | | 390pF | ±5% | **GRM31A7U2H391JW31#** |
| | | | 470pF | ±5% | **GRM31A7U2H471JW31#** |
| | | | 560pF | ±5% | **GRM31A7U2H561JW31#** |
| | | | 680pF | ±5% | **GRM31A7U2H681JW31#** |
| | | | 820pF | ±5% | **GRM31A7U2H821JW31#** |
| | | | 1000pF | ±5% | **GRM31A7U2H102JW31#** |
| | | | 1200pF | ±5% | **GRM31A7U2H122JW31#** |
| | | | 1500pF | ±5% | **GRM31A7U2H152JW31#** |
| | | | 1800pF | ±5% | **GRM31A7U2H182JW31#** |
| | | | 2200pF | ±5% | **GRM31A7U2H222JW31#** |
| | 250Vdc | U2J | 2700pF | ±5% | **GRM31A7U2E272JW31#** |
| | | | 3300pF | ±5% | **GRM31A7U2E332JW31#** |
| | | | 3900pF | ±5% | **GRM31A7U2E392JW31#** |
| | | | 4700pF | ±5% | **GRM31A7U2E472JW31#** |
| | | | 5600pF | ±5% | **GRM31A7U2E562JW31#** |
| | 200Vdc | U2J | 2700pF | ±5% | **GRM31A7U2D272JW31#** |
| | | | 3300pF | ±5% | **GRM31A7U2D332JW31#** |
| | | | 3900pF | ±5% | **GRM31A7U2D392JW31#** |
| | | | 4700pF | ±5% | **GRM31A7U2D472JW31#** |
| | | | 5600pF | ±5% | **GRM31A7U2D562JW31#** |
| 1.25mm | 1000Vdc | U2J | 390pF | ±5% | **GRM31B7U3A391JW31#** |
| | | | 470pF | ±5% | **GRM31B7U3A471JW31#** |
| | | | 560pF | ±5% | **GRM31B7U3A561JW31#** |
| | | | 680pF | ±5% | **GRM31B7U3A681JW31#** |
| | 630Vdc | C0G | 680pF | ±5% | **GRM31B5C2J681JW01#** |
| | | | 820pF | ±5% | **GRM31B5C2J821JW01#** |
| | | | 1000pF | ±5% | **GRM31B5C2J102JW01#** |
| | | U2J | 2700pF | ±5% | **GRM31B7U2J272JW31#** |
| | | | 3300pF | ±5% | **GRM31B7U2J332JW31#** |
| | 500Vdc | C0G | 680pF | ±5% | **GRM31B5C2H681JW01#** |
| | | | 820pF | ±5% | **GRM31B5C2H821JW01#** |
| | | | 1000pF | ±5% | **GRM31B5C2H102JW01#** |
| | | U2J | 2700pF | ±5% | **GRM31B7U2H272JW31#** |
| | | | 3300pF | ±5% | **GRM31B7U2H332JW31#** |
| | 250Vdc | U2J | 6800pF | ±5% | **GRM31B7U2E682JW31#** |
| | | | 8200pF | ±5% | **GRM31B7U2E822JW31#** |
| | | | 10000pF | ±5% | **GRM31B7U2E103JW31#** |
| | | | 12000pF | ±5% | **GRM31B7U2E123JW31#** |
| | 200Vdc | U2J | 6800pF | ±5% | **GRM31B7U2D682JW31#** |
| | | | 8200pF | ±5% | **GRM31B7U2D822JW31#** |
| | | | 10000pF | ±5% | **GRM31B7U2D103JW31#** |
| | 50Vdc | C0G | 47000pF | ±5% | **GRM31M5C1H473JA01#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.25mm | 50Vdc | C0G | 56000pF | ±5% | **GRM31M5C1H563JA01#** |
| | | CH | 47000pF | ±5% | **GRM31M2C1H473JA01#** |
| | | | 56000pF | ±5% | **GRM31M2C1H563JA01#** |
| | | SL | 68000pF | ±5% | **GRM31M1X1H683JA01#** |
| | | | 82000pF | ±5% | **GRM31M1X1H823JA01#** |
| | | | 0.10μF | ±5% | **GRM31M1X1H104JA01#** |
| | | U2J | 68000pF | ±5% | **GRM31M7U1H683JA01#** |
| | | | 82000pF | ±5% | **GRM31M7U1H823JA01#** |
| | | | 0.10μF | ±5% | **GRM31M7U1H104JA01#** |
| | | UJ | 68000pF | ±5% | **GRM31M3U1H683JA01#** |
| | | | 82000pF | ±5% | **GRM31M3U1H823JA01#** |
| | | | 0.10μF | ±5% | **GRM31M3U1H104JA01#** |
| 1.8mm | 1000Vdc | U2J | 820pF | ±5% | **GRM31C7U3A821JW32#** |
| | | | 1000pF | ±5% | **GRM31C7U3A102JW32#** |
| | 630Vdc | U2J | 3900pF | ±5% | **GRM31C7U2J392JW32#** |
| | | | 4700pF | ±5% | **GRM31C7U2J472JW32#** |
| | 500Vdc | U2J | 3900pF | ±5% | **GRM31C7U2H392JW32#** |
| | | | 4700pF | ±5% | **GRM31C7U2H472JW32#** |
| | 250Vdc | U2J | 15000pF | ±5% | **GRM31C7U2E153JW32#** |
| | | | 18000pF | ±5% | **GRM31C7U2E183JW32#** |
| | | | 22000pF | ±5% | **GRM31C7U2E223JW32#** |
| | 50Vdc | C0G | 68000pF | ±5% | **GRM31C5C1H683JA01#** |
| | | | 82000pF | ±5% | **GRM31C5C1H823JA01#** |
| | | | 0.10μF | ±5% | **GRM31C5C1H104JA01#** |
| | | CH | 68000pF | ±5% | **GRM31C2C1H683JA01#** |
| | | | 82000pF | ±5% | **GRM31C2C1H823JA01#** |
| | | | 0.10μF | ±5% | **GRM31C2C1H104JA01#** |

## ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 2000Vdc | U2J | 82pF | ±5% | **GRM32A7U3D820JW31#** |
| | | | 100pF | ±5% | **GRM32A7U3D101JW31#** |
| | | | 120pF | ±5% | **GRM32A7U3D121JW31#** |
| | | | 150pF | ±5% | **GRM32A7U3D151JW31#** |
| | 630Vdc | U2J | 1200pF | ±5% | **GRM32A7U2J122JW31#** |
| | | | 1500pF | ±5% | **GRM32A7U2J152JW31#** |
| | | | 1800pF | ±5% | **GRM32A7U2J182JW31#** |
| | | | 2200pF | ±5% | **GRM32A7U2J222JW31#** |
| | 500Vdc | U2J | 1200pF | ±5% | **GRM32A7U2H122JW31#** |
| | | | 1500pF | ±5% | **GRM32A7U2H152JW31#** |
| | | | 1800pF | ±5% | **GRM32A7U2H182JW31#** |
| | | | 2200pF | ±5% | **GRM32A7U2H222JW31#** |
| 1.25mm | 2000Vdc | U2J | 180pF | ±5% | **GRM32B7U3D181JW31#** |
| | | | 220pF | ±5% | **GRM32B7U3D221JW31#** |
| | 1000Vdc | U2J | 1200pF | ±5% | **GRM32B7U3A122JW31#** |
| | 630Vdc | U2J | 5600pF | ±5% | **GRM32B7U2J562JW31#** |
| | 500Vdc | U2J | 5600pF | ±5% | **GRM32B7U2H562JW31#** |
| 1.5mm | 1000Vdc | U2J | 1500pF | ±5% | **GRM32Q7U3A152JW31#** |
| | 630Vdc | U2J | 6800pF | ±5% | **GRM32Q7U2J682JW31#** |
| | 500Vdc | U2J | 6800pF | ±5% | **GRM32Q7U2H682JW31#** |
| | 250Vdc | U2J | 27000pF | ±5% | **GRM32Q7U2E273JW31#** |
| 2.0mm | 1000Vdc | U2J | 1800pF | ±5% | **GRM32D7U3A182JW31#** |
| | | | 2200pF | ±5% | **GRM32D7U3A222JW31#** |
| | 630Vdc | U2J | 8200pF | ±5% | **GRM32D7U2J822JW31#** |
| | | | 10000pF | ±5% | **GRM32D7U2J103JW31#** |
| | 500Vdc | U2J | 8200pF | ±5% | **GRM32D7U2H822JW31#** |
| | | | 10000pF | ±5% | **GRM32D7U2H103JW31#** |
| | 250Vdc | U2J | 33000pF | ±5% | **GRM32D7U2E333JW31#** |
| | | | 39000pF | ±5% | **GRM32D7U2E393JW31#** |
| | | | 47000pF | ±5% | **GRM32D7U2E473JW31#** |

## ■ 4.5×2.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 3150Vdc | U2J | 27pF | ±5% | **GRM42A7U3F270JW31#** |
| | | | 33pF | ±5% | **GRM42A7U3F330JW31#** |
| | | | 39pF | ±5% | **GRM42A7U3F390JW31#** |
| | | | 47pF | ±5% | **GRM42A7U3F470JW31#** |
| | | | 56pF | ±5% | **GRM42A7U3F560JW31#** |
| | | | 68pF | ±5% | **GRM42A7U3F680JW31#** |
| | | | 82pF | ±5% | **GRM42A7U3F820JW31#** |
| | | | 100pF | ±5% | **GRM42A7U3F101JW31#** |

## ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.5mm | 1000Vdc | U2J | 2700pF | ±5% | **GRM43Q7U3A272JW31#** |
| | | | 3300pF | ±5% | **GRM43Q7U3A332JW31#** |
| | 630Vdc | U2J | 12000pF | ±5% | **GRM43Q7U2J123JW31#** |
| | 500Vdc | U2J | 12000pF | ±5% | **GRM43Q7U2H123JW31#** |
| 2.0mm | 1000Vdc | U2J | 3900pF | ±5% | **GRM43D7U3A392JW31#** |
| | | | 4700pF | ±5% | **GRM43D7U3A472JW31#** |
| | 630Vdc | U2J | 15000pF | ±5% | **GRM43D7U2J153JW31#** |
| | | | 18000pF | ±5% | **GRM43D7U2J183JW31#** |
| | | | 22000pF | ±5% | **GRM43D7U2J223JW31#** |
| | 500Vdc | U2J | 15000pF | ±5% | **GRM43D7U2H153JW31#** |
| | | | 18000pF | ±5% | **GRM43D7U2H183JW31#** |
| | | | 22000pF | ±5% | **GRM43D7U2H223JW31#** |

## ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.5mm | 1000Vdc | U2J | 5600pF | ±5% | **GRM55Q7U3A562JW31#** |
| | | | 6800pF | ±5% | **GRM55Q7U3A682JW31#** |
| | 630Vdc | U2J | 27000pF | ±5% | **GRM55Q7U2J273JW31#** |
| | 500Vdc | U2J | 27000pF | ±5% | **GRM55Q7U2H273JW31#** |
| 2.0mm | 1000Vdc | U2J | 8200pF | ±5% | **GRM55D7U3A822JW31#** |
| | | | 10000pF | ±5% | **GRM55D7U3A103JW31#** |
| | 630Vdc | U2J | 33000pF | ±5% | **GRM55D7U2J333JW31#** |
| | | | 39000pF | ±5% | **GRM55D7U2J393JW31#** |
| | | | 47000pF | ±5% | **GRM55D7U2J473JW31#** |
| | 500Vdc | U2J | 33000pF | ±5% | **GRM55D7U2H333JW31#** |
| | | | 39000pF | ±5% | **GRM55D7U2H393JW31#** |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 5.7×5.0mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.0mm | 500Vdc | U2J | 47000pF | ±5% | **GRM55D7U2H473JW31#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

## ■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 10Vdc | X7R | 100pF | ±10% | GRM022R71A101KA01# | |
| | | | | ±20% | GRM022R71A101MA01# | |
| | | | 150pF | ±10% | GRM022R71A151KA01# | |
| | | | | ±20% | GRM022R71A151MA01# | |
| | | | 220pF | ±10% | GRM022R71A221KA01# | |
| | | | | ±20% | GRM022R71A221MA01# | |
| | | | 330pF | ±10% | GRM022R71A331KA01# | |
| | | | | ±20% | GRM022R71A331MA01# | |
| | | | 470pF | ±10% | GRM022R71A471KA01# | |
| | | | | ±20% | GRM022R71A471MA01# | |
| | | | 680pF | ±10% | GRM022R71A681KA12# | |
| | | | | ±20% | GRM022R71A681MA12# | |
| | | | 820pF | ±10% | GRM022R71A821KA12# | |
| | | | | ±20% | GRM022R71A821MA12# | |
| | | | 1000pF | ±10% | GRM022R71A102KA12# | |
| | | | | ±20% | GRM022R71A102MA12# | |
| | | X5R | 100pF | ±10% | GRM022R61A101KA01# | |
| | | | | ±20% | GRM022R61A101MA01# | |
| | | | 150pF | ±10% | GRM022R61A151KA01# | |
| | | | | ±20% | GRM022R61A151MA01# | |
| | | | 220pF | ±10% | GRM022R61A221KA01# | |
| | | | | ±20% | GRM022R61A221MA01# | |
| | | | 330pF | ±10% | GRM022R61A331KA01# | |
| | | | | ±20% | GRM022R61A331MA01# | |
| | | | 470pF | ±10% | GRM022R61A471KA01# | |
| | | | | ±20% | GRM022R61A471MA01# | |
| | | | 680pF | ±10% | GRM022R61A681KE19# | |
| | | | | ±20% | GRM022R61A681ME19# | |
| | | | 1000pF | ±10% | GRM022R61A102KE19# | |
| | | | | ±20% | GRM022R61A102ME19# | |
| | | | 1500pF | ±10% | GRM022R61A152KE19# | |
| | | | | ±20% | GRM022R61A152ME19# | |
| | | | 2200pF | ±10% | GRM022R61A222KE19# | |
| | | | | ±20% | GRM022R61A222ME19# | |
| | | | 3300pF | ±10% | GRM022R61A332KE19# | |
| | | | | ±20% | GRM022R61A332ME19# | |
| | | | 4700pF | ±10% | GRM022R61A472KE19# | |
| | | | | ±20% | GRM022R61A472ME19# | |
| | | | 6800pF | ±10% | GRM022R61A682KE19# | |
| | | | | ±20% | GRM022R61A682ME19# | |
| | | | 10000pF | ±10% | GRM022R61A103KE19# | |
| | | | | ±20% | GRM022R61A103ME19# | |
| | | B | 100pF | ±10% | GRM022B11A101KA01# | |
| | | | | ±20% | GRM022B11A101MA01# | |
| | | | 150pF | ±10% | GRM022B11A151KA01# | |
| | | | | ±20% | GRM022B11A151MA01# | |
| | | | 220pF | ±10% | GRM022B11A221KA01# | |
| | | | | ±20% | GRM022B11A221MA01# | |
| | | | 330pF | ±10% | GRM022B11A331KA01# | |
| | | | | ±20% | GRM022B11A331MA01# | |
| | | | 470pF | ±10% | GRM022B11A471KA01# | |
| | | | | ±20% | GRM022B11A471MA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 10Vdc | B | 680pF | ±10% | GRM022B31A681KE19# | |
| | | | | ±20% | GRM022B31A681ME19# | |
| | | | 1000pF | ±10% | GRM022B31A102KE19# | |
| | | | | ±20% | GRM022B31A102ME19# | |
| | | | 1500pF | ±10% | GRM022B31A152KE19# | |
| | | | | ±20% | GRM022B31A152ME19# | |
| | | | 2200pF | ±10% | GRM022B31A222KE19# | |
| | | | | ±20% | GRM022B31A222ME19# | |
| | | | 3300pF | ±10% | GRM022B31A332KE19# | |
| | | | | ±20% | GRM022B31A332ME19# | |
| | | | 4700pF | ±10% | GRM022B31A472KE19# | |
| | | | | ±20% | GRM022B31A472ME19# | |
| | | | 6800pF | ±10% | GRM022B31A682KE19# | |
| | | | | ±20% | GRM022B31A682ME19# | |
| | | | 10000pF | ±10% | GRM022B31A103KE19# | |
| | | | | ±20% | GRM022B31A103ME19# | |
| | 6.3Vdc | X5R | 1000pF | ±20% | GRM022R60J102ME19# | |
| | | | 1500pF | ±20% | GRM022R60J152ME19# | |
| | | | 2200pF | ±20% | GRM022R60J222ME19# | |
| | | | 3300pF | ±20% | GRM022R60J332ME19# | |
| | | | 4700pF | ±20% | GRM022R60J472ME19# | |
| | | | 6800pF | ±20% | GRM022R60J682ME19# | |
| | | | 10000pF | ±20% | GRM022R60J103ME19# | |
| | | | 15000pF | ±20% | GRM022R60J153ME15# | Derating |
| | | | 22000pF | ±10% | GRM022R60J223KE15# | Derating |
| | | | | ±20% | GRM022R60J223ME15# | Derating |
| | | | 33000pF | ±20% | GRM022R60J333ME15# | Derating |
| | | | 47000pF | ±20% | GRM022R60J473ME15# | Derating |
| | | | 68000pF | ±20% | GRM022R60J683ME15# | Derating |
| | | | 0.10µF | ±20% | GRM022R60J104ME15# | Derating |
| | | B | 1000pF | ±20% | GRM022B30J102ME19# | |
| | | | 1500pF | ±20% | GRM022B30J152ME19# | |
| | | | 2200pF | ±20% | GRM022B30J222ME19# | |
| | | | 3300pF | ±20% | GRM022B30J332ME19# | |
| | | | 4700pF | ±20% | GRM022B30J472ME19# | |
| | | | 6800pF | ±20% | GRM022B30J682ME19# | |
| | | | 10000pF | ±20% | GRM022B30J103ME19# | |
| | 4Vdc | X5R | 15000pF | ±10% | GRM022R60G153KE15# | |
| | | | | ±20% | GRM022R60G153ME15# | |
| | | | 22000pF | ±10% | GRM022R60G223KE15# | |
| | | | | ±20% | GRM022R60G223ME15# | |
| | | | 33000pF | ±10% | GRM022R60G333KE15# | |
| | | | | ±20% | GRM022R60G333ME15# | |
| | | | 47000pF | ±10% | GRM022R60G473KE15# | |
| | | | | ±20% | GRM022R60G473ME15# | |
| | | | 68000pF | ±20% | GRM022R60G683ME15# | |
| | | | 0.10µF | ±20% | GRM022R60G104ME15# | |

## ■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | X7R | 100pF | ±10% | GRM033R71H101KA12# | |
| | | | | ±20% | GRM033R71H101MA12# | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 50Vdc | X7R | 150pF | ±10% | GRM033R71H151KA12# | |
| | | | | ±20% | GRM033R71H151MA12# | |
| | | | 220pF | ±10% | GRM033R71H221KA12# | |
| | | | | ±20% | GRM033R71H221MA12# | |
| | | | 330pF | ±10% | GRM033R71H331KA12# | |
| | | | | ±20% | GRM033R71H331MA12# | |
| | | | 470pF | ±10% | GRM033R71H471KA12# | |
| | | | | ±20% | GRM033R71H471MA12# | |
| | | | 680pF | ±10% | GRM033R71H681KA12# | |
| | | | | ±20% | GRM033R71H681MA12# | |
| | | | 1000pF | ±10% | GRM033R71H102KA12# | |
| | | | | ±20% | GRM033R71H102MA12# | |
| | | | 1500pF | ±10% | GRM033R71H152KA12# | |
| | | | | ±20% | GRM033R71H152MA12# | |
| | | B | 100pF | ±10% | GRM033B31H101KA12# | |
| | | | | ±20% | GRM033B31H101MA12# | |
| | | | 150pF | ±10% | GRM033B31H151KA12# | |
| | | | | ±20% | GRM033B31H151MA12# | |
| | | | 220pF | ±10% | GRM033B31H221KA12# | |
| | | | | ±20% | GRM033B31H221MA12# | |
| | | | 330pF | ±10% | GRM033B31H331KA12# | |
| | | | | ±20% | GRM033B31H331MA12# | |
| | | | 470pF | ±10% | GRM033B31H471KA12# | |
| | | | | ±20% | GRM033B31H471MA12# | |
| | | | 680pF | ±10% | GRM033B31H681KA12# | |
| | | | | ±20% | GRM033B31H681MA12# | |
| | | | 1000pF | ±10% | GRM033B31H102KA12# | |
| | | | | ±20% | GRM033B31H102MA12# | |
| | | | 1500pF | ±10% | GRM033B31H152KA12# | |
| | | | | ±20% | GRM033B31H152MA12# | |
| | 25Vdc | X7R | 1000pF | ±10% | GRM033R71E102KA01# | |
| | | | 1500pF | ±10% | GRM033R71E152KA01# | |
| | | | 2200pF | ±10% | GRM033R71E222KA12# | |
| | | | | ±20% | GRM033R71E222MA12# | |
| | | | 3300pF | ±10% | GRM033R71E332KA12# | |
| | | | | ±20% | GRM033R71E332MA12# | |
| | | R | 100pF | ±10% | GRM033R11E101KA01# | |
| | | | 150pF | ±10% | GRM033R11E151KA01# | |
| | | | 220pF | ±10% | GRM033R11E221KA01# | |
| | | | 330pF | ±10% | GRM033R11E331KA01# | |
| | | | 470pF | ±10% | GRM033R11E471KA01# | |
| | | | 680pF | ±10% | GRM033R11E681KA01# | |
| | | | 1000pF | ±10% | GRM033R11E102KA01# | |
| | | | 1500pF | ±10% | GRM033R11E152KA01# | |
| | | X5R | 4700pF | ±10% | GRM033R61E472KA12# | Derating |
| | | | | ±20% | GRM033R61E472MA12# | Derating |
| | | | 6800pF | ±10% | GRM033R61E682KA12# | Derating |
| | | | | ±20% | GRM033R61E682MA12# | Derating |
| | | | 10000pF | ±10% | GRM033R61E103KA12# | Derating |
| | | | | ±20% | GRM033R61E103MA12# | Derating |
| | | B | 1000pF | ±10% | GRM033B11E102KA01# | |
| | | | | ±20% | GRM033B11E102MA01# | |
| | | | 1500pF | ±10% | GRM033B11E152KA01# | |
| | | | | ±20% | GRM033B11E152MA01# | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 25Vdc | B | 2200pF | ±10% | GRM033B31E222KA12# | |
| | | | | ±20% | GRM033B31E222MA12# | |
| | | | 3300pF | ±10% | GRM033B31E332KA12# | |
| | | | | ±20% | GRM033B31E332MA12# | |
| | | | 10000pF | ±10% | GRM033B31E103KA12# | Derating |
| | | | | ±20% | GRM033B31E103MA12# | Derating |
| | 16Vdc | X7R | 2200pF | ±10% | GRM033R71C222KA88# | |
| | | | 3300pF | ±10% | GRM033R71C332KA88# | |
| | | R | 2200pF | ±10% | GRM033R11C222KA88# | |
| | | | 3300pF | ±10% | GRM033R11C332KA88# | |
| | | X5R | 10000pF | ±10% | GRM033R61C103KA12# | |
| | | | | ±20% | GRM033R61C103MA12# | |
| | | | 15000pF | ±10% | GRM033R61C153KE84# | Derating |
| | | | | ±20% | GRM033R61C153ME84# | Derating |
| | | | 22000pF | ±10% | GRM033R61C223KE84# | Derating |
| | | | | ±20% | GRM033R61C223ME84# | Derating |
| | | | 33000pF | ±10% | GRM033R61C333KE84# | Derating |
| | | | | ±20% | GRM033R61C333ME84# | Derating |
| | | | 47000pF | ±10% | GRM033R61C473KE84# | Derating |
| | | | | ±20% | GRM033R61C473ME84# | Derating |
| | | | 68000pF | ±10% | GRM033R61C683KE84# | Derating |
| | | | | ±20% | GRM033R61C683ME84# | Derating |
| | | | 0.10µF | ±10% | GRM033R61C104KE84# | Derating |
| | | | | ±20% | GRM033R61C104ME84# | Derating |
| | | B | 2200pF | ±10% | GRM033B31C222KA87# | |
| | | | | ±20% | GRM033B31C222MA87# | |
| | | | 3300pF | ±10% | GRM033B31C332KA87# | |
| | | | | ±20% | GRM033B31C332MA87# | |
| | | | 10000pF | ±10% | GRM033B31C103KA12# | |
| | | | | ±20% | GRM033B31C103MA12# | |
| | | | 15000pF | ±10% | GRM033B31C153KE84# | Derating |
| | | | | ±20% | GRM033B31C153ME84# | Derating |
| | | | 22000pF | ±10% | GRM033B31C223KE84# | Derating |
| | | | | ±20% | GRM033B31C223ME84# | Derating |
| | | | 33000pF | ±10% | GRM033B31C333KE84# | Derating |
| | | | | ±20% | GRM033B31C333ME84# | Derating |
| | | | 47000pF | ±10% | GRM033B31C473KE84# | Derating |
| | | | | ±20% | GRM033B31C473ME84# | Derating |
| | | | 68000pF | ±10% | GRM033B31C683KE84# | Derating |
| | | | | ±20% | GRM033B31C683ME84# | Derating |
| | | | 0.10µF | ±10% | GRM033B31C104KE84# | Derating |
| | | | | ±20% | GRM033B31C104ME84# | Derating |
| | 10Vdc | X7R | 4700pF | ±10% | GRM033R71A472KA01# | |
| | | | | ±20% | GRM033R71A472MA01# | |
| | | | 6800pF | ±10% | GRM033R71A682KA01# | |
| | | | | ±20% | GRM033R71A682MA01# | |
| | | | 10000pF | ±10% | GRM033R71A103KA01# | |
| | | | | ±20% | GRM033R71A103MA01# | |
| | | R | 4700pF | ±10% | GRM033R11A472KA01# | |
| | | | | ±20% | GRM033R11A472MA01# | |
| | | | 6800pF | ±10% | GRM033R11A682KA01# | |
| | | | | ±20% | GRM033R11A682MA01# | |
| | | | 10000pF | ±10% | GRM033R11A103KA01# | |
| | | | | ±20% | GRM033R11A103MA01# | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.33mm | 10Vdc | X5R | 4700pF | ±10% | **GRM033R61A472KA01#** | |
| | | | | ±20% | **GRM033R61A472MA01#** | |
| | | | 6800pF | ±10% | **GRM033R61A682KA01#** | |
| | | | | ±20% | **GRM033R61A682MA01#** | |
| | | | 15000pF | ±10% | **GRM033R61A153KE84#** | |
| | | | | ±20% | **GRM033R61A153ME84#** | |
| | | | 22000pF | ±10% | **GRM033R61A223KE84#** | |
| | | | | ±20% | **GRM033R61A223ME84#** | |
| | | | 33000pF | ±10% | **GRM033R61A333KE84#** | |
| | | | | ±20% | **GRM033R61A333ME84#** | |
| | | | 47000pF | ±10% | **GRM033R61A473KE84#** | |
| | | | | ±20% | **GRM033R61A473ME84#** | |
| | | | 68000pF | ±10% | **GRM033R61A683KE84#** | |
| | | | | ±20% | **GRM033R61A683ME84#** | |
| | | | 0.10μF | ±10% | **GRM033R61A104KE84#** | |
| | | | | ±20% | **GRM033R61A104ME84#** | |
| | | | 0.22μF | ±20% | **GRM033R61A224ME90#** | Derating |
| | | B | 4700pF | ±10% | **GRM033B11A472KA01#** | |
| | | | | ±20% | **GRM033B11A472MA01#** | |
| | | | 6800pF | ±10% | **GRM033B11A682KA01#** | |
| | | | | ±20% | **GRM033B11A682MA01#** | |
| | | | 15000pF | ±10% | **GRM033B31A153KE84#** | |
| | | | | ±20% | **GRM033B31A153ME84#** | |
| | | | 22000pF | ±10% | **GRM033B31A223KE84#** | |
| | | | | ±20% | **GRM033B31A223ME84#** | |
| | | | 33000pF | ±10% | **GRM033B31A333KE84#** | |
| | | | | ±20% | **GRM033B31A333ME84#** | |
| | | | 47000pF | ±10% | **GRM033B31A473KE84#** | |
| | | | | ±20% | **GRM033B31A473ME84#** | |
| | | | 68000pF | ±10% | **GRM033B31A683KE84#** | |
| | | | | ±20% | **GRM033B31A683ME84#** | |
| | | | 0.10μF | ±10% | **GRM033B31A104KE84#** | |
| | | | | ±20% | **GRM033B31A104ME84#** | |
| | 6.3Vdc | X7R | 4700pF | ±10% | **GRM033R70J472KA01#** | |
| | | | 6800pF | ±10% | **GRM033R70J682KA01#** | |
| | | | 10000pF | ±10% | **GRM033R70J103KA01#** | |
| | | R | 4700pF | ±10% | **GRM033R10J472KA01#** | |
| | | | 6800pF | ±10% | **GRM033R10J682KA01#** | |
| | | | 10000pF | ±10% | **GRM033R10J103KA01#** | |
| | | X6S | 15000pF | ±10% | **GRM033C80J153KE01#** | |
| | | | | ±20% | **GRM033C80J153ME01#** | |
| | | | 22000pF | ±10% | **GRM033C80J223KE01#** | |
| | | | | ±20% | **GRM033C80J223ME01#** | |
| | | | 33000pF | ±10% | **GRM033C80J333KE01#** | |
| | | | | ±20% | **GRM033C80J333ME01#** | |
| | | | 47000pF | ±10% | **GRM033C80J473KE19#** | |
| | | | | ±20% | **GRM033C80J473ME19#** | |
| | | | 68000pF | ±10% | **GRM033C80J683KE84#** | Derating |
| | | | | ±20% | **GRM033C80J683ME84#** | Derating |
| | | | 0.10μF | ±10% | **GRM033C80J104KE84#** | Derating |
| | | | | ±20% | **GRM033C80J104ME84#** | Derating |
| | | | 0.22μF | ±20% | **GRM033C80J224ME90#** | Derating |
| | | X5R | 0.22μF | ±20% | **GRM033R60J224ME90#** | |
| | | B | 4700pF | ±10% | **GRM033B10J472KA01#** | |
| | | | 6800pF | ±10% | **GRM033B10J682KA01#** | |
| | | | 15000pF | ±10% | **GRM033B10J153KE01#** | |
| | | | | ±20% | **GRM033B10J153ME01#** | |
| | | | 22000pF | ±10% | **GRM033B10J223KE01#** | |
| | | | | ±20% | **GRM033B10J223ME01#** | |
| | | | 33000pF | ±10% | **GRM033B10J333KE01#** | |
| | | | | ±20% | **GRM033B10J333ME01#** | |
| | 4Vdc | X6S | 0.22μF | ±20% | **GRM033C80G224ME90#** | |

## ■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 10Vdc | X5R | 0.10μF | ±10% | **GRM152R61A104KE19#** | Derating |
| | | | | ±20% | **GRM152R61A104ME19#** | Derating |
| | | | 0.22μF | ±10% | **GRM152R61A224KE19#** | Derating |
| | | | | ±20% | **GRM152R61A224ME19#** | Derating |
| | | B | 0.10μF | ±10% | **GRM152B31A104KE19#** | Derating |
| | | | | ±20% | **GRM152B31A104ME19#** | Derating |
| | | | 0.22μF | ±10% | **GRM152B31A224KE19#** | Derating |
| | | | | ±20% | **GRM152B31A224ME19#** | Derating |
| | 6.3Vdc | X6S | 0.10μF | ±10% | **GRM152C80J104KE19#** | Derating |
| | | | | ±20% | **GRM152C80J104ME19#** | Derating |
| | | | 0.22μF | ±10% | **GRM152C80J224KE19#** | Derating |
| | | | | ±20% | **GRM152C80J224ME19#** | Derating |
| | | X5R | 0.10μF | ±10% | **GRM152R60J104KE19#** | |
| | | | | ±20% | **GRM152R60J104ME19#** | |
| | | | 0.22μF | ±10% | **GRM152R60J224KE19#** | |
| | | | | ±20% | **GRM152R60J224ME19#** | |
| | | | 0.47μF | ±20% | **GRM152R60J474ME15#** | Derating |
| | | | 1.0μF | ±20% | **GRM152R60J105ME15#** | Derating |
| | | B | 0.10μF | ±10% | **GRM152B30J104KE19#** | |
| | | | | ±20% | **GRM152B30J104ME19#** | |
| | | | 0.22μF | ±10% | **GRM152B30J224KE19#** | |
| | | | | ±20% | **GRM152B30J224ME19#** | |
| | | | 0.47μF | ±20% | **GRM152B30J474ME15#** | Derating |
| | 4Vdc | X7T | 0.10μF | ±10% | **GRM152D70G104KE15#** | Derating |
| | | | | ±20% | **GRM152D70G104ME15#** | Derating |
| | | | 0.22μF | ±10% | **GRM152D70G224KE15#** | Derating |
| | | | | ±20% | **GRM152D70G224ME15#** | Derating |
| | | X6S | 0.10μF | ±10% | **GRM152C80G104KE19#** | |
| | | | | ±20% | **GRM152C80G104ME19#** | |
| | | | 0.22μF | ±10% | **GRM152C80G224KE19#** | |
| | | | | ±20% | **GRM152C80G224ME19#** | |
| | | X6T | 0.47μF | ±20% | **GRM152D80G474ME15#** | |
| | | | 1.0μF | ±20% | **GRM152D80G105ME15#** | Derating |
| | | X5R | 1.0μF | ±20% | **GRM152R60G105ME15#** | |
| | 2.5Vdc | X7T | 0.10μF | ±10% | **GRM152D70E104KE19#** | |
| | | | | ±20% | **GRM152D70E104ME19#** | |
| | | | 0.22μF | ±10% | **GRM152D70E224KE19#** | |
| | | | | ±20% | **GRM152D70E224ME19#** | |
| 0.3mm | 50Vdc | X7R | 220pF | ±10% | **GRM15XR71H221KA86#** | |
| | | | 330pF | ±10% | **GRM15XR71H331KA86#** | |
| | | | 470pF | ±10% | **GRM15XR71H471KA86#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.3mm | 50Vdc | X7R | 680pF | ±10% | **GRM15XR71H681KA86#** | |
| | | | 1000pF | ±10% | **GRM15XR71H102KA86#** | |
| | | | 1500pF | ±10% | **GRM15XR71H152KA86#** | |
| | | R | 220pF | ±10% | **GRM15XR11H221KA86#** | |
| | | | 330pF | ±10% | **GRM15XR11H331KA86#** | |
| | | | 470pF | ±10% | **GRM15XR11H471KA86#** | |
| | | | 680pF | ±10% | **GRM15XR11H681KA86#** | |
| | | | 1000pF | ±10% | **GRM15XR11H102KA86#** | |
| | | | 1500pF | ±10% | **GRM15XR11H152KA86#** | |
| | | B | 220pF | ±10% | **GRM15XB11H221KA86#** | |
| | | | | ±20% | **GRM15XB11H221MA86#** | |
| | | | 330pF | ±10% | **GRM15XB11H331KA86#** | |
| | | | | ±20% | **GRM15XB11H331MA86#** | |
| | | | 470pF | ±10% | **GRM15XB11H471KA86#** | |
| | | | | ±20% | **GRM15XB11H471MA86#** | |
| | | | 680pF | ±10% | **GRM15XB11H681KA86#** | |
| | | | | ±20% | **GRM15XB11H681MA86#** | |
| | | | 1000pF | ±10% | **GRM15XB11H102KA86#** | |
| | | | | ±20% | **GRM15XB11H102MA86#** | |
| | | | 1500pF | ±10% | **GRM15XB11H152KA86#** | |
| | | | | ±20% | **GRM15XB11H152MA86#** | |
| | 25Vdc | X7R | 2200pF | ±10% | **GRM15XR71E222KA86#** | |
| | | | | ±20% | **GRM15XR71E222MA86#** | |
| | | B | 2200pF | ±10% | **GRM15XB11E222KA86#** | |
| | | | | ±20% | **GRM15XB11E222MA86#** | |
| | 16Vdc | X7R | 3300pF | ±10% | **GRM15XR71C332KA86#** | |
| | | | | ±20% | **GRM15XR71C332MA86#** | |
| | | | 4700pF | ±10% | **GRM15XR71C472KA86#** | |
| | | | | ±20% | **GRM15XR71C472MA86#** | |
| | | | 6800pF | ±10% | **GRM15XR71C682KA86#** | |
| | | | | ±20% | **GRM15XR71C682MA86#** | |
| | | | 10000pF | ±10% | **GRM15XR71C103KA86#** | |
| | | | | ±20% | **GRM15XR71C103MA86#** | |
| | | B | 3300pF | ±10% | **GRM15XB11C332KA86#** | |
| | | | | ±20% | **GRM15XB11C332MA86#** | |
| | | | 4700pF | ±10% | **GRM15XB11C472KA86#** | |
| | | | | ±20% | **GRM15XB11C472MA86#** | |
| | | | 6800pF | ±10% | **GRM15XB11C682KA86#** | |
| | | | | ±20% | **GRM15XB11C682MA86#** | |
| | | | 10000pF | ±10% | **GRM15XB11C103KA86#** | |
| | | | | ±20% | **GRM15XB11C103MA86#** | |
| | 10Vdc | X5R | 15000pF | ±10% | **GRM15XR61A153KA86#** | |
| | | | | ±20% | **GRM15XR61A153MA86#** | |
| | | | 22000pF | ±10% | **GRM15XR61A223KA86#** | |
| | | | | ±20% | **GRM15XR61A223MA86#** | |
| | | | 33000pF | ±10% | **GRM15XR61A333KA86#** | |
| | | | | ±20% | **GRM15XR61A333MA86#** | |
| 0.33mm | 10Vdc | X5R | 1.0µF | ±20% | **GRM153R61A105ME95#** | Derating |
| | | B | 1.0µF | ±20% | **GRM153B31A105ME95#** | Derating |
| | 6.3Vdc | X6T | 1.0µF | ±20% | **GRM153D80J105ME95#** | Derating |
| | | X5R | 1.0µF | ±20% | **GRM153R60J105ME95#** | |
| | | B | 1.0µF | ±20% | **GRM153B30J105ME95#** | |
| | 4Vdc | X6T | 1.0µF | ±20% | **GRM153D80G105ME95#** | |
| 0.55mm | 100Vdc | X7R | 220pF | ±10% | **GRM155R72A221KA01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 100Vdc | X7R | 330pF | ±10% | **GRM155R72A331KA01#** | |
| | | | 470pF | ±10% | **GRM155R72A471KA01#** | |
| | | | 680pF | ±10% | **GRM155R72A681KA01#** | |
| | | | 1000pF | ±10% | **GRM155R72A102KA01#** | |
| | | | 1500pF | ±10% | **GRM155R72A152KA01#** | |
| | | | 2200pF | ±10% | **GRM155R72A222KA01#** | |
| | | | 3300pF | ±10% | **GRM155R72A332KA01#** | |
| | | | 4700pF | ±10% | **GRM155R72A472KA01#** | |
| | 50Vdc | X7R | 220pF | ±10% | **GRM155R71H221KA01#** | |
| | | | 330pF | ±10% | **GRM155R71H331KA01#** | |
| | | | 470pF | ±10% | **GRM155R71H471KA01#** | |
| | | | 680pF | ±10% | **GRM155R71H681KA01#** | |
| | | | 1000pF | ±10% | **GRM155R71H102KA01#** | |
| | | | 1500pF | ±10% | **GRM155R71H152KA01#** | |
| | | | 2200pF | ±10% | **GRM155R71H222KA01#** | |
| | | | 3300pF | ±10% | **GRM155R71H332KA01#** | |
| | | | 4700pF | ±10% | **GRM155R71H472KA01#** | |
| | | | 6800pF | ±10% | **GRM155R71H682KA88#** | |
| | | | 10000pF | ±10% | **GRM155R71H103KA88#** | |
| | | | 15000pF | ±10% | **GRM155R71H153KA12#** | |
| | | | 22000pF | ±10% | **GRM155R71H223KA12#** | |
| | | | 33000pF | ±10% | **GRM155R71H333KE14#** | |
| | | | | ±20% | **GRM155R71H333ME14#** | |
| | | | 47000pF | ±10% | **GRM155R71H473KE14#** | |
| | | | | ±20% | **GRM155R71H473ME14#** | |
| | | | 68000pF | ±10% | **GRM155R71H683KE14#** | |
| | | | | ±20% | **GRM155R71H683ME14#** | |
| | | | 0.10µF | ±10% | **GRM155R71H104KE14#** | |
| | | | | ±20% | **GRM155R71H104ME14#** | |
| | | R | 220pF | ±10% | **GRM155R11H221KA01#** | |
| | | | 330pF | ±10% | **GRM155R11H331KA01#** | |
| | | | 470pF | ±10% | **GRM155R11H471KA01#** | |
| | | | 680pF | ±10% | **GRM155R11H681KA01#** | |
| | | | 1000pF | ±10% | **GRM155R11H102KA01#** | |
| | | | 1500pF | ±10% | **GRM155R11H152KA01#** | |
| | | | 2200pF | ±10% | **GRM155R11H222KA01#** | |
| | | | 3300pF | ±10% | **GRM155R11H332KA01#** | |
| | | | 4700pF | ±10% | **GRM155R11H472KA01#** | |
| | | | 6800pF | ±10% | **GRM155R11H682KA88#** | |
| | | | 10000pF | ±10% | **GRM155R11H103KA88#** | |
| | | X5R | 33000pF | ±10% | **GRM155R61H333KE19#** | |
| | | | | ±20% | **GRM155R61H333ME19#** | |
| | | | 47000pF | ±10% | **GRM155R61H473KE19#** | |
| | | | | ±20% | **GRM155R61H473ME19#** | |
| | | | 68000pF | ±10% | **GRM155R61H683KE19#** | |
| | | | | ±20% | **GRM155R61H683ME19#** | |
| | | | 0.10µF | ±10% | **GRM155R61H104KE14#** | |
| | | | | ±20% | **GRM155R61H104ME14#** | |
| | | B | 220pF | ±10% | **GRM155B11H221KA01#** | |
| | | | | ±20% | **GRM155B11H221MA01#** | |
| | | | 330pF | ±10% | **GRM155B11H331KA01#** | |
| | | | | ±20% | **GRM155B11H331MA01#** | |
| | | | 470pF | ±10% | **GRM155B11H471KA01#** | |
| | | | | ±20% | **GRM155B11H471MA01#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | B | 680pF | ±10% | **GRM155B11H681KA01#** | |
| | | | | ±20% | **GRM155B11H681MA01#** | |
| | | | 1000pF | ±10% | **GRM155B11H102KA01#** | |
| | | | | ±20% | **GRM155B11H102MA01#** | |
| | | | 1500pF | ±10% | **GRM155B11H152KA01#** | |
| | | | | ±20% | **GRM155B11H152MA01#** | |
| | | | 2200pF | ±10% | **GRM155B11H222KA01#** | |
| | | | | ±20% | **GRM155B11H222MA01#** | |
| | | | 3300pF | ±10% | **GRM155B11H332KA01#** | |
| | | | | ±20% | **GRM155B11H332MA01#** | |
| | | | 4700pF | ±10% | **GRM155B11H472KA01#** | |
| | | | | ±20% | **GRM155B11H472MA01#** | |
| | | | 6800pF | ±10% | **GRM155B31H682KA88#** | |
| | | | | ±20% | **GRM155B31H682MA88#** | |
| | | | 10000pF | ±10% | **GRM155B31H103KA88#** | |
| | | | | ±20% | **GRM155B31H103MA88#** | |
| | | | 15000pF | ±10% | **GRM155B31H153KA12#** | |
| | | | | ±20% | **GRM155B31H153MA12#** | |
| | | | 22000pF | ±10% | **GRM155B31H223KA12#** | |
| | | | | ±20% | **GRM155B31H223MA12#** | |
| | | | 0.10μF | ±10% | **GRM155B31H104KE14#** | |
| | | | | ±20% | **GRM155B31H104ME14#** | |
| | 25Vdc | X7R | 10000pF | ±10% | **GRM155R71E103KA01#** | |
| | | | 15000pF | ±10% | **GRM155R71E153KA61#** | |
| | | | 22000pF | ±10% | **GRM155R71E223KA61#** | |
| | | | 33000pF | ±10% | **GRM155R71E333KA88#** | |
| | | | 47000pF | ±10% | **GRM155R71E473KA88#** | |
| | | | 68000pF | ±10% | **GRM155R71E683KE14#** | |
| | | | | ±20% | **GRM155R71E683ME14#** | |
| | | | 0.10μF | ±10% | **GRM155R71E104KE14#** | |
| | | | | ±20% | **GRM155R71E104ME14#** | |
| | | R | 6800pF | ±10% | **GRM155R11E682KA01#** | |
| | | | 10000pF | ±10% | **GRM155R11E103KA01#** | |
| | | | 15000pF | ±10% | **GRM155R11E153KA61#** | |
| | | | 22000pF | ±10% | **GRM155R11E223KA61#** | |
| | | | 33000pF | ±10% | **GRM155R11E333KA88#** | |
| | | | 47000pF | ±10% | **GRM155R11E473KA88#** | |
| | | X5R | 68000pF | ±10% | **GRM155R61E683KA87#** | |
| | | | | ±20% | **GRM155R61E683MA87#** | |
| | | | 0.10μF | ±10% | **GRM155R61E104KA87#** | |
| | | | | ±20% | **GRM155R61E104MA87#** | |
| | | | 0.47μF | ±10% | **GRM155R61E474KA12#** | Derating |
| | | | | ±20% | **GRM155R61E474MA12#** | Derating |
| | | | 1.0μF | ±10% | **GRM155R61E105KA12#** | Derating |
| | | | | ±20% | **GRM155R61E105MA12#** | Derating |
| | | B | 10000pF | ±10% | **GRM155B11E103KA01#** | |
| | | | | ±20% | **GRM155B11E103MA01#** | |
| | | | 15000pF | ±10% | **GRM155B11E153KA61#** | |
| | | | | ±20% | **GRM155B11E153MA61#** | |
| | | | 22000pF | ±10% | **GRM155B11E223KA61#** | |
| | | | | ±20% | **GRM155B11E223MA61#** | |
| | | | 33000pF | ±10% | **GRM155B31E333KA87#** | |
| | | | | ±20% | **GRM155B31E333MA87#** | |
| | | | 47000pF | ±10% | **GRM155B31E473KA87#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 25Vdc | B | 47000pF | ±20% | **GRM155B31E473MA87#** | |
| | | | 68000pF | ±10% | **GRM155B31E683KA87#** | |
| | | | | ±20% | **GRM155B31E683MA87#** | |
| | | | 0.10μF | ±10% | **GRM155B31E104KA87#** | |
| | | | | ±20% | **GRM155B31E104MA87#** | |
| | | | 1.0μF | ±10% | **GRM155B31E105KA12#** | Derating |
| | | | | ±20% | **GRM155B31E105MA12#** | Derating |
| | 16Vdc | X7R | 68000pF | ±10% | **GRM155R71C683KA88#** | |
| | | | 0.15μF | ±10% | **GRM155R71C154KA12#** | |
| | | | 0.22μF | ±10% | **GRM155R71C224KA12#** | |
| | | R | 68000pF | ±10% | **GRM155R11C683KA88#** | |
| | | X5R | 0.22μF | ±10% | **GRM155R61C224KA12#** | |
| | | | | ±20% | **GRM155R61C224MA12#** | |
| | | | 1.0μF | ±10% | **GRM155R61C105KA12#** | |
| | | | | ±20% | **GRM155R61C105MA12#** | |
| | | B | 1.0μF | ±10% | **GRM155B31C105KA12#** | |
| | | | | ±20% | **GRM155B31C105MA12#** | |
| | 10Vdc | X6S | 1.0μF | ±10% | **GRM155C81A105KA12#** | |
| | | | | ±20% | **GRM155C81A105MA12#** | |
| | | X5R | 0.15μF | ±10% | **GRM155R61A154KE19#** | |
| | | | | ±20% | **GRM155R61A154ME19#** | |
| | | | 0.22μF | ±10% | **GRM155R61A224KE19#** | |
| | | | | ±20% | **GRM155R61A224ME19#** | |
| | | | 0.33μF | ±10% | **GRM155R61A334KE15#** | |
| | | | | ±20% | **GRM155R61A334ME15#** | |
| | | | 0.47μF | ±10% | **GRM155R61A474KE15#** | |
| | | | | ±20% | **GRM155R61A474ME15#** | |
| | | | 0.68μF | ±10% | **GRM155R61A684KE15#** | |
| | | | | ±20% | **GRM155R61A684ME15#** | |
| | | B | 0.15μF | ±10% | **GRM155B31A154KE18#** | |
| | | | | ±20% | **GRM155B31A154ME18#** | |
| | | | 0.22μF | ±10% | **GRM155B31A224KE18#** | |
| | | | | ±20% | **GRM155B31A224ME18#** | |
| | | | 0.33μF | ±10% | **GRM155B31A334KE14#** | |
| | | | | ±20% | **GRM155B31A334ME14#** | |
| | | | 0.47μF | ±10% | **GRM155B31A474KE14#** | |
| | | | | ±20% | **GRM155B31A474ME14#** | |
| | | | 0.68μF | ±10% | **GRM155B31A684KE15#** | |
| | | | | ±20% | **GRM155B31A684ME15#** | |
| | | | 2.2μF | ±10% | **GRM155B31A225KE95#** | Derating |
| | | | | ±20% | **GRM155B31A225ME95#** | Derating |
| | 6.3Vdc | X7R | 1.0μF | ±10% | **GRM155R70J105KA12#** | Derating |
| | | | | ±20% | **GRM155R70J105MA12#** | Derating |
| | | X6S | 2.2μF | ±10% | **GRM155C80J225KE95#** | Derating |
| | | | | ±20% | **GRM155C80J225ME95#** | Derating |
| | | X5R | 0.15μF | ±10% | **GRM155R60J154KE01#** | |
| | | | | ±20% | **GRM155R60J154ME01#** | |
| | | | 0.22μF | ±10% | **GRM155R60J224KE01#** | |
| | | | | ±20% | **GRM155R60J224ME01#** | |
| | | | 0.33μF | ±10% | **GRM155R60J334KE01#** | |
| | | | | ±20% | **GRM155R60J334ME01#** | |
| | | | 0.47μF | ±10% | **GRM155R60J474KE19#** | |
| | | | | ±20% | **GRM155R60J474ME19#** | |
| | | | 0.68μF | ±10% | **GRM155R60J684KE19#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 6.3Vdc | X5R | 0.68μF | ±20% | GRM155R60J684ME19# | |
| | | B | 0.15μF | ±10% | GRM155B10J154KE01# | |
| | | | | ±20% | GRM155B10J154ME01# | |
| | | | 0.22μF | ±10% | GRM155B10J224KE01# | |
| | | | | ±20% | GRM155B10J224ME01# | |
| | | | 0.33μF | ±10% | GRM155B10J334KE01# | |
| | | | | ±20% | GRM155B10J334ME01# | |
| | | | 0.47μF | ±10% | GRM155B30J474KE18# | |
| | | | | ±20% | GRM155B30J474ME18# | |
| | | | 0.68μF | ±10% | GRM155B30J684KE18# | |
| | | | | ±20% | GRM155B30J684ME18# | |
| | | | 2.2μF | ±10% | GRM155B30J225KE95# | |
| | | | | ±20% | GRM155B30J225ME95# | |
| | 4Vdc | X7R | 1.0μF | ±10% | GRM155R70G105KA12# | |
| | | | | ±20% | GRM155R70G105MA12# | |
| 0.6mm | 35Vdc | X5R | 1.0μF | ±10% | GRM155R6YA105KE11# | Derating |
| | | | | ±20% | GRM155R6YA105ME11# | Derating |
| | 25Vdc | X6S | 1.0μF | ±10% | GRM155C81E105KE11# | Derating |
| | | | | ±20% | GRM155C81E105ME11# | Derating |
| | 16Vdc | X6S | 1.0μF | ±10% | GRM155C81C105KE11# | |
| | | | | ±20% | GRM155C81C105ME11# | |
| | 6.3Vdc | X5R | 4.7μF | ±20% | GRM155R60J475ME47# | Derating |
| | | B | 4.7μF | ±20% | GRM155B30J475ME47# | Derating |
| | 4Vdc | X5R | 4.7μF | ±20% | GRM155R60G475ME47# | |
| | | B | 4.7μF | ±20% | GRM155B30G475ME47# | |
| | 2.5Vdc | X6T | 4.7μF | ±20% | GRM155D80E475ME47# | Derating |
| 0.7mm | 25Vdc | X5R | 2.2μF | ±10% | GRM155R61E225KE11# | |
| | | | | ±20% | GRM155R61E225ME11# | |
| | 16Vdc | X6S | 2.2μF | ±10% | GRM155C81C225KE11# | |
| | | | | ±20% | GRM155C81C225ME11# | |
| | | X5R | 2.2μF | ±10% | GRM155R61C225KE11# | |
| | | | | ±20% | GRM155R61C225ME11# | |
| | 10Vdc | X7S | 2.2μF | ±10% | GRM155C71A225KE11# | |
| | | | | ±20% | GRM155C71A225ME11# | |
| | | X6S | 2.2μF | ±10% | GRM155C81A225KE11# | |
| | | | | ±20% | GRM155C81A225ME11# | |
| | 6.3Vdc | X7S | 2.2μF | ±10% | GRM155C70J225KE11# | |
| | | | | ±20% | GRM155C70J225ME11# | |
| | 4Vdc | X5R | 10μF | ±20% | GRM155R60G106ME44# | |
| | 2.5Vdc | X5R | 10μF | ±20% | GRM155R60E106ME16# | |

■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.5mm | 25Vdc | X5R | 1.0μF | ±10% | GRM185R61E105KA12# | Derating |
| | | | | ±20% | GRM185R61E105MA12# | Derating |
| | | B | 1.0μF | ±10% | GRM185B31E105KA12# | Derating |
| | | | | ±20% | GRM185B31E105MA12# | Derating |
| | 16Vdc | X5R | 1.0μF | ±10% | GRM185R61C105KE44# | |
| | | | | ±20% | GRM185R61C105ME44# | |
| | | B | 1.0μF | ±10% | GRM185B31C105KE43# | |
| | | | | ±20% | GRM185B31C105ME43# | |
| 0.9mm | 250Vdc | X7R | 220pF | ±10% | GRM188R72E221KW07# | |
| | | | 330pF | ±10% | GRM188R72E331KW07# | |
| | | | 470pF | ±10% | GRM188R72E471KW07# | |
| | | | 680pF | ±10% | GRM188R72E681KW07# | |
| | | | 1000pF | ±10% | GRM188R72E102KW07# | |
| | | | 1500pF | ±10% | GRM188R72E152KW07# | |
| | | | 2200pF | ±10% | GRM188R72E222KW07# | |
| | 200Vdc | X7R | 220pF | ±10% | GRM188R72D221KW07# | |
| | | | 330pF | ±10% | GRM188R72D331KW07# | |
| | | | 470pF | ±10% | GRM188R72D471KW07# | |
| | | | 680pF | ±10% | GRM188R72D681KW07# | |
| | | | 1000pF | ±10% | GRM188R72D102KW07# | |
| | | | 1500pF | ±10% | GRM188R72D152KW07# | |
| | | | 2200pF | ±10% | GRM188R72D222KW07# | |
| | 100Vdc | X7R | 220pF | ±10% | GRM188R72A221KA01# | |
| | | | 330pF | ±10% | GRM188R72A331KA01# | |
| | | | 470pF | ±10% | GRM188R72A471KA01# | |
| | | | 680pF | ±10% | GRM188R72A681KA01# | |
| | | | 1000pF | ±10% | GRM188R72A102KA01# | |
| | | | 1500pF | ±10% | GRM188R72A152KA01# | |
| | | | 2200pF | ±10% | GRM188R72A222KA01# | |
| | | | 3300pF | ±10% | GRM188R72A332KA01# | |
| | | | 4700pF | ±10% | GRM188R72A472KA01# | |
| | | | 6800pF | ±10% | GRM188R72A682KA01# | |
| | | | 10000pF | ±10% | GRM188R72A103KA01# | |
| | | | 15000pF | ±10% | GRM188R72A153KAC4# | |
| | | | | ±20% | GRM188R72A153MAC4# | |
| | | | 22000pF | ±10% | GRM188R72A223KAC4# | |
| | | | | ±20% | GRM188R72A223MAC4# | |
| | 50Vdc | X7R | 220pF | ±10% | GRM188R71H221KA01# | |
| | | | 330pF | ±10% | GRM188R71H331KA01# | |
| | | | 470pF | ±10% | GRM188R71H471KA01# | |
| | | | 680pF | ±10% | GRM188R71H681KA01# | |
| | | | 1000pF | ±10% | GRM188R71H102KA01# | |
| | | | 1500pF | ±10% | GRM188R71H152KA01# | |
| | | | 2200pF | ±10% | GRM188R71H222KA01# | |
| | | | 3300pF | ±10% | GRM188R71H332KA01# | |
| | | | 4700pF | ±10% | GRM188R71H472KA01# | |
| | | | 6800pF | ±10% | GRM188R71H682KA01# | |
| | | | 10000pF | ±10% | GRM188R71H103KA01# | |
| | | | 15000pF | ±10% | GRM188R71H153KA01# | |
| | | | 22000pF | ±10% | GRM188R71H223KA01# | |
| | | | 33000pF | ±10% | GRM188R71H333KA61# | |
| | | | 47000pF | ±10% | GRM188R71H473KA61# | |
| | | | 68000pF | ±10% | GRM188R71H683KA93# | |
| | | | 0.10μF | ±10% | GRM188R71H104KA93# | |
| | | R | 220pF | ±10% | GRM188R11H221KA01# | |
| | | | 330pF | ±10% | GRM188R11H331KA01# | |
| | | | 470pF | ±10% | GRM188R11H471KA01# | |
| | | | 680pF | ±10% | GRM188R11H681KA01# | |
| | | | 1000pF | ±10% | GRM188R11H102KA01# | |
| | | | 1500pF | ±10% | GRM188R11H152KA01# | |
| | | | 2200pF | ±10% | GRM188R11H222KA01# | |
| | | | 3300pF | ±10% | GRM188R11H332KA01# | |
| | | | 4700pF | ±10% | GRM188R11H472KA01# | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 50Vdc | R | 6800pF | ±10% | **GRM188R11H682KA01#** |
| | | | 10000pF | ±10% | **GRM188R11H103KA01#** |
| | | | 15000pF | ±10% | **GRM188R11H153KA01#** |
| | | | 22000pF | ±10% | **GRM188R11H223KA01#** |
| | | | 33000pF | ±10% | **GRM188R11H333KA61#** |
| | | | 47000pF | ±10% | **GRM188R11H473KA61#** |
| | | | 68000pF | ±10% | **GRM188R11H683KA93#** |
| | | | 0.10μF | ±10% | **GRM188R11H104KA93#** |
| | | X5R | 0.47μF | ±10% | **GRM188R61H474KA12#** |
| | | | | ±20% | **GRM188R61H474MA12#** |
| | | | 1.0μF | ±10% | **GRM188R61H105KAAL#** |
| | | | | ±20% | **GRM188R61H105MAAL#** |
| | | B | 220pF | ±10% | **GRM188B11H221KA01#** |
| | | | | ±20% | **GRM188B11H221MA01#** |
| | | | 330pF | ±10% | **GRM188B11H331KA01#** |
| | | | | ±20% | **GRM188B11H331MA01#** |
| | | | 470pF | ±10% | **GRM188B11H471KA01#** |
| | | | | ±20% | **GRM188B11H471MA01#** |
| | | | 680pF | ±10% | **GRM188B11H681KA01#** |
| | | | | ±20% | **GRM188B11H681MA01#** |
| | | | 1000pF | ±10% | **GRM188B11H102KA01#** |
| | | | | ±20% | **GRM188B11H102MA01#** |
| | | | 1500pF | ±10% | **GRM188B11H152KA01#** |
| | | | | ±20% | **GRM188B11H152MA01#** |
| | | | 2200pF | ±10% | **GRM188B11H222KA01#** |
| | | | | ±20% | **GRM188B11H222MA01#** |
| | | | 3300pF | ±10% | **GRM188B11H332KA01#** |
| | | | | ±20% | **GRM188B11H332MA01#** |
| | | | 4700pF | ±10% | **GRM188B11H472KA01#** |
| | | | | ±20% | **GRM188B11H472MA01#** |
| | | | 6800pF | ±10% | **GRM188B11H682KA01#** |
| | | | | ±20% | **GRM188B11H682MA01#** |
| | | | 10000pF | ±10% | **GRM188B11H103KA01#** |
| | | | | ±20% | **GRM188B11H103MA01#** |
| | | | 15000pF | ±10% | **GRM188B11H153KA01#** |
| | | | | ±20% | **GRM188B11H153MA01#** |
| | | | 22000pF | ±10% | **GRM188B11H223KA01#** |
| | | | | ±20% | **GRM188B11H223MA01#** |
| | | | 33000pF | ±10% | **GRM188B11H333KA61#** |
| | | | | ±20% | **GRM188B11H333MA61#** |
| | | | 47000pF | ±10% | **GRM188B11H473KA61#** |
| | | | | ±20% | **GRM188B11H473MA61#** |
| | | | 68000pF | ±10% | **GRM188B31H683KA92#** |
| | | | | ±20% | **GRM188B31H683MA92#** |
| | | | 0.10μF | ±10% | **GRM188B31H104KA92#** |
| | | | | ±20% | **GRM188B31H104MA92#** |
| | | | 1.0μF | ±10% | **GRM188B31H105KAAL#** |
| | | | | ±20% | **GRM188B31H105MAAL#** |
| | 25Vdc | X7R | 33000pF | ±10% | **GRM188R71E333KA01#** |
| | | | 47000pF | ±10% | **GRM188R71E473KA01#** |
| | | | 68000pF | ±10% | **GRM188R71E683KA01#** |
| | | | 0.15μF | ±10% | **GRM188R71E154KA01#** |
| | | | 0.22μF | ±10% | **GRM188R71E224KA88#** |
| | | | 1.0μF | ±10% | **GRM188R71E105KA12#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 25Vdc | X7R | 1.0μF | ±20% | **GRM188R71E105MA12#** |
| | | R | 33000pF | ±10% | **GRM188R11E333KA01#** |
| | | | 47000pF | ±10% | **GRM188R11E473KA01#** |
| | | | 68000pF | ±10% | **GRM188R11E683KA01#** |
| | | | 0.15μF | ±10% | **GRM188R11E154KA01#** |
| | | | 0.22μF | ±10% | **GRM188R11E224KA88#** |
| | | X5R | 0.22μF | ±10% | **GRM188R61E224KA88#** |
| | | | 0.47μF | ±10% | **GRM188R61E474KA12#** |
| | | | | ±20% | **GRM188R61E474MA12#** |
| | | | 0.68μF | ±10% | **GRM188R61E684KA75#** |
| | | | | ±20% | **GRM188R61E684MA75#** |
| | | | 1.0μF | ±10% | **GRM188R61E105KA12#** |
| | | | | ±20% | **GRM188R61E105MA12#** |
| | | | 2.2μF | ±10% | **GRM188R61E225KA12#** |
| | | | | ±20% | **GRM188R61E225MA12#** |
| | | B | 10000pF | ±10% | **GRM188B11E103KA01#** |
| | | | | ±20% | **GRM188B11E103MA01#** |
| | | | 15000pF | ±10% | **GRM188B11E153KA01#** |
| | | | | ±20% | **GRM188B11E153MA01#** |
| | | | 22000pF | ±10% | **GRM188B11E223KA01#** |
| | | | | ±20% | **GRM188B11E223MA01#** |
| | | | 33000pF | ±10% | **GRM188B11E333KA01#** |
| | | | | ±20% | **GRM188B11E333MA01#** |
| | | | 47000pF | ±10% | **GRM188B11E473KA01#** |
| | | | | ±20% | **GRM188B11E473MA01#** |
| | | | 68000pF | ±10% | **GRM188B11E683KA01#** |
| | | | | ±20% | **GRM188B11E683MA01#** |
| | | | 0.10μF | ±10% | **GRM188B11E104KA01#** |
| | | | | ±20% | **GRM188B11E104MA01#** |
| | | | 0.15μF | ±10% | **GRM188B11E154KA01#** |
| | | | 0.22μF | ±10% | **GRM188B31E224KA87#** |
| | | | 0.47μF | ±10% | **GRM188B31E474KA75#** |
| | | | | ±20% | **GRM188B31E474MA75#** |
| | | | 0.68μF | ±10% | **GRM188B31E684KA75#** |
| | | | | ±20% | **GRM188B31E684MA75#** |
| | | | 1.0μF | ±10% | **GRM188B31E105KA75#** |
| | | | | ±20% | **GRM188B31E105MA75#** |
| | | | 2.2μF | ±10% | **GRM188B31E225KA12#** |
| | | | | ±20% | **GRM188B31E225MA12#** |
| | 16Vdc | X7R | 0.15μF | ±10% | **GRM188R71C154KA01#** |
| | | | 0.22μF | ±10% | **GRM188R71C224KA01#** |
| | | | 0.33μF | ±10% | **GRM188R71C334KA01#** |
| | | | 0.47μF | ±10% | **GRM188R71C474KA88#** |
| | | | 1.0μF | ±10% | **GRM188R71C105KE15#** |
| | | | | ±20% | **GRM188R71C105ME15#** |
| | | R | 0.33μF | ±10% | **GRM188R11C334KA01#** |
| | | | 0.47μF | ±10% | **GRM188R11C474KA88#** |
| | | X6S | 2.2μF | ±10% | **GRM188C81C225KA12#** |
| | | | | ±20% | **GRM188C81C225MA12#** |
| | | X5R | 0.68μF | ±10% | **GRM188R61C684KA75#** |
| | | | | ±20% | **GRM188R61C684MA75#** |
| | | | 2.2μF | ±10% | **GRM188R61C225KE15#** |
| | | B | 0.33μF | ±10% | **GRM188B11C334KA01#** |
| | | | | ±20% | **GRM188B11C334MA01#** |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.9mm | 16Vdc | B | 0.68μF | ±10% | GRM188B31C684KA75# | |
| | | | | ±20% | GRM188B31C684MA75# | |
| | | | 2.2μF | ±10% | GRM188B31C225KE14# | |
| | 10Vdc | X7R | 0.33μF | ±10% | GRM188R71A334KA61# | |
| | | | | ±20% | GRM188R71A334MA61# | |
| | | | 0.68μF | ±10% | GRM188R71A684KA61# | |
| | | | | ±20% | GRM188R71A684MA61# | |
| | | | 2.2μF | ±10% | GRM188R71A225KE15# | |
| | | | | ±20% | GRM188R71A225ME15# | |
| | | X7T | 2.2μF | ±10% | GRM188D71A225KE34# | |
| | | | | ±20% | GRM188D71A225ME34# | |
| | | X5R | 0.33μF | ±10% | GRM188R61A334KA61# | |
| | | | | ±20% | GRM188R61A334MA61# | |
| | | B | 0.33μF | ±10% | GRM188B11A334KA61# | |
| | | | | ±20% | GRM188B11A334MA61# | |
| | 6.3Vdc | B | 10μF | ±20% | GRM188B30J106ME47# | |
| 0.95mm | 25Vdc | X5R | 4.7μF | ±10% | GRM188R61E475KE11# | |
| | | | | ±20% | GRM188R61E475ME11# | |
| | 16Vdc | X6S | 4.7μF | ±10% | GRM188C81C475KE11# | |
| | | | | ±20% | GRM188C81C475ME11# | |
| | | X5R | 4.7μF | ±10% | GRM188R61C475KE11# | |
| | | | | ±20% | GRM188R61C475ME11# | |
| | | | 10μF | ±10% | GRM188R61C106KAAL# | |
| | | | | ±20% | GRM188R61C106MAAL# | |
| | | B | 4.7μF | ±10% | GRM188B31C475KAAJ# | Derating |
| | | | | ±20% | GRM188B31C475MAAJ# | Derating |
| | 10Vdc | X7S | 4.7μF | ±10% | GRM188C71A475KE11# | |
| | | | | ±20% | GRM188C71A475ME11# | |
| | | B | 10μF | ±20% | GRM188B31A106ME69# | Derating |
| 1.0mm | 50Vdc | X5R | 2.2μF | ±10% | GRM188R61H225KE11# | |
| | | | | ±20% | GRM188R61H225ME11# | |
| | 35Vdc | X6S | 2.2μF | ±10% | GRM188C8YA225KE11# | |
| | | | | ±20% | GRM188C8YA225ME11# | |
| | | X5R | 4.7μF | ±10% | GRM188R6YA475KE15# | |
| | | | | ±20% | GRM188R6YA475ME15# | |
| | 25Vdc | X7S | 2.2μF | ±10% | GRM188C71E225KE11# | |
| | | | | ±20% | GRM188C71E225ME11# | |
| | | X6S | 2.2μF | ±10% | GRM188C81E225KE11# | |
| | | | | ±20% | GRM188C81E225ME11# | |
| | | | 4.7μF | ±10% | GRM188C81E475KE11# | Derating |
| | | | | ±20% | GRM188C81E475ME11# | Derating |
| | | X5R | 10μF | ±20% | GRM188R61E106MA73# | |
| | 16Vdc | X7S | 2.2μF | ±10% | GRM188C71C225KE11# | |
| | | | | ±20% | GRM188C71C225ME11# | |
| | | X6S | 10μF | ±20% | GRM188C81C106MA73# | |
| | 10Vdc | X7T | 10μF | ±20% | GRM188D71A106MA73# | |
| | 6.3Vdc | X7T | 10μF | ±20% | GRM188D70J106MA73# | |
| | | X5R | 22μF | ±20% | GRM188R60J226MEA0# | Derating |
| | | B | 22μF | ±20% | GRM188B30J226MEA0# | Derating |
| | 4Vdc | X6S | 22μF | ±20% | GRM188C80G226MEA0# | Derating |
| | | X5R | 22μF | ±20% | GRM188R60G226MEA0# | |
| | | B | 22μF | ±20% | GRM188B30G226MEA0# | |

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.7mm | 16Vdc | X6S | 1.0μF | ±10% | GRM216C81C105KA12# | |
| 0.95mm | 100Vdc | X7R | 10000pF | ±10% | GRM219R72A103KA01# | |
| | | | | ±20% | GRM219R72A103MA01# | |
| | 50Vdc | X7R | 10000pF | ±10% | GRM219R71H103KA01# | |
| | | | | ±20% | GRM219R71H103MA01# | |
| | | | 15000pF | ±10% | GRM219R71H153KA01# | |
| | | | | ±20% | GRM219R71H153MA01# | |
| | | | 33000pF | ±10% | GRM219R71H333KA01# | |
| | | | 0.33μF | ±10% | GRM219R71H334KA88# | |
| | | R | 33000pF | ±10% | GRM219R11H333KA01# | |
| | | X5R | 1.0μF | ±10% | GRM219R61H105KA73# | |
| | | | | ±20% | GRM219R61H105MA73# | |
| | | | 2.2μF | ±10% | GRM219R61H225KE15# | |
| | | | | ±20% | GRM219R61H225ME15# | |
| | | B | 0.33μF | ±10% | GRM219B31H334KA87# | |
| | | | | ±20% | GRM219B31H334MA87# | |
| | | | 1.0μF | ±10% | GRM219B31H105KA73# | |
| | | | | ±20% | GRM219B31H105MA73# | |
| | | | 2.2μF | ±10% | GRM219B31H225KE15# | |
| | | | | ±20% | GRM219B31H225ME15# | |
| | 35Vdc | X6S | 2.2μF | ±10% | GRM219C8YA225KE15# | |
| | | | | ±20% | GRM219C8YA225ME15# | |
| | | X5R | 4.7μF | ±10% | GRM219R6YA475KA73# | Derating |
| | | | | ±20% | GRM219R6YA475MA73# | Derating |
| | 25Vdc | X7R | 0.10μF | ±10% | GRM219R71E104KA01# | |
| | | | | ±20% | GRM219R71E104MA01# | |
| | | | 0.68μF | ±10% | GRM219R71E684KA88# | |
| | | | 1.0μF | ±10% | GRM219R71E105KA88# | |
| | | R | 68000pF | ±10% | GRM219R11E683KA01# | |
| | | X6S | 2.2μF | ±10% | GRM219C81E225KE15# | |
| | | | | ±20% | GRM219C81E225ME15# | |
| | | X5R | 2.2μF | ±10% | GRM219R61E225KA12# | |
| | | | | ±20% | GRM219R61E225MA12# | |
| | | | 4.7μF | ±10% | GRM219R61E475KA73# | |
| | | | | ±20% | GRM219R61E475MA73# | |
| | | | 10μF | ±10% | GRM219R61E106KA12# | Derating |
| | | | | ±20% | GRM219R61E106MA12# | Derating |
| | | B | 2.2μF | ±10% | GRM219B31E225KA75# | |
| | | | | ±20% | GRM219B31E225MA75# | |
| | | | 10μF | ±10% | GRM219B31E106KA12# | Derating |
| | | | | ±20% | GRM219B31E106MA12# | Derating |
| | 16Vdc | X7R | 0.33μF | ±10% | GRM219R71C334KA88# | |
| | | | 2.2μF | ±10% | GRM219R71C225KE15# | |
| | | | | ±20% | GRM219R71C225ME15# | |
| | | R | 0.68μF | ±10% | GRM219R11C684KA01# | |
| | | X6S | 4.7μF | ±10% | GRM219C81C475KA73# | |
| | | | | ±20% | GRM219C81C475MA73# | |
| | | X5R | 4.7μF | ±10% | GRM219R61C475KE15# | |
| | | | 10μF | ±10% | GRM219R61C106KA73# | |
| | | | | ±20% | GRM219R61C106MA73# | |
| | | B | 4.7μF | ±10% | GRM219B31C475KE15# | |
| | | | 10μF | ±10% | GRM219B31C106KA73# | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.95mm | 16Vdc | B | 10µF | ±20% | **GRM219B31C106MA73#** | |
| | 10Vdc | X7R | 2.2µF | ±10% | **GRM219R71A225KE15#** | |
| | | | | ±20% | **GRM219R71A225ME15#** | |
| | | X7T | 4.7µF | ±10% | **GRM219D71A475KE15#** | Derating |
| | | | | ±20% | **GRM219D71A475ME15#** | Derating |
| | | X5R | 22µF | ±20% | **GRM219R61A226MEA0#** | Derating |
| | | B | 22µF | ±20% | **GRM219B31A226MEA0#** | Derating |
| | 6.3Vdc | X6S | 10µF | ±10% | **GRM219C80J106KE39#** | |
| | | | | ±20% | **GRM219C80J106ME39#** | |
| | | X5R | 22µF | ±20% | **GRM219R60J226ME47#** | Derating |
| | | B | 22µF | ±20% | **GRM219B30J226ME47#** | Derating |
| | 4Vdc | X6S | 10µF | ±10% | **GRM219C80G106KE19#** | |
| | | | | ±20% | **GRM219C80G106ME19#** | |
| | | X5R | 47µF | ±20% | **GRM219R60G476ME44#** | Derating |
| | 2.5Vdc | X6T | 47µF | ±20% | **GRM219D80E476ME44#** | |
| 1.0mm | 250Vdc | X7R | 1000pF | ±10% | **GRM21AR72E102KW01#** | |
| | | | 1500pF | ±10% | **GRM21AR72E152KW01#** | |
| | | | 2200pF | ±10% | **GRM21AR72E222KW01#** | |
| | | | 3300pF | ±10% | **GRM21AR72E332KW01#** | |
| | | | 4700pF | ±10% | **GRM21AR72E472KW01#** | |
| | | | 6800pF | ±10% | **GRM21AR72E682KW01#** | |
| | 200Vdc | X7R | 1000pF | ±10% | **GRM21AR72D102KW01#** | |
| | | | 1500pF | ±10% | **GRM21AR72D152KW01#** | |
| | | | 2200pF | ±10% | **GRM21AR72D222KW01#** | |
| | | | 3300pF | ±10% | **GRM21AR72D332KW01#** | |
| | | | 4700pF | ±10% | **GRM21AR72D472KW01#** | |
| | | | 6800pF | ±10% | **GRM21AR72D682KW01#** | |
| | 50Vdc | X7R | 22000pF | ±10% | **GRM219R71H223KA17#** | |
| | | | | ±20% | **GRM219R71H223MA17#** | |
| | 16Vdc | X5R | 22µF | ±20% | **GRM219R61C226ME15#** | Derating |
| 1.35mm | 100Vdc | X7R | 10000pF | ±10% | **GRM21BR72A103KA01#** | |
| | | | 15000pF | ±10% | **GRM21BR72A153KA01#** | |
| | | | 22000pF | ±10% | **GRM21BR72A223KA01#** | |
| | | | 33000pF | ±10% | **GRM21BR72A333KA01#** | |
| | | | 47000pF | ±10% | **GRM21BR72A473KA01#** | |
| | | | 68000pF | ±10% | **GRM21BR72A683KAC4#** | |
| | | | | ±20% | **GRM21BR72A683MAC4#** | |
| | | | 0.10µF | ±10% | **GRM21BR72A104KAC4#** | |
| | | | | ±20% | **GRM21BR72A104MAC4#** | |
| | 50Vdc | X7R | 47000pF | ±10% | **GRM21BR71H473KA01#** | |
| | | | 68000pF | ±10% | **GRM21BR71H683KA01#** | |
| | | | 0.10µF | ±10% | **GRM21BR71H104KA01#** | |
| | | | | ±20% | **GRM21BR71H104MA01#** | |
| | | | 0.15µF | ±10% | **GRM21BR71H154KA01#** | |
| | | | 0.22µF | ±10% | **GRM21BR71H224KA01#** | |
| | | | 0.47µF | ±10% | **GRM21BR71H474KA88#** | |
| | | R | 0.10µF | ±10% | **GRM21BR11H104KA01#** | |
| | | | | ±20% | **GRM21BR11H104MA01#** | |
| | | B | 0.15µF | ±10% | **GRM21BB31H154KA88#** | |
| | | | | ±20% | **GRM21BB31H154MA88#** | |
| | | | 0.22µF | ±10% | **GRM21BB31H224KA88#** | |
| | | | | ±20% | **GRM21BB31H224MA88#** | |
| | | | 0.47µF | ±10% | **GRM21BB31H474KA87#** | |
| | | | | ±20% | **GRM21BB31H474MA87#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.35mm | 25Vdc | R | 0.15µF | ±10% | **GRM21BR11E154KA01#** | |
| | | | | ±20% | **GRM21BR11E154MA01#** | |
| | | X6S | 4.7µF | ±10% | **GRM21BC81E475KA12#** | |
| | | | | ±20% | **GRM21BC81E475MA12#** | |
| | | X5R | 4.7µF | ±10% | **GRM21BR61E475KA12#** | |
| | | | | ±20% | **GRM21BR61E475MA12#** | |
| | | B | 2.2µF | ±10% | **GRM21BB31E225KA75#** | |
| | | | | ±20% | **GRM21BB31E225MA75#** | |
| | | | 4.7µF | ±10% | **GRM21BB31E475KA75#** | |
| | | | | ±20% | **GRM21BB31E475MA75#** | |
| | 16Vdc | X7R | 2.2µF | ±10% | **GRM21BR71C225KA12#** | |
| | | | | ±20% | **GRM21BR71C225MA12#** | |
| | | X5R | 10µF | ±10% | **GRM21BR61C106KE15#** | |
| | | | | ±20% | **GRM21BR61C106ME15#** | |
| | | B | 10µF | ±10% | **GRM21BB31C106KE15#** | |
| | | | | ±20% | **GRM21BB31C106ME15#** | |
| 1.4mm | 50Vdc | X5R | 2.2µF | ±10% | **GRM21BR61H225KA73#** | |
| | | | | ±20% | **GRM21BR61H225MA73#** | |
| | | | 4.7µF | ±10% | **GRM21BR61H475KE51#** | |
| | | | | ±20% | **GRM21BR61H475ME51#** | |
| | | B | 2.2µF | ±10% | **GRM21BB31H225KA73#** | |
| | | | | ±20% | **GRM21BB31H225MA73#** | |
| | | | 4.7µF | ±10% | **GRM21BB31H475KE51#** | |
| | | | | ±20% | **GRM21BB31H475ME51#** | |
| | 25Vdc | X7R | 1.0µF | ±10% | **GRM21BR71E105KA99#** | |
| | | | 4.7µF | ±10% | **GRM21BR71E475KA73#** | Derating |
| | | | | ±20% | **GRM21BR71E475MA73#** | Derating |
| | | R | 1.0µF | ±10% | **GRM21BR11E105KA99#** | |
| | | X5R | 10µF | ±10% | **GRM21BR61E106KA73#** | |
| | | | | ±20% | **GRM21BR61E106MA73#** | |
| | | B | 10µF | ±10% | **GRM21BB31E106KA73#** | |
| | | | | ±20% | **GRM21BB31E106MA73#** | |
| | 16Vdc | X7R | 4.7µF | ±10% | **GRM21BR71C475KA73#** | |
| | | | | ±20% | **GRM21BR71C475MA73#** | |
| | | X6S | 10µF | ±10% | **GRM21BC81C106KA73#** | |
| | | | | ±20% | **GRM21BC81C106MA73#** | |
| | 10Vdc | X7R | 4.7µF | ±10% | **GRM21BR71A475KA73#** | |
| | | | | ±20% | **GRM21BR71A475MA73#** | |
| | | | 10µF | ±10% | **GRM21BR71A106KE51#** | |
| | | | | ±20% | **GRM21BR71A106ME51#** | |
| | | B | 22µF | ±20% | **GRM21BB31A226ME51#** | Derating |
| | 6.3Vdc | X7R | 10µF | ±10% | **GRM21BR70J106KE76#** | |
| | | | | ±20% | **GRM21BR70J106ME76#** | |
| | | X6S | 22µF | ±20% | **GRM21BC80J226ME51#** | Derating |
| | 4Vdc | X7U | 22µF | ±20% | **GRM21BE70G226ME51#** | |
| | | X6S | 22µF | ±20% | **GRM21BC80G226ME39#** | |
| 1.45mm | 250Vdc | X7R | 10000pF | ±10% | **GRM21BR72E103KW03#** | |
| | | | 15000pF | ±10% | **GRM21BR72E153KW03#** | |
| | | | 22000pF | ±10% | **GRM21BR72E223KW03#** | |
| | 200Vdc | X7R | 10000pF | ±10% | **GRM21BR72D103KW03#** | |
| | | | 15000pF | ±10% | **GRM21BR72D153KW03#** | |
| | | | 22000pF | ±10% | **GRM21BR72D223KW03#** | |
| | 25Vdc | X6S | 10µF | ±10% | **GRM21BC81E106KE11#** | Derating |
| | | | | ±20% | **GRM21BC81E106ME11#** | Derating |

Part number # indicates the package specification code.



muRata

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.45mm | 25Vdc | X5R | 22μF | ±20% | **GRM21BR61E226ME44#** | |
| | 16Vdc | X7S | 10μF | ±10% | **GRM21BC71C106KE11#** | |
| | | | | ±20% | **GRM21BC71C106ME11#** | |
| | | X6S | 22μF | ±20% | **GRM21BC81C226ME44#** | Derating |
| | | X5R | 22μF | ±20% | **GRM21BR61C226ME44#** | |
| | 10Vdc | X7T | 22μF | ±20% | **GRM21BD71A226ME44#** | Derating |
| | | X6S | 22μF | ±20% | **GRM21BC81A226ME44#** | |
| | | X5R | 22μF | ±20% | **GRM21BR61A226ME44#** | |
| | 6.3Vdc | X7T | 22μF | ±20% | **GRM21BD70J226ME44#** | |
| | | X5R | 47μF | ±20% | **GRM21BR60J476ME15#** | Derating |
| | | B | 47μF | ±20% | **GRM21BB30J476ME15#** | Derating |
| | 4Vdc | X6S | 47μF | ±20% | **GRM21BC80G476ME15#** | Derating |
| | | X5R | 47μF | ±20% | **GRM21BR60G476ME15#** | |
| | | B | 47μF | ±20% | **GRM21BB30G476ME15#** | |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.95mm | 35Vdc | X5R | 10μF | ±10% | **GRM319R6YA106KA12#** | Derating |
| | | | | ±20% | **GRM319R6YA106MA12#** | Derating |
| | 25Vdc | R | 0.33μF | ±10% | **GRM319R11E334KA01#** | |
| | 16Vdc | X5R | 10μF | ±10% | **GRM319R61C106KE15#** | |
| | | | | ±20% | **GRM319R61C106ME15#** | |
| | | | 22μF | ±20% | **GRM319R61C226ME15#** | Derating |
| | | B | 10μF | ±10% | **GRM319B31C106KE15#** | |
| | | | | ±20% | **GRM319B31C106ME15#** | |
| | | | 22μF | ±20% | **GRM319B31C226ME15#** | Derating |
| | 10Vdc | X5R | 22μF | ±20% | **GRM319R61A226ME15#** | |
| | | B | 22μF | ±20% | **GRM319B31A226ME15#** | |
| | 6.3Vdc | X6S | 22μF | ±20% | **GRM319C80J226ME15#** | |
| | | X5R | 22μF | ±20% | **GRM319R60J226ME15#** | |
| | | B | 22μF | ±20% | **GRM319B30J226ME15#** | |
| 1.0mm | 630Vdc | X7R | 1000pF | ±10% | **GRM31AR72J102KW01#** | |
| | | | 1500pF | ±10% | **GRM31AR72J152KW01#** | |
| | | | 2200pF | ±10% | **GRM31AR72J222KW01#** | |
| | | | 3300pF | ±10% | **GRM31AR72J332KW01#** | |
| | | | 4700pF | ±10% | **GRM31AR72J472KW01#** | |
| | 500Vdc | X7R | 1000pF | ±10% | **GRM31AR72H102KW01#** | |
| | | | 1500pF | ±10% | **GRM31AR72H152KW01#** | |
| | | | 2200pF | ±10% | **GRM31AR72H222KW01#** | |
| | | | 3300pF | ±10% | **GRM31AR72H332KW01#** | |
| | | | 4700pF | ±10% | **GRM31AR72H472KW01#** | |
| 1.25mm | 1000Vdc | X7R | 470pF | ±10% | **GRM31BR73A471KW01#** | |
| | | | 680pF | ±10% | **GRM31BR73A681KW01#** | |
| | | | 1000pF | ±10% | **GRM31BR73A102KW01#** | |
| | | | 1500pF | ±10% | **GRM31BR73A152KW01#** | |
| | | | 2200pF | ±10% | **GRM31BR73A222KW01#** | |
| | | | 3300pF | ±10% | **GRM31BR73A332KW01#** | |
| | | | 4700pF | ±10% | **GRM31BR73A472KW01#** | |
| | 630Vdc | X7R | 1000pF | ±10% | **GRM31BR72J102KW01#** | |
| | | | 1500pF | ±10% | **GRM31BR72J152KW01#** | |
| | | | 2200pF | ±10% | **GRM31BR72J222KW01#** | |
| | | | 3300pF | ±10% | **GRM31BR72J332KW01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.25mm | 630Vdc | X7R | 4700pF | ±10% | **GRM31BR72J472KW01#** | |
| | | | 6800pF | ±10% | **GRM31BR72J682KW01#** | |
| | | | 10000pF | ±10% | **GRM31BR72J103KW01#** | |
| | 500Vdc | X7R | 1000pF | ±10% | **GRM31BR72H102KW01#** | |
| | | | 1500pF | ±10% | **GRM31BR72H152KW01#** | |
| | | | 2200pF | ±10% | **GRM31BR72H222KW01#** | |
| | | | 3300pF | ±10% | **GRM31BR72H332KW01#** | |
| | | | 4700pF | ±10% | **GRM31BR72H472KW01#** | |
| | | | 6800pF | ±10% | **GRM31BR72H682KW01#** | |
| | | | 10000pF | ±10% | **GRM31BR72H103KW01#** | |
| | 250Vdc | X7R | 15000pF | ±10% | **GRM31BR72E153KW01#** | |
| | | | 22000pF | ±10% | **GRM31BR72E223KW01#** | |
| | | | 68000pF | ±10% | **GRM31BR72E683KW01#** | |
| | 200Vdc | X7R | 15000pF | ±10% | **GRM31BR72D153KW01#** | |
| | | | 22000pF | ±10% | **GRM31BR72D223KW01#** | |
| | | | 68000pF | ±10% | **GRM31BR72D683KW01#** | |
| | 50Vdc | X7R | 0.47μF | ±10% | **GRM31MR71H474KA01#** | |
| | | | 0.68μF | ±10% | **GRM31MR71H684KA88#** | |
| | | | 1.0μF | ±10% | **GRM31MR71H105KA88#** | |
| | | B | 1.0μF | ±10% | **GRM31MB31H105KA87#** | |
| | 25Vdc | X5R | 10μF | ±20% | **GRM31MR61E106MA12#** | |
| 1.8mm | 1000Vdc | X7R | 6800pF | ±10% | **GRM31CR73A682KW03#** | |
| | | | 10000pF | ±10% | **GRM31CR73A103KW03#** | |
| | 630Vdc | X7R | 15000pF | ±10% | **GRM31CR72J153KW03#** | |
| | | | 22000pF | ±10% | **GRM31CR72J223KW03#** | |
| | 500Vdc | X7R | 15000pF | ±10% | **GRM31CR72H153KW03#** | |
| | | | 22000pF | ±10% | **GRM31CR72H223KW03#** | |
| | 250Vdc | X7R | 33000pF | ±10% | **GRM31CR72E333KW03#** | |
| | | | 47000pF | ±10% | **GRM31CR72E473KW03#** | |
| | | | 0.10μF | ±10% | **GRM31CR72E104KW03#** | |
| | 200Vdc | X7R | 33000pF | ±10% | **GRM31CR72D333KW03#** | |
| | | | 47000pF | ±10% | **GRM31CR72D473KW03#** | |
| | | | 0.10μF | ±10% | **GRM31CR72D104KW03#** | |
| | 50Vdc | X7R | 2.2μF | ±10% | **GRM31CR71H225KA88#** | |
| | | | 4.7μF | ±10% | **GRM31CR71H475KA12#** | |
| | | | | ±20% | **GRM31CR71H475MA12#** | |
| | | X5R | 10μF | ±10% | **GRM31CR61H106KA12#** | |
| | | | | ±20% | **GRM31CR61H106MA12#** | |
| | | B | 2.2μF | ±10% | **GRM31CB31H225KA87#** | |
| | | | | ±20% | **GRM31CB31H225MA87#** | |
| | | | 4.7μF | ±10% | **GRM31CB31H475KA12#** | |
| | | | | ±20% | **GRM31CB31H475MA12#** | |
| | | | 10μF | ±10% | **GRM31CB31H106KA12#** | |
| | | | | ±20% | **GRM31CB31H106MA12#** | |
| | 25Vdc | X7R | 4.7μF | ±10% | **GRM31CR71E475KA88#** | |
| | | | 10μF | ±10% | **GRM31CR71E106KA12#** | |
| | | | | ±20% | **GRM31CR71E106MA12#** | |
| | | X5R | 22μF | ±20% | **GRM31CR61E226ME15#** | |
| | | B | 10μF | ±10% | **GRM31CB31E106KA75#** | |
| | | | 22μF | ±20% | **GRM31CB31E226ME15#** | |
| | 16Vdc | X7R | 4.7μF | ±20% | **GRM31CR71C475MA01#** | |
| | | X6S | 22μF | ±20% | **GRM31CC81C226ME15#** | |
| | | X5R | 22μF | ±20% | **GRM31CR61C226ME15#** | |
| | | B | 22μF | ±20% | **GRM31CB31C226ME15#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.8mm | 10Vdc | X7R | 22μF | ±20% | **GRM31CR71A226ME15#** | |
| | | X5R | 47μF | ±20% | **GRM31CR61A476ME15#** | |
| | | B | 47μF | ±20% | **GRM31CB31A476ME15#** | |
| | 6.3Vdc | X7R | 22μF | ±20% | **GRM31CR70J226ME19#** | |
| | | X7U | 47μF | ±20% | **GRM31CE70J476ME15#** | Derating |
| | | X6S | 47μF | ±20% | **GRM31CC80J476ME18#** | |
| | | X5R | 47μF | ±20% | **GRM31CR60J476ME19#** | |
| | | B | 47μF | ±20% | **GRM31CB30J476ME18#** | |
| | 4Vdc | X7U | 47μF | ±20% | **GRM31CE70G476ME15#** | |
| | | X6S | 47μF | ±20% | **GRM31CC80G476ME19#** | |
| 1.9mm | 100Vdc | X7R | 2.2μF | ±10% | **GRM31CR72A225KA73#** | |
| | | | | ±20% | **GRM31CR72A225MA73#** | |
| | 6.3Vdc | X6T | 100μF | ±20% | **GRM31CD80J107ME39#** | Derating |
| | | X5R | 100μF | ±20% | **GRM31CR60J107ME39#** | |
| | 4Vdc | X7U | 100μF | ±20% | **GRM31CE70G107ME39#** | Derating |
| | | X6T | 100μF | ±20% | **GRM31CD80G107ME39#** | |
| | | X5R | 100μF | ±20% | **GRM31CR60G107ME39#** | |

## ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.5mm | 1000Vdc | X7R | 6800pF | ±10% | **GRM32QR73A682KW01#** | |
| | | | 10000pF | ±10% | **GRM32QR73A103KW01#** | |
| | 630Vdc | X7R | 22000pF | ±10% | **GRM32QR72J223KW01#** | |
| | 500Vdc | X7R | 22000pF | ±10% | **GRM32QR72H223KW01#** | |
| | 250Vdc | X7R | 68000pF | ±10% | **GRM32QR72E683KW01#** | |
| | | | 0.15μF | ±10% | **GRM32QR72E154KW01#** | |
| | 200Vdc | X7R | 68000pF | ±10% | **GRM32QR72D683KW01#** | |
| | | | 0.15μF | ±10% | **GRM32QR72D154KW01#** | |
| 1.8mm | 6.3Vdc | X5S | 150μF | ±20% | **GRM32RC60J157ME15#** | Derating |
| | 4Vdc | X6T | 150μF | ±20% | **GRM32RD80G157ME15#** | Derating |
| | | X5S | 150μF | ±20% | **GRM32RC60G157ME15#** | |
| | 2.5Vdc | X6T | 150μF | ±20% | **GRM32RD80E157ME15#** | |
| 2.0mm | 1000Vdc | X7R | 15000pF | ±10% | **GRM32DR73A153KW01#** | |
| | | | 22000pF | ±10% | **GRM32DR73A223KW01#** | |
| | 630Vdc | X7R | 33000pF | ±10% | **GRM32DR72J333KW01#** | |
| | | | 47000pF | ±10% | **GRM32DR72J473KW01#** | |
| | 500Vdc | X7R | 33000pF | ±10% | **GRM32DR72H333KW01#** | |
| | | | 47000pF | ±10% | **GRM32DR72H473KW01#** | |
| | 250Vdc | X7R | 0.10μF | ±10% | **GRM32DR72E104KW01#** | |
| | | | 0.22μF | ±10% | **GRM32DR72E224KW01#** | |
| | 200Vdc | X7R | 0.10μF | ±10% | **GRM32DR72D104KW01#** | |
| | | | 0.22μF | ±10% | **GRM32DR72D224KW01#** | |
| 2.2mm | 25Vdc | X7R | 10μF | ±10% | **GRM32DR71E106KA12#** | |
| 2.7mm | 80Vdc | X7R | 4.7μF | ±10% | **GRM32ER71K475KE14#** | Derating |
| | | | | ±20% | **GRM32ER71K475ME14#** | Derating |
| | 63Vdc | X7R | 10μF | ±10% | **GRM32ER71J106KA12#** | Derating |
| | | | | ±20% | **GRM32ER71J106MA12#** | Derating |
| | 50Vdc | X7R | 4.7μF | ±10% | **GRM32ER71H475KA88#** | |
| | | | 10μF | ±10% | **GRM32ER71H106KA12#** | |
| | | | | ±20% | **GRM32ER71H106MA12#** | |
| | | X5R | 10μF | ±10% | **GRM32ER61H106KA12#** | |
| | | | | ±20% | **GRM32ER61H106MA12#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.7mm | 50Vdc | B | 10μF | ±10% | **GRM32EB31H106KA12#** | |
| | | | | ±20% | **GRM32EB31H106MA12#** | |
| | 35Vdc | X7R | 10μF | ±10% | **GRM32ER7YA106KA12#** | |
| | | | | ±20% | **GRM32ER7YA106MA12#** | |
| | | X5R | 10μF | ±10% | **GRM32ER6YA106KA12#** | |
| | | | | ±20% | **GRM32ER6YA106MA12#** | |
| | | B | 10μF | ±10% | **GRM32EB3YA106KA12#** | |
| | | | | ±20% | **GRM32EB3YA106MA12#** | |
| | 25Vdc | X7R | 22μF | ±20% | **GRM32ER71E226ME15#** | |
| | | X5R | 22μF | ±20% | **GRM32ER61E226ME15#** | |
| | | B | 22μF | ±20% | **GRM32EB31E226ME15#** | |
| | 16Vdc | X7R | 22μF | ±20% | **GRM32ER71C226MEA8#** | |
| | | X6S | 47μF | ±20% | **GRM32EC81C476ME15#** | Derating |
| | | X5R | 47μF | ±20% | **GRM32ER61C476ME15#** | |
| | | B | 47μF | ±20% | **GRM32EB31C476ME15#** | |
| | 10Vdc | X7R | 47μF | ±20% | **GRM32ER71A476ME15#** | |
| | | X5R | 47μF | ±20% | **GRM32ER61A476ME20#** | |
| | | | 100μF | ±20% | **GRM32ER61A107ME20#** | Derating |
| | | B | 47μF | ±20% | **GRM32EB31A476ME20#** | |
| | 6.3Vdc | X7R | 47μF | ±20% | **GRM32ER70J476ME20#** | |
| | | X7U | 100μF | ±20% | **GRM32EE70J107ME15#** | Derating |
| | | X5R | 100μF | ±20% | **GRM32ER60J107ME20#** | |
| | | B | 100μF | ±20% | **GRM32EB30J107ME16#** | |
| | 4Vdc | X7U | 100μF | ±20% | **GRM32EE70G107ME19#** | |

## ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.5mm | 630Vdc | X7R | 68000pF | ±10% | **GRM43QR72J683KW01#** | |
| | 500Vdc | X7R | 68000pF | ±10% | **GRM43QR72H683KW01#** | |
| | 250Vdc | X7R | 0.15μF | ±10% | **GRM43QR72E154KW01#** | |
| | 200Vdc | X7R | 0.15μF | ±10% | **GRM43QR72D154KW01#** | |
| 2.0mm | 1000Vdc | X7R | 33000pF | ±10% | **GRM43DR73A333KW01#** | |
| | | | 47000pF | ±10% | **GRM43DR73A473KW01#** | |
| | 630Vdc | X7R | 0.10μF | ±10% | **GRM43DR72J104KW01#** | |
| | 500Vdc | X7R | 0.10μF | ±10% | **GRM43DR72H104KW01#** | |
| | 250Vdc | X7R | 0.22μF | ±10% | **GRM43DR72E224KW01#** | |
| | | | 0.33μF | ±10% | **GRM43DR72E334KW01#** | |
| | | | 0.47μF | ±10% | **GRM43DR72E474KW01#** | |
| | 200Vdc | X7R | 0.22μF | ±10% | **GRM43DR72D224KW01#** | |
| | | | 0.33μF | ±10% | **GRM43DR72D334KW01#** | |
| | | | 0.47μF | ±10% | **GRM43DR72D474KW01#** | |

## ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.0mm | 1000Vdc | X7R | 68000pF | ±10% | **GRM55DR73A683KW01#** | |
| | | | 0.10μF | ±10% | **GRM55DR73A104KW01#** | |
| | 630Vdc | X7R | 0.15μF | ±10% | **GRM55DR72J154KW01#** | |
| | | | 0.22μF | ±10% | **GRM55DR72J224KW01#** | |
| | 500Vdc | X7R | 0.15μF | ±10% | **GRM55DR72H154KW01#** | |
| | | | 0.22μF | ±10% | **GRM55DR72H224KW01#** | |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 5.7×5.0mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.0mm | 250Vdc | X7R | 0.33µF | ±10% | **GRM55DR72E334KW01#** | |
| | | | 0.47µF | ±10% | **GRM55DR72E474KW01#** | |
| | | | 0.68µF | ±10% | **GRM55DR72E684KW01#** | |
| | | | 1.0µF | ±10% | **GRM55DR72E105KW01#** | |
| | 200Vdc | X7R | 0.33µF | ±10% | **GRM55DR72D334KW01#** | |
| | | | 0.47µF | ±10% | **GRM55DR72D474KW01#** | |
| | | | 0.68µF | ±10% | **GRM55DR72D684KW01#** | |
| | | | 1.0µF | ±10% | **GRM55DR72D105KW01#** | |

Part number # indicates the package specification code.

High Frequency High Q Type 1005(in mm)/0402(in inch) Size Max.

# GJM Series HiQ

**This product improves the high frequency characteristics and contributes to a reduction of power consumption by the High Q and low ESR.**

## Features

### 1 Mainly ideal for mobile communication devices and temperature compensation of related modules.

This product is ideal for temperature compensation of high frequency circuits, such as resonant circuits, tuning circuits, and impedance matching circuits where the operating characteristics of the device are greatly affected by the capacitance fluctuation.




<Example of Structure>

### 2 High Q and low ESR in VHF, UHF and microwave frequency bands.

High Q and low ESR were achieved at a high frequency by adopting ceramic material as the dielectric material which enables an extremely low loss at high frequency, and base metal electrodes as the internal electrodes.




<Comparison between ESR - Frequency Characteristics>




<Comparison between Q - Frequency Characteristics>

### 3 Can be used for tight tolerance.

In addition to standard tolerance, the allowable range of this product is also suitable for the following tight tolerance.

| Capacitance Range | Standard Capacitance Tolerance (Capacitance Tolerance Symbol) | Narrow Capacitance Tolerance (Capacitance Tolerance Symbol) |
|---|---|---|
| <=0.9pF | ±0.1pF (B) | ±0.05pF (W) |
| 1.0 to 5.0pF | ±0.25pF (C) | ±0.05pF (W), ±0.1pF (B) |
| 5.1 to 9.9pF | ±0.5pF (D) | ±0.05pF (W), ±0.1pF (B), ±0.25pF (C) |
| >=10pF | ±5% (J) | ±2% (G) |

## Specifications

| | |
|---|---|
| Size | 0.4×0.2mm to 1.0×0.5mm |
| Rated Voltage | DC6.3V to 50V |
| Capacitance | 0.1pF to 47pF |
| Main Applications | Small communication devices, such as mobile phones and high frequency communication modules |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GJM Series Temperature Compensating Type HiQ Part Number List

## ■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.22mm | 25Vdc | C0G | 0.20pF | ±0.05pF | **GJM0225C1ER20WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER20BB01#** | |
| | | | 0.30pF | ±0.05pF | **GJM0225C1ER30WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER30BB01#** | |
| | | | 0.40pF | ±0.05pF | **GJM0225C1ER40WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER40BB01#** | |
| | | | 0.50pF | ±0.05pF | **GJM0225C1ER50WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER50BB01#** | |
| | | | 0.60pF | ±0.05pF | **GJM0225C1ER60WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER60BB01#** | |
| | | | 0.70pF | ±0.05pF | **GJM0225C1ER70WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER70BB01#** | |
| | | | 0.80pF | ±0.05pF | **GJM0225C1ER80WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER80BB01#** | |
| | | | 0.90pF | ±0.05pF | **GJM0225C1ER90WB01#** | |
| | | | | ±0.1pF | **GJM0225C1ER90BB01#** | |
| | | | 1.0pF | ±0.05pF | **GJM0225C1E1R0WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R0BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R0CB01#** | |
| | | | 1.1pF | ±0.05pF | **GJM0225C1E1R1WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R1BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R1CB01#** | |
| | | | 1.2pF | ±0.05pF | **GJM0225C1E1R2WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R2BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R2CB01#** | |
| | | | 1.3pF | ±0.05pF | **GJM0225C1E1R3WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R3BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R3CB01#** | |
| | | | 1.4pF | ±0.05pF | **GJM0225C1E1R4WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R4BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R4CB01#** | |
| | | | 1.5pF | ±0.05pF | **GJM0225C1E1R5WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R5BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R5CB01#** | |
| | | | 1.6pF | ±0.05pF | **GJM0225C1E1R6WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R6BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R6CB01#** | |
| | | | 1.7pF | ±0.05pF | **GJM0225C1E1R7WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R7BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R7CB01#** | |
| | | | 1.8pF | ±0.05pF | **GJM0225C1E1R8WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R8BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R8CB01#** | |
| | | | 1.9pF | ±0.05pF | **GJM0225C1E1R9WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E1R9BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E1R9CB01#** | |
| | | | 2.0pF | ±0.05pF | **GJM0225C1E2R0WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R0BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R0CB01#** | |
| | | | 2.1pF | ±0.05pF | **GJM0225C1E2R1WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R1BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R1CB01#** | |
| 0.22mm | 25Vdc | C0G | 2.2pF | ±0.05pF | **GJM0225C1E2R2WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R2BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R2CB01#** | |
| | | | 2.3pF | ±0.05pF | **GJM0225C1E2R3WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R3BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R3CB01#** | |
| | | | 2.4pF | ±0.05pF | **GJM0225C1E2R4WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R4BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R4CB01#** | |
| | | | 2.5pF | ±0.05pF | **GJM0225C1E2R5WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R5BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R5CB01#** | |
| | | | 2.6pF | ±0.05pF | **GJM0225C1E2R6WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R6BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R6CB01#** | |
| | | | 2.7pF | ±0.05pF | **GJM0225C1E2R7WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R7BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R7CB01#** | |
| | | | 2.8pF | ±0.05pF | **GJM0225C1E2R8WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R8BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R8CB01#** | |
| | | | 2.9pF | ±0.05pF | **GJM0225C1E2R9WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E2R9BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E2R9CB01#** | |
| | | | 3.0pF | ±0.05pF | **GJM0225C1E3R0WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R0BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R0CB01#** | |
| | | | 3.1pF | ±0.05pF | **GJM0225C1E3R1WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R1BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R1CB01#** | |
| | | | 3.2pF | ±0.05pF | **GJM0225C1E3R2WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R2BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R2CB01#** | |
| | | | 3.3pF | ±0.05pF | **GJM0225C1E3R3WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R3BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R3CB01#** | |
| | | | 3.4pF | ±0.05pF | **GJM0225C1E3R4WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R4BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R4CB01#** | |
| | | | 3.5pF | ±0.05pF | **GJM0225C1E3R5WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R5BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R5CB01#** | |
| | | | 3.6pF | ±0.05pF | **GJM0225C1E3R6WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R6BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R6CB01#** | |
| | | | 3.7pF | ±0.05pF | **GJM0225C1E3R7WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R7BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R7CB01#** | |
| | | | 3.8pF | ±0.05pF | **GJM0225C1E3R8WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R8BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R8CB01#** | |
| | | | 3.9pF | ±0.05pF | **GJM0225C1E3R9WB01#** | |
| | | | | ±0.1pF | **GJM0225C1E3R9BB01#** | |
| | | | | ±0.25pF | **GJM0225C1E3R9CB01#** | |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | C0G | 4.0pF | ±0.05pF | GJM0225C1E4R0WB01# |
| | | | | ±0.1pF | GJM0225C1E4R0BB01# |
| | | | | ±0.25pF | GJM0225C1E4R0CB01# |
| | | | 4.1pF | ±0.05pF | GJM0225C1E4R1WB01# |
| | | | | ±0.1pF | GJM0225C1E4R1BB01# |
| | | | | ±0.25pF | GJM0225C1E4R1CB01# |
| | | | 4.2pF | ±0.05pF | GJM0225C1E4R2WB01# |
| | | | | ±0.1pF | GJM0225C1E4R2BB01# |
| | | | | ±0.25pF | GJM0225C1E4R2CB01# |
| | | | 4.3pF | ±0.05pF | GJM0225C1E4R3WB01# |
| | | | | ±0.1pF | GJM0225C1E4R3BB01# |
| | | | | ±0.25pF | GJM0225C1E4R3CB01# |
| | | | 4.4pF | ±0.05pF | GJM0225C1E4R4WB01# |
| | | | | ±0.1pF | GJM0225C1E4R4BB01# |
| | | | | ±0.25pF | GJM0225C1E4R4CB01# |
| | | | 4.5pF | ±0.05pF | GJM0225C1E4R5WB01# |
| | | | | ±0.1pF | GJM0225C1E4R5BB01# |
| | | | | ±0.25pF | GJM0225C1E4R5CB01# |
| | | | 4.6pF | ±0.05pF | GJM0225C1E4R6WB01# |
| | | | | ±0.1pF | GJM0225C1E4R6BB01# |
| | | | | ±0.25pF | GJM0225C1E4R6CB01# |
| | | | 4.7pF | ±0.05pF | GJM0225C1E4R7WB01# |
| | | | | ±0.1pF | GJM0225C1E4R7BB01# |
| | | | | ±0.25pF | GJM0225C1E4R7CB01# |
| | | | 4.8pF | ±0.05pF | GJM0225C1E4R8WB01# |
| | | | | ±0.1pF | GJM0225C1E4R8BB01# |
| | | | | ±0.25pF | GJM0225C1E4R8CB01# |
| | | | 4.9pF | ±0.05pF | GJM0225C1E4R9WB01# |
| | | | | ±0.1pF | GJM0225C1E4R9BB01# |
| | | | | ±0.25pF | GJM0225C1E4R9CB01# |
| | | | 5.0pF | ±0.05pF | GJM0225C1E5R0WB01# |
| | | | | ±0.1pF | GJM0225C1E5R0BB01# |
| | | | | ±0.25pF | GJM0225C1E5R0CB01# |
| | | | 5.1pF | ±0.05pF | GJM0225C1E5R1WB01# |
| | | | | ±0.1pF | GJM0225C1E5R1BB01# |
| | | | | ±0.25pF | GJM0225C1E5R1CB01# |
| | | | | ±0.5pF | GJM0225C1E5R1DB01# |
| | | | 5.2pF | ±0.05pF | GJM0225C1E5R2WB01# |
| | | | | ±0.1pF | GJM0225C1E5R2BB01# |
| | | | | ±0.25pF | GJM0225C1E5R2CB01# |
| | | | | ±0.5pF | GJM0225C1E5R2DB01# |
| | | | 5.3pF | ±0.05pF | GJM0225C1E5R3WB01# |
| | | | | ±0.1pF | GJM0225C1E5R3BB01# |
| | | | | ±0.25pF | GJM0225C1E5R3CB01# |
| | | | | ±0.5pF | GJM0225C1E5R3DB01# |
| | | | 5.4pF | ±0.05pF | GJM0225C1E5R4WB01# |
| | | | | ±0.1pF | GJM0225C1E5R4BB01# |
| | | | | ±0.25pF | GJM0225C1E5R4CB01# |
| | | | | ±0.5pF | GJM0225C1E5R4DB01# |
| | | | 5.5pF | ±0.05pF | GJM0225C1E5R5WB01# |
| | | | | ±0.1pF | GJM0225C1E5R5BB01# |
| | | | | ±0.25pF | GJM0225C1E5R5CB01# |
| | | | | ±0.5pF | GJM0225C1E5R5DB01# |
| | | | 5.6pF | ±0.05pF | GJM0225C1E5R6WB01# |
| | | | | ±0.1pF | GJM0225C1E5R6BB01# |
| | | | | ±0.25pF | GJM0225C1E5R6CB01# |
| | | | | ±0.5pF | GJM0225C1E5R6DB01# |
| | | | 5.7pF | ±0.05pF | GJM0225C1E5R7WB01# |
| | | | | ±0.1pF | GJM0225C1E5R7BB01# |
| | | | | ±0.25pF | GJM0225C1E5R7CB01# |
| | | | | ±0.5pF | GJM0225C1E5R7DB01# |
| | | | 5.8pF | ±0.05pF | GJM0225C1E5R8WB01# |
| | | | | ±0.1pF | GJM0225C1E5R8BB01# |
| | | | | ±0.25pF | GJM0225C1E5R8CB01# |
| | | | | ±0.5pF | GJM0225C1E5R8DB01# |
| | | | 5.9pF | ±0.05pF | GJM0225C1E5R9WB01# |
| | | | | ±0.1pF | GJM0225C1E5R9BB01# |
| | | | | ±0.25pF | GJM0225C1E5R9CB01# |
| | | | | ±0.5pF | GJM0225C1E5R9DB01# |
| | | | 6.0pF | ±0.05pF | GJM0225C1E6R0WB01# |
| | | | | ±0.1pF | GJM0225C1E6R0BB01# |
| | | | | ±0.25pF | GJM0225C1E6R0CB01# |
| | | | | ±0.5pF | GJM0225C1E6R0DB01# |
| | | | 6.1pF | ±0.05pF | GJM0225C1E6R1WB01# |
| | | | | ±0.1pF | GJM0225C1E6R1BB01# |
| | | | | ±0.25pF | GJM0225C1E6R1CB01# |
| | | | | ±0.5pF | GJM0225C1E6R1DB01# |
| | | | 6.2pF | ±0.05pF | GJM0225C1E6R2WB01# |
| | | | | ±0.1pF | GJM0225C1E6R2BB01# |
| | | | | ±0.25pF | GJM0225C1E6R2CB01# |
| | | | | ±0.5pF | GJM0225C1E6R2DB01# |
| | | | 6.3pF | ±0.05pF | GJM0225C1E6R3WB01# |
| | | | | ±0.1pF | GJM0225C1E6R3BB01# |
| | | | | ±0.25pF | GJM0225C1E6R3CB01# |
| | | | | ±0.5pF | GJM0225C1E6R3DB01# |
| | | | 6.4pF | ±0.05pF | GJM0225C1E6R4WB01# |
| | | | | ±0.1pF | GJM0225C1E6R4BB01# |
| | | | | ±0.25pF | GJM0225C1E6R4CB01# |
| | | | | ±0.5pF | GJM0225C1E6R4DB01# |
| | | | 6.5pF | ±0.05pF | GJM0225C1E6R5WB01# |
| | | | | ±0.1pF | GJM0225C1E6R5BB01# |
| | | | | ±0.25pF | GJM0225C1E6R5CB01# |
| | | | | ±0.5pF | GJM0225C1E6R5DB01# |
| | | | 6.6pF | ±0.05pF | GJM0225C1E6R6WB01# |
| | | | | ±0.1pF | GJM0225C1E6R6BB01# |
| | | | | ±0.25pF | GJM0225C1E6R6CB01# |
| | | | | ±0.5pF | GJM0225C1E6R6DB01# |
| | | | 6.7pF | ±0.05pF | GJM0225C1E6R7WB01# |
| | | | | ±0.1pF | GJM0225C1E6R7BB01# |
| | | | | ±0.25pF | GJM0225C1E6R7CB01# |
| | | | | ±0.5pF | GJM0225C1E6R7DB01# |
| | | | 6.8pF | ±0.05pF | GJM0225C1E6R8WB01# |
| | | | | ±0.1pF | GJM0225C1E6R8BB01# |
| | | | | ±0.25pF | GJM0225C1E6R8CB01# |
| | | | | ±0.5pF | GJM0225C1E6R8DB01# |
| | | | 6.9pF | ±0.05pF | GJM0225C1E6R9WB01# |
| | | | | ±0.1pF | GJM0225C1E6R9BB01# |
| | | | | ±0.25pF | GJM0225C1E6R9CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | C0G | 6.9pF | ±0.5pF | **GJM0225C1E6R9DB01#** |
| | | | 7.0pF | ±0.05pF | **GJM0225C1E7R0WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R0BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R0CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R0DB01#** |
| | | | 7.1pF | ±0.05pF | **GJM0225C1E7R1WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R1BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R1CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R1DB01#** |
| | | | 7.2pF | ±0.05pF | **GJM0225C1E7R2WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R2BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R2CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R2DB01#** |
| | | | 7.3pF | ±0.05pF | **GJM0225C1E7R3WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R3BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R3CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R3DB01#** |
| | | | 7.4pF | ±0.05pF | **GJM0225C1E7R4WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R4BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R4CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R4DB01#** |
| | | | 7.5pF | ±0.05pF | **GJM0225C1E7R5WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R5BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R5CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R5DB01#** |
| | | | 7.6pF | ±0.05pF | **GJM0225C1E7R6WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R6BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R6CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R6DB01#** |
| | | | 7.7pF | ±0.05pF | **GJM0225C1E7R7WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R7BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R7CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R7DB01#** |
| | | | 7.8pF | ±0.05pF | **GJM0225C1E7R8WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R8BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R8CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R8DB01#** |
| | | | 7.9pF | ±0.05pF | **GJM0225C1E7R9WB01#** |
| | | | | ±0.1pF | **GJM0225C1E7R9BB01#** |
| | | | | ±0.25pF | **GJM0225C1E7R9CB01#** |
| | | | | ±0.5pF | **GJM0225C1E7R9DB01#** |
| | | | 8.0pF | ±0.05pF | **GJM0225C1E8R0WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R0BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R0CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R0DB01#** |
| | | | 8.1pF | ±0.05pF | **GJM0225C1E8R1WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R1BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R1CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R1DB01#** |
| | | | 8.2pF | ±0.05pF | **GJM0225C1E8R2WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R2BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R2CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R2DB01#** |
| | | | 8.3pF | ±0.05pF | **GJM0225C1E8R3WB01#** |
| 0.22mm | 25Vdc | C0G | 8.3pF | ±0.1pF | **GJM0225C1E8R3BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R3CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R3DB01#** |
| | | | 8.4pF | ±0.05pF | **GJM0225C1E8R4WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R4BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R4CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R4DB01#** |
| | | | 8.5pF | ±0.05pF | **GJM0225C1E8R5WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R5BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R5CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R5DB01#** |
| | | | 8.6pF | ±0.05pF | **GJM0225C1E8R6WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R6BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R6CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R6DB01#** |
| | | | 8.7pF | ±0.05pF | **GJM0225C1E8R7WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R7BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R7CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R7DB01#** |
| | | | 8.8pF | ±0.05pF | **GJM0225C1E8R8WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R8BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R8CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R8DB01#** |
| | | | 8.9pF | ±0.05pF | **GJM0225C1E8R9WB01#** |
| | | | | ±0.1pF | **GJM0225C1E8R9BB01#** |
| | | | | ±0.25pF | **GJM0225C1E8R9CB01#** |
| | | | | ±0.5pF | **GJM0225C1E8R9DB01#** |
| | | | 9.0pF | ±0.05pF | **GJM0225C1E9R0WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R0BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R0CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R0DB01#** |
| | | | 9.1pF | ±0.05pF | **GJM0225C1E9R1WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R1BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R1CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R1DB01#** |
| | | | 9.2pF | ±0.05pF | **GJM0225C1E9R2WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R2BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R2CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R2DB01#** |
| | | | 9.3pF | ±0.05pF | **GJM0225C1E9R3WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R3BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R3CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R3DB01#** |
| | | | 9.4pF | ±0.05pF | **GJM0225C1E9R4WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R4BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R4CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R4DB01#** |
| | | | 9.5pF | ±0.05pF | **GJM0225C1E9R5WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R5BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R5CB01#** |
| | | | | ±0.5pF | **GJM0225C1E9R5DB01#** |
| | | | 9.6pF | ±0.05pF | **GJM0225C1E9R6WB01#** |
| | | | | ±0.1pF | **GJM0225C1E9R6BB01#** |
| | | | | ±0.25pF | **GJM0225C1E9R6CB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | C0G | 9.6pF | ±0.5pF | GJM0225C1E9R6DB01# |
| | | | 9.7pF | ±0.05pF | GJM0225C1E9R7WB01# |
| | | | | ±0.1pF | GJM0225C1E9R7BB01# |
| | | | | ±0.25pF | GJM0225C1E9R7CB01# |
| | | | | ±0.5pF | GJM0225C1E9R7DB01# |
| | | | 9.8pF | ±0.05pF | GJM0225C1E9R8WB01# |
| | | | | ±0.1pF | GJM0225C1E9R8BB01# |
| | | | | ±0.25pF | GJM0225C1E9R8CB01# |
| | | | | ±0.5pF | GJM0225C1E9R8DB01# |
| | | | 9.9pF | ±0.05pF | GJM0225C1E9R9WB01# |
| | | | | ±0.1pF | GJM0225C1E9R9BB01# |
| | | | | ±0.25pF | GJM0225C1E9R9CB01# |
| | | | | ±0.5pF | GJM0225C1E9R9DB01# |
| | | | 10pF | ±2% | GJM0225C1E100GB01# |
| | | | | ±5% | GJM0225C1E100JB01# |
| | | | 11pF | ±2% | GJM0225C1E110GB01# |
| | | | | ±5% | GJM0225C1E110JB01# |
| | | | 12pF | ±2% | GJM0225C1E120GB01# |
| | | | | ±5% | GJM0225C1E120JB01# |
| | | | 13pF | ±2% | GJM0225C1E130GB01# |
| | | | | ±5% | GJM0225C1E130JB01# |
| | | | 15pF | ±2% | GJM0225C1E150GB01# |
| | | | | ±5% | GJM0225C1E150JB01# |
| | | | 16pF | ±2% | GJM0225C1E160GB01# |
| | | | | ±5% | GJM0225C1E160JB01# |
| | | | 18pF | ±2% | GJM0225C1E180GB01# |
| | | | | ±5% | GJM0225C1E180JB01# |
| | | | 20pF | ±2% | GJM0225C1E200GB01# |
| | | | | ±5% | GJM0225C1E200JB01# |
| | | | 22pF | ±2% | GJM0225C1E220GB01# |
| | | | | ±5% | GJM0225C1E220JB01# |
| | | CK | 0.20pF | ±0.05pF | GJM0224C1ER20WB01# |
| | | | | ±0.1pF | GJM0224C1ER20BB01# |
| | | | 0.30pF | ±0.05pF | GJM0224C1ER30WB01# |
| | | | | ±0.1pF | GJM0224C1ER30BB01# |
| | | | 0.40pF | ±0.05pF | GJM0224C1ER40WB01# |
| | | | | ±0.1pF | GJM0224C1ER40BB01# |
| | | | 0.50pF | ±0.05pF | GJM0224C1ER50WB01# |
| | | | | ±0.1pF | GJM0224C1ER50BB01# |
| | | | 0.60pF | ±0.05pF | GJM0224C1ER60WB01# |
| | | | | ±0.1pF | GJM0224C1ER60BB01# |
| | | | 0.70pF | ±0.05pF | GJM0224C1ER70WB01# |
| | | | | ±0.1pF | GJM0224C1ER70BB01# |
| | | | 0.80pF | ±0.05pF | GJM0224C1ER80WB01# |
| | | | | ±0.1pF | GJM0224C1ER80BB01# |
| | | | 0.90pF | ±0.05pF | GJM0224C1ER90WB01# |
| | | | | ±0.1pF | GJM0224C1ER90BB01# |
| | | | 1.0pF | ±0.05pF | GJM0224C1E1R0WB01# |
| | | | | ±0.1pF | GJM0224C1E1R0BB01# |
| | | | | ±0.25pF | GJM0224C1E1R0CB01# |
| | | | 1.1pF | ±0.05pF | GJM0224C1E1R1WB01# |
| | | | | ±0.1pF | GJM0224C1E1R1BB01# |
| | | | | ±0.25pF | GJM0224C1E1R1CB01# |
| | | | 1.2pF | ±0.05pF | GJM0224C1E1R2WB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | CK | 1.2pF | ±0.1pF | GJM0224C1E1R2BB01# |
| | | | | ±0.25pF | GJM0224C1E1R2CB01# |
| | | | 1.3pF | ±0.05pF | GJM0224C1E1R3WB01# |
| | | | | ±0.1pF | GJM0224C1E1R3BB01# |
| | | | | ±0.25pF | GJM0224C1E1R3CB01# |
| | | | 1.4pF | ±0.05pF | GJM0224C1E1R4WB01# |
| | | | | ±0.1pF | GJM0224C1E1R4BB01# |
| | | | | ±0.25pF | GJM0224C1E1R4CB01# |
| | | | 1.5pF | ±0.05pF | GJM0224C1E1R5WB01# |
| | | | | ±0.1pF | GJM0224C1E1R5BB01# |
| | | | | ±0.25pF | GJM0224C1E1R5CB01# |
| | | | 1.6pF | ±0.05pF | GJM0224C1E1R6WB01# |
| | | | | ±0.1pF | GJM0224C1E1R6BB01# |
| | | | | ±0.25pF | GJM0224C1E1R6CB01# |
| | | | 1.7pF | ±0.05pF | GJM0224C1E1R7WB01# |
| | | | | ±0.1pF | GJM0224C1E1R7BB01# |
| | | | | ±0.25pF | GJM0224C1E1R7CB01# |
| | | | 1.8pF | ±0.05pF | GJM0224C1E1R8WB01# |
| | | | | ±0.1pF | GJM0224C1E1R8BB01# |
| | | | | ±0.25pF | GJM0224C1E1R8CB01# |
| | | | 1.9pF | ±0.05pF | GJM0224C1E1R9WB01# |
| | | | | ±0.1pF | GJM0224C1E1R9BB01# |
| | | | | ±0.25pF | GJM0224C1E1R9CB01# |
| | | | 2.0pF | ±0.05pF | GJM0224C1E2R0WB01# |
| | | | | ±0.1pF | GJM0224C1E2R0BB01# |
| | | | | ±0.25pF | GJM0224C1E2R0CB01# |
| | | CJ | 2.1pF | ±0.05pF | GJM0223C1E2R1WB01# |
| | | | | ±0.1pF | GJM0223C1E2R1BB01# |
| | | | | ±0.25pF | GJM0223C1E2R1CB01# |
| | | | 2.2pF | ±0.05pF | GJM0223C1E2R2WB01# |
| | | | | ±0.1pF | GJM0223C1E2R2BB01# |
| | | | | ±0.25pF | GJM0223C1E2R2CB01# |
| | | | 2.3pF | ±0.05pF | GJM0223C1E2R3WB01# |
| | | | | ±0.1pF | GJM0223C1E2R3BB01# |
| | | | | ±0.25pF | GJM0223C1E2R3CB01# |
| | | | 2.4pF | ±0.05pF | GJM0223C1E2R4WB01# |
| | | | | ±0.1pF | GJM0223C1E2R4BB01# |
| | | | | ±0.25pF | GJM0223C1E2R4CB01# |
| | | | 2.5pF | ±0.05pF | GJM0223C1E2R5WB01# |
| | | | | ±0.1pF | GJM0223C1E2R5BB01# |
| | | | | ±0.25pF | GJM0223C1E2R5CB01# |
| | | | 2.6pF | ±0.05pF | GJM0223C1E2R6WB01# |
| | | | | ±0.1pF | GJM0223C1E2R6BB01# |
| | | | | ±0.25pF | GJM0223C1E2R6CB01# |
| | | | 2.7pF | ±0.05pF | GJM0223C1E2R7WB01# |
| | | | | ±0.1pF | GJM0223C1E2R7BB01# |
| | | | | ±0.25pF | GJM0223C1E2R7CB01# |
| | | | 2.8pF | ±0.05pF | GJM0223C1E2R8WB01# |
| | | | | ±0.1pF | GJM0223C1E2R8BB01# |
| | | | | ±0.25pF | GJM0223C1E2R8CB01# |
| | | | 2.9pF | ±0.05pF | GJM0223C1E2R9WB01# |
| | | | | ±0.1pF | GJM0223C1E2R9BB01# |
| | | | | ±0.25pF | GJM0223C1E2R9CB01# |
| | | | 3.0pF | ±0.05pF | GJM0223C1E3R0WB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | CJ | 3.0pF | ±0.1pF | GJM0223C1E3R0BB01# |
| | | | | ±0.25pF | GJM0223C1E3R0CB01# |
| | | | 3.1pF | ±0.05pF | GJM0223C1E3R1WB01# |
| | | | | ±0.1pF | GJM0223C1E3R1BB01# |
| | | | | ±0.25pF | GJM0223C1E3R1CB01# |
| | | | 3.2pF | ±0.05pF | GJM0223C1E3R2WB01# |
| | | | | ±0.1pF | GJM0223C1E3R2BB01# |
| | | | | ±0.25pF | GJM0223C1E3R2CB01# |
| | | | 3.3pF | ±0.05pF | GJM0223C1E3R3WB01# |
| | | | | ±0.1pF | GJM0223C1E3R3BB01# |
| | | | | ±0.25pF | GJM0223C1E3R3CB01# |
| | | | 3.4pF | ±0.05pF | GJM0223C1E3R4WB01# |
| | | | | ±0.1pF | GJM0223C1E3R4BB01# |
| | | | | ±0.25pF | GJM0223C1E3R4CB01# |
| | | | 3.5pF | ±0.05pF | GJM0223C1E3R5WB01# |
| | | | | ±0.1pF | GJM0223C1E3R5BB01# |
| | | | | ±0.25pF | GJM0223C1E3R5CB01# |
| | | | 3.6pF | ±0.05pF | GJM0223C1E3R6WB01# |
| | | | | ±0.1pF | GJM0223C1E3R6BB01# |
| | | | | ±0.25pF | GJM0223C1E3R6CB01# |
| | | | 3.7pF | ±0.05pF | GJM0223C1E3R7WB01# |
| | | | | ±0.1pF | GJM0223C1E3R7BB01# |
| | | | | ±0.25pF | GJM0223C1E3R7CB01# |
| | | | 3.8pF | ±0.05pF | GJM0223C1E3R8WB01# |
| | | | | ±0.1pF | GJM0223C1E3R8BB01# |
| | | | | ±0.25pF | GJM0223C1E3R8CB01# |
| | | | 3.9pF | ±0.05pF | GJM0223C1E3R9WB01# |
| | | | | ±0.1pF | GJM0223C1E3R9BB01# |
| | | | | ±0.25pF | GJM0223C1E3R9CB01# |
| | | CH | 4.0pF | ±0.05pF | GJM0222C1E4R0WB01# |
| | | | | ±0.1pF | GJM0222C1E4R0BB01# |
| | | | | ±0.25pF | GJM0222C1E4R0CB01# |
| | | | 4.1pF | ±0.05pF | GJM0222C1E4R1WB01# |
| | | | | ±0.1pF | GJM0222C1E4R1BB01# |
| | | | | ±0.25pF | GJM0222C1E4R1CB01# |
| | | | 4.2pF | ±0.05pF | GJM0222C1E4R2WB01# |
| | | | | ±0.1pF | GJM0222C1E4R2BB01# |
| | | | | ±0.25pF | GJM0222C1E4R2CB01# |
| | | | 4.3pF | ±0.05pF | GJM0222C1E4R3WB01# |
| | | | | ±0.1pF | GJM0222C1E4R3BB01# |
| | | | | ±0.25pF | GJM0222C1E4R3CB01# |
| | | | 4.4pF | ±0.05pF | GJM0222C1E4R4WB01# |
| | | | | ±0.1pF | GJM0222C1E4R4BB01# |
| | | | | ±0.25pF | GJM0222C1E4R4CB01# |
| | | | 4.5pF | ±0.05pF | GJM0222C1E4R5WB01# |
| | | | | ±0.1pF | GJM0222C1E4R5BB01# |
| | | | | ±0.25pF | GJM0222C1E4R5CB01# |
| | | | 4.6pF | ±0.05pF | GJM0222C1E4R6WB01# |
| | | | | ±0.1pF | GJM0222C1E4R6BB01# |
| | | | | ±0.25pF | GJM0222C1E4R6CB01# |
| | | | 4.7pF | ±0.05pF | GJM0222C1E4R7WB01# |
| | | | | ±0.1pF | GJM0222C1E4R7BB01# |
| | | | | ±0.25pF | GJM0222C1E4R7CB01# |
| | | | 4.8pF | ±0.05pF | GJM0222C1E4R8WB01# |
| 0.22mm | 25Vdc | CH | 4.8pF | ±0.1pF | GJM0222C1E4R8BB01# |
| | | | | ±0.25pF | GJM0222C1E4R8CB01# |
| | | | 4.9pF | ±0.05pF | GJM0222C1E4R9WB01# |
| | | | | ±0.1pF | GJM0222C1E4R9BB01# |
| | | | | ±0.25pF | GJM0222C1E4R9CB01# |
| | | | 5.0pF | ±0.05pF | GJM0222C1E5R0WB01# |
| | | | | ±0.1pF | GJM0222C1E5R0BB01# |
| | | | | ±0.25pF | GJM0222C1E5R0CB01# |
| | | | 5.1pF | ±0.05pF | GJM0222C1E5R1WB01# |
| | | | | ±0.1pF | GJM0222C1E5R1BB01# |
| | | | | ±0.25pF | GJM0222C1E5R1CB01# |
| | | | | ±0.5pF | GJM0222C1E5R1DB01# |
| | | | 5.2pF | ±0.05pF | GJM0222C1E5R2WB01# |
| | | | | ±0.1pF | GJM0222C1E5R2BB01# |
| | | | | ±0.25pF | GJM0222C1E5R2CB01# |
| | | | | ±0.5pF | GJM0222C1E5R2DB01# |
| | | | 5.3pF | ±0.05pF | GJM0222C1E5R3WB01# |
| | | | | ±0.1pF | GJM0222C1E5R3BB01# |
| | | | | ±0.25pF | GJM0222C1E5R3CB01# |
| | | | | ±0.5pF | GJM0222C1E5R3DB01# |
| | | | 5.4pF | ±0.05pF | GJM0222C1E5R4WB01# |
| | | | | ±0.1pF | GJM0222C1E5R4BB01# |
| | | | | ±0.25pF | GJM0222C1E5R4CB01# |
| | | | | ±0.5pF | GJM0222C1E5R4DB01# |
| | | | 5.5pF | ±0.05pF | GJM0222C1E5R5WB01# |
| | | | | ±0.1pF | GJM0222C1E5R5BB01# |
| | | | | ±0.25pF | GJM0222C1E5R5CB01# |
| | | | | ±0.5pF | GJM0222C1E5R5DB01# |
| | | | 5.6pF | ±0.05pF | GJM0222C1E5R6WB01# |
| | | | | ±0.1pF | GJM0222C1E5R6BB01# |
| | | | | ±0.25pF | GJM0222C1E5R6CB01# |
| | | | | ±0.5pF | GJM0222C1E5R6DB01# |
| | | | 5.7pF | ±0.05pF | GJM0222C1E5R7WB01# |
| | | | | ±0.1pF | GJM0222C1E5R7BB01# |
| | | | | ±0.25pF | GJM0222C1E5R7CB01# |
| | | | | ±0.5pF | GJM0222C1E5R7DB01# |
| | | | 5.8pF | ±0.05pF | GJM0222C1E5R8WB01# |
| | | | | ±0.1pF | GJM0222C1E5R8BB01# |
| | | | | ±0.25pF | GJM0222C1E5R8CB01# |
| | | | | ±0.5pF | GJM0222C1E5R8DB01# |
| | | | 5.9pF | ±0.05pF | GJM0222C1E5R9WB01# |
| | | | | ±0.1pF | GJM0222C1E5R9BB01# |
| | | | | ±0.25pF | GJM0222C1E5R9CB01# |
| | | | | ±0.5pF | GJM0222C1E5R9DB01# |
| | | | 6.0pF | ±0.05pF | GJM0222C1E6R0WB01# |
| | | | | ±0.1pF | GJM0222C1E6R0BB01# |
| | | | | ±0.25pF | GJM0222C1E6R0CB01# |
| | | | | ±0.5pF | GJM0222C1E6R0DB01# |
| | | | 6.1pF | ±0.05pF | GJM0222C1E6R1WB01# |
| | | | | ±0.1pF | GJM0222C1E6R1BB01# |
| | | | | ±0.25pF | GJM0222C1E6R1CB01# |
| | | | | ±0.5pF | GJM0222C1E6R1DB01# |
| | | | 6.2pF | ±0.05pF | GJM0222C1E6R2WB01# |
| | | | | ±0.1pF | GJM0222C1E6R2BB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | CH | 6.2pF | ±0.25pF | GJM0222C1E6R2CB01# |
| | | | | ±0.5pF | GJM0222C1E6R2DB01# |
| | | | 6.3pF | ±0.05pF | GJM0222C1E6R3WB01# |
| | | | | ±0.1pF | GJM0222C1E6R3BB01# |
| | | | | ±0.25pF | GJM0222C1E6R3CB01# |
| | | | | ±0.5pF | GJM0222C1E6R3DB01# |
| | | | 6.4pF | ±0.05pF | GJM0222C1E6R4WB01# |
| | | | | ±0.1pF | GJM0222C1E6R4BB01# |
| | | | | ±0.25pF | GJM0222C1E6R4CB01# |
| | | | | ±0.5pF | GJM0222C1E6R4DB01# |
| | | | 6.5pF | ±0.05pF | GJM0222C1E6R5WB01# |
| | | | | ±0.1pF | GJM0222C1E6R5BB01# |
| | | | | ±0.25pF | GJM0222C1E6R5CB01# |
| | | | | ±0.5pF | GJM0222C1E6R5DB01# |
| | | | 6.6pF | ±0.05pF | GJM0222C1E6R6WB01# |
| | | | | ±0.1pF | GJM0222C1E6R6BB01# |
| | | | | ±0.25pF | GJM0222C1E6R6CB01# |
| | | | | ±0.5pF | GJM0222C1E6R6DB01# |
| | | | 6.7pF | ±0.05pF | GJM0222C1E6R7WB01# |
| | | | | ±0.1pF | GJM0222C1E6R7BB01# |
| | | | | ±0.25pF | GJM0222C1E6R7CB01# |
| | | | | ±0.5pF | GJM0222C1E6R7DB01# |
| | | | 6.8pF | ±0.05pF | GJM0222C1E6R8WB01# |
| | | | | ±0.1pF | GJM0222C1E6R8BB01# |
| | | | | ±0.25pF | GJM0222C1E6R8CB01# |
| | | | | ±0.5pF | GJM0222C1E6R8DB01# |
| | | | 6.9pF | ±0.05pF | GJM0222C1E6R9WB01# |
| | | | | ±0.1pF | GJM0222C1E6R9BB01# |
| | | | | ±0.25pF | GJM0222C1E6R9CB01# |
| | | | | ±0.5pF | GJM0222C1E6R9DB01# |
| | | | 7.0pF | ±0.05pF | GJM0222C1E7R0WB01# |
| | | | | ±0.1pF | GJM0222C1E7R0BB01# |
| | | | | ±0.25pF | GJM0222C1E7R0CB01# |
| | | | | ±0.5pF | GJM0222C1E7R0DB01# |
| | | | 7.1pF | ±0.05pF | GJM0222C1E7R1WB01# |
| | | | | ±0.1pF | GJM0222C1E7R1BB01# |
| | | | | ±0.25pF | GJM0222C1E7R1CB01# |
| | | | | ±0.5pF | GJM0222C1E7R1DB01# |
| | | | 7.2pF | ±0.05pF | GJM0222C1E7R2WB01# |
| | | | | ±0.1pF | GJM0222C1E7R2BB01# |
| | | | | ±0.25pF | GJM0222C1E7R2CB01# |
| | | | | ±0.5pF | GJM0222C1E7R2DB01# |
| | | | 7.3pF | ±0.05pF | GJM0222C1E7R3WB01# |
| | | | | ±0.1pF | GJM0222C1E7R3BB01# |
| | | | | ±0.25pF | GJM0222C1E7R3CB01# |
| | | | | ±0.5pF | GJM0222C1E7R3DB01# |
| | | | 7.4pF | ±0.05pF | GJM0222C1E7R4WB01# |
| | | | | ±0.1pF | GJM0222C1E7R4BB01# |
| | | | | ±0.25pF | GJM0222C1E7R4CB01# |
| | | | | ±0.5pF | GJM0222C1E7R4DB01# |
| | | | 7.5pF | ±0.05pF | GJM0222C1E7R5WB01# |
| | | | | ±0.1pF | GJM0222C1E7R5BB01# |
| | | | | ±0.25pF | GJM0222C1E7R5CB01# |
| | | | | ±0.5pF | GJM0222C1E7R5DB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | CH | 7.6pF | ±0.05pF | GJM0222C1E7R6WB01# |
| | | | | ±0.1pF | GJM0222C1E7R6BB01# |
| | | | | ±0.25pF | GJM0222C1E7R6CB01# |
| | | | | ±0.5pF | GJM0222C1E7R6DB01# |
| | | | 7.7pF | ±0.05pF | GJM0222C1E7R7WB01# |
| | | | | ±0.1pF | GJM0222C1E7R7BB01# |
| | | | | ±0.25pF | GJM0222C1E7R7CB01# |
| | | | | ±0.5pF | GJM0222C1E7R7DB01# |
| | | | 7.8pF | ±0.05pF | GJM0222C1E7R8WB01# |
| | | | | ±0.1pF | GJM0222C1E7R8BB01# |
| | | | | ±0.25pF | GJM0222C1E7R8CB01# |
| | | | | ±0.5pF | GJM0222C1E7R8DB01# |
| | | | 7.9pF | ±0.05pF | GJM0222C1E7R9WB01# |
| | | | | ±0.1pF | GJM0222C1E7R9BB01# |
| | | | | ±0.25pF | GJM0222C1E7R9CB01# |
| | | | | ±0.5pF | GJM0222C1E7R9DB01# |
| | | | 8.0pF | ±0.05pF | GJM0222C1E8R0WB01# |
| | | | | ±0.1pF | GJM0222C1E8R0BB01# |
| | | | | ±0.25pF | GJM0222C1E8R0CB01# |
| | | | | ±0.5pF | GJM0222C1E8R0DB01# |
| | | | 8.1pF | ±0.05pF | GJM0222C1E8R1WB01# |
| | | | | ±0.1pF | GJM0222C1E8R1BB01# |
| | | | | ±0.25pF | GJM0222C1E8R1CB01# |
| | | | | ±0.5pF | GJM0222C1E8R1DB01# |
| | | | 8.2pF | ±0.05pF | GJM0222C1E8R2WB01# |
| | | | | ±0.1pF | GJM0222C1E8R2BB01# |
| | | | | ±0.25pF | GJM0222C1E8R2CB01# |
| | | | | ±0.5pF | GJM0222C1E8R2DB01# |
| | | | 8.3pF | ±0.05pF | GJM0222C1E8R3WB01# |
| | | | | ±0.1pF | GJM0222C1E8R3BB01# |
| | | | | ±0.25pF | GJM0222C1E8R3CB01# |
| | | | | ±0.5pF | GJM0222C1E8R3DB01# |
| | | | 8.4pF | ±0.05pF | GJM0222C1E8R4WB01# |
| | | | | ±0.1pF | GJM0222C1E8R4BB01# |
| | | | | ±0.25pF | GJM0222C1E8R4CB01# |
| | | | | ±0.5pF | GJM0222C1E8R4DB01# |
| | | | 8.5pF | ±0.05pF | GJM0222C1E8R5WB01# |
| | | | | ±0.1pF | GJM0222C1E8R5BB01# |
| | | | | ±0.25pF | GJM0222C1E8R5CB01# |
| | | | | ±0.5pF | GJM0222C1E8R5DB01# |
| | | | 8.6pF | ±0.05pF | GJM0222C1E8R6WB01# |
| | | | | ±0.1pF | GJM0222C1E8R6BB01# |
| | | | | ±0.25pF | GJM0222C1E8R6CB01# |
| | | | | ±0.5pF | GJM0222C1E8R6DB01# |
| | | | 8.7pF | ±0.05pF | GJM0222C1E8R7WB01# |
| | | | | ±0.1pF | GJM0222C1E8R7BB01# |
| | | | | ±0.25pF | GJM0222C1E8R7CB01# |
| | | | | ±0.5pF | GJM0222C1E8R7DB01# |
| | | | 8.8pF | ±0.05pF | GJM0222C1E8R8WB01# |
| | | | | ±0.1pF | GJM0222C1E8R8BB01# |
| | | | | ±0.25pF | GJM0222C1E8R8CB01# |
| | | | | ±0.5pF | GJM0222C1E8R8DB01# |
| | | | 8.9pF | ±0.05pF | GJM0222C1E8R9WB01# |
| | | | | ±0.1pF | GJM0222C1E8R9BB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.22mm | 25Vdc | CH | 8.9pF | ±0.25pF | GJM0222C1E8R9CB01# |
| | | | | ±0.5pF | GJM0222C1E8R9DB01# |
| | | | 9.0pF | ±0.05pF | GJM0222C1E9R0WB01# |
| | | | | ±0.1pF | GJM0222C1E9R0BB01# |
| | | | | ±0.25pF | GJM0222C1E9R0CB01# |
| | | | | ±0.5pF | GJM0222C1E9R0DB01# |
| | | | 9.1pF | ±0.05pF | GJM0222C1E9R1WB01# |
| | | | | ±0.1pF | GJM0222C1E9R1BB01# |
| | | | | ±0.25pF | GJM0222C1E9R1CB01# |
| | | | | ±0.5pF | GJM0222C1E9R1DB01# |
| | | | 9.2pF | ±0.05pF | GJM0222C1E9R2WB01# |
| | | | | ±0.1pF | GJM0222C1E9R2BB01# |
| | | | | ±0.25pF | GJM0222C1E9R2CB01# |
| | | | | ±0.5pF | GJM0222C1E9R2DB01# |
| | | | 9.3pF | ±0.05pF | GJM0222C1E9R3WB01# |
| | | | | ±0.1pF | GJM0222C1E9R3BB01# |
| | | | | ±0.25pF | GJM0222C1E9R3CB01# |
| | | | | ±0.5pF | GJM0222C1E9R3DB01# |
| | | | 9.4pF | ±0.05pF | GJM0222C1E9R4WB01# |
| | | | | ±0.1pF | GJM0222C1E9R4BB01# |
| | | | | ±0.25pF | GJM0222C1E9R4CB01# |
| | | | | ±0.5pF | GJM0222C1E9R4DB01# |
| | | | 9.5pF | ±0.05pF | GJM0222C1E9R5WB01# |
| | | | | ±0.1pF | GJM0222C1E9R5BB01# |
| | | | | ±0.25pF | GJM0222C1E9R5CB01# |
| | | | | ±0.5pF | GJM0222C1E9R5DB01# |
| | | | 9.6pF | ±0.05pF | GJM0222C1E9R6WB01# |
| | | | | ±0.1pF | GJM0222C1E9R6BB01# |
| | | | | ±0.25pF | GJM0222C1E9R6CB01# |
| | | | | ±0.5pF | GJM0222C1E9R6DB01# |
| | | | 9.7pF | ±0.05pF | GJM0222C1E9R7WB01# |
| | | | | ±0.1pF | GJM0222C1E9R7BB01# |
| | | | | ±0.25pF | GJM0222C1E9R7CB01# |
| | | | | ±0.5pF | GJM0222C1E9R7DB01# |
| | | | 9.8pF | ±0.05pF | GJM0222C1E9R8WB01# |
| | | | | ±0.1pF | GJM0222C1E9R8BB01# |
| | | | | ±0.25pF | GJM0222C1E9R8CB01# |
| | | | | ±0.5pF | GJM0222C1E9R8DB01# |
| | | | 9.9pF | ±0.05pF | GJM0222C1E9R9WB01# |
| | | | | ±0.1pF | GJM0222C1E9R9BB01# |
| | | | | ±0.25pF | GJM0222C1E9R9CB01# |
| | | | | ±0.5pF | GJM0222C1E9R9DB01# |
| | | | 10pF | ±2% | GJM0222C1E100GB01# |
| | | | | ±5% | GJM0222C1E100JB01# |
| | | | 11pF | ±2% | GJM0222C1E110GB01# |
| | | | | ±5% | GJM0222C1E110JB01# |
| | | | 12pF | ±2% | GJM0222C1E120GB01# |
| | | | | ±5% | GJM0222C1E120JB01# |
| | | | 13pF | ±2% | GJM0222C1E130GB01# |
| | | | | ±5% | GJM0222C1E130JB01# |
| | | | 15pF | ±2% | GJM0222C1E150GB01# |
| | | | | ±5% | GJM0222C1E150JB01# |
| | | | 16pF | ±2% | GJM0222C1E160GB01# |
| | | | | ±5% | GJM0222C1E160JB01# |
| 0.22mm | 25Vdc | CH | 18pF | ±2% | GJM0222C1E180GB01# |
| | | | | ±5% | GJM0222C1E180JB01# |
| | | | 20pF | ±2% | GJM0222C1E200GB01# |
| | | | | ±5% | GJM0222C1E200JB01# |
| | | | 22pF | ±2% | GJM0222C1E220GB01# |
| | | | | ±5% | GJM0222C1E220JB01# |

## ■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 0.20pF | ±0.05pF | GJM0335C1ER20WB01# |
| | | | | ±0.1pF | GJM0335C1ER20BB01# |
| | | | 0.30pF | ±0.05pF | GJM0335C1ER30WB01# |
| | | | | ±0.1pF | GJM0335C1ER30BB01# |
| | | | 0.40pF | ±0.05pF | GJM0335C1ER40WB01# |
| | | | | ±0.1pF | GJM0335C1ER40BB01# |
| | | | 0.50pF | ±0.05pF | GJM0335C1ER50WB01# |
| | | | | ±0.1pF | GJM0335C1ER50BB01# |
| | | | 0.60pF | ±0.05pF | GJM0335C1ER60WB01# |
| | | | | ±0.1pF | GJM0335C1ER60BB01# |
| | | | 0.70pF | ±0.05pF | GJM0335C1ER70WB01# |
| | | | | ±0.1pF | GJM0335C1ER70BB01# |
| | | | 0.80pF | ±0.05pF | GJM0335C1ER80WB01# |
| | | | | ±0.1pF | GJM0335C1ER80BB01# |
| | | | 0.90pF | ±0.05pF | GJM0335C1ER90WB01# |
| | | | | ±0.1pF | GJM0335C1ER90BB01# |
| | | | 1.0pF | ±0.05pF | GJM0335C1E1R0WB01# |
| | | | | ±0.1pF | GJM0335C1E1R0BB01# |
| | | | | ±0.25pF | GJM0335C1E1R0CB01# |
| | | | 1.1pF | ±0.05pF | GJM0335C1E1R1WB01# |
| | | | | ±0.1pF | GJM0335C1E1R1BB01# |
| | | | | ±0.25pF | GJM0335C1E1R1CB01# |
| | | | 1.2pF | ±0.05pF | GJM0335C1E1R2WB01# |
| | | | | ±0.1pF | GJM0335C1E1R2BB01# |
| | | | | ±0.25pF | GJM0335C1E1R2CB01# |
| | | | 1.3pF | ±0.05pF | GJM0335C1E1R3WB01# |
| | | | | ±0.1pF | GJM0335C1E1R3BB01# |
| | | | | ±0.25pF | GJM0335C1E1R3CB01# |
| | | | 1.4pF | ±0.05pF | GJM0335C1E1R4WB01# |
| | | | | ±0.1pF | GJM0335C1E1R4BB01# |
| | | | | ±0.25pF | GJM0335C1E1R4CB01# |
| | | | 1.5pF | ±0.05pF | GJM0335C1E1R5WB01# |
| | | | | ±0.1pF | GJM0335C1E1R5BB01# |
| | | | | ±0.25pF | GJM0335C1E1R5CB01# |
| | | | 1.6pF | ±0.05pF | GJM0335C1E1R6WB01# |
| | | | | ±0.1pF | GJM0335C1E1R6BB01# |
| | | | | ±0.25pF | GJM0335C1E1R6CB01# |
| | | | 1.7pF | ±0.05pF | GJM0335C1E1R7WB01# |
| | | | | ±0.1pF | GJM0335C1E1R7BB01# |
| | | | | ±0.25pF | GJM0335C1E1R7CB01# |
| | | | 1.8pF | ±0.05pF | GJM0335C1E1R8WB01# |
| | | | | ±0.1pF | GJM0335C1E1R8BB01# |
| | | | | ±0.25pF | GJM0335C1E1R8CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 1.9pF | ±0.05pF | **GJM0335C1E1R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E1R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E1R9CB01#** |
| | | | 2.0pF | ±0.05pF | **GJM0335C1E2R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R0CB01#** |
| | | | 2.1pF | ±0.05pF | **GJM0335C1E2R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R1CB01#** |
| | | | 2.2pF | ±0.05pF | **GJM0335C1E2R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R2CB01#** |
| | | | 2.3pF | ±0.05pF | **GJM0335C1E2R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R3CB01#** |
| | | | 2.4pF | ±0.05pF | **GJM0335C1E2R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R4CB01#** |
| | | | 2.5pF | ±0.05pF | **GJM0335C1E2R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R5CB01#** |
| | | | 2.6pF | ±0.05pF | **GJM0335C1E2R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R6CB01#** |
| | | | 2.7pF | ±0.05pF | **GJM0335C1E2R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R7BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R7CB01#** |
| | | | 2.8pF | ±0.05pF | **GJM0335C1E2R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R8CB01#** |
| | | | 2.9pF | ±0.05pF | **GJM0335C1E2R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E2R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E2R9CB01#** |
| | | | 3.0pF | ±0.05pF | **GJM0335C1E3R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R0CB01#** |
| | | | 3.1pF | ±0.05pF | **GJM0335C1E3R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R1CB01#** |
| | | | 3.2pF | ±0.05pF | **GJM0335C1E3R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R2CB01#** |
| | | | 3.3pF | ±0.05pF | **GJM0335C1E3R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R3CB01#** |
| | | | 3.4pF | ±0.05pF | **GJM0335C1E3R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R4CB01#** |
| | | | 3.5pF | ±0.05pF | **GJM0335C1E3R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R5CB01#** |
| | | | 3.6pF | ±0.05pF | **GJM0335C1E3R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R6CB01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 3.7pF | ±0.05pF | **GJM0335C1E3R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R7BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R7CB01#** |
| | | | 3.8pF | ±0.05pF | **GJM0335C1E3R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R8CB01#** |
| | | | 3.9pF | ±0.05pF | **GJM0335C1E3R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E3R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E3R9CB01#** |
| | | | 4.0pF | ±0.05pF | **GJM0335C1E4R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R0CB01#** |
| | | | 4.1pF | ±0.05pF | **GJM0335C1E4R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R1CB01#** |
| | | | 4.2pF | ±0.05pF | **GJM0335C1E4R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R2CB01#** |
| | | | 4.3pF | ±0.05pF | **GJM0335C1E4R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R3CB01#** |
| | | | 4.4pF | ±0.05pF | **GJM0335C1E4R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R4CB01#** |
| | | | 4.5pF | ±0.05pF | **GJM0335C1E4R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R5CB01#** |
| | | | 4.6pF | ±0.05pF | **GJM0335C1E4R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R6CB01#** |
| | | | 4.7pF | ±0.05pF | **GJM0335C1E4R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R7BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R7CB01#** |
| | | | 4.8pF | ±0.05pF | **GJM0335C1E4R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R8CB01#** |
| | | | 4.9pF | ±0.05pF | **GJM0335C1E4R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E4R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E4R9CB01#** |
| | | | 5.0pF | ±0.05pF | **GJM0335C1E5R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R0CB01#** |
| | | | 5.1pF | ±0.05pF | **GJM0335C1E5R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R1CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R1DB01#** |
| | | | 5.2pF | ±0.05pF | **GJM0335C1E5R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R2CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R2DB01#** |
| | | | 5.3pF | ±0.05pF | **GJM0335C1E5R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R3CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R3DB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 5.4pF | ±0.05pF | **GJM0335C1E5R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R4CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R4DB01#** |
| | | | 5.5pF | ±0.05pF | **GJM0335C1E5R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R5CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R5DB01#** |
| | | | 5.6pF | ±0.05pF | **GJM0335C1E5R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R6CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R6DB01#** |
| | | | 5.7pF | ±0.05pF | **GJM0335C1E5R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R7BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R7CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R7DB01#** |
| | | | 5.8pF | ±0.05pF | **GJM0335C1E5R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R8CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R8DB01#** |
| | | | 5.9pF | ±0.05pF | **GJM0335C1E5R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E5R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E5R9CB01#** |
| | | | | ±0.5pF | **GJM0335C1E5R9DB01#** |
| | | | 6.0pF | ±0.05pF | **GJM0335C1E6R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R0CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R0DB01#** |
| | | | 6.1pF | ±0.05pF | **GJM0335C1E6R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R1CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R1DB01#** |
| | | | 6.2pF | ±0.05pF | **GJM0335C1E6R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R2CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R2DB01#** |
| | | | 6.3pF | ±0.05pF | **GJM0335C1E6R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R3CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R3DB01#** |
| | | | 6.4pF | ±0.05pF | **GJM0335C1E6R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R4CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R4DB01#** |
| | | | 6.5pF | ±0.05pF | **GJM0335C1E6R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R5CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R5DB01#** |
| | | | 6.6pF | ±0.05pF | **GJM0335C1E6R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R6CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R6DB01#** |
| | | | 6.7pF | ±0.05pF | **GJM0335C1E6R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R7BB01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 6.7pF | ±0.25pF | **GJM0335C1E6R7CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R7DB01#** |
| | | | 6.8pF | ±0.05pF | **GJM0335C1E6R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R8CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R8DB01#** |
| | | | 6.9pF | ±0.05pF | **GJM0335C1E6R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E6R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E6R9CB01#** |
| | | | | ±0.5pF | **GJM0335C1E6R9DB01#** |
| | | | 7.0pF | ±0.05pF | **GJM0335C1E7R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R0CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R0DB01#** |
| | | | 7.1pF | ±0.05pF | **GJM0335C1E7R1WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R1BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R1CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R1DB01#** |
| | | | 7.2pF | ±0.05pF | **GJM0335C1E7R2WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R2BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R2CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R2DB01#** |
| | | | 7.3pF | ±0.05pF | **GJM0335C1E7R3WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R3BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R3CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R3DB01#** |
| | | | 7.4pF | ±0.05pF | **GJM0335C1E7R4WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R4BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R4CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R4DB01#** |
| | | | 7.5pF | ±0.05pF | **GJM0335C1E7R5WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R5BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R5CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R5DB01#** |
| | | | 7.6pF | ±0.05pF | **GJM0335C1E7R6WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R6BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R6CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R6DB01#** |
| | | | 7.7pF | ±0.05pF | **GJM0335C1E7R7WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R7BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R7CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R7DB01#** |
| | | | 7.8pF | ±0.05pF | **GJM0335C1E7R8WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R8BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R8CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R8DB01#** |
| | | | 7.9pF | ±0.05pF | **GJM0335C1E7R9WB01#** |
| | | | | ±0.1pF | **GJM0335C1E7R9BB01#** |
| | | | | ±0.25pF | **GJM0335C1E7R9CB01#** |
| | | | | ±0.5pF | **GJM0335C1E7R9DB01#** |
| | | | 8.0pF | ±0.05pF | **GJM0335C1E8R0WB01#** |
| | | | | ±0.1pF | **GJM0335C1E8R0BB01#** |
| | | | | ±0.25pF | **GJM0335C1E8R0CB01#** |
| | | | | ±0.5pF | **GJM0335C1E8R0DB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | C0G | 8.1pF | ±0.05pF | GJM0335C1E8R1WB01# |
| | | | | ±0.1pF | GJM0335C1E8R1BB01# |
| | | | | ±0.25pF | GJM0335C1E8R1CB01# |
| | | | | ±0.5pF | GJM0335C1E8R1DB01# |
| | | | 8.2pF | ±0.05pF | GJM0335C1E8R2WB01# |
| | | | | ±0.1pF | GJM0335C1E8R2BB01# |
| | | | | ±0.25pF | GJM0335C1E8R2CB01# |
| | | | | ±0.5pF | GJM0335C1E8R2DB01# |
| | | | 8.3pF | ±0.05pF | GJM0335C1E8R3WB01# |
| | | | | ±0.1pF | GJM0335C1E8R3BB01# |
| | | | | ±0.25pF | GJM0335C1E8R3CB01# |
| | | | | ±0.5pF | GJM0335C1E8R3DB01# |
| | | | 8.4pF | ±0.05pF | GJM0335C1E8R4WB01# |
| | | | | ±0.1pF | GJM0335C1E8R4BB01# |
| | | | | ±0.25pF | GJM0335C1E8R4CB01# |
| | | | | ±0.5pF | GJM0335C1E8R4DB01# |
| | | | 8.5pF | ±0.05pF | GJM0335C1E8R5WB01# |
| | | | | ±0.1pF | GJM0335C1E8R5BB01# |
| | | | | ±0.25pF | GJM0335C1E8R5CB01# |
| | | | | ±0.5pF | GJM0335C1E8R5DB01# |
| | | | 8.6pF | ±0.05pF | GJM0335C1E8R6WB01# |
| | | | | ±0.1pF | GJM0335C1E8R6BB01# |
| | | | | ±0.25pF | GJM0335C1E8R6CB01# |
| | | | | ±0.5pF | GJM0335C1E8R6DB01# |
| | | | 8.7pF | ±0.05pF | GJM0335C1E8R7WB01# |
| | | | | ±0.1pF | GJM0335C1E8R7BB01# |
| | | | | ±0.25pF | GJM0335C1E8R7CB01# |
| | | | | ±0.5pF | GJM0335C1E8R7DB01# |
| | | | 8.8pF | ±0.05pF | GJM0335C1E8R8WB01# |
| | | | | ±0.1pF | GJM0335C1E8R8BB01# |
| | | | | ±0.25pF | GJM0335C1E8R8CB01# |
| | | | | ±0.5pF | GJM0335C1E8R8DB01# |
| | | | 8.9pF | ±0.05pF | GJM0335C1E8R9WB01# |
| | | | | ±0.1pF | GJM0335C1E8R9BB01# |
| | | | | ±0.25pF | GJM0335C1E8R9CB01# |
| | | | | ±0.5pF | GJM0335C1E8R9DB01# |
| | | | 9.0pF | ±0.05pF | GJM0335C1E9R0WB01# |
| | | | | ±0.1pF | GJM0335C1E9R0BB01# |
| | | | | ±0.25pF | GJM0335C1E9R0CB01# |
| | | | | ±0.5pF | GJM0335C1E9R0DB01# |
| | | | 9.1pF | ±0.05pF | GJM0335C1E9R1WB01# |
| | | | | ±0.1pF | GJM0335C1E9R1BB01# |
| | | | | ±0.25pF | GJM0335C1E9R1CB01# |
| | | | | ±0.5pF | GJM0335C1E9R1DB01# |
| | | | 9.2pF | ±0.05pF | GJM0335C1E9R2WB01# |
| | | | | ±0.1pF | GJM0335C1E9R2BB01# |
| | | | | ±0.25pF | GJM0335C1E9R2CB01# |
| | | | | ±0.5pF | GJM0335C1E9R2DB01# |
| | | | 9.3pF | ±0.05pF | GJM0335C1E9R3WB01# |
| | | | | ±0.1pF | GJM0335C1E9R3BB01# |
| | | | | ±0.25pF | GJM0335C1E9R3CB01# |
| | | | | ±0.5pF | GJM0335C1E9R3DB01# |
| | | | 9.4pF | ±0.05pF | GJM0335C1E9R4WB01# |
| | | | | ±0.1pF | GJM0335C1E9R4BB01# |
| 0.33mm | 25Vdc | C0G | 9.4pF | ±0.25pF | GJM0335C1E9R4CB01# |
| | | | | ±0.5pF | GJM0335C1E9R4DB01# |
| | | | 9.5pF | ±0.05pF | GJM0335C1E9R5WB01# |
| | | | | ±0.1pF | GJM0335C1E9R5BB01# |
| | | | | ±0.25pF | GJM0335C1E9R5CB01# |
| | | | | ±0.5pF | GJM0335C1E9R5DB01# |
| | | | 9.6pF | ±0.05pF | GJM0335C1E9R6WB01# |
| | | | | ±0.1pF | GJM0335C1E9R6BB01# |
| | | | | ±0.25pF | GJM0335C1E9R6CB01# |
| | | | | ±0.5pF | GJM0335C1E9R6DB01# |
| | | | 9.7pF | ±0.05pF | GJM0335C1E9R7WB01# |
| | | | | ±0.1pF | GJM0335C1E9R7BB01# |
| | | | | ±0.25pF | GJM0335C1E9R7CB01# |
| | | | | ±0.5pF | GJM0335C1E9R7DB01# |
| | | | 9.8pF | ±0.05pF | GJM0335C1E9R8WB01# |
| | | | | ±0.1pF | GJM0335C1E9R8BB01# |
| | | | | ±0.25pF | GJM0335C1E9R8CB01# |
| | | | | ±0.5pF | GJM0335C1E9R8DB01# |
| | | | 9.9pF | ±0.05pF | GJM0335C1E9R9WB01# |
| | | | | ±0.1pF | GJM0335C1E9R9BB01# |
| | | | | ±0.25pF | GJM0335C1E9R9CB01# |
| | | | | ±0.5pF | GJM0335C1E9R9DB01# |
| | | | 10pF | ±2% | GJM0335C1E100GB01# |
| | | | | ±5% | GJM0335C1E100JB01# |
| | | | 11pF | ±2% | GJM0335C1E110GB01# |
| | | | | ±5% | GJM0335C1E110JB01# |
| | | | 12pF | ±2% | GJM0335C1E120GB01# |
| | | | | ±5% | GJM0335C1E120JB01# |
| | | | 13pF | ±2% | GJM0335C1E130GB01# |
| | | | | ±5% | GJM0335C1E130JB01# |
| | | | 15pF | ±2% | GJM0335C1E150GB01# |
| | | | | ±5% | GJM0335C1E150JB01# |
| | | | 16pF | ±2% | GJM0335C1E160GB01# |
| | | | | ±5% | GJM0335C1E160JB01# |
| | | | 18pF | ±2% | GJM0335C1E180GB01# |
| | | | | ±5% | GJM0335C1E180JB01# |
| | | | 20pF | ±2% | GJM0335C1E200GB01# |
| | | | | ±5% | GJM0335C1E200JB01# |
| | | | 22pF | ±2% | GJM0335C1E220GB01# |
| | | | | ±5% | GJM0335C1E220JB01# |
| | | | 24pF | ±2% | GJM0335C1E240GB01# |
| | | | | ±5% | GJM0335C1E240JB01# |
| | | | 27pF | ±2% | GJM0335C1E270GB01# |
| | | | | ±5% | GJM0335C1E270JB01# |
| | | | 30pF | ±2% | GJM0335C1E300GB01# |
| | | | | ±5% | GJM0335C1E300JB01# |
| | | | 33pF | ±2% | GJM0335C1E330GB01# |
| | | | | ±5% | GJM0335C1E330JB01# |
| | | CK | 0.20pF | ±0.05pF | GJM0334C1ER20WB01# |
| | | | | ±0.1pF | GJM0334C1ER20BB01# |
| | | | 0.30pF | ±0.05pF | GJM0334C1ER30WB01# |
| | | | | ±0.1pF | GJM0334C1ER30BB01# |
| | | | 0.40pF | ±0.05pF | GJM0334C1ER40WB01# |
| | | | | ±0.1pF | GJM0334C1ER40BB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | CK | 0.50pF | ±0.05pF | GJM0334C1ER50WB01# |
| | | | | ±0.1pF | GJM0334C1ER50BB01# |
| | | | 0.60pF | ±0.05pF | GJM0334C1ER60WB01# |
| | | | | ±0.1pF | GJM0334C1ER60BB01# |
| | | | 0.70pF | ±0.05pF | GJM0334C1ER70WB01# |
| | | | | ±0.1pF | GJM0334C1ER70BB01# |
| | | | 0.80pF | ±0.05pF | GJM0334C1ER80WB01# |
| | | | | ±0.1pF | GJM0334C1ER80BB01# |
| | | | 0.90pF | ±0.05pF | GJM0334C1ER90WB01# |
| | | | | ±0.1pF | GJM0334C1ER90BB01# |
| | | | 1.0pF | ±0.05pF | GJM0334C1E1R0WB01# |
| | | | | ±0.1pF | GJM0334C1E1R0BB01# |
| | | | | ±0.25pF | GJM0334C1E1R0CB01# |
| | | | 1.1pF | ±0.05pF | GJM0334C1E1R1WB01# |
| | | | | ±0.1pF | GJM0334C1E1R1BB01# |
| | | | | ±0.25pF | GJM0334C1E1R1CB01# |
| | | | 1.2pF | ±0.05pF | GJM0334C1E1R2WB01# |
| | | | | ±0.1pF | GJM0334C1E1R2BB01# |
| | | | | ±0.25pF | GJM0334C1E1R2CB01# |
| | | | 1.3pF | ±0.05pF | GJM0334C1E1R3WB01# |
| | | | | ±0.1pF | GJM0334C1E1R3BB01# |
| | | | | ±0.25pF | GJM0334C1E1R3CB01# |
| | | | 1.4pF | ±0.05pF | GJM0334C1E1R4WB01# |
| | | | | ±0.1pF | GJM0334C1E1R4BB01# |
| | | | | ±0.25pF | GJM0334C1E1R4CB01# |
| | | | 1.5pF | ±0.05pF | GJM0334C1E1R5WB01# |
| | | | | ±0.1pF | GJM0334C1E1R5BB01# |
| | | | | ±0.25pF | GJM0334C1E1R5CB01# |
| | | | 1.6pF | ±0.05pF | GJM0334C1E1R6WB01# |
| | | | | ±0.1pF | GJM0334C1E1R6BB01# |
| | | | | ±0.25pF | GJM0334C1E1R6CB01# |
| | | | 1.7pF | ±0.05pF | GJM0334C1E1R7WB01# |
| | | | | ±0.1pF | GJM0334C1E1R7BB01# |
| | | | | ±0.25pF | GJM0334C1E1R7CB01# |
| | | | 1.8pF | ±0.05pF | GJM0334C1E1R8WB01# |
| | | | | ±0.1pF | GJM0334C1E1R8BB01# |
| | | | | ±0.25pF | GJM0334C1E1R8CB01# |
| | | | 1.9pF | ±0.05pF | GJM0334C1E1R9WB01# |
| | | | | ±0.1pF | GJM0334C1E1R9BB01# |
| | | | | ±0.25pF | GJM0334C1E1R9CB01# |
| | | | 2.0pF | ±0.05pF | GJM0334C1E2R0WB01# |
| | | | | ±0.1pF | GJM0334C1E2R0BB01# |
| | | | | ±0.25pF | GJM0334C1E2R0CB01# |
| | | CJ | 2.1pF | ±0.05pF | GJM0333C1E2R1WB01# |
| | | | | ±0.1pF | GJM0333C1E2R1BB01# |
| | | | | ±0.25pF | GJM0333C1E2R1CB01# |
| | | | 2.2pF | ±0.05pF | GJM0333C1E2R2WB01# |
| | | | | ±0.1pF | GJM0333C1E2R2BB01# |
| | | | | ±0.25pF | GJM0333C1E2R2CB01# |
| | | | 2.3pF | ±0.05pF | GJM0333C1E2R3WB01# |
| | | | | ±0.1pF | GJM0333C1E2R3BB01# |
| | | | | ±0.25pF | GJM0333C1E2R3CB01# |
| | | | 2.4pF | ±0.05pF | GJM0333C1E2R4WB01# |
| | | | | ±0.1pF | GJM0333C1E2R4BB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | CJ | 2.4pF | ±0.25pF | GJM0333C1E2R4CB01# |
| | | | 2.5pF | ±0.05pF | GJM0333C1E2R5WB01# |
| | | | | ±0.1pF | GJM0333C1E2R5BB01# |
| | | | | ±0.25pF | GJM0333C1E2R5CB01# |
| | | | 2.6pF | ±0.05pF | GJM0333C1E2R6WB01# |
| | | | | ±0.1pF | GJM0333C1E2R6BB01# |
| | | | | ±0.25pF | GJM0333C1E2R6CB01# |
| | | | 2.7pF | ±0.05pF | GJM0333C1E2R7WB01# |
| | | | | ±0.1pF | GJM0333C1E2R7BB01# |
| | | | | ±0.25pF | GJM0333C1E2R7CB01# |
| | | | 2.8pF | ±0.05pF | GJM0333C1E2R8WB01# |
| | | | | ±0.1pF | GJM0333C1E2R8BB01# |
| | | | | ±0.25pF | GJM0333C1E2R8CB01# |
| | | | 2.9pF | ±0.05pF | GJM0333C1E2R9WB01# |
| | | | | ±0.1pF | GJM0333C1E2R9BB01# |
| | | | | ±0.25pF | GJM0333C1E2R9CB01# |
| | | | 3.0pF | ±0.05pF | GJM0333C1E3R0WB01# |
| | | | | ±0.1pF | GJM0333C1E3R0BB01# |
| | | | | ±0.25pF | GJM0333C1E3R0CB01# |
| | | | 3.1pF | ±0.05pF | GJM0333C1E3R1WB01# |
| | | | | ±0.1pF | GJM0333C1E3R1BB01# |
| | | | | ±0.25pF | GJM0333C1E3R1CB01# |
| | | | 3.2pF | ±0.05pF | GJM0333C1E3R2WB01# |
| | | | | ±0.1pF | GJM0333C1E3R2BB01# |
| | | | | ±0.25pF | GJM0333C1E3R2CB01# |
| | | | 3.3pF | ±0.05pF | GJM0333C1E3R3WB01# |
| | | | | ±0.1pF | GJM0333C1E3R3BB01# |
| | | | | ±0.25pF | GJM0333C1E3R3CB01# |
| | | | 3.4pF | ±0.05pF | GJM0333C1E3R4WB01# |
| | | | | ±0.1pF | GJM0333C1E3R4BB01# |
| | | | | ±0.25pF | GJM0333C1E3R4CB01# |
| | | | 3.5pF | ±0.05pF | GJM0333C1E3R5WB01# |
| | | | | ±0.1pF | GJM0333C1E3R5BB01# |
| | | | | ±0.25pF | GJM0333C1E3R5CB01# |
| | | | 3.6pF | ±0.05pF | GJM0333C1E3R6WB01# |
| | | | | ±0.1pF | GJM0333C1E3R6BB01# |
| | | | | ±0.25pF | GJM0333C1E3R6CB01# |
| | | | 3.7pF | ±0.05pF | GJM0333C1E3R7WB01# |
| | | | | ±0.1pF | GJM0333C1E3R7BB01# |
| | | | | ±0.25pF | GJM0333C1E3R7CB01# |
| | | | 3.8pF | ±0.05pF | GJM0333C1E3R8WB01# |
| | | | | ±0.1pF | GJM0333C1E3R8BB01# |
| | | | | ±0.25pF | GJM0333C1E3R8CB01# |
| | | | 3.9pF | ±0.05pF | GJM0333C1E3R9WB01# |
| | | | | ±0.1pF | GJM0333C1E3R9BB01# |
| | | | | ±0.25pF | GJM0333C1E3R9CB01# |
| | | CH | 4.0pF | ±0.05pF | GJM0332C1E4R0WB01# |
| | | | | ±0.1pF | GJM0332C1E4R0BB01# |
| | | | | ±0.25pF | GJM0332C1E4R0CB01# |
| | | | 4.1pF | ±0.05pF | GJM0332C1E4R1WB01# |
| | | | | ±0.1pF | GJM0332C1E4R1BB01# |
| | | | | ±0.25pF | GJM0332C1E4R1CB01# |
| | | | 4.2pF | ±0.05pF | GJM0332C1E4R2WB01# |
| | | | | ±0.1pF | GJM0332C1E4R2BB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | CH | 4.2pF | ±0.25pF | GJM0332C1E4R2CB01# |
| | | | 4.3pF | ±0.05pF | GJM0332C1E4R3WB01# |
| | | | | ±0.1pF | GJM0332C1E4R3BB01# |
| | | | | ±0.25pF | GJM0332C1E4R3CB01# |
| | | | 4.4pF | ±0.05pF | GJM0332C1E4R4WB01# |
| | | | | ±0.1pF | GJM0332C1E4R4BB01# |
| | | | | ±0.25pF | GJM0332C1E4R4CB01# |
| | | | 4.5pF | ±0.05pF | GJM0332C1E4R5WB01# |
| | | | | ±0.1pF | GJM0332C1E4R5BB01# |
| | | | | ±0.25pF | GJM0332C1E4R5CB01# |
| | | | 4.6pF | ±0.05pF | GJM0332C1E4R6WB01# |
| | | | | ±0.1pF | GJM0332C1E4R6BB01# |
| | | | | ±0.25pF | GJM0332C1E4R6CB01# |
| | | | 4.7pF | ±0.05pF | GJM0332C1E4R7WB01# |
| | | | | ±0.1pF | GJM0332C1E4R7BB01# |
| | | | | ±0.25pF | GJM0332C1E4R7CB01# |
| | | | 4.8pF | ±0.05pF | GJM0332C1E4R8WB01# |
| | | | | ±0.1pF | GJM0332C1E4R8BB01# |
| | | | | ±0.25pF | GJM0332C1E4R8CB01# |
| | | | 4.9pF | ±0.05pF | GJM0332C1E4R9WB01# |
| | | | | ±0.1pF | GJM0332C1E4R9BB01# |
| | | | | ±0.25pF | GJM0332C1E4R9CB01# |
| | | | 5.0pF | ±0.05pF | GJM0332C1E5R0WB01# |
| | | | | ±0.1pF | GJM0332C1E5R0BB01# |
| | | | | ±0.25pF | GJM0332C1E5R0CB01# |
| | | | 5.1pF | ±0.05pF | GJM0332C1E5R1WB01# |
| | | | | ±0.1pF | GJM0332C1E5R1BB01# |
| | | | | ±0.25pF | GJM0332C1E5R1CB01# |
| | | | | ±0.5pF | GJM0332C1E5R1DB01# |
| | | | 5.2pF | ±0.05pF | GJM0332C1E5R2WB01# |
| | | | | ±0.1pF | GJM0332C1E5R2BB01# |
| | | | | ±0.25pF | GJM0332C1E5R2CB01# |
| | | | | ±0.5pF | GJM0332C1E5R2DB01# |
| | | | 5.3pF | ±0.05pF | GJM0332C1E5R3WB01# |
| | | | | ±0.1pF | GJM0332C1E5R3BB01# |
| | | | | ±0.25pF | GJM0332C1E5R3CB01# |
| | | | | ±0.5pF | GJM0332C1E5R3DB01# |
| | | | 5.4pF | ±0.05pF | GJM0332C1E5R4WB01# |
| | | | | ±0.1pF | GJM0332C1E5R4BB01# |
| | | | | ±0.25pF | GJM0332C1E5R4CB01# |
| | | | | ±0.5pF | GJM0332C1E5R4DB01# |
| | | | 5.5pF | ±0.05pF | GJM0332C1E5R5WB01# |
| | | | | ±0.1pF | GJM0332C1E5R5BB01# |
| | | | | ±0.25pF | GJM0332C1E5R5CB01# |
| | | | | ±0.5pF | GJM0332C1E5R5DB01# |
| | | | 5.6pF | ±0.05pF | GJM0332C1E5R6WB01# |
| | | | | ±0.1pF | GJM0332C1E5R6BB01# |
| | | | | ±0.25pF | GJM0332C1E5R6CB01# |
| | | | | ±0.5pF | GJM0332C1E5R6DB01# |
| | | | 5.7pF | ±0.05pF | GJM0332C1E5R7WB01# |
| | | | | ±0.1pF | GJM0332C1E5R7BB01# |
| | | | | ±0.25pF | GJM0332C1E5R7CB01# |
| | | | | ±0.5pF | GJM0332C1E5R7DB01# |
| | | | 5.8pF | ±0.05pF | GJM0332C1E5R8WB01# |
| | | | | ±0.1pF | GJM0332C1E5R8BB01# |
| | | | | ±0.25pF | GJM0332C1E5R8CB01# |
| | | | | ±0.5pF | GJM0332C1E5R8DB01# |
| | | | 5.9pF | ±0.05pF | GJM0332C1E5R9WB01# |
| | | | | ±0.1pF | GJM0332C1E5R9BB01# |
| | | | | ±0.25pF | GJM0332C1E5R9CB01# |
| | | | | ±0.5pF | GJM0332C1E5R9DB01# |
| | | | 6.0pF | ±0.05pF | GJM0332C1E6R0WB01# |
| | | | | ±0.1pF | GJM0332C1E6R0BB01# |
| | | | | ±0.25pF | GJM0332C1E6R0CB01# |
| | | | | ±0.5pF | GJM0332C1E6R0DB01# |
| | | | 6.1pF | ±0.05pF | GJM0332C1E6R1WB01# |
| | | | | ±0.1pF | GJM0332C1E6R1BB01# |
| | | | | ±0.25pF | GJM0332C1E6R1CB01# |
| | | | | ±0.5pF | GJM0332C1E6R1DB01# |
| | | | 6.2pF | ±0.05pF | GJM0332C1E6R2WB01# |
| | | | | ±0.1pF | GJM0332C1E6R2BB01# |
| | | | | ±0.25pF | GJM0332C1E6R2CB01# |
| | | | | ±0.5pF | GJM0332C1E6R2DB01# |
| | | | 6.3pF | ±0.05pF | GJM0332C1E6R3WB01# |
| | | | | ±0.1pF | GJM0332C1E6R3BB01# |
| | | | | ±0.25pF | GJM0332C1E6R3CB01# |
| | | | | ±0.5pF | GJM0332C1E6R3DB01# |
| | | | 6.4pF | ±0.05pF | GJM0332C1E6R4WB01# |
| | | | | ±0.1pF | GJM0332C1E6R4BB01# |
| | | | | ±0.25pF | GJM0332C1E6R4CB01# |
| | | | | ±0.5pF | GJM0332C1E6R4DB01# |
| | | | 6.5pF | ±0.05pF | GJM0332C1E6R5WB01# |
| | | | | ±0.1pF | GJM0332C1E6R5BB01# |
| | | | | ±0.25pF | GJM0332C1E6R5CB01# |
| | | | | ±0.5pF | GJM0332C1E6R5DB01# |
| | | | 6.6pF | ±0.05pF | GJM0332C1E6R6WB01# |
| | | | | ±0.1pF | GJM0332C1E6R6BB01# |
| | | | | ±0.25pF | GJM0332C1E6R6CB01# |
| | | | | ±0.5pF | GJM0332C1E6R6DB01# |
| | | | 6.7pF | ±0.05pF | GJM0332C1E6R7WB01# |
| | | | | ±0.1pF | GJM0332C1E6R7BB01# |
| | | | | ±0.25pF | GJM0332C1E6R7CB01# |
| | | | | ±0.5pF | GJM0332C1E6R7DB01# |
| | | | 6.8pF | ±0.05pF | GJM0332C1E6R8WB01# |
| | | | | ±0.1pF | GJM0332C1E6R8BB01# |
| | | | | ±0.25pF | GJM0332C1E6R8CB01# |
| | | | | ±0.5pF | GJM0332C1E6R8DB01# |
| | | | 6.9pF | ±0.05pF | GJM0332C1E6R9WB01# |
| | | | | ±0.1pF | GJM0332C1E6R9BB01# |
| | | | | ±0.25pF | GJM0332C1E6R9CB01# |
| | | | | ±0.5pF | GJM0332C1E6R9DB01# |
| | | | 7.0pF | ±0.05pF | GJM0332C1E7R0WB01# |
| | | | | ±0.1pF | GJM0332C1E7R0BB01# |
| | | | | ±0.25pF | GJM0332C1E7R0CB01# |
| | | | | ±0.5pF | GJM0332C1E7R0DB01# |
| | | | 7.1pF | ±0.05pF | GJM0332C1E7R1WB01# |
| | | | | ±0.1pF | GJM0332C1E7R1BB01# |
| | | | | ±0.25pF | GJM0332C1E7R1CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | CH | 7.1pF | ±0.5pF | GJM0332C1E7R1DB01# |
| | | | 7.2pF | ±0.05pF | GJM0332C1E7R2WB01# |
| | | | | ±0.1pF | GJM0332C1E7R2BB01# |
| | | | | ±0.25pF | GJM0332C1E7R2CB01# |
| | | | | ±0.5pF | GJM0332C1E7R2DB01# |
| | | | 7.3pF | ±0.05pF | GJM0332C1E7R3WB01# |
| | | | | ±0.1pF | GJM0332C1E7R3BB01# |
| | | | | ±0.25pF | GJM0332C1E7R3CB01# |
| | | | | ±0.5pF | GJM0332C1E7R3DB01# |
| | | | 7.4pF | ±0.05pF | GJM0332C1E7R4WB01# |
| | | | | ±0.1pF | GJM0332C1E7R4BB01# |
| | | | | ±0.25pF | GJM0332C1E7R4CB01# |
| | | | | ±0.5pF | GJM0332C1E7R4DB01# |
| | | | 7.5pF | ±0.05pF | GJM0332C1E7R5WB01# |
| | | | | ±0.1pF | GJM0332C1E7R5BB01# |
| | | | | ±0.25pF | GJM0332C1E7R5CB01# |
| | | | | ±0.5pF | GJM0332C1E7R5DB01# |
| | | | 7.6pF | ±0.05pF | GJM0332C1E7R6WB01# |
| | | | | ±0.1pF | GJM0332C1E7R6BB01# |
| | | | | ±0.25pF | GJM0332C1E7R6CB01# |
| | | | | ±0.5pF | GJM0332C1E7R6DB01# |
| | | | 7.7pF | ±0.05pF | GJM0332C1E7R7WB01# |
| | | | | ±0.1pF | GJM0332C1E7R7BB01# |
| | | | | ±0.25pF | GJM0332C1E7R7CB01# |
| | | | | ±0.5pF | GJM0332C1E7R7DB01# |
| | | | 7.8pF | ±0.05pF | GJM0332C1E7R8WB01# |
| | | | | ±0.1pF | GJM0332C1E7R8BB01# |
| | | | | ±0.25pF | GJM0332C1E7R8CB01# |
| | | | | ±0.5pF | GJM0332C1E7R8DB01# |
| | | | 7.9pF | ±0.05pF | GJM0332C1E7R9WB01# |
| | | | | ±0.1pF | GJM0332C1E7R9BB01# |
| | | | | ±0.25pF | GJM0332C1E7R9CB01# |
| | | | | ±0.5pF | GJM0332C1E7R9DB01# |
| | | | 8.0pF | ±0.05pF | GJM0332C1E8R0WB01# |
| | | | | ±0.1pF | GJM0332C1E8R0BB01# |
| | | | | ±0.25pF | GJM0332C1E8R0CB01# |
| | | | | ±0.5pF | GJM0332C1E8R0DB01# |
| | | | 8.1pF | ±0.05pF | GJM0332C1E8R1WB01# |
| | | | | ±0.1pF | GJM0332C1E8R1BB01# |
| | | | | ±0.25pF | GJM0332C1E8R1CB01# |
| | | | | ±0.5pF | GJM0332C1E8R1DB01# |
| | | | 8.2pF | ±0.05pF | GJM0332C1E8R2WB01# |
| | | | | ±0.1pF | GJM0332C1E8R2BB01# |
| | | | | ±0.25pF | GJM0332C1E8R2CB01# |
| | | | | ±0.5pF | GJM0332C1E8R2DB01# |
| | | | 8.3pF | ±0.05pF | GJM0332C1E8R3WB01# |
| | | | | ±0.1pF | GJM0332C1E8R3BB01# |
| | | | | ±0.25pF | GJM0332C1E8R3CB01# |
| | | | | ±0.5pF | GJM0332C1E8R3DB01# |
| | | | 8.4pF | ±0.05pF | GJM0332C1E8R4WB01# |
| | | | | ±0.1pF | GJM0332C1E8R4BB01# |
| | | | | ±0.25pF | GJM0332C1E8R4CB01# |
| | | | | ±0.5pF | GJM0332C1E8R4DB01# |
| | | | 8.5pF | ±0.05pF | GJM0332C1E8R5WB01# |
| | | | | ±0.1pF | GJM0332C1E8R5BB01# |
| | | | | ±0.25pF | GJM0332C1E8R5CB01# |
| | | | | ±0.5pF | GJM0332C1E8R5DB01# |
| | | | 8.6pF | ±0.05pF | GJM0332C1E8R6WB01# |
| | | | | ±0.1pF | GJM0332C1E8R6BB01# |
| | | | | ±0.25pF | GJM0332C1E8R6CB01# |
| | | | | ±0.5pF | GJM0332C1E8R6DB01# |
| | | | 8.7pF | ±0.05pF | GJM0332C1E8R7WB01# |
| | | | | ±0.1pF | GJM0332C1E8R7BB01# |
| | | | | ±0.25pF | GJM0332C1E8R7CB01# |
| | | | | ±0.5pF | GJM0332C1E8R7DB01# |
| | | | 8.8pF | ±0.05pF | GJM0332C1E8R8WB01# |
| | | | | ±0.1pF | GJM0332C1E8R8BB01# |
| | | | | ±0.25pF | GJM0332C1E8R8CB01# |
| | | | | ±0.5pF | GJM0332C1E8R8DB01# |
| | | | 8.9pF | ±0.05pF | GJM0332C1E8R9WB01# |
| | | | | ±0.1pF | GJM0332C1E8R9BB01# |
| | | | | ±0.25pF | GJM0332C1E8R9CB01# |
| | | | | ±0.5pF | GJM0332C1E8R9DB01# |
| | | | 9.0pF | ±0.05pF | GJM0332C1E9R0WB01# |
| | | | | ±0.1pF | GJM0332C1E9R0BB01# |
| | | | | ±0.25pF | GJM0332C1E9R0CB01# |
| | | | | ±0.5pF | GJM0332C1E9R0DB01# |
| | | | 9.1pF | ±0.05pF | GJM0332C1E9R1WB01# |
| | | | | ±0.1pF | GJM0332C1E9R1BB01# |
| | | | | ±0.25pF | GJM0332C1E9R1CB01# |
| | | | | ±0.5pF | GJM0332C1E9R1DB01# |
| | | | 9.2pF | ±0.05pF | GJM0332C1E9R2WB01# |
| | | | | ±0.1pF | GJM0332C1E9R2BB01# |
| | | | | ±0.25pF | GJM0332C1E9R2CB01# |
| | | | | ±0.5pF | GJM0332C1E9R2DB01# |
| | | | 9.3pF | ±0.05pF | GJM0332C1E9R3WB01# |
| | | | | ±0.1pF | GJM0332C1E9R3BB01# |
| | | | | ±0.25pF | GJM0332C1E9R3CB01# |
| | | | | ±0.5pF | GJM0332C1E9R3DB01# |
| | | | 9.4pF | ±0.05pF | GJM0332C1E9R4WB01# |
| | | | | ±0.1pF | GJM0332C1E9R4BB01# |
| | | | | ±0.25pF | GJM0332C1E9R4CB01# |
| | | | | ±0.5pF | GJM0332C1E9R4DB01# |
| | | | 9.5pF | ±0.05pF | GJM0332C1E9R5WB01# |
| | | | | ±0.1pF | GJM0332C1E9R5BB01# |
| | | | | ±0.25pF | GJM0332C1E9R5CB01# |
| | | | | ±0.5pF | GJM0332C1E9R5DB01# |
| | | | 9.6pF | ±0.05pF | GJM0332C1E9R6WB01# |
| | | | | ±0.1pF | GJM0332C1E9R6BB01# |
| | | | | ±0.25pF | GJM0332C1E9R6CB01# |
| | | | | ±0.5pF | GJM0332C1E9R6DB01# |
| | | | 9.7pF | ±0.05pF | GJM0332C1E9R7WB01# |
| | | | | ±0.1pF | GJM0332C1E9R7BB01# |
| | | | | ±0.25pF | GJM0332C1E9R7CB01# |
| | | | | ±0.5pF | GJM0332C1E9R7DB01# |
| | | | 9.8pF | ±0.05pF | GJM0332C1E9R8WB01# |
| | | | | ±0.1pF | GJM0332C1E9R8BB01# |
| | | | | ±0.25pF | GJM0332C1E9R8CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | CH | 9.8pF | ±0.5pF | GJM0332C1E9R8DB01# |
| | | | 9.9pF | ±0.05pF | GJM0332C1E9R9WB01# |
| | | | | ±0.1pF | GJM0332C1E9R9BB01# |
| | | | | ±0.25pF | GJM0332C1E9R9CB01# |
| | | | | ±0.5pF | GJM0332C1E9R9DB01# |
| | | | 10pF | ±2% | GJM0332C1E100GB01# |
| | | | | ±5% | GJM0332C1E100JB01# |
| | | | 11pF | ±2% | GJM0332C1E110GB01# |
| | | | | ±5% | GJM0332C1E110JB01# |
| | | | 12pF | ±2% | GJM0332C1E120GB01# |
| | | | | ±5% | GJM0332C1E120JB01# |
| | | | 13pF | ±2% | GJM0332C1E130GB01# |
| | | | | ±5% | GJM0332C1E130JB01# |
| | | | 15pF | ±2% | GJM0332C1E150GB01# |
| | | | | ±5% | GJM0332C1E150JB01# |
| | | | 16pF | ±2% | GJM0332C1E160GB01# |
| | | | | ±5% | GJM0332C1E160JB01# |
| | | | 18pF | ±2% | GJM0332C1E180GB01# |
| | | | | ±5% | GJM0332C1E180JB01# |
| | | | 20pF | ±2% | GJM0332C1E200GB01# |
| | | | | ±5% | GJM0332C1E200JB01# |
| | | | 22pF | ±2% | GJM0332C1E220GB01# |
| | | | | ±5% | GJM0332C1E220JB01# |
| | | | 24pF | ±2% | GJM0332C1E240GB01# |
| | | | | ±5% | GJM0332C1E240JB01# |
| | | | 27pF | ±2% | GJM0332C1E270GB01# |
| | | | | ±5% | GJM0332C1E270JB01# |
| | | | 30pF | ±2% | GJM0332C1E300GB01# |
| | | | | ±5% | GJM0332C1E300JB01# |
| | | | 33pF | ±2% | GJM0332C1E330GB01# |
| | | | | ±5% | GJM0332C1E330JB01# |

## ■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 0.10pF | ±0.05pF | GJM1555C1HR10WB01# |
| | | | | ±0.1pF | GJM1555C1HR10BB01# |
| | | | 0.20pF | ±0.05pF | GJM1555C1HR20WB01# |
| | | | | ±0.1pF | GJM1555C1HR20BB01# |
| | | | 0.30pF | ±0.05pF | GJM1555C1HR30WB01# |
| | | | | ±0.1pF | GJM1555C1HR30BB01# |
| | | | 0.40pF | ±0.05pF | GJM1555C1HR40WB01# |
| | | | | ±0.1pF | GJM1555C1HR40BB01# |
| | | | 0.50pF | ±0.05pF | GJM1555C1HR50WB01# |
| | | | | ±0.1pF | GJM1555C1HR50BB01# |
| | | | 0.60pF | ±0.05pF | GJM1555C1HR60WB01# |
| | | | | ±0.1pF | GJM1555C1HR60BB01# |
| | | | 0.70pF | ±0.05pF | GJM1555C1HR70WB01# |
| | | | | ±0.1pF | GJM1555C1HR70BB01# |
| | | | 0.80pF | ±0.05pF | GJM1555C1HR80WB01# |
| | | | | ±0.1pF | GJM1555C1HR80BB01# |
| | | | 0.90pF | ±0.05pF | GJM1555C1HR90WB01# |
| | | | | ±0.1pF | GJM1555C1HR90BB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 1.0pF | ±0.05pF | GJM1555C1H1R0WB01# |
| | | | | ±0.1pF | GJM1555C1H1R0BB01# |
| | | | | ±0.25pF | GJM1555C1H1R0CB01# |
| | | | 1.1pF | ±0.05pF | GJM1555C1H1R1WB01# |
| | | | | ±0.1pF | GJM1555C1H1R1BB01# |
| | | | | ±0.25pF | GJM1555C1H1R1CB01# |
| | | | 1.2pF | ±0.05pF | GJM1555C1H1R2WB01# |
| | | | | ±0.1pF | GJM1555C1H1R2BB01# |
| | | | | ±0.25pF | GJM1555C1H1R2CB01# |
| | | | 1.3pF | ±0.05pF | GJM1555C1H1R3WB01# |
| | | | | ±0.1pF | GJM1555C1H1R3BB01# |
| | | | | ±0.25pF | GJM1555C1H1R3CB01# |
| | | | 1.4pF | ±0.05pF | GJM1555C1H1R4WB01# |
| | | | | ±0.1pF | GJM1555C1H1R4BB01# |
| | | | | ±0.25pF | GJM1555C1H1R4CB01# |
| | | | 1.5pF | ±0.05pF | GJM1555C1H1R5WB01# |
| | | | | ±0.1pF | GJM1555C1H1R5BB01# |
| | | | | ±0.25pF | GJM1555C1H1R5CB01# |
| | | | 1.6pF | ±0.05pF | GJM1555C1H1R6WB01# |
| | | | | ±0.1pF | GJM1555C1H1R6BB01# |
| | | | | ±0.25pF | GJM1555C1H1R6CB01# |
| | | | 1.7pF | ±0.05pF | GJM1555C1H1R7WB01# |
| | | | | ±0.1pF | GJM1555C1H1R7BB01# |
| | | | | ±0.25pF | GJM1555C1H1R7CB01# |
| | | | 1.8pF | ±0.05pF | GJM1555C1H1R8WB01# |
| | | | | ±0.1pF | GJM1555C1H1R8BB01# |
| | | | | ±0.25pF | GJM1555C1H1R8CB01# |
| | | | 1.9pF | ±0.05pF | GJM1555C1H1R9WB01# |
| | | | | ±0.1pF | GJM1555C1H1R9BB01# |
| | | | | ±0.25pF | GJM1555C1H1R9CB01# |
| | | | 2.0pF | ±0.05pF | GJM1555C1H2R0WB01# |
| | | | | ±0.1pF | GJM1555C1H2R0BB01# |
| | | | | ±0.25pF | GJM1555C1H2R0CB01# |
| | | | 2.1pF | ±0.05pF | GJM1555C1H2R1WB01# |
| | | | | ±0.1pF | GJM1555C1H2R1BB01# |
| | | | | ±0.25pF | GJM1555C1H2R1CB01# |
| | | | 2.2pF | ±0.05pF | GJM1555C1H2R2WB01# |
| | | | | ±0.1pF | GJM1555C1H2R2BB01# |
| | | | | ±0.25pF | GJM1555C1H2R2CB01# |
| | | | 2.3pF | ±0.05pF | GJM1555C1H2R3WB01# |
| | | | | ±0.1pF | GJM1555C1H2R3BB01# |
| | | | | ±0.25pF | GJM1555C1H2R3CB01# |
| | | | 2.4pF | ±0.05pF | GJM1555C1H2R4WB01# |
| | | | | ±0.1pF | GJM1555C1H2R4BB01# |
| | | | | ±0.25pF | GJM1555C1H2R4CB01# |
| | | | 2.5pF | ±0.05pF | GJM1555C1H2R5WB01# |
| | | | | ±0.1pF | GJM1555C1H2R5BB01# |
| | | | | ±0.25pF | GJM1555C1H2R5CB01# |
| | | | 2.6pF | ±0.05pF | GJM1555C1H2R6WB01# |
| | | | | ±0.1pF | GJM1555C1H2R6BB01# |
| | | | | ±0.25pF | GJM1555C1H2R6CB01# |
| | | | 2.7pF | ±0.05pF | GJM1555C1H2R7WB01# |
| | | | | ±0.1pF | GJM1555C1H2R7BB01# |
| | | | | ±0.25pF | GJM1555C1H2R7CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 2.8pF | ±0.05pF | **GJM1555C1H2R8WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H2R8BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H2R8CB01#** | |
| | | | 2.9pF | ±0.05pF | **GJM1555C1H2R9WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H2R9BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H2R9CB01#** | |
| | | | 3.0pF | ±0.05pF | **GJM1555C1H3R0WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R0BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R0CB01#** | |
| | | | 3.1pF | ±0.05pF | **GJM1555C1H3R1WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R1BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R1CB01#** | |
| | | | 3.2pF | ±0.05pF | **GJM1555C1H3R2WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R2BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R2CB01#** | |
| | | | 3.3pF | ±0.05pF | **GJM1555C1H3R3WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R3BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R3CB01#** | |
| | | | 3.4pF | ±0.05pF | **GJM1555C1H3R4WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R4BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R4CB01#** | |
| | | | 3.5pF | ±0.05pF | **GJM1555C1H3R5WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R5BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R5CB01#** | |
| | | | 3.6pF | ±0.05pF | **GJM1555C1H3R6WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R6BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R6CB01#** | |
| | | | 3.7pF | ±0.05pF | **GJM1555C1H3R7WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R7BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R7CB01#** | |
| | | | 3.8pF | ±0.05pF | **GJM1555C1H3R8WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R8BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R8CB01#** | |
| | | | 3.9pF | ±0.05pF | **GJM1555C1H3R9WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H3R9BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H3R9CB01#** | |
| | | | 4.0pF | ±0.05pF | **GJM1555C1H4R0WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R0BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R0CB01#** | |
| | | | 4.1pF | ±0.05pF | **GJM1555C1H4R1WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R1BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R1CB01#** | |
| | | | 4.2pF | ±0.05pF | **GJM1555C1H4R2WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R2BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R2CB01#** | |
| | | | 4.3pF | ±0.05pF | **GJM1555C1H4R3WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R3BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R3CB01#** | |
| | | | 4.4pF | ±0.05pF | **GJM1555C1H4R4WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R4BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R4CB01#** | |
| | | | 4.5pF | ±0.05pF | **GJM1555C1H4R5WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R5BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R5CB01#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 4.6pF | ±0.05pF | **GJM1555C1H4R6WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R6BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R6CB01#** | |
| | | | 4.7pF | ±0.05pF | **GJM1555C1H4R7WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R7BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R7CB01#** | |
| | | | 4.8pF | ±0.05pF | **GJM1555C1H4R8WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R8BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R8CB01#** | |
| | | | 4.9pF | ±0.05pF | **GJM1555C1H4R9WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H4R9BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H4R9CB01#** | |
| | | | 5.0pF | ±0.05pF | **GJM1555C1H5R0WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R0BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R0CB01#** | |
| | | | 5.1pF | ±0.05pF | **GJM1555C1H5R1WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R1BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R1CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R1DB01#** | |
| | | | 5.2pF | ±0.05pF | **GJM1555C1H5R2WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R2BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R2CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R2DB01#** | |
| | | | 5.3pF | ±0.05pF | **GJM1555C1H5R3WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R3BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R3CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R3DB01#** | |
| | | | 5.4pF | ±0.05pF | **GJM1555C1H5R4WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R4BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R4CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R4DB01#** | |
| | | | 5.5pF | ±0.05pF | **GJM1555C1H5R5WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R5BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R5CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R5DB01#** | |
| | | | 5.6pF | ±0.05pF | **GJM1555C1H5R6WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R6BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R6CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R6DB01#** | |
| | | | 5.7pF | ±0.05pF | **GJM1555C1H5R7WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R7BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R7CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R7DB01#** | |
| | | | 5.8pF | ±0.05pF | **GJM1555C1H5R8WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R8BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R8CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R8DB01#** | |
| | | | 5.9pF | ±0.05pF | **GJM1555C1H5R9WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H5R9BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H5R9CB01#** | |
| | | | | ±0.5pF | **GJM1555C1H5R9DB01#** | |
| | | | 6.0pF | ±0.05pF | **GJM1555C1H6R0WB01#** | |
| | | | | ±0.1pF | **GJM1555C1H6R0BB01#** | |
| | | | | ±0.25pF | **GJM1555C1H6R0CB01#** | |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 6.0pF | ±0.5pF | **GJM1555C1H6R0DB01#** |
| | | | 6.1pF | ±0.05pF | **GJM1555C1H6R1WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R1BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R1CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R1DB01#** |
| | | | 6.2pF | ±0.05pF | **GJM1555C1H6R2WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R2BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R2CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R2DB01#** |
| | | | 6.3pF | ±0.05pF | **GJM1555C1H6R3WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R3BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R3CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R3DB01#** |
| | | | 6.4pF | ±0.05pF | **GJM1555C1H6R4WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R4BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R4CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R4DB01#** |
| | | | 6.5pF | ±0.05pF | **GJM1555C1H6R5WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R5BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R5CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R5DB01#** |
| | | | 6.6pF | ±0.05pF | **GJM1555C1H6R6WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R6BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R6CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R6DB01#** |
| | | | 6.7pF | ±0.05pF | **GJM1555C1H6R7WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R7BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R7CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R7DB01#** |
| | | | 6.8pF | ±0.05pF | **GJM1555C1H6R8WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R8BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R8CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R8DB01#** |
| | | | 6.9pF | ±0.05pF | **GJM1555C1H6R9WB01#** |
| | | | | ±0.1pF | **GJM1555C1H6R9BB01#** |
| | | | | ±0.25pF | **GJM1555C1H6R9CB01#** |
| | | | | ±0.5pF | **GJM1555C1H6R9DB01#** |
| | | | 7.0pF | ±0.05pF | **GJM1555C1H7R0WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R0BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R0CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R0DB01#** |
| | | | 7.1pF | ±0.05pF | **GJM1555C1H7R1WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R1BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R1CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R1DB01#** |
| | | | 7.2pF | ±0.05pF | **GJM1555C1H7R2WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R2BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R2CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R2DB01#** |
| | | | 7.3pF | ±0.05pF | **GJM1555C1H7R3WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R3BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R3CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R3DB01#** |
| | | | 7.4pF | ±0.05pF | **GJM1555C1H7R4WB01#** |
| 0.55mm | 50Vdc | C0G | 7.4pF | ±0.1pF | **GJM1555C1H7R4BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R4CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R4DB01#** |
| | | | 7.5pF | ±0.05pF | **GJM1555C1H7R5WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R5BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R5CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R5DB01#** |
| | | | 7.6pF | ±0.05pF | **GJM1555C1H7R6WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R6BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R6CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R6DB01#** |
| | | | 7.7pF | ±0.05pF | **GJM1555C1H7R7WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R7BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R7CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R7DB01#** |
| | | | 7.8pF | ±0.05pF | **GJM1555C1H7R8WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R8BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R8CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R8DB01#** |
| | | | 7.9pF | ±0.05pF | **GJM1555C1H7R9WB01#** |
| | | | | ±0.1pF | **GJM1555C1H7R9BB01#** |
| | | | | ±0.25pF | **GJM1555C1H7R9CB01#** |
| | | | | ±0.5pF | **GJM1555C1H7R9DB01#** |
| | | | 8.0pF | ±0.05pF | **GJM1555C1H8R0WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R0BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R0CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R0DB01#** |
| | | | 8.1pF | ±0.05pF | **GJM1555C1H8R1WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R1BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R1CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R1DB01#** |
| | | | 8.2pF | ±0.05pF | **GJM1555C1H8R2WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R2BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R2CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R2DB01#** |
| | | | 8.3pF | ±0.05pF | **GJM1555C1H8R3WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R3BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R3CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R3DB01#** |
| | | | 8.4pF | ±0.05pF | **GJM1555C1H8R4WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R4BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R4CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R4DB01#** |
| | | | 8.5pF | ±0.05pF | **GJM1555C1H8R5WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R5BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R5CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R5DB01#** |
| | | | 8.6pF | ±0.05pF | **GJM1555C1H8R6WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R6BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R6CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R6DB01#** |
| | | | 8.7pF | ±0.05pF | **GJM1555C1H8R7WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R7BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R7CB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | C0G | 8.7pF | ±0.5pF | **GJM1555C1H8R7DB01#** |
| | | | 8.8pF | ±0.05pF | **GJM1555C1H8R8WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R8BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R8CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R8DB01#** |
| | | | 8.9pF | ±0.05pF | **GJM1555C1H8R9WB01#** |
| | | | | ±0.1pF | **GJM1555C1H8R9BB01#** |
| | | | | ±0.25pF | **GJM1555C1H8R9CB01#** |
| | | | | ±0.5pF | **GJM1555C1H8R9DB01#** |
| | | | 9.0pF | ±0.05pF | **GJM1555C1H9R0WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R0BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R0CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R0DB01#** |
| | | | 9.1pF | ±0.05pF | **GJM1555C1H9R1WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R1BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R1CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R1DB01#** |
| | | | 9.2pF | ±0.05pF | **GJM1555C1H9R2WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R2BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R2CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R2DB01#** |
| | | | 9.3pF | ±0.05pF | **GJM1555C1H9R3WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R3BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R3CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R3DB01#** |
| | | | 9.4pF | ±0.05pF | **GJM1555C1H9R4WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R4BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R4CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R4DB01#** |
| | | | 9.5pF | ±0.05pF | **GJM1555C1H9R5WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R5BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R5CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R5DB01#** |
| | | | 9.6pF | ±0.05pF | **GJM1555C1H9R6WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R6BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R6CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R6DB01#** |
| | | | 9.7pF | ±0.05pF | **GJM1555C1H9R7WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R7BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R7CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R7DB01#** |
| | | | 9.8pF | ±0.05pF | **GJM1555C1H9R8WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R8BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R8CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R8DB01#** |
| | | | 9.9pF | ±0.05pF | **GJM1555C1H9R9WB01#** |
| | | | | ±0.1pF | **GJM1555C1H9R9BB01#** |
| | | | | ±0.25pF | **GJM1555C1H9R9CB01#** |
| | | | | ±0.5pF | **GJM1555C1H9R9DB01#** |
| | | | 10pF | ±2% | **GJM1555C1H100GB01#** |
| | | | | ±5% | **GJM1555C1H100JB01#** |
| | | | 11pF | ±2% | **GJM1555C1H110GB01#** |
| | | | | ±5% | **GJM1555C1H110JB01#** |
| | | | 12pF | ±2% | **GJM1555C1H120GB01#** |
| 0.55mm | 50Vdc | C0G | 12pF | ±5% | **GJM1555C1H120JB01#** |
| | | | 13pF | ±2% | **GJM1555C1H130GB01#** |
| | | | | ±5% | **GJM1555C1H130JB01#** |
| | | | 15pF | ±2% | **GJM1555C1H150GB01#** |
| | | | | ±5% | **GJM1555C1H150JB01#** |
| | | | 16pF | ±2% | **GJM1555C1H160GB01#** |
| | | | | ±5% | **GJM1555C1H160JB01#** |
| | | | 18pF | ±2% | **GJM1555C1H180GB01#** |
| | | | | ±5% | **GJM1555C1H180JB01#** |
| | | | 20pF | ±2% | **GJM1555C1H200GB01#** |
| | | | | ±5% | **GJM1555C1H200JB01#** |
| | | | 22pF | ±1% | **GJM1555C1H220FB01#** |
| | | | | ±2% | **GJM1555C1H220GB01#** |
| | | | | ±5% | **GJM1555C1H220JB01#** |
| | | | 24pF | ±1% | **GJM1555C1H240FB01#** |
| | | | | ±2% | **GJM1555C1H240GB01#** |
| | | | | ±5% | **GJM1555C1H240JB01#** |
| | | | 27pF | ±1% | **GJM1555C1H270FB01#** |
| | | | | ±2% | **GJM1555C1H270GB01#** |
| | | | | ±5% | **GJM1555C1H270JB01#** |
| | | | 30pF | ±1% | **GJM1555C1H300FB01#** |
| | | | | ±2% | **GJM1555C1H300GB01#** |
| | | | | ±5% | **GJM1555C1H300JB01#** |
| | | | 33pF | ±1% | **GJM1555C1H330FB01#** |
| | | | | ±2% | **GJM1555C1H330GB01#** |
| | | | | ±5% | **GJM1555C1H330JB01#** |
| | | | 36pF | ±1% | **GJM1555C1H360FB01#** |
| | | | | ±2% | **GJM1555C1H360GB01#** |
| | | | | ±5% | **GJM1555C1H360JB01#** |
| | | | 39pF | ±1% | **GJM1555C1H390FB01#** |
| | | | | ±2% | **GJM1555C1H390GB01#** |
| | | | | ±5% | **GJM1555C1H390JB01#** |
| | | | 43pF | ±1% | **GJM1555C1H430FB01#** |
| | | | | ±2% | **GJM1555C1H430GB01#** |
| | | | | ±5% | **GJM1555C1H430JB01#** |
| | | | 47pF | ±1% | **GJM1555C1H470FB01#** |
| | | | | ±2% | **GJM1555C1H470GB01#** |
| | | | | ±5% | **GJM1555C1H470JB01#** |
| | | CK | 0.10pF | ±0.05pF | **GJM1554C1HR10WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR10BB01#** |
| | | | 0.20pF | ±0.05pF | **GJM1554C1HR20WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR20BB01#** |
| | | | 0.30pF | ±0.05pF | **GJM1554C1HR30WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR30BB01#** |
| | | | 0.40pF | ±0.05pF | **GJM1554C1HR40WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR40BB01#** |
| | | | 0.50pF | ±0.05pF | **GJM1554C1HR50WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR50BB01#** |
| | | | 0.60pF | ±0.05pF | **GJM1554C1HR60WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR60BB01#** |
| | | | 0.70pF | ±0.05pF | **GJM1554C1HR70WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR70BB01#** |
| | | | 0.80pF | ±0.05pF | **GJM1554C1HR80WB01#** |
| | | | | ±0.1pF | **GJM1554C1HR80BB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CK | 0.90pF | ±0.05pF | GJM1554C1HR90WB01# |
| | | | | ±0.1pF | GJM1554C1HR90BB01# |
| | | | 1.0pF | ±0.05pF | GJM1554C1H1R0WB01# |
| | | | | ±0.1pF | GJM1554C1H1R0BB01# |
| | | | | ±0.25pF | GJM1554C1H1R0CB01# |
| | | | 1.1pF | ±0.05pF | GJM1554C1H1R1WB01# |
| | | | | ±0.1pF | GJM1554C1H1R1BB01# |
| | | | | ±0.25pF | GJM1554C1H1R1CB01# |
| | | | 1.2pF | ±0.05pF | GJM1554C1H1R2WB01# |
| | | | | ±0.1pF | GJM1554C1H1R2BB01# |
| | | | | ±0.25pF | GJM1554C1H1R2CB01# |
| | | | 1.3pF | ±0.05pF | GJM1554C1H1R3WB01# |
| | | | | ±0.1pF | GJM1554C1H1R3BB01# |
| | | | | ±0.25pF | GJM1554C1H1R3CB01# |
| | | | 1.4pF | ±0.05pF | GJM1554C1H1R4WB01# |
| | | | | ±0.1pF | GJM1554C1H1R4BB01# |
| | | | | ±0.25pF | GJM1554C1H1R4CB01# |
| | | | 1.5pF | ±0.05pF | GJM1554C1H1R5WB01# |
| | | | | ±0.1pF | GJM1554C1H1R5BB01# |
| | | | | ±0.25pF | GJM1554C1H1R5CB01# |
| | | | 1.6pF | ±0.05pF | GJM1554C1H1R6WB01# |
| | | | | ±0.1pF | GJM1554C1H1R6BB01# |
| | | | | ±0.25pF | GJM1554C1H1R6CB01# |
| | | | 1.7pF | ±0.05pF | GJM1554C1H1R7WB01# |
| | | | | ±0.1pF | GJM1554C1H1R7BB01# |
| | | | | ±0.25pF | GJM1554C1H1R7CB01# |
| | | | 1.8pF | ±0.05pF | GJM1554C1H1R8WB01# |
| | | | | ±0.1pF | GJM1554C1H1R8BB01# |
| | | | | ±0.25pF | GJM1554C1H1R8CB01# |
| | | | 1.9pF | ±0.05pF | GJM1554C1H1R9WB01# |
| | | | | ±0.1pF | GJM1554C1H1R9BB01# |
| | | | | ±0.25pF | GJM1554C1H1R9CB01# |
| | | | 2.0pF | ±0.05pF | GJM1554C1H2R0WB01# |
| | | | | ±0.1pF | GJM1554C1H2R0BB01# |
| | | | | ±0.25pF | GJM1554C1H2R0CB01# |
| | | CJ | 2.1pF | ±0.05pF | GJM1553C1H2R1WB01# |
| | | | | ±0.1pF | GJM1553C1H2R1BB01# |
| | | | | ±0.25pF | GJM1553C1H2R1CB01# |
| | | | 2.2pF | ±0.05pF | GJM1553C1H2R2WB01# |
| | | | | ±0.1pF | GJM1553C1H2R2BB01# |
| | | | | ±0.25pF | GJM1553C1H2R2CB01# |
| | | | 2.3pF | ±0.05pF | GJM1553C1H2R3WB01# |
| | | | | ±0.1pF | GJM1553C1H2R3BB01# |
| | | | | ±0.25pF | GJM1553C1H2R3CB01# |
| | | | 2.4pF | ±0.05pF | GJM1553C1H2R4WB01# |
| | | | | ±0.1pF | GJM1553C1H2R4BB01# |
| | | | | ±0.25pF | GJM1553C1H2R4CB01# |
| | | | 2.5pF | ±0.05pF | GJM1553C1H2R5WB01# |
| | | | | ±0.1pF | GJM1553C1H2R5BB01# |
| | | | | ±0.25pF | GJM1553C1H2R5CB01# |
| | | | 2.6pF | ±0.05pF | GJM1553C1H2R6WB01# |
| | | | | ±0.1pF | GJM1553C1H2R6BB01# |
| | | | | ±0.25pF | GJM1553C1H2R6CB01# |
| | | | 2.7pF | ±0.05pF | GJM1553C1H2R7WB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CJ | 2.7pF | ±0.1pF | GJM1553C1H2R7BB01# |
| | | | | ±0.25pF | GJM1553C1H2R7CB01# |
| | | | 2.8pF | ±0.05pF | GJM1553C1H2R8WB01# |
| | | | | ±0.1pF | GJM1553C1H2R8BB01# |
| | | | | ±0.25pF | GJM1553C1H2R8CB01# |
| | | | 2.9pF | ±0.05pF | GJM1553C1H2R9WB01# |
| | | | | ±0.1pF | GJM1553C1H2R9BB01# |
| | | | | ±0.25pF | GJM1553C1H2R9CB01# |
| | | | 3.0pF | ±0.05pF | GJM1553C1H3R0WB01# |
| | | | | ±0.1pF | GJM1553C1H3R0BB01# |
| | | | | ±0.25pF | GJM1553C1H3R0CB01# |
| | | | 3.1pF | ±0.05pF | GJM1553C1H3R1WB01# |
| | | | | ±0.1pF | GJM1553C1H3R1BB01# |
| | | | | ±0.25pF | GJM1553C1H3R1CB01# |
| | | | 3.2pF | ±0.05pF | GJM1553C1H3R2WB01# |
| | | | | ±0.1pF | GJM1553C1H3R2BB01# |
| | | | | ±0.25pF | GJM1553C1H3R2CB01# |
| | | | 3.3pF | ±0.05pF | GJM1553C1H3R3WB01# |
| | | | | ±0.1pF | GJM1553C1H3R3BB01# |
| | | | | ±0.25pF | GJM1553C1H3R3CB01# |
| | | | 3.4pF | ±0.05pF | GJM1553C1H3R4WB01# |
| | | | | ±0.1pF | GJM1553C1H3R4BB01# |
| | | | | ±0.25pF | GJM1553C1H3R4CB01# |
| | | | 3.5pF | ±0.05pF | GJM1553C1H3R5WB01# |
| | | | | ±0.1pF | GJM1553C1H3R5BB01# |
| | | | | ±0.25pF | GJM1553C1H3R5CB01# |
| | | | 3.6pF | ±0.05pF | GJM1553C1H3R6WB01# |
| | | | | ±0.1pF | GJM1553C1H3R6BB01# |
| | | | | ±0.25pF | GJM1553C1H3R6CB01# |
| | | | 3.7pF | ±0.05pF | GJM1553C1H3R7WB01# |
| | | | | ±0.1pF | GJM1553C1H3R7BB01# |
| | | | | ±0.25pF | GJM1553C1H3R7CB01# |
| | | | 3.8pF | ±0.05pF | GJM1553C1H3R8WB01# |
| | | | | ±0.1pF | GJM1553C1H3R8BB01# |
| | | | | ±0.25pF | GJM1553C1H3R8CB01# |
| | | | 3.9pF | ±0.05pF | GJM1553C1H3R9WB01# |
| | | | | ±0.1pF | GJM1553C1H3R9BB01# |
| | | | | ±0.25pF | GJM1553C1H3R9CB01# |
| | | CH | 4.0pF | ±0.05pF | GJM1552C1H4R0WB01# |
| | | | | ±0.1pF | GJM1552C1H4R0BB01# |
| | | | | ±0.25pF | GJM1552C1H4R0CB01# |
| | | | 4.1pF | ±0.05pF | GJM1552C1H4R1WB01# |
| | | | | ±0.1pF | GJM1552C1H4R1BB01# |
| | | | | ±0.25pF | GJM1552C1H4R1CB01# |
| | | | 4.2pF | ±0.05pF | GJM1552C1H4R2WB01# |
| | | | | ±0.1pF | GJM1552C1H4R2BB01# |
| | | | | ±0.25pF | GJM1552C1H4R2CB01# |
| | | | 4.3pF | ±0.05pF | GJM1552C1H4R3WB01# |
| | | | | ±0.1pF | GJM1552C1H4R3BB01# |
| | | | | ±0.25pF | GJM1552C1H4R3CB01# |
| | | | 4.4pF | ±0.05pF | GJM1552C1H4R4WB01# |
| | | | | ±0.1pF | GJM1552C1H4R4BB01# |
| | | | | ±0.25pF | GJM1552C1H4R4CB01# |
| | | | 4.5pF | ±0.05pF | GJM1552C1H4R5WB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 4.5pF | ±0.1pF | GJM1552C1H4R5BB01# |
| | | | | ±0.25pF | GJM1552C1H4R5CB01# |
| | | | 4.6pF | ±0.05pF | GJM1552C1H4R6WB01# |
| | | | | ±0.1pF | GJM1552C1H4R6BB01# |
| | | | | ±0.25pF | GJM1552C1H4R6CB01# |
| | | | 4.7pF | ±0.05pF | GJM1552C1H4R7WB01# |
| | | | | ±0.1pF | GJM1552C1H4R7BB01# |
| | | | | ±0.25pF | GJM1552C1H4R7CB01# |
| | | | 4.8pF | ±0.05pF | GJM1552C1H4R8WB01# |
| | | | | ±0.1pF | GJM1552C1H4R8BB01# |
| | | | | ±0.25pF | GJM1552C1H4R8CB01# |
| | | | 4.9pF | ±0.05pF | GJM1552C1H4R9WB01# |
| | | | | ±0.1pF | GJM1552C1H4R9BB01# |
| | | | | ±0.25pF | GJM1552C1H4R9CB01# |
| | | | 5.0pF | ±0.05pF | GJM1552C1H5R0WB01# |
| | | | | ±0.1pF | GJM1552C1H5R0BB01# |
| | | | | ±0.25pF | GJM1552C1H5R0CB01# |
| | | | 5.1pF | ±0.05pF | GJM1552C1H5R1WB01# |
| | | | | ±0.1pF | GJM1552C1H5R1BB01# |
| | | | | ±0.25pF | GJM1552C1H5R1CB01# |
| | | | | ±0.5pF | GJM1552C1H5R1DB01# |
| | | | 5.2pF | ±0.05pF | GJM1552C1H5R2WB01# |
| | | | | ±0.1pF | GJM1552C1H5R2BB01# |
| | | | | ±0.25pF | GJM1552C1H5R2CB01# |
| | | | | ±0.5pF | GJM1552C1H5R2DB01# |
| | | | 5.3pF | ±0.05pF | GJM1552C1H5R3WB01# |
| | | | | ±0.1pF | GJM1552C1H5R3BB01# |
| | | | | ±0.25pF | GJM1552C1H5R3CB01# |
| | | | | ±0.5pF | GJM1552C1H5R3DB01# |
| | | | 5.4pF | ±0.05pF | GJM1552C1H5R4WB01# |
| | | | | ±0.1pF | GJM1552C1H5R4BB01# |
| | | | | ±0.25pF | GJM1552C1H5R4CB01# |
| | | | | ±0.5pF | GJM1552C1H5R4DB01# |
| | | | 5.5pF | ±0.05pF | GJM1552C1H5R5WB01# |
| | | | | ±0.1pF | GJM1552C1H5R5BB01# |
| | | | | ±0.25pF | GJM1552C1H5R5CB01# |
| | | | | ±0.5pF | GJM1552C1H5R5DB01# |
| | | | 5.6pF | ±0.05pF | GJM1552C1H5R6WB01# |
| | | | | ±0.1pF | GJM1552C1H5R6BB01# |
| | | | | ±0.25pF | GJM1552C1H5R6CB01# |
| | | | | ±0.5pF | GJM1552C1H5R6DB01# |
| | | | 5.7pF | ±0.05pF | GJM1552C1H5R7WB01# |
| | | | | ±0.1pF | GJM1552C1H5R7BB01# |
| | | | | ±0.25pF | GJM1552C1H5R7CB01# |
| | | | | ±0.5pF | GJM1552C1H5R7DB01# |
| | | | 5.8pF | ±0.05pF | GJM1552C1H5R8WB01# |
| | | | | ±0.1pF | GJM1552C1H5R8BB01# |
| | | | | ±0.25pF | GJM1552C1H5R8CB01# |
| | | | | ±0.5pF | GJM1552C1H5R8DB01# |
| | | | 5.9pF | ±0.05pF | GJM1552C1H5R9WB01# |
| | | | | ±0.1pF | GJM1552C1H5R9BB01# |
| | | | | ±0.25pF | GJM1552C1H5R9CB01# |
| | | | | ±0.5pF | GJM1552C1H5R9DB01# |
| | | | 6.0pF | ±0.05pF | GJM1552C1H6R0WB01# |
| 0.55mm | 50Vdc | CH | 6.0pF | ±0.1pF | GJM1552C1H6R0BB01# |
| | | | | ±0.25pF | GJM1552C1H6R0CB01# |
| | | | | ±0.5pF | GJM1552C1H6R0DB01# |
| | | | 6.1pF | ±0.05pF | GJM1552C1H6R1WB01# |
| | | | | ±0.1pF | GJM1552C1H6R1BB01# |
| | | | | ±0.25pF | GJM1552C1H6R1CB01# |
| | | | | ±0.5pF | GJM1552C1H6R1DB01# |
| | | | 6.2pF | ±0.05pF | GJM1552C1H6R2WB01# |
| | | | | ±0.1pF | GJM1552C1H6R2BB01# |
| | | | | ±0.25pF | GJM1552C1H6R2CB01# |
| | | | | ±0.5pF | GJM1552C1H6R2DB01# |
| | | | 6.3pF | ±0.05pF | GJM1552C1H6R3WB01# |
| | | | | ±0.1pF | GJM1552C1H6R3BB01# |
| | | | | ±0.25pF | GJM1552C1H6R3CB01# |
| | | | | ±0.5pF | GJM1552C1H6R3DB01# |
| | | | 6.4pF | ±0.05pF | GJM1552C1H6R4WB01# |
| | | | | ±0.1pF | GJM1552C1H6R4BB01# |
| | | | | ±0.25pF | GJM1552C1H6R4CB01# |
| | | | | ±0.5pF | GJM1552C1H6R4DB01# |
| | | | 6.5pF | ±0.05pF | GJM1552C1H6R5WB01# |
| | | | | ±0.1pF | GJM1552C1H6R5BB01# |
| | | | | ±0.25pF | GJM1552C1H6R5CB01# |
| | | | | ±0.5pF | GJM1552C1H6R5DB01# |
| | | | 6.6pF | ±0.05pF | GJM1552C1H6R6WB01# |
| | | | | ±0.1pF | GJM1552C1H6R6BB01# |
| | | | | ±0.25pF | GJM1552C1H6R6CB01# |
| | | | | ±0.5pF | GJM1552C1H6R6DB01# |
| | | | 6.7pF | ±0.05pF | GJM1552C1H6R7WB01# |
| | | | | ±0.1pF | GJM1552C1H6R7BB01# |
| | | | | ±0.25pF | GJM1552C1H6R7CB01# |
| | | | | ±0.5pF | GJM1552C1H6R7DB01# |
| | | | 6.8pF | ±0.05pF | GJM1552C1H6R8WB01# |
| | | | | ±0.1pF | GJM1552C1H6R8BB01# |
| | | | | ±0.25pF | GJM1552C1H6R8CB01# |
| | | | | ±0.5pF | GJM1552C1H6R8DB01# |
| | | | 6.9pF | ±0.05pF | GJM1552C1H6R9WB01# |
| | | | | ±0.1pF | GJM1552C1H6R9BB01# |
| | | | | ±0.25pF | GJM1552C1H6R9CB01# |
| | | | | ±0.5pF | GJM1552C1H6R9DB01# |
| | | | 7.0pF | ±0.05pF | GJM1552C1H7R0WB01# |
| | | | | ±0.1pF | GJM1552C1H7R0BB01# |
| | | | | ±0.25pF | GJM1552C1H7R0CB01# |
| | | | | ±0.5pF | GJM1552C1H7R0DB01# |
| | | | 7.1pF | ±0.05pF | GJM1552C1H7R1WB01# |
| | | | | ±0.1pF | GJM1552C1H7R1BB01# |
| | | | | ±0.25pF | GJM1552C1H7R1CB01# |
| | | | | ±0.5pF | GJM1552C1H7R1DB01# |
| | | | 7.2pF | ±0.05pF | GJM1552C1H7R2WB01# |
| | | | | ±0.1pF | GJM1552C1H7R2BB01# |
| | | | | ±0.25pF | GJM1552C1H7R2CB01# |
| | | | | ±0.5pF | GJM1552C1H7R2DB01# |
| | | | 7.3pF | ±0.05pF | GJM1552C1H7R3WB01# |
| | | | | ±0.1pF | GJM1552C1H7R3BB01# |
| | | | | ±0.25pF | GJM1552C1H7R3CB01# |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 7.3pF | ±0.5pF | **GJM1552C1H7R3DB01#** |
| | | | 7.4pF | ±0.05pF | **GJM1552C1H7R4WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R4BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R4CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R4DB01#** |
| | | | 7.5pF | ±0.05pF | **GJM1552C1H7R5WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R5BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R5CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R5DB01#** |
| | | | 7.6pF | ±0.05pF | **GJM1552C1H7R6WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R6BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R6CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R6DB01#** |
| | | | 7.7pF | ±0.05pF | **GJM1552C1H7R7WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R7BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R7CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R7DB01#** |
| | | | 7.8pF | ±0.05pF | **GJM1552C1H7R8WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R8BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R8CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R8DB01#** |
| | | | 7.9pF | ±0.05pF | **GJM1552C1H7R9WB01#** |
| | | | | ±0.1pF | **GJM1552C1H7R9BB01#** |
| | | | | ±0.25pF | **GJM1552C1H7R9CB01#** |
| | | | | ±0.5pF | **GJM1552C1H7R9DB01#** |
| | | | 8.0pF | ±0.05pF | **GJM1552C1H8R0WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R0BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R0CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R0DB01#** |
| | | | 8.1pF | ±0.05pF | **GJM1552C1H8R1WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R1BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R1CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R1DB01#** |
| | | | 8.2pF | ±0.05pF | **GJM1552C1H8R2WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R2BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R2CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R2DB01#** |
| | | | 8.3pF | ±0.05pF | **GJM1552C1H8R3WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R3BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R3CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R3DB01#** |
| | | | 8.4pF | ±0.05pF | **GJM1552C1H8R4WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R4BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R4CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R4DB01#** |
| | | | 8.5pF | ±0.05pF | **GJM1552C1H8R5WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R5BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R5CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R5DB01#** |
| | | | 8.6pF | ±0.05pF | **GJM1552C1H8R6WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R6BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R6CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R6DB01#** |
| | | | 8.7pF | ±0.05pF | **GJM1552C1H8R7WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R7BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R7CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R7DB01#** |
| | | | 8.8pF | ±0.05pF | **GJM1552C1H8R8WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R8BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R8CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R8DB01#** |
| | | | 8.9pF | ±0.05pF | **GJM1552C1H8R9WB01#** |
| | | | | ±0.1pF | **GJM1552C1H8R9BB01#** |
| | | | | ±0.25pF | **GJM1552C1H8R9CB01#** |
| | | | | ±0.5pF | **GJM1552C1H8R9DB01#** |
| | | | 9.0pF | ±0.05pF | **GJM1552C1H9R0WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R0BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R0CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R0DB01#** |
| | | | 9.1pF | ±0.05pF | **GJM1552C1H9R1WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R1BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R1CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R1DB01#** |
| | | | 9.2pF | ±0.05pF | **GJM1552C1H9R2WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R2BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R2CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R2DB01#** |
| | | | 9.3pF | ±0.05pF | **GJM1552C1H9R3WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R3BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R3CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R3DB01#** |
| | | | 9.4pF | ±0.05pF | **GJM1552C1H9R4WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R4BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R4CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R4DB01#** |
| | | | 9.5pF | ±0.05pF | **GJM1552C1H9R5WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R5BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R5CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R5DB01#** |
| | | | 9.6pF | ±0.05pF | **GJM1552C1H9R6WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R6BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R6CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R6DB01#** |
| | | | 9.7pF | ±0.05pF | **GJM1552C1H9R7WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R7BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R7CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R7DB01#** |
| | | | 9.8pF | ±0.05pF | **GJM1552C1H9R8WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R8BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R8CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R8DB01#** |
| | | | 9.9pF | ±0.05pF | **GJM1552C1H9R9WB01#** |
| | | | | ±0.1pF | **GJM1552C1H9R9BB01#** |
| | | | | ±0.25pF | **GJM1552C1H9R9CB01#** |
| | | | | ±0.5pF | **GJM1552C1H9R9DB01#** |
| | | | 10pF | ±2% | **GJM1552C1H100GB01#** |
| | | | | ±5% | **GJM1552C1H100JB01#** |
| | | | 11pF | ±2% | **GJM1552C1H110GB01#** |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | CH | 11pF | ±5% | **GJM1552C1H110JB01#** | |
| | | | 12pF | ±2% | **GJM1552C1H120GB01#** | |
| | | | | ±5% | **GJM1552C1H120JB01#** | |
| | | | 13pF | ±2% | **GJM1552C1H130GB01#** | |
| | | | | ±5% | **GJM1552C1H130JB01#** | |
| | | | 15pF | ±2% | **GJM1552C1H150GB01#** | |
| | | | | ±5% | **GJM1552C1H150JB01#** | |
| | | | 16pF | ±2% | **GJM1552C1H160GB01#** | |
| | | | | ±5% | **GJM1552C1H160JB01#** | |
| | | | 18pF | ±2% | **GJM1552C1H180GB01#** | |
| | | | | ±5% | **GJM1552C1H180JB01#** | |
| | | | 20pF | ±2% | **GJM1552C1H200GB01#** | |
| | | | | ±5% | **GJM1552C1H200JB01#** | |
| | | | 22pF | ±1% | **GJM1552C1H220FB01#** | |
| | | | | ±2% | **GJM1552C1H220GB01#** | |
| | | | | ±5% | **GJM1552C1H220JB01#** | |
| | | | 24pF | ±1% | **GJM1552C1H240FB01#** | |
| | | | | ±2% | **GJM1552C1H240GB01#** | |
| | | | | ±5% | **GJM1552C1H240JB01#** | |
| | | | 27pF | ±1% | **GJM1552C1H270FB01#** | |
| | | | | ±2% | **GJM1552C1H270GB01#** | |
| | | | | ±5% | **GJM1552C1H270JB01#** | |
| | | | 30pF | ±1% | **GJM1552C1H300FB01#** | |
| | | | | ±2% | **GJM1552C1H300GB01#** | |
| | | | | ±5% | **GJM1552C1H300JB01#** | |
| | | | 33pF | ±1% | **GJM1552C1H330FB01#** | |
| | | | | ±2% | **GJM1552C1H330GB01#** | |
| | | | | ±5% | **GJM1552C1H330JB01#** | |
| | | | 36pF | ±1% | **GJM1552C1H360FB01#** | |
| | | | | ±2% | **GJM1552C1H360GB01#** | |
| | | | | ±5% | **GJM1552C1H360JB01#** | |
| | | | 39pF | ±1% | **GJM1552C1H390FB01#** | |
| | | | | ±2% | **GJM1552C1H390GB01#** | |
| | | | | ±5% | **GJM1552C1H390JB01#** | |
| | | | 43pF | ±1% | **GJM1552C1H430FB01#** | |
| | | | | ±2% | **GJM1552C1H430GB01#** | |
| | | | | ±5% | **GJM1552C1H430JB01#** | |
| | | | 47pF | ±1% | **GJM1552C1H470FB01#** | |
| | | | | ±2% | **GJM1552C1H470GB01#** | |
| | | | | ±5% | **GJM1552C1H470JB01#** | |

Part number # indicates the package specification code.

Top & Bottom Electrode Type for Bonding

# GMA Series

**This capacitor is suitable for wire bonding mounting by the external electrodes of Au plating.
Mounting in IC packages is also possible with the upper/lower electrode structure!**

## Features

### 1 Allows for high density mounting.

Noise can be reduced by eliminating the routing of the wire, and high efficiency can be achieved with a built-in capacitor in a package, such as IC. Miniaturization of the set is also possible.




<Example of Structure>




<Mounting Example>

### 2 Ideal for bypass applications.

Achieved small size and large capacity with a multilayer structure.

### 3 Excellent in high frequency characteristics.

Since the capacitor consists of an upper/lower electrode structure, the current path becomes shorter and lowers the ESL. Compared with the general purpose GRM series of the same capacity, the impedance of this product becomes lower at high frequencies.




<Comparison between Impedance - Frequency Characteristics>

## Specifications

| | |
|---|---|
| Size | 0.38×0.38mm to 0.8×0.8mm |
| Rated Voltage | DC6.3V to 100V |
| Capacitance | 100pF to 0.47μF |
| Main Applications | 1. Optical communication related equipment<br>2. Various device related, such as GaAsIC (mounted in IC packages)<br>3. Measuring instruments, other ultra compact/thin devices |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GMA Series High Dielectric Constant Type Part Number List

## ■ 0.38×0.38mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.35mm | 10Vdc | X7R | 10000pF | ±20% | **GMA0D3R71A103MA01#** |
| | | R | 10000pF | ±20% | **GMA0D3R11A103MA01#** |

## ■ 0.5×0.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.4mm | 100Vdc | X7R | 100pF | ±20% | **GMA05XR72A101MA01#** |
| | | | 150pF | ±20% | **GMA05XR72A151MA01#** |
| | | | 220pF | ±20% | **GMA05XR72A221MA01#** |
| | | | 330pF | ±20% | **GMA05XR72A331MA01#** |
| | | | 470pF | ±20% | **GMA05XR72A471MA01#** |
| | | | 680pF | ±20% | **GMA05XR72A681MA01#** |
| | | | 1000pF | ±20% | **GMA05XR72A102MA01#** |
| | 25Vdc | X7R | 1500pF | ±20% | **GMA05XR71E152MA11#** |
| | | | 2200pF | ±20% | **GMA05XR71E222MA11#** |
| | | | 3300pF | ±20% | **GMA05XR71E332MA11#** |
| | | | 4700pF | ±20% | **GMA05XR71E472MA11#** |
| | | B | 1500pF | ±20% | **GMA05XB31E152MA11#** |
| | | | 2200pF | ±20% | **GMA05XB31E222MA11#** |
| | | | 3300pF | ±20% | **GMA05XB31E332MA11#** |
| | | | 4700pF | ±20% | **GMA05XB31E472MA11#** |
| | 10Vdc | X7R | 6800pF | ±20% | **GMA05XR71A682MA01#** |
| | | | 10000pF | ±20% | **GMA05XR71A103MA01#** |
| | | | 15000pF | ±20% | **GMA05XR71A153MA01#** |
| | | | 22000pF | ±20% | **GMA05XR71A223MA01#** |
| | | R | 6800pF | ±20% | **GMA05XR11A682MA01#** |
| | | | 10000pF | ±20% | **GMA05XR11A103MA01#** |
| | | | 15000pF | ±20% | **GMA05XR11A153MA01#** |
| | | | 22000pF | ±20% | **GMA05XR11A223MA01#** |
| | | B | 6800pF | ±20% | **GMA05XB11A682MA01#** |
| | | | 10000pF | ±20% | **GMA05XB11A103MA01#** |
| | | | 15000pF | ±20% | **GMA05XB11A153MA01#** |
| | | | 22000pF | ±20% | **GMA05XB11A223MA01#** |
| | 6.3Vdc | X5R | 0.10μF | ±20% | **GMA05XR60J104ME12#** |
| | | B | 0.10μF | ±20% | **GMA05XB30J104ME12#** |

## ■ 0.8×0.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.6mm | 100Vdc | X7R | 1500pF | ±20% | **GMA085R72A152MA01#** |
| | | | 2200pF | ±20% | **GMA085R72A222MA01#** |
| | | | 3300pF | ±20% | **GMA085R72A332MA01#** |
| | | | 4700pF | ±20% | **GMA085R72A472MA01#** |
| | | | 6800pF | ±20% | **GMA085R72A682MA01#** |
| | 25Vdc | X7R | 10000pF | ±20% | **GMA085R71E103MA11#** |
| | | | 15000pF | ±20% | **GMA085R71E153MA11#** |
| | | | 22000pF | ±20% | **GMA085R71E223MA11#** |
| | | B | 10000pF | ±20% | **GMA085B31E103MA11#** |
| | | | 15000pF | ±20% | **GMA085B31E153MA11#** |
| | | | 22000pF | ±20% | **GMA085B31E223MA11#** |
| 0.6mm | 10Vdc | X7R | 33000pF | ±20% | **GMA085R71A333MA01#** |
| | | | 47000pF | ±20% | **GMA085R71A473MA01#** |
| | | | 68000pF | ±20% | **GMA085R71A683MA01#** |
| | | | 0.10μF | ±20% | **GMA085R71A104MA01#** |
| | | R | 33000pF | ±20% | **GMA085R11A333MA01#** |
| | | | 47000pF | ±20% | **GMA085R11A473MA01#** |
| | | | 68000pF | ±20% | **GMA085R11A683MA01#** |
| | | | 0.10μF | ±20% | **GMA085R11A104MA01#** |
| | | B | 33000pF | ±20% | **GMA085B11A333MA01#** |
| | | | 47000pF | ±20% | **GMA085B11A473MA01#** |
| | | | 68000pF | ±20% | **GMA085B11A683MA01#** |
| | | | 0.10μF | ±20% | **GMA085B11A104MA01#** |
| | 6.3Vdc | X5R | 0.47μF | ±20% | **GMA085R60J474ME12#** |
| | | B | 0.47μF | ±20% | **GMA085B30J474ME12#** |

Part number # indicates the package specification code.

Compatible to Bonding / AuSn Soldering

# GMD Series

**This capacitor is compatible to wire bonding mounting by the external electrodes of Au plating.**

## Features

### ① Can be mounted by wire bonding and AuSn soldering.

Since the external electrodes are based on the Au plating specification, mounting by wire/die bonding is possible.




<Example of Structure>




<Mounting Example>

### ② Ideal for mounting in packages, such as optical communication related devices , IC and etc.

Noise can be reduced by eliminating the routing of the wire, and high efficiency can be achieved with a built-in capacitor in the package, such as TO-CAN, IC and etc. by wire bonding mounting.

### ③ Contributes to the miniaturization of the set.

Murata offers a lineup of small size products, such as the 0603 (0201) and 1005 (0402) in mm (inch).

## Specifications

| | |
|---|---|
| Size | 0.6×0.3mm to 1.0×0.5mm |
| Rated Voltage | DC6.3V to 50V |
| Capacitance | 100pF to 1.0μF |
| Main Applications | 1. Optical communication related equipment<br>2. Mounting in IC packages |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GMD Series High Dielectric Constant Type Part Number List

## ■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.33mm | 25Vdc | X7R | 100pF | ±10% | **GMD033R71E101KA01#** |
| | | | 120pF | ±10% | **GMD033R71E121KA01#** |
| | | | 150pF | ±10% | **GMD033R71E151KA01#** |
| | | | 180pF | ±10% | **GMD033R71E181KA01#** |
| | | | 220pF | ±10% | **GMD033R71E221KA01#** |
| | | | 270pF | ±10% | **GMD033R71E271KA01#** |
| | | | 330pF | ±10% | **GMD033R71E331KA01#** |
| | | | 390pF | ±10% | **GMD033R71E391KA01#** |
| | | | 470pF | ±10% | **GMD033R71E471KA01#** |
| | | | 560pF | ±10% | **GMD033R71E561KA01#** |
| | | | 680pF | ±10% | **GMD033R71E681KA01#** |
| | | | 820pF | ±10% | **GMD033R71E821KA01#** |
| | | | 1000pF | ±10% | **GMD033R71E102KA01#** |
| | | | 1200pF | ±10% | **GMD033R71E122KA01#** |
| | | | 1500pF | ±10% | **GMD033R71E152KA01#** |
| | | R | 100pF | ±10% | **GMD033R11E101KA01#** |
| | | | 120pF | ±10% | **GMD033R11E121KA01#** |
| | | | 150pF | ±10% | **GMD033R11E151KA01#** |
| | | | 180pF | ±10% | **GMD033R11E181KA01#** |
| | | | 220pF | ±10% | **GMD033R11E221KA01#** |
| | | | 270pF | ±10% | **GMD033R11E271KA01#** |
| | | | 330pF | ±10% | **GMD033R11E331KA01#** |
| | | | 390pF | ±10% | **GMD033R11E391KA01#** |
| | | | 470pF | ±10% | **GMD033R11E471KA01#** |
| | | | 560pF | ±10% | **GMD033R11E561KA01#** |
| | | | 680pF | ±10% | **GMD033R11E681KA01#** |
| | | | 820pF | ±10% | **GMD033R11E821KA01#** |
| | | | 1000pF | ±10% | **GMD033R11E102KA01#** |
| | | | 1200pF | ±10% | **GMD033R11E122KA01#** |
| | | | 1500pF | ±10% | **GMD033R11E152KA01#** |
| | | B | 100pF | ±10% | **GMD033B11E101KA01#** |
| | | | 120pF | ±10% | **GMD033B11E121KA01#** |
| | | | 150pF | ±10% | **GMD033B11E151KA01#** |
| | | | 180pF | ±10% | **GMD033B11E181KA01#** |
| | | | 220pF | ±10% | **GMD033B11E221KA01#** |
| | | | 270pF | ±10% | **GMD033B11E271KA01#** |
| | | | 330pF | ±10% | **GMD033B11E331KA01#** |
| | | | 390pF | ±10% | **GMD033B11E391KA01#** |
| | | | 470pF | ±10% | **GMD033B11E471KA01#** |
| | | | 560pF | ±10% | **GMD033B11E561KA01#** |
| | | | 680pF | ±10% | **GMD033B11E681KA01#** |
| | | | 820pF | ±10% | **GMD033B11E821KA01#** |
| | | | 1000pF | ±10% | **GMD033B11E102KA01#** |
| | | | 1200pF | ±10% | **GMD033B11E122KA01#** |
| | | | 1500pF | ±10% | **GMD033B11E152KA01#** |
| | 16Vdc | X7R | 1800pF | ±10% | **GMD033R71C182KA11#** |
| | | | 2200pF | ±10% | **GMD033R71C222KA11#** |
| | | | 2700pF | ±10% | **GMD033R71C272KA11#** |
| | | | 3300pF | ±10% | **GMD033R71C332KA11#** |
| | | R | 1800pF | ±10% | **GMD033R11C182KA11#** |
| | | | 2200pF | ±10% | **GMD033R11C222KA11#** |
| | | | 2700pF | ±10% | **GMD033R11C272KA11#** |
| 0.33mm | 16Vdc | R | 3300pF | ±10% | **GMD033R11C332KA11#** |
| | | B | 1800pF | ±10% | **GMD033B31C182KA11#** |
| | | | 2200pF | ±10% | **GMD033B31C222KA11#** |
| | | | 2700pF | ±10% | **GMD033B31C272KA11#** |
| | | | 3300pF | ±10% | **GMD033B31C332KA11#** |
| | 10Vdc | X7R | 3900pF | ±10% | **GMD033R71A392KA01#** |
| | | | 4700pF | ±10% | **GMD033R71A472KA01#** |
| | | | 5600pF | ±10% | **GMD033R71A562KA01#** |
| | | | 6800pF | ±10% | **GMD033R71A682KA01#** |
| | | | 8200pF | ±10% | **GMD033R71A822KA01#** |
| | | | 10000pF | ±10% | **GMD033R71A103KA01#** |
| | | R | 3900pF | ±10% | **GMD033R11A392KA01#** |
| | | | 4700pF | ±10% | **GMD033R11A472KA01#** |
| | | | 5600pF | ±10% | **GMD033R11A562KA01#** |
| | | | 6800pF | ±10% | **GMD033R11A682KA01#** |
| | | | 8200pF | ±10% | **GMD033R11A822KA01#** |
| | | | 10000pF | ±10% | **GMD033R11A103KA01#** |
| | | B | 3900pF | ±10% | **GMD033B11A392KA01#** |
| | | | 4700pF | ±10% | **GMD033B11A472KA01#** |
| | | | 5600pF | ±10% | **GMD033B11A562KA01#** |
| | | | 6800pF | ±10% | **GMD033B11A682KA01#** |
| | | | 8200pF | ±10% | **GMD033B11A822KA01#** |
| | | | 10000pF | ±10% | **GMD033B11A103KA01#** |
| | 6.3Vdc | X5R | 56000pF | ±10% | **GMD033R60J563KE11#** |
| | | | 68000pF | ±10% | **GMD033R60J683KE11#** |
| | | | 82000pF | ±10% | **GMD033R60J823KE11#** |
| | | | 0.10µF | ±10% | **GMD033R60J104KE11#** |
| | | B | 56000pF | ±10% | **GMD033B30J563KE11#** |
| | | | 68000pF | ±10% | **GMD033B30J683KE11#** |
| | | | 82000pF | ±10% | **GMD033B30J823KE11#** |
| | | | 0.10µF | ±10% | **GMD033B30J104KE11#** |

## ■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.55mm | 50Vdc | X7R | 220pF | ±10% | **GMD155R71H221KA01#** |
| | | | 270pF | ±10% | **GMD155R71H271KA01#** |
| | | | 330pF | ±10% | **GMD155R71H331KA01#** |
| | | | 390pF | ±10% | **GMD155R71H391KA01#** |
| | | | 470pF | ±10% | **GMD155R71H471KA01#** |
| | | | 560pF | ±10% | **GMD155R71H561KA01#** |
| | | | 680pF | ±10% | **GMD155R71H681KA01#** |
| | | | 820pF | ±10% | **GMD155R71H821KA01#** |
| | | | 1000pF | ±10% | **GMD155R71H102KA01#** |
| | | | 1200pF | ±10% | **GMD155R71H122KA01#** |
| | | | 1500pF | ±10% | **GMD155R71H152KA01#** |
| | | | 1800pF | ±10% | **GMD155R71H182KA01#** |
| | | | 2200pF | ±10% | **GMD155R71H222KA01#** |
| | | | 2700pF | ±10% | **GMD155R71H272KA01#** |
| | | | 3300pF | ±10% | **GMD155R71H332KA01#** |
| | | | 3900pF | ±10% | **GMD155R71H392KA01#** |
| | | | 4700pF | ±10% | **GMD155R71H472KA01#** |
| | | R | 220pF | ±10% | **GMD155R11H221KA01#** |

Part number # indicates the package specification code.

# GMD Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 50Vdc | R | 270pF | ±10% | **GMD155R11H271KA01#** | |
| | | | 330pF | ±10% | **GMD155R11H331KA01#** | |
| | | | 390pF | ±10% | **GMD155R11H391KA01#** | |
| | | | 470pF | ±10% | **GMD155R11H471KA01#** | |
| | | | 560pF | ±10% | **GMD155R11H561KA01#** | |
| | | | 680pF | ±10% | **GMD155R11H681KA01#** | |
| | | | 820pF | ±10% | **GMD155R11H821KA01#** | |
| | | | 1000pF | ±10% | **GMD155R11H102KA01#** | |
| | | | 1200pF | ±10% | **GMD155R11H122KA01#** | |
| | | | 1500pF | ±10% | **GMD155R11H152KA01#** | |
| | | | 1800pF | ±10% | **GMD155R11H182KA01#** | |
| | | | 2200pF | ±10% | **GMD155R11H222KA01#** | |
| | | | 2700pF | ±10% | **GMD155R11H272KA01#** | |
| | | | 3300pF | ±10% | **GMD155R11H332KA01#** | |
| | | | 3900pF | ±10% | **GMD155R11H392KA01#** | |
| | | | 4700pF | ±10% | **GMD155R11H472KA01#** | |
| | | B | 220pF | ±10% | **GMD155B11H221KA01#** | |
| | | | 270pF | ±10% | **GMD155B11H271KA01#** | |
| | | | 330pF | ±10% | **GMD155B11H331KA01#** | |
| | | | 390pF | ±10% | **GMD155B11H391KA01#** | |
| | | | 470pF | ±10% | **GMD155B11H471KA01#** | |
| | | | 560pF | ±10% | **GMD155B11H561KA01#** | |
| | | | 680pF | ±10% | **GMD155B11H681KA01#** | |
| | | | 820pF | ±10% | **GMD155B11H821KA01#** | |
| | | | 1000pF | ±10% | **GMD155B11H102KA01#** | |
| | | | 1200pF | ±10% | **GMD155B11H122KA01#** | |
| | | | 1500pF | ±10% | **GMD155B11H152KA01#** | |
| | | | 1800pF | ±10% | **GMD155B11H182KA01#** | |
| | | | 2200pF | ±10% | **GMD155B11H222KA01#** | |
| | | | 2700pF | ±10% | **GMD155B11H272KA01#** | |
| | | | 3300pF | ±10% | **GMD155B11H332KA01#** | |
| | | | 3900pF | ±10% | **GMD155B11H392KA01#** | |
| | | | 4700pF | ±10% | **GMD155B11H472KA01#** | |
| | 25Vdc | X7R | 5600pF | ±10% | **GMD155R71E562KA01#** | |
| | | | 6800pF | ±10% | **GMD155R71E682KA01#** | |
| | | | 8200pF | ±10% | **GMD155R71E822KA01#** | |
| | | | 10000pF | ±10% | **GMD155R71E103KA01#** | |
| | | | 12000pF | ±10% | **GMD155R71E123KA01#** | |
| | | | 15000pF | ±10% | **GMD155R71E153KA01#** | |
| | | | 18000pF | ±10% | **GMD155R71E183KA01#** | |
| | | | 22000pF | ±10% | **GMD155R71E223KA01#** | |
| | | | 27000pF | ±10% | **GMD155R71E273KA11#** | |
| | | | 33000pF | ±10% | **GMD155R71E333KA11#** | |
| | | | 39000pF | ±10% | **GMD155R71E393KA11#** | |
| | | | 47000pF | ±10% | **GMD155R71E473KA11#** | |
| | | R | 5600pF | ±10% | **GMD155R11E562KA01#** | |
| | | | 6800pF | ±10% | **GMD155R11E682KA01#** | |
| | | | 8200pF | ±10% | **GMD155R11E822KA01#** | |
| | | | 10000pF | ±10% | **GMD155R11E103KA01#** | |
| | | | 12000pF | ±10% | **GMD155R11E123KA01#** | |
| | | | 15000pF | ±10% | **GMD155R11E153KA01#** | |
| | | | 18000pF | ±10% | **GMD155R11E183KA01#** | |
| | | | 22000pF | ±10% | **GMD155R11E223KA01#** | |
| | | | 27000pF | ±10% | **GMD155R11E273KA11#** | |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 25Vdc | R | 33000pF | ±10% | **GMD155R11E333KA11#** | |
| | | | 39000pF | ±10% | **GMD155R11E393KA11#** | |
| | | | 47000pF | ±10% | **GMD155R11E473KA11#** | |
| | | B | 5600pF | ±10% | **GMD155B11E562KA01#** | |
| | | | 6800pF | ±10% | **GMD155B11E682KA01#** | |
| | | | 8200pF | ±10% | **GMD155B11E822KA01#** | |
| | | | 10000pF | ±10% | **GMD155B11E103KA01#** | |
| | | | 12000pF | ±10% | **GMD155B11E123KA01#** | |
| | | | 15000pF | ±10% | **GMD155B11E153KA01#** | |
| | | | 18000pF | ±10% | **GMD155B11E183KA01#** | |
| | | | 22000pF | ±10% | **GMD155B11E223KA01#** | |
| | | | 27000pF | ±10% | **GMD155B31E273KA11#** | |
| | | | 33000pF | ±10% | **GMD155B31E333KA11#** | |
| | | | 39000pF | ±10% | **GMD155B31E393KA11#** | |
| | | | 47000pF | ±10% | **GMD155B31E473KA11#** | |
| | 16Vdc | X7R | 56000pF | ±10% | **GMD155R71C563KA11#** | |
| | | | 68000pF | ±10% | **GMD155R71C683KA11#** | |
| | | | 82000pF | ±10% | **GMD155R71C823KA11#** | |
| | | | 0.10μF | ±10% | **GMD155R71C104KA11#** | |
| | | R | 56000pF | ±10% | **GMD155R11C563KA11#** | |
| | | | 68000pF | ±10% | **GMD155R11C683KA11#** | |
| | | | 82000pF | ±10% | **GMD155R11C823KA11#** | |
| | | | 0.10μF | ±10% | **GMD155R11C104KA11#** | |
| | | B | 56000pF | ±10% | **GMD155B31C563KA11#** | |
| | | | 68000pF | ±10% | **GMD155B31C683KA11#** | |
| | | | 82000pF | ±10% | **GMD155B31C823KA11#** | |
| | | | 0.10μF | ±10% | **GMD155B31C104KA11#** | |
| | 10Vdc | X5R | 0.12μF | ±10% | **GMD155R61A124KE12#** | |
| | | | 0.15μF | ±10% | **GMD155R61A154KE12#** | |
| | | | 0.18μF | ±10% | **GMD155R61A184KE12#** | |
| | | | 0.22μF | ±10% | **GMD155R61A224KE12#** | |
| | | | 0.27μF | ±10% | **GMD155R61A274KE11#** | |
| | | | 0.33μF | ±10% | **GMD155R61A334KE11#** | |
| | | | 0.39μF | ±10% | **GMD155R61A394KE11#** | |
| | | | 0.47μF | ±10% | **GMD155R61A474KE11#** | |
| | | B | 0.12μF | ±10% | **GMD155B31A124KE12#** | |
| | | | 0.15μF | ±10% | **GMD155B31A154KE12#** | |
| | | | 0.18μF | ±10% | **GMD155B31A184KE12#** | |
| | | | 0.22μF | ±10% | **GMD155B31A224KE12#** | |
| | | | 0.27μF | ±10% | **GMD155B31A274KE11#** | |
| | | | 0.33μF | ±10% | **GMD155B31A334KE11#** | |
| | | | 0.39μF | ±10% | **GMD155B31A394KE11#** | |
| | | | 0.47μF | ±10% | **GMD155B31A474KE11#** | |

Part number # indicates the package specification code.

High Frequency High Q Type 1608(in mm)/0603(in inch) Size Min.

# GQM Series HiQ

## High Frequency Capacitor Ideal for PA Design of Base Stations

### Features

**1 Mainly ideal for base stations of mobile communication devices and temperature compensation of related modules.**

This product is ideal for temperature compensation of high frequency circuits, such as resonant circuits, tuning circuits, and impedance matching circuits where the operating characteristics of the device are greatly affected by the capacitance fluctuation.



<Example of Structure>

**2 High Q and low ESR in VHF, UHF and microwave frequency bands.**

High Q and low ESR were achieved at a high frequency by adopting ceramic material as the dielectric material which enables an extremely low loss at high frequency, and base metal electrodes as the internal electrodes.



<Comparison between Q - Frequency Characteristics>



<Comparison between Q - Frequency Characteristics>

**3 Can be used for tight tolerance.**

In addition to standard tolerance, the allowable range of this product is also suitable for the following narrow tolerance.

| Capacitance Range | Standard Capacitance Tolerance (Capacitance Tolerance Symbol) | Narrow Capacitance Tolerance (Capacitance Tolerance Symbol) |
|---|---|---|
| <=0.9pF | ±0.1pF (B) | ±0.05pF (W) |
| 1.0 to 5.0pF | ±0.25pF (C) | ±0.05pF (W), ±0.1pF (B) |
| 5.1 to 9.9pF | ±0.5pF (D) | ±0.05pF (W), ±0.1pF (B), ±0.25pF (C) |
| >=10pF | ±5% (J) | ±2% (G) |

### Specifications

| | |
|---|---|
| Size | 1.6×0.8mm to 2.8×2.8mm |
| Rated Voltage | DC50V to 500V |
| Capacitance | 0.1pF to 510pF |
| Main Applications | Mobile phone base stations |



<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GQM Series Temperature Compensating Type HiQ Part Number List

## ■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.8mm | 250Vdc | C0G | 1.0pF | ±0.1pF | **GQM1875C2E1R0BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R0CB12#** |
| | | | 1.1pF | ±0.1pF | **GQM1875C2E1R1BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R1CB12#** |
| | | | 1.2pF | ±0.1pF | **GQM1875C2E1R2BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R2CB12#** |
| | | | 1.3pF | ±0.1pF | **GQM1875C2E1R3BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R3CB12#** |
| | | | 1.5pF | ±0.1pF | **GQM1875C2E1R5BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R5CB12#** |
| | | | 1.6pF | ±0.1pF | **GQM1875C2E1R6BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R6CB12#** |
| | | | 1.8pF | ±0.1pF | **GQM1875C2E1R8BB12#** |
| | | | | ±0.25pF | **GQM1875C2E1R8CB12#** |
| | | | 2.0pF | ±0.1pF | **GQM1875C2E2R0BB12#** |
| | | | | ±0.25pF | **GQM1875C2E2R0CB12#** |
| | | | 2.2pF | ±0.1pF | **GQM1875C2E2R2BB12#** |
| | | | | ±0.25pF | **GQM1875C2E2R2CB12#** |
| | | | 2.4pF | ±0.1pF | **GQM1875C2E2R4BB12#** |
| | | | | ±0.25pF | **GQM1875C2E2R4CB12#** |
| | | | 2.7pF | ±0.1pF | **GQM1875C2E2R7BB12#** |
| | | | | ±0.25pF | **GQM1875C2E2R7CB12#** |
| | | | 3.0pF | ±0.1pF | **GQM1875C2E3R0BB12#** |
| | | | | ±0.25pF | **GQM1875C2E3R0CB12#** |
| | | | 3.3pF | ±0.1pF | **GQM1875C2E3R3BB12#** |
| | | | | ±0.25pF | **GQM1875C2E3R3CB12#** |
| | | | 3.6pF | ±0.1pF | **GQM1875C2E3R6BB12#** |
| | | | | ±0.25pF | **GQM1875C2E3R6CB12#** |
| | | | 3.9pF | ±0.1pF | **GQM1875C2E3R9BB12#** |
| | | | | ±0.25pF | **GQM1875C2E3R9CB12#** |
| | | | 4.0pF | ±0.1pF | **GQM1875C2E4R0BB12#** |
| | | | | ±0.25pF | **GQM1875C2E4R0CB12#** |
| | | | 4.3pF | ±0.1pF | **GQM1875C2E4R3BB12#** |
| | | | | ±0.25pF | **GQM1875C2E4R3CB12#** |
| | | | 4.7pF | ±0.1pF | **GQM1875C2E4R7BB12#** |
| | | | | ±0.25pF | **GQM1875C2E4R7CB12#** |
| | | | 5.0pF | ±0.1pF | **GQM1875C2E5R0BB12#** |
| | | | | ±0.25pF | **GQM1875C2E5R0CB12#** |
| | | | 5.1pF | ±0.25pF | **GQM1875C2E5R1CB12#** |
| | | | | ±0.5pF | **GQM1875C2E5R1DB12#** |
| | | | 5.6pF | ±0.25pF | **GQM1875C2E5R6CB12#** |
| | | | | ±0.5pF | **GQM1875C2E5R6DB12#** |
| | | | 6.0pF | ±0.25pF | **GQM1875C2E6R0CB12#** |
| | | | | ±0.5pF | **GQM1875C2E6R0DB12#** |
| | | | 6.2pF | ±0.25pF | **GQM1875C2E6R2CB12#** |
| | | | | ±0.5pF | **GQM1875C2E6R2DB12#** |
| | | | 6.8pF | ±0.25pF | **GQM1875C2E6R8CB12#** |
| | | | | ±0.5pF | **GQM1875C2E6R8DB12#** |
| | | | 7.0pF | ±0.25pF | **GQM1875C2E7R0CB12#** |
| | | | | ±0.5pF | **GQM1875C2E7R0DB12#** |
| | | | 7.5pF | ±0.25pF | **GQM1875C2E7R5CB12#** |
| | | | | ±0.5pF | **GQM1875C2E7R5DB12#** |
| 0.8mm | 250Vdc | C0G | 8.0pF | ±0.25pF | **GQM1875C2E8R0CB12#** |
| | | | | ±0.5pF | **GQM1875C2E8R0DB12#** |
| | | | 8.2pF | ±0.25pF | **GQM1875C2E8R2CB12#** |
| | | | | ±0.5pF | **GQM1875C2E8R2DB12#** |
| | | | 9.0pF | ±0.25pF | **GQM1875C2E9R0CB12#** |
| | | | | ±0.5pF | **GQM1875C2E9R0DB12#** |
| | | | 9.1pF | ±0.25pF | **GQM1875C2E9R1CB12#** |
| | | | | ±0.5pF | **GQM1875C2E9R1DB12#** |
| | | | 10pF | ±2% | **GQM1875C2E100GB12#** |
| | | | | ±5% | **GQM1875C2E100JB12#** |
| | | | 11pF | ±2% | **GQM1875C2E110GB12#** |
| | | | | ±5% | **GQM1875C2E110JB12#** |
| | | | 12pF | ±2% | **GQM1875C2E120GB12#** |
| | | | | ±5% | **GQM1875C2E120JB12#** |
| | | | 13pF | ±2% | **GQM1875C2E130GB12#** |
| | | | | ±5% | **GQM1875C2E130JB12#** |
| | | | 15pF | ±2% | **GQM1875C2E150GB12#** |
| | | | | ±5% | **GQM1875C2E150JB12#** |
| | | | 16pF | ±2% | **GQM1875C2E160GB12#** |
| | | | | ±5% | **GQM1875C2E160JB12#** |
| | | | 18pF | ±2% | **GQM1875C2E180GB12#** |
| | | | | ±5% | **GQM1875C2E180JB12#** |
| | | | 20pF | ±2% | **GQM1875C2E200GB12#** |
| | | | | ±5% | **GQM1875C2E200JB12#** |
| | | | 22pF | ±2% | **GQM1875C2E220GB12#** |
| | | | | ±5% | **GQM1875C2E220JB12#** |
| | | | 24pF | ±2% | **GQM1875C2E240GB12#** |
| | | | | ±5% | **GQM1875C2E240JB12#** |
| | | | 27pF | ±2% | **GQM1875C2E270GB12#** |
| | | | | ±5% | **GQM1875C2E270JB12#** |
| | | | 30pF | ±2% | **GQM1875C2E300GB12#** |
| | | | | ±5% | **GQM1875C2E300JB12#** |
| | | | 33pF | ±2% | **GQM1875C2E330GB12#** |
| | | | | ±5% | **GQM1875C2E330JB12#** |
| | | | 36pF | ±2% | **GQM1875C2E360GB12#** |
| | | | | ±5% | **GQM1875C2E360JB12#** |
| | | | 39pF | ±2% | **GQM1875C2E390GB12#** |
| | | | | ±5% | **GQM1875C2E390JB12#** |
| | | | 43pF | ±2% | **GQM1875C2E430GB12#** |
| | | | | ±5% | **GQM1875C2E430JB12#** |
| | | | 47pF | ±2% | **GQM1875C2E470GB12#** |
| | | | | ±5% | **GQM1875C2E470JB12#** |
| 0.9mm | 100Vdc | C0G | 1.0pF | ±0.1pF | **GQM1885C2A1R0BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R0CB01#** |
| | | | 1.1pF | ±0.1pF | **GQM1885C2A1R1BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R1CB01#** |
| | | | 1.2pF | ±0.1pF | **GQM1885C2A1R2BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R2CB01#** |
| | | | 1.3pF | ±0.1pF | **GQM1885C2A1R3BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R3CB01#** |
| | | | 1.5pF | ±0.1pF | **GQM1885C2A1R5BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R5CB01#** |
| | | | 1.6pF | ±0.1pF | **GQM1885C2A1R6BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R6CB01#** |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | C0G | 1.8pF | ±0.1pF | **GQM1885C2A1R8BB01#** |
| | | | | ±0.25pF | **GQM1885C2A1R8CB01#** |
| | | | 2.0pF | ±0.1pF | **GQM1885C2A2R0BB01#** |
| | | | | ±0.25pF | **GQM1885C2A2R0CB01#** |
| | | | 2.2pF | ±0.1pF | **GQM1885C2A2R2BB01#** |
| | | | | ±0.25pF | **GQM1885C2A2R2CB01#** |
| | | | 2.4pF | ±0.1pF | **GQM1885C2A2R4BB01#** |
| | | | | ±0.25pF | **GQM1885C2A2R4CB01#** |
| | | | 2.7pF | ±0.1pF | **GQM1885C2A2R7BB01#** |
| | | | | ±0.25pF | **GQM1885C2A2R7CB01#** |
| | | | 3.0pF | ±0.1pF | **GQM1885C2A3R0BB01#** |
| | | | | ±0.25pF | **GQM1885C2A3R0CB01#** |
| | | | 3.3pF | ±0.1pF | **GQM1885C2A3R3BB01#** |
| | | | | ±0.25pF | **GQM1885C2A3R3CB01#** |
| | | | 3.6pF | ±0.1pF | **GQM1885C2A3R6BB01#** |
| | | | | ±0.25pF | **GQM1885C2A3R6CB01#** |
| | | | 3.9pF | ±0.1pF | **GQM1885C2A3R9BB01#** |
| | | | | ±0.25pF | **GQM1885C2A3R9CB01#** |
| | | | 4.0pF | ±0.1pF | **GQM1885C2A4R0BB01#** |
| | | | | ±0.25pF | **GQM1885C2A4R0CB01#** |
| | | | 4.3pF | ±0.1pF | **GQM1885C2A4R3BB01#** |
| | | | | ±0.25pF | **GQM1885C2A4R3CB01#** |
| | | | 4.7pF | ±0.1pF | **GQM1885C2A4R7BB01#** |
| | | | | ±0.25pF | **GQM1885C2A4R7CB01#** |
| | | | 5.0pF | ±0.1pF | **GQM1885C2A5R0BB01#** |
| | | | | ±0.25pF | **GQM1885C2A5R0CB01#** |
| | | | 5.1pF | ±0.25pF | **GQM1885C2A5R1CB01#** |
| | | | | ±0.5pF | **GQM1885C2A5R1DB01#** |
| | | | 5.6pF | ±0.25pF | **GQM1885C2A5R6CB01#** |
| | | | | ±0.5pF | **GQM1885C2A5R6DB01#** |
| | | | 6.0pF | ±0.25pF | **GQM1885C2A6R0CB01#** |
| | | | | ±0.5pF | **GQM1885C2A6R0DB01#** |
| | | | 6.2pF | ±0.25pF | **GQM1885C2A6R2CB01#** |
| | | | | ±0.5pF | **GQM1885C2A6R2DB01#** |
| | | | 6.8pF | ±0.25pF | **GQM1885C2A6R8CB01#** |
| | | | | ±0.5pF | **GQM1885C2A6R8DB01#** |
| | | CK | 1.0pF | ±0.1pF | **GQM1884C2A1R0BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R0CB01#** |
| | | | 1.1pF | ±0.1pF | **GQM1884C2A1R1BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R1CB01#** |
| | | | 1.2pF | ±0.1pF | **GQM1884C2A1R2BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R2CB01#** |
| | | | 1.3pF | ±0.1pF | **GQM1884C2A1R3BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R3CB01#** |
| | | | 1.5pF | ±0.1pF | **GQM1884C2A1R5BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R5CB01#** |
| | | | 1.6pF | ±0.1pF | **GQM1884C2A1R6BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R6CB01#** |
| | | | 1.8pF | ±0.1pF | **GQM1884C2A1R8BB01#** |
| | | | | ±0.25pF | **GQM1884C2A1R8CB01#** |
| | | | 2.0pF | ±0.1pF | **GQM1884C2A2R0BB01#** |
| | | | | ±0.25pF | **GQM1884C2A2R0CB01#** |
| | | CJ | 2.2pF | ±0.1pF | **GQM1883C2A2R2BB01#** |
| | | | | ±0.25pF | **GQM1883C2A2R2CB01#** |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 100Vdc | CJ | 2.4pF | ±0.1pF | **GQM1883C2A2R4BB01#** |
| | | | | ±0.25pF | **GQM1883C2A2R4CB01#** |
| | | | 2.7pF | ±0.1pF | **GQM1883C2A2R7BB01#** |
| | | | | ±0.25pF | **GQM1883C2A2R7CB01#** |
| | | | 3.0pF | ±0.1pF | **GQM1883C2A3R0BB01#** |
| | | | | ±0.25pF | **GQM1883C2A3R0CB01#** |
| | | | 3.3pF | ±0.1pF | **GQM1883C2A3R3BB01#** |
| | | | | ±0.25pF | **GQM1883C2A3R3CB01#** |
| | | | 3.6pF | ±0.1pF | **GQM1883C2A3R6BB01#** |
| | | | | ±0.25pF | **GQM1883C2A3R6CB01#** |
| | | | 3.9pF | ±0.1pF | **GQM1883C2A3R9BB01#** |
| | | | | ±0.25pF | **GQM1883C2A3R9CB01#** |
| | | CH | 4.0pF | ±0.1pF | **GQM1882C2A4R0BB01#** |
| | | | | ±0.25pF | **GQM1882C2A4R0CB01#** |
| | | | 4.3pF | ±0.1pF | **GQM1882C2A4R3BB01#** |
| | | | | ±0.25pF | **GQM1882C2A4R3CB01#** |
| | | | 4.7pF | ±0.1pF | **GQM1882C2A4R7BB01#** |
| | | | | ±0.25pF | **GQM1882C2A4R7CB01#** |
| | | | 5.0pF | ±0.1pF | **GQM1882C2A5R0BB01#** |
| | | | | ±0.25pF | **GQM1882C2A5R0CB01#** |
| | | | 5.1pF | ±0.25pF | **GQM1882C2A5R1CB01#** |
| | | | | ±0.5pF | **GQM1882C2A5R1DB01#** |
| | | | 5.6pF | ±0.25pF | **GQM1882C2A5R6CB01#** |
| | | | | ±0.5pF | **GQM1882C2A5R6DB01#** |
| | | | 6.0pF | ±0.25pF | **GQM1882C2A6R0CB01#** |
| | | | | ±0.5pF | **GQM1882C2A6R0DB01#** |
| | | | 6.2pF | ±0.25pF | **GQM1882C2A6R2CB01#** |
| | | | | ±0.5pF | **GQM1882C2A6R2DB01#** |
| | | | 6.8pF | ±0.25pF | **GQM1882C2A6R8CB01#** |
| | | | | ±0.5pF | **GQM1882C2A6R8DB01#** |
| | 50Vdc | C0G | 7.0pF | ±0.25pF | **GQM1885C1H7R0CB01#** |
| | | | | ±0.5pF | **GQM1885C1H7R0DB01#** |
| | | | 7.5pF | ±0.25pF | **GQM1885C1H7R5CB01#** |
| | | | | ±0.5pF | **GQM1885C1H7R5DB01#** |
| | | | 8.0pF | ±0.25pF | **GQM1885C1H8R0CB01#** |
| | | | | ±0.5pF | **GQM1885C1H8R0DB01#** |
| | | | 8.2pF | ±0.25pF | **GQM1885C1H8R2CB01#** |
| | | | | ±0.5pF | **GQM1885C1H8R2DB01#** |
| | | | 9.0pF | ±0.25pF | **GQM1885C1H9R0CB01#** |
| | | | | ±0.5pF | **GQM1885C1H9R0DB01#** |
| | | | 9.1pF | ±0.25pF | **GQM1885C1H9R1CB01#** |
| | | | | ±0.5pF | **GQM1885C1H9R1DB01#** |
| | | | 10pF | ±2% | **GQM1885C1H100GB01#** |
| | | | | ±5% | **GQM1885C1H100JB01#** |
| | | | 11pF | ±2% | **GQM1885C1H110GB01#** |
| | | | | ±5% | **GQM1885C1H110JB01#** |
| | | | 12pF | ±2% | **GQM1885C1H120GB01#** |
| | | | | ±5% | **GQM1885C1H120JB01#** |
| | | | 13pF | ±2% | **GQM1885C1H130GB01#** |
| | | | | ±5% | **GQM1885C1H130JB01#** |
| | | | 15pF | ±2% | **GQM1885C1H150GB01#** |
| | | | | ±5% | **GQM1885C1H150JB01#** |
| | | | 16pF | ±2% | **GQM1885C1H160GB01#** |
| | | | | ±5% | **GQM1885C1H160JB01#** |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 50Vdc | C0G | 18pF | ±2% | GQM1885C1H180GB01# |
| | | | | ±5% | GQM1885C1H180JB01# |
| | | | 20pF | ±2% | GQM1885C1H200GB01# |
| | | | | ±5% | GQM1885C1H200JB01# |
| | | | 22pF | ±2% | GQM1885C1H220GB01# |
| | | | | ±5% | GQM1885C1H220JB01# |
| | | | 24pF | ±2% | GQM1885C1H240GB01# |
| | | | | ±5% | GQM1885C1H240JB01# |
| | | | 27pF | ±2% | GQM1885C1H270GB01# |
| | | | | ±5% | GQM1885C1H270JB01# |
| | | | 30pF | ±2% | GQM1885C1H300GB01# |
| | | | | ±5% | GQM1885C1H300JB01# |
| | | | 33pF | ±2% | GQM1885C1H330GB01# |
| | | | | ±5% | GQM1885C1H330JB01# |
| | | | 36pF | ±2% | GQM1885C1H360GB01# |
| | | | | ±5% | GQM1885C1H360JB01# |
| | | | 39pF | ±2% | GQM1885C1H390GB01# |
| | | | | ±5% | GQM1885C1H390JB01# |
| | | | 43pF | ±2% | GQM1885C1H430GB01# |
| | | | | ±5% | GQM1885C1H430JB01# |
| | | | 47pF | ±2% | GQM1885C1H470GB01# |
| | | | | ±5% | GQM1885C1H470JB01# |
| | | | 51pF | ±2% | GQM1885C1H510GB01# |
| | | | | ±5% | GQM1885C1H510JB01# |
| | | | 56pF | ±2% | GQM1885C1H560GB01# |
| | | | | ±5% | GQM1885C1H560JB01# |
| | | | 62pF | ±2% | GQM1885C1H620GB01# |
| | | | | ±5% | GQM1885C1H620JB01# |
| | | | 68pF | ±2% | GQM1885C1H680GB01# |
| | | | | ±5% | GQM1885C1H680JB01# |
| | | | 75pF | ±2% | GQM1885C1H750GB01# |
| | | | | ±5% | GQM1885C1H750JB01# |
| | | | 82pF | ±2% | GQM1885C1H820GB01# |
| | | | | ±5% | GQM1885C1H820JB01# |
| | | | 91pF | ±2% | GQM1885C1H910GB01# |
| | | | | ±5% | GQM1885C1H910JB01# |
| | | | 100pF | ±2% | GQM1885C1H101GB01# |
| | | | | ±5% | GQM1885C1H101JB01# |
| | | CH | 7.0pF | ±0.25pF | GQM1882C1H7R0CB01# |
| | | | | ±0.5pF | GQM1882C1H7R0DB01# |
| | | | 7.5pF | ±0.25pF | GQM1882C1H7R5CB01# |
| | | | | ±0.5pF | GQM1882C1H7R5DB01# |
| | | | 8.0pF | ±0.25pF | GQM1882C1H8R0CB01# |
| | | | | ±0.5pF | GQM1882C1H8R0DB01# |
| | | | 8.2pF | ±0.25pF | GQM1882C1H8R2CB01# |
| | | | | ±0.5pF | GQM1882C1H8R2DB01# |
| | | | 9.0pF | ±0.25pF | GQM1882C1H9R0CB01# |
| | | | | ±0.5pF | GQM1882C1H9R0DB01# |
| | | | 9.1pF | ±0.25pF | GQM1882C1H9R1CB01# |
| | | | | ±0.5pF | GQM1882C1H9R1DB01# |
| | | | 10pF | ±2% | GQM1882C1H100GB01# |
| | | | | ±5% | GQM1882C1H100JB01# |
| | | | 11pF | ±2% | GQM1882C1H110GB01# |
| | | | | ±5% | GQM1882C1H110JB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.9mm | 50Vdc | CH | 12pF | ±2% | GQM1882C1H120GB01# |
| | | | | ±5% | GQM1882C1H120JB01# |
| | | | 13pF | ±2% | GQM1882C1H130GB01# |
| | | | | ±5% | GQM1882C1H130JB01# |
| | | | 15pF | ±2% | GQM1882C1H150GB01# |
| | | | | ±5% | GQM1882C1H150JB01# |
| | | | 16pF | ±2% | GQM1882C1H160GB01# |
| | | | | ±5% | GQM1882C1H160JB01# |
| | | | 18pF | ±2% | GQM1882C1H180GB01# |
| | | | | ±5% | GQM1882C1H180JB01# |
| | | | 20pF | ±2% | GQM1882C1H200GB01# |
| | | | | ±5% | GQM1882C1H200JB01# |
| | | | 22pF | ±2% | GQM1882C1H220GB01# |
| | | | | ±5% | GQM1882C1H220JB01# |
| | | | 24pF | ±2% | GQM1882C1H240GB01# |
| | | | | ±5% | GQM1882C1H240JB01# |
| | | | 27pF | ±2% | GQM1882C1H270GB01# |
| | | | | ±5% | GQM1882C1H270JB01# |
| | | | 30pF | ±2% | GQM1882C1H300GB01# |
| | | | | ±5% | GQM1882C1H300JB01# |
| | | | 33pF | ±2% | GQM1882C1H330GB01# |
| | | | | ±5% | GQM1882C1H330JB01# |
| | | | 36pF | ±2% | GQM1882C1H360GB01# |
| | | | | ±5% | GQM1882C1H360JB01# |
| | | | 39pF | ±2% | GQM1882C1H390GB01# |
| | | | | ±5% | GQM1882C1H390JB01# |
| | | | 43pF | ±2% | GQM1882C1H430GB01# |
| | | | | ±5% | GQM1882C1H430JB01# |
| | | | 47pF | ±2% | GQM1882C1H470GB01# |
| | | | | ±5% | GQM1882C1H470JB01# |
| | | | 51pF | ±2% | GQM1882C1H510GB01# |
| | | | | ±5% | GQM1882C1H510JB01# |
| | | | 56pF | ±2% | GQM1882C1H560GB01# |
| | | | | ±5% | GQM1882C1H560JB01# |
| | | | 62pF | ±2% | GQM1882C1H620GB01# |
| | | | | ±5% | GQM1882C1H620JB01# |
| | | | 68pF | ±2% | GQM1882C1H680GB01# |
| | | | | ±5% | GQM1882C1H680JB01# |
| | | | 75pF | ±2% | GQM1882C1H750GB01# |
| | | | | ±5% | GQM1882C1H750JB01# |
| | | | 82pF | ±2% | GQM1882C1H820GB01# |
| | | | | ±5% | GQM1882C1H820JB01# |
| | | | 91pF | ±2% | GQM1882C1H910GB01# |
| | | | | ±5% | GQM1882C1H910JB01# |
| | | | 100pF | ±2% | GQM1882C1H101GB01# |
| | | | | ±5% | GQM1882C1H101JB01# |

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 100Vdc | C0G | 1.0pF | ±0.1pF | GQM2195C2A1R0BB01# |
| | | | | ±0.25pF | GQM2195C2A1R0CB01# |
| | | | 1.1pF | ±0.1pF | GQM2195C2A1R1BB01# |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 100Vdc | C0G | 1.1pF | ±0.25pF | **GQM2195C2A1R1CB01#** |
| | | | 1.2pF | ±0.1pF | **GQM2195C2A1R2BB01#** |
| | | | | ±0.25pF | **GQM2195C2A1R2CB01#** |
| | | | 1.3pF | ±0.1pF | **GQM2195C2A1R3BB01#** |
| | | | | ±0.25pF | **GQM2195C2A1R3CB01#** |
| | | | 1.5pF | ±0.1pF | **GQM2195C2A1R5BB01#** |
| | | | | ±0.25pF | **GQM2195C2A1R5CB01#** |
| | | | 1.6pF | ±0.1pF | **GQM2195C2A1R6BB01#** |
| | | | | ±0.25pF | **GQM2195C2A1R6CB01#** |
| | | | 1.8pF | ±0.1pF | **GQM2195C2A1R8BB01#** |
| | | | | ±0.25pF | **GQM2195C2A1R8CB01#** |
| | | | 2.0pF | ±0.1pF | **GQM2195C2A2R0BB01#** |
| | | | | ±0.25pF | **GQM2195C2A2R0CB01#** |
| | | | 2.2pF | ±0.1pF | **GQM2195C2A2R2BB01#** |
| | | | | ±0.25pF | **GQM2195C2A2R2CB01#** |
| | | | 2.4pF | ±0.1pF | **GQM2195C2A2R4BB01#** |
| | | | | ±0.25pF | **GQM2195C2A2R4CB01#** |
| | | | 2.7pF | ±0.1pF | **GQM2195C2A2R7BB01#** |
| | | | | ±0.25pF | **GQM2195C2A2R7CB01#** |
| | | | 3.0pF | ±0.1pF | **GQM2195C2A3R0BB01#** |
| | | | | ±0.25pF | **GQM2195C2A3R0CB01#** |
| | | | 3.3pF | ±0.1pF | **GQM2195C2A3R3BB01#** |
| | | | | ±0.25pF | **GQM2195C2A3R3CB01#** |
| | | | 3.6pF | ±0.1pF | **GQM2195C2A3R6BB01#** |
| | | | | ±0.25pF | **GQM2195C2A3R6CB01#** |
| | | | 3.9pF | ±0.1pF | **GQM2195C2A3R9BB01#** |
| | | | | ±0.25pF | **GQM2195C2A3R9CB01#** |
| | | | 4.0pF | ±0.1pF | **GQM2195C2A4R0BB01#** |
| | | | | ±0.25pF | **GQM2195C2A4R0CB01#** |
| | | | 4.3pF | ±0.1pF | **GQM2195C2A4R3BB01#** |
| | | | | ±0.25pF | **GQM2195C2A4R3CB01#** |
| | | | 4.7pF | ±0.1pF | **GQM2195C2A4R7BB01#** |
| | | | | ±0.25pF | **GQM2195C2A4R7CB01#** |
| | | | 5.0pF | ±0.1pF | **GQM2195C2A5R0BB01#** |
| | | | | ±0.25pF | **GQM2195C2A5R0CB01#** |
| | | | 5.1pF | ±0.25pF | **GQM2195C2A5R1CB01#** |
| | | | | ±0.5pF | **GQM2195C2A5R1DB01#** |
| | | | 5.6pF | ±0.25pF | **GQM2195C2A5R6CB01#** |
| | | | | ±0.5pF | **GQM2195C2A5R6DB01#** |
| | | | 6.0pF | ±0.25pF | **GQM2195C2A6R0CB01#** |
| | | | | ±0.5pF | **GQM2195C2A6R0DB01#** |
| | | | 6.2pF | ±0.25pF | **GQM2195C2A6R2CB01#** |
| | | | | ±0.5pF | **GQM2195C2A6R2DB01#** |
| | | | 6.8pF | ±0.25pF | **GQM2195C2A6R8CB01#** |
| | | | | ±0.5pF | **GQM2195C2A6R8DB01#** |
| | | | 7.0pF | ±0.25pF | **GQM2195C2A7R0CB01#** |
| | | | | ±0.5pF | **GQM2195C2A7R0DB01#** |
| | | | 7.5pF | ±0.25pF | **GQM2195C2A7R5CB01#** |
| | | | | ±0.5pF | **GQM2195C2A7R5DB01#** |
| | | | 8.0pF | ±0.25pF | **GQM2195C2A8R0CB01#** |
| | | | | ±0.5pF | **GQM2195C2A8R0DB01#** |
| | | | 8.2pF | ±0.25pF | **GQM2195C2A8R2CB01#** |
| | | | | ±0.5pF | **GQM2195C2A8R2DB01#** |
| | | | 9.0pF | ±0.25pF | **GQM2195C2A9R0CB01#** |
| 0.95mm | 100Vdc | C0G | 9.0pF | ±0.5pF | **GQM2195C2A9R0DB01#** |
| | | | 9.1pF | ±0.25pF | **GQM2195C2A9R1CB01#** |
| | | | | ±0.5pF | **GQM2195C2A9R1DB01#** |
| | | | 10pF | ±2% | **GQM2195C2A100GB01#** |
| | | | | ±5% | **GQM2195C2A100JB01#** |
| | | | 11pF | ±2% | **GQM2195C2A110GB01#** |
| | | | | ±5% | **GQM2195C2A110JB01#** |
| | | | 12pF | ±2% | **GQM2195C2A120GB01#** |
| | | | | ±5% | **GQM2195C2A120JB01#** |
| | | | 13pF | ±2% | **GQM2195C2A130GB01#** |
| | | | | ±5% | **GQM2195C2A130JB01#** |
| | | | 15pF | ±2% | **GQM2195C2A150GB01#** |
| | | | | ±5% | **GQM2195C2A150JB01#** |
| | | | 16pF | ±2% | **GQM2195C2A160GB01#** |
| | | | | ±5% | **GQM2195C2A160JB01#** |
| | | | 18pF | ±2% | **GQM2195C2A180GB01#** |
| | | | | ±5% | **GQM2195C2A180JB01#** |
| | | CK | 1.0pF | ±0.1pF | **GQM2194C2A1R0BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R0CB01#** |
| | | | 1.1pF | ±0.1pF | **GQM2194C2A1R1BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R1CB01#** |
| | | | 1.2pF | ±0.1pF | **GQM2194C2A1R2BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R2CB01#** |
| | | | 1.3pF | ±0.1pF | **GQM2194C2A1R3BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R3CB01#** |
| | | | 1.5pF | ±0.1pF | **GQM2194C2A1R5BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R5CB01#** |
| | | | 1.6pF | ±0.1pF | **GQM2194C2A1R6BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R6CB01#** |
| | | | 1.8pF | ±0.1pF | **GQM2194C2A1R8BB01#** |
| | | | | ±0.25pF | **GQM2194C2A1R8CB01#** |
| | | | 2.0pF | ±0.1pF | **GQM2194C2A2R0BB01#** |
| | | | | ±0.25pF | **GQM2194C2A2R0CB01#** |
| | | CJ | 2.2pF | ±0.1pF | **GQM2193C2A2R2BB01#** |
| | | | | ±0.25pF | **GQM2193C2A2R2CB01#** |
| | | | 2.4pF | ±0.1pF | **GQM2193C2A2R4BB01#** |
| | | | | ±0.25pF | **GQM2193C2A2R4CB01#** |
| | | | 2.7pF | ±0.1pF | **GQM2193C2A2R7BB01#** |
| | | | | ±0.25pF | **GQM2193C2A2R7CB01#** |
| | | | 3.0pF | ±0.1pF | **GQM2193C2A3R0BB01#** |
| | | | | ±0.25pF | **GQM2193C2A3R0CB01#** |
| | | | 3.3pF | ±0.1pF | **GQM2193C2A3R3BB01#** |
| | | | | ±0.25pF | **GQM2193C2A3R3CB01#** |
| | | | 3.6pF | ±0.1pF | **GQM2193C2A3R6BB01#** |
| | | | | ±0.25pF | **GQM2193C2A3R6CB01#** |
| | | | 3.9pF | ±0.1pF | **GQM2193C2A3R9BB01#** |
| | | | | ±0.25pF | **GQM2193C2A3R9CB01#** |
| | | CH | 4.0pF | ±0.1pF | **GQM2192C2A4R0BB01#** |
| | | | | ±0.25pF | **GQM2192C2A4R0CB01#** |
| | | | 4.3pF | ±0.1pF | **GQM2192C2A4R3BB01#** |
| | | | | ±0.25pF | **GQM2192C2A4R3CB01#** |
| | | | 4.7pF | ±0.1pF | **GQM2192C2A4R7BB01#** |
| | | | | ±0.25pF | **GQM2192C2A4R7CB01#** |
| | | | 5.0pF | ±0.1pF | **GQM2192C2A5R0BB01#** |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 100Vdc | CH | 5.0pF | ±0.25pF | GQM2192C2A5R0CB01# |
| | | | 5.1pF | ±0.25pF | GQM2192C2A5R1CB01# |
| | | | | ±0.5pF | GQM2192C2A5R1DB01# |
| | | | 5.6pF | ±0.25pF | GQM2192C2A5R6CB01# |
| | | | | ±0.5pF | GQM2192C2A5R6DB01# |
| | | | 6.0pF | ±0.25pF | GQM2192C2A6R0CB01# |
| | | | | ±0.5pF | GQM2192C2A6R0DB01# |
| | | | 6.2pF | ±0.25pF | GQM2192C2A6R2CB01# |
| | | | | ±0.5pF | GQM2192C2A6R2DB01# |
| | | | 6.8pF | ±0.25pF | GQM2192C2A6R8CB01# |
| | | | | ±0.5pF | GQM2192C2A6R8DB01# |
| | | | 7.0pF | ±0.25pF | GQM2192C2A7R0CB01# |
| | | | | ±0.5pF | GQM2192C2A7R0DB01# |
| | | | 7.5pF | ±0.25pF | GQM2192C2A7R5CB01# |
| | | | | ±0.5pF | GQM2192C2A7R5DB01# |
| | | | 8.0pF | ±0.25pF | GQM2192C2A8R0CB01# |
| | | | | ±0.5pF | GQM2192C2A8R0DB01# |
| | | | 8.2pF | ±0.25pF | GQM2192C2A8R2CB01# |
| | | | | ±0.5pF | GQM2192C2A8R2DB01# |
| | | | 9.0pF | ±0.25pF | GQM2192C2A9R0CB01# |
| | | | | ±0.5pF | GQM2192C2A9R0DB01# |
| | | | 9.1pF | ±0.25pF | GQM2192C2A9R1CB01# |
| | | | | ±0.5pF | GQM2192C2A9R1DB01# |
| | | | 10pF | ±2% | GQM2192C2A100GB01# |
| | | | | ±5% | GQM2192C2A100JB01# |
| | | | 11pF | ±2% | GQM2192C2A110GB01# |
| | | | | ±5% | GQM2192C2A110JB01# |
| | | | 12pF | ±2% | GQM2192C2A120GB01# |
| | | | | ±5% | GQM2192C2A120JB01# |
| | | | 13pF | ±2% | GQM2192C2A130GB01# |
| | | | | ±5% | GQM2192C2A130JB01# |
| | | | 15pF | ±2% | GQM2192C2A150GB01# |
| | | | | ±5% | GQM2192C2A150JB01# |
| | | | 16pF | ±2% | GQM2192C2A160GB01# |
| | | | | ±5% | GQM2192C2A160JB01# |
| | | | 18pF | ±2% | GQM2192C2A180GB01# |
| | | | | ±5% | GQM2192C2A180JB01# |
| | 50Vdc | C0G | 20pF | ±2% | GQM2195C1H200GB01# |
| | | | | ±5% | GQM2195C1H200JB01# |
| | | | 22pF | ±2% | GQM2195C1H220GB01# |
| | | | | ±5% | GQM2195C1H220JB01# |
| | | | 24pF | ±2% | GQM2195C1H240GB01# |
| | | | | ±5% | GQM2195C1H240JB01# |
| | | | 27pF | ±2% | GQM2195C1H270GB01# |
| | | | | ±5% | GQM2195C1H270JB01# |
| | | | 30pF | ±2% | GQM2195C1H300GB01# |
| | | | | ±5% | GQM2195C1H300JB01# |
| | | | 33pF | ±2% | GQM2195C1H330GB01# |
| | | | | ±5% | GQM2195C1H330JB01# |
| | | | 36pF | ±2% | GQM2195C1H360GB01# |
| | | | | ±5% | GQM2195C1H360JB01# |
| | | | 39pF | ±2% | GQM2195C1H390GB01# |
| | | | | ±5% | GQM2195C1H390JB01# |
| | | | 43pF | ±2% | GQM2195C1H430GB01# |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 50Vdc | C0G | 43pF | ±5% | GQM2195C1H430JB01# |
| | | | 47pF | ±2% | GQM2195C1H470GB01# |
| | | | | ±5% | GQM2195C1H470JB01# |
| | | | 51pF | ±2% | GQM2195C1H510GB01# |
| | | | | ±5% | GQM2195C1H510JB01# |
| | | | 56pF | ±2% | GQM2195C1H560GB01# |
| | | | | ±5% | GQM2195C1H560JB01# |
| | | | 62pF | ±2% | GQM2195C1H620GB01# |
| | | | | ±5% | GQM2195C1H620JB01# |
| | | | 68pF | ±2% | GQM2195C1H680GB01# |
| | | | | ±5% | GQM2195C1H680JB01# |
| | | | 75pF | ±2% | GQM2195C1H750GB01# |
| | | | | ±5% | GQM2195C1H750JB01# |
| | | | 82pF | ±2% | GQM2195C1H820GB01# |
| | | | | ±5% | GQM2195C1H820JB01# |
| | | | 91pF | ±2% | GQM2195C1H910GB01# |
| | | | | ±5% | GQM2195C1H910JB01# |
| | | | 100pF | ±2% | GQM2195C1H101GB01# |
| | | | | ±5% | GQM2195C1H101JB01# |
| | | CH | 20pF | ±2% | GQM2192C1H200GB01# |
| | | | | ±5% | GQM2192C1H200JB01# |
| | | | 22pF | ±2% | GQM2192C1H220GB01# |
| | | | | ±5% | GQM2192C1H220JB01# |
| | | | 24pF | ±2% | GQM2192C1H240GB01# |
| | | | | ±5% | GQM2192C1H240JB01# |
| | | | 27pF | ±2% | GQM2192C1H270GB01# |
| | | | | ±5% | GQM2192C1H270JB01# |
| | | | 30pF | ±2% | GQM2192C1H300GB01# |
| | | | | ±5% | GQM2192C1H300JB01# |
| | | | 33pF | ±2% | GQM2192C1H330GB01# |
| | | | | ±5% | GQM2192C1H330JB01# |
| | | | 36pF | ±2% | GQM2192C1H360GB01# |
| | | | | ±5% | GQM2192C1H360JB01# |
| | | | 39pF | ±2% | GQM2192C1H390GB01# |
| | | | | ±5% | GQM2192C1H390JB01# |
| | | | 43pF | ±2% | GQM2192C1H430GB01# |
| | | | | ±5% | GQM2192C1H430JB01# |
| | | | 47pF | ±2% | GQM2192C1H470GB01# |
| | | | | ±5% | GQM2192C1H470JB01# |
| | | | 51pF | ±2% | GQM2192C1H510GB01# |
| | | | | ±5% | GQM2192C1H510JB01# |
| | | | 56pF | ±2% | GQM2192C1H560GB01# |
| | | | | ±5% | GQM2192C1H560JB01# |
| | | | 62pF | ±2% | GQM2192C1H620GB01# |
| | | | | ±5% | GQM2192C1H620JB01# |
| | | | 68pF | ±2% | GQM2192C1H680GB01# |
| | | | | ±5% | GQM2192C1H680JB01# |
| | | | 75pF | ±2% | GQM2192C1H750GB01# |
| | | | | ±5% | GQM2192C1H750JB01# |
| | | | 82pF | ±2% | GQM2192C1H820GB01# |
| | | | | ±5% | GQM2192C1H820JB01# |
| | | | 91pF | ±2% | GQM2192C1H910GB01# |
| | | | | ±5% | GQM2192C1H910JB01# |
| | | | 100pF | ±2% | GQM2192C1H101GB01# |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 0.95mm | 50Vdc | CH | 100pF | ±5% | **GQM2192C1H101JB01#** |
| 1.0mm | 250Vdc | C0G | 1.0pF | ±0.1pF | **GQM2195C2E1R0BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R0CB12#** |
| | | | 1.1pF | ±0.1pF | **GQM2195C2E1R1BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R1CB12#** |
| | | | 1.2pF | ±0.1pF | **GQM2195C2E1R2BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R2CB12#** |
| | | | 1.3pF | ±0.1pF | **GQM2195C2E1R3BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R3CB12#** |
| | | | 1.5pF | ±0.1pF | **GQM2195C2E1R5BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R5CB12#** |
| | | | 1.6pF | ±0.1pF | **GQM2195C2E1R6BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R6CB12#** |
| | | | 1.8pF | ±0.1pF | **GQM2195C2E1R8BB12#** |
| | | | | ±0.25pF | **GQM2195C2E1R8CB12#** |
| | | | 2.0pF | ±0.1pF | **GQM2195C2E2R0BB12#** |
| | | | | ±0.25pF | **GQM2195C2E2R0CB12#** |
| | | | 2.2pF | ±0.1pF | **GQM2195C2E2R2BB12#** |
| | | | | ±0.25pF | **GQM2195C2E2R2CB12#** |
| | | | 2.4pF | ±0.1pF | **GQM2195C2E2R4BB12#** |
| | | | | ±0.25pF | **GQM2195C2E2R4CB12#** |
| | | | 2.7pF | ±0.1pF | **GQM2195C2E2R7BB12#** |
| | | | | ±0.25pF | **GQM2195C2E2R7CB12#** |
| | | | 3.0pF | ±0.1pF | **GQM2195C2E3R0BB12#** |
| | | | | ±0.25pF | **GQM2195C2E3R0CB12#** |
| | | | 3.3pF | ±0.1pF | **GQM2195C2E3R3BB12#** |
| | | | | ±0.25pF | **GQM2195C2E3R3CB12#** |
| | | | 3.6pF | ±0.1pF | **GQM2195C2E3R6BB12#** |
| | | | | ±0.25pF | **GQM2195C2E3R6CB12#** |
| | | | 3.9pF | ±0.1pF | **GQM2195C2E3R9BB12#** |
| | | | | ±0.25pF | **GQM2195C2E3R9CB12#** |
| | | | 4.0pF | ±0.1pF | **GQM2195C2E4R0BB12#** |
| | | | | ±0.25pF | **GQM2195C2E4R0CB12#** |
| | | | 4.3pF | ±0.1pF | **GQM2195C2E4R3BB12#** |
| | | | | ±0.25pF | **GQM2195C2E4R3CB12#** |
| | | | 4.7pF | ±0.1pF | **GQM2195C2E4R7BB12#** |
| | | | | ±0.25pF | **GQM2195C2E4R7CB12#** |
| | | | 5.0pF | ±0.1pF | **GQM2195C2E5R0BB12#** |
| | | | | ±0.25pF | **GQM2195C2E5R0CB12#** |
| | | | 5.1pF | ±0.25pF | **GQM2195C2E5R1CB12#** |
| | | | | ±0.5pF | **GQM2195C2E5R1DB12#** |
| | | | 5.6pF | ±0.25pF | **GQM2195C2E5R6CB12#** |
| | | | | ±0.5pF | **GQM2195C2E5R6DB12#** |
| | | | 6.0pF | ±0.25pF | **GQM2195C2E6R0CB12#** |
| | | | | ±0.5pF | **GQM2195C2E6R0DB12#** |
| | | | 6.2pF | ±0.25pF | **GQM2195C2E6R2CB12#** |
| | | | | ±0.5pF | **GQM2195C2E6R2DB12#** |
| | | | 6.8pF | ±0.25pF | **GQM2195C2E6R8CB12#** |
| | | | | ±0.5pF | **GQM2195C2E6R8DB12#** |
| | | | 7.0pF | ±0.25pF | **GQM2195C2E7R0CB12#** |
| | | | | ±0.5pF | **GQM2195C2E7R0DB12#** |
| | | | 7.5pF | ±0.25pF | **GQM2195C2E7R5CB12#** |
| | | | | ±0.5pF | **GQM2195C2E7R5DB12#** |
| | | | 8.0pF | ±0.25pF | **GQM2195C2E8R0CB12#** |
| 1.0mm | 250Vdc | C0G | 8.0pF | ±0.5pF | **GQM2195C2E8R0DB12#** |
| | | | 8.2pF | ±0.25pF | **GQM2195C2E8R2CB12#** |
| | | | | ±0.5pF | **GQM2195C2E8R2DB12#** |
| | | | 9.0pF | ±0.25pF | **GQM2195C2E9R0CB12#** |
| | | | | ±0.5pF | **GQM2195C2E9R0DB12#** |
| | | | 9.1pF | ±0.25pF | **GQM2195C2E9R1CB12#** |
| | | | | ±0.5pF | **GQM2195C2E9R1DB12#** |
| | | | 10pF | ±2% | **GQM2195C2E100GB12#** |
| | | | | ±5% | **GQM2195C2E100JB12#** |
| | | | 11pF | ±2% | **GQM2195C2E110GB12#** |
| | | | | ±5% | **GQM2195C2E110JB12#** |
| | | | 12pF | ±2% | **GQM2195C2E120GB12#** |
| | | | | ±5% | **GQM2195C2E120JB12#** |
| | | | 13pF | ±2% | **GQM2195C2E130GB12#** |
| | | | | ±5% | **GQM2195C2E130JB12#** |
| | | | 15pF | ±2% | **GQM2195C2E150GB12#** |
| | | | | ±5% | **GQM2195C2E150JB12#** |
| | | | 16pF | ±2% | **GQM2195C2E160GB12#** |
| | | | | ±5% | **GQM2195C2E160JB12#** |
| | | | 18pF | ±2% | **GQM2195C2E180GB12#** |
| | | | | ±5% | **GQM2195C2E180JB12#** |
| | | | 20pF | ±2% | **GQM2195C2E200GB12#** |
| | | | | ±5% | **GQM2195C2E200JB12#** |
| | | | 22pF | ±2% | **GQM2195C2E220GB12#** |
| | | | | ±5% | **GQM2195C2E220JB12#** |
| | | | 24pF | ±2% | **GQM2195C2E240GB12#** |
| | | | | ±5% | **GQM2195C2E240JB12#** |
| | | | 27pF | ±2% | **GQM2195C2E270GB12#** |
| | | | | ±5% | **GQM2195C2E270JB12#** |
| | | | 30pF | ±2% | **GQM2195C2E300GB12#** |
| | | | | ±5% | **GQM2195C2E300JB12#** |
| | | | 33pF | ±2% | **GQM2195C2E330GB12#** |
| | | | | ±5% | **GQM2195C2E330JB12#** |
| | | | 36pF | ±2% | **GQM2195C2E360GB12#** |
| | | | | ±5% | **GQM2195C2E360JB12#** |
| | | | 39pF | ±2% | **GQM2195C2E390GB12#** |
| | | | | ±5% | **GQM2195C2E390JB12#** |
| | | | 43pF | ±2% | **GQM2195C2E430GB12#** |
| | | | | ±5% | **GQM2195C2E430JB12#** |
| | | | 47pF | ±2% | **GQM2195C2E470GB12#** |
| | | | | ±5% | **GQM2195C2E470JB12#** |
| | | | 51pF | ±2% | **GQM2195C2E510GB12#** |
| | | | | ±5% | **GQM2195C2E510JB12#** |
| | | | 56pF | ±2% | **GQM2195C2E560GB12#** |
| | | | | ±5% | **GQM2195C2E560JB12#** |
| | | | 62pF | ±2% | **GQM2195C2E620GB12#** |
| | | | | ±5% | **GQM2195C2E620JB12#** |
| | | | 68pF | ±2% | **GQM2195C2E680GB12#** |
| | | | | ±5% | **GQM2195C2E680JB12#** |
| | | | 75pF | ±2% | **GQM2195C2E750GB12#** |
| | | | | ±5% | **GQM2195C2E750JB12#** |
| | | | 82pF | ±2% | **GQM2195C2E820GB12#** |
| | | | | ±5% | **GQM2195C2E820JB12#** |
| | | | 91pF | ±2% | **GQM2195C2E910GB12#** |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 250Vdc | C0G | 91pF | ±5% | **GQM2195C2E910JB12#** |
| | | | 100pF | ±2% | **GQM2195C2E101GB12#** |
| | | | | ±5% | **GQM2195C2E101JB12#** |

## ■ 2.8×2.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.35mm | 500Vdc | C0G | 1.0pF | ±0.1pF | **GQM22M5C2H1R0BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R0CB01#** |
| | | | 1.1pF | ±0.1pF | **GQM22M5C2H1R1BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R1CB01#** |
| | | | 1.2pF | ±0.1pF | **GQM22M5C2H1R2BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R2CB01#** |
| | | | 1.3pF | ±0.1pF | **GQM22M5C2H1R3BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R3CB01#** |
| | | | 1.5pF | ±0.1pF | **GQM22M5C2H1R5BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R5CB01#** |
| | | | 1.6pF | ±0.1pF | **GQM22M5C2H1R6BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R6CB01#** |
| | | | 1.8pF | ±0.1pF | **GQM22M5C2H1R8BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H1R8CB01#** |
| | | | 2.0pF | ±0.1pF | **GQM22M5C2H2R0BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H2R0CB01#** |
| | | | 2.2pF | ±0.1pF | **GQM22M5C2H2R2BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H2R2CB01#** |
| | | | 2.4pF | ±0.1pF | **GQM22M5C2H2R4BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H2R4CB01#** |
| | | | 2.7pF | ±0.1pF | **GQM22M5C2H2R7BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H2R7CB01#** |
| | | | 3.0pF | ±0.1pF | **GQM22M5C2H3R0BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H3R0CB01#** |
| | | | 3.3pF | ±0.1pF | **GQM22M5C2H3R3BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H3R3CB01#** |
| | | | 3.6pF | ±0.1pF | **GQM22M5C2H3R6BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H3R6CB01#** |
| | | | 3.9pF | ±0.1pF | **GQM22M5C2H3R9BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H3R9CB01#** |
| | | | 4.0pF | ±0.1pF | **GQM22M5C2H4R0BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H4R0CB01#** |
| | | | 4.3pF | ±0.1pF | **GQM22M5C2H4R3BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H4R3CB01#** |
| | | | 4.7pF | ±0.1pF | **GQM22M5C2H4R7BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H4R7CB01#** |
| | | | 5.0pF | ±0.1pF | **GQM22M5C2H5R0BB01#** |
| | | | | ±0.25pF | **GQM22M5C2H5R0CB01#** |
| | | | 5.1pF | ±0.25pF | **GQM22M5C2H5R1CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H5R1DB01#** |
| | | | 5.6pF | ±0.25pF | **GQM22M5C2H5R6CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H5R6DB01#** |
| | | | 6.0pF | ±0.25pF | **GQM22M5C2H6R0CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H6R0DB01#** |
| | | | 6.2pF | ±0.25pF | **GQM22M5C2H6R2CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H6R2DB01#** |
| 1.35mm | 500Vdc | C0G | 6.8pF | ±0.25pF | **GQM22M5C2H6R8CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H6R8DB01#** |
| | | | 7.0pF | ±0.25pF | **GQM22M5C2H7R0CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H7R0DB01#** |
| | | | 7.5pF | ±0.25pF | **GQM22M5C2H7R5CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H7R5DB01#** |
| | | | 8.0pF | ±0.25pF | **GQM22M5C2H8R0CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H8R0DB01#** |
| | | | 8.2pF | ±0.25pF | **GQM22M5C2H8R2CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H8R2DB01#** |
| | | | 9.0pF | ±0.25pF | **GQM22M5C2H9R0CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H9R0DB01#** |
| | | | 9.1pF | ±0.25pF | **GQM22M5C2H9R1CB01#** |
| | | | | ±0.5pF | **GQM22M5C2H9R1DB01#** |
| | | | 10pF | ±2% | **GQM22M5C2H100GB01#** |
| | | | | ±5% | **GQM22M5C2H100JB01#** |
| | | | 11pF | ±2% | **GQM22M5C2H110GB01#** |
| | | | | ±5% | **GQM22M5C2H110JB01#** |
| | | | 12pF | ±2% | **GQM22M5C2H120GB01#** |
| | | | | ±5% | **GQM22M5C2H120JB01#** |
| | | | 13pF | ±2% | **GQM22M5C2H130GB01#** |
| | | | | ±5% | **GQM22M5C2H130JB01#** |
| | | | 15pF | ±2% | **GQM22M5C2H150GB01#** |
| | | | | ±5% | **GQM22M5C2H150JB01#** |
| | | | 16pF | ±2% | **GQM22M5C2H160GB01#** |
| | | | | ±5% | **GQM22M5C2H160JB01#** |
| | | | 18pF | ±2% | **GQM22M5C2H180GB01#** |
| | | | | ±5% | **GQM22M5C2H180JB01#** |
| | | | 20pF | ±2% | **GQM22M5C2H200GB01#** |
| | | | | ±5% | **GQM22M5C2H200JB01#** |
| | | | 22pF | ±2% | **GQM22M5C2H220GB01#** |
| | | | | ±5% | **GQM22M5C2H220JB01#** |
| | | | 24pF | ±2% | **GQM22M5C2H240GB01#** |
| | | | | ±5% | **GQM22M5C2H240JB01#** |
| | | | 27pF | ±2% | **GQM22M5C2H270GB01#** |
| | | | | ±5% | **GQM22M5C2H270JB01#** |
| | | | 30pF | ±2% | **GQM22M5C2H300GB01#** |
| | | | | ±5% | **GQM22M5C2H300JB01#** |
| | | | 33pF | ±2% | **GQM22M5C2H330GB01#** |
| | | | | ±5% | **GQM22M5C2H330JB01#** |
| | | | 36pF | ±2% | **GQM22M5C2H360GB01#** |
| | | | | ±5% | **GQM22M5C2H360JB01#** |
| | | | 39pF | ±2% | **GQM22M5C2H390GB01#** |
| | | | | ±5% | **GQM22M5C2H390JB01#** |
| | | | 43pF | ±2% | **GQM22M5C2H430GB01#** |
| | | | | ±5% | **GQM22M5C2H430JB01#** |
| | | | 47pF | ±2% | **GQM22M5C2H470GB01#** |
| | | | | ±5% | **GQM22M5C2H470JB01#** |
| | | | 51pF | ±2% | **GQM22M5C2H510GB01#** |
| | | | | ±5% | **GQM22M5C2H510JB01#** |
| | | | 56pF | ±2% | **GQM22M5C2H560GB01#** |
| | | | | ±5% | **GQM22M5C2H560JB01#** |
| | | | 62pF | ±2% | **GQM22M5C2H620GB01#** |
| | | | | ±5% | **GQM22M5C2H620JB01#** |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.8×2.8mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.35mm | 500Vdc | C0G | 68pF | ±2% | **GQM22M5C2H680GB01#** | |
| | | | | ±5% | **GQM22M5C2H680JB01#** | |
| | | | 75pF | ±2% | **GQM22M5C2H750GB01#** | |
| | | | | ±5% | **GQM22M5C2H750JB01#** | |
| | | | 82pF | ±2% | **GQM22M5C2H820GB01#** | |
| | | | | ±5% | **GQM22M5C2H820JB01#** | |
| | | | 91pF | ±2% | **GQM22M5C2H910GB01#** | |
| | | | | ±5% | **GQM22M5C2H910JB01#** | |
| | | | 100pF | ±2% | **GQM22M5C2H101GB01#** | |
| | | | | ±5% | **GQM22M5C2H101JB01#** | |

Part number # indicates the package specification code.

Resin External Electrode Type

# GRJ Series

Deflecting crack

**The resin external electrodes prevent the occurrence of cracking caused by deflection stress after board mounting!**

## Features

### ① The resin external electrodes suppress cracks by board deflection.

Cracking of the ceramic element is suppressed by the resin of the external electrodes, which releases the stress.




Resin electrodes relieve the stress

<Example of Structure>

●General Purpose Product (GRM Series)



Occurrence of cracking on edge of terminal electrode

●Resin External Electrode Type (GRJ Series)



**Conductive resin layer relieves the mechanical stress of the ceramic**

Separated foundation electrode and resin electrode

### ② Suppresses the occurrence of cracking caused by deflection stress at the time of board mounting, etc.







Due to the specification of the measuring instrument, measurements can be performed up to 8mm.

### ③ Ideal for consumer and industrial electronic equipment, etc. where there heat stress, vibration and impact are applied.

## Specifications

| | |
|---|---|
| Size | 2.0×1.25mm to 5.7×5.0mm |
| Rated Voltage | DC250V to 1kV |
| Capacitance | 470pF to 1.0μF |
| Main Applications | Consumer & Industrial Electronic Equipment |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GRJ Series High Dielectric Constant Type Deflecting crack Part Number List

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.0mm | 250Vdc | X7R | 1000pF | ±10% | **GRJ21AR72E102KWJ1#** | |
| | | | 1500pF | ±10% | **GRJ21AR72E152KWJ1#** | |
| | | | 2200pF | ±10% | **GRJ21AR72E222KWJ1#** | |
| | | | 3300pF | ±10% | **GRJ21AR72E332KWJ1#** | |
| | | | 4700pF | ±10% | **GRJ21AR72E472KWJ1#** | |
| | | | 6800pF | ±10% | **GRJ21AR72E682KWJ1#** | |
| 1.45mm | 250Vdc | X7R | 10000pF | ±10% | **GRJ21BR72E103KWJ3#** | |
| | | | 15000pF | ±10% | **GRJ21BR72E153KWJ3#** | |
| | | | 22000pF | ±10% | **GRJ21BR72E223KWJ3#** | |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.25mm | 1000Vdc | X7R | 470pF | ±10% | **GRJ31BR73A471KWJ1#** | |
| | | | 680pF | ±10% | **GRJ31BR73A681KWJ1#** | |
| | | | 1000pF | ±10% | **GRJ31BR73A102KWJ1#** | |
| | | | 1500pF | ±10% | **GRJ31BR73A152KWJ1#** | |
| | | | 2200pF | ±10% | **GRJ31BR73A222KWJ1#** | |
| | | | 3300pF | ±10% | **GRJ31BR73A332KWJ1#** | |
| | | | 4700pF | ±10% | **GRJ31BR73A472KWJ1#** | |
| | 630Vdc | X7R | 1000pF | ±10% | **GRJ31BR72J102KWJ1#** | |
| | | | 1500pF | ±10% | **GRJ31BR72J152KWJ1#** | |
| | | | 2200pF | ±10% | **GRJ31BR72J222KWJ1#** | |
| | | | 3300pF | ±10% | **GRJ31BR72J332KWJ1#** | |
| | | | 4700pF | ±10% | **GRJ31BR72J472KWJ1#** | |
| | | | 6800pF | ±10% | **GRJ31BR72J682KWJ1#** | |
| | | | 10000pF | ±10% | **GRJ31BR72J103KWJ1#** | |
| | 250Vdc | X7R | 15000pF | ±10% | **GRJ31BR72E153KWJ1#** | |
| | | | 22000pF | ±10% | **GRJ31BR72E223KWJ1#** | |
| | | | 68000pF | ±10% | **GRJ31BR72E683KWJ1#** | |
| 1.8mm | 1000Vdc | X7R | 6800pF | ±10% | **GRJ31CR73A682KWJ3#** | |
| | | | 10000pF | ±10% | **GRJ31CR73A103KWJ3#** | |
| | 630Vdc | X7R | 15000pF | ±10% | **GRJ31CR72J153KWJ3#** | |
| | | | 22000pF | ±10% | **GRJ31CR72J223KWJ3#** | |
| | 250Vdc | X7R | 33000pF | ±10% | **GRJ31CR72E333KWJ3#** | |
| | | | 47000pF | ±10% | **GRJ31CR72E473KWJ3#** | |
| | | | 0.10μF | ±10% | **GRJ31CR72E104KWJ3#** | |

## ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.5mm | 1000Vdc | X7R | 6800pF | ±10% | **GRJ32QR73A682KWJ1#** | |
| | | | 10000pF | ±10% | **GRJ32QR73A103KWJ1#** | |
| | 630Vdc | X7R | 22000pF | ±10% | **GRJ32QR72J223KWJ1#** | |
| | 250Vdc | X7R | 68000pF | ±10% | **GRJ32QR72E683KWJ1#** | |
| | | | 0.15μF | ±10% | **GRJ32QR72E154KWJ1#** | |
| 2.0mm | 1000Vdc | X7R | 15000pF | ±10% | **GRJ32DR73A153KWJ1#** | |
| | | | 22000pF | ±10% | **GRJ32DR73A223KWJ1#** | |
| | 630Vdc | X7R | 33000pF | ±10% | **GRJ32DR72J333KWJ1#** | |
| | | | 47000pF | ±10% | **GRJ32DR72J473KWJ1#** | |
| 2.0mm | 250Vdc | X7R | 0.10μF | ±10% | **GRJ32DR72E104KWJ1#** | |
| | | | 0.22μF | ±10% | **GRJ32DR72E224KWJ1#** | |

## ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.5mm | 630Vdc | X7R | 68000pF | ±10% | **GRJ43QR72J683KWJ1#** | |
| | 250Vdc | X7R | 0.15μF | ±10% | **GRJ43QR72E154KWJ1#** | |
| 2.0mm | 1000Vdc | X7R | 33000pF | ±10% | **GRJ43DR73A333KWJ1#** | |
| | | | 47000pF | ±10% | **GRJ43DR73A473KWJ1#** | |
| | 630Vdc | X7R | 0.10μF | ±10% | **GRJ43DR72J104KWJ1#** | |
| | 250Vdc | X7R | 0.22μF | ±10% | **GRJ43DR72E224KWJ1#** | |
| | | | 0.33μF | ±10% | **GRJ43DR72E334KWJ1#** | |
| | | | 0.47μF | ±10% | **GRJ43DR72E474KWJ1#** | |

## ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.0mm | 1000Vdc | X7R | 68000pF | ±10% | **GRJ55DR73A683KWJ1#** | |
| | | | 0.10μF | ±10% | **GRJ55DR73A104KWJ1#** | |
| | 630Vdc | X7R | 0.15μF | ±10% | **GRJ55DR72J154KWJ1#** | |
| | | | 0.22μF | ±10% | **GRJ55DR72J224KWJ1#** | |
| | 250Vdc | X7R | 0.33μF | ±10% | **GRJ55DR72E334KWJ1#** | |
| | | | 0.47μF | ±10% | **GRJ55DR72E474KWJ1#** | |
| | | | 0.68μF | ±10% | **GRJ55DR72E684KWJ1#** | |
| | | | 1.0μF | ±10% | **GRJ55DR72E105KWJ1#** | |

Part number # indicates the package specification code.

High Effective Capacitance & High Allowable Ripple Current

# GR3 Series

Anti-noise

**This is a general purpose high ripple resistance product excellent in DC bias characteristics.**

## Features

### ① When a DC bias is applied, a capacitance higher than conventional products (X7R characteristics) can be acquired.

About twice the capacitance can be secured when DC200V is applied.




<Comparison between Capacitance - DC Bias Characteristics>

### ② Improved ripple resistance performance compared to conventional products (X7R characteristics).

In the case of a product with a capacitance of 1μF, when the exothermic temperature reaches 20°C at frequency f=300kHz, the amount of resistance of a product with conventional material is 2.9Ar.m.s.; however, the new material is 4.7Ar.m.s..




<Comparison of Ripple Heat Generation Characteristics>

### ③ This product has a noise reduction effect.

Since dielectric materials which enable a reduction of noise are used, this product is more effective for reducing noise compared to the general purpose GRM series.




## Specifications

| | |
|---|---|
| Size | 2.0×1.25mm to 5.7×5.0mm |
| Rated Voltage | DC250V to 630V |
| Capacitance | 0.01μF to 1.0μF |
| Main Applications | For PFC (Power Factor Correction) Circuits of Power Supplies, EMI Suppression and Smoothing Circuits |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# GR3 Series High Dielectric Constant Type Anti-noise Part Number List

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 250Vdc | X7T | 10000pF | ±10% | **GR321AD72E103KW01#** |
| | | | 15000pF | ±10% | **GR321AD72E153KW01#** |
| 1.45mm | 250Vdc | X7T | 22000pF | ±10% | **GR321BD72E223KW03#** |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.0mm | 450Vdc | X7T | 10000pF | ±10% | **GR331AD72W103KW01#** |
| | | | 15000pF | ±10% | **GR331AD72W153KW01#** |
| | 250Vdc | X7T | 33000pF | ±10% | **GR331AD72E333KW01#** |
| 1.25mm | 630Vdc | X7T | 10000pF | ±10% | **GR331BD72J103KW01#** |
| | 450Vdc | X7T | 22000pF | ±10% | **GR331BD72W223KW01#** |
| | | | 33000pF | ±10% | **GR331BD72W333KW01#** |
| | 250Vdc | X7T | 47000pF | ±10% | **GR331BD72E473KW01#** |
| 1.8mm | 630Vdc | X7T | 15000pF | ±10% | **GR331CD72J153KW03#** |
| | 450Vdc | X7T | 47000pF | ±10% | **GR331CD72W473KW03#** |
| | 250Vdc | X7T | 68000pF | ±10% | **GR331CD72E683KW03#** |

## ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.5mm | 630Vdc | X7T | 22000pF | ±10% | **GR332QD72J223KW01#** |
| | 250Vdc | X7T | 0.10μF | ±10% | **GR332QD72E104KW01#** |
| 2.0mm | 630Vdc | X7T | 33000pF | ±10% | **GR332DD72J333KW01#** |
| | | | 47000pF | ±10% | **GR332DD72J473KW01#** |
| | 450Vdc | X7T | 68000pF | ±10% | **GR332DD72W683KW01#** |
| | | | 0.10μF | ±10% | **GR332DD72W104KW01#** |
| | 250Vdc | X7T | 0.15μF | ±10% | **GR332DD72E154KW01#** |

## ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 1.5mm | 250Vdc | X7T | 0.22μF | ±10% | **GR343QD72E224KW01#** |
| 2.0mm | 630Vdc | X7T | 68000pF | ±10% | **GR343DD72J683KW01#** |
| | 450Vdc | X7T | 0.15μF | ±10% | **GR343DD72W154KW01#** |
| | 250Vdc | X7T | 0.33μF | ±10% | **GR343DD72E334KW01#** |

## ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number |
|---|---|---|---|---|---|
| 2.0mm | 630Vdc | X7T | 0.10μF | ±10% | **GR355DD72J104KW01#** |
| | | | 0.15μF | ±10% | **GR355DD72J154KW01#** |
| | 450Vdc | X7T | 0.22μF | ±10% | **GR355DD72W224KW01#** |
| | | | 0.33μF | ±10% | **GR355DD72W334KW01#** |
| | | | 0.47μF | ±10% | **GR355DD72W474KW01#** |
| | 250Vdc | X7T | 0.47μF | ±10% | **GR355DD72E474KW01#** |
| | | | 0.68μF | ±10% | **GR355DD72E684KW01#** |
| 2.7mm | 630Vdc | X7T | 0.22μF | ±10% | **GR355XD72J224KW05#** |
| | | | 0.27μF | ±10% | **GR355XD72J274KW05#** |
| | 450Vdc | X7T | 0.56μF | ±10% | **GR355XD72W564KW05#** |
| | 250Vdc | X7T | 1.0μF | ±10% | **GR355XD72E105KW05#** |

Part number # indicates the package specification code.

Metal Terminal Type For General Purpose

# KRM Series

Anti-noise | Deflecting crack | Soldering crack

## Bonding the metal terminals to external electrodes solves design issues by mounting large size MLCC!

## Features

### ① Bond metal terminals to the external electrodes of chips.

The stress applied to the chip is relieved by the elastic action of the metal terminal.




### ② Substantially reduces noise, board deflection cracks and soldering cracks.

This product is not damaged even with a board deflection of 6 mm.
Solder cracks do not occur even with 2,000 cycles of heat stress.

**●Acoustic Noise is Reduced with Metal Terminals**




**●Reduces Stress Caused by Board Deflection**




**●Suppresses Solder Cracks Caused by Heat Stress**

| Chip Size | Chip Only (5750 (in mm)/2220 (in inch) size) | Metal Terminal Type (5750 (in mm)/2220 (in inch) size) |
|---|---|---|
| 1000 Cycle |   | |
| 2000 Cycle |   |  |

Compared with chips only, this product is excellent in solder cracking resistance.

Test Condition: -55 to +125°C, 5min.,(Tank)
Board Used: Glass Epoxy Board (FR-4)

Demonstrates replacement value of low noise capacitors Experience the effectiveness of the KRM Series.

‣ Examples of Noise Countermeasures

### ③ 2 chips can be stacked.

Realize large capacity by stacking 2 capacitors.

## Specifications

| | |
|---|---|
| Size | 2.2×1.25mm to 6.1×5.3mm |
| Rated Voltage | DC16V to 1kV |
| Capacitance | 0.068μF to 47μF |
| Main Applications | For smoothing and noise suppression of DC-DC converters |

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.




<Dimensions>

# KRM Series High Dielectric Constant Type Anti-noise Deflecting crack Soldering crack Part Number List

## ■ 2.2×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 1.9mm | 25Vdc | X5R | 10μF | ±10% | **KRM21ER61E106KHA1#** | |
| | 16Vdc | X5R | 10μF | ±10% | **KRM21ER61C106KHA1#** | |

## ■ 3.5×1.7mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.0mm | 25Vdc | X5R | 10μF | ±10% | **KRM31FR61E106KH01#** | |
| 2.9mm | 100Vdc | X7R | 1.0μF | ±10% | **KRM31KR72A105KH01#** | |
| | 50Vdc | X7R | 4.7μF | ±10% | **KRM31KR71H475KH01#** | |
| | 35Vdc | X6S | 10μF | ±10% | **KRM31KC8YA106KH01#** | |
| | 25Vdc | X6S | 10μF | ±10% | **KRM31KC81E106KH01#** | |

## ■ 3.6×1.7mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.9mm | 50Vdc | X7R | 2.2μF | ±10% | **KRM31KR71H225KH01#** | |

## ■ 3.7×1.85mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 2.9mm | 100Vdc | X7R | 2.2μF | ±10% | **KRM31KR72A225KH01#** | |

## ■ 6.1×5.3mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 3.0mm | 1000Vdc | X7R | 68000pF | ±10% | **KRM55LR73A683KH01#** | |
| | | | 0.10μF | ±10% | **KRM55LR73A104KH01#** | |
| | 630Vdc | X7R | 0.15μF | ±10% | **KRM55LR72J154KH01#** | |
| | | | 0.22μF | ±10% | **KRM55LR72J224KH01#** | |
| | 250Vdc | X7R | 0.68μF | ±10% | **KRM55LR72E684KH01#** | |
| | | | 1.0μF | ±10% | **KRM55LR72E105KH01#** | |
| | 100Vdc | X7R | 4.7μF | ±10% | **KRM55LR72A475KH01#** | |
| | 63Vdc | X7R | 4.7μF | ±10% | **KRM55LR71J475KH01#** | |
| | 50Vdc | X7R | 4.7μF | ±10% | **KRM55LR71H475KH01#** | |
| | 35Vdc | X7R | 10μF | ±10% | **KRM55LR7YA106KH01#** | |
| | 25Vdc | X7R | 15μF | ±10% | **KRM55LR71E156KH01#** | |
| 3.9mm | 100Vdc | X7R | 6.8μF | ±10% | **KRM55QR72A685KH01#** | |
| | 63Vdc | X7R | 10μF | ±10% | **KRM55QR71J106KH01#** | |
| | 50Vdc | X7R | 10μF | ±10% | **KRM55QR71H106KH01#** | |
| | 35Vdc | X7R | 17μF | ±10% | **KRM55QR7YA176KH01#** | |
| | 25Vdc | X7R | 22μF | ±10% | **KRM55QR71E226KH01#** | |
| 5.0mm | 1000Vdc | X7R | 0.15μF | ±20% | **KRM55TR73A154MH01#** | |
| | | | 0.22μF | ±20% | **KRM55TR73A224MH01#** | |
| | 630Vdc | X7R | 0.33μF | ±20% | **KRM55TR72J334MH01#** | |
| | | | 0.47μF | ±20% | **KRM55TR72J474MH01#** | |
| | 250Vdc | X7R | 1.5μF | ±20% | **KRM55TR72E155MH01#** | |
| | | | 2.2μF | ±20% | **KRM55TR72E225MH01#** | |
| | 100Vdc | X7R | 10μF | ±20% | **KRM55TR72A106MH01#** | |
| 5.0mm | 35Vdc | X7R | 22μF | ±20% | **KRM55TR7YA226MH01#** | |
| | 25Vdc | X7R | 33μF | ±20% | **KRM55TR71E336MH01#** | |
| 6.7mm | 100Vdc | X7R | 15μF | ±20% | **KRM55WR72A156MH01#** | |
| | 63Vdc | X7R | 22μF | ±20% | **KRM55WR71J226MH01#** | |
| | 50Vdc | X7R | 22μF | ±20% | **KRM55WR71H226MH01#** | |
| | 35Vdc | X7R | 33μF | ±20% | **KRM55WR7YA336MH01#** | |
| | 25Vdc | X7R | 47μF | ±20% | **KRM55WR71E476MH01#** | |

Part number # indicates the package specification code.

Metal Terminal Type High Effective Capacitance & High Allowable Ripple Current

# KR3 Series

Anti-noise | Deflecting crack | Soldering crack

## Bonding the metal terminals to external electrodes solves design issues by mounting large size MLCC!

## Features

### 1 Bond metal terminals to the external electrodes of chips.

The stress applied to the chip is relieved by the elastic action of the metal terminal.




### 2 Substantially reduces noise, board deflection cracks and soldering cracks.

This product is not damaged even with a board deflection of 6 mm.
Solder cracks do not occur even with 2,000 cycles of heat stress.

**●Comparison of Noise Reduction Effects**




Evaluation Items: 5750 (in mm)/2220 (in inch) size/DC630V/220nF
Test Method: DC50V, AC10Vp-p/3kHz
Test Board: Glass Epoxy Board (T: 1.6mm)
Test Quantity: 3pc
Distance Between Microphone and Board: 3mm

Note: Results Using Murata's Evaluation Board

**●Reduces Stress Caused by Board Deflection**




**●Suppresses Solder Cracks Caused by Heat Stress**

| Chip Size | Chip Only (5750 (in mm)/2220 (in inch) size) | Metal Terminal Type (5750 (in mm)/2220 (in inch) size) |
|---|---|---|
| 1000 Cycle |  ⇧Solder Crack | |
| 2000 Cycle | ⇧Solder Crack |  |

Compared with chips only, this product is excellent in solder cracking resistance.

Test Condition: -55 to +125°C, 5min.,(Tank)
Board Used: Glass Epoxy Board (FR-4)

## ③ Adopted Low Dielectric Constant Materials

Improved effective capacity and ripple resistant performance, compared to conventional products (X7R characteristics).




## Specifications

| | |
|---|---|
| Size | 6.1×5.3mm |
| Rated Voltage | DC250V to 630V |
| Capacitance | 0.1μF to 2.2μF |
| Main Applications | For DC-DC converters of general electronic equipment |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# KR3 Series High Dielectric Constant Type Anti-noise Deflecting crack Soldering crack Part Number List

## ■ 6.1×5.3mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 3.0mm | 630Vdc | X7T | 0.10μF | ±10% | **KR355LD72J104KH01#** | |
| | | | 0.15μF | ±10% | **KR355LD72J154KH01#** | |
| | 450Vdc | X7T | 0.22μF | ±10% | **KR355LD72W224KH01#** | |
| | | | 0.33μF | ±10% | **KR355LD72W334KH01#** | |
| | | | 0.47μF | ±10% | **KR355LD72W474KH01#** | |
| | 250Vdc | X7T | 0.47μF | ±10% | **KR355LD72E474KH01#** | |
| | | | 0.68μF | ±10% | **KR355LD72E684KH01#** | |
| 3.9mm | 630Vdc | X7T | 0.22μF | ±10% | **KR355QD72J224KH01#** | |
| | | | 0.27μF | ±10% | **KR355QD72J274KH01#** | |
| | 450Vdc | X7T | 0.56μF | ±10% | **KR355QD72W564KH01#** | |
| | 250Vdc | X7T | 1.0μF | ±10% | **KR355QD72E105KH01#** | |
| 5.0mm | 450Vdc | X7T | 0.68μF | ±20% | **KR355TD72W684MH01#** | |
| | | | 1.0μF | ±20% | **KR355TD72W105MH01#** | |
| | 250Vdc | X7T | 1.5μF | ±20% | **KR355TD72E155MH01#** | |
| 6.7mm | 630Vdc | X7T | 0.47μF | ±20% | **KR355WD72J474MH01#** | |
| | | | 0.56μF | ±20% | **KR355WD72J564MH01#** | |
| | 450Vdc | X7T | 1.2μF | ±20% | **KR355WD72W125MH01#** | |
| | 250Vdc | X7T | 2.2μF | ±20% | **KR355WD72E225MH01#** | |

Part number # indicates the package specification code.

8-Terminal Low ESL Type

# LLA Series

Low ESL

## 8-Terminal Type Low ESL Capacitor Ideal for Power Supply Decoupling of High-speed Operation IC

## Features

### ① Ultra-low ESL

Since the equivalent series inductance (ESL) is very low with excellent high frequency characteristics due to the design structure, this capacitor is ideal for power supply decoupling of high-speed operation IC.




<Example of Structure>




<Effectiveness of Cancelling Out Inductance by Mutual Inductance>




<Effectiveness of Suppressing Inductance when Mounting a Multi-terminal Capacitor>

**The inductance for the boards also becomes lower, not only the capacitor.**

### ② A maximum operating temperature up to 125ºC.

This product is applicable to high temperatures (X7* characteristics); however, Murata also offers numerous thin type products, which are ideal as decoupling capacitors on IC package.

## Specifications

| | |
|---|---|
| Size | 1.6×0.8mm to 3.2×1.6mm |
| Rated Voltage | DC4V to 25V |
| Capacitance | 0.01µF to 4.7µF |
| Main Applications | Application processor/CPU/GPU |

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.




<Dimensions>

# LLA Series High Dielectric Constant Type Low ESL Part Number List

## ■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 4Vdc | X7S | 0.10μF | ±20% | **LLA185C70G104MA01#** | |
| | | | 0.22μF | ±20% | **LLA185C70G224MA01#** | |
| | | | 0.47μF | ±20% | **LLA185C70G474MA01#** | |
| | | | 2.2μF | ±20% | **LLA185C70G225ME16#** | |

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 25Vdc | X7R | 10000pF | ±20% | **LLA215R71E103MA14#** | |
| | | | 22000pF | ±20% | **LLA215R71E223MA14#** | |
| | 16Vdc | X7R | 47000pF | ±20% | **LLA215R71C473MA14#** | |
| | | | 0.10μF | ±20% | **LLA215R71C104MA14#** | |
| | 10Vdc | X7R | 0.22μF | ±20% | **LLA215R71A224MA14#** | |
| | 6.3Vdc | X7R | 0.47μF | ±20% | **LLA215R70J474MA14#** | |
| | 4Vdc | X7S | 1.0μF | ±20% | **LLA215C70G105MA14#** | |
| | | | 4.7μF | ±20% | **LLA215C70G475ME19#** | |
| 0.95mm | 25Vdc | X7R | 10000pF | ±20% | **LLA219R71E103MA01#** | |
| | | | 22000pF | ±20% | **LLA219R71E223MA01#** | |
| | | | 47000pF | ±20% | **LLA219R71E473MA01#** | |
| | 16Vdc | X7R | 0.10μF | ±20% | **LLA219R71C104MA01#** | |
| | | | 0.22μF | ±20% | **LLA219R71C224MA01#** | |
| | 10Vdc | X7R | 0.47μF | ±20% | **LLA219R71A474MA01#** | |
| | 6.3Vdc | X7R | 1.0μF | ±20% | **LLA219R70J105MA01#** | |
| | 4Vdc | X7S | 2.2μF | ±20% | **LLA219C70G225MA01#** | |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 16Vdc | X7R | 0.22μF | ±20% | **LLA315R71C224MA14#** | |
| | 10Vdc | X7R | 0.47μF | ±20% | **LLA315R71A474MA14#** | |
| | 6.3Vdc | X7R | 1.0μF | ±20% | **LLA315R70J105MA14#** | |
| | | | 2.2μF | ±20% | **LLA315R70J225MA14#** | |
| 0.95mm | 16Vdc | X7R | 0.47μF | ±20% | **LLA319R71C474MA01#** | |
| | 10Vdc | X7R | 1.0μF | ±20% | **LLA319R71A105MA01#** | |
| 1.25mm | 16Vdc | X7R | 1.0μF | ±20% | **LLA31MR71C105MA01#** | |
| | 10Vdc | X7R | 2.2μF | ±20% | **LLA31MR71A225MA01#** | |

Part number # indicates the package specification code.

LW Reversed Low ESL Type

# LLL Series

Low ESL

**This low ESL capacitor is ideal for power supply decoupling of high-speed operation electronic equipment.**

## Features

### ① Low ESL

Since the equivalent series inductance (ESL) is low and excellent in high frequency characteristics, this capacitor is suitable for power supply decoupling of high-speed operation electronic equipment.




<Example of Structure>

### ② Contributes to a reduction in the number of components.

The number of components can be reduced by using low ESL capacitors, while maintaining functions equivalent to general purpose capacitors (GRM Series).

Murata proposes the use of the LLL series to reduce the number of components and high costs. Simulation is also possible. ▸Proposal for Cost Reductions




### ③ A maximum operating temperature up to 125ºC.

We also offer an abundant lineup of X7* characteristics that can be used in high temperature locations, such as IC packages.

## Specifications

| | |
|---|---|
| Size | 0.5×1.0mm to 1.6×3.2mm |
| Rated Voltage | DC2.5V to 50V |
| Capacitance | 2,200pF to 10µF |
| Main Applications | Application processor/CPU/GPU |




<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# LLL Series High Dielectric Constant Type Low ESL Part Number List

## ■ 0.5×1.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.35mm | 6.3Vdc | X6S | 0.10μF | ±20% | **LLL153C80J104ME01#** | |
| | | | 0.22μF | ±20% | **LLL153C80J224ME14#** | |
| | 4Vdc | X7S | 0.47μF | ±20% | **LLL153C70G474ME17#** | |
| | | X6S | 1.0μF | ±20% | **LLL153C80G105ME21#** | |

## ■ 0.6×1.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.45mm | 4Vdc | X5R | 4.3μF | ±20% | **LLL1U4R60G435ME22#** | |

## ■ 0.8×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.5mm | 25Vdc | X7R | 10000pF | ±20% | **LLL185R71E103MA11#** | |
| | 16Vdc | X7R | 22000pF | ±20% | **LLL185R71C223MA11#** | |
| | | | 47000pF | ±20% | **LLL185R71C473MA11#** | |
| | 10Vdc | X7R | 0.10μF | ±20% | **LLL185R71A104MA11#** | |
| | 4Vdc | X7S | 0.22μF | ±20% | **LLL185C70G224MA11#** | |
| 0.55mm | 4Vdc | X7S | 2.2μF | ±20% | **LLL185C70G225ME01#** | |
| 0.6mm | 50Vdc | X7R | 2200pF | ±20% | **LLL185R71H222MA01#** | |
| | | | 4700pF | ±20% | **LLL185R71H472MA01#** | |
| | 25Vdc | X7R | 10000pF | ±20% | **LLL185R71E103MA01#** | |
| | | | 22000pF | ±20% | **LLL185R71E223MA01#** | |
| | 16Vdc | X7R | 47000pF | ±20% | **LLL185R71C473MA01#** | |
| | 10Vdc | X7R | 0.10μF | ±20% | **LLL185R71A104MA01#** | |
| | | | 0.22μF | ±20% | **LLL185R71A224MA01#** | |
| | 4Vdc | X7S | 0.47μF | ±20% | **LLL185C70G474MA01#** | |

## ■ 1.25×2.0mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.5mm | 50Vdc | X7R | 10000pF | ±20% | **LLL215R71H103MA11#** | |
| | 25Vdc | X7R | 22000pF | ±20% | **LLL215R71E223MA11#** | |
| | 16Vdc | X7R | 47000pF | ±20% | **LLL215R71C473MA11#** | |
| | | | 0.10μF | ±20% | **LLL215R71C104MA11#** | |
| | 10Vdc | X7R | 0.22μF | ±20% | **LLL215R71A224MA11#** | |
| | 6.3Vdc | X7R | 0.47μF | ±20% | **LLL215R70J474MA11#** | |
| | 4Vdc | X7S | 1.0μF | ±20% | **LLL215C70G105MA11#** | |
| 0.7mm | 50Vdc | X7R | 10000pF | ±20% | **LLL216R71H103MA01#** | |
| | | | 22000pF | ±20% | **LLL216R71H223MA01#** | |
| | 25Vdc | X7R | 47000pF | ±20% | **LLL216R71E473MA01#** | |
| | | | 0.10μF | ±20% | **LLL216R71E104MA01#** | |
| | 10Vdc | X7R | 0.22μF | ±20% | **LLL216R71A224MA01#** | |
| 0.95mm | 16Vdc | X7R | 0.22μF | ±20% | **LLL219R71C224MA01#** | |
| | 10Vdc | X7R | 0.47μF | ±20% | **LLL219R71A474MA01#** | |
| | | | 1.0μF | ±20% | **LLL219R71A105MA01#** | |
| | 4Vdc | X7S | 2.2μF | ±20% | **LLL219C70G225MA01#** | |

## ■ 1.6×3.2mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.5mm | 50Vdc | X7R | 10000pF | ±20% | **LLL315R71H103MA11#** | |
| | | | 22000pF | ±20% | **LLL315R71H223MA11#** | |
| | 25Vdc | X7R | 47000pF | ±20% | **LLL315R71E473MA11#** | |
| | | | 0.10μF | ±20% | **LLL315R71E104MA11#** | |
| | 16Vdc | X7R | 0.22μF | ±20% | **LLL315R71C224MA11#** | |
| | 10Vdc | X7R | 0.47μF | ±20% | **LLL315R71A474MA11#** | |
| 0.8mm | 50Vdc | X7R | 10000pF | ±20% | **LLL317R71H103MA01#** | |
| | | | 22000pF | ±20% | **LLL317R71H223MA01#** | |
| | | | 47000pF | ±20% | **LLL317R71H473MA01#** | |
| | 25Vdc | X7R | 0.10μF | ±20% | **LLL317R71E104MA01#** | |
| | 16Vdc | X7R | 0.22μF | ±20% | **LLL317R71C224MA01#** | |
| | | | 0.47μF | ±20% | **LLL317R71C474MA01#** | |
| | 10Vdc | X7R | 1.0μF | ±20% | **LLL317R71A105MA01#** | |
| | 6.3Vdc | X7R | 2.2μF | ±20% | **LLL317R70J225MA01#** | |
| 1.25mm | 50Vdc | X7R | 0.10μF | ±20% | **LLL31MR71H104MA01#** | |
| | 25Vdc | X7R | 0.22μF | ±20% | **LLL31MR71E224MA01#** | |
| | | | 0.47μF | ±20% | **LLL31MR71E474MA01#** | |
| | 16Vdc | X7R | 1.0μF | ±20% | **LLL31MR71C105MA01#** | |
| | 10Vdc | X7R | 2.2μF | ±20% | **LLL31MR71A225MA01#** | |
| | 6.3Vdc | X7R | 4.7μF | ±20% | **LLL31MR70J475MA01#** | |
| | | X5R | 10μF | ±20% | **LLL31MR60J106ME01#** | |

Part number # indicates the package specification code.

10-Terminal Low ESL Type

# LLM Series

Low ESL

## 10-Terminal Type Low ESL Capacitor Ideal for Power Supply Decoupling of High-speed Operation IC

### Features

**1 This is the lowest ESL LW reversed type capacitor.**

Since the equivalent series inductance (ESL) of this product is even lower than the LLA series (8-terminal product) with excellent high frequency characteristics, this capacitor is ideal for power supply decoupling of high-speed operation IC.




<Example of Structure>




<Effectiveness of Cancelling Out Inductance by Mutual Inductance>




<Effectiveness of Suppressing Inductance when Mounting a Multi-terminal Capacitor>

**The inductance for the boards also becomes lower, not only the capacitor.**

**2 A maximum operating temperature up to 125ºC.**

This product is applicable to high temperatures (X7* characteristics); however, Murata also offers numerous thin type products, which are ideal as decoupling capacitors on IC package.

### Specifications

| | |
|---|---|
| Size | 2.0×1.25mm to 3.2×1.6mm |
| Rated Voltage | DC4V to 25V |
| Capacitance | 0.01µF to 2.2µF |
| Main Applications | Application processor/CPU/GPU |

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.




<Dimensions>

# LLM Series High Dielectric Constant Type Low ESL Part Number List

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 25Vdc | X7R | 10000pF | ±20% | **LLM215R71E103MA11#** | |
| | | | 22000pF | ±20% | **LLM215R71E223MA11#** | |
| | 16Vdc | X7R | 47000pF | ±20% | **LLM215R71C473MA11#** | |
| | | | 0.10μF | ±20% | **LLM215R71C104MA11#** | |
| | 6.3Vdc | X7R | 0.22μF | ±20% | **LLM215R70J224MA11#** | |
| | | | 0.47μF | ±20% | **LLM215R70J474MA11#** | |
| | 4Vdc | X7S | 1.0μF | ±20% | **LLM215C70G105MA11#** | |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number | |
|---|---|---|---|---|---|---|
| 0.55mm | 16Vdc | X7R | 0.10μF | ±20% | **LLM315R71C104MA11#** | |
| | | | 0.22μF | ±20% | **LLM315R71C224MA11#** | |
| | 10Vdc | X7R | 0.47μF | ±20% | **LLM315R71A474MA11#** | |
| | 6.3Vdc | X7R | 2.2μF | ±20% | **LLM315R70J225MA11#** | |

Part number # indicates the package specification code.

ESR Controlled Low ESL Type

# LLR Series

Low ESL

## ESR Controlled Type Low ESL Capacitors Equipped with Anti-resonance Control Function

### Features

#### ① Reduces Anti-resonance

This capacitor is controlled so that the equivalent series resistance (ESR) becomes slightly higher, and is effective in reducing the anti-resonance that occurs when capacitor arrays are used.




#### ② Lineup of capacitors with ESR values from 100 to 1,000mΩ.

According to the conditions of the anti-resonance, the most suitable ESR value can be selected from 4 types.

#### ③ Low ESL

This ESR controlled type capacitor has excellent high frequency characteristics, with low equivalent series inductance (ESL). This is also ideal as a decoupling component.

### Specifications

| | |
|---|---|
| Size | 0.8×1.6mm |
| Rated Voltage | DC4V |
| Capacitance | 1.0μF |
| Main Applications | Network processor/ASIC/PMIC |



<Dimensions>

This catalog contains only a portion of the product lineup.
Please refer to the capacitor search tool on the Murata Web site for details.

# LLR Series High Dielectric Constant Type Low ESL Part Number List

## ■ 0.8×1.6mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | ESR | Part Number | |
|---|---|---|---|---|---|---|---|
| 0.55mm | 4Vdc | X7S | 1.0μF | ±20% | 100mΩ | **LLR185C70G105ME01#** | |
| | | | | ±20% | 220mΩ | **LLR185C70G105ME03#** | |
| | | | | ±20% | 470mΩ | **LLR185C70G105ME05#** | |
| | | | | ±20% | 1000mΩ | **LLR185C70G105ME07#** | |

Part number # indicates the package specification code.

# ⚠Caution/Notice

## ⚠Caution

■ Storage and Operation Conditions ····· 138

■ Rating ····· 138
1. Temperature Dependent Characteristics ····· 138
2. Measurement of Capacitance ····· 138
3. Applied Voltage ····· 139
4. Type of Applied Voltage and Self-heating Temperature ····· 139
5. DC Voltage and AC Voltage Characteristics ····· 142
6. Capacitance Aging ····· 142
7. Vibration and Shock ····· 143

■ Soldering and Mounting ····· 143
1. Mounting Position ····· 143
2. Information before Mounting ····· 144
3. Maintenance of the Mounting (pick and place) Machine ····· 144
4-1. Reflow Soldering ····· 145
4-2. Flow Soldering ····· 146
4-3. Correction of Soldered Portion ····· 147
5. Washing ····· 148
6. Electrical Test on Printed Circuit Board ····· 148
7. Printed Circuit Board Cropping ····· 148
8. Assembly ····· 151
9. Die Bonding/Wire Bonding ····· 152

■ Other ····· 152
1. Under Operation of Equipment ····· 152
2. Other ····· 152

## Notice

■ Rating ····· 153
1. Operating Temperature ····· 153
2. Atmosphere Surroundings ····· 153
3. Piezo-electric Phenomenon ····· 153

■ Soldering and Mounting ····· 153
1. PCB Design ····· 153
1. Notice for Pattern Forms ····· 153
2. Land Dimensions ····· 154
3. Board Design ····· 155
2. Adhesive Application ····· 156
3. Adhesive Curing ····· 156
4. Flux Application ····· 156
5. Flow Soldering ····· 156
6. Washing ····· 157
7. Coating ····· 157

■ Other ····· 157
1. Transportation ····· 157
2. Characteristics Evaluation in the Actual System ····· 157

# ⚠Caution

## ■ Storage and Operation Conditions

1. The performance of chip monolithic ceramic capacitors may be affected by the storage conditions.
   1-1. Store the capacitors in the following conditions: Room Temperature of +5°C to +40°C and a Relative Humidity of 20% to 70%.
   (1) Sunlight, dust, rapid temperature changes, corrosive gas atmosphere, or high temperature and humidity conditions during storage may affect solderability and packaging performance. Therefore, please maintain the storage temperature and humidity. Use the product within six months, as prolonged storage may cause oxidation of the electrodes.
   (2) Please confirm solderability before using after six months. Store the capacitors without opening the original bag. Even if the storage period is short, do not exceed the specified atmospheric conditions.
   1-2. Corrosive gas can react with the termination (external) electrodes or lead wires of capacitors, and result in poor solderability. Do not store the capacitors in an atmosphere consisting of corrosive gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas, etc.).
   1-3. Due to moisture condensation caused by rapid humidity changes, or the photochemical change caused by direct sunlight on the terminal electrodes and/or the resin/epoxy coatings, the solderability and electrical performance may deteriorate. Do not store capacitors under direct sunlight or in high humidity conditions.

## ■ Rating

### 1. Temperature Dependent Characteristics

1. The electrical characteristics of a capacitor can change with temperature.
   1-1. For capacitors having larger temperature dependency, the capacitance may change with temperature changes.
   The following actions are recommended in order to ensure suitable capacitance values.
   (1) Select a suitable capacitance for the operating temperature range.
   (2) The capacitance may change within the rated temperature.
   When you use a high dielectric constant type capacitor in a circuit that needs a tight (narrow) capacitance tolerance (e.g., a time-constant circuit), please carefully consider the temperature characteristics, and carefully confirm the various characteristics in actual use conditions and the actual system.

[Typical Temperature Characteristics X7R]
Sample: 0.1µF, Rated Voltage 50VDC




[Typical Temperature Characteristics X5R]
Sample: 22µF, Rated Voltage 4VDC




### 2. Measurement of Capacitance

1. Measure capacitance with the voltage and frequency specified in the product specifications.
   1-1. The output voltage of the measuring equipment may decrease occasionally when capacitance is high. Please confirm whether a prescribed measured voltage is impressed to the capacitor.
   1-2. The capacitance values of high dielectric constant type capacitors change depending on the AC voltage applied. Please consider the AC voltage characteristics when selecting a capacitor to be used in an AC circuit.

Continued on the following page.

## ⚠Caution

Continued from the preceding page.

### 3. Applied Voltage

1. Do not apply a voltage to the capacitor that exceeds the rated voltage as called out in the specifications.
   1-1. Applied voltage between the terminals of a capacitor shall be less than or equal to the rated voltage.
   (1) When AC voltage is superimposed on DC voltage, the zero-to-peak voltage shall not exceed the rated DC voltage.
   When AC voltage or pulse voltage is applied, the peak-to-peak voltage shall not exceed the rated DC voltage.
   (2) Abnormal voltages (surge voltage, static electricity, pulse voltage, etc.) shall not exceed the rated DC voltage.

Typical Voltage Applied to the DC Capacitor

| DC Voltage | DC Voltage+AC | AC Voltage | Pulse Voltage |
|---|---|---|---|
|  |  |  |  |



(E: Maximum possible applied voltage.)

   1-2. Influence of over voltage
   Over voltage that is applied to the capacitor may result in an electrical short circuit caused by the breakdown of the internal dielectric layers.
   The time duration until breakdown depends on the applied voltage and the ambient temperature.
2. Use a safety standard certified capacitor in a power supply input circuit (AC filter), as it is also necessary to consider the withstand voltage and impulse withstand voltage defined for each device.

### 4. Type of Applied Voltage and Self-heating Temperature

1. Confirm the operating conditions to make sure that no large current is flowing into the capacitor due to the continuous application of an AC voltage or pulse voltage.
   When a DC rated voltage product is used in an AC voltage circuit or a pulse voltage circuit, the AC current or pulse current will flow into the capacitor; therefore check the self-heating condition.
   Please confirm the surface temperature of the capacitor so that the temperature remains within the upper limits of the operating temperature, including the rise in temperature due to self-heating. When the capacitor is used with a high-frequency voltage or pulse voltage, heat may be generated by dielectric loss.
   <Applicable to Rated Voltage of less than 100VDC>
   1-1. The load should be contained to the level such that when measuring at atmospheric temperature of 25°C, the product's self-heating remains below 20°C and the surface temperature of the capacitor in the actual circuit remains within the maximum operating temperature.

[Example of Temperature Rise (Heat Generation) in Chip Monolithic Ceramic Capacitors in Contrast to Ripple Current]
Sample: R characteristics 10μF, Rated voltage: DC10V




Continued on the following page.

## ⚠Caution

Continued from the preceding page.

<Applicable to Temperature Characteristic X7R, X7T beyond Rated Voltage of 200VDC>

1-2. The load should be contained so that the self-heating of the capacitor body remains below 20°C, when measuring at an ambient temperature of 25°C. In addition, use a K thermocouple of ø0.1mm with less heat capacity when measuring, and measure in a condition where there is no effect from the radiant heat of other components or air flow caused by convection. Excessive generation of heat may cause deterioration of the characteristics and reliability of the capacitor. (Absolutely do not perform measurements while the cooling fan is operating, as an accurate measurement may not be performed.)

<Applicable to Temperature Characteristic U2J, C0G beyond Rated Voltage of 200VDC>

1-3. Since the self-heating is low in the low loss series, the allowable power becomes extremely high compared to the common X7R characteristics.
However, when a load with self-heating of 20°C is applied at the rated voltage, the allowable power may be exceeded. When the capacitor is used in a high-frequency voltage circuit of 1kHz or more, the frequency of the applied voltage should be less than 500kHz sine wave (less than 100kHz for a product with rated voltage of DC3.15kV), to limit the voltage load so that the load remains within the derating shown in the following figure. In the case of non-sine wave, high-frequency components exceeding the fundamental frequency may be included. In such a case, please contact Murata. The excessive generation of heat may cause deterioration of the characteristics and reliability of the capacitor.
(Absolutely do not perform measurements while the cooling fan is operating, as an accurate measurement may not be performed.)

The temperature of the surface
of capacitor: 125°C or less (including self-heating)




The sine-wave frequency VS allowable voltage

Continued on the following page.

## ⚠Caution

Continued from the preceding page.

The temperature of the surface
of capacitor: 125°C or less (including self-heating)

U2J char., Rated Voltage: DC200V




U2J char., Rated Voltage: DC250V




U2J char., Rated Voltage: DC500V




U2J char., Rated Voltage: DC630V




U2J char., Rated Voltage: DC1kV




U2J char., Rated Voltage: DC2kV




U2J char., Rated Voltage: DC3.15kV




The sine-wave frequency VS allowable voltage

<Design Tool>

· Simsurfing

Simsurfing is a web application to display the characteristics charts and download the characteristics data of our products. The frequency characteristics, temperature characteristics, bias characteristics etc. can be checked.

(Address: http://www.murata.com/simsurfing/)

· Medium Voltage Ceramic Capacitor Selection Tool

The selection tool "Murata Medium Voltage Capacitors Selection Tool by Voltage Form" is installed in the above SimSurfing, where the usability of the preferred medium voltage ceramic capacitors can be determined according to the application including automobiles.

By using this tool, the preferred products* can be checked by specifications, such as the power, voltage, and fundamental frequency of the voltage waveform to be input into the capacitor.

*Supported Series

Temperature characteristic U2J, C0G of GRM/DC200V or more

Continued on the following page.

# ⚠Caution

Continued from the preceding page.

## 5. DC Voltage and AC Voltage Characteristics

1. The capacitance value of a high dielectric constant type capacitor changes depending on the DC voltage applied. Please consider the DC voltage characteristics when a capacitor is selected for use in a DC circuit.
   1-1. The capacitance of ceramic capacitors may change sharply depending on the applied voltage (see figure).
   Please confirm the following in order to secure the capacitance.
   (1) Determine whether the capacitance change caused by the applied voltage is within the allowed range.
   (2) In the DC voltage characteristics, the rate of capacitance change becomes larger as voltage increases, even if the applied voltage is below the rated voltage. When a high dielectric constant type capacitor is used in a circuit that requires a tight (narrow) capacitance tolerance (e.g., a time constant circuit), please carefully consider the voltage characteristics, and confirm the various characteristics in actual operating conditions in an actual system.
2. The capacitance values of high dielectric constant type capacitors changes depending on the AC voltage applied. Please consider the AC voltage characteristics when selecting a capacitor to be used in an AC circuit.

[DC Voltage Characteristics]
Sample: X7R Characteristics 0.1μF, Rated Voltage 50VDC




[AC Voltage Characteristics]
Sample: X7R Characteristics 10μF, Rated Voltage 6.3VDC




## 6. Capacitance Aging

1. The high dielectric constant type capacitors have the characteristic in which the capacitance value decreases with the passage of time.
   When you use high dielectric constant type capacitors in a circuit that needs a tight (narrow) capacitance tolerance (e.g., a time-constant circuit), please carefully consider the characteristics of these capacitors, such as their aging, voltage, and temperature characteristics. In addition, check capacitors using your actual appliances at the intended environment and operating conditions.

[Example of Change Over Time (Aging Characteristics)]




Continued on the following page.

# ⚠Caution

Continued from the preceding page.

### 7. Vibration and Shock

1. Please confirm the kind of vibration and/or shock, its condition, and any generation of resonance.
   Please mount the capacitor so as not to generate resonance, and do not allow any impact on the terminals.
2. Mechanical shock due to being dropped may cause damage or a crack in the dielectric material of the capacitor.
   Do not use a dropped capacitor because the quality and reliability may be deteriorated.




3. When printed circuit boards are piled up or handled, the corner of another printed circuit board should not be allowed to hit the capacitor, in order to avoid a crack or other damage to the capacitor.




## ■ Soldering and Mounting

### 1. Mounting Position

1. Confirm the best mounting position and direction that minimizes the stress imposed on the capacitor during flexing or bending the printed circuit board.
   1-1. Choose a mounting position that minimizes the stress imposed on the chip during flexing or bending of the board.

[Component Direction]



Locate chip horizontal to the direction in which stress acts.

[Chip Mounting Close to Board Separation Point]

It is effective to implement the following measures, to reduce stress in separating the board.
It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

| Contents of Measures | Stress Level |
|---|---|
| (1) Turn the mounting direction of the component parallel to the board separation surface. | A > D |
| (2) Add slits in the board separation part. | A > B |
| (3) Keep the mounting position of the component away from the board separation surface. | A > C |




[Mounting Capacitors Near Screw Holes]

When a capacitor is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the capacitor in a position as far away from the screw holes as possible.




Continued on the following page.

# ⚠Caution

Continued from the preceding page.

## 2. Information before Mounting

1. Do not re-use capacitors that were removed from the equipment.
2. Confirm capacitance characteristics under actual applied voltage.
3. Confirm the mechanical stress under actual process and equipment use.
4. Confirm the rated capacitance, rated voltage and other electrical characteristics before assembly.
5. Prior to use, confirm the solderability of capacitors that were in long-term storage.
6. Prior to measuring capacitance, carry out a heat treatment for capacitors that were in long-term storage.
7. The use of Sn-Zn based solder will deteriorate the reliability of the MLCC.
   Please contact our sales representative or product engineers on the use of Sn-Zn based solder in advance.
8. We have also produced a DVD which shows a summary of our opinions, regarding the precautions for mounting.
   Please contact our sales representative to request the DVD.

## 3. Maintenance of the Mounting (pick and place) Machine

1. Make sure that the following excessive forces are not applied to the capacitors.
   1-1. In mounting the capacitors on the printed circuit board, any bending force against them shall be kept to a minimum to prevent them from any bending damage or cracking. Please take into account the following precautions and recommendations for use in your process.
   (1) Adjust the lowest position of the pickup nozzle so as not to bend the printed circuit board.
   (2) Adjust the nozzle pressure within a static load of 1N to 3N during mounting.

2. Dirt particles and dust accumulated between the suction nozzle and the cylinder inner wall prevent the nozzle from moving smoothly. This imposes greater force upon the chip during mounting, causing cracked chips. Also, the locating claw, when worn out, imposes uneven forces on the chip when positioning, causing cracked chips. The suction nozzle and the locating claw must be maintained, checked, and replaced periodically.




Continued on the following page.

# ⚠Caution

Continued from the preceding page.

## 4-1. Reflow Soldering

1. When sudden heat is applied to the components, the mechanical strength of the components will decrease because a sudden temperature change causes deformation inside the components. In order to prevent mechanical damage to the components, preheating is required for both the components and the PCB. Preheating conditions are shown in table 1. It is required to keep the temperature differential between the solder and the components surface (ΔT) as small as possible.
2. Solderability of tin plating termination chips might be deteriorated when a low temperature soldering profile where the peak solder temperature is below the melting point of tin is used. Please confirm the solderability of tin plated termination chips before use.
3. When components are immersed in solvent after mounting, be sure to maintain the temperature difference (ΔT) between the component and the solvent within the range shown in table 1.

**Table 1**

| Part Number | Temperature Differential |
|---|---|
| **GJM/GMA/GMD/GQM/GR3/GRJ/GRM/KRM/LLL/LLR** Series **02/03/15/18/21/31** sizes<br>**LLL** Series **1U** size | ΔT≦190°C |
| **GR3/GRJ/GRM/KR3/KRM** Series **32/43/55** sizes<br>**LLA/LLM** Series **18/21/31** sizes<br>**GQM** Series **22** size | ΔT≦130°C |

**Recommended Conditions**

| | Pb-Sn Solder | | Lead Free Solder |
|---|---|---|---|
| | Reflow | Vapor Reflow | |
| Peak Temperature | 230 to 250°C | 230 to 240°C | 240 to 260°C |
| Atmosphere | Air | Saturated vapor of inactive solvent | Air or $N_2$ |

Pb-Sn Solder: Sn-37Pb
Lead Free Solder: Sn-3.0Ag-0.5Cu

[Standard Conditions for Reflow Soldering]




Temperature
Incase of Lead Free Solder
( ): In case of Pb-Sn Solder




[Allowable Reflow Soldering Temperature and Time]




In the case of repeated soldering, the accumulated soldering time must be within the range shown above.

4. Optimum Solder Amount for Reflow Soldering
   4-1. Overly thick application of solder paste results in a excessive solder fillet height.
   This makes the chip more susceptible to mechanical and thermal stress on the board and may cause the chips to crack.
   4-2. Too little solder paste results in a lack of adhesive strength on the outer electrode, which may result in chips breaking loose from the PCB.
   4-3. Make sure the solder has been applied smoothly to the end surface to a height of 0.2mm* min.




* 02/03 sizes: 1/3 of Chip Thickness min.

in section

**Inverting the PCB**

Make sure not to impose any abnormal mechanical shocks to the PCB.

Continued on the following page.

# ⚠Caution

Continued from the preceding page.

## 4-2. Flow Soldering

1. Do not apply flow soldering to chips not listed in table 2.

Table 2

| Part Number | Temperature Differential |
|---|---|
| **GR3/GRM** Series **18/21/31** sizes<br>**GQM** Series **18/21** sizes<br>**LLL** Series **21/31** sizes<br>**GRJ** Series Rated Voltage 250VDC or more **18/21/31** sizes | ΔT≦150°C |

2. When sudden heat is applied to the components, the mechanical strength of the components will decrease because a sudden temperature change causes deformation inside the components. In order to prevent mechanical damage to the components, preheating is required for both of the components and the PCB. Preheating conditions are shown in table 2. It is required to keep the temperature differential between the solder and the components surface (ΔT) as low as possible.
3. Excessively long soldering time or high soldering temperature can result in leaching of the outer electrodes, causing poor adhesion or a reduction in capacitance value due to loss of contact between the electrodes and end termination.
4. When components are immersed in solvent after mounting, be sure to maintain the temperature differential (ΔT) between the component and solvent within the range shown in the table 2.

[Standard Conditions for Flow Soldering]




[Allowable Flow Soldering Temperature and Time]




In the case of repeated soldering, the accumulated soldering time must be within the range shown above.

Recommended Conditions

| | Pb-Sn Solder | Lead Free Solder |
|---|---|---|
| Preheating Peak Temperature | 90 to 110°C | 100 to 120°C |
| Soldering Peak Temperature | 240 to 250°C | 250 to 260°C |
| Atmosphere | Air | $N_2$ |

Pb-Sn Solder: Sn-37Pb
Lead Free Solder: Sn-3.0Ag-0.5Cu

5. Optimum Solder Amount for Flow Soldering
   5-1. The top of the solder fillet should be lower than the thickness of the components. If the solder amount is excessive, the risk of cracking is higher during board bending or any other stressful condition.




Continued on the following page.

## ⚠Caution

Continued from the preceding page.

### 4-3. Correction of Soldered Portion

When sudden heat is applied to the capacitor, distortion caused by the large temperature difference occurs internally, and can be the cause of cracks. Capacitors also tend to be affected by mechanical and thermal stress depending on the board preheating temperature or the soldering fillet shape, and can be the cause of cracks. Please refer to "1. PCB Design" or "3. Optimum solder amount" for the solder amount and the fillet shapes.

1. Correction with a Soldering Iron
   1-1. In order to reduce damage to the capacitor, be sure to preheat the capacitor and the mounting board. Preheat to the temperature range shown in Table 3. A hot plate, hot air type preheater, etc. can be used for preheating.
   1-2. After soldering, do not allow the component/PCB to cool down repidly.
   1-3. Perform the corrections with a soldering iron as quickly as possible. If the soldering iron is applied too long, there is a possibility of causing solder leaching on the terminal electrodes, which will cause deterioration of the adhesive strength and other problems.
2. Correction with Spot Heater
   Compared to local heating with a soldering iron, hot air heating by a spot heater heats the overall component and board, therefore, it tends to lessen the thermal shock. In the case of a high density mounted board, a spot heater can also prevent concerns of the soldering iron making direct contact with the component.
   2-1. If the distance from the hot air outlet of the spot heater to the component is too close, cracks may occur due to thermal shock. To prevent this problem, follow the conditions shown in Table 4.

Table 3

| Part Number | Temperature of Soldering Iron Tip | Preheating Temperature | Temperature Differential (ΔT) | Atmosphere |
|---|---|---|---|---|
| **GJM/GQM/GR3/ GRJ/GRM** Series **03/15/18/21/31** sizes | 350°C max. | 150°C min. | ΔT≦190°C | Air |
| **GRJ/GRM** Series **32/43/55** sizes<br>**GQM** Series **22** size | 280°C max. | 150°C min. | ΔT≦130°C | Air |

*Applicable for both Pb-Sn and Lead Free Solder.
Pb-Sn Solder: Sn-37Pb
Lead Free Solder: Sn-3.0Ag-0.5Cu

Table 4

| | |
|---|---|
| Distance | 5mm or more |
| Hot Air Application angle | 45° *Figure 1 |
| Hot Air Temperature Nozzle Outlet | 400°C max. |
| Application Time | Less than 10 seconds (1206 (3216 in mm) size or smaller) |
| | Less than 30 seconds (1210 (3225 in mm) size or larger) |

   2-2. In order to create an appropriate solder fillet shape, it is recommended that hot air be applied at the angle shown in Figure 1.

[Figure 1]




3. Optimum solder amount when re-working with a soldering iron
   3-1. In the case of sizes smaller than 0603, (GJM/GQM/GR3/ GRJ/GRM Series, 03/15/18 sizes), the top of the solder fillet should be lower than $^2/_3$ of the thickness of the component or 0.5mm, whichever is smaller. In the case of 0805 and larger sizes, (GJM/GQM/GR3/GRJ/ GRM Series, 21/22/31/32/43/55 sizes), the top of the solder fillet should be lower than $^2/_3$ of the thickness of the component. If the solder amount is excessive, the risk of cracking is higher during board bending or under any other stressful condition.




Continued on the following page.

# ⚠Caution

Continued from the preceding page.

3-2. A soldering iron with a tip of ø3mm or smaller should be used. It is also necessary to keep the soldering iron from touching the components during the re-work.
3-3. Solder wire with ø0.5mm or smaller is required for soldering.

<Applicable to KR3/KRM Series>

4. For the shape of the soldering iron tip, refer to the figure on the right.
Regarding the type of solder, use a wire diameter of ø0.5mm or less (rosin core wire solder).




How to Apply the Soldering Iron

Apply the tip of the soldering iron against the lower end of the metal terminal.

1) In order to prevent cracking caused by sudden heating of the ceramic device, do not touch the ceramic base directly.
2) In order to prevent deviations and dislocating of the chip, do not touch the junction of the chip and the metal terminal, and the metal portion on the outside directly.

Appropriate Amount of Solder

The amount of solder for corrections by soldering iron, should be lower than the height of the lower side of the chip.

## 5. Washing

Excessive ultrasonic oscillation during cleaning can cause the PCBs to resonate, resulting in cracked chips or broken solder joints. Take note not to vibrate PCBs.

## 6. Electrical Test on Printed Circuit Board

1. Confirm position of the backup pin or specific jig, when inspecting the electrical performance of a capacitor after mounting on the printed circuit board.
1-1. Avoid bending the printed circuit board by the pressure of a test-probe, etc.
The thrusting force of the test probe can flex the PCB, resulting in cracked chips or open solder joints.
Provide backup pins on the back side of the PCB to prevent warping or flexing. Install backup pins as close to the capacitor as possible.
1-2. Avoid vibration of the board by shock when a test-probe contacts a printed circuit board.




## 7. Printed Circuit Board Cropping

1. After mounting a capacitor on a printed circuit board, do not apply any stress to the capacitor that causes bending or twisting the board.
1-1. In cropping the board, the stress as shown at right may cause the capacitor to crack.
Cracked capacitors may cause deterioration of the insulation resistance, and result in a short.
Avoid this type of stress to a capacitor.




Continued on the following page.

## ⚠Caution

Continued from the preceding page.

2. Check the cropping method for the printed circuit board in advance.

2-1. Printed circuit board cropping shall be carried out by using a jig or an apparatus (Disk separator, router type separator, etc.) to prevent the mechanical stress that can occur to the board.

| Board Separation Method | Hand Separation Nipper Separation | (1) Board Separation Jig | Board Separation Apparatus | |
|---|---|---|---|---|
| | | | (2) Disk Separator | (3) Router Type Separator |
| Level of stress on board | High | Medium | Medium | Low |
| Recommended | × | △* | △* | ○ |
| Notes | Hand and nipper separation apply a high level of stress. Use another method. | · Board handling<br>· Board bending direction<br>· Layout of capacitors | · Board handling<br>· Layout of slits<br>· Design of V groove<br>· Arrangement of blades<br>· Controlling blade life | Board handling |

* When a board separation jig or disk separator is used, if the following precautions are not observed, a large board deflection stress will occur and the capacitors may crack. Use router type separator if at all possible.

(1) Example of a suitable jig

[In the case of Single-side Mounting]

An outline of the board separation jig is shown as follows. Recommended example: Stress on the component mounting position can be minimized by holding the portion close to the jig, and bend in the direction towards the side where the capacitors are mounted. Not recommended example: The risk of cracks occurring in the capacitors increases due to large stress being applied to the component mounting position, if the portion away from the jig is held and bent in the direction opposite the side where the capacitors are mounted.

[Outline of Jig]




| Recommended | Not recommended |
|---|---|
|  |  |





[In the case of Double-sided Mounting]

Since components are mounted on both sides of the board, the risk of cracks occurring can not be avoided with the above method.

Therefore, implement the following measures to prevent stress from being applied to the components.

(Measures)

(1) Consider introducing a router type separator. If it is difficult to introduce a router type separator, implement the following measures. (Refer to item 1. Mounting Position)

(2) Mount the components at a right angle to the board separation surface.

(3) When mounting components near the board separation point, add slits in the separation position near the component.

(4) Keep the mounting position of the components away from the board separation point.

Continued on the following page.

# ⚠Caution

Continued from the preceding page.

(2) Example of a Disk Separator

An outline of a disk separator is shown as follows. As shown in the Principle of Operation, the top blade and bottom blade are aligned with the V-grooves on the printed circuit board to separate the board.

In the following case, board deflection stress will be applied and cause cracks in the capacitors.

(1) When the adjustment of the top and bottom blades are misaligned, such as deviating in the top-bottom, left-right or front-rear directions

(2) The angle of the V groove is too low, depth of the V groove is too shallow, or the V groove is misaligned top-bottom

IF V groove is too deep, it is possible to brake when you handle and carry it. Carefully design depth of the V groove with consideration about strength of material of the printed circuit board.




| Recommended | Not Recommended | | |
|---|---|---|---|
| | Top-bottom Misalignment | Left-right Misalignment | Front-rear Misalignment |
|  |  |  | |



| Example of Recommended V-groove Design | Not Recommended | | | |
|---|---|---|---|---|
| | Left-right Misalignment | Low-Angle | Depth too Shallow | Depth too Deep |
|  |  |  |  |  |

(3) Example of Router Type Separator

The router type separator performs cutting by a router rotating at a high speed. Since the board does not bend in the cutting process, stress on the board can be suppressed during board separation.

When attaching or removing boards to/from the router type separator, carefully handle the boards to prevent bending.




Continued on the following page.

## ⚠Caution

Continued from the preceding page.

### 8. Assembly

1. Handling

If a board mounted with capacitors is held with one hand, the board may bend. Firmly hold the edges of the board with both hands when handling.

If a board mounted with capacitors is dropped, cracks may occur in the capacitors.

Do not use dropped boards, as there is a possibility that the quality of the capacitors may be impaired.

2. Attachment of Other Components

2-1. Mounting of Other Components

Pay attention to the following items, when mounting other components on the back side of the board after capacitors have been mounted on the opposite side. When the bottom dead point of the suction nozzle is set too low, board deflection stress may be applied to the capacitors on the back side (bottom side), and cracks may occur in the capacitors.

· After the board is straightened, set the bottom dead point of the nozzle on the upper surface of the board.
· Periodically check and adjust the bottom dead point.




2-2. Inserting Components with Leads into Boards

When inserting components (transformers, IC, etc.) into boards, bending the board may cause cracks in the capacitors or cracks in the solder.

Pay attention to the following.

· Increase the size of the holes to insert the leads, to reduce the stress on the board during insertion.
· Fix the board with backup pins or a dedicated jig before insertion.
· Support below the board so that the board does not bend. When using multiple backup pins on the board, periodically confirm that there is no difference in the height of each backup pin.




2-3. Attaching/Removing Sockets

When the board itself is a connector, the board may bend when a socket is attached or removed. Plan the work so that the board does not bend when a socket is attached or removed.




2-4. Tightening Screws

The board may be bent, when tightening screws, etc. during the attachment of the board to a shield or chassis.

Pay attention to the following items before performing the work.

· Plan the work to prevent the board from bending.
· Use a torque screwdriver, to prevent over-tightening of the screws.
· The board may bend after mounting by reflow soldering, etc. Please note, as stress may be applied to the chips by forcibly flattening the board when tightening the screws.




Continued on the following page.

# ⚠Caution

Continued from the preceding page.

<Applicable to GMA or GMD Series>

**9. Die Bonding/Wire Bonding**

1. Die Bonding of Capacitors
   1-1. Use the following materials for the Brazing alloys:
   Au-Sn (80/20) 300 to 320 °C in $N_2$ atmosphere
   1-2. Mounting
   (1) Control the temperature of the substrate so it matches the temperature of the brazing alloy.
   (2) Place the brazing alloy on the substrate and place the capacitor on the alloy. Hold the capacitor and gently apply the load. Be sure to complete the operation within 1 minute.

2. Wire Bonding
   2-1. Wire
   Gold wire: 25 micro m (0.001 inch) diameter
   2-2. Bonding
   (1) Thermo compression, ultrasonic ball bonding.
   (2) Required stage temperature: 150 to 200 °C
   (3) Required wedge or capillary weight: 0.2N to 0.5N
   (4) Bond the capacitor and base substrate or other devices with gold wire.

## ■ Other

1. Under Operation of Equipment
   1-1. Do not touch a capacitor directly with bare hands during operation in order to avoid the danger of an electric shock.
   1-2. Do not allow the terminals of a capacitor to come in contact with any conductive objects (short-circuit). Do not expose a capacitor to a conductive liquid, including any acid or alkali solutions.
   1-3. Confirm the environment in which the equipment will operate is under the specified conditions. Do not use the equipment under the following environments.
   (1) Being spattered with water or oil.
   (2) Being exposed to direct sunlight.
   (3) Being exposed to ozone, ultraviolet rays, or radiation.
   (4) Being exposed to toxic gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas, etc.)
   (5) Any vibrations or mechanical shocks exceeding the specified limits.
   (6) Moisture condensing environments.
   1-4. Use damp proof countermeasures if using under any conditions that can cause condensation.
2. Other
   2-1. In an Emergency
   (1) If the equipment should generate smoke, fire, or smell, immediately turn off or unplug the equipment. If the equipment is not turned off or unplugged, the hazards may be worsened by supplying continuous power.
   (2) In this type of situation, do not allow face and hands to come in contact with the capacitor or burns may be caused by the capacitor's high temperature.
   2-2. Disposal of Waste
   When capacitors are disposed of, they must be burned or buried by an industrial waste vendor with the appropriate licenses.
   2-3. Circuit Design
   (1) Addition of Fail Safe Function
   Capacitors that are cracked by dropping or bending of the board may cause deterioration of the insulation resistance, and result in a short. If the circuit being used may cause an electrical shock, smoke or fire when a capacitor is shorted, be sure to install fail-safe functions, such as a fuse, to prevent secondary accidents.
   (2) Capacitors used to prevent electromagnetic interference in the primary AC side circuit, or as a connection/insulation, must be a safety standard certified product, or satisfy the contents stipulated in the Electrical Appliance and Material Safety Law. Install a fuse for each line in case of a short.
   (3) The GJM, GMA, GMD, GQM, GR3, GRJ, GRM, KR3, KRM, LLA, LLL, LLM and LLR series are not safety standard certified products.
   2-4. Remarks
   Failure to follow the cautions may result, worst case, in a short circuit and smoking when the product is used.
   The above notices are for standard applications and conditions. Contact us when the products are used in special mounting conditions.
   Select optimum conditions for operation as they determine the reliability of the product after assembly.
   The data herein are given in typical values, not guaranteed ratings.

# Notice

## ■ Rating

1. Operating Temperature
   1. The operating temperature limit depends on the capacitor.
      1-1. Do not apply temperatures exceeding the upper operating temperature.
      It is necessary to select a capacitor with a suitable rated temperature that will cover the operating temperature range.
      It is also necessary to consider the temperature distribution in equipment and the seasonal temperature variable factor.
      1-2. Consider the self-heating factor of the capacitor.
      The surface temperature of the capacitor shall be the upper operating temperature or less when including the self-heating factors.
2. Atmosphere Surroundings (gaseous and liquid)
   1. Restriction on the operating environment of capacitors.
      1-1. Capacitors, when used in the above, unsuitable, operating environments may deteriorate due to the corrosion of the terminations and the penetration of moisture into the capacitor.
      1-2. The same phenomenon as the above may occur when the electrodes or terminals of the capacitor are subject to moisture condensation.
      1-3. The deterioration of characteristics and insulation resistance due to the oxidization or corrosion of terminal electrodes may result in breakdown when the capacitor is exposed to corrosive or volatile gases or solvents for long periods of time.
3. Piezo-electric Phenomenon
   1. When using high dielectric constant type capacitors in AC or pulse circuits, the capacitor itself vibrates at specific frequencies and noise may be generated. Moreover, when the mechanical vibration or shock is added to the capacitor, noise may occur.

## ■ Soldering and Mounting

### 1. PCB Design

1. Notice for Pattern Forms
   1-1. Unlike leaded components, chip components are susceptible to flexing stresses since they are mounted directly on the substrate.
   They are also more sensitive to mechanical and thermal stresses than leaded components.
   Excess solder fillet height can multiply these stresses and cause chip cracking. When designing substrates, take land patterns and dimensions into consideration to eliminate the possibility of excess solder fillet height.
   1-2. There is a possibility of chip cracking caused by PCB expansion/contraction with heat, because stress on a chip is different depending on PCB material and structure. When the thermal expansion coefficient greatly differs between the board used for mounting and the chip, it will cause cracking of the chip due to the thermal expansion and contraction. When small size capacitors of 1005 size or less are mounted on a single-layered glass epoxy board, it will also cause cracking of the chip for the same reason.

**Pattern Forms**

| | Prohibited | Correct |
|---|---|---|
| Placing Close to Chassis |  |  |
| Placing of Chip Components and Leaded Components |  |  |
| Placing of Leaded Components after Chip Component |  |  |
| Lateral Mounting |  |  |

Continued on the following page.

# Notice

Continued from the preceding page.

2. Land Dimensions

2-1. Chip capacitors can be cracked due to the stress of PCB bending, etc. if the land area is larger than needed and has an excess amount of solder.
Please refer to the land dimensions in table 1 for flow soldering, table 2 for reflow soldering, table 3 for reflow soldering for LLA Series, table 4 for reflow soldering for LLM Series.
Please confirm the suitable land dimension by evaluating of the actual SET / PCB.




**Table 1 Flow Soldering Method**

| Part Number \ Dimensions | Chip (L×W) | a | b | c |
|---|---|---|---|---|
| **GQM/GR3/GRJ/GRM** Series **18** size | 1.6×0.8 | 0.6 to 1.0 | 0.8 to 0.9 | 0.6 to 0.8 |
| **GQM/GR3/GRJ/GRM** Series **21** size | 2.0×1.25 | 1.0 to 1.2 | 0.9 to 1.0 | 0.8 to 1.1 |
| **GR3/GRJ/GRM** Series **31** size | 3.2×1.6 | 2.2 to 2.6 | 1.0 to 1.1 | 1.0 to 1.4 |
| **LLL** Series **21** size | 1.25×2.0 | 0.4 to 0.7 | 0.5 to 0.7 | 1.4 to 1.8 |
| **LLL** Series **31** size | 1.6×3.2 | 0.6 to 1.0 | 0.8 to 0.9 | 2.6 to 2.8 |

Flow soldering can only be used for products with a chip size of 3.2x1.6mm or less.

(in mm)

**Table 2 Reflow Soldering Method**

| Part Number \ Dimensions | Chip (L×W) | a | b | c |
|---|---|---|---|---|
| **GJM/GRM** Series **02** size | 0.4×0.2 | 0.16 to 0.2 | 0.12 to 0.18 | 0.2 to 0.23 |
| **GJM/GRM** Series **03** size | 0.6×0.3 | 0.2 to 0.3 | 0.2 to 0.35 | 0.2 to 0.4 |
| **GJM/GRM** Series **15** size | 1.0×0.5 (within ±0.10) | 0.3 to 0.5 | 0.35 to 0.45 | 0.4 to 0.6 |
| | 1.0×0.5 (±0.15/±0.20) | 0.4 to 0.6 | 0.4 to 0.5 | 0.5 to 0.7 |
| **GQM/GR3/GRJ/GRM** Series **18** size | 1.6×0.8 (within ±0.10) | 0.6 to 0.8 | 0.6 to 0.7 | 0.6 to 0.8 |
| | 1.6×0.8 (±0.15/±0.20) | 0.7 to 0.9 | 0.7 to 0.8 | 0.8 to 1.0 |
| **GQM** Series **21** size | 2.0×1.25 | 1.0 to 1.2 | 0.6 to 0.7 | 0.8 to 1.1 |
| **GR3/GRJ/GRM** Series **21** size | 2.0×1.25 (within ±0.10) | 1.2 | 0.6 | 1.25 |
| | 2.0×1.25 (±0.15) | 1.2 | 0.6 to 0.8 | 1.2 to 1.4 |
| | 2.0×1.25 (±0.20) | 1.0 to 1.4 | 0.6 to 0.8 | 1.2 to 1.4 |
| **GR3/GRJ/GRM** Series **31** size | 3.2×1.6 (within ±0.20) | 1.8 to 2.0 | 0.9 to 1.2 | 1.5 to 1.7 |
| | 3.2×1.6 (±0.30) | 1.9 to 2.1 | 1.0 to 1.3 | 1.7 to 1.9 |
| **GR3/GRJ/GRM** Series **32** size | 3.2×2.5 | 2.0 to 2.4 | 1.0 to 1.2 | 1.8 to 2.3 |
| **GR3/GRJ/GRM** Series **43** size | 4.5×3.2 | 3.0 to 3.5 | 1.2 to 1.4 | 2.3 to 3.0 |
| **GR3/GRJ/GRM** Series **55** size | 5.7×5.0 | 4.0 to 4.6 | 1.4 to 1.6 | 3.5 to 4.8 |
| **LLL** Series **15** size | 0.5×1.0 | 0.15 to 0.2 | 0.2 to 0.25 | 0.7 to 1.0 |
| **LLL** Series **1U** size | 0.6×1.0 | 0.20 to 0.25 | 0.25 to 0.35 | 0.7 to 1.0 |
| **LLL/LLR** Series **18** size | 0.8×1.6 | 0.2 to 0.3 | 0.3 to 0.4 | 1.4 to 1.6 |
| **LLL** Series **21** size | 1.25×2.0 | 0.4 to 0.6 | 0.4 to 0.5 | 1.4 to 1.8 |
| **LLL** Series **31** size | 1.6×3.2 | 0.6 to 0.8 | 0.6 to 0.7 | 2.6 to 2.8 |
| **GQM** Series **22** size | 2.8×2.8 | 2.2 to 2.5 | 0.8 to 1.0 | 1.9 to 2.3 |

(in mm)

**<Applicable to Part Number KR3/KRM>**

| Part Number \ Dimensions | Chip (L×W) | a | b | c |
|---|---|---|---|---|
| **KRM** Series **21** size | 2.0×1.25 | 1.0 to 1.2 | 0.6 to 0.7 | 0.8 to 1.1 |
| **KRM** Series **31** size | 3.2×1.6 | 2.2 to 2.4 | 0.8 to 0.9 | 1.0 to 1.4 |
| **KR3/KRM** Series **55** size | 5.7×5.0 | 2.6 | 2.7 | 5.6 |

(in mm)

Continued on the following page.

# Notice

Continued from the preceding page.

[Land for LLA Series]




[Land for LLM Series]




**Table 3 LLA Series Reflow Soldering Method**

| Part Number \ Dimensions | Chip (L×W) | a | b | c | p |
|---|---|---|---|---|---|
| **LLA** Series **18** size | 1.6×0.8 | 0.3 to 0.4 | 0.25 to 0.35 | 0.2 to 0.23 | 0.4 |
| **LLA** Series **21** size | 2.0×1.25 | 0.5 to 0.7 | 0.35 to 0.6 | 0.2 to 0.3 | 0.5 |
| **LLA** Series **31** size | 3.2×1.6 | 0.7 to 0.9 | 0.4 to 0.7 | 0.3 to 0.4 | 0.8 |

(in mm)

**Table 4 LLM Series Reflow Soldering Method**

| Part Number \ Dimensions | Chip (L×W) | a | b, b' | c, c' | d | e | f | p |
|---|---|---|---|---|---|---|---|---|
| **LLM** Series **21** size | 2.0×1.25 | 0.6 to 0.8 | (0.3 to 0.5) | 0.3 | 2.0 to 2.6 | 1.3 to 1.8 | 1.4 to 1.6 | 0.5 |
| **LLM** Series **31** size | 3.2×1.6 | 1.0 | (0.3 to 0.5) | 0.4 | 3.2 to 3.6 | 1.6 to 2.0 | 2.6 | 0.8 |

b=(c-e)/2, b'=(d-f)/2

(in mm)

3. Board Design

When designing the board, keep in mind that the amount of strain which occurs will increase depending on the size and material of the board.

[Relationship with amount of strain to the board thickness, length, width, etc.]

$$\varepsilon=\frac{3PL}{2Ewh^2}$$ Relationship between load and strain

ε: Strain on center of board (μst)
L: Distance between supporting points (mm)
$w$: Board width (mm)
$h$: Board thickness (mm)
$E$: Elastic modulus of board (N/m²=Pa)
$Y$: Deflection (mm)
P: Load (N)




When the load is constant, the following relationship can be established.
· As the distance between the supporting points (L) increases, the amount of strain also increases.
→Reduce the distance between the supporting points.
· As the elastic modulus ($E$) decreases, the amount of strain increases.
→Increase the elastic modulus.
· As the board width ($w$) decreases, the amount of strain increases.
→Increase the width of the board.
· As the board thickness ($h$) decreases, the amount of strain increases.
→Increase the thickness of the board.
Since the board thickness is squared, the effect on the amount of strain becomes even greater.

Continued on the following page.

# Notice

Continued from the preceding page.

## 2. Adhesive Application

1. Thin or insufficient adhesive can cause the chips to loosen or become disconnected during flow soldering. The amount of adhesive must be more than dimension c, shown in the drawing at right, to obtain the correct bonding strength.
   The chip's electrode thickness and land thickness must also be taken into consideration.
2. Low viscosity adhesive can cause chips to slip after mounting. The adhesive must have a viscosity of 5000Pa・s (500ps) min. (at 25°C).
3. Adhesive Coverage

| Size (L×W) (in mm) | Adhesive Coverage* |
|---|---|
| 1.6×0.8 | 0.05mg min. |
| 2.0×1.25 | 0.1mg min. |
| 3.2×1.6 | 0.15mg min. |

*Nominal Value




## 3. Adhesive Curing

1. Insufficient curing of the adhesive can cause chips to disconnect during flow soldering and causes deterioration in the insulation resistance between the outer electrodes due to moisture absorption.
   Control curing temperature and time in order to prevent insufficient hardening.

## 4. Flux Application

1. An excessive amount of flux generates a large quantity of flux gas, which can cause a deterioration of solder ability, so apply flux thinly and evenly throughout. (A foaming system is generally used for flow soldering.)
2. Flux containing too high a percentage of halide may cause corrosion of the outer electrodes unless there is sufficient cleaning. Use flux with a halide content of 0.1% max.
3. Do not use strong acidic flux.
4. Do not use water-soluble flux.*
   (*Water-soluble flux can be defined as non-rosin type flux including wash-type flux and non-wash-type flux.)

## 5. Flow Soldering

● Set temperature and time to ensure that leaching of the outer electrode does not exceed 25% of the chip end area as a single chip (full length of the edge A-B-C-D shown at right) and 25% of the length A-B shown as mounted on substrate.

[As a Single Chip]




[As Mounted on Substrate]




Continued on the following page.

# Notice

Continued from the preceding page.

### 6. Washing

1. Please evaluate the capacitor using actual cleaning equipment and conditions to confirm the quality, and select the solvent for cleaning.
2. Unsuitable cleaning solvent may leave residual flux or other foreign substances, causing deterioration of electrical characteristics and the reliability of the capacitors.
3. Select the proper cleaning conditions.
   3-1. Improper cleaning conditions (excessive or insufficient) may result in deterioration of the performance of the capacitors.

### 7. Coating

1. A crack may be caused in the capacitor due to the stress of the thermal contraction of the resin during curing process.
   The stress is affected by the amount of resin and curing contraction.
   Select a resin with low curing contraction.
   The difference in the thermal expansion coefficient between a coating resin or a molding resin and the capacitor may cause the destruction and deterioration of the capacitor such as a crack or peeling, and lead to the deterioration of insulation resistance or dielectric breakdown.
   Select a resin for which the thermal expansion coefficient is as close to that of the capacitor as possible.
   A silicone resin can be used as an under-coating to buffer against the stress.
2. Select a resin that is less hygroscopic.
   Using hygroscopic resins under high humidity conditions may cause the deterioration of the insulation resistance of a capacitor.
   An epoxy resin can be used as a less hygroscopic resin.

## ■ Other

1. Transportation
   1. The performance of a capacitor may be affected by the conditions during transportation.
      1-1. The capacitors shall be protected against excessive temperature, humidity, and mechanical force during transportation.
      (1) Climatic condition
      • low air temperature: -40°C
      • change of temperature air/air: -25°C/+25°C
      • low air pressure: 30 kPa
      • change of air pressure: 6 kPa/min.
      (2) Mechanical condition
      Transportation shall be done in such a way that the boxes are not deformed and forces are not directly passed on to the inner packaging.
      1-2. Do not apply excessive vibration, shock, or pressure to the capacitor.
      (1) When excessive mechanical shock or pressure is applied to a capacitor, chipping or cracking may occur in the ceramic body of the capacitor.
      (2) When the sharp edge of an air driver, a soldering iron, tweezers, a chassis, etc. impacts strongly on the surface of the capacitor, the capacitor may crack and short-circuit.
      1-3. Do not use a capacitor to which excessive shock was applied by dropping, etc.
      A capacitor dropped accidentally during processing may be damaged.
2. Characteristics Evaluation in the Actual System
   1. Evaluate the capacitor in the actual system, to confirm that there is no problem with the performance and specification values in a finished product before using.
   2. Since a voltage dependency and temperature dependency exists in the capacitance of high dielectric type ceramic capacitors, the capacitance may change depending on the operating conditions in the actual system. Therefore, be sure to evaluate the various characteristics, such as the leakage current and noise absorptivity, which will affect the capacitance value of the capacitor.
   3. In addition, voltages exceeding the predetermined surge may be applied to the capacitor by the inductance in the actual system. Evaluate the surge resistance in the actual system as required.

# Qualified Standards

The products listed here have been produced by ISO 9001 certified factory.

| Plant |
|---|
| Fukui Murata Mfg. Co., Ltd. |
| Izumo Murata Mfg. Co., Ltd. |
| Okayama Murata Mfg. Co., Ltd. |
| Murata Electronics Singapore (Pte.) Ltd. |
| Beijing Murata Electronics Co., Ltd. |
| Wuxi Murata Electronics Co., Ltd. |

# MEMO

# Design assistant tool: SimSurfing

muRata
Innovator in Electronics

# SimSurfing

for MLCC and various devices.
- Polymer capacitors
- RF inductors/Power inductors
- NTC thermisters/PTC thermisters

## Available function for MLCCs:

① Products search
② View frequency characteristics (S parameters, Z, R, X, Q, DF, L, C)
DC bias can be applied to available part number.
③ DC voltage bias characteristics (absolute capacitance/change rate)
④ Temperature characteristics (absolute capacitance/change rate)
⑤ AC voltage bias characteristics (absolute capacitance/change rate)
⑥ Download SPICE netlist/ S parameter

### 1 Select the Products

(1) By part number
(2) By specification

### 2 View characteristics

By clicking buttons in this area with part number selected, you can view any electrical characteristics chart.

### 3 Data download

You can download SPICE netlist and S parameter files (S2P)




Added the capacitor finder tool for middle and high voltage capacitor which are capable for specified voltage waveform.

These images are captured at August/2013. Be sure that this software will be updated frequently.

**http://ds.murata.com/software/simsurfing/en-us/mlcc/**

# EMICON-FUN!

Please check Murata's newsletter!
You can learn about electric parts with fun.
http://www.murata.com/products/emicon_fun/

EMICON-FUN! disseminated widely from basics (principles, characteristics, mounting, etc.) of capacitors, EMI suppression filters and inductors to information can practically be used.
Updated information is also distributed via the mail magazine.

## Click here to register as reader → https://fofa.jp/murata/a.p/107/

You can register from Murata Manufacturing Web site page TOP.
**http://www.murata.com/products/**

← This banner is the entrance of register form



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.
C02E.pdf
Sep.25,2013

# Capacitor Website Introduction

The website and search engine of ceramic capacitors has been drastically renewed.

capacitor murata Search

**http://www.murata.com/products/capacitor/**

**Convenient Search**

The type of searches has been increased to respond to various ways of searching.
The products you are searching for can easily be found from about 40,000 part numbers!
The frequency of revisions and discontinuance has been increased to provide the latest information at all times!

**Substantial Technical Information**

- Reference drawings (Specifications and Test Methods) can be downloaded in PDF format.
- Graphs of the electrical characteristic data (Capacitance - Temperature characteristics / DC bias characteristics / AC voltage characteristics / Frequency characteristics) can be displayed.
- Reliability test data can be downloaded.




**1 Examples of Problem Solving**
Contents for Solving customers' problems.
- Examples of Replacement (Video)
- Proposal for Cost Reductions
- Examples of Noise Countermeasures (Video)

**2 Industry Pickup**
Introducing the recommended series and the latest information on Murata for each industry.
- Automobile
- Smart Phones

**3 Advantages of Murata Capacitors**
We explain the unique benefits of Murata capacitors, our matchless quality, track record in the market, supply systems and development capability.

You can contact us and download catalogs from here.

**1 Search by features**
Products can be searched by problems, shapes or mounting methods.

**2 Search in the lineups**
Products can be searched by entire product lineup.

**3 Search by specifications**
Products can be searched by capacitance, rated voltage or temperature characteristics.

**4 Cross reference search**
Equivalent products of Murata can be searched by competitors' part numbers.

**5 Search by part number**
Products can be searched by Murata's part numbers.




**SimSurfing**
This is a web application to display characteristics charts of Murata products, and download the characteristics data.

- **S parameter**
- **Netlist (SPICE Model)**
- **Data Libraries (for Agilent ADS, for AWR Microwave Office®)**

**Frequently Asked Questions (FAQ)**
This is a collection of questions asked by customers.
The contents of problems can easily be searched by keywords with this search function.

**Characteristics Data**
(Dimensions / Capacitance - Temperature Characteristics / DC Bias Characteristics / AC Voltage / Frequency Characteristics / Heat Generation by Ripple Currents, etc.)

**Reliability Test Data**
Initial Characteristics / Board Bending Resistance / Humidity Resistance / High Temperature Load / Solderability, etc.

**Safety Certificates by Series**

**List of ISO14001 Certified Plants**

## ⚠Note:

1. Export Control
   <For customers outside Japan>
   No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.
   <For customers in Japan>
   For products which are controlled items subject to the “Foreign Exchange and Foreign Trade Law” of Japan, the export license specified by the law is required for export.
2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
   ① Aircraft equipment
   ② Aerospace equipment
   ③ Undersea equipment
   ④ Power plant equipment
   ⑤ Medical equipment
   ⑥ Transportation equipment (vehicles, trains, ships, etc.)
   ⑦ Traffic signal equipment
   ⑧ Disaster prevention / crime prevention equipment
   ⑨ Data-processing equipment
   ⑩ Application of similar complexity and/or reliability requirements to the applications listed above
3. Product specifications in this catalog are as of August 2013. They are subject to change or our products in it may be discontinued without advance notice.
   Please check with our sales representatives or product engineers before ordering. If there are any questions,please contact our sales representatives or product engineers.
4. Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
5. This catalog has only typical specifications.Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.
6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

**Murata Manufacturing Co., Ltd.**

http://www.murata.com/

**Head Office**
1-10-1, Higashi Kotari, Nagaokakyo-shi, Kyoto 617-8555, Japan
Phone: 81-75-951-9111

**International Division**
3-29-12, Shibuya, Shibuya-ku, Tokyo 150-0002, Japan
Phone: 81-3-5469-6123 Fax: 81-3-5469-6155 E-mail: intl@murata.co.jp

**Cat. No. C02E-18**