

Zener Diode

1N4728A-1N4764A

Features:

- High reliability.
- Very sharp reverse characteristic.
- Low reverse current level.
- V_Z -tolerance $\pm 5\%$.



Applications:

Voltage stabilization

Absolute Maximum Ratings $T_j = 25^\circ\text{C}$

Parameter	Test Conditions	Symbol	Value	Unit
Power dissipation	$T_{\text{amb}} \leq 50^\circ\text{C}$	P_V	1	W
Z-current	-	I_Z	P_V/V_Z	mA
Junction temperature	-	T_j	200	$^\circ\text{C}$
Storage temperature range	-	T_{stg}	-65 to +175	

Maximum Thermal Resistance $T_j = 25^\circ\text{C}$

Parameter	Test Conditions	Symbol	Value	Unit
Junction ambient	$l = 9.5\text{mm}$ (3/8 inches) $T_L = \text{constant}$	R_{thJA}	100	K/W

Stresses exceeding maximum ratings may damage the device. Maximum ratings are stress ratings only. Functional operation above the recommended operating conditions is not implied. Extended exposure to stresses above the recommended operating conditions may affect device reliability.

Electrical Characteristics $T_j = 25^\circ\text{C}$

Parameter	Test Conditions	Symbol	Maximum	Unit
Forward voltage	$I_F = 200\text{mA}$	V_F	1.2	V

Zener Diode

1N4728A-1N4764A


Specification Table

Description	V _{Znom} ¹⁾	I _{ZT}	for	r _{ziT}	r _{ziK}	at	I _{ZK}	I _R	at	V _R	Part Number
	V	mA		Ω	Ω		mA	μA		V	
Zener Diode	3.3	76	< 10	< 400	1	0.5	0.25	< 100	1	47.1	1N4728A
Zener Diode	3.6	69						1N4729A			
Zener Diode	3.9	64						< 9			< 50
Zener Diode	4.7	53	< 8	< 500				1N4732A			
Zener Diode	5.1	49	< 7	< 550				1N4733A			
Zener Diode	5.6	45	< 5	< 600				2	1N4734A		
Zener Diode	6.2	41	< 2	< 700				3	1N4735A		
Zener Diode	6.8	37	< 3.5					4	1N4736A		
Zener Diode	7.5	34	< 4		5	1N4737A					
Zener Diode	8.2	31	< 4.5		6	1N4738A					
Zener Diode	9.1	28	< 5		7	1N4739A					
Zener Diode	10	25	< 7	7.6	1N4740A						
Zener Diode	62	4	< 125	< 2000	< 5	47.1	1N4759A				

1) Based on DC-measurement at thermal equilibrium while maintaining the lead temperature (T_L) at 30°C, 9.5mm (3/8 inches) from the diode body.

Characteristics ($T_j = 25^\circ C$ unless otherwise specified)

Symbol	Parameter
V_Z	Reverse zener voltage at I_{ZT}
I_{ZT}	Reverse current
Z_{ZT}	Maximum zener impedance at I_{ZT}
I_{ZK}	Reverse current
Z_{ZK}	Maximum zener impedance at I_{ZK}
I_R	Reverse leakage current at V_R
V_R	Breakdown voltage
I_F	Forward current
V_F	Forward voltage at I_F





Zener Voltage Regulator

Zener Diode


1N4728A-1N4764A

Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise specified)




Temperature Coefficients

(-55°C to $+150^\circ\text{C}$ temperature range; 90% of the units are in the ranges indicated.)




Effect of Zener Current on Zener Impedance




Effect of Zener Voltage on Zener Impedance

Zener Diode

1N4728A-1N4764A



Marking



Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.