

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED

© COPYRIGHT — BY

1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

△₂ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.

3 RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.



$\triangle$ $\boxed{\oplus}$.020 $\textcircled{M}$ FOR KINKED TAILS.

5 0.000381 [0.00015] GOLD IN CONTACT AREA, 0.00254-0.00504 [0.00100-0.00200]
MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [0.00050] NICKEL.




6 HOUSING: LCP, COLOR-BLACK.
POSTS: COPPER ALLOY.

0.000381 [0.00015] GOLD IN CONTACT AREA, 0.00254-0.00504 [0.00100-0.00200]
MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [0.00050] NICKEL.

8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK.

		101.19 [3.984]	99.06 [3.900]	39	40	9-146288-0
A)		98.65 [3.884]	96.52 [3.800]	38	39	8-146288-9
		96.11 [3.784]	93.98 [3.700]	37	38	8-146288-8
		93.57 [3.684]	91.44 [3.600]	36	37	8-146288-7
		91.03 [3.584]	88.90 [3.500]	35	36	8-146288-6
		88.49 [3.484]	86.36 [3.400]	34	35	8-146288-5
		85.95 [3.384]	83.82 [3.300]	33	34	8-146288-4
		83.41 [3.284]	81.28 [3.200]	32	33	8-146288-3
		80.87 [3.184]	78.74 [3.100]	31	32	8-146288-2
		78.33 [3.084]	76.20 [3.000]	30	31	8-146288-1
		75.79 [2.984]	73.66 [2.900]	29	30	8-146288-0
		73.25 [2.884]	71.12 [2.800]	28	29	7-146288-9
		70.71 [2.784]	68.58 [2.700]	27	28	7-146288-8
		68.17 [2.684]	66.04 [2.600]	26	27	7-146288-7
		65.63 [2.584]	63.5 [2.500]	25	26	7-146288-6
		63.09 [2.484]	60.96 [2.400]	24	25	7-146288-5
		60.55 [2.384]	58.42 [2.300]	23	24	7-146288-4
		58.01 [2.284]	55.88 [2.200]	22	23	7-146288-3
		55.47 [2.184]	53.34 [2.100]	21	22	7-146288-2
		52.93 [2.084]	50.80 [2.000]	20	21	7-146288-1
		50.39 [1.984]	48.26 [1.900]	19	20	7-146288-0
		47.85 [1.884]	45.72 [1.800]	18	19	6-146288-9
		45.31 [1.784]	43.18 [1.700]	17	18	6-146288-8
		42.77 [1.684]	40.64 [1.600]	16	17	6-146288-7
		40.23 [1.584]	38.10 [1.500]	15	16	6-146288-6
		37.69 [1.484]	35.56 [1.400]	14	15	6-146288-5
		35.15 [1.384]	33.02 [1.300]	13	14	6-146288-4
	32.61 [1.284]	30.48 [1.200]	12	13	6-146288-3	
		30.07 [1.184]	27.94 [1.100]	11	12	6-146288-2
OBSOLETE		27.53 [1.084]	25.40 [1.000]	10	11	6-146288-1
		24.99 [.984]	22.86 [.900]	9	10	6-146288-0
		22.45 [.884]	20.32 [.800]	8	9	5-146288-9
OBSOLETE		19.91 [.784]	17.78 [.700]	7	8	5-146288-8
		17.37 [.684]	15.24 [.600]	6	7	5-146288-7
		14.83 [.584]	12.70 [.500]	5	6	5-146288-6
		12.29 [.484]	10.16 [.400]	4	5	5-146288-5
OBSOLETE		9.75 [.384]	7.62 [.300]	3	4	5-146288-4
		7.21 [.284]	5.08 [.200]	2	3	5-146288-3
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

8 OBSOLETE		5	101.19 [3.984]	99.06 [3.900]	39	40	4-146288-0
		5	98.65 [3.884]	96.52 [3.800]	38	39	3-146288-9
		5	96.11 [3.784]	93.98 [3.700]	37	38	3-146288-8
		5	93.57 [3.684]	91.44 [3.600]	36	37	3-146288-7
		5	91.03 [3.584]	88.90 [3.500]	35	36	3-146288-6
		5	88.49 [3.484]	86.36 [3.400]	34	35	3-146288-5
		5	85.95 [3.384]	83.82 [3.300]	33	34	3-146288-4
		5	83.41 [3.284]	81.28 [3.200]	32	33	3-146288-3
		5	80.87 [3.184]	78.74 [3.100]	31	32	3-146288-2
		5	78.33 [3.084]	76.20 [3.000]	30	31	3-146288-1
		5	75.79 [2.984]	73.66 [2.900]	29	30	3-146288-0
		5	73.25 [2.884]	71.12 [2.800]	28	29	2-146288-9
		5	70.71 [2.784]	68.58 [2.700]	27	28	2-146288-8
		5	68.17 [2.684]	66.04 [2.600]	26	27	2-146288-7
		5	65.63 [2.584]	63.5 [2.500]	25	26	2-146288-6
		5	63.09 [2.484]	60.96 [2.400]	24	25	2-146288-5
		5	60.55 [2.384]	58.42 [2.300]	23	24	2-146288-4
		5	58.01 [2.284]	55.88 [2.200]	22	23	2-146288-3
		5	55.47 [2.184]	53.34 [2.100]	21	22	2-146288-2
		5	52.93 [2.084]	50.80 [2.000]	20	21	2-146288-1
		5	50.39 [1.984]	48.26 [1.900]	19	20	2-146288-0
		5	47.85 [1.884]	45.72 [1.800]	18	19	1-146288-9
		5	45.31 [1.784]	43.18 [1.700]	17	18	1-146288-8
		5	42.77 [1.684]	40.64 [1.600]	16	17	1-146288-7
		5	40.23 [1.584]	38.10 [1.500]	15	16	1-146288-6
		5	37.69 [1.484]	35.56 [1.400]	14	15	1-146288-5
	5	35.15 [1.384]	33.02 [1.300]	13	14	1-146288-4	
	5	32.61 [1.284]	30.48 [1.200]	12	13	1-146288-3	
8	SUPERSEDED	5	30.07 [1.184]	27.94 [1.100]	11	12	1-146288-2
8 OBSOLETE		5	27.53 [1.084]	25.40 [1.000]	10	11	1-146288-1
		5	24.99 [.984]	22.86 [.900]	9	10	1-146288-0
8	SUPERSEDED	5	22.45 [.884]	20.32 [.800]	8	9	1-146288-9
8 OBSOLETE		5	19.91 [.784]	17.78 [.700]	7	8	1-146288-8
		5	17.37 [.684]	15.24 [.600]	6	7	1-146288-7
8	SUPERSEDED	5	14.83 [.584]	12.70 [.500]	5	6	1-146288-6
		5	12.29 [.484]	10.16 [.400]	4	5	146288-5
8	OBSOLETE	5	9.75 [.384]	7.62 [.300]	3	4	1-146288-4
8	SUPERSEDED	5	7.21 [.284]	5.08 [.200]	2	3	1-146288-3
SUPERSEDED BY 146264-1			4.67 [.184]	2.54 [.100]	1	2	146288-2
	OBSOLETE		2.13 [.084]	- [-]	0	1	146288-1
		PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 12/6/95 T. HOFFMAN CHK. 2/1/96 G. DUBNICKI APP'D. 2/1/96 G. DUBNICKI	 TE Connectivity		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW HIGH TEMPERATURE, VERTICAL WITH RETENTION FEATURE, W/025 SQ. POSTS, .100 C/L			
	0 PL/C ± — 1 PL/C ± — 2 PL/C ± — 3 PL/C ± — 4 PL/C ± — ANGLES ± —	PRODUCT SPEC APPLICATION SPEC	SIZE A1	GAGE CODE 00779	
	MATERIAL 	FINISH SEE TABLE	WEIGHT —	DRAWING NO C=146288	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV