


4

3

2

1

LOC	DIST	REVISIONS				
G	02	P	LTR	DESCRIPTION	DATE	APVD
			A1	REV PER ECR 10-004261	25FEB10	JR TM



- 1 STAMP "AMP 24-20", LOCATED APPROX AS SHOWN ON BOTTOM OF PART.
- 2 FOR INSULATION DIA OF .040 TO .100 DIA.
- 3 MATERIAL
BODY: COPPER PER ASTM B-152
ANNEALED
SLEEVE: COPPER PER ASTM B-152
INSULATION: NYLON
- 4 FINISH
BODY: TIN PLATE PER ASTM B-545
SLEEVE: TIN PL PER ASTM B-545
INSULATION - COLOR-TRANSLUCENT
- 5 APPLIES FROM EDGE OF MEATL WIRE BARREL TO CENTER OF STUD HOLE.

150493

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 25FEB10	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK TOM MICHIELUTTI 25FEB10				
		APVD TOM MICHIELUTTI 25FEB10	NAME WIRE TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 24-20			
		PRODUCT SPEC	—			
MATERIAL — 3		APPLICATION SPEC	—			
		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-150493	RESTRICTED TO —
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .008 4 PLC ± — ANGLES ± 5° FINISH		CUSTOMER DRAWING				
— 4		SCALE 6:1 SHEET 1 OF 1 REV A1				