



Micro Commercial Components



Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

## SR208 THRU SR2010

### Features

- Halogen free available upon request by adding suffix "-HF"
- Guard Ring Protection
- Low Power Loss for High Efficiency
- Lead Free Finish/RoHS Compliant (Note1) ("P" Suffix designates Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

### Maximum Ratings

- Operating Temperature: -50°C to +125°C
- Storage Temperature: -50°C to +125°C
- Maximum Thermal Resistance: 35°C/W Junction To Ambient

MCC catalog Number	Device Marking	Maximum Reccurent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
SR208	SR208	80V	56V	80V
SR2010	SR2010	100V	70V	100V

### Electrical Characteristics @ 25°C Unless Otherwise Specified


Average forward current	$I_{F(AV)}$	2A	
Maximum surge current	$I_{FSM}$	50A	8.3ms, half sine,
Max peak forward voltage	$V_{FM}$	.85V	$I_{FM} = 2.0A; T_J = 25^\circ C^*$
Max peak reverse current	$I_{RM}$	1.0mA	$V_{RRM}, T_J = 25^\circ C$
Typical junction capacitance	$C_J$	170pF	$V_R = 4.0V$ $f = 1.0MHz$

\*Pulse test: Pulse width 300  $\mu$ sec, Duty cycle 2%

Note: 1. High Temperature Solder Exemption Applied, see EU Directive Annex 7.

## 2 Amp Schottky Barrier Rectifier 80 to 100 Volts

### DO-41



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.166	.205	4.10	5.20	
B	.080	.107	2.00	2.70	
C	.028	.034	.70	.90	
D	1.000	---	25.40	---	

[www.mccsemi.com](http://www.mccsemi.com)

Revision: A

2013/01/01

# SR208 thru SR2010




Fig. 1-FORWARD CURRENT DERATING CURVE




Fig. 2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




Fig. 3-TYPICAL REVERSE CHARACTERISTICS




Fig. 4-TYPICAL JUNCTION CAPACITANCE




Fig. 5-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT

## Ordering Information :

Device	Packing
Part Number-TP	Tape&Reel: 5Kpcs/Reel
Part Number-AP	Ammo Packing: 5Kpcs/Ammo Box
Part Number-BP	Bulk: 50Kpcs/Carton

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.