




FRONT SHELL






INSERTED BODY



REAR SHELL



ASSEMBLED PLUG



PLUG SPECIFICATIONS:

SHELL: MAT'L- STEEL

FINISH- NICKEL PLATE

CONTACT: MAT'L- PHOSPHOR BRONZE

FINISH- GOLD FLASH OVER NICKEL

INSULATION: MAT'L- THERMOPLASTIC, UL 94V-0

ELECTRICAL CHARACTERISTICS:

RATED VOLTAGE: 30V (RMS)

CONTACT CURRENT RATING: 1.8 Amp DC MAX.


CONTACT RESISTANCE: 50m Ω max.

DIELECTRIC WITHSTANDING VOLTAGE: AC 100 V R.M.S.

MECHANICAL CHARACTERISTICS:

OPERATING TEMPERATURE: -13°F (-25°C) TO 176°F (+80°C)

DURABILITY: 1500 CYCLES MIN.



DATE		DESCRIPTION		REV.
6.01.11		CHANGE AS PER ECN 11-076		A
3.26.15		CHANGE AS PER ECN 15-040 B1 WAS 1.008 [25.60]		B

KEYSTONE ELECTRONICS CORP.				
www.keystecorp.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900				
PART NAME				
USB 3.0 MICRO PLUG				
MATERIAL				
AS NOTED				
FINISH				
AS NOTED		DRN BY	NT	DATE
		App'D	LN	SCALE
		1.5X		
TOLERANCES		INCH	[MM]	CODE
DECIMAL		± .010	[± 0.25]	C
ANGULAR		± 1°		
UNLESS OTHERWISE SPECIFIED				