


## N-CHANNEL ENHANCEMENT-MODE POWER MOSFET

Low gate charge  
Simple drive requirement  
Fast switching




$BV_{DSS}$  30V  
 $R_{DS(ON)}$  17m $\Omega$   
 $I_D$  40A

### Description

Power MOSFETs from Silicon Standard provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-220 package is widely preferred for commercial and industrial applications and suited for low voltage applications such as DC/DC converters and high efficiency switching circuits.



### Absolute Maximum Ratings

| Symbol                        | Parameter                                       | Rating     | Units               |
|-------------------------------|-------------------------------------------------|------------|---------------------|
| $V_{DS}$                      | Drain-Source Voltage                            | 30         | V                   |
| $V_{GS}$                      | Gate-Source Voltage                             | $\pm 20$   | V                   |
| $I_D @ T_C=25^\circ\text{C}$  | Continuous Drain Current, $V_{GS} @ 10\text{V}$ | 40         | A                   |
| $I_D @ T_C=100^\circ\text{C}$ | Continuous Drain Current, $V_{GS} @ 10\text{V}$ | 30         | A                   |
| $I_{DM}$                      | Pulsed Drain Current <sup>1</sup>               | 169        | A                   |
| $P_D @ T_C=25^\circ\text{C}$  | Total Power Dissipation                         | 50         | W                   |
|                               | Linear Derating Factor                          | 0.4        | W/ $^\circ\text{C}$ |
| $T_{STG}$                     | Storage Temperature Range                       | -55 to 150 | $^\circ\text{C}$    |
| $T_J$                         | Operating Junction Temperature Range            | -55 to 150 | $^\circ\text{C}$    |

### Thermal Data

| Symbol | Parameter                                | Value | Unit               |
|--------|------------------------------------------|-------|--------------------|
| Rthj-c | Thermal Resistance Junction-case Max.    | 2.5   | $^\circ\text{C/W}$ |
| Rthj-a | Thermal Resistance Junction-ambient Max. | 62    | $^\circ\text{C/W}$ |

**Electrical Characteristics @  $T_j=25^{\circ}\text{C}$  (unless otherwise specified)**

| Symbol                       | Parameter                                                  | Test Conditions                               | Min. | Typ.  | Max.      | Units                |
|------------------------------|------------------------------------------------------------|-----------------------------------------------|------|-------|-----------|----------------------|
| $BV_{DSS}$                   | Drain-Source Breakdown Voltage                             | $V_{GS}=0V, I_D=250\mu A$                     | 30   | -     | -         | V                    |
| $\Delta BV_{DSS}/\Delta T_j$ | Breakdown Voltage Temperature Coefficient                  | Reference to $25^{\circ}\text{C}$ , $I_D=1mA$ | -    | 0.037 | -         | $V/^{\circ}\text{C}$ |
| $R_{DS(ON)}$                 | Static Drain-Source On-Resistance                          | $V_{GS}=10V, I_D=20A$                         | -    | 14    | 17        | $m\Omega$            |
|                              |                                                            | $V_{GS}=4.5V, I_D=16A$                        | -    | 20    | 23        | $m\Omega$            |
| $V_{GS(th)}$                 | Gate Threshold Voltage                                     | $V_{DS}=V_{GS}, I_D=250\mu A$                 | 1    | -     | 3         | V                    |
| $g_{fs}$                     | Forward Transconductance                                   | $V_{DS}=10V, I_D=20A$                         | -    | 26    | -         | S                    |
| $I_{DSS}$                    | Drain-Source Leakage Current ( $T_j=25^{\circ}\text{C}$ )  | $V_{DS}=30V, V_{GS}=0V$                       | -    | -     | 1         | $\mu A$              |
|                              | Drain-Source Leakage Current ( $T_j=150^{\circ}\text{C}$ ) | $V_{DS}=24V, V_{GS}=0V$                       | -    | -     | 25        | $\mu A$              |
| $I_{GSS}$                    | Gate-Source Leakage                                        | $V_{GS}= \pm 20V$                             | -    | -     | $\pm 100$ | nA                   |
| $Q_g$                        | Total Gate Charge <sup>2</sup>                             | $I_D=20A$                                     | -    | 17    | -         | nC                   |
| $Q_{gs}$                     | Gate-Source Charge                                         | $V_{DS}=24V$                                  | -    | 3     | -         | nC                   |
| $Q_{gd}$                     | Gate-Drain ("Miller") Charge                               | $V_{GS}=5V$                                   | -    | 10    | -         | nC                   |
| $t_{d(on)}$                  | Turn-on Delay Time <sup>2</sup>                            | $V_{DS}=15V$                                  | -    | 7.2   | -         | ns                   |
| $t_r$                        | Rise Time                                                  | $I_D=20A$                                     | -    | 60    | -         | ns                   |
| $t_{d(off)}$                 | Turn-off Delay Time                                        | $R_G=3.3\Omega, V_{GS}=10V$                   | -    | 22.5  | -         | ns                   |
| $t_f$                        | Fall Time                                                  | $R_D=0.75\Omega$                              | -    | 10    | -         | ns                   |
| $C_{iss}$                    | Input Capacitance                                          | $V_{GS}=0V$                                   | -    | 800   | -         | pF                   |
| $C_{oss}$                    | Output Capacitance                                         | $V_{DS}=25V$                                  | -    | 380   | -         | pF                   |
| $C_{rss}$                    | Reverse Transfer Capacitance                               | $f=1.0MHz$                                    | -    | 133   | -         | pF                   |

**Source-Drain Diode**

| Symbol   | Parameter                                         | Test Conditions                              | Min. | Typ. | Max. | Units |
|----------|---------------------------------------------------|----------------------------------------------|------|------|------|-------|
| $I_S$    | Continuous Source Current ( Body Diode )          | $V_D=V_G=0V, V_S=1.3V$                       | -    | -    | 40   | A     |
| $I_{SM}$ | Pulsed Source Current ( Body Diode ) <sup>1</sup> |                                              | -    | -    | 169  | A     |
| $V_{SD}$ | Forward On Voltage <sup>2</sup>                   | $T_j=25^{\circ}\text{C}, I_S=40A, V_{GS}=0V$ | -    | -    | 1.3  | V     |

**Notes:**

- 1.Pulse width limited by safe operating area.
- 2.Pulse width  $\leq 300\mu s$  , duty cycle  $\leq 2\%$ .




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics





Fig 3. On-Resistance v.s. Gate Voltage


 Fig 4. Normalized On-Resistance  
 vs. Junction Temperature




Fig 5. Maximum Drain Current vs. Case Temperature




Fig 6. Typical Power Dissipation




Fig 7. Maximum Safe Operating Area








Fig 8. Effective Transient Thermal Impedance






Fig 13. Switching Time Circuit




Fig 14. Switching Time Waveform




Fig 15. Gate Charge Circuit




Fig 16. Gate Charge Waveform

Information furnished by Silicon Standard Corporation is believed to be accurate and reliable. However, Silicon Standard Corporation makes no guarantee or warranty, express or implied, as to the reliability, accuracy, timeliness or completeness of such information and assumes no responsibility for its use, or for infringement of any patent or other intellectual property rights of third parties that may result from its use. Silicon Standard reserves the right to make changes as it deems necessary to any products described herein for any reason, including without limitation enhancement in reliability, functionality or design. No license is granted, whether expressly or by implication, in relation to the use of any products described herein or to the use of any information provided herein, under any patent or other intellectual property rights of Silicon Standard Corporation or any third parties.