





断面 A-A
SECT. A-A



断面 B-B
SECT. B-B



注記 NOTES:

l. 適合ハウジング:
APPLICABLE HOUSING: 5||9|-**00

錫メッキ済リン青銅 PRE-TINNED PHOS-BRO.	50802-8100	バラ状 LOOSE
錫メッキ済リン青銅 PRE-TINNED PHOS-BRO.	50802-8000	連鎖状 CHAIN
錫メッキ済黄銅 PRE-TINNED BRASS	50802-9101	バラ状 LOOSE
錫メッキ済黄銅 PRE-TINNED BRASS	50802-9001	連鎖状 CHAIN
材料 MATERIAL	MATERIAL NO.	端子形状 FORM

MODEL NO. 50802-****		DIMENSIONS:		SHT	REV
DESIGN UNITS	 THIRD ANGLE PROJECTION	☐ mm ☐ INCH	☐ mm ONLY	REVISE ON CAD ONLY	
☒ mm ☐ INCH					

5	DRAWN BY & DATE S.MATSUZAKI 98/4/9 CHECKED BY & DATE K. INATSUKI 98/4/10	TITLE: 2.5 WIRE TO BOARD CONN. CRIMP RECEPTACLE
---	---	---

APPROVED BY & DATE M.FUKUSHIMA 98/4/10		MOLEX MOLEX INCORPORATED	
CAD FILENAME 50802002.S01	MATERIAL NO. 50802-****	DRAWING NO. SD-50802-002	SHEET NO. 1/1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

P84NO. DRWN: CH'K: APPR:	P83NO. DRWN: CH'K: APPR:	P82NO. DRWN: CH'K: APPR:	P81NO. DRWN: CH'K: APPR:	RELEASED P80NO. JC80766 DRWN: S.MATSUZAKI '98/4/9 CH'K: S.KUNISHI '98/4/10 APPR: M.FUKUSHIMA '98/4/10	DESCRIPTION MATERIAL 材料 表参照 (t=0.203) SEE TABLE	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	
						10 UNDER 未満	+0.2
						10 OVER 以上	30 UNDER 未満 +0.2
						30 OVER 以上	+0.3
INS. RANGE 被覆外径	WIRE RANGE 適用電線規格 AWG #22~#28 0.33~0.08mm ²		ANGLE 角度	+3°			
					Ø 1.15 ~ 1.9		