

Linear codec IC for digital cellular telephones

BU8730KV

The BU8730KV is a linear codec IC developed for use with digital cellular telephones. It contains a 14-bit precision linear codec and various other analog input / output features.

Also, there is a built-in DAI and many tone signal functions making this IC perfect for use with GSM cellular telephones.

● Applications

Digital cellular telephones

● Features

- 1) +3V single power supply ($V_{DD} = 2.7V$ to $3.3V$).
- 2) Low current consumption of $8.2mA$ (typ.) when fully operating and $20\ \mu A$ (max.) when powered down ($V_{DD} = 3V$).
- 3) Built-in 14-bit precision linear codec.
- 4) Transmission filter for the codec unit conforms to ITU-T recommendation G.714.
- 5) DTMF signal, GSM triple tone, and scale tone signal generator functions are built into the tone signal generator block.
- 6) Signal generator and output level adjustment circuits are built in with the sounder output functions.
- 7) Built-in PLL circuit for system clock generation.
- 8) Analog input / output functions:
 - Built-in mic amplifier with gain switching capabilities.
 - Data signal I / O circuit allows for connection to external devices.
 - Receiver output, ringer output, and EXT output are soft mute compatible.
- 9) Internal DAI (digital audio interface) with GSM11.10 support.
- 10) Internal DSP interface circuit supports multiple DSP formats.
- 11) VQFP 48-pin package.

● Absolute maximum ratings ($T_a = 25^\circ C$)

Parameter	Symbol	Limits	Unit
Digital power supply voltage	DV_{DD}	$-0.3 \sim +4.5$	V
Analog power supply voltage	RXV_{DD}	$-0.3 \sim +4.5$	V
	TXV_{DD}	$-0.3 \sim +4.5$	V
Digital input voltage	V_{DIN}	$DV_{SS} \sim DV_{DD} + 0.3$	V
Analog input voltage	V_{AIN}	$RXGND \sim RXV_{DD} + 0.3$	V
		$TXGND \sim TXV_{DD} + 0.3$	V
Input current	I_{IN}	$-10 \sim +10$	mA
Power dissipation	P_d	400^*1	mW
Operating temperature	T_{stg}	$-50 \sim +125$	°C
Storage temperature	T_{opr}	$-30 \sim +85$	°C


*1 Reduced by $4.0mW$ for each increase in T_a of $1^\circ C$ over $25^\circ C$.

● Recommended operating conditions (Ta = 25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit
Digital power supply voltage	DV _{DD}	2.7	—	3.3	V
Analog power supply voltage	RXV _{DD}	2.7	—	3.3	V
	TXV _{DD}	2.7	—	3.3	V
PLL sync signal frequency	FSY	—	8	—	kHz

◎Not designed for radiation resistance.

● Block diagram



● Pin descriptions

Pin No.	Pin name	I / O	Function
1	BUZZER	O	Rectangular wave output for each tone pattern
2	TNIN	I	Tone output gain control amplifier inverse input
3	TNO	O	Tone output gain control amplifier output
4	RINGER	O	Tone waveform output
5	REXTIN	I	Reception external signal input
6	REXTOUT	O	Reception external signal output
7	RECO	O	Reception signal output
8	RECPRI	I	Receiver gain control amplifier inverse input
9	RECPRO	O	Receiver gain control amplifier output
10	RECON	O	Receiver amplifier inverse output
11	RECOP	O	Receiver amplifier non-inverse output
12	RXGND	—	Analog ground for reception
13	RXV _{DD}	—	Analog power supply for reception
14	RXCOM	O	Analog reference voltage output for reception
15	REFCOM	O	Reference voltage output for internal reference
16	COMIN	O	Analog reference voltage output
17	TXCOM	O	Analog reference voltage output for transmission
18	MICIP	I	Mic amplifier non-inverse input
19	MICIN	I	Mic amplifier inverse input
20	MICO1	O	Mic amplifier output 1
21	MICO2	O	Mic amplifier output 2
22	TXV _{DD}	—	Analog power supply for transmission
23	TXGND	—	Analog ground for transmission
24	N.C.	—	—
25	TEXTIN	I	Transmission external input
26	TEXTOUT	O	Transmission external output
27	PLLLPF	I / O	Input / output connection for PLL filter
28	TESTB	I	Test input (\rightarrow DV _{DD})
29	FSYNC	I	PLL reference 8kHz clock input
30	CPUSTR	I	CPU I / F strobe input
31	CPUCLK	I	CPU I / F shift clock input
32	CPUDATA	I	CPU I / F address data input
33	RESETB	I	System reset input (L: reset)
34	TC2	I	DAI test input
35	TC1	I	DAI test input
36	DRSTB	I	DAI reset input
37	DV _{SS}	—	Digital ground
38	DV _{DD}	—	Digital power supply
39	DI	I	Digital serial data input

Pin No.	Pin name	I/O	Function			
40	DO	O	DAI serial data output			
41	DCLK	O	DAI shift clock output			
42	DSPREQB	I	DSP serial data request input			
43	DSPIN	I	DSP serial data input			
44	DSPOUT	O	DSP serial data output			
45	DSPEB	O	DSP serial data enable output			
46	DSPCLK	O	DSP serial data clock output			
47	BPULSE	O	Tone pattern intermittent output			
48	MUTE _τ	I	Connector for capacitor for soft mute setting			

- Electrical characteristics (unless otherwise noted, Ta = 25°C, DV_{DD} = RXV_{DD} = TXV_{DD} = 3.0V, FSYNC = 8kHz, gain of each attenuator = 0dB)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions	
⟨DC characteristicss⟩							
Current consumption*1	I _{DD}	—	8.2	—	mA	All power on	FSYNC=8kHz
	I _{DD1}	—	0.1	20	μA	Complete power down	FSYNC pin fixed
Digital input high level voltage	I _{DD2}	0.8DV _{DD}	—	—	V	—	—
Digital input low level voltage	I _{DD3}	—	—	0.2DV _{DD}	V	—	—
Digital input high level current	I _{IH}	—	—	10	μA	V _{IH} =DV _{DD}	
Digital input low level current	I _{IL}	—10	—	—	μA	V _{IL} =0V	
Digital output high level voltage	V _{OH}	DV _{DD} —0.5	—	—	V	I _{OH} =—1mA	
Digital output low level voltage	V _{OL}	—	—	0.5	V	I _{OL} =1mA	

*1 The power supply voltage (DV_{DD}, RXV_{DD}, and TXV_{DD}) is 3V. There is no load on the digital and analog output pins.

Digital input pins other than the FSYNC pin are connected to DV_{DD} or DV_{SS}.

Analog input pins are connected to TXCOM or RXCOM with the proper resistance.

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions		
⟨Transmission characteristics⟩								
Signal to total power distortion ratio (A→D) TEXTIN→DSPOUT	S _{DT}	24	—	—	dB	1020Hz reference	—45dBm0	
		29	—	—			—40dBm0	
		35	—	—			0, —30dBm0	
Signal to total power distortion ratio (D→A) DSPIN→RECO	S _{DR}	24	—	—	dB	1020Hz reference	—45dBm0	
		29	—	—			—40dBm0	
		35	—	—			0, —30dBm0	
Transmission level characteristics (A→D) TEXTIN→DSPOUT	G _{TX}	—0.9	—	0.9	dB	1020Hz reference	—55dBm0	
		—0.6	—	0.6			—50dBm0	
		—0.3	—	0.3			0, —40dBm0	
Transmission level characteristics (D→A) DSPIN→RECO	G _{TR}	—0.9	—	0.9	dB	1020Hz reference	—55dBm0	
		—0.6	—	0.6			—50dBm0	
		—0.3	—	0.3			0, —40dBm0	
Transmission output level	V _{OTX}	—	0.395	—	V _{rms}	1020Hz, 0dBm0 input reference	MICO1 →DSPOUT	Set the MIC1 level to 0dB
		—	0.125	—			TEXTIN →DSPOUT	Set the TESTIN level to 0dB
Reception output level	V _{ORX}	—	0.346	—	V _{rms}	1020Hz, 0dBm0 input reference	DSPIN →REXTOUT	—
		—	0.346	—			DSPIN →RECOP RECOM	When RECO→ RECOP—6dB
Transmission loss frequency characteristics (A→D) TEXTIN→DSPOUT	G _{RX}	24	—	—	dB	1020Hz, 0dBm0 input reference	0.06kHz	—
		0	—	2.5			0.2kHz	
		—0.3	—	0.3			0.3~3.0kHz	
		—0.3	—	0.9			3.4kHz	
		0	—	—			3.6kHz	
		6.5	—	—			3.78kHz	
Transmission loss frequency characteristics (D→A) DSPIN→RECO	G _{RR}	—0.3	—	0.3	dB	1020Hz, 0dBm0 input reference	0.0~3.0kHz	—
		—0.3	—	0.9			3.4kHz	
		0	—	—			3.6kHz	
		6.5	—	—			3.78kHz	

Parameter		Symbol	Min.	Typ.	Max.	Unit	Conditions		
⟨Tone generator⟩									
Tone output level	HTONE	V _{TNH}	−10.4	−8.9	−7.4	dBm	Set at 2kHz	→RINGER	
			−10.9	−8.9	−6.9	dBm		→REXTOUT	
	HTONE ATONE	V _{TNL}	−12.6	−11.1	−9.6	dBm		→RINGER	
								C-Wgt 0dBm=0.775V _{rms}	
Tone loss		G _{LOSS}	15	18	21	dB	HTONE set at 2kHz	→RINGER	
Tone distortion		S _{DTN}	—	—	−29	dB	HTONE set at 2kHz	→RINGER	
⟨Attenuator⟩									
Gain error	ATT1	ΔATT1	—	—	±0.6	dB	1020Hz input	→DSPOUT	
	ATT2	ΔATT2	—	—	±2	dB		→RECO	
	ATT3	ΔATT3	—	—				→REXTOUT	
	ATT4	ΔATT4	—	—	±0.8	dB	Set at 2kHz	→RINGER	
	ATT5	ΔATT5	—	—	±0.1	V	—	→BUZZER	
	ATT6	ΔATT6	—	—	±0.8	dB	1020Hz input	→RECO	
	ATT7	ΔATT7	—	—				→REXTOUT	
⟨PLL block⟩									
PLL lead-in time		T _{PL}	—	5	100	msec	—		

●Digital AC characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
⟨Serial data interface / timing⟩					
DSPCLK frequency	f _{SCK}	—	256	—	kHz
DSPREQB input setup time	t _{SUR}	3.0	—	—	μs
DSPREQB input hold time	t _{HTR}	3.0	—	—	μs
DSPIN input setup time	t _{SUS}	100	—	—	ns
DSPIN input hold time	t _{HTS}	100	—	—	ns
DSPEB low pulse width	t _{WEN}	5.0	—	—	μs
DSPREQB scan internal clock frequency	t _{REX}	—	8	—	kHz
⟨Register write timing⟩					
CPUCLK frequency	f _{CLK}	—	—	3	MHz
CPUDATA input setup time	t _{SUDA}	100	—	—	ns
CPUDATA input hold time	t _{HHTDA}	100	—	—	ns
Input setup time (CPUCLK high vs. CPUSTR high)	t _{SUD}	333	—	—	ns
Input hold time (CPUCLK high vs. CPUSTR low)	t _{HTD}	1000	—	—	ns
CPUSTR strobe pulse width	f _{PWD}	667	—	—	ns
⟨DAI timing⟩					
DCLK frequency	f _{DCLK}	—	104	—	kHz
DCLK low pulse width	t _{WDCL}	3.8	4.8	5.8	μs
DCLK high pulse width	t _{WDCH}	3.8	4.8	5.8	μs
DRSTB low pulse width	t _{WDR}	4	—	—	ms
DI input setup time	t _{SUDI}	100	—	—	ns
DI input hold time	t _{HIDI}	100	—	—	ns

● Measurement circuit




Fig.1

● Application example





Fig.2

● External dimensions (Units: mm)



VQFP48

Appendix

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document use silicon as a basic material.

Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.