




NOTES:

- MATERIAL: NYLON 6/6 UL94 V-2 (RMS-01).
 - NYLON 6/6 UL94 V-0 (RMS-19), AVAILABLE BY SPECIAL ORDER. TO ORDER REPLACE "-01" WITH "-19"
 - NYLON 4/6 UL94 V-2 (RMS-109), AVAILABLE BY SPECIAL ORDER. TO ORDER REPLACE "-01" WITH "-109".
- COLOR: NATURAL

PART NO.	"B"	MAX. BUNDLE DIA. "C" LOCKED	BOARD THICKNESS RANGE
*SLCSE-250	.57 (14.5)	.22 (5.6)	1/32-5/64 (0.8-2.0)
SLCSE-370	.71 (18.0)	.35 (8.9)	
SLCSE-500	.83 (21.0)	.47 (12.0)	
SLCSE-750	1.08 (27.5)	.73 (18.4)	
*SLCSE2-250	.57 (14.5)	.22 (5.6)	5/64-5/32 (2.0-4.0)
SLCSE2-370	.71 (18.0)	.35 (8.9)	
SLCSE2-500	.83 (21.0)	.47 (12.0)	
SLCSE2-750	1.08 (27.5)	.73 (18.4)	


PART NO. CODE

SLCSE - 500 - 8 - 01

| | | |
 PART# SIZE "A" MAT'L

SUFFIX	"A" ±.015(0.4)
-3	3/16(4.8)
-4	1/4(6.4)
-6	3/8(9.5)
-8	1/2(12.7)
*-10	5/8(15.9)
*-12	3/4(19.1)
*-14	7/8(22.2)
*-16	1.0(25.4)

*PARTS AVAILABLE BY SPECIAL ORDER ONLY

			TITLE: STANDOFF LOCK CLIP SERIES						DWG IN IN (MM)	
D	SEE CO 200473 FOR CHANGES	SK 12.03.09	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # SLCSE	DWN: J.B.	APP:	FINAL			
C	SEE ECN #914 FOR CHANGES	SK 01.14.05		MAT'L: SEE NOTES	DT: 02-13-96	DT:	PART #	SEE CHART	PRINT TYPE CA	
B	SEE ECN #818 FOR CHANGES	SM 10.01.04	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060						
A	CHANGED FILE NUMBER	SM 05.31.01								
REV	DESCRIPTION	ENGR DATE								