







PRODUCT NO.
10071375-001LF



rev	ecn no	dr	date
A	S07-0075	HKL	2007-03-13
B	S08-0135	HKL	2008-05-05
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ASME Y14.5	tolerance std ASME Y14.5	projection	MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	HK LIM	2006-09-01	ANGULAR 0° ±2°	0.X ±0.25	size	Scale
Eng	HK LIM	2008-05-05		0.XX ±0.20	A4	2:1
Chr	HK LIM	2008-05-05		0.XXX ±0.050	ECN	S08-0135
Appr	JOEY NG	2008-05-05	Product family			Spec ref
FCI			title SAS PLUG VERTICAL SMT ASSY			Rev. B
			catalog no			dwg no 10071375
						sheet 1 of 2




REV E - 2006-03-28

PDM: Rev:B

STATUS: Released



Printed: Dec 01, 2010

PRODUCT NO.	WITH PICK-UP CAP	PACKAGING
10071375-001LF	NO	TRAY
10071375-001CLF	YES	



NOTES:

1. MATERIAL:
HOUSING & CAP: HIGH TEMPERATURE PLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY
HOLD DOWN: COPPER ALLOY
2. FINISH:
1.27um MIN NICKEL UNDERPLATE OVERALL,
2.54um MIN TIN (LEAD-FREE) ON SOLDER TAIL,
0.76um MIN GOLD ON CONTACT AREA
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN
5. PART WITH PICK-UP CAP, P/N. XXXXXXXX-XXXCLF
6. A SYMBOL B WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH
HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION



title
SAS PLUG
VERTICAL SMT ASSY
catalog no

dwg no
10071375

Rev.
B

CUSTOMER sheet 2 of 2