






NOTES:

1. MATERIALS OF CONSTRUCTION:
HOUSING & CONTACT PIN = BRASS, GOLD PLATED
BODY = BERYLLIUM COPPER, GOLD PLATED
FERRULE = COPPER, GOLD PLATED
INSULATOR = TEFLON, MIL-P-19468
2. CRIMPED FERRULE = HEX CRIMP SIZE .128
3. ELECTRICAL DATA:
VSWR = 1.05 MAX TO 1 GHz
1.15 MAX TO 6 GHz
INSERTION LOSS = .05 dB MAX TO 1 GHz
(MATED PAIR) = .15 dB MAX TO 6 GHz

919-137P-7ISX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	5/31/00	43382	CPM



SCALE 3.500



RECOMMENDED CABLE
STRIPPING DIMENSIONS
SCALE 3.000

CUSTOMER OUTLINE DRAWING
FOR REFERENCE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 0.5 - 6mm ±0.2mm	MATERIAL	DRAWN C. McGRATH	DATE 16-May-00	TITLE MCX (M) CRIMP FOR RG-179/U	Amphenol Amphenol Corporation Communication and Network Products Division Danbury, CT U.S.A. 06810		
		ENGINEER T. AUBIN	DATE 16-May-00				
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE GEN# 919-137P-7ISX_ASSY	APPROVED 	DATE 5/31/00	SCALE: 7.0:1 SHEET 2 OF 2			
		CAD FILE I:\MCX\919-137P-7ISX					CODE ID 74868