







THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA			SCALE	FULL
OPERATING FORCE — — — — 6-10 LB		CONTACT ARRANGEMENT			DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE — — 30 LB MAX		S P D T (2)			UNLESS OTHERWISE NOTED	
RELEASE FORCE — — — — — 4 LB MIN		LOAD	28 VDC		DIMENSIONS ARE IN INCHES	
PRETRAVEL — — — — — .040 MAX			SEA LEVEL	50,000 FT.	TOLERANCES ARE:	
DIFFERENTIAL TRAVEL — — — — .020 MAX			RES	4	4	ONE PLACE (.0) ±.030
OVERTRAVEL — — — — — .250 MIN			IND	2	2	TWO PLACE (.00) ±.010
			MOTOR	4		THREE PLACE (.000) ±.000
		LAMP			ANGLES ±	WEIGHT 5.5 OZ MAX

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805, SYMBOL 4
- 3 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
- 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 6 - NOTED ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-S-8805/40-1 UP TO 185°F
- 7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805



- HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

121EN187-R

N

DRAWING
NUMBER

17

10

REVISIONS

A	CO 44351
---	-------------

GLH
8 FEB 80

B	CU47573
	PART 4
	R J H

14	AUG 80
C	CO47968

C 1047968
J A P
29 OCT 80

D	C048563
---	---------

25 KAG
FEB 83

E	C059459
	WIK

WJK
16 SEPT 86
F

F C068501
TSM
00 552 01

22 FEB 91
G C071719

LJF
3 JAN 92

H	CO- 82809A
---	---------------

JAK
31 JUL 96
CO-

J	83450
	C S L

3 APR 97	
----------	--

--	--

--	--

1

TEK
AWN

RM	DR
----	----

FO

FORMTEK