



NOTES:

1. SUGGESTED MOUNTING HOLE = ϕ .218
2. SOLDER PREFORM SUPPLIED AS HARDWARE.



LEAD FINISH:	-----
BUSHING FINISH:	SILVER
CAPACITANCE	470 $\pm$ 20%
TEMP. RANGE	-55°C TO 125°C
CURRENT	AMP MAX.
WORKING VOLTAGE	85°C VDC MAX. 125°C VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
10	N/A
100	N/A
1 GHz	N/A
10 GHz	N/A

SCHEMATIC



MARKING:

PART: NONE
BAG:
54-802-002-471M
376 MIN./564 MAX.
DATE CODE
QTY./BAG (200 MAX.)

	13	12	11	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api  FAIRVIEW PENNSYLVANIA	
					Fractions $\pm$ 1/64	Dwn. M WOJTECKI	Description FT
					Dec. .xx $\pm$	Date 2-04-14	CERAMIC FILTER
					Dec. .xxx $\pm$.015	Apvd.	
					Angles $\pm$ 0° 30'	Scale NONE	
					CODE IDENT. NO. DLSP2		54802002X5R471M
	CN #2069	CN. 210178	CN. 185173	CHANGE NOTICE			