


LOW LOSS SUPER HIGH SPEED RECTIFIER

Outline drawings, mm



Features

- Insulated package by fully molding
- Low V_F
- Super high speed switching
- High reliability by planer design


Applications

- High speed power switching

Maximum ratings and characteristics

- Absolute maximum ratings

Connection diagram



Item	Symbol	Conditions	Rating	Unit
Repetitive peak reverse voltage	V_{RRM}		300	V
Non-Repetitive peak reverse voltage	V_{RSM}		300	V
Isolating voltage	V_{iso}	Terminals-to-case, AC, 1 min.	1500	V
Average output current	I_o	Square wave, duty=1/2, $T_c=96^{\circ}C$	20*	A
Surge current	I_{FSM}	Sine wave 10ms	80	A
Operating junction temperature	T_j		-40 to +150	$^{\circ}C$
Storage temperature	T_{stg}		-40 to +150	$^{\circ}C$


*Average forward current of centertap full wave connection

- Electrical characteristics ($T_a=25^{\circ}C$ Unless otherwise specified)


Item	Symbol	Conditions	Max.	Unit
Forward voltage drop	V_{FM}	$I_{FM}=10A$	1.2	V
Reverse current	I_{RRM}	$V_R=V_{RRM}$	200	μA
Reverse recovery time	t_{rr}	$I_F=0.1A$, $I_R=0.2A$, $I_{rec}=0.05A$	40	ns
Thermal resistance	$R_{th(j-c)}$	Junction to case	2.0*	$^{\circ}C/W$

■ Characteristics


Forward characteristics




Reverse characteristics




Forward power dissipation




Reverse power dissipation




Output current-case temperature



Junction capacitance characteristics



Surge capability



Transient thermal impedance

