



CONTACT LAYOUT

4805 (3/11)

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

APPD

AD

00

1

15JUL05

15JUL05

15JUL05

1

2

3

4

5

6

7

8

9

10

11

12

13

MATERIAL:

CONTACT: PHOSPHOR BRONZE.

HOUSING: GLASS-FILLED POLYESTER.

GENERAL PLATING SPECIFICATION: UNDERPLATING

(ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION

PIN: 0.5µm MIN TIN.

FOR PLATING OF MATING SURFACES SEE APPLICABLE

SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101

PERFORMANCE LEVEL 2.

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101

PERFORMANCE LEVEL 1.

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,

CENTRAL OFFICE APPLICATIONS.

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,

UNCONTROLLED ENVIROMENT APPLICATIONS.

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.

ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,

MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID

PATTERN DEFINED BY CONTACT LAYOUT.

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".

TO BE MEASURED AT BOTTOM OF SHROUD.

CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,

TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

B. CARBO

15JUL05

CHK

G. SKIPPER

15JUL05

APPD

G. SKIPPER

15JUL05

DIMENSIONS:

mm

0-PLG

1-PLG

2-PLG

3-PLG

4-PLG

ANGLES

±0.2

MATERIAL

SEE SHEET 1

FINISH

SEE SHEET 1

WEIGHT

—

TE Connectivity

MALE ASSEMBLY, Z-PACK 2mm HM,

TYPE B

SIZE

A1

CAGE CODE

00779

DRAWING NO

5352033

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

4:1

SHEET

2

OF

2

REV

B