

# Coaxial Directional Coupler

50Ω

1 to 2000 MHz

ZFDC-10-5+

## Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

## Coaxial Connections

|         |   |
|---------|---|
| INPUT   | 1 |
| OUTPUT  | 2 |
| COUPLED | 3 |

## Features

- very wideband, 1 to 2000 MHz
- excellent directivity, 30 dB typ.
- rugged shielded case

## Applications

- cellular
- instrumentation
- communication receivers & transmitters
- GPS



BNC version shown


CASE STYLE: K18

| Connectors           | Model        |
|----------------------|--------------|
| BNC                  | ZFDC-10-5+   |
| SMA                  | ZFDC-10-5-S+ |
| N-TYPE               | ZFDC-10-5-N+ |
| BRACKET (OPTION "B") |              |

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Outline Drawing



## Outline Dimensions (inch)

| A     | B     | C     | D     | E     | F     | G    | H     |
|-------|-------|-------|-------|-------|-------|------|-------|
| 1.25  | 1.25  | .75   | .63   | .38   | 1.00  | .125 | 1.000 |
| 31.75 | 31.75 | 19.05 | 16.00 | 9.65  | 25.40 | 3.18 | 25.40 |
| J     | K     | L     | M     | N     | P     | Q    | wt    |
| --    | --    | .125  | 1.688 | 2.18  | .75   | .07  | grams |
| --    | --    | 3.18  | 42.88 | 55.37 | 19.05 | 1.78 | 70.0  |

## Directional Coupler Electrical Specifications




| FREQ.<br>RANGE<br>(MHz) | COUPLING<br>(dB)               |      | MAINLINE LOSS¹<br>(dB) |      |      |      |      |      | DIRECTIVITY<br>(dB) |      |      |      |      |      | VSWR<br>(:1) | POWER<br>INPUT<br>(W) |     |
|-------------------------|--------------------------------|------|------------------------|------|------|------|------|------|---------------------|------|------|------|------|------|--------------|-----------------------|-----|
|                         |                                |      | L                      |      | M    |      | U    |      | L                   |      | M    |      | U    |      |              |                       |     |
|                         | f <sub>L</sub> -f <sub>U</sub> | Nom. | Flatness               | Typ. | Max. | Typ. | Max. | Typ. | Max.                | Typ. | Min. | Typ. | Min. | Typ. | Min.         | Typ.                  | L   |
| 1-2000                  | 10.8±0.5                       | ±0.5 | 1.2                    | 1.9  | 1.2  | 1.8  | 1.8  | 2.5  | 38                  | 25   | 30   | 18   | 22   | 18   | 1.3          | 0.5                   | 0.5 |

L = low range [f<sub>L</sub> to 10 f<sub>L</sub>] M = mid range [10 f<sub>L</sub> to f<sub>U</sub>/2] U = upper range [f<sub>U</sub>/2 to f<sub>U</sub>]


1. Mainline loss includes theoretical power loss at coupled port.

## Typical Performance Data

| Frequency (MHz) | Mainline Loss (dB) In-Out | Coupling (dB) In-Cpl | Directivity (dB) | Return Loss (dB) |       |       |
|-----------------|---------------------------|----------------------|------------------|------------------|-------|-------|
|                 |                           |                      |                  | In               | Out   | Cpl   |
| 1.00            | 1.47                      | 11.03                | 47.08            | 14.55            | 18.01 | 18.03 |
| 40.00           | 1.13                      | 10.71                | 49.57            | 18.26            | 30.69 | 31.26 |
| 80.00           | 1.12                      | 10.70                | 47.38            | 18.32            | 30.20 | 30.46 |
| 260.00          | 1.20                      | 10.78                | 39.74            | 18.61            | 27.02 | 25.80 |
| 600.00          | 1.19                      | 10.77                | 31.82            | 18.79            | 22.14 | 19.98 |
| 1050.00         | 1.19                      | 10.73                | 26.87            | 18.84            | 19.38 | 15.98 |
| 1300.00         | 1.31                      | 10.81                | 25.29            | 18.83            | 18.76 | 14.75 |
| 1550.00         | 1.34                      | 10.96                | 23.98            | 18.70            | 17.75 | 13.90 |
| 1800.00         | 1.33                      | 11.08                | 22.06            | 17.99            | 15.32 | 13.15 |
| 2000.00         | 1.59                      | 11.68                | 19.78            | 16.91            | 12.53 | 12.52 |



## Electrical Schematic



\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TERMINATION THAT ROUTES DC FROM RF PORTS TO GROUND.

## Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCStore/terms.jsp](http://www.minicircuits.com/MCStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D  
M151107  
ZFDC-10-5+  
WZ/TD/CP/AM  
151007