



SYMBOL DEFINITION				MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	20			
	LAST NO. USED	40			


DWS STATUS				ZONE		REVISION HISTORY		AUTH	DR	AP/D	AP/D
DATE	STG	REV	N/P	CHG						1	2
25AU99	R	02	-	-			CLEARED REVISION COLUMN PART DRAWING UPDATED	196586	DRR	DRR	SAN
19OC99	R	03	-	-			ALL PARTS - REVISED GRAPHICS	196725	LMM	RMM	SAN
14JL03	R	04	-	-			ALL PARTS - REVISED CHART TO SHOW MATING TPA P/Ns; REVISED MATING COMPONENT NOTE, ADDED CPA P/N	242960	ADK	ADK	SAN
22SE05	R	05	-	-			13538370 & 13540547 - RELEASED	272748	LMB	LMB	BR
09MR06	R	06	-	-			ALL PARTS - TERMINAL 15304720 WAS 15304718; CABLE SEAL 15366067 WAS 12191232; 15326654 - 39.85 WAS 39.9; 29.02 +/-0.5 WAS 29; 15326660 - 46.37 WAS 46.4; 15326666 - 65.85 WAS 65.9; 15326910 - 52.85 WAS 52.9; 15326917 - 59.35 WAS 59.4; 13538370 - UPDATED PD ATTRIBUTES; 13540547 - REVISED DELPHI LOGO & VIEW TYPE LABEL	277561	MAC	MAC	SAN
26AP06	R	07	-	-			13540547 - 29.77 +0.37/-0.2 WAS 29.77	279991	JPH	FKV	RWR
17MY06	R	08	-	-			ALL PARTS - UPDATED PDM ATTRIBUTES; 15326654 - RESTRICTED AND ADDED REPLACED BY COLUMN IN CHART	280598	CCV	JVM	RWR
23MR07	R	09	-	-			15326654, 15326660, 15326666, 15326910 & 15326917 - UPDATED PDM ATTRIBUTES	400960	JBD	JVM	061




TYPE 110
SAME AS TYPE 108
EXCEPT AS SHOWN




TYPE 112
SAME AS TYPE 108
EXCEPT AS SHOWN





TYPE 114
SAME AS TYPE 108
EXCEPT AS SHOWN






TYPE 116
SAME AS TYPE 108
EXCEPT AS SHOWN




TYPE 208
SAME AS TYPE 108
EXCEPT AS SHOWN




TYPE 214
SAME AS TYPE 114
EXCEPT AS SHOWN



SECTION A - A



TYPE 108



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
ASSEMBLY CONNECTOR SEE CHART
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 15304720
CABLE SEAL 15366067
CONNECTOR POSITION ASSURANCE LOCK 15317832
TERMINAL POSITION ASSURANCE LOCK SEE CHART
- FOR MATING CONFIGURATION REQUIREMENTS SEE CHART
- SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAE/USCAR-2 CONNECTOR SYTEM ENVIRONMENTAL TEST FLOWCHART (PRESSURE/VACUUM AND SUBMERSTION).
- ALL ASSEMBLIES WILL EXCEED 80N MATING FORCE.

13540547	01	AB		214	13540546	PBT-0F20	BLACK	15326919 / ID406343	15326920 / ID406344	15326922 / ID406342		15336319	
13538370	01	AA		208	13534968	PBT-0F20	BLACK	15326652 / ID406319	15326653 / ID406320	15326655 / ID406321	15430896	15336316	
15326917 / ID406341	02	AD		114	15326916 / ID406345	PA6-6B20 0F10	BLACK	15326919 / ID406343	15326920 / ID406344	15326922 / ID406342		15336319	
15326910 / ID406335	02	AD		112	15326909 / ID406339	PA6-6B20 0F10	BLACK	15326912 / ID406337	15326913 / ID406338	15326915 / ID406336		15336318	
15326666 / ID406349	02	AD		116	15326662 / ID406350	PA6-6B20 0F10	BLACK	15326664 / ID406352	15326665 / ID406353	15326667 / ID406347		15336320	
15326660 / ID406334	02	AD		110	15326656 / ID406328	PA6-6B20 0F10	BLACK	15326658 / ID406332	15326659 / ID406332	15326661 / ID406329	15430900	15336317	
15326654 / ID406322	02	AE	RESTRICTED	108	15326650 / ID406317	PA6-6B20 0F10	BLACK	15326652 / ID406319	15326653 / ID406320	15326655 / ID406321	15430896	15336316	
												13538370	
PART NO	REV	N/P	STATUS	TYPE	CONN	MATERIAL RECYCLING CODE	COLOR	PLR	CONN SEAL	MATING CONN ASM	MATING TPA	CONFIG REQ INFORMATION	REPLACED BY

(N/A) PROCESS SENSITIVE DIMENSION										REFERENCE	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED											
DIMENSIONAL RANGE (MM)								CHART 1-1			
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2											
ANGULAR TOLERANCE 2°											

THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	

IMMAGINATIONS

DELPHI			
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE			
WYOMING, OH			
DR	B. NAGY	DATE	
APV01	M. MCCALL	0BMR97	
APV02	M. MCCALL	09JL97	
APV03	S.A. NORLING	030C97	
APV04			
APV05			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001			
MATERIAL SEE DRAWING			
DRAWING NAME			
TAXI ASM CONN F 0T 2B0 SLD			
DRAWING NUMBER			
15326672			
SHEET NO	SCALE 2:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1
REV 09	REV 09	REV 09	REV 09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15326917-B](#)