


ADTRAN P/N	REV	FCI P/N	L (MR)
31251252-E0B	B	10075926-N0305YYLF	3.048



⑨	LABEL	1	PC
⑧	HEAT SHRINK TUBE	AR	MR
⑦	lug,22~26awg	1	PC
⑥	24 awg, tinned ,stranded wire,UL1015, black	AR	MR
⑤	SCREW	1	PC
④	CONN HOOD	1	PC
③	64 POS CONN	1	PC
②	32 pair dual shielded cable,120 Ohm,	AR	MR
①	FCI 72 pos. CONN KITS	1	PC
No.	DESCRIPTION	QTY	UNIT

rev	ecn no	dr	date
A	V07-0119	DAI	2007-02-06
B	N10-0410	JY	2010-12-07
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - ✓	tolerance std -	projection -	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	Jack Yang	2010-12-07	ANGULAR	0.X	±-	size A3
Eng	Jack Yang	2010-12-07		0.XX	±-	Scale 2:3
Chr	Jack Yang	2010-12-07	0° ±-	0.XXX	±-	ECN Preliminary
Appr	Jackson Wang	2010-12-07	Product family Sofix			Spec ref -
FCI			title CABLE ASSEMBLY ADAPTER ETSI-CHAMP			Rev. B
			catalog no	-	Customer	sheet 1 of 3

WIRE DIAGRAM

BINDER	GROUP	PAIR NO	WIRE COLOR	CONN A	CONN B
NONE	1	17	YELLOW	C1	49
			ORANGE	D1	17
		18	YELLOW	C2	50
			GREEN	D2	18
		19	YELLOW	C3	51
			BROWN	D3	19
		20	YELLOW	C4	52
			GRAY	D4	20
		21	VIOLET	C5	53
			BLUE	D5	21
		22	VIOLET	C6	54
			ORANGE	D6	22
BLUE	2	23	VIOLET	C1	55
			GREEN	D1	23
		24	VIOLET	C2	56
			BROWN	D2	24
		25	VIOLET	C3	57
			GRAY	D3	25
		26	WHITE	C4	58
			BLUE	D4	26
		27	WHITE	C5	59
			ORANGE	D5	27
		28	WHITE	C6	60
			GREEN	D6	28
		29	WHITE	C1	61
			BROWN	D1	29
		30	WHITE	C2	62
			GRAY	D2	30
		31	RED	C3	63
			BLUE	D3	31
	3	32	RED	C4	64
			ORANGE	D4	32
				C5	
				D5	
				C6	
				D6	
			DRAIN WIRE	D6	LUG

BINDER	GROUP	PAIR NO	WIRE COLOR	CONN A	CONN B
NONE	1	1	WHITE	A1	33
			BLUE	B1	1
		2	WHITE	A2	34
			ORANGE	B2	2
		3	WHITE	A3	35
			GREEN	B3	3
		4	WHITE	A4	36
			BROWN	B4	4
		5	WHITE	A5	37
			GRAY	B5	5
		6	RED	A6	38
			BLUE	B6	6
	2	7	RED	A1	39
			ORANGE	B1	7
		8	RED	A2	240
			GREEN	B2	8
		9	RED	A3	41
			BROWN	B3	9
		10	RED	A4	42
			GRAY	B4	10
		11	BLACK	A5	43
			BLUE	B5	11
		12	BLACK	A6	44
			ORANGE	B6	12
3	3	13	BLACK	A1	45
			GREEN	B1	13
		14	BLACK	A2	346
			BROWN	B2	14
		15	BLACK	A3	47
			GRAY	B3	15
		16	YELLOW	A4	48
			BLUE	B4	16
				A5	
				B5	
				A6	
				B6	

rev	ecn no	dr	date
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface - ☒	tolerance std - -	projection 	mm 
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	Jack Yang	2010-12-07	ANGULAR	0.X ±	size A3
Eng	Jack Yang	2010-12-07	LINEAR	0.XX ±	Scale 2:3
Chr	Jack Yang	2010-12-07	0° ±	0.XXX ±	ECN Preliminary
Appr	Jackson Wang	2010-12-07	Product family	Sofix	Spec ref -
		title CABLE ASSEMBLY ADAPTER ETSI-CHAMP		dwg no 10075926	Rev. B
catalog no -		Customer		sheet 2 of 3	

NOTES:

1. UNLESS OTHERWISE SPECIFIED ASSEMBLED LENGTH TOLERANCE
±100
2. DEFINE THE PART NUMBER SCHEME FOR THE CABLE ASSEMBLY, REFER TO 10076663
3. CONNECTOR SHOULD BE BUBBLE WRAPPED.
4. UNLESS OTHERWISE SPECIFIED ,LABEL CONTENT SHALL CONTAIS THE BELOW:
 - FCI LOGO
 - CUSTOMER P/N REVISION
 - MADE IN CHINA WW/YY
 - EU WEEE LOGO CHINA ROHS LOGO
5. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST
6. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE 100% HI-POT TESTED BY APPLYING DC 500V FOR MINIMUM OF 0.01S,CONTACTTION RESISTANCE 5 Ohm,INSULATION RESISTANCE 20 M Ohm, UNLESS ACTIVE COMPONENTS ARE USED IN THIS ASSEMBLY.
7. OTHER TESTING PERFORMED AS REQUIRED BY PRODUCT SPECIFICATION
8. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS AS DESCRIBED IN GS-22-008
9. CONNECTOR ASSEMBLIES SHOWN ARE FOR REFERENCE ONLY AND MAY NOT SHOW ALL PART DETAIL. REFERENCE CONNECTOR ASSEMBLY DRAWING FOR COMPLETE DETAILS.
10. GLOBAL STANDARDS FOR CABLE PACKAGING: GS-14-1093
11. REFER TO A SEPARATE FCI RAW CABLE DRAWING 10082026-001LF

rev	ecn no	dr	date
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - ✓	tolerance std - -	projection ⊕	mm ↔
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	Jack Yang	2010-12-07	ANGULAR 0° ±'	LINEAR	0.X ±-	size A3
Eng	Jack Yang	2010-12-07			0.XX ±-	Scale 2:3
Chr	Jack Yang	2010-12-07			0.XXX ±-	ECN Preliminary
Appr	Jackson Wang	2010-12-07	Product family			Sofix Spec ref -
			FCI			
			title CABLE ASSEMBLY ADAPTER ETSI-CHAMP			dwg no 10075926
			catalog no			Rev. B
						sheet 3 of 3