


Product: [9364](#)

High Perform Instr, 1 Tri #20 Str TC, PVC Ins E1, OS, PVC Jkt, PLTC

[Request Sample](#)
Product Description

High Performance Instrumentation, 1 Triad 20AWG (19x32) Tinned Copper, PVC Insulation E1 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC

Technical Specifications
Product Overview

Suitable Applications:	Instrumentation, Sensors, Valves, Positioners, RTD, 4-20mA, 0-10V
------------------------	---

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Triad(s)	1	20 AWG	19x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Triad(s)	PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.072 in (1.8 mm)	ICEA Chart E1

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (19x34) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.234 in (5.94 mm)	Yes

Overall Cable Diameter (Nominal): 0.234 in (5.94 mm)

Electrical Characteristics
Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Nom. Inductance	Max. Current
Triad(s)	11.3 Ohm/1000ft	30 pF/ft (98 pF/m)	55 pF/ft (180 pF/m)	0.19 µH/ft (0.62 µH/m)	3.8 Amps per Conductor at 25°C

Nom Outer Shield DCR@Cond DCR1-cnv: 12.14 Ohm/1000ft (39.83 Ohm/km)

Voltage

UL Voltage Rating
300 V (PLTC, CMG)

Mechanical Characteristics
Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

Temperature Table Notes: AWM 80°C

Bend Radius

Stationary Min.	Installation Min.
-----------------	-------------------

2.3 in (58 mm)

2.3 in (58 mm)

Max. Pull Tension: 54 lbs (24 kg)

Bulk Cable Weight: 31 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 UL Loading, FT4, T-29-520, IEEE 1202
NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, ITC, PLTC
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Revision Number: 0.613 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9364 060U500	Chrome	UnReel	500 ft	612825239437	
9364 060U1000	Chrome	UnReel	1,000 ft	612825239420	
9364 0602500	Chrome	Reel	2,500 ft	612825239451	Z
9364 0605000	Chrome	Reel	5,000 ft	612825239468	C
9364 06010000	Chrome	Reel	10,000 ft	612825239444	C

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.