

# 5 Watt Surmetic 40 Zener Voltage Regulators 1N53 Series

This is a complete series of 5 Watt Zener diodes with tight limits and better operating characteristics that reflect the superior capabilities of silicon-oxide passivated junctions. All this in an axial lead, transfer-molded plastic package that offers protection in all common environmental conditions.

## Features

- Zener Voltage Range – 3.3 V to 200 V
- ESD Rating of Class 3 (>16 kV) per Human Body Model
- Surge Rating of up to 180 W @ 8.3 ms
- Maximum Limits Guaranteed on up to Six Electrical Parameters
- Pb-Free Packages are Available\*

## Mechanical Characteristics


**CASE:** Void free, transfer-molded, thermosetting plastic

**FINISH:** All external surfaces are corrosion resistant and leads are readily solderable


**MAXIMUM LEAD TEMPERATURE FOR SOLDERING PURPOSES:** 260°C, 1/16 in. from the case for 10 seconds

**POLARITY:** Cathode indicated by polarity band

**MOUNTING POSITION:** Any



## MARKING DIAGRAM



- A = Assembly Location  
 1N53xxB = Device Number  
 (Refer to Tables on Pages 3 & 4)  
 YY = Year  
 WW = Work Week  
 ■ = Pb-Free Package

(Note: Microdot may be in either location)

## MAXIMUM RATINGS

| Rating                                                                                                                      | Symbol         | Value                   | Unit  |
|-----------------------------------------------------------------------------------------------------------------------------|----------------|-------------------------|-------|
| Max. Steady State Power Dissipation<br>@ $T_L = 25^\circ\text{C}$ , Lead Length = 3/8 in<br>Derate above $25^\circ\text{C}$ | $P_D$          | 5                       | W     |
| Junction-to-Lead Thermal Resistance                                                                                         | $\theta_{JL}$  | 40                      | mW/°C |
|                                                                                                                             |                | 25                      | °C/W  |
| Operating and Storage<br>Temperature Range                                                                                  | $T_J, T_{stg}$ | -65 to +200<br>(Note 1) | °C    |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Max operating temperature for DC conditions is  $150^\circ\text{C}$ , but not to exceed  $200^\circ\text{C}$  for pulsed conditions with low duty cycle or non-repetitive.

\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

## ORDERING INFORMATION

| Device       | Package                 | Shipping†        |
|--------------|-------------------------|------------------|
| 1N53xxB, G   | Axial Lead<br>(Pb-Free) | 1000 Units/Box   |
| 1N53xxBRL, G | Axial Lead<br>(Pb-Free) | 4000/Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# 1N53 Series

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted,  $V_F = 1.2\text{ V Max}$  @  $I_F = 1.0\text{ A}$  for all types)

| Symbol       | Parameter                                        |
|--------------|--------------------------------------------------|
| $V_Z$        | Reverse Zener Voltage @ $I_{ZT}$                 |
| $I_{ZT}$     | Reverse Current                                  |
| $Z_{ZT}$     | Maximum Zener Impedance @ $I_{ZT}$               |
| $I_{ZK}$     | Reverse Current                                  |
| $Z_{ZK}$     | Maximum Zener Impedance @ $I_{ZK}$               |
| $I_R$        | Reverse Leakage Current @ $V_R$                  |
| $V_R$        | Breakdown Voltage                                |
| $I_F$        | Forward Current                                  |
| $V_F$        | Forward Voltage @ $I_F$                          |
| $I_R$        | Maximum Surge Current @ $T_A = 25^\circ\text{C}$ |
| $\Delta V_Z$ | Reverse Zener Voltage Change                     |
| $I_{ZM}$     | Maximum DC Zener Current                         |



**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted,  $V_F = 1.2\text{ V Max}$  @  $I_F = 1.0\text{ A}$  for all types)

| Device <sup>†</sup><br>(Note 2) | Device<br>Marking | Zener Voltage (Note 3) |            |             |                   | Zener Impedance (Note 3)          |                                   |                 | Leakage<br>Current              |            | I <sub>R</sub><br>(Note 4) | ΔV <sub>Z</sub><br>(Note 5) | I <sub>ZM</sub><br>(Note 6) |
|---------------------------------|-------------------|------------------------|------------|-------------|-------------------|-----------------------------------|-----------------------------------|-----------------|---------------------------------|------------|----------------------------|-----------------------------|-----------------------------|
|                                 |                   | V <sub>Z</sub> (Volts) |            |             | @ I <sub>ZT</sub> | Z <sub>ZT</sub> @ I <sub>ZT</sub> | Z <sub>ZK</sub> @ I <sub>ZK</sub> | I <sub>ZK</sub> | I <sub>R</sub> @ V <sub>R</sub> |            |                            |                             |                             |
|                                 |                   | Min                    | Nom        | Max         | mA                | Ω                                 | Ω                                 | mA              | μA Max                          | Volts      |                            |                             |                             |
| <b>1N5333B</b>                  | <b>1N5333B</b>    | <b>3.14</b>            | <b>3.3</b> | <b>3.47</b> | <b>380</b>        | <b>3</b>                          | <b>400</b>                        | <b>1</b>        | <b>300</b>                      | <b>1</b>   | <b>20</b>                  | <b>0.85</b>                 | <b>1440</b>                 |
| 1N5334B                         | 1N5334B           | 3.42                   | 3.6        | 3.78        | 350               | 2.5                               | 500                               | 1               | 150                             | 1          | 18.7                       | 0.8                         | 1320                        |
| 1N5335B                         | 1N5335B           | 3.71                   | 3.9        | 4.10        | 320               | 2                                 | 500                               | 1               | 50                              | 1          | 17.6                       | 0.54                        | 1220                        |
| 1N5336B                         | 1N5336B           | 4.09                   | 4.3        | 4.52        | 290               | 2                                 | 500                               | 1               | 10                              | 1          | 16.4                       | 0.49                        | 1100                        |
| <b>1N5337B</b>                  | <b>1N5337B</b>    | <b>4.47</b>            | <b>4.7</b> | <b>4.94</b> | <b>260</b>        | <b>2</b>                          | <b>450</b>                        | <b>1</b>        | <b>5</b>                        | <b>1</b>   | <b>15.3</b>                | <b>0.44</b>                 | <b>1010</b>                 |
| <b>1N5338B</b>                  | <b>1N5338B</b>    | <b>4.85</b>            | <b>5.1</b> | <b>5.36</b> | <b>240</b>        | <b>1.5</b>                        | <b>400</b>                        | <b>1</b>        | <b>1</b>                        | <b>1</b>   | <b>14.4</b>                | <b>0.39</b>                 | <b>930</b>                  |
| <b>1N5339B</b>                  | <b>1N5339B</b>    | <b>5.32</b>            | <b>5.6</b> | <b>5.88</b> | <b>220</b>        | <b>1</b>                          | <b>400</b>                        | <b>1</b>        | <b>1</b>                        | <b>2</b>   | <b>13.4</b>                | <b>0.25</b>                 | <b>865</b>                  |
| 1N5340B                         | 1N5340B           | 5.70                   | 6.0        | 6.30        | 200               | 1                                 | 300                               | 1               | 1                               | 3          | 12.7                       | 0.19                        | 790                         |
| <b>1N5341B</b>                  | <b>1N5341B</b>    | <b>5.89</b>            | <b>6.2</b> | <b>6.51</b> | <b>200</b>        | <b>1</b>                          | <b>200</b>                        | <b>1</b>        | <b>1</b>                        | <b>3</b>   | <b>12.4</b>                | <b>0.1</b>                  | <b>765</b>                  |
| <b>1N5342B</b>                  | <b>1N5342B</b>    | <b>6.46</b>            | <b>6.8</b> | <b>7.14</b> | <b>175</b>        | <b>1</b>                          | <b>200</b>                        | <b>1</b>        | <b>10</b>                       | <b>5.2</b> | <b>11.5</b>                | <b>0.15</b>                 | <b>700</b>                  |
| 1N5343B                         | 1N5343B           | 7.13                   | 7.5        | 7.88        | 175               | 1.5                               | 200                               | 1               | 10                              | 5.7        | 10.7                       | 0.15                        | 630                         |
| 1N5344B                         | 1N5344B           | 7.79                   | 8.2        | 8.61        | 150               | 1.5                               | 200                               | 1               | 10                              | 6.2        | 10                         | 0.2                         | 580                         |
| 1N5345B                         | 1N5345B           | 8.27                   | 8.7        | 9.14        | 150               | 2                                 | 200                               | 1               | 10                              | 6.6        | 9.5                        | 0.2                         | 545                         |
| 1N5346B                         | 1N5346B           | 8.65                   | 9.1        | 9.56        | 150               | 2                                 | 150                               | 1               | 7.5                             | 6.9        | 9.2                        | 0.22                        | 520                         |
| <b>1N5347B</b>                  | <b>1N5347B</b>    | <b>9.50</b>            | <b>10</b>  | <b>10.5</b> | <b>125</b>        | <b>2</b>                          | <b>125</b>                        | <b>1</b>        | <b>5</b>                        | <b>7.6</b> | <b>8.6</b>                 | <b>0.22</b>                 | <b>475</b>                  |

Devices listed in **bold, italic** are onsemi Preferred devices. Preferred devices are recommended choices for future use and best overall value.

- TOLERANCE AND TYPE NUMBER DESIGNATION:** The JEDEC type numbers shown indicate a tolerance of  $\pm 5\%$ .
- ZENER VOLTAGE ( $V_Z$ ) and IMPEDANCE ( $I_{ZT}$  and  $I_{ZK}$ ):** Test conditions for zener voltage and impedance are as follows:  $I_Z$  is applied  $40 \pm 10$  ms prior to reading. Mounting contacts are located  $3/8''$  to  $1/2''$  from the inside edge of mounting clips to the body of the diode ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- SURGE CURRENT ( $I_R$ ):** Surge current is specified as the maximum allowable peak, non-recurrent square-wave current with a pulse width, PW, of 8.3 ms. The data given in Figure 5 may be used to find the maximum surge current for a square wave of any pulse width between 1 ms and 1000 ms by plotting the applicable points on logarithmic paper. Examples of this, using the 3.3 V and 200 V zener are shown in Figure 6. Mounting contact located as specified in Note 2 ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- VOLTAGE REGULATION ( $\Delta V_Z$ ):** The conditions for voltage regulation are as follows:  $V_Z$  measurements are made at 10% and then at 50% of the  $I_Z$  max value listed in the electrical characteristics table. The test current time duration for each  $V_Z$  measurement is  $40 \pm 10$  ms. Mounting contact located as specified in Note 2 ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- MAXIMUM REGULATOR CURRENT ( $I_{ZM}$ ):** The maximum current shown is based on the maximum voltage of a 5% type unit, therefore, it applies only to the B-suffix device. The actual  $I_{ZM}$  for any device may not exceed the value of 5 watts divided by the actual  $V_Z$  of the device.  $T_L = 25^\circ\text{C}$  at  $3/8''$  maximum from the device body.

<sup>†</sup>The "G" suffix indicates Pb-Free package or Pb-Free packages are available.

# 1N53 Series

## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 1.2\text{ V Max}$ @ $I_F = 1.0\text{ A}$ for all types)

| Device <sup>†</sup><br>(Note 7) | Device<br>Marking | Zener Voltage (Note 8) |            |              |                   | Zener Impedance (Note 8)          |                                   |                 | Leakage<br>Current              |             | I <sub>R</sub><br>(Note 9) | ΔV <sub>Z</sub><br>(Note 10) | I <sub>ZM</sub><br>(Note 11) |
|---------------------------------|-------------------|------------------------|------------|--------------|-------------------|-----------------------------------|-----------------------------------|-----------------|---------------------------------|-------------|----------------------------|------------------------------|------------------------------|
|                                 |                   | V <sub>Z</sub> (Volts) |            |              | @ I <sub>ZT</sub> | Z <sub>ZT</sub> @ I <sub>ZT</sub> | Z <sub>ZK</sub> @ I <sub>ZK</sub> | I <sub>ZK</sub> | I <sub>R</sub> @ V <sub>R</sub> |             |                            |                              |                              |
|                                 |                   | Min                    | Nom        | Max          | mA                | Ω                                 | Ω                                 | mA              | μA Max                          | Volts       | A                          | Volts                        | mA                           |
| 1N5348B                         | 1N5348B           | 10.45                  | 11         | 11.55        | 125               | 2.5                               | 125                               | 1               | 5                               | 8.4         | 8.0                        | 0.25                         | 430                          |
| <b>1N5349B</b>                  | <b>1N5349B</b>    | <b>11.4</b>            | <b>12</b>  | <b>12.6</b>  | <b>100</b>        | <b>2.5</b>                        | <b>125</b>                        | <b>1</b>        | <b>2</b>                        | <b>9.1</b>  | <b>7.5</b>                 | <b>0.25</b>                  | <b>395</b>                   |
| <b>1N5350B</b>                  | <b>1N5350B</b>    | <b>12.35</b>           | <b>13</b>  | <b>13.65</b> | <b>100</b>        | <b>2.5</b>                        | <b>100</b>                        | <b>1</b>        | <b>1</b>                        | <b>9.9</b>  | <b>7.0</b>                 | <b>0.25</b>                  | <b>365</b>                   |
| 1N5351B                         | 1N5351B           | 13.3                   | 14         | 14.7         | 100               | 2.5                               | 75                                | 1               | 1                               | 10.6        | 6.7                        | 0.25                         | 340                          |
| <b>1N5352B</b>                  | <b>1N5352B</b>    | <b>14.25</b>           | <b>15</b>  | <b>15.75</b> | <b>75</b>         | <b>2.5</b>                        | <b>75</b>                         | <b>1</b>        | <b>1</b>                        | <b>11.5</b> | <b>6.3</b>                 | <b>0.25</b>                  | <b>315</b>                   |
| <b>1N5353B</b>                  | <b>1N5353B</b>    | <b>15.2</b>            | <b>16</b>  | <b>16.8</b>  | <b>75</b>         | <b>2.5</b>                        | <b>75</b>                         | <b>1</b>        | <b>1</b>                        | <b>12.2</b> | <b>6.0</b>                 | <b>0.3</b>                   | <b>295</b>                   |
| 1N5354B                         | 1N5354B           | 16.15                  | 17         | 17.85        | 70                | 2.5                               | 75                                | 1               | 0.5                             | 12.9        | 5.8                        | 0.35                         | 280                          |
| 1N5355B                         | 1N5355B           | 17.1                   | 18         | 18.9         | 65                | 2.5                               | 75                                | 1               | 0.5                             | 13.7        | 5.5                        | 0.4                          | 264                          |
| 1N5356B                         | 1N5356B           | 18.05                  | 19         | 19.95        | 65                | 3                                 | 75                                | 1               | 0.5                             | 14.4        | 5.3                        | 0.4                          | 250                          |
| 1N5357B                         | 1N5357B           | 19                     | 20         | 21           | 65                | 3                                 | 75                                | 1               | 0.5                             | 15.2        | 5.1                        | 0.4                          | 237                          |
| <b>1N5358B</b>                  | <b>1N5358B</b>    | <b>20.9</b>            | <b>22</b>  | <b>23.1</b>  | <b>50</b>         | <b>3.5</b>                        | <b>75</b>                         | <b>1</b>        | <b>0.5</b>                      | <b>16.7</b> | <b>4.7</b>                 | <b>0.45</b>                  | <b>216</b>                   |
| <b>1N5359B</b>                  | <b>1N5359B</b>    | <b>22.8</b>            | <b>24</b>  | <b>25.2</b>  | <b>50</b>         | <b>3.5</b>                        | <b>100</b>                        | <b>1</b>        | <b>0.5</b>                      | <b>18.2</b> | <b>4.4</b>                 | <b>0.55</b>                  | <b>198</b>                   |
| 1N5360B                         | 1N5360B           | 23.75                  | 25         | 26.25        | 50                | 4                                 | 110                               | 1               | 0.5                             | 19          | 4.3                        | 0.55                         | 190                          |
| <b>1N5361B</b>                  | <b>1N5361B</b>    | <b>25.65</b>           | <b>27</b>  | <b>28.35</b> | <b>50</b>         | <b>5</b>                          | <b>120</b>                        | <b>1</b>        | <b>0.5</b>                      | <b>20.6</b> | <b>4.1</b>                 | <b>0.6</b>                   | <b>176</b>                   |
| 1N5362B                         | 1N5362B           | 26.6                   | 28         | 29.4         | 50                | 6                                 | 130                               | 1               | 0.5                             | 21.2        | 3.9                        | 0.6                          | 170                          |
| 1N5363B                         | 1N5363B           | 28.5                   | 30         | 31.5         | 40                | 8                                 | 140                               | 1               | 0.5                             | 22.8        | 3.7                        | 0.6                          | 158                          |
| 1N5364B                         | 1N5364B           | 31.35                  | 33         | 34.65        | 40                | 10                                | 150                               | 1               | 0.5                             | 25.1        | 3.5                        | 0.6                          | 144                          |
| <b>1N5365B</b>                  | <b>1N5365B</b>    | <b>34.2</b>            | <b>36</b>  | <b>37.8</b>  | <b>30</b>         | <b>11</b>                         | <b>160</b>                        | <b>1</b>        | <b>0.5</b>                      | <b>27.4</b> | <b>3.5</b>                 | <b>0.65</b>                  | <b>132</b>                   |
| 1N5366B                         | 1N5366B           | 37.05                  | 39         | 40.95        | 30                | 14                                | 170                               | 1               | 0.5                             | 29.7        | 3.1                        | 0.65                         | 122                          |
| 1N5367B                         | 1N5367B           | 40.85                  | 43         | 45.15        | 30                | 20                                | 190                               | 1               | 0.5                             | 32.7        | 2.8                        | 0.7                          | 110                          |
| <b>1N5368B</b>                  | <b>1N5368B</b>    | <b>44.65</b>           | <b>47</b>  | <b>49.35</b> | <b>25</b>         | <b>25</b>                         | <b>210</b>                        | <b>1</b>        | <b>0.5</b>                      | <b>35.8</b> | <b>2.7</b>                 | <b>0.8</b>                   | <b>100</b>                   |
| 1N5369B                         | 1N5369B           | 48.45                  | 51         | 53.55        | 25                | 27                                | 230                               | 1               | 0.5                             | 38.8        | 2.5                        | 0.9                          | 93                           |
| 1N5370B                         | 1N5370B           | 53.2                   | 56         | 58.8         | 20                | 35                                | 280                               | 1               | 0.5                             | 42.6        | 2.3                        | 1.0                          | 86                           |
| 1N5371B                         | 1N5371B           | 57                     | 60         | 63           | 20                | 40                                | 350                               | 1               | 0.5                             | 45.5        | 2.2                        | 1.2                          | 79                           |
| 1N5372B                         | 1N5372B           | 58.9                   | 62         | 65.1         | 20                | 42                                | 400                               | 1               | 0.5                             | 47.1        | 2.1                        | 1.35                         | 76                           |
| 1N5373B                         | 1N5373B           | 64.6                   | 68         | 71.4         | 20                | 44                                | 500                               | 1               | 0.5                             | 51.7        | 2.0                        | 1.52                         | 70                           |
| 1N5374B                         | 1N5374B           | 71.25                  | 75         | 78.75        | 20                | 45                                | 620                               | 1               | 0.5                             | 56          | 1.9                        | 1.6                          | 63                           |
| 1N5375B                         | 1N5375B           | 77.9                   | 82         | 86.1         | 15                | 65                                | 720                               | 1               | 0.5                             | 62.2        | 1.8                        | 1.8                          | 58                           |
| 1N5377B                         | 1N5377B           | 86.45                  | 91         | 95.55        | 15                | 75                                | 760                               | 1               | 0.5                             | 69.2        | 1.6                        | 2.2                          | 52.5                         |
| 1N5378B                         | 1N5378B           | 95                     | 100        | 105          | 12                | 90                                | 800                               | 1               | 0.5                             | 76          | 1.5                        | 2.5                          | 47.5                         |
| 1N5380B                         | 1N5380B           | 114                    | 120        | 126          | 10                | 170                               | 1150                              | 1               | 0.5                             | 91.2        | 1.3                        | 2.5                          | 39.5                         |
| 1N5381B                         | 1N5381B           | 123.5                  | 130        | 136.5        | 10                | 190                               | 1250                              | 1               | 0.5                             | 98.8        | 1.2                        | 2.5                          | 36.6                         |
| <b>1N5383B</b>                  | <b>1N5383B</b>    | <b>142.5</b>           | <b>150</b> | <b>157.5</b> | <b>8</b>          | <b>330</b>                        | <b>1500</b>                       | <b>1</b>        | <b>0.5</b>                      | <b>114</b>  | <b>1.1</b>                 | <b>3.0</b>                   | <b>31.6</b>                  |
| 1N5384B                         | 1N5384B           | 152                    | 160        | 168          | 8                 | 350                               | 1650                              | 1               | 0.5                             | 122         | 1.1                        | 3.0                          | 29.4                         |
| 1N5386B                         | 1N5386B           | 171                    | 180        | 189          | 5                 | 430                               | 1750                              | 1               | 0.5                             | 137         | 1.0                        | 4.0                          | 26.4                         |
| 1N5387B                         | 1N5387B           | 180.5                  | 190        | 199.5        | 5                 | 450                               | 1850                              | 1               | 0.5                             | 144         | 0.9                        | 5.0                          | 25                           |
| 1N5388B                         | 1N5388B           | 190                    | 200        | 210          | 5                 | 480                               | 1850                              | 1               | 0.5                             | 152         | 0.9                        | 5.0                          | 23.6                         |

Devices listed in **bold, italic** are onsemi Preferred devices. Preferred devices are recommended choices for future use and best overall value.

- TOLERANCE AND TYPE NUMBER DESIGNATION:** The JEDEC type numbers shown indicate a tolerance of  $\pm 5\%$ .
- ZENER VOLTAGE ( $V_Z$ ) and IMPEDANCE ( $I_{ZT}$  and  $I_{ZK}$ ):** Test conditions for zener voltage and impedance are as follows:  $I_Z$  is applied  $40 \pm 10$  ms prior to reading. Mounting contacts are located  $3/8''$  to  $1/2''$  from the inside edge of mounting clips to the body of the diode ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- SURGE CURRENT ( $I_R$ ):** Surge current is specified as the maximum allowable peak, non-recurrent square-wave current with a pulse width, PW, of 8.3 ms. The data given in Figure 5 may be used to find the maximum surge current for a square wave of any pulse width between 1 ms and 1000 ms by plotting the applicable points on logarithmic paper. Examples of this, using the 3.3 V and 200 V zener are shown in Figure 6. Mounting contact located as specified in Note 7 ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- VOLTAGE REGULATION ( $\Delta V_Z$ ):** The conditions for voltage regulation are as follows:  $V_Z$  measurements are made at 10% and then at 50% of the  $I_Z$  max value listed in the electrical characteristics table. The test current time duration for each  $V_Z$  measurement is  $40 \pm 10$  ms. Mounting contact located as specified in Note 7 ( $T_A = 25^\circ\text{C} + 8^\circ\text{C}, -2^\circ\text{C}$ ).
- MAXIMUM REGULATOR CURRENT ( $I_{ZM}$ ):** The maximum current shown is based on the maximum voltage of a 5% type unit, therefore, it applies only to the B-suffix device. The actual  $I_{ZM}$  for any device may not exceed the value of 5 watts divided by the actual  $V_Z$  of the device.  $T_L = 25^\circ\text{C}$  at  $3/8''$  maximum from the device body.

†The "G" suffix indicates Pb-Free package or Pb-Free packages are available.

# 1N53 Series



Figure 1. Typical Thermal Resistance

## TEMPERATURE COEFFICIENTS




Figure 2. Temperature Coefficient-Range for Units 3 to 10 Volts




Figure 3. Temperature Coefficient-Range for Units 10 to 220 Volts


# 1N53 Series



**Figure 4. Typical Thermal Response**  
L, Lead Length = 3/8 Inch




**Figure 5. Maximum Non-Repetitive Surge Current**  
versus Nominal Zener Voltage  
(See Note 4)



**Figure 6. Peak Surge Current versus Pulse Width**  
(See Note 4)



**Figure 7. Zener Voltage versus Zener Current**  
 $V_Z = 3.3$  thru 10 Volts



**Figure 8. Zener Voltage versus Zener Current**  
 $V_Z = 11$  thru 75 Volts

## 1N53 Series



**Figure 9. Zener Voltage versus Zener Current**  
 **$V_Z = 82$  thru 200 Volts**

### APPLICATION NOTE

Since the actual voltage available from a given Zener diode is temperature dependent, it is necessary to determine junction temperature under any set of operating conditions in order to calculate its value. The following procedure is recommended:

Lead Temperature,  $T_L$ , should be determined from:

$$T_L = \theta_{LA} P_D + T_A$$

$\theta_{LA}$  is the lead-to-ambient thermal resistance and  $P_D$  is the power dissipation.

Junction Temperature,  $T_J$ , may be found from:

$$T_J = T_L + \Delta T_{JL}$$

$\Delta T_{JL}$  is the increase in junction temperature above the lead temperature and may be found from Figure 4 for a train of power pulses or from Figure 1 for dc power.

$$\Delta T_{JL} = \theta_{JL} P_D$$

SURMETIC 40, AXIAL LEAD  
CASE 017AA  
ISSUE O

DATE 23 SEP 2005



SCALE 1:1



NOTES:

1. CONTROLLING DIMENSION: INCH
2. LEAD DIAMETER AND FINISH NOT CONTROLLED WITHIN DIMENSION F.
3. CATHODE BAND INDICATES POLARITY

| DIM | INCHES |       | MILLIMETERS |       |
|-----|--------|-------|-------------|-------|
|     | MIN    | MAX   | MIN         | MAX   |
| A   | 0.330  | 0.350 | 8.38        | 8.89  |
| B   | 0.130  | 0.145 | 3.30        | 3.68  |
| D   | 0.037  | 0.043 | 0.94        | 1.09  |
| F   | ---    | 0.050 | ---         | 1.27  |
| K   | 1.000  | 1.250 | 25.40       | 31.75 |

|                  |                         |                                                                                                                                                                                  |
|------------------|-------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON21393D             | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SURMETIC 40, AXIAL LEAD | PAGE 1 OF 1                                                                                                                                                                      |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)