

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0191210026

Status:

Active

Description:

InsulKrimp™ Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 6



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19902-009 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Mil-Spec

Product Name

Type

Ring and Spade Terminals

19121

N/A

InsulKrimp™

Spade

Physical

Barrel Type

Color - Resin

Flammability

Insulation

Material - Plating Mating

Packaging Type

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Stud Size

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

Natural

94V-2

PVC

Tin

Bag

160

4

160

4

6 (M3.5)

4.45mm (.175")

14, 16

1.00 - 2.50

Electrical

CSA

UL

LR18689

E32244

Material Info

Old Part Number

BB-216-06X

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-009

SD-19121-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19121Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051400
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640011400

This document was generated on 02/02/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION