



## RECTANGULAR POWER CONNECTORS



✓ Active

### TE CONNECTIVITY (TE) UMNL CAP HSG. 15 POS

MATE-N-LOK | Universal MATE-N-LOK

926647-8

TE Internal Number: 926647-8

EU RoHS Compliant

EU ELV Compliant

Product Type Housing

Housing Type Receptacle

Connector System Wire-to-Panel, Wire-to-Wire

Number of Positions 15

Centerline (Pitch) 6.35 mm [ .25 in ]

**PRODUCT DRAWING**  
English

**3D PDF**

### DOCUMENTATION

Product Drawings

#### UMNL 15-WAY CAP HOUSING

PDF

English

CAD Files

#### 3D PDF

PDF

3D

#### Customer View Model

2D\_DXF.ZIP

English

#### **Customer View Model**

3D\_IGS.ZIP

English

#### **Customer View Model**

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

#### **Universal MATE-N-LOK Connectors**

PDF

English

---

Agency Approvals

UL Report

#### **UMNL, UMNL BULKHEAD AND UMNL2 CONNECTORS REPORT**

PDF

English

---

### **FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Product Type** Housing

**Housing Type** Receptacle

**Connector System** Wire-to-Panel, Wire-to-Wire

**Connector & Contact Terminates To** Wire & Cable

**Contact Type** Pin

---

Configuration Features

**Number of Positions** 15

**Number of Rows** 3

**Row-to-Row Spacing** .25 mm [ 6.35 in ]

**Contact Layout** Matrix

---

Electrical Characteristics

**Operating Voltage (VAC)** 600

---

Contact Features

**Contact Retention** Without

**Multiple Contact Types** Without

---

## Mechanical Attachment

**Panel Mount Feature Type** Patch & Tabs

**Panel Mount Feature** With

**Connector Mounting Type** Panel

---

## Housing Features

**Centerline (Pitch)** 6.35 mm [.25 in]

**UL Flammability Rating** UL 94V-0

**Housing Material** PA 6

---

## Dimensions

**Panel Thickness** .76 – 2.29 mm [.76 – 2.29 in]

---

## Usage Conditions

**Operating Temperature Range** -55 – 105 °C [-67 – 221 °F]

**Sealed Condition** Not Sealed

---

## Operation/Application

**Assembly Integration Feature** Without

---

## Industry Standards

**Glow Wire Rating** GWT 750°C (Without Flame)

**Agency/Standard** UL

**VDE Tested** Yes

**Agency/Standard Number** E28476

**UL Rating** Recognized

---

## Packaging Features

**Packaging Method** Bag

**Packaging Quantity** 700

---

## PRODUCT COMPLIANCE



### Statement of Compliance

#### [Statement of Compliance](#)

PDF