


D

C





B

A


SECTION F-F



(0.63)
TYP(26)




(SCALE: 10:1)



RECOMMENDED PCB LAYOUT
(PRECONISATION DE L'IMPLANTATION
DU CIRCUIT IMPRIME)


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
F	00		A	MISE A JOUR	07-AUG-96	NT
			B	NEW REFERENCES ADDED	15-NOV-96	NT
			C	LEAD REMOVED	05-FEB-08	MV

Ø 0.4
Ø 0.6
Ø 0.89 MAX



DETAIL G

(SCALE: 20:1)



	BLUE (bleu)	3.5 ±0.2	185534-4
		2.6 ±0.2	185534-2
	YELLOW (jaune)	3.5 ±0.2	185534-3
		2.6 ±0.2	185534-1
CODING (Detrompage)	COLOR (Couleur)	"Z"	P/N ASS'Y (reference- assemble)

PBT 20% GLASS FIBER (PBT 20% FIBRE DE VERRE)	COPPER ALLOY (ALLIAGE CUIVRE)	TIN OVER NICKEL (ETAIN SUR SOUS-COUCHE NICKEL)
HOUSING MATERIAL (MATIERE EMBASE)	PIN MATERIAL (MATIERE CONTACT)	PIN FINISH (FINITION CONTACT)

NOTES:

- 1

DATE CODE
- 2

"AMP" LOGO
- 3

TYCO ELECTRONICS PART NUMBER
- 4

MOLD CAVITY MARKING
- 5

MATERIAL REFERENCE
- 6

DIMENSIONS REQUIRED FOR CONNECTOR MATING
- DATE CODE
- LOGO D' "AMP"
- REFERENCE PRODUIT TYCO ELECTRONICS
- N° EMPREINTE MOULE
- REFERENCE MATIERE
- ZONE LIBRE POUR MONTAGE PORTE CLIP

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T NGUYEN 29-FEB-96	Tyco Electronics France SAS 95300 Pontoise, France	
DIMENSIONS: mm		CHK J LAQUERBE 28-NOV-96	NAME HEADER ASSY, 26 POSN, MQS, RIGHT ANGLE WITH BOARD-LOCK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JJ REVII 28-NOV-96	EMBASE ASSEMBLEE, 26 POSITIONS, MQS, COUDEE AVEC BOARD-LOCK	
0 PLC ± 1 PLC ± 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±5°		PRODUCT SPEC 108-15140	SIZE A200779	
MATERIAL SEE TABLE		APPLICATION SPEC -	CAGE CODE C-185534	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV C	