

Coaxial Power Splitter/Combiner

2 Way-0° 50Ω

2000 to 4200 MHz

ZAPD-4+
ZAPD-4



N-Type version shown

CASE STYLE: F14

Connectors	Model	Price	Qty.
N-TYPE	ZAPD-4-N	\$59.95	(1-9)
SMA	ZAPD-4-S	\$59.95	(1-9)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.125W max.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Features

- wideband, 2000 to 4200 MHz
- low insertion loss, 0.4 dB typ.
- good isolation, 25 dB typ.
- up to 10W power input as splitter
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.5 deg. typ.
- rugged shielded case


Applications

- MMDS
- ISM
- wireless
- communication systems
- instrumentation

Splitter Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.
2000-4200	25	19	0.4	0.8	6	0.4

Outline Drawing






Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
2.00	2.00	.75	1.00	.25	1.500	.125
50.80	50.80	19.05	25.40	6.35	38.10	3.18
H	J	K	L			wt
.39	1.00	.50	1.00			grams
9.91	25.40	12.70	25.40			170.0

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) S-1	Insertion Loss (dB) S-2	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
2000.00	3.29	3.28	0.01	21.06	0.12	1.33	1.10	1.10
2055.00	3.32	3.32	0.00	21.81	0.06	1.32	1.11	1.11
2165.00	3.36	3.36	0.00	23.52	0.02	1.28	1.12	1.12
2275.00	3.28	3.28	0.01	25.26	0.06	1.26	1.12	1.13
2385.00	3.26	3.26	0.01	27.29	0.06	1.25	1.14	1.16
2550.00	3.21	3.22	0.01	30.80	0.03	1.23	1.16	1.19
2715.00	3.26	3.26	0.00	34.52	0.07	1.22	1.15	1.20
2880.00	3.27	3.27	0.01	35.28	0.11	1.24	1.19	1.25
3100.00	3.19	3.19	0.01	31.23	0.05	1.23	1.20	1.27
3320.00	3.30	3.28	0.02	28.17	0.13	1.25	1.22	1.28
3540.00	3.25	3.23	0.02	26.28	0.06	1.20	1.21	1.26
3760.00	3.31	3.28	0.02	25.49	0.06	1.16	1.15	1.20
3980.00	3.27	3.24	0.04	25.51	0.02	1.10	1.13	1.17
4090.00	3.16	3.12	0.03	25.74	0.04	1.09	1.10	1.15
4200.00	3.27	3.24	0.04	25.99	0.02	1.10	1.08	1.13



electrical schematic



Mini-Circuits

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. A
M98898
ZAPD-4
HY/TD/CP/AM
060315